

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832249

Luminaire Tested: S123RDIP-S560D365U950-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832249
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U950-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3500.1 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 29.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66																				
1	102	98	95	92	96	93	90	87	83	80	78	73	71	70	64	63	62	58																				
2	94	87	81	77	89	83	77	73	74	70	66	65	63	60	58	56	54	50																				
3	87	78	71	65	82	74	68	63	66	61	57	59	55	52	52	50	47	44																				
4	80	70	62	57	75	66	60	54	60	54	50	53	49	46	48	45	42	39																				
5	74	63	55	50	70	60	53	48	54	49	44	49	44	41	44	40	37	35																				
6	69	57	50	44	65	55	48	42	50	44	39	45	40	37	40	37	34	31																				
7	64	52	45	39	61	50	43	38	45	40	36	41	37	33	37	34	31	28																				
8	60	48	41	36	57	46	39	34	42	36	32	38	34	30	35	31	28	26																				
9	56	44	37	32	53	43	36	31	39	33	29	36	31	28	32	29	26	24																				
10	53	41	34	30	50	39	33	29	36	31	27	33	29	25	30	27	24	22																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	18755	18755	18755	18755	18755
5°	22269	21558	18872	15257	14164
10°	20176	21898	18779	12223	10486
15°	13892	18775	18580	9990	8295
20°	9664	14455	18207	8424	7291
25°	7365	11017	17664	7487	6720
30°	6411	8809	16986	6953	6224
35°	5886	7430	16023	6501	5773
40°	5370	6635	14765	6058	5361
45°	4850	6068	13408	5638	4947
50°	4402	5598	11807	5228	4438
55°	3982	5142	10269	4827	3808
60°	3567	4676	8919	4383	3599
65°	3293	4149	7679	3940	3403
70°	2675	3585	6700	3563	2766
75°	2346	2853	5673	2957	2437
80°	2126	2411	4649	2479	2300
85°	1939	2112	3532	2248	2112

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 14148 cd/sqm



TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.8	4.5
10°-20°	367.5	10.5
20°-30°	421.6	12.0
30°-40°	415.6	11.9
40°-50°	366.5	10.5
50°-60°	282.0	8.1
60°-70°	185.4	5.3
70°-80°	90.0	2.6
80°-90°	23.6	0.7
90°-100°	27.6	0.8
100°-110°	83.6	2.4
110°-120°	142.3	4.1
120°-130°	187.3	5.4
130°-140°	210.5	6.0
140°-150°	206.9	5.9
150°-160°	174.2	5.0
160°-170°	116.0	3.3
170°-180°	40.6	1.2
0°-30°	947.9	27.1
0°-40°	1363.5	39.0
0°-60°	2012.0	57.5
0°-90°	2311.0	66.0
90°-120°	253.6	7.2
90°-150°	858.3	24.5
90°-180°	1189.0	34.0
0°-180°	3500.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1742	1742	1742	1742	1742	
5°	2061	1995	1747	1412	1311	188
15°	1247	1685	1667	896	744	352
25°	620	928	1487	630	566	293
35°	448	565	1219	495	439	279
45°	319	399	881	370	325	247
55°	212	274	547	257	203	190
65°	129	163	302	155	134	127
75°	56	69	136	71	59	61
85°	16	17	29	18	17	17
90°	10	8	0	8	10	6
95°	26	25	20	25	26	26
105°	80	80	76	80	80	85
115°	144	144	143	144	144	142
125°	207	210	210	210	207	185
135°	272	274	272	274	272	209
145°	330	332	330	332	330	206
155°	377	378	378	378	377	174
165°	410	411	412	411	410	116
175°	426	427	428	427	426	41
180°	429	429	429	429	429	



TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4
2.5°	1930.9	1924.9	1918.8	1917.0	1915.2	1909.5	1903.8	1890.9	1878.1	1864.9	1851.7
5°	2061.0	2061.7	2062.4	2060.6	2058.8	2051.3	2043.8	2028.1	2012.4	1995.2	1978.1
7.5°	2021.0	2032.4	2043.8	2046.0	2048.1	2053.8	2059.5	2056.0	2052.4	2046.0	2039.5
10°	1845.9	1845.2	1844.5	1857.4	1870.2	1908.4	1946.7	1966.3	1986.0	2003.5	2021.0
12.5°	1560.2	1561.3	1562.3	1604.5	1646.6	1682.7	1718.8	1768.8	1818.8	1872.7	1926.7
15°	1246.6	1264.1	1281.6	1319.1	1356.6	1410.9	1465.2	1532.3	1599.5	1684.8	1770.2
17.5°	1023.7	1031.2	1038.7	1074.8	1110.8	1162.3	1213.7	1289.8	1365.9	1475.9	1585.9
20°	843.7	850.5	857.2	883.3	909.4	958.7	1008.0	1080.5	1153.0	1261.9	1370.9
22.5°	704.4	717.6	730.8	748.3	765.8	801.5	837.2	911.2	985.1	1084.4	1183.7
25°	620.1	626.1	632.2	647.2	662.2	696.5	730.8	779.7	828.7	927.6	1026.6
27.5°	562.9	564.7	566.5	577.6	588.6	610.8	632.9	678.3	723.7	805.1	886.5
30°	515.8	519.0	522.2	530.8	539.4	555.4	571.5	603.6	635.8	708.7	781.5
32.5°	479.3	481.1	482.9	490.1	497.2	509.0	520.8	546.1	571.5	627.2	682.9
35°	447.9	448.3	448.6	454.0	459.3	470.8	482.2	503.3	524.3	565.4	606.5
37.5°	412.2	414.7	417.2	421.1	425.1	435.1	445.1	462.2	479.3	513.3	547.2
40°	382.2	384.3	386.5	391.1	395.8	403.6	411.5	427.2	442.9	472.2	501.5
42.5°	352.2	353.6	355.0	359.7	364.3	374.0	383.6	396.1	408.6	432.9	457.2
45°	318.6	322.2	325.8	330.8	335.8	344.0	352.2	365.0	377.9	398.6	419.3
47.5°	290.7	292.5	294.3	298.6	302.9	312.9	322.9	334.3	345.8	365.0	384.3
50°	262.9	263.6	264.3	268.2	272.2	281.1	290.0	303.3	316.5	334.3	352.2
52.5°	236.5	238.2	240.0	244.0	247.9	254.0	260.0	273.6	287.2	304.7	322.2
55°	212.2	213.2	214.3	217.2	220.0	227.2	234.3	246.1	257.9	274.0	290.0
57.5°	189.3	190.7	192.2	194.3	196.5	202.9	209.3	219.7	230.0	246.1	262.2
60°	165.7	167.5	169.3	171.8	174.3	179.3	184.3	193.6	202.9	217.2	231.5
62.5°	148.6	148.9	149.3	151.4	153.6	157.2	160.7	168.2	175.7	190.0	204.3
65°	129.3	130.4	131.4	132.5	133.6	136.4	139.3	145.7	152.2	162.9	173.6
67.5°	109.3	110.4	111.4	113.2	115.0	117.5	120.0	124.3	128.6	138.6	148.6
70°	85.0	85.0	85.0	87.9	90.7	95.0	99.3	102.5	105.7	113.9	122.2
72.5°	69.3	69.7	70.0	70.4	70.7	73.2	75.7	81.1	86.4	91.4	96.4
75°	56.4	56.8	57.1	57.5	57.9	58.6	59.3	61.1	62.9	68.6	74.3
77.5°	45.0	45.4	45.7	46.1	46.4	47.1	47.9	48.6	49.3	51.4	53.6
80°	34.3	34.6	35.0	35.4	35.7	36.1	36.4	37.1	37.9	38.9	40.0
82.5°	25.0	25.0	25.0	25.0	25.0	25.7	26.4	26.4	26.4	27.1	27.9
85°	15.7	15.7	15.7	16.1	16.4	16.4	16.4	16.8	17.1	17.1	17.1
87.5°	7.1	6.8	6.4	6.8	7.1	7.1	7.1	7.5	7.9	7.9	7.9
90°	10.1	10.0	9.8	9.7	9.5	9.3	9.0	8.7	8.4	8.1	7.1
92.5°	14.5	14.6	14.8	14.9	15.1	15.1	14.8	14.6	14.4	14.2	13.7
95°	26.3	26.3	26.3	26.3	26.3	26.1	25.8	25.5	25.2	24.9	24.3
97.5°	37.8	37.8	37.9	38.0	38.1	37.9	37.5	37.2	36.8	36.4	36.0
100°	51.2	51.1	50.9	50.8	50.6	50.5	50.2	50.0	49.8	49.6	49.2
102.5°	65.1	65.1	65.2	65.3	65.4	65.3	65.1	64.8	64.6	64.4	63.9
105°	80.2	80.1	79.9	79.8	79.6	79.6	79.6	79.6	79.6	79.6	78.9
107.5°	95.7	95.8	95.9	96.0	96.0	96.0	95.7	95.5	95.3	95.1	94.8
110°	111.6	111.7	111.9	112.0	112.2	112.1	111.8	111.5	111.2	110.9	110.8



TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	128.4	128.4	128.4	128.4	128.4	128.3	127.9	127.5	127.1	126.8	126.8
115°	143.6	143.7	143.8	143.8	143.9	143.9	143.8	143.8	143.7	143.6	143.8
117.5°	159.1	159.4	159.6	159.8	160.0	160.1	160.1	160.1	160.1	160.1	160.3
120°	175.6	175.8	175.9	176.1	176.2	176.4	176.4	176.5	176.6	176.7	177.0
122.5°	191.5	191.7	191.9	192.2	192.4	192.6	192.8	193.1	193.3	193.5	193.7
125°	207.3	207.6	207.9	208.2	208.5	208.8	209.1	209.4	209.7	210.0	210.2
127.5°	223.2	223.5	223.8	224.1	224.4	224.8	225.2	225.7	226.1	226.6	226.7
130°	238.7	239.2	239.7	240.3	240.8	241.2	241.5	241.8	242.1	242.4	242.6
132.5°	254.9	255.2	255.6	256.0	256.4	256.7	257.1	257.5	257.9	258.2	258.4
135°	271.7	271.9	272.0	272.2	272.3	272.6	272.9	273.2	273.5	273.8	273.8
137.5°	286.6	286.8	287.0	287.2	287.5	287.8	288.1	288.5	288.9	289.3	289.0
140°	301.1	301.6	302.1	302.6	303.2	303.5	303.5	303.6	303.7	303.8	303.7
142.5°	315.9	316.3	316.6	317.0	317.4	317.6	317.7	317.8	317.8	317.9	317.8
145°	330.1	330.4	330.7	331.0	331.3	331.4	331.5	331.6	331.7	331.7	331.5
147.5°	342.9	343.3	343.8	344.2	344.7	344.9	344.9	344.9	344.9	344.9	344.7
150°	355.0	355.5	355.9	356.4	356.8	357.0	357.0	357.0	357.0	357.0	356.9
152.5°	366.8	367.2	367.6	367.9	368.3	368.4	368.3	368.1	368.0	367.8	367.7
155°	377.3	377.8	378.3	378.8	379.4	379.5	379.2	378.9	378.6	378.3	378.2
157.5°	387.0	387.5	387.9	388.4	388.8	388.9	388.6	388.3	388.0	387.7	387.6
160°	396.5	396.8	397.1	397.4	397.7	397.6	397.3	396.9	396.5	396.1	396.1
162.5°	403.6	404.1	404.6	405.1	405.6	405.7	405.3	405.0	404.6	404.2	404.2
165°	410.3	410.8	411.3	411.9	412.4	412.4	412.0	411.5	411.1	410.6	410.6
167.5°	416.4	416.8	417.3	417.7	418.2	418.2	417.7	417.3	416.8	416.4	416.3
170°	420.7	421.3	421.8	422.3	422.8	422.8	422.3	421.8	421.3	420.7	420.7
172.5°	424.1	424.6	425.2	425.7	426.2	426.3	425.8	425.4	424.9	424.5	424.5
175°	426.5	427.0	427.5	428.0	428.6	428.6	428.2	427.7	427.3	426.8	426.8
177.5°	427.8	428.3	428.9	429.4	429.9	430.0	429.5	429.1	428.6	428.2	428.2
180°	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2



TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4
2.5°	1849.9	1848.1	1830.9	1813.8	1797.0	1780.2	1767.7	1755.2	1734.1	1713.1	1699.8
5°	1964.5	1950.9	1923.8	1896.7	1855.9	1815.2	1780.9	1746.6	1703.1	1659.5	1623.1
7.5°	2028.5	2017.4	1984.5	1951.7	1897.7	1843.8	1790.2	1736.6	1672.3	1608.1	1553.0
10°	2030.2	2039.5	2012.4	1985.2	1924.5	1863.8	1790.9	1718.1	1631.6	1545.2	1474.1
12.5°	1966.7	2006.7	2001.0	1995.2	1933.4	1871.7	1783.1	1694.5	1588.4	1482.3	1393.4
15°	1847.7	1925.2	1948.1	1971.0	1919.9	1868.8	1768.1	1667.3	1542.7	1418.0	1315.9
17.5°	1694.5	1803.1	1863.4	1923.8	1886.7	1849.5	1739.1	1628.8	1488.4	1348.0	1236.9
20°	1513.0	1655.2	1749.9	1844.5	1830.9	1817.4	1703.4	1589.5	1438.0	1286.6	1166.2
22.5°	1333.7	1483.8	1614.5	1745.2	1759.1	1773.1	1658.1	1543.0	1377.3	1211.6	1089.1
25°	1179.1	1331.6	1487.3	1643.1	1674.5	1705.9	1596.6	1487.3	1315.5	1143.7	1021.9
27.5°	1031.6	1176.6	1348.0	1519.5	1576.6	1633.8	1533.8	1433.7	1254.8	1075.8	954.4
30°	911.2	1040.8	1215.9	1390.9	1470.5	1550.2	1458.4	1366.6	1189.1	1011.6	892.6
32.5°	799.0	915.1	1090.8	1266.6	1359.1	1451.6	1372.3	1293.0	1122.3	951.5	834.0
35°	710.4	814.4	978.3	1142.3	1245.9	1349.4	1284.4	1219.4	1052.6	885.8	774.7
37.5°	634.4	721.5	875.5	1029.4	1139.4	1249.4	1195.1	1140.9	984.0	827.2	722.2
40°	571.5	641.5	784.7	928.0	1035.8	1143.7	1097.3	1050.8	910.5	770.1	671.9
42.5°	517.6	577.9	706.5	835.1	934.0	1033.0	1002.3	971.5	844.4	717.2	626.1
45°	470.1	520.8	634.0	747.2	838.3	929.4	905.1	880.8	771.2	661.5	577.9
47.5°	427.9	471.5	572.6	673.7	755.4	837.2	814.7	792.2	701.5	610.8	534.7
50°	389.3	426.5	510.8	595.1	668.7	742.2	723.7	705.1	630.1	555.1	489.3
52.5°	352.9	383.6	459.3	535.1	594.4	653.7	639.4	625.1	567.2	509.3	449.7
55°	318.3	346.5	410.4	474.3	525.1	575.8	561.5	547.2	502.2	457.2	404.7
57.5°	286.8	311.5	363.3	415.1	455.4	495.8	489.0	482.2	444.7	407.2	364.0
60°	253.6	275.7	320.4	365.0	397.5	430.1	422.2	414.3	387.5	360.8	323.6
62.5°	224.0	243.6	279.3	315.0	341.5	367.9	362.2	356.5	336.1	315.8	285.0
65°	192.9	212.2	241.1	270.0	290.7	311.5	306.5	301.5	286.1	270.7	246.1
67.5°	164.7	180.7	205.7	230.7	244.7	258.6	255.7	252.9	241.1	229.3	210.0
70°	136.1	150.0	170.7	191.5	201.1	210.7	211.8	212.9	202.2	191.5	177.2
72.5°	107.5	118.6	137.9	157.2	164.7	172.2	171.8	171.4	165.0	158.6	145.7
75°	82.5	90.7	105.7	120.7	127.2	133.6	135.0	136.4	130.4	124.3	117.2
77.5°	59.3	65.0	76.4	87.9	95.0	102.2	102.9	103.6	100.7	97.9	91.1
80°	41.8	43.6	50.7	57.9	65.4	72.9	73.9	75.0	72.2	69.3	65.0
82.5°	28.9	30.0	32.5	35.0	41.1	47.1	48.6	50.0	48.6	47.1	42.5
85°	17.5	17.9	18.9	20.0	22.9	25.7	27.1	28.6	27.9	27.1	24.6
87.5°	7.9	7.9	8.2	8.6	9.3	10.0	11.8	13.6	12.5	11.4	10.4
90°	6.1	5.2	4.2	3.3	2.6	1.8	1.1	0.3	1.1	1.8	2.6
92.5°	13.3	12.8	12.4	11.9	11.5	11.0	10.6	10.1	10.6	11.0	11.5
95°	23.7	23.1	22.6	22.0	21.5	20.9	20.4	19.9	20.4	20.9	21.5
97.5°	35.5	35.1	34.6	34.2	33.8	33.5	33.1	32.7	33.1	33.5	33.8
100°	48.8	48.4	48.1	47.6	47.2	46.7	46.3	45.9	46.3	46.7	47.2
102.5°	63.3	62.8	62.3	61.9	61.7	61.5	61.2	61.0	61.2	61.5	61.7
105°	78.2	77.5	76.9	76.5	76.3	76.2	76.0	75.9	76.0	76.2	76.3
107.5°	94.5	94.2	93.9	93.7	93.6	93.5	93.5	93.4	93.5	93.5	93.6
110°	110.6	110.5	110.3	110.2	110.0	109.9	109.7	109.6	109.7	109.9	110.0



TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	126.8	126.8	126.8	126.7	126.7	126.6	126.5	126.4	126.5	126.6	126.7
115°	143.9	144.1	144.2	144.2	144.0	143.7	143.5	143.3	143.5	143.7	144.0
117.5°	160.4	160.6	160.7	160.8	160.7	160.6	160.6	160.5	160.6	160.6	160.7
120°	177.4	177.8	178.2	178.1	177.7	177.2	176.8	176.3	176.8	177.2	177.7
122.5°	193.8	194.0	194.1	194.0	193.7	193.4	193.1	192.8	193.1	193.4	193.7
125°	210.3	210.5	210.6	210.6	210.4	210.1	209.9	209.7	209.9	210.1	210.4
127.5°	226.9	227.0	227.2	227.0	226.6	226.1	225.7	225.2	225.7	226.1	226.6
130°	242.8	243.1	243.3	243.1	242.5	241.9	241.3	240.7	241.3	241.9	242.5
132.5°	258.5	258.7	258.8	258.6	258.0	257.4	256.8	256.2	256.8	257.4	258.0
135°	273.9	274.0	274.1	273.9	273.4	273.0	272.5	272.1	272.5	273.0	273.4
137.5°	288.8	288.6	288.4	288.1	287.7	287.3	286.9	286.6	286.9	287.3	287.7
140°	303.6	303.5	303.5	303.2	302.9	302.5	302.1	301.7	302.1	302.5	302.9
142.5°	317.6	317.5	317.3	317.1	316.7	316.3	315.9	315.6	315.9	316.3	316.7
145°	331.3	331.1	330.8	330.7	330.5	330.4	330.2	330.1	330.2	330.4	330.5
147.5°	344.4	344.2	344.0	343.7	343.4	343.1	342.8	342.5	342.8	343.1	343.4
150°	356.7	356.6	356.4	356.3	356.1	356.0	355.8	355.7	355.8	356.0	356.1
152.5°	367.7	367.6	367.5	367.4	367.1	366.9	366.7	366.5	366.7	366.9	367.1
155°	378.1	378.0	378.0	377.9	377.9	377.9	377.9	377.9	377.9	377.9	377.9
157.5°	387.6	387.5	387.4	387.4	387.5	387.6	387.6	387.7	387.6	387.6	387.5
160°	396.1	396.1	396.1	396.2	396.4	396.5	396.7	396.8	396.7	396.5	396.4
162.5°	404.1	404.0	403.9	404.0	404.2	404.4	404.7	404.9	404.7	404.4	404.2
165°	410.6	410.6	410.6	410.7	411.0	411.2	411.4	411.6	411.4	411.2	411.0
167.5°	416.2	416.1	416.1	416.2	416.5	416.8	417.1	417.4	417.1	416.8	416.5
170°	420.7	420.7	420.7	420.9	421.2	421.5	421.8	422.1	421.8	421.5	421.2
172.5°	424.5	424.5	424.5	424.6	424.9	425.2	425.5	425.8	425.5	425.2	424.9
175°	426.8	426.8	426.8	427.0	427.3	427.6	427.9	428.2	427.9	427.6	427.3
177.5°	428.2	428.2	428.2	428.3	428.6	428.9	429.2	429.5	429.2	428.9	428.6
180°	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2



TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4	1742.4
2.5°	1686.6	1666.3	1645.9	1631.3	1616.6	1598.4	1580.2	1579.5	1578.8	1565.2	1551.6
5°	1586.6	1551.3	1515.9	1481.2	1446.6	1412.0	1377.3	1369.5	1361.6	1349.8	1338.0
7.5°	1498.0	1441.6	1385.2	1340.9	1296.6	1261.9	1227.3	1203.7	1180.1	1161.9	1143.7
10°	1403.0	1333.0	1263.0	1209.4	1155.9	1118.3	1080.8	1053.7	1026.6	1013.7	1000.8
12.5°	1304.4	1228.4	1152.3	1099.8	1047.3	1002.3	957.3	932.6	908.0	890.1	872.2
15°	1213.7	1131.9	1050.1	994.4	938.7	896.5	854.4	829.7	805.1	787.2	769.4
17.5°	1125.8	1043.3	960.8	904.4	848.0	809.7	771.5	747.6	723.7	712.6	701.5
20°	1045.8	962.6	879.4	826.2	773.0	735.4	697.9	685.1	672.2	661.9	651.5
22.5°	966.5	886.5	806.5	755.4	704.4	677.2	650.1	639.7	629.4	621.5	613.6
25°	900.1	820.5	740.8	696.2	651.5	630.4	609.4	602.6	595.8	587.9	580.1
27.5°	833.0	757.2	681.5	645.8	610.1	592.9	575.8	567.2	558.6	552.2	545.8
30°	773.7	703.7	633.6	604.0	574.4	559.4	544.4	535.1	525.8	519.7	513.6
32.5°	716.5	654.4	592.2	566.9	541.5	526.8	512.2	503.3	494.3	487.2	480.1
35°	663.7	609.7	555.8	532.6	509.3	494.7	480.1	471.1	462.2	455.1	447.9
37.5°	617.2	568.3	519.3	497.6	475.8	462.9	450.1	440.8	431.5	424.0	416.5
40°	573.6	530.4	487.2	466.1	445.1	431.1	417.2	409.0	400.8	394.0	387.2
42.5°	535.1	495.4	455.8	435.1	414.3	401.1	387.9	378.3	368.6	364.7	360.8
45°	494.3	459.3	424.3	404.3	384.3	370.4	356.5	348.3	340.0	336.5	332.9
47.5°	458.6	426.1	393.6	374.0	354.3	341.8	329.3	322.9	316.5	311.5	306.5
50°	423.6	392.2	360.8	341.8	322.9	312.2	301.5	293.6	285.7	282.2	278.6
52.5°	390.0	361.5	332.9	313.6	294.3	284.0	273.6	266.8	260.0	252.5	245.0
55°	352.2	327.2	302.2	285.0	267.9	257.2	246.5	238.6	230.7	222.9	215.0
57.5°	320.8	296.1	271.5	256.1	240.7	230.4	220.0	211.5	202.9	196.5	190.0
60°	286.5	265.0	243.6	228.6	213.6	203.6	193.6	185.4	177.2	173.9	170.7
62.5°	254.3	234.3	214.3	201.1	187.9	178.2	168.6	163.2	157.9	155.7	153.6
65°	221.5	204.3	187.2	175.0	162.9	154.7	146.4	143.9	141.4	139.7	137.9
67.5°	190.7	176.1	161.4	150.7	140.0	134.3	128.6	125.7	122.9	120.7	118.6
70°	162.9	150.0	137.2	127.9	118.6	113.2	107.9	105.4	102.9	98.9	95.0
72.5°	132.9	122.9	112.9	105.7	98.6	93.9	89.3	84.3	79.3	75.7	72.2
75°	110.0	100.0	90.0	83.2	76.4	71.1	65.7	63.9	62.2	61.1	60.0
77.5°	84.3	75.7	67.2	61.8	56.4	53.9	51.4	50.4	49.3	48.9	48.6
80°	60.7	53.6	46.4	43.6	40.7	40.0	39.3	38.6	37.9	37.5	37.1
82.5°	37.9	34.3	30.7	30.0	29.3	28.9	28.6	28.2	27.9	27.5	27.1
85°	22.1	20.7	19.3	18.9	18.6	18.2	17.9	17.9	17.9	17.9	17.9
87.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	8.9	8.6
90°	3.3	4.2	5.2	6.1	7.1	8.1	8.4	8.7	9.0	9.3	9.5
92.5°	11.9	12.4	12.8	13.3	13.7	14.2	14.4	14.6	14.8	15.1	15.1
95°	22.0	22.6	23.1	23.7	24.3	24.9	25.2	25.5	25.8	26.1	26.3
97.5°	34.2	34.6	35.1	35.5	36.0	36.4	36.8	37.2	37.5	37.9	38.1
100°	47.6	48.1	48.4	48.8	49.2	49.6	49.8	50.0	50.2	50.5	50.6
102.5°	61.9	62.3	62.8	63.3	63.9	64.4	64.6	64.8	65.1	65.3	65.4
105°	76.5	76.9	77.5	78.2	78.9	79.6	79.6	79.6	79.6	79.6	79.6
107.5°	93.7	93.9	94.2	94.5	94.8	95.1	95.3	95.5	95.7	96.0	96.0
110°	110.2	110.3	110.5	110.6	110.8	110.9	111.2	111.5	111.8	112.1	112.2



TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	126.7	126.8	126.8	126.8	126.8	126.8	127.1	127.5	127.9	128.3	128.4
115°	144.2	144.2	144.1	143.9	143.8	143.6	143.7	143.8	143.8	143.9	143.9
117.5°	160.8	160.7	160.6	160.4	160.3	160.1	160.1	160.1	160.1	160.1	160.0
120°	178.1	178.2	177.8	177.4	177.0	176.7	176.6	176.5	176.4	176.4	176.2
122.5°	194.0	194.1	194.0	193.8	193.7	193.5	193.3	193.1	192.8	192.6	192.4
125°	210.6	210.6	210.5	210.3	210.2	210.0	209.7	209.4	209.1	208.8	208.5
127.5°	227.0	227.2	227.0	226.9	226.7	226.6	226.1	225.7	225.2	224.8	224.4
130°	243.1	243.3	243.1	242.8	242.6	242.4	242.1	241.8	241.5	241.2	240.8
132.5°	258.6	258.8	258.7	258.5	258.4	258.2	257.9	257.5	257.1	256.7	256.4
135°	273.9	274.1	274.0	273.9	273.8	273.8	273.5	273.2	272.9	272.6	272.3
137.5°	288.1	288.4	288.6	288.8	289.0	289.3	288.9	288.5	288.1	287.8	287.5
140°	303.2	303.5	303.5	303.6	303.7	303.8	303.7	303.6	303.5	303.5	303.2
142.5°	317.1	317.3	317.5	317.6	317.8	317.9	317.8	317.8	317.7	317.6	317.4
145°	330.7	330.8	331.1	331.3	331.5	331.7	331.7	331.6	331.5	331.4	331.3
147.5°	343.7	344.0	344.2	344.4	344.7	344.9	344.9	344.9	344.9	344.9	344.7
150°	356.3	356.4	356.6	356.7	356.9	357.0	357.0	357.0	357.0	357.0	356.8
152.5°	367.4	367.5	367.6	367.7	367.7	367.8	368.0	368.1	368.3	368.4	368.3
155°	377.9	378.0	378.0	378.1	378.2	378.3	378.6	378.9	379.2	379.5	379.4
157.5°	387.4	387.4	387.5	387.6	387.6	387.7	388.0	388.3	388.6	388.9	388.8
160°	396.2	396.1	396.1	396.1	396.1	396.1	396.5	396.9	397.3	397.6	397.7
162.5°	404.0	403.9	404.0	404.1	404.2	404.2	404.6	405.0	405.3	405.7	405.6
165°	410.7	410.6	410.6	410.6	410.6	410.6	411.1	411.5	412.0	412.4	412.4
167.5°	416.2	416.1	416.1	416.2	416.3	416.4	416.8	417.3	417.7	418.2	418.2
170°	420.9	420.7	420.7	420.7	420.7	420.7	421.3	421.8	422.3	422.8	422.8
172.5°	424.6	424.5	424.5	424.5	424.5	424.5	424.9	425.4	425.8	426.3	426.2
175°	427.0	426.8	426.8	426.8	426.8	426.8	427.3	427.7	428.2	428.6	428.6
177.5°	428.3	428.2	428.2	428.2	428.2	428.2	428.6	429.1	429.5	430.0	429.9
180°	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2	429.2



TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1742.4	1742.4	1742.4	1742.4
2.5°	1548.0	1544.5	1543.0	1541.6
5°	1326.9	1315.9	1313.4	1310.9
7.5°	1139.1	1134.4	1119.1	1103.7
10°	986.5	972.3	965.8	959.4
12.5°	859.0	845.8	843.7	841.5
15°	760.1	750.8	747.6	744.4
17.5°	695.1	688.7	684.7	680.8
20°	646.9	642.2	639.4	636.5
22.5°	610.1	606.5	604.4	602.2
25°	574.7	569.4	567.6	565.8
27.5°	541.1	536.5	534.7	532.9
30°	509.7	505.8	503.3	500.8
32.5°	475.4	470.8	469.3	467.9
35°	445.1	442.2	440.8	439.3
37.5°	412.9	409.3	407.2	405.0
40°	385.4	383.6	382.5	381.5
42.5°	357.5	354.3	354.0	353.6
45°	329.7	326.5	325.8	325.0
47.5°	303.6	300.8	300.4	300.0
50°	274.7	270.7	267.9	265.0
52.5°	241.5	237.9	235.4	232.9
55°	211.1	207.2	205.0	202.9
57.5°	188.2	186.5	185.4	184.3
60°	169.7	168.6	167.9	167.2
62.5°	152.5	151.4	151.4	151.4
65°	136.8	135.7	134.7	133.6
67.5°	116.4	114.3	113.9	113.6
70°	91.8	88.6	88.2	87.9
72.5°	71.8	71.4	70.7	70.0
75°	59.3	58.6	58.6	58.6
77.5°	47.9	47.1	47.1	47.1
80°	36.8	36.4	36.8	37.1
82.5°	27.1	27.1	26.8	26.4
85°	17.5	17.1	17.1	17.1
87.5°	8.6	8.6	8.6	8.6
90°	9.7	9.8	10.0	10.1
92.5°	14.9	14.8	14.6	14.5
95°	26.3	26.3	26.3	26.3
97.5°	38.0	37.9	37.8	37.8
100°	50.8	50.9	51.1	51.2
102.5°	65.3	65.2	65.1	65.1
105°	79.8	79.9	80.1	80.2
107.5°	96.0	95.9	95.8	95.7
110°	112.0	111.9	111.7	111.6



TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	128.4	128.4	128.4	128.4
115°	143.8	143.8	143.7	143.6
117.5°	159.8	159.6	159.4	159.1
120°	176.1	175.9	175.8	175.6
122.5°	192.2	191.9	191.7	191.5
125°	208.2	207.9	207.6	207.3
127.5°	224.1	223.8	223.5	223.2
130°	240.3	239.7	239.2	238.7
132.5°	256.0	255.6	255.2	254.9
135°	272.2	272.0	271.9	271.7
137.5°	287.2	287.0	286.8	286.6
140°	302.6	302.1	301.6	301.1
142.5°	317.0	316.6	316.3	315.9
145°	331.0	330.7	330.4	330.1
147.5°	344.2	343.8	343.3	342.9
150°	356.4	355.9	355.5	355.0
152.5°	367.9	367.6	367.2	366.8
155°	378.8	378.3	377.8	377.3
157.5°	388.4	387.9	387.5	387.0
160°	397.4	397.1	396.8	396.5
162.5°	405.1	404.6	404.1	403.6
165°	411.9	411.3	410.8	410.3
167.5°	417.7	417.3	416.8	416.4
170°	422.3	421.8	421.3	420.7
172.5°	425.7	425.2	424.6	424.1
175°	428.0	427.5	427.0	426.5
177.5°	429.4	428.9	428.3	427.8
180°	429.2	429.2	429.2	429.2



TEST NUMBER: P832249

CATALOG NUMBER: S123RDIP-S560D365U950-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.32	13.27	13.14	14.10	15.13	16.99	17.93	17.81	18.77	19.79
	3H	13.55	14.40	14.39	15.24	16.30	18.49	19.34	19.33	20.18	21.24
	4H	13.94	14.74	14.79	15.59	16.65	18.99	19.79	19.84	20.64	21.70
	6H	14.23	14.96	15.09	15.82	16.90	19.31	20.04	20.17	20.90	21.98
	8H	14.32	15.02	15.19	15.89	16.97	19.39	20.09	20.26	20.96	22.04
	12H	14.37	15.04	15.25	15.90	17.01	19.43	20.09	20.30	20.96	22.06
4H	2H	13.06	13.86	13.91	14.71	15.77	17.00	17.79	17.85	18.64	19.71
	3H	14.44	15.10	15.30	15.98	17.07	18.66	19.33	19.53	20.21	21.29
	4H	14.90	15.50	15.77	16.38	17.49	19.28	19.88	20.15	20.76	21.86
	6H	15.27	15.79	16.16	16.69	17.81	19.72	20.24	20.61	21.14	22.25
	8H	15.40	15.88	16.29	16.78	17.91	19.85	20.34	20.75	21.23	22.36
	12H	15.48	15.91	16.39	16.83	17.96	19.92	20.35	20.83	21.27	22.40
8H	4H	15.22	15.70	16.11	16.60	17.73	19.25	19.73	20.14	20.63	21.76
	6H	15.69	16.09	16.61	17.03	18.15	19.75	20.15	20.67	21.09	22.21
	8H	15.88	16.23	16.81	17.17	18.31	19.94	20.29	20.87	21.22	22.36
	12H	16.03	16.34	16.96	17.26	18.45	20.06	20.37	20.99	21.29	22.49
12H	4H	15.24	15.67	16.15	16.59	17.72	19.21	19.64	20.12	20.56	21.69
	6H	15.75	16.10	16.68	17.03	18.17	19.72	20.08	20.66	21.01	22.15
	8H	15.97	16.28	16.90	17.20	18.40	19.92	20.23	20.86	21.16	22.35