

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332578

Luminaire Tested: **S124DIP-S575D1205U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332578
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D1205U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6664.3 lumens
Efficiency: N/A
Efficacy: 134.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332578

CATALOG NUMBER: S124DIP-S575D1205U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332578

CATALOG NUMBER: S124DIP-S575D1205U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	91	87	83	86	82	79	76	67	65	62	53	51	50	39	38	38	31
2	86	79	73	68	78	72	67	62	58	55	52	46	44	41	35	33	32	26
3	79	70	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	22	41	31	24	20	25	21	17	21	17	14	16	13	12	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7840	7840	7840
5°	7864	7769	7826
10°	7814	7706	7744
15°	7720	7596	7616
20°	7594	7460	7467
25°	7451	7306	7285
30°	7276	7124	7058
35°	7094	6933	6841
40°	6905	6716	6593
45°	6707	6503	6379
50°	6489	6314	6118
55°	6253	6068	5871
60°	6018	5792	5616
65°	5752	5530	5307
70°	5455	5179	4978
75°	5000	4757	4635
80°	4449	4268	4161
85°	3890	3751	3677



TEST NUMBER: P332578

CATALOG NUMBER: S124DIP-S575D1205U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.4
10°-20°	257.7	3.9
20°-30°	379.3	5.7
30°-40°	440.9	6.6
40°-50°	440.9	6.6
50°-60°	385.7	5.8
60°-70°	286.4	4.3
70°-80°	162.7	2.4
80°-90°	51.5	0.8
90°-100°	99.1	1.5
100°-110°	293.5	4.4
110°-120°	498.2	7.5
120°-130°	656.9	9.9
130°-140°	737.7	11.1
140°-150°	724.9	10.9
150°-160°	609.7	9.1
160°-170°	405.7	6.1
170°-180°	142.1	2.1
0°-30°	728.4	10.9
0°-40°	1169.3	17.5
0°-60°	1996.0	29.9
0°-90°	2496.6	37.5
90°-120°	890.8	13.4
90°-150°	3010.3	45.2
90°-180°	4168.0	62.5
0°-180°	6664.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	920	909	913	911	260
25°	836	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	150	149	170
85°	42	42	40	40	40	46
90°	4	16	26	32	35	7
95°	70	80	88	92	92	78
105°	271	272	276	280	284	287
115°	506	506	504	503	502	499
125°	738	738	737	734	732	657
135°	952	958	958	956	953	736
145°	1156	1160	1162	1160	1157	723
155°	1324	1324	1323	1327	1323	609
165°	1442	1438	1436	1442	1438	406
175°	1500	1494	1493	1500	1493	142
180°	1502	1502	1502	1502	1502	



TEST NUMBER: P332578

CATALOG NUMBER: S124DIP-S575D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	973.6	973.2	972.8	972.4	972.0	971.0	969.5	968.0	966.4	964.9	966.3
5°	970.4	969.7	969.0	968.3	967.6	966.3	964.4	962.5	960.6	958.7	960.6
7.5°	961.3	960.6	960.0	959.3	958.6	957.2	955.1	953.0	950.8	948.7	950.3
10°	953.2	952.6	951.9	951.2	950.5	949.0	946.8	944.5	942.3	940.0	941.4
12.5°	942.7	942.0	941.3	940.6	939.9	938.4	936.0	933.6	931.2	928.8	930.3
15°	923.7	923.0	922.3	921.6	920.9	919.3	916.7	914.1	911.5	908.9	909.9
17.5°	900.8	899.9	899.1	898.2	897.3	895.7	893.2	890.8	888.3	885.9	886.5
20°	884.0	883.1	882.3	881.4	880.5	878.8	876.2	873.6	871.0	868.4	868.9
22.5°	865.9	864.8	863.7	862.5	861.4	859.5	856.9	854.3	851.7	849.1	850.1
25°	836.5	835.3	834.1	832.9	831.7	829.9	827.4	825.0	822.6	820.2	820.4
27.5°	802.9	801.7	800.4	799.2	797.9	796.2	793.9	791.7	789.4	787.2	786.8
30°	780.5	779.1	777.7	776.3	775.0	773.1	770.9	768.6	766.4	764.2	763.5
32.5°	756.8	755.6	754.3	753.1	751.9	750.0	747.7	745.3	742.9	740.5	739.7
35°	719.8	718.6	717.4	716.2	715.0	713.1	710.7	708.3	705.9	703.5	702.2
37.5°	680.7	679.6	678.5	677.4	676.3	674.5	671.9	669.3	666.7	664.1	662.8
40°	655.2	653.8	652.4	651.1	649.7	647.7	645.1	642.5	639.9	637.3	635.6
42.5°	627.8	627.0	626.2	625.3	624.5	622.6	619.8	616.9	614.0	611.2	609.2
45°	587.5	586.3	585.1	583.9	582.7	580.7	577.9	575.1	572.4	569.6	567.7
47.5°	545.3	544.5	543.7	542.8	542.0	540.3	537.8	535.2	532.6	530.1	527.9
50°	516.7	516.0	515.3	514.6	513.9	512.4	510.0	507.5	505.1	502.7	500.3
52.5°	488.7	487.9	487.0	486.2	485.4	483.7	481.1	478.6	476.0	473.4	471.3
55°	444.3	443.8	443.3	442.8	442.3	440.8	438.4	435.9	433.5	431.1	429.0
57.5°	402.0	401.4	400.8	400.2	399.6	398.2	395.8	393.4	391.0	388.6	386.6
60°	372.7	371.9	371.0	370.1	369.3	367.7	365.5	363.2	361.0	358.7	357.2
62.5°	344.1	343.4	342.6	341.9	341.2	339.6	337.3	334.9	332.5	330.1	328.7
65°	301.1	300.3	299.4	298.6	297.7	296.4	294.7	292.9	291.2	289.5	287.7
67.5°	257.9	257.1	256.3	255.5	254.7	253.5	251.8	250.2	248.5	246.8	245.2
70°	231.1	229.9	228.7	227.5	226.3	225.0	223.6	222.2	220.8	219.4	218.1
72.5°	202.5	201.3	200.1	198.8	197.6	196.5	195.4	194.3	193.2	192.0	190.9
75°	160.3	159.4	158.6	157.7	156.8	156.0	155.1	154.2	153.4	152.5	151.8
77.5°	120.0	119.6	119.2	118.9	118.5	117.9	117.1	116.4	115.6	114.9	114.6
80°	95.7	95.2	94.7	94.2	93.6	93.2	92.9	92.5	92.2	91.8	91.5
82.5°	72.1	71.8	71.6	71.3	71.1	70.9	70.9	70.8	70.7	70.7	70.4
85°	42.0	42.0	42.0	42.0	42.0	41.8	41.5	41.2	40.8	40.5	40.5
87.5°	16.9	17.3	17.7	18.2	18.6	19.0	19.2	19.5	19.8	20.1	20.4
90°	3.5	6.3	9.2	12.0	14.8	17.3	19.4	21.4	23.5	25.6	27.1
92.5°	24.9	28.1	31.4	34.6	37.9	40.2	41.7	43.1	44.6	46.0	46.9
95°	69.7	72.0	74.4	76.7	79.0	81.1	82.9	84.7	86.5	88.3	89.1
97.5°	121.8	123.6	125.5	127.3	129.2	131.2	133.3	135.4	137.5	139.6	140.6
100°	162.7	163.7	164.7	165.7	166.8	168.5	170.8	173.1	175.4	177.8	178.3
102.5°	205.4	205.8	206.2	206.6	207.1	208.3	210.4	212.6	214.7	216.8	217.5
105°	270.7	271.0	271.2	271.5	271.7	272.4	273.4	274.4	275.5	276.5	277.3
107.5°	339.2	339.6	339.9	340.2	340.5	340.7	340.9	341.0	341.2	341.3	342.1
110°	385.7	386.2	386.7	387.3	387.8	387.9	387.7	387.4	387.1	386.9	386.4



TEST NUMBER: P332578

CATALOG NUMBER: S124DIP-S575D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.0	434.2	434.3	434.4	434.5	434.3	433.8	433.4	432.9	432.4	432.3
115°	506.5	506.5	506.5	506.5	506.5	506.3	505.8	505.3	504.7	504.2	504.0
117.5°	574.9	575.1	575.3	575.5	575.7	575.6	575.2	574.9	574.5	574.2	573.3
120°	620.4	621.4	622.5	623.5	624.5	624.7	623.9	623.1	622.3	621.6	620.3
122.5°	667.8	668.2	668.6	669.0	669.5	669.5	669.1	668.8	668.4	668.0	667.2
125°	737.7	737.7	737.7	737.7	737.7	737.6	737.4	737.1	736.8	736.6	736.1
127.5°	801.2	802.0	802.7	803.5	804.3	804.5	804.0	803.6	803.2	802.8	802.3
130°	845.8	846.6	847.3	848.1	848.9	849.3	849.3	849.3	849.3	849.3	848.8
132.5°	891.3	891.9	892.5	893.0	893.6	893.8	893.6	893.4	893.2	893.0	892.4
135°	951.5	953.1	954.6	956.2	957.7	958.5	958.5	958.5	958.5	958.5	958.0
137.5°	1017.0	1017.8	1018.5	1019.2	1019.9	1020.5	1020.9	1021.3	1021.7	1022.1	1021.5
140°	1060.7	1061.2	1061.8	1062.3	1062.8	1063.0	1063.0	1063.0	1063.0	1063.0	1062.8
142.5°	1100.7	1101.2	1101.7	1102.2	1102.8	1102.9	1102.7	1102.5	1102.3	1102.1	1102.0
145°	1156.0	1157.0	1158.1	1159.1	1160.1	1160.8	1161.0	1161.3	1161.5	1161.8	1161.5
147.5°	1210.8	1212.1	1213.3	1214.5	1215.8	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3
150°	1244.3	1245.3	1246.4	1247.4	1248.4	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9
152.5°	1275.9	1276.5	1277.1	1277.7	1278.4	1278.8	1279.0	1279.2	1279.4	1279.6	1280.2
155°	1324.4	1324.4	1324.4	1324.4	1324.4	1324.3	1324.1	1323.8	1323.5	1323.3	1324.3
157.5°	1365.3	1364.9	1364.4	1364.0	1363.5	1363.2	1363.2	1363.1	1363.1	1363.0	1363.8
160°	1389.5	1389.3	1389.0	1388.7	1388.5	1388.2	1388.0	1387.7	1387.4	1387.2	1388.0
162.5°	1411.8	1411.1	1410.5	1409.8	1409.1	1408.7	1408.4	1408.2	1407.9	1407.6	1409.0
165°	1441.8	1441.0	1440.2	1439.5	1438.7	1438.0	1437.5	1437.0	1436.5	1436.0	1437.5
167.5°	1464.8	1463.7	1462.6	1461.5	1460.5	1459.9	1460.0	1460.0	1460.1	1460.1	1461.7
170°	1477.8	1476.5	1475.2	1473.9	1472.6	1472.1	1472.4	1472.6	1472.9	1473.2	1474.7
172.5°	1487.1	1486.0	1484.9	1483.8	1482.8	1482.2	1482.3	1482.4	1482.4	1482.5	1484.2
175°	1499.9	1498.6	1497.3	1496.0	1494.7	1493.9	1493.7	1493.4	1493.2	1492.9	1494.7
177.5°	1504.1	1503.0	1502.0	1501.0	1499.9	1499.4	1499.4	1499.4	1499.4	1499.4	1500.9
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332578

CATALOG NUMBER: S124DIP-S575D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	967.7	969.1	970.5	971.1	970.9	970.8	970.7	970.5
5°	962.5	964.4	966.3	967.1	966.7	966.4	966.0	965.7
7.5°	951.8	953.3	954.8	955.5	955.3	955.1	954.9	954.6
10°	942.8	944.2	945.6	946.1	945.7	945.4	945.0	944.7
12.5°	931.9	933.4	934.9	935.4	934.9	934.4	934.0	933.5
15°	911.0	912.0	913.0	913.3	912.8	912.3	911.7	911.2
17.5°	887.2	887.8	888.5	888.6	888.3	887.9	887.6	887.3
20°	869.5	870.0	870.5	870.6	870.2	869.9	869.6	869.2
22.5°	851.0	851.9	852.9	853.0	852.4	851.8	851.2	850.5
25°	820.5	820.7	820.9	820.6	819.9	819.2	818.5	817.8
27.5°	786.4	785.9	785.5	784.9	784.0	783.2	782.3	781.4
30°	762.8	762.1	761.4	760.6	759.7	758.9	758.0	757.1
32.5°	738.8	738.0	737.2	736.3	735.5	734.6	733.7	732.9
35°	701.0	699.8	698.6	697.6	696.7	695.8	695.0	694.1
37.5°	661.5	660.1	658.8	657.6	656.5	655.3	654.2	653.0
40°	633.9	632.1	630.4	629.1	628.2	627.4	626.5	625.6
42.5°	607.2	605.1	603.1	601.8	601.3	600.7	600.1	599.5
45°	565.8	563.9	562.0	560.8	560.3	559.8	559.2	558.7
47.5°	525.8	523.6	521.5	519.8	518.5	517.1	515.8	514.5
50°	497.8	495.4	493.0	491.3	490.2	489.2	488.2	487.1
52.5°	469.1	467.0	464.9	463.1	461.8	460.5	459.2	457.9
55°	427.0	424.9	422.8	421.2	420.2	419.2	418.1	417.1
57.5°	384.7	382.7	380.7	379.2	378.2	377.2	376.2	375.2
60°	355.6	354.1	352.5	351.3	350.4	349.6	348.7	347.8
62.5°	327.3	325.8	324.4	323.3	322.4	321.6	320.7	319.8
65°	286.0	284.3	282.6	281.3	280.4	279.5	278.7	277.8
67.5°	243.5	241.9	240.2	239.2	239.0	238.8	238.5	238.3
70°	216.7	215.3	213.9	213.0	212.4	211.9	211.4	210.9
72.5°	189.8	188.7	187.6	186.8	186.3	185.8	185.3	184.7
75°	151.1	150.4	149.8	149.3	149.1	149.0	148.8	148.6
77.5°	114.4	114.2	114.0	113.7	113.2	112.8	112.3	111.9
80°	91.1	90.8	90.4	90.2	90.0	89.8	89.7	89.5
82.5°	70.2	70.0	69.8	69.6	69.5	69.3	69.1	68.9
85°	40.5	40.5	40.5	40.4	40.2	40.0	39.9	39.7
87.5°	20.7	21.0	21.3	21.5	21.6	21.7	21.8	21.9
90°	28.7	30.2	31.8	32.8	33.3	33.8	34.3	34.9
92.5°	47.9	48.8	49.7	50.3	50.7	51.0	51.3	51.6
95°	89.8	90.6	91.4	91.8	91.8	91.8	91.8	91.8
97.5°	141.5	142.4	143.4	143.8	143.8	143.8	143.8	143.8
100°	178.8	179.3	179.8	180.1	180.1	180.1	180.1	180.1
102.5°	218.2	219.0	219.7	220.1	220.4	220.6	220.8	221.0
105°	278.1	278.8	279.6	280.4	281.2	281.9	282.7	283.5
107.5°	342.8	343.5	344.2	344.6	344.5	344.5	344.4	344.4
110°	385.8	385.3	384.8	384.9	385.7	386.5	387.3	388.0



TEST NUMBER: P332578

CATALOG NUMBER: S124DIP-S575D1205U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.2	432.1	432.0	432.0	432.2	432.3	432.5	432.7
115°	503.7	503.4	503.2	502.9	502.7	502.4	502.2	501.9
117.5°	572.4	571.5	570.6	570.0	569.4	568.9	568.4	567.9
120°	619.0	617.7	616.4	616.0	616.5	617.0	617.6	618.1
122.5°	666.3	665.4	664.5	663.6	662.7	661.8	660.8	659.9
125°	735.5	735.0	734.5	734.0	733.5	733.0	732.4	731.9
127.5°	801.8	801.3	800.7	800.3	799.9	799.4	799.0	798.6
130°	848.2	847.7	847.2	846.4	845.4	844.4	843.3	842.3
132.5°	891.9	891.4	890.9	890.4	890.0	889.6	889.2	888.8
135°	957.5	956.9	956.4	955.8	955.0	954.2	953.4	952.7
137.5°	1020.8	1020.1	1019.5	1019.2	1019.4	1019.5	1019.7	1019.8
140°	1062.5	1062.3	1062.0	1061.8	1061.5	1061.2	1061.0	1060.7
142.5°	1102.0	1101.9	1101.9	1101.8	1101.8	1101.7	1101.7	1101.6
145°	1161.3	1161.0	1160.8	1160.2	1159.5	1158.7	1157.9	1157.2
147.5°	1215.1	1214.9	1214.6	1214.4	1214.2	1213.9	1213.6	1213.4
150°	1248.9	1248.9	1248.9	1248.8	1248.5	1248.3	1248.0	1247.8
152.5°	1280.8	1281.5	1282.1	1282.1	1281.4	1280.7	1280.0	1279.4
155°	1325.4	1326.4	1327.4	1327.4	1326.4	1325.4	1324.3	1323.3
157.5°	1364.6	1365.3	1366.1	1366.1	1365.2	1364.3	1363.4	1362.6
160°	1388.7	1389.5	1390.3	1390.0	1388.7	1387.4	1386.2	1384.9
162.5°	1410.4	1411.8	1413.2	1413.3	1412.0	1410.7	1409.4	1408.1
165°	1439.1	1440.6	1442.2	1442.4	1441.4	1440.4	1439.3	1438.3
167.5°	1463.2	1464.8	1466.3	1466.3	1464.7	1463.1	1461.5	1459.9
170°	1476.3	1477.8	1479.4	1479.2	1477.4	1475.6	1473.8	1472.0
172.5°	1486.0	1487.7	1489.5	1489.5	1487.6	1485.8	1484.0	1482.2
175°	1496.5	1498.3	1500.1	1500.1	1498.3	1496.5	1494.7	1492.9
177.5°	1502.3	1503.8	1505.2	1505.1	1503.4	1501.8	1500.1	1498.5
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2

(END OF REPORT)