

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831743

Luminaire Tested: S123DP-S340D930-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831743
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, -)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DP-S340D930-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1286.8 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831743
CATALOG NUMBER: S123DP-S340D930-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831743

CATALOG NUMBER: S123DP-S340D930-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86				86
2	101	94	88	82	99	92	86	81	88	84	80	85	81	78	82	79	76	74				74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64				64
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	54	78	67	59	54	65	58	53	63	57	52	61	56	52	50				50
6	74	62	54	48	73	61	53	48	60	53	47	58	52	47	56	51	47	45				45
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40				40
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34				34
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33	31				31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	8617	8617	8617	8617	8617
5°	10897	10284	8694	7006	6438
10°	11002	11335	8636	5584	4880
15°	8286	10524	8576	4729	4126
20°	5774	8517	8467	4136	3748
25°	4403	6549	8280	3805	3515
30°	3808	5203	7982	3571	3329
35°	3533	4393	7638	3402	3197
40°	3346	3940	7156	3242	3153
45°	3235	3647	6543	3116	3133
50°	3178	3414	5816	3001	3116
55°	3061	3245	5103	2894	3130
60°	2951	3063	4398	2790	3078
65°	2771	2891	3795	2682	3018
70°	2559	2672	3226	2502	2842
75°	2316	2396	2766	2325	2595
80°	1909	2095	2188	2027	2188
85°	1519	1692	1606	1717	1741

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 7470 cd/sqm

TEST NUMBER: P831743

CATALOG NUMBER: S123DP-S340D930-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.7	5.9
10°-20°	188.3	14.6
20°-30°	222.9	17.3
30°-40°	224.1	17.4
40°-50°	205.6	16.0
50°-60°	169.7	13.2
60°-70°	120.1	9.3
70°-80°	64.1	5.0
80°-90°	16.3	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	486.9	37.8
0°-40°	711.0	55.3
0°-60°	1086.4	84.4
0°-90°	1286.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1286.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	800	800	800	800	800	
5°	1008	952	805	648	596	96
15°	744	944	770	424	370	205
25°	371	551	697	320	296	175
35°	269	334	581	259	243	169
45°	212	240	430	205	206	165
55°	163	173	272	154	167	146
65°	109	114	149	105	118	108
75°	56	58	66	56	62	59
85°	12	14	13	14	14	14
90°	0	0	0	0	0	



TEST NUMBER: P831743

CATALOG NUMBER: S123DP-S340D930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5
2.5°	902.3	901.3	900.4	895.8	891.1	888.9	886.7	880.0	873.3	865.9	858.4
5°	1008.5	1011.1	1013.7	1010.7	1007.8	998.7	989.5	977.5	965.4	951.8	938.3
7.5°	1057.5	1059.0	1060.5	1058.6	1056.8	1054.4	1052.0	1041.2	1030.4	1016.5	1002.6
10°	1006.6	1010.0	1013.3	1020.6	1027.8	1036.0	1044.2	1042.7	1041.2	1037.1	1033.0
12.5°	894.8	898.9	903.0	917.5	932.0	950.5	969.1	985.1	1001.1	1012.2	1023.4
15°	743.6	755.0	766.3	779.5	792.7	820.0	847.3	880.9	914.5	944.4	974.3
17.5°	612.5	616.8	621.1	635.2	649.3	683.7	718.0	756.8	795.7	845.2	894.8
20°	504.1	508.0	511.9	530.4	549.0	575.9	602.9	646.5	690.2	743.5	796.8
22.5°	423.5	429.6	435.7	446.1	456.5	482.3	508.1	547.0	585.8	644.7	703.5
25°	370.7	375.2	379.6	385.9	392.3	412.9	433.5	465.4	497.4	551.4	605.5
27.5°	334.7	336.5	338.4	344.7	351.0	364.4	377.8	405.3	432.7	478.6	524.5
30°	306.4	307.7	309.0	314.6	320.2	329.3	338.4	358.3	378.1	418.6	459.1
32.5°	286.8	287.7	288.6	292.9	297.2	303.7	310.2	324.6	339.1	372.6	406.0
35°	268.9	269.5	270.0	273.2	276.4	281.2	286.0	297.0	307.9	334.3	360.7
37.5°	253.3	254.1	254.8	256.7	258.5	262.8	267.1	275.8	284.5	304.8	325.0
40°	238.1	239.4	240.7	242.0	243.3	246.8	250.4	257.0	263.7	280.4	297.2
42.5°	225.1	226.4	227.7	228.3	228.8	230.9	232.9	239.0	245.2	257.6	270.0
45°	212.5	213.0	213.6	214.1	214.7	216.4	218.0	223.4	228.8	239.6	250.4
47.5°	201.0	201.0	201.0	201.3	201.7	203.2	204.7	208.6	212.5	220.8	229.2
50°	189.8	189.8	189.8	189.3	188.7	189.6	190.6	193.5	196.5	203.9	211.4
52.5°	176.4	176.4	176.4	176.6	176.8	176.8	176.8	179.4	182.0	188.7	195.4
55°	163.1	163.8	164.6	164.0	163.4	163.8	164.2	165.9	167.5	172.9	178.3
57.5°	149.7	150.1	150.4	150.3	150.1	150.3	150.4	151.9	153.4	157.5	161.6
60°	137.1	137.1	137.1	136.7	136.3	136.7	137.1	137.8	138.6	142.3	146.0
62.5°	123.0	123.1	123.3	123.5	123.7	123.3	123.0	123.9	124.8	127.6	130.4
65°	108.8	109.0	109.2	109.8	110.3	109.9	109.6	110.5	111.4	113.5	115.5
67.5°	96.2	95.8	95.5	95.6	95.8	96.4	96.9	97.1	97.3	99.5	101.8
70°	81.3	81.7	82.1	81.9	81.7	81.9	82.1	82.6	83.2	84.9	86.5
72.5°	68.0	68.2	68.3	68.3	68.3	68.7	69.1	69.6	70.2	71.1	72.1
75°	55.7	55.7	55.7	56.1	56.5	56.6	56.8	56.8	56.8	57.6	58.3
77.5°	42.3	43.3	44.2	44.0	43.8	44.2	44.6	45.1	45.7	46.1	46.4
80°	30.8	30.8	30.8	31.0	31.2	31.8	32.3	32.7	33.1	33.8	34.5
82.5°	19.7	19.9	20.1	20.6	21.2	21.5	21.9	22.5	23.0	23.0	23.0
85°	12.3	11.9	11.5	11.9	12.3	12.6	13.0	13.2	13.4	13.7	14.1
87.5°	5.9	5.9	5.9	5.9	5.9	6.1	6.3	6.3	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P831743

CATALOG NUMBER: S123DP-S340D930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5
2.5°	856.2	854.0	845.8	837.6	828.3	819.1	812.2	805.3	795.1	784.9	776.5
5°	927.9	917.5	900.2	882.9	859.5	836.1	820.4	804.6	783.4	762.2	745.3
7.5°	984.7	966.9	942.7	918.6	888.0	857.3	828.3	799.4	767.0	734.7	708.4
10°	1020.9	1008.9	981.0	953.1	912.1	871.1	830.6	790.1	748.5	706.9	672.0
12.5°	1024.5	1025.6	1000.0	974.3	927.9	881.5	832.2	783.0	730.6	678.3	637.6
15°	993.4	1012.6	998.5	984.3	937.5	890.7	830.2	769.6	709.3	648.9	601.9
17.5°	935.9	976.9	979.0	981.0	934.2	887.4	820.4	753.3	685.0	616.6	567.2
20°	857.3	917.9	938.7	959.5	921.4	883.3	811.3	739.2	662.7	586.2	534.3
22.5°	777.1	850.6	888.7	926.8	898.5	870.3	793.6	716.9	636.1	555.3	502.8
25°	685.7	765.9	824.4	882.9	865.7	848.4	772.8	697.2	611.2	525.2	471.6
27.5°	606.0	687.6	758.1	828.7	825.0	821.3	746.2	671.2	583.2	495.1	443.3
30°	535.1	611.0	690.0	768.9	778.0	787.1	714.7	642.2	554.0	465.8	415.8
32.5°	472.3	538.6	623.3	708.0	725.8	743.6	678.3	612.9	525.6	438.3	390.2
35°	420.9	481.0	565.7	650.4	672.7	695.0	638.2	581.3	496.3	411.2	365.3
37.5°	375.4	425.7	508.3	591.0	618.3	645.6	594.7	543.8	464.1	384.5	342.3
40°	337.7	378.1	454.1	530.1	561.6	593.2	551.2	509.3	433.7	358.1	319.3
42.5°	306.1	342.1	411.0	479.9	510.2	540.5	505.0	469.5	402.3	335.1	299.6
45°	279.1	307.9	370.5	433.1	461.9	490.7	460.2	429.8	370.5	311.3	278.2
47.5°	253.9	278.6	332.1	385.6	411.2	436.8	413.1	389.3	339.1	289.0	259.1
50°	231.2	251.1	297.9	344.7	367.0	389.3	368.3	347.3	306.1	264.8	238.8
52.5°	211.5	227.7	266.9	306.1	325.2	344.3	326.3	308.3	275.6	242.9	220.3
55°	192.0	205.8	239.8	273.8	286.8	299.8	285.8	271.9	245.5	219.2	200.0
57.5°	173.8	186.1	214.0	241.8	251.8	261.9	249.2	236.6	216.7	196.9	180.9
60°	156.0	166.0	189.3	212.5	218.6	224.7	214.5	204.3	190.4	176.4	162.1
62.5°	139.5	148.6	165.9	183.1	187.2	191.3	183.5	175.7	165.1	154.5	143.4
65°	122.4	129.3	143.4	157.5	160.1	162.7	155.8	149.0	141.0	133.0	124.8
67.5°	106.6	111.4	123.0	134.5	134.7	134.8	129.3	123.7	119.2	114.8	108.3
70°	91.2	95.8	103.4	111.1	111.3	111.4	107.0	102.5	99.2	95.8	91.0
72.5°	75.4	78.7	84.5	90.3	89.9	89.5	86.7	83.9	81.3	78.7	75.2
75°	61.1	63.9	67.8	71.7	70.6	69.5	68.0	66.5	64.3	62.0	59.8
77.5°	48.1	49.8	52.0	54.2	53.5	52.7	51.4	50.1	48.5	46.8	45.9
80°	35.3	36.0	37.5	39.0	38.6	38.3	36.8	35.3	34.9	34.5	33.2
82.5°	24.0	24.9	25.3	25.6	25.4	25.3	24.1	23.0	22.7	22.3	22.1
85°	14.3	14.5	14.7	14.9	14.3	13.7	13.4	13.0	13.0	13.0	12.8
87.5°	6.5	6.7	6.7	6.7	6.5	6.3	5.9	5.6	5.8	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P831743

CATALOG NUMBER: S123DP-S340D930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5
2.5°	768.2	760.9	753.7	748.1	742.5	733.1	723.6	721.4	719.1	716.0	712.8
5°	728.4	710.6	692.8	676.8	660.8	648.4	635.9	627.8	619.6	613.6	607.7
7.5°	682.0	655.2	628.5	609.6	590.6	572.6	554.6	548.8	543.1	535.3	527.5
10°	637.0	607.5	578.0	553.3	528.6	510.9	493.3	486.2	479.2	469.3	459.5
12.5°	596.9	564.6	532.3	507.4	482.5	465.4	448.3	438.1	427.9	422.3	416.8
15°	555.0	520.4	485.9	462.8	439.8	424.4	409.0	400.1	391.1	385.8	380.4
17.5°	517.8	483.6	449.5	427.4	405.3	391.1	377.0	369.2	361.4	357.3	353.3
20°	482.5	449.1	415.7	394.1	372.6	361.1	349.5	344.5	339.5	336.2	332.8
22.5°	450.2	417.3	384.5	366.1	347.7	338.4	329.1	325.6	322.0	319.3	316.5
25°	417.9	388.5	359.2	343.6	328.0	320.4	312.8	309.2	305.7	302.9	300.1
27.5°	391.5	363.5	335.4	322.0	308.7	302.7	296.8	294.0	291.2	288.6	286.0
30°	365.9	340.8	315.7	304.2	292.7	287.3	281.9	279.1	276.4	273.9	271.5
32.5°	342.1	320.6	299.0	288.4	277.8	273.4	268.9	265.6	262.2	260.4	258.5
35°	319.4	300.1	280.8	272.1	263.4	258.9	254.4	251.7	248.9	247.4	245.9
37.5°	300.1	282.9	265.6	257.2	248.9	244.6	240.3	237.9	235.5	234.9	234.4
40°	280.4	265.6	250.7	242.6	234.4	230.7	227.0	225.5	224.0	223.6	223.2
42.5°	264.1	249.6	235.1	227.7	220.3	217.1	214.0	213.2	212.5	213.0	213.6
45°	245.2	233.1	221.0	214.1	207.3	204.7	202.1	201.5	201.0	202.1	203.2
47.5°	229.2	218.0	206.9	200.4	193.9	192.0	190.2	190.0	189.8	191.3	192.8
50°	212.8	202.1	191.3	186.1	180.9	179.2	177.6	178.1	178.7	181.1	183.5
52.5°	197.6	187.6	177.6	172.7	167.9	166.8	165.7	167.0	168.3	170.9	173.5
55°	180.9	171.8	162.7	159.0	155.3	154.2	153.0	155.6	158.2	160.7	163.1
57.5°	164.9	156.9	149.0	145.6	142.3	142.1	141.9	144.3	146.7	149.3	151.9
60°	147.8	141.2	134.5	131.9	129.3	129.6	130.0	132.8	135.6	137.6	139.7
62.5°	132.2	126.7	121.1	118.7	116.3	117.2	118.1	120.9	123.7	126.1	128.5
65°	116.6	112.0	107.3	105.7	104.0	105.3	106.6	109.0	111.4	113.1	114.8
67.5°	101.8	97.9	94.0	92.7	91.4	92.7	94.0	96.4	98.8	100.5	102.1
70°	86.2	83.0	79.9	78.9	78.0	79.5	81.0	83.0	85.1	86.7	88.4
72.5°	71.7	69.3	66.9	66.7	66.5	67.8	69.1	71.1	73.2	74.3	75.4
75°	57.6	56.3	55.0	54.8	54.6	55.9	57.2	58.3	59.4	60.4	61.3
77.5°	44.9	43.8	42.7	42.9	43.1	44.0	44.9	46.1	47.2	47.7	48.3
80°	31.9	31.6	31.2	31.6	31.9	32.7	33.4	34.2	34.9	35.3	35.7
82.5°	21.9	21.5	21.2	21.7	22.3	22.8	23.4	24.0	24.5	24.7	24.9
85°	12.6	13.2	13.7	13.7	13.7	13.9	14.1	14.3	14.5	14.3	14.1
87.5°	5.9	6.1	6.3	6.3	6.3	6.5	6.7	6.7	6.7	6.5	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P831743

CATALOG NUMBER: S123DP-S340D930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	800.5	800.5	800.5	800.5
2.5°	711.5	710.2	705.0	699.8
5°	603.2	598.8	597.3	595.8
7.5°	527.1	526.7	518.9	511.1
10°	460.0	460.6	453.5	446.5
12.5°	412.1	407.5	406.9	406.4
15°	376.1	371.8	371.1	370.3
17.5°	350.7	348.1	347.3	346.6
20°	331.3	329.8	328.5	327.2
22.5°	314.6	312.8	311.6	310.5
25°	298.5	296.8	296.4	296.0
27.5°	284.0	281.9	281.9	281.9
30°	270.2	268.9	268.4	267.8
32.5°	257.4	256.3	256.3	256.3
35°	245.3	244.8	244.0	243.3
37.5°	234.4	234.4	234.0	233.6
40°	223.8	224.4	224.4	224.4
42.5°	214.1	214.7	214.7	214.7
45°	204.1	205.0	205.4	205.8
47.5°	194.3	195.8	196.1	196.5
50°	184.6	185.7	185.9	186.1
52.5°	174.8	176.1	177.0	177.9
55°	164.4	165.7	166.2	166.8
57.5°	153.2	154.5	154.7	154.9
60°	141.0	142.3	142.6	143.0
62.5°	129.3	130.0	130.4	130.8
65°	115.9	117.0	117.8	118.5
67.5°	103.1	104.0	104.0	104.0
70°	88.8	89.1	89.7	90.3
72.5°	75.6	75.8	75.8	75.8
75°	61.7	62.0	62.2	62.4
77.5°	48.5	48.7	48.7	48.7
80°	35.5	35.3	35.3	35.3
82.5°	24.3	23.8	23.8	23.8
85°	13.9	13.7	13.9	14.1
87.5°	6.3	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P831743

CATALOG NUMBER: S123DP-S340D930-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.96	16.47	15.33	16.79	17.10	17.20	18.71	17.57	19.02	19.34
	3H	16.65	18.01	17.03	18.34	18.70	18.67	20.02	19.05	20.35	20.71
	4H	17.26	18.53	17.66	18.88	19.26	19.15	20.42	19.55	20.77	21.15
	6H	17.66	18.83	18.07	19.20	19.59	19.45	20.63	19.86	20.99	21.39
	8H	17.77	18.89	18.20	19.28	19.68	19.53	20.65	19.96	21.04	21.44
	12H	17.84	18.91	18.27	19.29	19.72	19.57	20.64	20.00	21.02	21.45
4H	2H	15.61	16.88	16.01	17.23	17.61	17.43	18.71	17.83	19.06	19.43
	3H	17.49	18.55	17.90	18.95	19.35	19.11	20.16	19.52	20.56	20.97
	4H	18.21	19.17	18.64	19.58	20.02	19.71	20.67	20.15	21.08	21.52
	6H	18.72	19.55	19.18	19.99	20.45	20.15	20.98	20.61	21.42	21.88
	8H	18.87	19.64	19.33	20.09	20.55	20.27	21.05	20.74	21.49	21.96
	12H	18.96	19.66	19.45	20.14	20.61	20.35	21.04	20.83	21.52	21.99
8H	4H	18.52	19.30	18.99	19.74	20.21	19.86	20.64	20.33	21.08	21.55
	6H	19.13	19.77	19.63	20.27	20.74	20.39	21.03	20.89	21.52	22.00
	8H	19.35	19.92	19.86	20.43	20.92	20.57	21.14	21.09	21.65	22.14
	12H	19.50	20.00	20.01	20.50	21.06	20.70	21.21	21.21	21.70	22.27
12H	4H	18.55	19.25	19.04	19.72	20.20	19.87	20.56	20.35	21.04	21.51
	6H	19.19	19.76	19.70	20.27	20.76	20.41	20.98	20.92	21.49	21.98
	8H	19.45	19.96	19.96	20.45	21.01	20.63	21.14	21.14	21.63	22.20