

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332613

Luminaire Tested: **S124DIP-S795D1035U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332613
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S795D1035U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7538.9 lumens
Efficiency: N/A
Efficacy: 145.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332613

CATALOG NUMBER: S124DIP-S795D1035U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332613

CATALOG NUMBER: S124DIP-S795D1035U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	55	46	45	44	38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10717	10717	10717
5°	10749	10619	10697
10°	10681	10533	10585
15°	10552	10384	10410
20°	10381	10198	10207
25°	10185	9986	9958
30°	9945	9737	9648
35°	9697	9477	9351
40°	9438	9180	9013
45°	9169	8889	8719
50°	8871	8629	8363
55°	8549	8294	8024
60°	8226	7918	7677
65°	7862	7559	7253
70°	7456	7081	6805
75°	6834	6503	6338
80°	6081	5835	5686
85°	5317	5122	5020



TEST NUMBER: P332613

CATALOG NUMBER: S124DIP-S795D1035U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	1.7
10°-20°	352.2	4.7
20°-30°	518.4	6.9
30°-40°	602.7	8.0
40°-50°	602.7	8.0
50°-60°	527.2	7.0
60°-70°	391.5	5.2
70°-80°	222.4	3.0
80°-90°	68.0	0.9
90°-100°	45.7	0.6
100°-110°	291.1	3.9
110°-120°	556.8	7.4
120°-130°	706.8	9.4
130°-140°	756.2	10.0
140°-150°	707.2	9.4
150°-160°	570.3	7.6
160°-170°	367.8	4.9
170°-180°	126.8	1.7
0°-30°	995.7	13.2
0°-40°	1598.4	21.2
0°-60°	2728.3	36.2
0°-90°	3410.3	45.2
90°-120°	893.5	11.9
90°-150°	3063.7	40.6
90°-180°	4129.0	54.8
0°-180°	7538.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1328	1328	1328	1328	1328	
5°	1326	1322	1310	1321	1320	126
15°	1263	1258	1242	1248	1246	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	962	954	949	615
45°	803	795	779	767	764	619
55°	607	604	589	577	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	233
85°	57	57	55	55	54	63
90°	3	14	22	28	30	6
95°	55	23	22	28	29	71
105°	300	306	312	318	284	314
115°	561	564	563	565	565	552
125°	789	792	791	794	795	704
135°	978	978	981	983	985	753
145°	1128	1131	1131	1132	1134	705
155°	1237	1238	1235	1238	1236	570
165°	1305	1300	1300	1307	1299	369
175°	1335	1329	1330	1338	1327	127
180°	1335	1335	1335	1335	1335	



TEST NUMBER: P332613

CATALOG NUMBER: S124DIP-S795D1035U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1330.9	1330.3	1329.7	1329.2	1328.6	1327.3	1325.2	1323.1	1321.0	1319.0	1320.8
5°	1326.4	1325.5	1324.5	1323.6	1322.6	1320.8	1318.2	1315.6	1313.0	1310.4	1313.0
7.5°	1314.1	1313.1	1312.2	1311.2	1310.3	1308.4	1305.5	1302.6	1299.7	1296.8	1298.9
10°	1303.0	1302.1	1301.1	1300.2	1299.2	1297.2	1294.1	1291.1	1288.0	1284.9	1286.8
12.5°	1288.5	1287.6	1286.6	1285.7	1284.8	1282.6	1279.4	1276.1	1272.9	1269.6	1271.7
15°	1262.6	1261.6	1260.7	1259.7	1258.8	1256.6	1253.0	1249.5	1245.9	1242.4	1243.8
17.5°	1231.3	1230.1	1228.9	1227.8	1226.6	1224.3	1221.0	1217.6	1214.2	1210.9	1211.8
20°	1208.3	1207.1	1206.0	1204.8	1203.6	1201.2	1197.7	1194.1	1190.6	1187.1	1187.8
22.5°	1183.7	1182.1	1180.5	1179.0	1177.4	1174.9	1171.3	1167.8	1164.2	1160.7	1162.0
25°	1143.4	1141.8	1140.1	1138.5	1136.8	1134.3	1131.0	1127.7	1124.4	1121.1	1121.3
27.5°	1097.5	1095.8	1094.1	1092.4	1090.7	1088.3	1085.2	1082.2	1079.1	1076.0	1075.4
30°	1066.9	1065.0	1063.1	1061.2	1059.3	1056.8	1053.7	1050.7	1047.6	1044.5	1043.6
32.5°	1034.5	1032.8	1031.1	1029.4	1027.7	1025.2	1022.0	1018.7	1015.5	1012.2	1011.1
35°	983.9	982.2	980.6	978.9	977.3	974.8	971.5	968.2	964.9	961.6	959.9
37.5°	930.5	929.0	927.5	926.0	924.4	921.9	918.4	914.8	911.3	907.7	905.9
40°	895.6	893.7	891.8	889.9	888.0	885.3	881.8	878.2	874.7	871.1	868.8
42.5°	858.2	857.0	855.9	854.8	853.6	851.1	847.2	843.3	839.3	835.4	832.7
45°	803.1	801.4	799.8	798.1	796.5	793.7	790.0	786.2	782.4	778.6	776.0
47.5°	745.4	744.3	743.2	742.0	740.9	738.6	735.1	731.6	728.1	724.6	721.6
50°	706.3	705.3	704.4	703.4	702.5	700.4	697.1	693.8	690.4	687.1	683.8
52.5°	668.0	666.9	665.7	664.6	663.4	661.1	657.6	654.1	650.6	647.1	644.2
55°	607.4	606.6	605.9	605.2	604.5	602.5	599.2	595.9	592.6	589.3	586.4
57.5°	549.5	548.7	547.9	547.1	546.3	544.2	541.0	537.7	534.5	531.2	528.5
60°	509.5	508.3	507.1	506.0	504.8	502.6	499.6	496.5	493.4	490.4	488.2
62.5°	470.4	469.4	468.4	467.4	466.4	464.3	461.0	457.7	454.5	451.2	449.3
65°	411.6	410.5	409.3	408.1	406.9	405.1	402.8	400.4	398.0	395.7	393.3
67.5°	352.5	351.4	350.3	349.2	348.2	346.5	344.2	341.9	339.7	337.4	335.1
70°	315.9	314.3	312.6	310.9	309.3	307.5	305.6	303.7	301.8	300.0	298.1
72.5°	276.8	275.1	273.5	271.8	270.1	268.6	267.1	265.5	264.0	262.5	261.0
75°	219.1	217.9	216.8	215.6	214.4	213.2	212.0	210.8	209.7	208.5	207.5
77.5°	164.0	163.5	163.0	162.5	161.9	161.2	160.1	159.1	158.0	157.0	156.7
80°	130.8	130.1	129.4	128.7	128.0	127.4	126.9	126.5	126.0	125.5	125.0
82.5°	98.5	98.2	97.8	97.5	97.2	97.0	96.9	96.8	96.7	96.6	96.3
85°	57.4	57.4	57.4	57.4	57.4	57.2	56.7	56.3	55.8	55.3	55.3
87.5°	22.7	23.0	23.3	23.6	23.9	24.2	24.3	24.5	24.6	24.8	25.1
90°	3.0	5.4	7.9	10.3	12.8	14.9	16.6	18.4	20.2	22.0	23.3
92.5°	12.6	12.7	12.8	13.0	13.1	14.1	15.8	17.6	19.4	21.2	22.5
95°	54.9	47.4	39.8	32.3	24.7	21.1	21.3	21.5	21.7	22.0	23.3
97.5°	116.6	121.3	126.0	130.7	135.4	125.4	100.6	75.9	51.1	26.4	26.5
100°	163.7	167.7	171.7	175.7	179.7	166.4	135.8	105.2	74.5	43.9	40.2
102.5°	216.4	219.4	222.3	225.2	228.1	227.6	223.6	219.6	215.6	211.6	170.9
105°	300.5	301.8	303.1	304.5	305.8	307.0	308.1	309.2	310.4	311.5	313.5
107.5°	378.5	379.2	379.9	380.5	381.2	382.3	383.8	385.3	386.8	388.3	389.3
110°	431.3	431.9	432.6	433.2	433.9	434.9	436.2	437.6	438.9	440.2	440.7



TEST NUMBER: P332613

CATALOG NUMBER: S124DIP-S795D1035U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	482.4	483.6	484.8	486.0	487.2	488.1	488.7	489.3	489.9	490.5	490.5
115°	561.0	561.7	562.4	563.0	563.7	563.9	563.7	563.5	563.2	563.0	563.5
117.5°	631.9	632.8	633.7	634.6	635.5	636.1	636.6	637.1	637.6	638.1	638.0
120°	679.8	680.7	681.6	682.5	683.4	683.7	683.5	683.3	683.0	682.8	683.3
122.5°	724.5	725.1	725.6	726.1	726.7	727.1	727.4	727.7	728.0	728.3	728.6
125°	788.6	789.5	790.4	791.3	792.2	792.4	792.0	791.5	791.1	790.6	791.3
127.5°	849.3	849.5	849.8	850.0	850.2	850.8	851.9	852.9	853.9	854.9	854.8
130°	888.5	888.7	888.9	889.1	889.3	889.8	890.5	891.1	891.8	892.5	892.7
132.5°	924.4	924.8	925.2	925.6	926.0	926.6	927.5	928.3	929.1	930.0	930.2
135°	978.3	978.1	977.9	977.6	977.4	977.7	978.6	979.5	980.4	981.3	981.7
137.5°	1026.0	1026.1	1026.2	1026.3	1026.4	1026.9	1027.9	1028.9	1029.8	1030.8	1031.3
140°	1057.2	1057.6	1058.1	1058.5	1058.9	1059.4	1059.8	1060.3	1060.7	1061.2	1061.8
142.5°	1085.1	1085.9	1086.7	1087.5	1088.3	1088.8	1089.1	1089.4	1089.6	1089.9	1090.4
145°	1128.0	1128.7	1129.4	1130.0	1130.7	1131.0	1131.0	1131.0	1131.0	1131.0	1131.3
147.5°	1162.2	1163.4	1164.7	1165.9	1167.2	1167.7	1167.4	1167.2	1167.0	1166.8	1167.0
150°	1186.9	1187.8	1188.7	1189.6	1190.5	1190.8	1190.6	1190.4	1190.2	1189.9	1189.9
152.5°	1207.7	1208.4	1209.1	1209.8	1210.5	1210.7	1210.3	1209.9	1209.5	1209.1	1209.5
155°	1236.9	1237.1	1237.3	1237.5	1237.7	1237.5	1236.9	1236.2	1235.5	1234.9	1235.7
157.5°	1261.4	1261.3	1261.1	1261.0	1260.9	1260.4	1259.7	1258.9	1258.2	1257.4	1258.6
160°	1275.8	1275.1	1274.5	1273.8	1273.1	1272.7	1272.5	1272.2	1272.0	1271.8	1273.1
162.5°	1288.6	1287.7	1286.9	1286.0	1285.2	1284.7	1284.4	1284.2	1284.0	1283.8	1285.1
165°	1304.7	1303.6	1302.5	1301.4	1300.3	1299.7	1299.7	1299.7	1299.7	1299.7	1301.5
167.5°	1317.5	1316.4	1315.2	1314.1	1312.9	1312.3	1312.1	1312.0	1311.9	1311.7	1313.7
170°	1324.7	1323.4	1322.0	1320.7	1319.4	1318.8	1319.0	1319.3	1319.5	1319.7	1321.5
172.5°	1329.5	1328.2	1326.8	1325.5	1324.2	1323.6	1323.8	1324.1	1324.3	1324.5	1326.3
175°	1334.7	1333.4	1332.0	1330.7	1329.4	1328.8	1329.0	1329.3	1329.5	1329.7	1331.7
177.5°	1337.1	1335.8	1334.6	1333.4	1332.1	1331.7	1332.0	1332.4	1332.7	1333.1	1334.5
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P332613

CATALOG NUMBER: S124DIP-S795D1035U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1322.7	1324.6	1326.5	1327.4	1327.2	1327.0	1326.8	1326.6
5°	1315.6	1318.2	1320.8	1321.9	1321.4	1321.0	1320.5	1320.0
7.5°	1301.0	1303.1	1305.1	1306.0	1305.8	1305.5	1305.2	1304.9
10°	1288.7	1290.6	1292.5	1293.2	1292.7	1292.2	1291.8	1291.3
12.5°	1273.8	1275.8	1277.9	1278.6	1278.0	1277.3	1276.6	1276.0
15°	1245.2	1246.6	1248.0	1248.4	1247.7	1247.0	1246.3	1245.6
17.5°	1212.7	1213.6	1214.5	1214.7	1214.2	1213.7	1213.3	1212.8
20°	1188.5	1189.2	1189.9	1190.0	1189.5	1189.1	1188.6	1188.1
22.5°	1163.2	1164.5	1165.8	1166.0	1165.1	1164.3	1163.4	1162.6
25°	1121.6	1121.8	1122.1	1121.7	1120.8	1119.8	1118.9	1117.9
27.5°	1074.9	1074.3	1073.7	1072.9	1071.7	1070.5	1069.3	1068.1
30°	1042.6	1041.7	1040.7	1039.7	1038.5	1037.3	1036.1	1035.0
32.5°	1009.9	1008.8	1007.7	1006.5	1005.3	1004.1	1002.9	1001.8
35°	958.3	956.6	954.9	953.5	952.3	951.2	950.0	948.8
37.5°	904.1	902.3	900.6	898.9	897.3	895.8	894.2	892.6
40°	866.4	864.1	861.7	859.9	858.7	857.6	856.4	855.2
42.5°	829.9	827.2	824.4	822.7	821.9	821.1	820.3	819.5
45°	773.4	770.8	768.2	766.6	765.8	765.1	764.4	763.7
47.5°	718.7	715.8	712.8	710.5	708.7	706.9	705.1	703.3
50°	680.5	677.2	673.9	671.5	670.1	668.7	667.3	665.9
52.5°	641.3	638.3	635.4	633.1	631.3	629.5	627.7	625.9
55°	583.6	580.8	577.9	575.8	574.4	573.0	571.5	570.1
57.5°	525.8	523.1	520.4	518.4	517.0	515.6	514.3	512.9
60°	486.1	484.0	481.8	480.2	479.0	477.8	476.6	475.5
62.5°	447.3	445.4	443.5	441.9	440.7	439.5	438.4	437.2
65°	391.0	388.6	386.2	384.5	383.3	382.1	380.9	379.7
67.5°	332.9	330.6	328.3	327.0	326.7	326.4	326.0	325.7
70°	296.2	294.3	292.4	291.1	290.4	289.7	289.0	288.3
72.5°	259.5	258.0	256.5	255.4	254.6	253.9	253.2	252.5
75°	206.6	205.6	204.7	204.1	203.9	203.6	203.4	203.2
77.5°	156.4	156.1	155.9	155.4	154.8	154.2	153.6	153.0
80°	124.6	124.1	123.6	123.3	123.0	122.8	122.6	122.3
82.5°	96.0	95.7	95.4	95.2	95.0	94.7	94.5	94.2
85°	55.3	55.3	55.3	55.2	55.0	54.7	54.5	54.2
87.5°	25.3	25.6	25.9	26.1	26.1	26.2	26.3	26.4
90°	24.6	26.0	27.3	28.2	28.6	29.1	29.5	29.9
92.5°	23.8	25.2	26.5	27.2	27.3	27.4	27.5	27.6
95°	24.6	26.0	27.3	28.1	28.3	28.5	28.7	28.9
97.5°	26.6	26.8	26.9	27.1	27.3	27.5	27.7	28.0
100°	36.4	32.6	28.8	27.1	27.3	27.5	27.7	28.0
102.5°	130.3	89.6	48.9	28.6	28.6	28.7	28.7	28.8
105°	315.5	317.4	319.4	316.5	308.5	300.5	292.5	284.5
107.5°	390.3	391.3	392.2	393.1	394.0	394.8	395.7	396.5
110°	441.1	441.6	442.0	442.6	443.2	443.9	444.6	445.2



TEST NUMBER: P332613

CATALOG NUMBER: S124DIP-S795D1035U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	490.4	490.3	490.2	490.6	491.4	492.3	493.1	493.9
115°	563.9	564.4	564.8	565.0	565.0	565.0	565.0	565.0
117.5°	637.9	637.8	637.7	637.7	637.6	637.5	637.4	637.3
120°	683.7	684.1	684.6	684.6	684.1	683.7	683.3	682.8
122.5°	728.9	729.1	729.4	729.3	728.9	728.4	728.0	727.5
125°	792.0	792.6	793.3	793.7	794.0	794.2	794.4	794.6
127.5°	854.7	854.5	854.4	854.2	854.1	853.9	853.7	853.5
130°	892.9	893.1	893.3	893.5	893.5	893.5	893.5	893.5
132.5°	930.4	930.7	930.9	930.9	930.7	930.5	930.4	930.2
135°	982.2	982.6	983.1	983.5	984.0	984.4	984.8	985.3
137.5°	1031.8	1032.3	1032.8	1032.9	1032.8	1032.7	1032.5	1032.4
140°	1062.5	1063.2	1063.8	1064.3	1064.5	1064.7	1064.9	1065.2
142.5°	1090.9	1091.4	1091.9	1092.1	1092.2	1092.2	1092.3	1092.3
145°	1131.5	1131.7	1131.9	1132.3	1132.7	1133.1	1133.6	1134.0
147.5°	1167.1	1167.3	1167.5	1167.7	1167.9	1168.1	1168.4	1168.6
150°	1189.9	1189.9	1189.9	1190.0	1190.3	1190.5	1190.7	1190.9
152.5°	1209.8	1210.2	1210.5	1210.6	1210.5	1210.4	1210.2	1210.1
155°	1236.6	1237.5	1238.4	1238.5	1237.9	1237.2	1236.5	1235.9
157.5°	1259.7	1260.9	1262.0	1262.0	1260.9	1259.7	1258.6	1257.4
160°	1274.5	1275.8	1277.1	1277.1	1275.8	1274.5	1273.1	1271.8
162.5°	1286.4	1287.8	1289.1	1289.0	1287.5	1286.0	1284.5	1283.0
165°	1303.3	1305.1	1306.8	1306.7	1304.7	1302.7	1300.7	1298.7
167.5°	1315.6	1317.6	1319.5	1319.4	1317.2	1315.0	1312.7	1310.5
170°	1323.3	1325.0	1326.8	1326.6	1324.4	1322.2	1319.9	1317.7
172.5°	1328.1	1329.8	1331.6	1331.3	1328.9	1326.5	1324.1	1321.7
175°	1333.7	1335.7	1337.7	1337.3	1334.7	1332.0	1329.4	1326.7
177.5°	1335.9	1337.3	1338.8	1338.4	1336.3	1334.2	1332.0	1329.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7

(END OF REPORT)