

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332589

Luminaire Tested: **S124DIP-S795D590U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332589
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S795D590U835-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5903.5 lumens
Efficiency: N/A
Efficacy: 146.5 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	89	94	90	87	83	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	52	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	71	62	55	49	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10365	10365	10365	10365
5°	12206	10391	9172	10391
10°	14614	10346	8257	10346
15°	17291	10242	7583	10242
20°	19254	10134	6981	10134
25°	19565	9977	6566	9977
30°	16648	9826	6435	9826
35°	12799	9581	6436	9581
40°	9977	9293	6558	9293
45°	8318	8859	6667	8859
50°	7321	8329	6894	8329
55°	6707	7695	7171	7695
60°	6286	7127	7505	7127
65°	5851	6491	7782	6491
70°	5349	5863	7959	5863
75°	4779	5159	7863	5159
80°	4007	4226	7615	4226
85°	2955	3057	7290	3057



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.1
10°-20°	385.5	6.5
20°-30°	611.3	10.4
30°-40°	680.3	11.5
40°-50°	619.3	10.5
50°-60°	506.1	8.6
60°-70°	361.3	6.1
70°-80°	198.9	3.4
80°-90°	56.5	1.0
90°-100°	26.1	0.4
100°-110°	166.3	2.8
110°-120°	318.2	5.4
120°-130°	403.9	6.8
130°-140°	432.1	7.3
140°-150°	404.1	6.8
150°-160°	325.9	5.5
160°-170°	210.2	3.6
170°-180°	72.4	1.2
0°-30°	1121.9	19.0
0°-40°	1802.3	30.5
0°-60°	2927.7	49.6
0°-90°	3544.4	60.0
90°-120°	510.6	8.6
90°-150°	1750.6	29.7
90°-180°	2359.0	40.0
0°-180°	5903.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1506	1282	1132	1282	1506	153
15°	2069	1225	907	1225	2069	585
25°	2196	1120	737	1120	2196	968
35°	1299	972	653	972	1299	824
45°	729	776	584	776	729	574
55°	476	547	510	547	476	430
65°	306	340	407	340	306	303
75°	153	165	252	165	153	163
85°	32	33	79	33	32	39
90°	17	2	17	2	17	9
95°	16	31	16	31	16	13
105°	163	172	163	172	163	142
115°	323	321	323	321	323	320
125°	454	451	454	451	454	404
135°	563	559	563	559	563	433
145°	648	645	648	645	648	405
155°	706	707	706	707	706	326
165°	742	746	742	746	742	210
175°	758	763	758	763	758	72
180°	763	763	763	763	763	



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1366.4	1366.0	1361.7	1360.9	1357.9	1354.1	1353.2	1346.4	1332.8	1326.4	1324.7
5°	1506.2	1516.8	1503.0	1500.3	1498.7	1481.2	1472.1	1461.5	1437.0	1422.7	1411.5
7.5°	1673.0	1674.2	1668.2	1663.3	1649.8	1634.4	1611.5	1587.0	1557.9	1527.5	1504.7
10°	1782.7	1787.0	1780.1	1779.0	1751.9	1734.9	1700.8	1672.1	1639.1	1602.4	1568.9
12.5°	1898.5	1892.5	1889.0	1866.2	1861.2	1830.2	1790.6	1761.0	1710.2	1668.0	1623.4
15°	2068.9	2057.2	2049.7	2018.3	2002.9	1959.8	1917.8	1885.4	1818.9	1755.6	1707.7
17.5°	2168.8	2180.5	2163.3	2150.4	2110.5	2080.3	2037.4	1969.3	1917.3	1838.7	1778.3
20°	2241.2	2242.2	2232.7	2219.4	2188.0	2149.7	2102.9	2028.4	1966.2	1888.0	1805.1
22.5°	2260.7	2261.0	2256.9	2244.5	2220.7	2189.7	2142.5	2080.3	2004.9	1919.9	1837.0
25°	2196.5	2194.4	2199.2	2213.0	2203.9	2194.4	2167.2	2121.0	2050.8	1960.9	1871.5
27.5°	1957.8	1972.5	1999.5	2033.5	2066.3	2091.3	2098.3	2088.8	2045.3	1971.4	1877.8
30°	1785.9	1804.0	1824.2	1858.2	1924.2	1962.0	2003.4	2034.8	2017.3	1958.2	1871.0
32.5°	1597.0	1601.5	1631.5	1670.2	1730.6	1803.3	1869.0	1932.7	1953.9	1922.9	1850.2
35°	1298.7	1306.2	1338.6	1376.9	1450.9	1539.7	1638.6	1726.9	1799.7	1829.0	1791.8
37.5°	1059.8	1081.2	1104.1	1145.3	1210.4	1290.3	1393.1	1507.3	1615.9	1688.7	1701.0
40°	946.7	960.0	976.5	1007.8	1063.1	1141.9	1230.1	1361.0	1476.4	1580.6	1614.7
42.5°	857.3	865.1	875.2	903.6	945.7	1024.0	1104.6	1219.7	1335.6	1460.2	1517.2
45°	728.6	736.6	753.6	770.1	802.0	856.3	931.2	1025.9	1142.4	1262.6	1367.9
47.5°	635.7	640.8	650.9	668.5	695.6	731.4	792.4	871.5	979.4	1096.1	1208.3
50°	582.9	587.1	595.1	611.1	631.8	663.7	713.7	787.7	872.2	989.8	1099.8
52.5°	541.2	542.9	548.8	559.6	576.1	602.9	643.9	705.1	783.7	888.5	998.2
55°	476.5	478.7	484.0	492.0	506.3	523.3	554.7	600.4	669.1	760.0	855.2
57.5°	423.3	424.8	429.3	432.4	444.2	458.0	482.2	514.8	566.8	643.9	728.9
60°	389.3	388.2	393.6	396.2	404.2	415.9	434.5	465.9	511.1	573.3	651.5
62.5°	356.1	354.6	359.1	362.6	367.2	377.2	392.4	417.0	453.7	509.9	577.5
65°	306.3	304.2	306.9	311.1	315.4	320.7	331.9	353.7	382.9	423.3	474.9
67.5°	256.3	258.6	259.0	261.1	263.6	270.8	278.5	293.9	314.5	346.9	390.6
70°	226.6	227.1	229.2	229.2	230.8	237.2	243.6	252.6	272.8	302.6	338.2
72.5°	196.8	199.0	198.2	199.9	201.0	205.3	210.0	218.6	235.8	257.9	288.0
75°	153.2	154.8	154.8	155.3	156.9	158.5	162.2	168.6	180.8	197.3	218.1
77.5°	111.7	111.9	112.6	114.6	114.6	117.1	119.9	125.0	131.0	142.3	155.0
80°	86.2	87.2	86.7	87.8	87.8	89.9	90.9	97.3	100.0	107.4	117.5
82.5°	63.2	64.2	64.1	65.6	66.5	66.9	68.4	70.9	73.6	80.2	84.3
85°	31.9	33.0	31.9	33.0	34.6	35.1	36.7	37.2	39.4	41.0	44.7
87.5°	12.8	14.0	14.0	14.3	15.1	15.5	15.7	15.2	16.7	17.0	18.5
90°	17.1	16.9	16.6	16.4	16.1	15.6	14.8	14.1	13.3	12.5	11.5
92.5°	15.7	15.7	15.6	15.6	15.5	15.1	14.4	13.6	12.9	12.1	11.1
95°	16.5	16.4	16.3	16.2	16.0	15.6	14.8	14.1	13.3	12.5	12.4
97.5°	16.0	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.1	15.1	29.2
100°	16.0	15.8	15.7	15.6	15.5	16.5	18.6	20.8	22.9	25.1	42.6
102.5°	16.4	16.4	16.4	16.4	16.3	27.9	51.2	74.4	97.7	120.9	123.2
105°	162.6	167.1	171.7	176.3	180.8	182.5	181.4	180.3	179.1	178.0	177.3
107.5°	226.6	226.1	225.6	225.1	224.6	224.1	223.6	223.0	222.5	221.9	221.0
110°	254.4	254.0	253.6	253.3	252.9	252.6	252.3	252.1	251.8	251.6	250.8



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	282.2	281.8	281.3	280.8	280.3	280.1	280.2	280.2	280.3	280.3	280.0
115°	322.9	322.9	322.9	322.9	322.9	322.7	322.5	322.2	322.0	321.7	321.8
117.5°	364.2	364.2	364.3	364.3	364.4	364.4	364.5	364.5	364.6	364.6	364.3
120°	390.2	390.4	390.7	390.9	391.2	391.2	390.9	390.7	390.4	390.2	390.3
122.5°	415.7	416.0	416.2	416.5	416.7	416.8	416.6	416.5	416.3	416.2	416.0
125°	454.1	453.9	453.8	453.7	453.6	453.3	452.9	452.5	452.2	451.8	452.0
127.5°	487.7	487.8	487.9	488.0	488.1	488.2	488.3	488.4	488.4	488.5	487.9
130°	510.5	510.5	510.5	510.5	510.5	510.5	510.3	510.2	510.1	510.0	509.6
132.5°	531.5	531.6	531.7	531.8	531.9	531.9	531.8	531.7	531.5	531.4	530.9
135°	563.0	562.8	562.5	562.2	562.0	561.7	561.5	561.2	561.0	560.7	560.2
137.5°	589.9	590.0	590.1	590.2	590.2	590.1	589.9	589.6	589.3	589.0	588.5
140°	608.6	608.5	608.4	608.3	608.1	607.9	607.5	607.1	606.7	606.4	606.1
142.5°	624.2	624.1	624.1	624.1	624.1	623.9	623.6	623.3	623.1	622.8	622.6
145°	648.0	647.8	647.5	647.2	647.0	646.8	646.7	646.5	646.4	646.3	646.3
147.5°	667.7	667.6	667.5	667.4	667.2	667.1	667.0	666.9	666.8	666.7	666.8
150°	680.5	680.4	680.3	680.1	680.0	679.9	679.9	679.9	679.9	679.9	680.1
152.5°	691.5	691.5	691.6	691.7	691.8	691.7	691.5	691.3	691.1	690.9	691.1
155°	706.2	706.6	706.9	707.3	707.7	707.6	707.1	706.6	706.1	705.6	706.0
157.5°	718.5	719.2	719.8	720.5	721.1	721.1	720.5	719.8	719.2	718.5	718.9
160°	726.7	727.5	728.2	729.0	729.8	729.8	729.0	728.2	727.5	726.7	726.8
162.5°	733.1	734.0	734.8	735.7	736.6	736.6	735.8	735.1	734.3	733.6	733.7
165°	742.1	743.3	744.4	745.5	746.7	746.8	745.7	744.7	743.7	742.7	742.7
167.5°	748.9	750.1	751.4	752.7	753.9	754.0	752.9	751.8	750.7	749.5	749.6
170°	753.0	754.2	755.5	756.8	758.0	758.2	757.1	756.1	755.1	754.1	754.0
172.5°	755.2	756.6	758.0	759.4	760.7	760.9	759.9	758.9	757.9	756.8	756.7
175°	758.1	759.6	761.1	762.7	764.2	764.4	763.2	762.1	760.9	759.8	759.7
177.5°	759.9	761.1	762.4	763.6	764.8	765.0	764.2	763.4	762.6	761.7	761.5
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1325.1	1319.2	1314.9	1311.5	1302.2	1296.6	1292.4	1286.4	1279.6	1272.4	1263.4
5°	1400.3	1382.2	1369.0	1348.7	1329.6	1313.6	1297.2	1282.3	1264.2	1244.5	1230.1
7.5°	1479.4	1452.5	1418.0	1388.1	1354.5	1325.2	1299.1	1272.3	1244.4	1217.4	1192.6
10°	1529.6	1495.0	1456.7	1411.5	1369.0	1331.2	1296.1	1262.1	1229.1	1196.1	1167.9
12.5°	1583.6	1540.5	1483.9	1431.1	1383.4	1332.9	1290.6	1248.9	1209.1	1174.4	1141.5
15°	1656.1	1593.9	1528.5	1457.8	1395.0	1336.0	1278.0	1225.4	1180.7	1134.9	1103.0
17.5°	1700.7	1623.7	1548.9	1475.0	1399.1	1324.6	1262.1	1201.3	1145.4	1099.9	1059.7
20°	1730.1	1653.5	1560.4	1486.5	1396.1	1319.5	1247.2	1179.6	1121.1	1072.7	1031.2
22.5°	1755.6	1667.1	1574.0	1476.7	1386.7	1305.5	1226.3	1158.3	1098.6	1047.6	1007.8
25°	1769.4	1667.8	1566.8	1470.0	1367.9	1271.6	1199.8	1120.1	1056.2	1002.5	960.0
27.5°	1770.9	1662.3	1548.0	1440.4	1335.0	1245.4	1154.7	1083.5	1017.2	960.4	919.5
30°	1766.2	1653.0	1530.1	1413.6	1307.8	1210.5	1131.8	1054.1	986.6	930.2	887.6
32.5°	1751.3	1633.4	1507.1	1383.8	1274.2	1179.0	1097.7	1023.9	958.1	902.5	857.9
35°	1708.3	1591.8	1457.2	1329.1	1216.8	1120.6	1047.2	972.2	906.3	853.6	810.5
37.5°	1640.9	1535.6	1398.8	1266.2	1156.0	1059.3	986.6	918.8	859.3	805.8	761.7
40°	1582.2	1489.7	1352.5	1223.2	1104.1	1012.1	944.0	881.8	822.8	772.2	730.2
42.5°	1514.6	1433.9	1307.4	1170.5	1055.6	963.2	896.8	840.9	785.3	738.6	696.6
45°	1393.9	1340.8	1221.6	1095.1	975.4	888.2	824.9	776.0	729.2	683.4	648.3
47.5°	1255.2	1228.9	1128.6	1008.4	894.8	808.8	753.9	708.7	667.7	629.0	598.0
50°	1162.1	1149.3	1062.6	946.7	838.2	757.3	702.0	663.2	628.1	594.1	564.8
52.5°	1070.2	1069.7	991.6	885.4	785.0	707.1	652.2	616.0	585.6	557.9	531.6
55°	929.7	944.5	883.4	788.7	698.8	628.6	579.2	546.7	525.5	502.6	482.9
57.5°	800.6	825.3	774.9	691.5	616.5	551.8	508.8	484.4	461.7	447.9	433.6
60°	716.4	739.8	700.4	630.2	559.5	504.2	463.2	441.4	421.7	412.2	402.1
62.5°	641.5	662.4	633.2	568.1	506.7	453.6	419.0	398.0	384.7	374.3	367.6
65°	534.5	552.0	527.1	479.7	427.1	384.5	356.3	339.8	327.1	322.8	315.4
67.5°	432.1	448.0	434.5	394.3	352.1	319.8	297.8	282.0	274.4	270.7	265.4
70°	371.2	387.2	372.8	337.7	305.3	278.2	257.4	248.4	240.4	238.8	231.3
72.5°	319.7	330.6	316.2	288.8	261.0	238.2	222.1	212.6	208.5	205.6	201.6
75°	239.9	249.4	239.9	218.6	198.9	183.0	169.1	165.4	160.6	159.0	156.4
77.5°	169.8	178.1	170.7	157.4	142.7	130.4	123.0	118.2	117.1	114.3	115.6
80°	129.8	135.1	128.2	119.1	107.4	98.9	93.6	90.9	87.8	86.7	88.8
82.5°	93.2	95.5	92.0	85.9	77.2	71.7	68.1	65.0	64.4	64.6	64.6
85°	48.4	47.9	47.3	42.0	39.4	35.6	33.5	33.0	32.4	33.5	34.6
87.5°	18.3	18.5	17.9	15.9	14.4	12.8	12.1	11.4	12.1	12.8	13.5
90°	10.5	9.5	8.5	7.3	5.9	4.5	3.1	1.7	3.1	4.5	5.9
92.5°	10.1	9.1	8.0	7.5	7.4	7.3	7.3	7.2	7.3	7.3	7.4
95°	12.3	12.2	12.0	14.1	18.4	22.8	27.1	31.4	27.1	22.8	18.4
97.5°	43.4	57.5	71.6	77.4	74.7	72.0	69.3	66.6	69.3	72.0	74.7
100°	60.1	77.6	95.1	102.7	100.4	98.1	95.8	93.5	95.8	98.1	100.4
102.5°	125.5	127.8	130.1	130.4	128.7	127.0	125.3	123.7	125.3	127.0	128.7
105°	176.7	176.1	175.4	174.7	174.0	173.2	172.5	171.7	172.5	173.2	174.0
107.5°	220.2	219.3	218.4	217.8	217.4	217.1	216.7	216.3	216.7	217.1	217.4
110°	250.0	249.3	248.5	247.9	247.6	247.2	246.8	246.4	246.8	247.2	247.6



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	279.6	279.2	278.9	278.4	277.7	277.0	276.3	275.6	276.3	277.0	277.7
115°	322.0	322.1	322.2	322.1	321.7	321.3	321.0	320.6	321.0	321.3	321.7
117.5°	364.1	363.8	363.5	363.1	362.6	362.1	361.6	361.1	361.6	362.1	362.6
120°	390.4	390.6	390.7	390.5	390.0	389.5	389.0	388.5	389.0	389.5	390.0
122.5°	415.8	415.7	415.5	415.2	414.9	414.6	414.3	414.0	414.3	414.6	414.9
125°	452.3	452.5	452.8	452.7	452.2	451.7	451.1	450.6	451.1	451.7	452.2
127.5°	487.3	486.8	486.2	485.8	485.7	485.6	485.4	485.3	485.4	485.6	485.7
130°	509.2	508.8	508.4	508.2	508.1	507.9	507.8	507.7	507.8	507.9	508.1
132.5°	530.4	530.0	529.5	529.1	528.9	528.7	528.4	528.2	528.4	528.7	528.9
135°	559.7	559.2	558.7	558.5	558.6	558.8	558.9	559.0	558.9	558.8	558.6
137.5°	587.9	587.3	586.8	586.5	586.4	586.4	586.3	586.3	586.3	586.4	586.4
140°	605.9	605.6	605.3	605.1	604.8	604.6	604.3	604.1	604.3	604.6	604.8
142.5°	622.5	622.3	622.2	621.9	621.4	621.0	620.5	620.1	620.5	621.0	621.4
145°	646.3	646.3	646.3	646.1	645.7	645.3	645.0	644.6	645.0	645.3	645.7
147.5°	667.0	667.1	667.2	666.9	666.2	665.5	664.8	664.1	664.8	665.5	666.2
150°	680.2	680.3	680.5	680.3	679.8	679.3	678.7	678.2	678.7	679.3	679.8
152.5°	691.4	691.6	691.8	691.7	691.3	690.9	690.5	690.1	690.5	690.9	691.3
155°	706.4	706.8	707.1	707.3	707.1	707.0	706.9	706.8	706.9	707.0	707.1
157.5°	719.4	719.8	720.2	720.5	720.6	720.6	720.7	720.8	720.7	720.6	720.6
160°	727.0	727.1	727.2	727.5	727.9	728.2	728.6	729.0	728.6	728.2	727.9
162.5°	733.8	733.9	734.1	734.4	734.9	735.3	735.8	736.3	735.8	735.3	734.9
165°	742.7	742.7	742.7	743.0	743.6	744.3	744.9	745.5	744.9	744.3	743.6
167.5°	749.7	749.8	749.8	750.2	750.9	751.5	752.2	752.8	752.2	751.5	750.9
170°	753.8	753.7	753.6	753.9	754.7	755.4	756.2	757.0	756.2	755.4	754.7
172.5°	756.6	756.5	756.3	756.7	757.4	758.2	758.9	759.7	758.9	758.2	757.4
175°	759.6	759.4	759.3	759.6	760.4	761.1	761.9	762.7	761.9	761.1	760.4
177.5°	761.3	761.1	760.9	761.2	761.9	762.6	763.3	764.0	763.3	762.6	761.9
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1259.2	1255.4	1249.8	1242.2	1235.8	1229.0	1227.3	1224.7	1229.8	1225.6	1224.3
5°	1217.9	1206.7	1192.4	1175.9	1166.3	1152.5	1149.8	1144.5	1139.2	1138.7	1133.3
7.5°	1174.2	1157.8	1139.0	1122.2	1106.6	1091.5	1081.7	1079.5	1071.7	1067.1	1061.8
10°	1146.1	1125.9	1104.1	1088.1	1070.1	1054.1	1042.9	1036.6	1031.2	1025.4	1020.1
12.5°	1112.9	1091.4	1073.5	1056.2	1034.7	1022.6	1004.2	993.2	992.1	992.2	978.4
15°	1074.3	1053.0	1025.4	1000.9	989.2	965.8	955.7	942.9	935.0	927.0	920.6
17.5°	1030.2	1003.7	982.1	954.0	931.7	913.1	899.8	892.1	880.1	868.8	860.6
20°	1002.5	974.3	951.5	921.7	897.2	874.3	863.2	852.5	843.5	833.9	824.9
22.5°	974.4	945.0	917.0	888.1	865.3	841.2	830.4	815.9	807.3	802.0	793.0
25°	930.2	898.3	866.4	838.7	815.3	794.0	779.7	768.5	758.9	754.7	748.8
27.5°	882.1	850.4	819.6	788.2	761.6	746.2	734.7	726.3	720.7	715.1	712.5
30°	851.5	818.5	785.5	756.3	731.8	716.4	705.7	699.9	695.6	693.0	690.3
32.5°	820.4	787.9	753.2	726.5	704.6	690.9	682.8	676.9	674.8	673.8	672.9
35°	770.6	737.7	705.7	681.8	661.1	655.8	648.8	645.7	644.6	648.3	649.9
37.5°	722.4	691.8	662.5	639.3	625.7	617.9	615.5	615.7	619.5	622.8	626.6
40°	691.4	661.6	634.0	613.7	601.0	596.2	595.1	597.8	602.0	605.8	610.0
42.5°	661.2	631.8	606.7	587.8	578.9	574.5	575.1	577.8	583.7	588.3	594.7
45°	614.3	589.8	565.3	549.9	542.5	543.5	543.5	548.3	554.2	561.1	568.0
47.5°	570.1	545.5	525.3	512.4	508.5	507.6	510.6	516.8	525.2	533.8	543.4
50°	540.3	516.9	499.4	487.7	483.4	485.0	489.3	495.1	505.2	515.9	526.0
52.5°	510.1	488.9	472.6	461.7	458.8	461.6	465.9	475.1	484.0	495.5	507.7
55°	463.2	445.1	432.4	424.4	423.3	424.9	429.7	439.8	452.6	467.0	478.7
57.5°	416.5	401.4	389.7	384.2	384.7	386.2	394.1	406.1	419.7	435.0	450.1
60°	385.1	371.2	361.7	357.4	357.9	361.1	370.7	381.9	398.9	413.8	429.7
62.5°	355.3	343.1	334.0	330.2	329.4	336.4	345.6	357.2	374.2	390.8	408.0
65°	307.4	297.8	290.4	288.3	289.9	295.2	306.9	322.3	336.7	354.2	372.3
67.5°	260.6	252.7	247.6	248.6	250.5	258.4	268.2	281.4	297.7	315.9	333.8
70°	230.8	223.4	219.1	219.6	222.8	232.4	240.9	254.2	271.8	290.4	305.3
72.5°	200.2	195.3	191.5	193.7	196.9	203.5	214.1	227.4	242.8	260.2	275.9
75°	153.7	153.7	151.6	153.2	158.0	164.3	172.3	186.1	201.6	215.4	228.2
77.5°	114.0	112.9	114.2	116.2	118.9	126.5	135.6	145.5	157.1	170.9	181.5
80°	87.2	87.8	90.4	93.6	94.7	100.5	110.1	119.1	128.2	139.9	150.0
82.5°	65.5	66.1	67.4	71.5	72.5	78.8	85.0	94.0	102.2	110.1	118.5
85°	35.6	35.6	38.3	39.9	42.5	46.8	50.5	55.8	63.3	68.6	76.6
87.5°	15.1	15.3	17.2	18.3	19.8	22.1	23.1	27.9	29.8	32.1	36.0
90°	7.3	8.5	9.5	10.5	11.5	12.5	13.3	14.1	14.8	15.6	16.1
92.5°	7.5	8.0	9.1	10.1	11.1	12.1	12.9	13.6	14.4	15.1	15.5
95°	14.1	12.0	12.2	12.3	12.4	12.5	13.3	14.1	14.8	15.6	16.0
97.5°	77.4	71.6	57.5	43.4	29.2	15.1	15.1	15.2	15.3	15.4	15.5
100°	102.7	95.1	77.6	60.1	42.6	25.1	22.9	20.8	18.6	16.5	15.5
102.5°	130.4	130.1	127.8	125.5	123.2	120.9	97.7	74.4	51.2	27.9	16.3
105°	174.7	175.4	176.1	176.7	177.3	178.0	179.1	180.3	181.4	182.5	180.8
107.5°	217.8	218.4	219.3	220.2	221.0	221.9	222.5	223.0	223.6	224.1	224.6
110°	247.9	248.5	249.3	250.0	250.8	251.6	251.8	252.1	252.3	252.6	252.9



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	278.4	278.9	279.2	279.6	280.0	280.3	280.3	280.2	280.2	280.1	280.3
115°	322.1	322.2	322.1	322.0	321.8	321.7	322.0	322.2	322.5	322.7	322.9
117.5°	363.1	363.5	363.8	364.1	364.3	364.6	364.6	364.5	364.5	364.4	364.4
120°	390.5	390.7	390.6	390.4	390.3	390.2	390.4	390.7	390.9	391.2	391.2
122.5°	415.2	415.5	415.7	415.8	416.0	416.2	416.3	416.5	416.6	416.8	416.7
125°	452.7	452.8	452.5	452.3	452.0	451.8	452.2	452.5	452.9	453.3	453.6
127.5°	485.8	486.2	486.8	487.3	487.9	488.5	488.4	488.4	488.3	488.2	488.1
130°	508.2	508.4	508.8	509.2	509.6	510.0	510.1	510.2	510.3	510.5	510.5
132.5°	529.1	529.5	530.0	530.4	530.9	531.4	531.5	531.7	531.8	531.9	531.9
135°	558.5	558.7	559.2	559.7	560.2	560.7	561.0	561.2	561.5	561.7	562.0
137.5°	586.5	586.8	587.3	587.9	588.5	589.0	589.3	589.6	589.9	590.1	590.2
140°	605.1	605.3	605.6	605.9	606.1	606.4	606.7	607.1	607.5	607.9	608.1
142.5°	621.9	622.2	622.3	622.5	622.6	622.8	623.1	623.3	623.6	623.9	624.1
145°	646.1	646.3	646.3	646.3	646.3	646.3	646.4	646.5	646.7	646.8	647.0
147.5°	666.9	667.2	667.1	667.0	666.8	666.7	666.8	666.9	667.0	667.1	667.2
150°	680.3	680.5	680.3	680.2	680.1	679.9	679.9	679.9	679.9	679.9	680.0
152.5°	691.7	691.8	691.6	691.4	691.1	690.9	691.1	691.3	691.5	691.7	691.8
155°	707.3	707.1	706.8	706.4	706.0	705.6	706.1	706.6	707.1	707.6	707.7
157.5°	720.5	720.2	719.8	719.4	718.9	718.5	719.2	719.8	720.5	721.1	721.1
160°	727.5	727.2	727.1	727.0	726.8	726.7	727.5	728.2	729.0	729.8	729.8
162.5°	734.4	734.1	733.9	733.8	733.7	733.6	734.3	735.1	735.8	736.6	736.6
165°	743.0	742.7	742.7	742.7	742.7	742.7	743.7	744.7	745.7	746.8	746.7
167.5°	750.2	749.8	749.8	749.7	749.6	749.5	750.7	751.8	752.9	754.0	753.9
170°	753.9	753.6	753.7	753.8	754.0	754.1	755.1	756.1	757.1	758.2	758.0
172.5°	756.7	756.3	756.5	756.6	756.7	756.8	757.9	758.9	759.9	760.9	760.7
175°	759.6	759.3	759.4	759.6	759.7	759.8	760.9	762.1	763.2	764.4	764.2
177.5°	761.2	760.9	761.1	761.3	761.5	761.7	762.6	763.4	764.2	765.0	764.8
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1223.4	1222.6	1219.6	1219.2	1219.6	1222.6	1223.4	1224.3	1225.6	1229.8	1224.7
5°	1130.2	1127.5	1125.9	1131.8	1125.9	1127.5	1130.2	1133.3	1138.7	1139.2	1144.5
7.5°	1059.8	1057.7	1053.0	1051.6	1053.0	1057.7	1059.8	1061.8	1067.1	1071.7	1079.5
10°	1014.7	1012.6	1008.4	1007.3	1008.4	1012.6	1014.7	1020.1	1025.4	1031.2	1036.6
12.5°	971.3	967.1	966.2	967.3	966.2	967.1	971.3	978.4	992.2	992.1	993.2
15°	913.7	911.6	905.7	907.3	905.7	911.6	913.7	920.6	927.0	935.0	942.9
17.5°	856.9	854.3	847.2	853.5	847.2	854.3	856.9	860.6	868.8	880.1	892.1
20°	821.2	816.9	813.2	812.6	813.2	816.9	821.2	824.9	833.9	843.5	852.5
22.5°	787.1	783.3	783.0	779.5	783.0	783.3	787.1	793.0	802.0	807.3	815.9
25°	744.6	740.9	739.8	737.1	739.8	740.9	744.6	748.8	754.7	758.9	768.5
27.5°	711.9	710.1	708.2	709.0	708.2	710.1	711.9	712.5	715.1	720.7	726.3
30°	691.9	691.4	690.3	690.3	690.3	691.4	691.9	690.3	693.0	695.6	699.9
32.5°	675.3	675.2	675.9	675.9	675.9	675.2	675.3	672.9	673.8	674.8	676.9
35°	652.0	653.6	654.7	653.1	654.7	653.6	652.0	649.9	648.3	644.6	645.7
37.5°	631.0	632.6	634.1	635.9	634.1	632.6	631.0	626.6	622.8	619.5	615.7
40°	614.8	618.5	619.6	622.3	619.6	618.5	614.8	610.0	605.8	602.0	597.8
42.5°	599.5	603.6	606.4	606.9	606.4	603.6	599.5	594.7	588.3	583.7	577.8
45°	576.0	580.2	584.0	584.0	584.0	580.2	576.0	568.0	561.1	554.2	548.3
47.5°	551.6	557.8	561.5	562.5	561.5	557.8	551.6	543.4	533.8	525.2	516.8
50°	535.0	542.5	546.2	548.9	546.2	542.5	535.0	526.0	515.9	505.2	495.1
52.5°	518.9	526.3	531.3	532.7	531.3	526.3	518.9	507.7	495.5	484.0	475.1
55°	490.9	501.5	507.4	509.5	507.4	501.5	490.9	478.7	467.0	452.6	439.8
57.5°	464.5	474.3	481.1	482.7	481.1	474.3	464.5	450.1	435.0	419.7	406.1
60°	444.1	454.7	463.2	464.8	463.2	454.7	444.1	429.7	413.8	398.9	381.9
62.5°	423.2	434.3	442.0	446.1	442.0	434.3	423.2	408.0	390.8	374.2	357.2
65°	387.2	398.3	405.8	407.4	405.8	398.3	387.2	372.3	354.2	336.7	322.3
67.5°	347.8	359.0	363.9	367.0	363.9	359.0	347.8	333.8	315.9	297.7	281.4
70°	320.2	329.2	334.5	337.2	334.5	329.2	320.2	305.3	290.4	271.8	254.2
72.5°	288.7	298.1	304.3	304.8	304.3	298.1	288.7	275.9	260.2	242.8	227.4
75°	240.4	248.9	252.1	252.1	252.1	248.9	240.4	228.2	215.4	201.6	186.1
77.5°	190.3	194.7	198.7	199.5	198.7	194.7	190.3	181.5	170.9	157.1	145.5
80°	158.0	160.6	163.8	163.8	163.8	160.6	158.0	150.0	139.9	128.2	119.1
82.5°	124.8	127.0	130.2	129.8	130.2	127.0	124.8	118.5	110.1	102.2	94.0
85°	75.5	80.3	79.8	78.7	79.8	80.3	75.5	76.6	68.6	63.3	55.8
87.5°	37.3	37.8	39.1	40.0	39.1	37.8	37.3	36.0	32.1	29.8	27.9
90°	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	15.6	14.8	14.1
92.5°	15.6	15.6	15.7	15.7	15.7	15.6	15.6	15.5	15.1	14.4	13.6
95°	16.2	16.3	16.4	16.5	16.4	16.3	16.2	16.0	15.6	14.8	14.1
97.5°	15.6	15.7	15.8	16.0	15.8	15.7	15.6	15.5	15.4	15.3	15.2
100°	15.6	15.7	15.8	16.0	15.8	15.7	15.6	15.5	16.5	18.6	20.8
102.5°	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.3	27.9	51.2	74.4
105°	176.3	171.7	167.1	162.6	167.1	171.7	176.3	180.8	182.5	181.4	180.3
107.5°	225.1	225.6	226.1	226.6	226.1	225.6	225.1	224.6	224.1	223.6	223.0
110°	253.3	253.6	254.0	254.4	254.0	253.6	253.3	252.9	252.6	252.3	252.1



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	280.8	281.3	281.8	282.2	281.8	281.3	280.8	280.3	280.1	280.2	280.2
115°	322.9	322.9	322.9	322.9	322.9	322.9	322.9	322.9	322.7	322.5	322.2
117.5°	364.3	364.3	364.2	364.2	364.2	364.3	364.3	364.4	364.4	364.5	364.5
120°	390.9	390.7	390.4	390.2	390.4	390.7	390.9	391.2	391.2	390.9	390.7
122.5°	416.5	416.2	416.0	415.7	416.0	416.2	416.5	416.7	416.8	416.6	416.5
125°	453.7	453.8	453.9	454.1	453.9	453.8	453.7	453.6	453.3	452.9	452.5
127.5°	488.0	487.9	487.8	487.7	487.8	487.9	488.0	488.1	488.2	488.3	488.4
130°	510.5	510.5	510.5	510.5	510.5	510.5	510.5	510.5	510.5	510.3	510.2
132.5°	531.8	531.7	531.6	531.5	531.6	531.7	531.8	531.9	531.9	531.8	531.7
135°	562.2	562.5	562.8	563.0	562.8	562.5	562.2	562.0	561.7	561.5	561.2
137.5°	590.2	590.1	590.0	589.9	590.0	590.1	590.2	590.2	590.1	589.9	589.6
140°	608.3	608.4	608.5	608.6	608.5	608.4	608.3	608.1	607.9	607.5	607.1
142.5°	624.1	624.1	624.1	624.2	624.1	624.1	624.1	624.1	623.9	623.6	623.3
145°	647.2	647.5	647.8	648.0	647.8	647.5	647.2	647.0	646.8	646.7	646.5
147.5°	667.4	667.5	667.6	667.7	667.6	667.5	667.4	667.2	667.1	667.0	666.9
150°	680.1	680.3	680.4	680.5	680.4	680.3	680.1	680.0	679.9	679.9	679.9
152.5°	691.7	691.6	691.5	691.5	691.5	691.6	691.7	691.8	691.7	691.5	691.3
155°	707.3	706.9	706.6	706.2	706.6	706.9	707.3	707.7	707.6	707.1	706.6
157.5°	720.5	719.8	719.2	718.5	719.2	719.8	720.5	721.1	721.1	720.5	719.8
160°	729.0	728.2	727.5	726.7	727.5	728.2	729.0	729.8	729.8	729.0	728.2
162.5°	735.7	734.8	734.0	733.1	734.0	734.8	735.7	736.6	736.6	735.8	735.1
165°	745.5	744.4	743.3	742.1	743.3	744.4	745.5	746.7	746.8	745.7	744.7
167.5°	752.7	751.4	750.1	748.9	750.1	751.4	752.7	753.9	754.0	752.9	751.8
170°	756.8	755.5	754.2	753.0	754.2	755.5	756.8	758.0	758.2	757.1	756.1
172.5°	759.4	758.0	756.6	755.2	756.6	758.0	759.4	760.7	760.9	759.9	758.9
175°	762.7	761.1	759.6	758.1	759.6	761.1	762.7	764.2	764.4	763.2	762.1
177.5°	763.6	762.4	761.1	759.9	761.1	762.4	763.6	764.8	765.0	764.2	763.4
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1227.3	1229.0	1235.8	1242.2	1249.8	1255.4	1259.2	1263.4	1272.4	1279.6	1286.4
5°	1149.8	1152.5	1166.3	1175.9	1192.4	1206.7	1217.9	1230.1	1244.5	1264.2	1282.3
7.5°	1081.7	1091.5	1106.6	1122.2	1139.0	1157.8	1174.2	1192.6	1217.4	1244.4	1272.3
10°	1042.9	1054.1	1070.1	1088.1	1104.1	1125.9	1146.1	1167.9	1196.1	1229.1	1262.1
12.5°	1004.2	1022.6	1034.7	1056.2	1073.5	1091.4	1112.9	1141.5	1174.4	1209.1	1248.9
15°	955.7	965.8	989.2	1000.9	1025.4	1053.0	1074.3	1103.0	1134.9	1180.7	1225.4
17.5°	899.8	913.1	931.7	954.0	982.1	1003.7	1030.2	1059.7	1099.9	1145.4	1201.3
20°	863.2	874.3	897.2	921.7	951.5	974.3	1002.5	1031.2	1072.7	1121.1	1179.6
22.5°	830.4	841.2	865.3	888.1	917.0	945.0	974.4	1007.8	1047.6	1098.6	1158.3
25°	779.7	794.0	815.3	838.7	866.4	898.3	930.2	960.0	1002.5	1056.2	1120.1
27.5°	734.7	746.2	761.6	788.2	819.6	850.4	882.1	919.5	960.4	1017.2	1083.5
30°	705.7	716.4	731.8	756.3	785.5	818.5	851.5	887.6	930.2	986.6	1054.1
32.5°	682.8	690.9	704.6	726.5	753.2	787.9	820.4	857.9	902.5	958.1	1023.9
35°	648.8	655.8	661.1	681.8	705.7	737.7	770.6	810.5	853.6	906.3	972.2
37.5°	615.5	617.9	625.7	639.3	662.5	691.8	722.4	761.7	805.8	859.3	918.8
40°	595.1	596.2	601.0	613.7	634.0	661.6	691.4	730.2	772.2	822.8	881.8
42.5°	575.1	574.5	578.9	587.8	606.7	631.8	661.2	696.6	738.6	785.3	840.9
45°	543.5	543.5	542.5	549.9	565.3	589.8	614.3	648.3	683.4	729.2	776.0
47.5°	510.6	507.6	508.5	512.4	525.3	545.5	570.1	598.0	629.0	667.7	708.7
50°	489.3	485.0	483.4	487.7	499.4	516.9	540.3	564.8	594.1	628.1	663.2
52.5°	465.9	461.6	458.8	461.7	472.6	488.9	510.1	531.6	557.9	585.6	616.0
55°	429.7	424.9	423.3	424.4	432.4	445.1	463.2	482.9	502.6	525.5	546.7
57.5°	394.1	386.2	384.7	384.2	389.7	401.4	416.5	433.6	447.9	461.7	484.4
60°	370.7	361.1	357.9	357.4	361.7	371.2	385.1	402.1	412.2	421.7	441.4
62.5°	345.6	336.4	329.4	330.2	334.0	343.1	355.3	367.6	374.3	384.7	398.0
65°	306.9	295.2	289.9	288.3	290.4	297.8	307.4	315.4	322.8	327.1	339.8
67.5°	268.2	258.4	250.5	248.6	247.6	252.7	260.6	265.4	270.7	274.4	282.0
70°	240.9	232.4	222.8	219.6	219.1	223.4	230.8	231.3	238.8	240.4	248.4
72.5°	214.1	203.5	196.9	193.7	191.5	195.3	200.2	201.6	205.6	208.5	212.6
75°	172.3	164.3	158.0	153.2	151.6	153.7	153.7	156.4	159.0	160.6	165.4
77.5°	135.6	126.5	118.9	116.2	114.2	112.9	114.0	115.6	114.3	117.1	118.2
80°	110.1	100.5	94.7	93.6	90.4	87.8	87.2	88.8	86.7	87.8	90.9
82.5°	85.0	78.8	72.5	71.5	67.4	66.1	65.5	64.6	64.6	64.4	65.0
85°	50.5	46.8	42.5	39.9	38.3	35.6	35.6	34.6	33.5	32.4	33.0
87.5°	23.1	22.1	19.8	18.3	17.2	15.3	15.1	13.5	12.8	12.1	11.4
90°	13.3	12.5	11.5	10.5	9.5	8.5	7.3	5.9	4.5	3.1	1.7
92.5°	12.9	12.1	11.1	10.1	9.1	8.0	7.5	7.4	7.3	7.3	7.2
95°	13.3	12.5	12.4	12.3	12.2	12.0	14.1	18.4	22.8	27.1	31.4
97.5°	15.1	15.1	29.2	43.4	57.5	71.6	77.4	74.7	72.0	69.3	66.6
100°	22.9	25.1	42.6	60.1	77.6	95.1	102.7	100.4	98.1	95.8	93.5
102.5°	97.7	120.9	123.2	125.5	127.8	130.1	130.4	128.7	127.0	125.3	123.7
105°	179.1	178.0	177.3	176.7	176.1	175.4	174.7	174.0	173.2	172.5	171.7
107.5°	222.5	221.9	221.0	220.2	219.3	218.4	217.8	217.4	217.1	216.7	216.3
110°	251.8	251.6	250.8	250.0	249.3	248.5	247.9	247.6	247.2	246.8	246.4



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.3	280.3	280.0	279.6	279.2	278.9	278.4	277.7	277.0	276.3	275.6
115°	322.0	321.7	321.8	322.0	322.1	322.2	322.1	321.7	321.3	321.0	320.6
117.5°	364.6	364.6	364.3	364.1	363.8	363.5	363.1	362.6	362.1	361.6	361.1
120°	390.4	390.2	390.3	390.4	390.6	390.7	390.5	390.0	389.5	389.0	388.5
122.5°	416.3	416.2	416.0	415.8	415.7	415.5	415.2	414.9	414.6	414.3	414.0
125°	452.2	451.8	452.0	452.3	452.5	452.8	452.7	452.2	451.7	451.1	450.6
127.5°	488.4	488.5	487.9	487.3	486.8	486.2	485.8	485.7	485.6	485.4	485.3
130°	510.1	510.0	509.6	509.2	508.8	508.4	508.2	508.1	507.9	507.8	507.7
132.5°	531.5	531.4	530.9	530.4	530.0	529.5	529.1	528.9	528.7	528.4	528.2
135°	561.0	560.7	560.2	559.7	559.2	558.7	558.5	558.6	558.8	558.9	559.0
137.5°	589.3	589.0	588.5	587.9	587.3	586.8	586.5	586.4	586.4	586.3	586.3
140°	606.7	606.4	606.1	605.9	605.6	605.3	605.1	604.8	604.6	604.3	604.1
142.5°	623.1	622.8	622.6	622.5	622.3	622.2	621.9	621.4	621.0	620.5	620.1
145°	646.4	646.3	646.3	646.3	646.3	646.3	646.1	645.7	645.3	645.0	644.6
147.5°	666.8	666.7	666.8	667.0	667.1	667.2	666.9	666.2	665.5	664.8	664.1
150°	679.9	679.9	680.1	680.2	680.3	680.5	680.3	679.8	679.3	678.7	678.2
152.5°	691.1	690.9	691.1	691.4	691.6	691.8	691.7	691.3	690.9	690.5	690.1
155°	706.1	705.6	706.0	706.4	706.8	707.1	707.3	707.1	707.0	706.9	706.8
157.5°	719.2	718.5	718.9	719.4	719.8	720.2	720.5	720.6	720.6	720.7	720.8
160°	727.5	726.7	726.8	727.0	727.1	727.2	727.5	727.9	728.2	728.6	729.0
162.5°	734.3	733.6	733.7	733.8	733.9	734.1	734.4	734.9	735.3	735.8	736.3
165°	743.7	742.7	742.7	742.7	742.7	742.7	743.0	743.6	744.3	744.9	745.5
167.5°	750.7	749.5	749.6	749.7	749.8	749.8	750.2	750.9	751.5	752.2	752.8
170°	755.1	754.1	754.0	753.8	753.7	753.6	753.9	754.7	755.4	756.2	757.0
172.5°	757.9	756.8	756.7	756.6	756.5	756.3	756.7	757.4	758.2	758.9	759.7
175°	760.9	759.8	759.7	759.6	759.4	759.3	759.6	760.4	761.1	761.9	762.7
177.5°	762.6	761.7	761.5	761.3	761.1	760.9	761.2	761.9	762.6	763.3	764.0
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1292.4	1296.6	1302.2	1311.5	1314.9	1319.2	1325.1	1324.7	1326.4	1332.8	1346.4
5°	1297.2	1313.6	1329.6	1348.7	1369.0	1382.2	1400.3	1411.5	1422.7	1437.0	1461.5
7.5°	1299.1	1325.2	1354.5	1388.1	1418.0	1452.5	1479.4	1504.7	1527.5	1557.9	1587.0
10°	1296.1	1331.2	1369.0	1411.5	1456.7	1495.0	1529.6	1568.9	1602.4	1639.1	1672.1
12.5°	1290.6	1332.9	1383.4	1431.1	1483.9	1540.5	1583.6	1623.4	1668.0	1710.2	1761.0
15°	1278.0	1336.0	1395.0	1457.8	1528.5	1593.9	1656.1	1707.7	1755.6	1818.9	1885.4
17.5°	1262.1	1324.6	1399.1	1475.0	1548.9	1623.7	1700.7	1778.3	1838.7	1917.3	1969.3
20°	1247.2	1319.5	1396.1	1486.5	1560.4	1653.5	1730.1	1805.1	1888.0	1966.2	2028.4
22.5°	1226.3	1305.5	1386.7	1476.7	1574.0	1667.1	1755.6	1837.0	1919.9	2004.9	2080.3
25°	1199.8	1271.6	1367.9	1470.0	1566.8	1667.8	1769.4	1871.5	1960.9	2050.8	2121.0
27.5°	1154.7	1245.4	1335.0	1440.4	1548.0	1662.3	1770.9	1877.8	1971.4	2045.3	2088.8
30°	1131.8	1210.5	1307.8	1413.6	1530.1	1653.0	1766.2	1871.0	1958.2	2017.3	2034.8
32.5°	1097.7	1179.0	1274.2	1383.8	1507.1	1633.4	1751.3	1850.2	1922.9	1953.9	1932.7
35°	1047.2	1120.6	1216.8	1329.1	1457.2	1591.8	1708.3	1791.8	1829.0	1799.7	1726.9
37.5°	986.6	1059.3	1156.0	1266.2	1398.8	1535.6	1640.9	1701.0	1688.7	1615.9	1507.3
40°	944.0	1012.1	1104.1	1223.2	1352.5	1489.7	1582.2	1614.7	1580.6	1476.4	1361.0
42.5°	896.8	963.2	1055.6	1170.5	1307.4	1433.9	1514.6	1517.2	1460.2	1335.6	1219.7
45°	824.9	888.2	975.4	1095.1	1221.6	1340.8	1393.9	1367.9	1262.6	1142.4	1025.9
47.5°	753.9	808.8	894.8	1008.4	1128.6	1228.9	1255.2	1208.3	1096.1	979.4	871.5
50°	702.0	757.3	838.2	946.7	1062.6	1149.3	1162.1	1099.8	989.8	872.2	787.7
52.5°	652.2	707.1	785.0	885.4	991.6	1069.7	1070.2	998.2	888.5	783.7	705.1
55°	579.2	628.6	698.8	788.7	883.4	944.5	929.7	855.2	760.0	669.1	600.4
57.5°	508.8	551.8	616.5	691.5	774.9	825.3	800.6	728.9	643.9	566.8	514.8
60°	463.2	504.2	559.5	630.2	700.4	739.8	716.4	651.5	573.3	511.1	465.9
62.5°	419.0	453.6	506.7	568.1	633.2	662.4	641.5	577.5	509.9	453.7	417.0
65°	356.3	384.5	427.1	479.7	527.1	552.0	534.5	474.9	423.3	382.9	353.7
67.5°	297.8	319.8	352.1	394.3	434.5	448.0	432.1	390.6	346.9	314.5	293.9
70°	257.4	278.2	305.3	337.7	372.8	387.2	371.2	338.2	302.6	272.8	252.6
72.5°	222.1	238.2	261.0	288.8	316.2	330.6	319.7	288.0	257.9	235.8	218.6
75°	169.1	183.0	198.9	218.6	239.9	249.4	239.9	218.1	197.3	180.8	168.6
77.5°	123.0	130.4	142.7	157.4	170.7	178.1	169.8	155.0	142.3	131.0	125.0
80°	93.6	98.9	107.4	119.1	128.2	135.1	129.8	117.5	107.4	100.0	97.3
82.5°	68.1	71.7	77.2	85.9	92.0	95.5	93.2	84.3	80.2	73.6	70.9
85°	33.5	35.6	39.4	42.0	47.3	47.9	48.4	44.7	41.0	39.4	37.2
87.5°	12.1	12.8	14.4	15.9	17.9	18.5	18.3	18.5	17.0	16.7	15.2
90°	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3	14.1
92.5°	7.3	7.3	7.4	7.5	8.0	9.1	10.1	11.1	12.1	12.9	13.6
95°	27.1	22.8	18.4	14.1	12.0	12.2	12.3	12.4	12.5	13.3	14.1
97.5°	69.3	72.0	74.7	77.4	71.6	57.5	43.4	29.2	15.1	15.1	15.2
100°	95.8	98.1	100.4	102.7	95.1	77.6	60.1	42.6	25.1	22.9	20.8
102.5°	125.3	127.0	128.7	130.4	130.1	127.8	125.5	123.2	120.9	97.7	74.4
105°	172.5	173.2	174.0	174.7	175.4	176.1	176.7	177.3	178.0	179.1	180.3
107.5°	216.7	217.1	217.4	217.8	218.4	219.3	220.2	221.0	221.9	222.5	223.0
110°	246.8	247.2	247.6	247.9	248.5	249.3	250.0	250.8	251.6	251.8	252.1



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.3	277.0	277.7	278.4	278.9	279.2	279.6	280.0	280.3	280.3	280.2
115°	321.0	321.3	321.7	322.1	322.2	322.1	322.0	321.8	321.7	322.0	322.2
117.5°	361.6	362.1	362.6	363.1	363.5	363.8	364.1	364.3	364.6	364.6	364.5
120°	389.0	389.5	390.0	390.5	390.7	390.6	390.4	390.3	390.2	390.4	390.7
122.5°	414.3	414.6	414.9	415.2	415.5	415.7	415.8	416.0	416.2	416.3	416.5
125°	451.1	451.7	452.2	452.7	452.8	452.5	452.3	452.0	451.8	452.2	452.5
127.5°	485.4	485.6	485.7	485.8	486.2	486.8	487.3	487.9	488.5	488.4	488.4
130°	507.8	507.9	508.1	508.2	508.4	508.8	509.2	509.6	510.0	510.1	510.2
132.5°	528.4	528.7	528.9	529.1	529.5	530.0	530.4	530.9	531.4	531.5	531.7
135°	558.9	558.8	558.6	558.5	558.7	559.2	559.7	560.2	560.7	561.0	561.2
137.5°	586.3	586.4	586.4	586.5	586.8	587.3	587.9	588.5	589.0	589.3	589.6
140°	604.3	604.6	604.8	605.1	605.3	605.6	605.9	606.1	606.4	606.7	607.1
142.5°	620.5	621.0	621.4	621.9	622.2	622.3	622.5	622.6	622.8	623.1	623.3
145°	645.0	645.3	645.7	646.1	646.3	646.3	646.3	646.3	646.3	646.4	646.5
147.5°	664.8	665.5	666.2	666.9	667.2	667.1	667.0	666.8	666.7	666.8	666.9
150°	678.7	679.3	679.8	680.3	680.5	680.3	680.2	680.1	679.9	679.9	679.9
152.5°	690.5	690.9	691.3	691.7	691.8	691.6	691.4	691.1	690.9	691.1	691.3
155°	706.9	707.0	707.1	707.3	707.1	706.8	706.4	706.0	705.6	706.1	706.6
157.5°	720.7	720.6	720.6	720.5	720.2	719.8	719.4	718.9	718.5	719.2	719.8
160°	728.6	728.2	727.9	727.5	727.2	727.1	727.0	726.8	726.7	727.5	728.2
162.5°	735.8	735.3	734.9	734.4	734.1	733.9	733.8	733.7	733.6	734.3	735.1
165°	744.9	744.3	743.6	743.0	742.7	742.7	742.7	742.7	742.7	743.7	744.7
167.5°	752.2	751.5	750.9	750.2	749.8	749.8	749.7	749.6	749.5	750.7	751.8
170°	756.2	755.4	754.7	753.9	753.6	753.7	753.8	754.0	754.1	755.1	756.1
172.5°	758.9	758.2	757.4	756.7	756.3	756.5	756.6	756.7	756.8	757.9	758.9
175°	761.9	761.1	760.4	759.6	759.3	759.4	759.6	759.7	759.8	760.9	762.1
177.5°	763.3	762.6	761.9	761.2	760.9	761.1	761.3	761.5	761.7	762.6	763.4
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1353.2	1354.1	1357.9	1360.9	1361.7	1366.0	1366.4
5°	1472.1	1481.2	1498.7	1500.3	1503.0	1516.8	1506.2
7.5°	1611.5	1634.4	1649.8	1663.3	1668.2	1674.2	1673.0
10°	1700.8	1734.9	1751.9	1779.0	1780.1	1787.0	1782.7
12.5°	1790.6	1830.2	1861.2	1866.2	1889.0	1892.5	1898.5
15°	1917.8	1959.8	2002.9	2018.3	2049.7	2057.2	2068.9
17.5°	2037.4	2080.3	2110.5	2150.4	2163.3	2180.5	2168.8
20°	2102.9	2149.7	2188.0	2219.4	2232.7	2242.2	2241.2
22.5°	2142.5	2189.7	2220.7	2244.5	2256.9	2261.0	2260.7
25°	2167.2	2194.4	2203.9	2213.0	2199.2	2194.4	2196.5
27.5°	2098.3	2091.3	2066.3	2033.5	1999.5	1972.5	1957.8
30°	2003.4	1962.0	1924.2	1858.2	1824.2	1804.0	1785.9
32.5°	1869.0	1803.3	1730.6	1670.2	1631.5	1601.5	1597.0
35°	1638.6	1539.7	1450.9	1376.9	1338.6	1306.2	1298.7
37.5°	1393.1	1290.3	1210.4	1145.3	1104.1	1081.2	1059.8
40°	1230.1	1141.9	1063.1	1007.8	976.5	960.0	946.7
42.5°	1104.6	1024.0	945.7	903.6	875.2	865.1	857.3
45°	931.2	856.3	802.0	770.1	753.6	736.6	728.6
47.5°	792.4	731.4	695.6	668.5	650.9	640.8	635.7
50°	713.7	663.7	631.8	611.1	595.1	587.1	582.9
52.5°	643.9	602.9	576.1	559.6	548.8	542.9	541.2
55°	554.7	523.3	506.3	492.0	484.0	478.7	476.5
57.5°	482.2	458.0	444.2	432.4	429.3	424.8	423.3
60°	434.5	415.9	404.2	396.2	393.6	388.2	389.3
62.5°	392.4	377.2	367.2	362.6	359.1	354.6	356.1
65°	331.9	320.7	315.4	311.1	306.9	304.2	306.3
67.5°	278.5	270.8	263.6	261.1	259.0	258.6	256.3
70°	243.6	237.2	230.8	229.2	229.2	227.1	226.6
72.5°	210.0	205.3	201.0	199.9	198.2	199.0	196.8
75°	162.2	158.5	156.9	155.3	154.8	154.8	153.2
77.5°	119.9	117.1	114.6	114.6	112.6	111.9	111.7
80°	90.9	89.9	87.8	87.8	86.7	87.2	86.2
82.5°	68.4	66.9	66.5	65.6	64.1	64.2	63.2
85°	36.7	35.1	34.6	33.0	31.9	33.0	31.9
87.5°	15.7	15.5	15.1	14.3	14.0	14.0	12.8
90°	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	14.4	15.1	15.5	15.6	15.6	15.7	15.7
95°	14.8	15.6	16.0	16.2	16.3	16.4	16.5
97.5°	15.3	15.4	15.5	15.6	15.7	15.8	16.0
100°	18.6	16.5	15.5	15.6	15.7	15.8	16.0
102.5°	51.2	27.9	16.3	16.4	16.4	16.4	16.4
105°	181.4	182.5	180.8	176.3	171.7	167.1	162.6
107.5°	223.6	224.1	224.6	225.1	225.6	226.1	226.6
110°	252.3	252.6	252.9	253.3	253.6	254.0	254.4



TEST NUMBER: P332589

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	280.2	280.1	280.3	280.8	281.3	281.8	282.2
115°	322.5	322.7	322.9	322.9	322.9	322.9	322.9
117.5°	364.5	364.4	364.4	364.3	364.3	364.2	364.2
120°	390.9	391.2	391.2	390.9	390.7	390.4	390.2
122.5°	416.6	416.8	416.7	416.5	416.2	416.0	415.7
125°	452.9	453.3	453.6	453.7	453.8	453.9	454.1
127.5°	488.3	488.2	488.1	488.0	487.9	487.8	487.7
130°	510.3	510.5	510.5	510.5	510.5	510.5	510.5
132.5°	531.8	531.9	531.9	531.8	531.7	531.6	531.5
135°	561.5	561.7	562.0	562.2	562.5	562.8	563.0
137.5°	589.9	590.1	590.2	590.2	590.1	590.0	589.9
140°	607.5	607.9	608.1	608.3	608.4	608.5	608.6
142.5°	623.6	623.9	624.1	624.1	624.1	624.1	624.2
145°	646.7	646.8	647.0	647.2	647.5	647.8	648.0
147.5°	667.0	667.1	667.2	667.4	667.5	667.6	667.7
150°	679.9	679.9	680.0	680.1	680.3	680.4	680.5
152.5°	691.5	691.7	691.8	691.7	691.6	691.5	691.5
155°	707.1	707.6	707.7	707.3	706.9	706.6	706.2
157.5°	720.5	721.1	721.1	720.5	719.8	719.2	718.5
160°	729.0	729.8	729.8	729.0	728.2	727.5	726.7
162.5°	735.8	736.6	736.6	735.7	734.8	734.0	733.1
165°	745.7	746.8	746.7	745.5	744.4	743.3	742.1
167.5°	752.9	754.0	753.9	752.7	751.4	750.1	748.9
170°	757.1	758.2	758.0	756.8	755.5	754.2	753.0
172.5°	759.9	760.9	760.7	759.4	758.0	756.6	755.2
175°	763.2	764.4	764.2	762.7	761.1	759.6	758.1
177.5°	764.2	765.0	764.8	763.6	762.4	761.1	759.9
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7

(END OF REPORT)