

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332590

Luminaire Tested: **S124DIP-S795D590U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332590
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S795D590U835-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5590.4 lumens
Efficiency: N/A
Efficacy: 138.7 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68	63
1	101	97	93	89	95	91	88	85	80	78	75	70	68	67	61	60	58	54
2	92	85	79	74	86	80	74	70	71	66	63	62	59	56	54	52	50	46
3	84	75	67	62	79	71	64	59	62	57	53	55	51	48	48	45	43	39
4	77	67	59	52	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	59	51	45	67	56	49	43	50	44	40	44	40	36	39	35	32	29
6	66	54	45	39	62	51	43	38	45	39	35	40	35	32	36	32	29	26
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	32	29	26	23
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10365	10365	10365	10365
5°	12206	10391	9172	10391
10°	14614	10346	8257	10346
15°	17291	10242	7583	10242
20°	19254	10134	6981	10134
25°	19565	9977	6566	9977
30°	16648	9826	6435	9826
35°	12799	9581	6436	9581
40°	9977	9293	6558	9293
45°	8318	8859	6667	8859
50°	7321	8329	6894	8329
55°	6707	7695	7171	7695
60°	6286	7127	7505	7127
65°	5851	6491	7782	6491
70°	5349	5863	7959	5863
75°	4779	5159	7863	5159
80°	4007	4226	7615	4226
85°	2955	3057	7290	3057



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.2
10°-20°	385.5	6.9
20°-30°	611.3	10.9
30°-40°	680.3	12.2
40°-50°	619.3	11.1
50°-60°	506.1	9.1
60°-70°	361.3	6.5
70°-80°	198.9	3.6
80°-90°	56.5	1.0
90°-100°	48.6	0.9
100°-110°	144.1	2.6
110°-120°	244.6	4.4
120°-130°	322.5	5.8
130°-140°	362.2	6.5
140°-150°	355.9	6.4
150°-160°	299.3	5.4
160°-170°	199.1	3.6
170°-180°	69.7	1.2
0°-30°	1121.9	20.1
0°-40°	1802.3	32.2
0°-60°	2927.7	52.4
0°-90°	3544.4	63.4
90°-120°	437.3	7.8
90°-150°	1477.8	26.4
90°-180°	2046.0	36.6
0°-180°	5590.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1506	1282	1132	1282	1506	153
15°	2069	1225	907	1225	2069	585
25°	2196	1120	737	1120	2196	968
35°	1299	972	653	972	1299	824
45°	729	776	584	776	729	574
55°	476	547	510	547	476	430
65°	306	340	407	340	306	303
75°	153	165	252	165	153	163
85°	32	33	79	33	32	39
90°	17	2	17	2	17	10
95°	45	34	45	34	45	47
105°	139	133	139	133	139	147
115°	246	249	246	249	246	244
125°	359	362	359	362	359	321
135°	468	467	468	467	468	361
145°	568	568	568	568	568	355
155°	650	650	650	650	650	299
165°	706	708	706	708	706	199
175°	733	736	733	736	733	70
180°	738	738	738	738	738	



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1366.4	1366.0	1361.7	1360.9	1357.9	1354.1	1353.2	1346.4	1332.8	1326.4	1324.7
5°	1506.2	1516.8	1503.0	1500.3	1498.7	1481.2	1472.1	1461.5	1437.0	1422.7	1411.5
7.5°	1673.0	1674.2	1668.2	1663.3	1649.8	1634.4	1611.5	1587.0	1557.9	1527.5	1504.7
10°	1782.7	1787.0	1780.1	1779.0	1751.9	1734.9	1700.8	1672.1	1639.1	1602.4	1568.9
12.5°	1898.5	1892.5	1889.0	1866.2	1861.2	1830.2	1790.6	1761.0	1710.2	1668.0	1623.4
15°	2068.9	2057.2	2049.7	2018.3	2002.9	1959.8	1917.8	1885.4	1818.9	1755.6	1707.7
17.5°	2168.8	2180.5	2163.3	2150.4	2110.5	2080.3	2037.4	1969.3	1917.3	1838.7	1778.3
20°	2241.2	2242.2	2232.7	2219.4	2188.0	2149.7	2102.9	2028.4	1966.2	1888.0	1805.1
22.5°	2260.7	2261.0	2256.9	2244.5	2220.7	2189.7	2142.5	2080.3	2004.9	1919.9	1837.0
25°	2196.5	2194.4	2199.2	2213.0	2203.9	2194.4	2167.2	2121.0	2050.8	1960.9	1871.5
27.5°	1957.8	1972.5	1999.5	2033.5	2066.3	2091.3	2098.3	2088.8	2045.3	1971.4	1877.8
30°	1785.9	1804.0	1824.2	1858.2	1924.2	1962.0	2003.4	2034.8	2017.3	1958.2	1871.0
32.5°	1597.0	1601.5	1631.5	1670.2	1730.6	1803.3	1869.0	1932.7	1953.9	1922.9	1850.2
35°	1298.7	1306.2	1338.6	1376.9	1450.9	1539.7	1638.6	1726.9	1799.7	1829.0	1791.8
37.5°	1059.8	1081.2	1104.1	1145.3	1210.4	1290.3	1393.1	1507.3	1615.9	1688.7	1701.0
40°	946.7	960.0	976.5	1007.8	1063.1	1141.9	1230.1	1361.0	1476.4	1580.6	1614.7
42.5°	857.3	865.1	875.2	903.6	945.7	1024.0	1104.6	1219.7	1335.6	1460.2	1517.2
45°	728.6	736.6	753.6	770.1	802.0	856.3	931.2	1025.9	1142.4	1262.6	1367.9
47.5°	635.7	640.8	650.9	668.5	695.6	731.4	792.4	871.5	979.4	1096.1	1208.3
50°	582.9	587.1	595.1	611.1	631.8	663.7	713.7	787.7	872.2	989.8	1099.8
52.5°	541.2	542.9	548.8	559.6	576.1	602.9	643.9	705.1	783.7	888.5	998.2
55°	476.5	478.7	484.0	492.0	506.3	523.3	554.7	600.4	669.1	760.0	855.2
57.5°	423.3	424.8	429.3	432.4	444.2	458.0	482.2	514.8	566.8	643.9	728.9
60°	389.3	388.2	393.6	396.2	404.2	415.9	434.5	465.9	511.1	573.3	651.5
62.5°	356.1	354.6	359.1	362.6	367.2	377.2	392.4	417.0	453.7	509.9	577.5
65°	306.3	304.2	306.9	311.1	315.4	320.7	331.9	353.7	382.9	423.3	474.9
67.5°	256.3	258.6	259.0	261.1	263.6	270.8	278.5	293.9	314.5	346.9	390.6
70°	226.6	227.1	229.2	229.2	230.8	237.2	243.6	252.6	272.8	302.6	338.2
72.5°	196.8	199.0	198.2	199.9	201.0	205.3	210.0	218.6	235.8	257.9	288.0
75°	153.2	154.8	154.8	155.3	156.9	158.5	162.2	168.6	180.8	197.3	218.1
77.5°	111.7	111.9	112.6	114.6	114.6	117.1	119.9	125.0	131.0	142.3	155.0
80°	86.2	87.2	86.7	87.8	87.8	89.9	90.9	97.3	100.0	107.4	117.5
82.5°	63.2	64.2	64.1	65.6	66.5	66.9	68.4	70.9	73.6	80.2	84.3
85°	31.9	33.0	31.9	33.0	34.6	35.1	36.7	37.2	39.4	41.0	44.7
87.5°	12.8	14.0	14.0	14.3	15.1	15.5	15.7	15.2	16.7	17.0	18.5
90°	17.1	16.9	16.6	16.4	16.1	15.6	14.8	14.1	13.3	12.5	11.5
92.5°	25.3	25.2	25.0	24.9	24.7	24.4	24.0	23.5	23.0	22.6	21.9
95°	45.1	45.1	45.1	45.1	45.1	44.9	44.5	44.1	43.7	43.3	42.5
97.5°	70.6	70.6	70.6	70.6	70.6	70.4	69.9	69.5	69.0	68.6	67.5
100°	88.4	88.4	88.4	88.4	88.4	88.3	88.0	87.8	87.5	87.3	86.1
102.5°	108.5	108.4	108.3	108.2	108.1	107.8	107.5	107.1	106.8	106.4	105.4
105°	139.2	138.8	138.4	138.0	137.6	137.3	136.9	136.5	136.1	135.7	135.2
107.5°	169.1	169.1	169.1	169.1	169.2	169.0	168.6	168.3	167.9	167.6	167.5
110°	190.5	190.1	189.7	189.4	189.0	188.9	189.2	189.4	189.7	189.9	190.1



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	212.4	212.3	212.2	212.2	212.1	212.1	212.1	212.2	212.2	212.3	212.5
115°	246.4	246.5	246.6	246.8	246.9	247.0	247.2	247.3	247.4	247.5	247.8
117.5°	278.8	279.0	279.3	279.5	279.8	280.1	280.6	281.0	281.4	281.9	282.0
120°	303.4	303.2	302.9	302.7	302.4	302.6	303.2	303.9	304.5	305.1	305.5
122.5°	324.0	324.4	324.9	325.3	325.8	326.2	326.7	327.1	327.5	328.0	328.1
125°	359.3	359.6	359.8	360.1	360.3	360.6	360.8	361.1	361.3	361.6	361.7
127.5°	392.1	392.3	392.5	392.7	392.9	393.1	393.4	393.6	393.9	394.1	394.3
130°	413.5	414.0	414.5	415.0	415.5	415.9	416.2	416.4	416.7	416.9	416.9
132.5°	436.3	436.5	436.7	436.9	437.1	437.4	437.6	437.9	438.1	438.4	438.5
135°	467.7	468.1	468.4	468.8	469.2	469.5	469.8	470.0	470.3	470.5	470.5
137.5°	500.7	500.6	500.5	500.4	500.3	500.5	500.8	501.1	501.5	501.8	501.6
140°	520.7	520.9	521.0	521.1	521.2	521.4	521.5	521.6	521.7	521.9	521.9
142.5°	540.8	540.8	540.9	540.9	540.9	540.9	541.0	541.0	541.0	541.0	541.1
145°	568.1	568.4	568.8	569.2	569.6	569.8	570.0	570.1	570.2	570.3	570.2
147.5°	595.7	595.8	595.9	596.1	596.2	596.3	596.4	596.5	596.6	596.7	596.8
150°	612.6	612.7	612.8	612.9	613.1	613.1	613.1	613.1	613.1	613.1	613.1
152.5°	628.1	628.4	628.7	629.1	629.4	629.4	629.1	628.8	628.5	628.2	628.1
155°	649.6	650.1	650.6	651.1	651.7	651.7	651.1	650.6	650.1	649.6	649.8
157.5°	668.9	669.3	669.8	670.2	670.6	670.7	670.3	669.9	669.5	669.1	669.2
160°	679.9	680.5	681.1	681.8	682.4	682.5	682.1	681.8	681.4	681.0	681.1
162.5°	691.3	691.9	692.5	693.2	693.8	693.8	693.1	692.4	691.7	691.0	691.2
165°	706.1	706.6	707.1	707.6	708.1	708.0	707.2	706.5	705.7	705.0	705.2
167.5°	716.7	717.5	718.3	719.1	719.8	719.9	719.1	718.3	717.6	716.8	716.8
170°	722.6	723.5	724.4	725.3	726.2	726.2	725.5	724.7	724.0	723.2	723.1
172.5°	727.7	728.5	729.4	730.3	731.2	731.2	730.4	729.5	728.6	727.8	727.7
175°	732.9	733.8	734.7	735.6	736.4	736.4	735.6	734.7	733.8	732.9	733.0
177.5°	735.6	736.4	737.3	738.1	738.9	738.9	738.2	737.5	736.8	736.1	736.1
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1325.1	1319.2	1314.9	1311.5	1302.2	1296.6	1292.4	1286.4	1279.6	1272.4	1263.4
5°	1400.3	1382.2	1369.0	1348.7	1329.6	1313.6	1297.2	1282.3	1264.2	1244.5	1230.1
7.5°	1479.4	1452.5	1418.0	1388.1	1354.5	1325.2	1299.1	1272.3	1244.4	1217.4	1192.6
10°	1529.6	1495.0	1456.7	1411.5	1369.0	1331.2	1296.1	1262.1	1229.1	1196.1	1167.9
12.5°	1583.6	1540.5	1483.9	1431.1	1383.4	1332.9	1290.6	1248.9	1209.1	1174.4	1141.5
15°	1656.1	1593.9	1528.5	1457.8	1395.0	1336.0	1278.0	1225.4	1180.7	1134.9	1103.0
17.5°	1700.7	1623.7	1548.9	1475.0	1399.1	1324.6	1262.1	1201.3	1145.4	1099.9	1059.7
20°	1730.1	1653.5	1560.4	1486.5	1396.1	1319.5	1247.2	1179.6	1121.1	1072.7	1031.2
22.5°	1755.6	1667.1	1574.0	1476.7	1386.7	1305.5	1226.3	1158.3	1098.6	1047.6	1007.8
25°	1769.4	1667.8	1566.8	1470.0	1367.9	1271.6	1199.8	1120.1	1056.2	1002.5	960.0
27.5°	1770.9	1662.3	1548.0	1440.4	1335.0	1245.4	1154.7	1083.5	1017.2	960.4	919.5
30°	1766.2	1653.0	1530.1	1413.6	1307.8	1210.5	1131.8	1054.1	986.6	930.2	887.6
32.5°	1751.3	1633.4	1507.1	1383.8	1274.2	1179.0	1097.7	1023.9	958.1	902.5	857.9
35°	1708.3	1591.8	1457.2	1329.1	1216.8	1120.6	1047.2	972.2	906.3	853.6	810.5
37.5°	1640.9	1535.6	1398.8	1266.2	1156.0	1059.3	986.6	918.8	859.3	805.8	761.7
40°	1582.2	1489.7	1352.5	1223.2	1104.1	1012.1	944.0	881.8	822.8	772.2	730.2
42.5°	1514.6	1433.9	1307.4	1170.5	1055.6	963.2	896.8	840.9	785.3	738.6	696.6
45°	1393.9	1340.8	1221.6	1095.1	975.4	888.2	824.9	776.0	729.2	683.4	648.3
47.5°	1255.2	1228.9	1128.6	1008.4	894.8	808.8	753.9	708.7	667.7	629.0	598.0
50°	1162.1	1149.3	1062.6	946.7	838.2	757.3	702.0	663.2	628.1	594.1	564.8
52.5°	1070.2	1069.7	991.6	885.4	785.0	707.1	652.2	616.0	585.6	557.9	531.6
55°	929.7	944.5	883.4	788.7	698.8	628.6	579.2	546.7	525.5	502.6	482.9
57.5°	800.6	825.3	774.9	691.5	616.5	551.8	508.8	484.4	461.7	447.9	433.6
60°	716.4	739.8	700.4	630.2	559.5	504.2	463.2	441.4	421.7	412.2	402.1
62.5°	641.5	662.4	633.2	568.1	506.7	453.6	419.0	398.0	384.7	374.3	367.6
65°	534.5	552.0	527.1	479.7	427.1	384.5	356.3	339.8	327.1	322.8	315.4
67.5°	432.1	448.0	434.5	394.3	352.1	319.8	297.8	282.0	274.4	270.7	265.4
70°	371.2	387.2	372.8	337.7	305.3	278.2	257.4	248.4	240.4	238.8	231.3
72.5°	319.7	330.6	316.2	288.8	261.0	238.2	222.1	212.6	208.5	205.6	201.6
75°	239.9	249.4	239.9	218.6	198.9	183.0	169.1	165.4	160.6	159.0	156.4
77.5°	169.8	178.1	170.7	157.4	142.7	130.4	123.0	118.2	117.1	114.3	115.6
80°	129.8	135.1	128.2	119.1	107.4	98.9	93.6	90.9	87.8	86.7	88.8
82.5°	93.2	95.5	92.0	85.9	77.2	71.7	68.1	65.0	64.4	64.6	64.6
85°	48.4	47.9	47.3	42.0	39.4	35.6	33.5	33.0	32.4	33.5	34.6
87.5°	18.3	18.5	17.9	15.9	14.4	12.8	12.1	11.4	12.1	12.8	13.5
90°	10.5	9.5	8.5	7.3	5.9	4.5	3.1	1.7	3.1	4.5	5.9
92.5°	21.2	20.5	19.7	18.6	17.0	15.4	13.8	12.2	13.8	15.4	17.0
95°	41.6	40.7	39.8	38.8	37.6	36.5	35.4	34.2	35.4	36.5	37.6
97.5°	66.5	65.4	64.4	63.4	62.5	61.6	60.7	59.8	60.7	61.6	62.5
100°	85.0	83.8	82.7	81.9	81.4	80.9	80.4	79.8	80.4	80.9	81.4
102.5°	104.3	103.3	102.3	101.6	101.4	101.2	101.0	100.8	101.0	101.2	101.4
105°	134.7	134.2	133.7	133.4	133.3	133.1	133.0	132.9	133.0	133.1	133.3
107.5°	167.4	167.3	167.3	167.2	167.0	166.8	166.7	166.5	166.7	166.8	167.0
110°	190.2	190.3	190.4	190.4	190.1	189.9	189.6	189.4	189.6	189.9	190.1



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	212.7	213.0	213.2	213.3	213.2	213.2	213.1	213.1	213.1	213.2	213.2
115°	248.0	248.3	248.5	248.7	248.7	248.7	248.7	248.7	248.7	248.7	248.7
117.5°	282.2	282.4	282.6	282.6	282.5	282.4	282.3	282.2	282.3	282.4	282.5
120°	305.9	306.3	306.7	306.6	306.1	305.6	305.1	304.6	305.1	305.6	306.1
122.5°	328.3	328.5	328.7	328.6	328.4	328.2	328.0	327.8	328.0	328.2	328.4
125°	361.9	362.0	362.1	362.2	362.2	362.2	362.2	362.2	362.2	362.2	362.2
127.5°	394.5	394.7	394.9	394.8	394.5	394.1	393.7	393.3	393.7	394.1	394.5
130°	416.9	416.9	416.9	416.7	416.4	416.0	415.6	415.2	415.6	416.0	416.4
132.5°	438.6	438.7	438.8	438.7	438.4	438.1	437.9	437.6	437.9	438.1	438.4
135°	470.5	470.5	470.5	470.2	469.4	468.6	467.9	467.1	467.9	468.6	469.4
137.5°	501.4	501.2	501.0	500.7	500.3	500.0	499.6	499.3	499.6	500.0	500.3
140°	521.9	521.9	521.9	521.7	521.5	521.2	521.0	520.7	521.0	521.2	521.5
142.5°	541.2	541.3	541.4	541.4	541.1	540.9	540.6	540.3	540.6	540.9	541.1
145°	570.1	570.0	569.8	569.5	569.0	568.5	568.0	567.5	568.0	568.5	569.0
147.5°	596.9	597.0	597.1	596.9	596.2	595.6	595.0	594.4	595.0	595.6	596.2
150°	613.1	613.1	613.1	612.9	612.4	611.9	611.4	610.8	611.4	611.9	612.4
152.5°	628.0	627.9	627.8	627.6	627.3	627.0	626.7	626.4	626.7	627.0	627.3
155°	649.9	650.0	650.1	650.2	650.2	650.2	650.2	650.2	650.2	650.2	650.2
157.5°	669.2	669.2	669.2	669.4	669.6	669.8	670.0	670.3	670.0	669.8	669.6
160°	681.3	681.4	681.5	681.6	681.8	681.9	682.0	682.1	682.0	681.9	681.8
162.5°	691.3	691.4	691.5	691.8	692.1	692.4	692.8	693.1	692.8	692.4	692.1
165°	705.5	705.7	706.0	706.3	706.7	707.0	707.4	707.8	707.4	707.0	706.7
167.5°	716.8	716.7	716.7	717.0	717.5	718.0	718.6	719.1	718.6	718.0	717.5
170°	722.9	722.8	722.7	722.9	723.6	724.2	724.9	725.5	724.9	724.2	723.6
172.5°	727.7	727.7	727.7	727.9	728.5	729.0	729.5	730.0	729.5	729.0	728.5
175°	733.2	733.3	733.4	733.8	734.4	735.1	735.7	736.3	735.7	735.1	734.4
177.5°	736.1	736.1	736.1	736.3	736.9	737.4	737.9	738.4	737.9	737.4	736.9
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1259.2	1255.4	1249.8	1242.2	1235.8	1229.0	1227.3	1224.7	1229.8	1225.6	1224.3
5°	1217.9	1206.7	1192.4	1175.9	1166.3	1152.5	1149.8	1144.5	1139.2	1138.7	1133.3
7.5°	1174.2	1157.8	1139.0	1122.2	1106.6	1091.5	1081.7	1079.5	1071.7	1067.1	1061.8
10°	1146.1	1125.9	1104.1	1088.1	1070.1	1054.1	1042.9	1036.6	1031.2	1025.4	1020.1
12.5°	1112.9	1091.4	1073.5	1056.2	1034.7	1022.6	1004.2	993.2	992.1	992.2	978.4
15°	1074.3	1053.0	1025.4	1000.9	989.2	965.8	955.7	942.9	935.0	927.0	920.6
17.5°	1030.2	1003.7	982.1	954.0	931.7	913.1	899.8	892.1	880.1	868.8	860.6
20°	1002.5	974.3	951.5	921.7	897.2	874.3	863.2	852.5	843.5	833.9	824.9
22.5°	974.4	945.0	917.0	888.1	865.3	841.2	830.4	815.9	807.3	802.0	793.0
25°	930.2	898.3	866.4	838.7	815.3	794.0	779.7	768.5	758.9	754.7	748.8
27.5°	882.1	850.4	819.6	788.2	761.6	746.2	734.7	726.3	720.7	715.1	712.5
30°	851.5	818.5	785.5	756.3	731.8	716.4	705.7	699.9	695.6	693.0	690.3
32.5°	820.4	787.9	753.2	726.5	704.6	690.9	682.8	676.9	674.8	673.8	672.9
35°	770.6	737.7	705.7	681.8	661.1	655.8	648.8	645.7	644.6	648.3	649.9
37.5°	722.4	691.8	662.5	639.3	625.7	617.9	615.5	615.7	619.5	622.8	626.6
40°	691.4	661.6	634.0	613.7	601.0	596.2	595.1	597.8	602.0	605.8	610.0
42.5°	661.2	631.8	606.7	587.8	578.9	574.5	575.1	577.8	583.7	588.3	594.7
45°	614.3	589.8	565.3	549.9	542.5	543.5	543.5	548.3	554.2	561.1	568.0
47.5°	570.1	545.5	525.3	512.4	508.5	507.6	510.6	516.8	525.2	533.8	543.4
50°	540.3	516.9	499.4	487.7	483.4	485.0	489.3	495.1	505.2	515.9	526.0
52.5°	510.1	488.9	472.6	461.7	458.8	461.6	465.9	475.1	484.0	495.5	507.7
55°	463.2	445.1	432.4	424.4	423.3	424.9	429.7	439.8	452.6	467.0	478.7
57.5°	416.5	401.4	389.7	384.2	384.7	386.2	394.1	406.1	419.7	435.0	450.1
60°	385.1	371.2	361.7	357.4	357.9	361.1	370.7	381.9	398.9	413.8	429.7
62.5°	355.3	343.1	334.0	330.2	329.4	336.4	345.6	357.2	374.2	390.8	408.0
65°	307.4	297.8	290.4	288.3	289.9	295.2	306.9	322.3	336.7	354.2	372.3
67.5°	260.6	252.7	247.6	248.6	250.5	258.4	268.2	281.4	297.7	315.9	333.8
70°	230.8	223.4	219.1	219.6	222.8	232.4	240.9	254.2	271.8	290.4	305.3
72.5°	200.2	195.3	191.5	193.7	196.9	203.5	214.1	227.4	242.8	260.2	275.9
75°	153.7	153.7	151.6	153.2	158.0	164.3	172.3	186.1	201.6	215.4	228.2
77.5°	114.0	112.9	114.2	116.2	118.9	126.5	135.6	145.5	157.1	170.9	181.5
80°	87.2	87.8	90.4	93.6	94.7	100.5	110.1	119.1	128.2	139.9	150.0
82.5°	65.5	66.1	67.4	71.5	72.5	78.8	85.0	94.0	102.2	110.1	118.5
85°	35.6	35.6	38.3	39.9	42.5	46.8	50.5	55.8	63.3	68.6	76.6
87.5°	15.1	15.3	17.2	18.3	19.8	22.1	23.1	27.9	29.8	32.0	36.0
90°	7.3	8.5	9.5	10.5	11.5	12.5	13.3	14.1	14.8	15.6	16.1
92.5°	18.6	19.7	20.5	21.2	21.9	22.6	23.0	23.5	24.0	24.4	24.7
95°	38.8	39.8	40.7	41.6	42.5	43.3	43.7	44.1	44.5	44.9	45.1
97.5°	63.4	64.4	65.4	66.5	67.5	68.6	69.0	69.5	69.9	70.4	70.6
100°	81.9	82.7	83.8	85.0	86.1	87.3	87.5	87.8	88.0	88.3	88.4
102.5°	101.6	102.3	103.3	104.3	105.4	106.4	106.8	107.1	107.5	107.8	108.1
105°	133.4	133.7	134.2	134.7	135.2	135.7	136.1	136.5	136.9	137.3	137.6
107.5°	167.2	167.3	167.3	167.4	167.5	167.6	167.9	168.3	168.6	169.0	169.2
110°	190.4	190.4	190.3	190.2	190.1	189.9	189.7	189.4	189.2	188.9	189.0



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	213.3	213.2	213.0	212.7	212.5	212.3	212.2	212.2	212.1	212.1	212.1
115°	248.7	248.5	248.3	248.0	247.8	247.5	247.4	247.3	247.2	247.0	246.9
117.5°	282.6	282.6	282.4	282.2	282.0	281.9	281.4	281.0	280.6	280.1	279.8
120°	306.6	306.7	306.3	305.9	305.5	305.1	304.5	303.9	303.2	302.6	302.4
122.5°	328.6	328.7	328.5	328.3	328.1	328.0	327.5	327.1	326.7	326.2	325.8
125°	362.2	362.1	362.0	361.9	361.7	361.6	361.3	361.1	360.8	360.6	360.3
127.5°	394.8	394.9	394.7	394.5	394.3	394.1	393.9	393.6	393.4	393.1	392.9
130°	416.7	416.9	416.9	416.9	416.9	416.9	416.7	416.4	416.2	415.9	415.5
132.5°	438.7	438.8	438.7	438.6	438.5	438.4	438.1	437.9	437.6	437.4	437.1
135°	470.2	470.5	470.5	470.5	470.5	470.5	470.3	470.0	469.8	469.5	469.2
137.5°	500.7	501.0	501.2	501.4	501.6	501.8	501.5	501.1	500.8	500.5	500.3
140°	521.7	521.9	521.9	521.9	521.9	521.9	521.7	521.6	521.5	521.4	521.2
142.5°	541.4	541.4	541.3	541.2	541.1	541.0	541.0	541.0	541.0	540.9	540.9
145°	569.5	569.8	570.0	570.1	570.2	570.3	570.2	570.1	570.0	569.8	569.6
147.5°	596.9	597.1	597.0	596.9	596.8	596.7	596.6	596.5	596.4	596.3	596.2
150°	612.9	613.1	613.1	613.1	613.1	613.1	613.1	613.1	613.1	613.1	613.1
152.5°	627.6	627.8	627.9	628.0	628.1	628.2	628.5	628.8	629.1	629.4	629.4
155°	650.2	650.1	650.0	649.9	649.8	649.6	650.1	650.6	651.1	651.7	651.7
157.5°	669.4	669.2	669.2	669.2	669.2	669.1	669.5	669.9	670.3	670.7	670.6
160°	681.6	681.5	681.4	681.3	681.1	681.0	681.4	681.8	682.1	682.5	682.4
162.5°	691.8	691.5	691.4	691.3	691.2	691.0	691.7	692.4	693.1	693.8	693.8
165°	706.3	706.0	705.7	705.5	705.2	705.0	705.7	706.5	707.2	708.0	708.1
167.5°	717.0	716.7	716.7	716.8	716.8	716.8	717.6	718.3	719.1	719.9	719.8
170°	722.9	722.7	722.8	722.9	723.1	723.2	724.0	724.7	725.5	726.2	726.2
172.5°	727.9	727.7	727.7	727.7	727.7	727.8	728.6	729.5	730.4	731.2	731.2
175°	733.8	733.4	733.3	733.2	733.0	732.9	733.8	734.7	735.6	736.4	736.4
177.5°	736.3	736.1	736.1	736.1	736.1	736.1	736.8	737.5	738.2	738.9	738.9
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1223.4	1222.6	1219.6	1219.2	1219.6	1222.6	1223.4	1224.3	1225.6	1229.8	1224.7
5°	1130.2	1127.5	1125.9	1131.8	1125.9	1127.5	1130.2	1133.3	1138.7	1139.2	1144.5
7.5°	1059.8	1057.7	1053.0	1051.6	1053.0	1057.7	1059.8	1061.8	1067.1	1071.7	1079.5
10°	1014.7	1012.6	1008.4	1007.3	1008.4	1012.6	1014.7	1020.1	1025.4	1031.2	1036.6
12.5°	971.3	967.1	966.2	967.3	966.2	967.1	971.3	978.4	992.2	992.1	993.2
15°	913.7	911.6	905.7	907.3	905.7	911.6	913.7	920.6	927.0	935.0	942.9
17.5°	856.9	854.3	847.2	853.5	847.2	854.3	856.9	860.6	868.8	880.1	892.1
20°	821.2	816.9	813.2	812.6	813.2	816.9	821.2	824.9	833.9	843.5	852.5
22.5°	787.1	783.3	783.0	779.5	783.0	783.3	787.1	793.0	802.0	807.3	815.9
25°	744.6	740.9	739.8	737.1	739.8	740.9	744.6	748.8	754.7	758.9	768.5
27.5°	711.9	710.1	708.2	709.0	708.2	710.1	711.9	712.5	715.1	720.7	726.3
30°	691.9	691.4	690.3	690.3	690.3	691.4	691.9	690.3	693.0	695.6	699.9
32.5°	675.3	675.2	675.9	675.9	675.9	675.2	675.3	672.9	673.8	674.8	676.9
35°	652.0	653.6	654.7	653.1	654.7	653.6	652.0	649.9	648.3	644.6	645.7
37.5°	631.0	632.6	634.1	635.9	634.1	632.6	631.0	626.6	622.8	619.5	615.7
40°	614.8	618.5	619.6	622.3	619.6	618.5	614.8	610.0	605.8	602.0	597.8
42.5°	599.5	603.6	606.4	606.9	606.4	603.6	599.5	594.7	588.3	583.7	577.8
45°	576.0	580.2	584.0	584.0	584.0	580.2	576.0	568.0	561.1	554.2	548.3
47.5°	551.6	557.8	561.5	562.5	561.5	557.8	551.6	543.4	533.8	525.2	516.8
50°	535.0	542.5	546.2	548.9	546.2	542.5	535.0	526.0	515.9	505.2	495.1
52.5°	518.9	526.3	531.3	532.7	531.3	526.3	518.9	507.7	495.5	484.0	475.1
55°	490.9	501.5	507.4	509.5	507.4	501.5	490.9	478.7	467.0	452.6	439.8
57.5°	464.5	474.3	481.1	482.7	481.1	474.3	464.5	450.1	435.0	419.7	406.1
60°	444.1	454.7	463.2	464.8	463.2	454.7	444.1	429.7	413.8	398.9	381.9
62.5°	423.2	434.3	442.0	446.1	442.0	434.3	423.2	408.0	390.8	374.2	357.2
65°	387.2	398.3	405.8	407.4	405.8	398.3	387.2	372.3	354.2	336.7	322.3
67.5°	347.8	359.0	363.9	367.0	363.9	359.0	347.8	333.8	315.9	297.7	281.4
70°	320.2	329.2	334.5	337.2	334.5	329.2	320.2	305.3	290.4	271.8	254.2
72.5°	288.7	298.1	304.3	304.8	304.3	298.1	288.7	275.9	260.2	242.8	227.4
75°	240.4	248.9	252.1	252.1	252.1	248.9	240.4	228.2	215.4	201.6	186.1
77.5°	190.3	194.7	198.7	199.5	198.7	194.7	190.3	181.5	170.9	157.1	145.5
80°	158.0	160.6	163.8	163.8	163.8	160.6	158.0	150.0	139.9	128.2	119.1
82.5°	124.8	127.0	130.2	129.8	130.2	127.0	124.8	118.5	110.1	102.2	94.0
85°	75.5	80.3	79.8	78.7	79.8	80.3	75.5	76.6	68.6	63.3	55.8
87.5°	37.3	37.8	39.1	40.0	39.1	37.8	37.3	36.0	32.0	29.8	27.9
90°	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	15.6	14.8	14.1
92.5°	24.9	25.0	25.2	25.3	25.2	25.0	24.9	24.7	24.4	24.0	23.5
95°	45.1	45.1	45.1	45.1	45.1	45.1	45.1	45.1	44.9	44.5	44.1
97.5°	70.6	70.6	70.6	70.6	70.6	70.6	70.6	70.6	70.4	69.9	69.5
100°	88.4	88.4	88.4	88.4	88.4	88.4	88.4	88.4	88.3	88.0	87.8
102.5°	108.2	108.3	108.4	108.5	108.4	108.3	108.2	108.1	107.8	107.5	107.1
105°	138.0	138.4	138.8	139.2	138.8	138.4	138.0	137.6	137.3	136.9	136.5
107.5°	169.1	169.1	169.1	169.1	169.1	169.1	169.1	169.2	169.0	168.6	168.3
110°	189.4	189.7	190.1	190.5	190.1	189.7	189.4	189.0	188.9	189.2	189.4



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	212.2	212.2	212.3	212.4	212.3	212.2	212.2	212.1	212.1	212.1	212.2
115°	246.8	246.6	246.5	246.4	246.5	246.6	246.8	246.9	247.0	247.2	247.3
117.5°	279.5	279.3	279.0	278.8	279.0	279.3	279.5	279.8	280.1	280.6	281.0
120°	302.7	302.9	303.2	303.4	303.2	302.9	302.7	302.4	302.6	303.2	303.9
122.5°	325.3	324.9	324.4	324.0	324.4	324.9	325.3	325.8	326.2	326.7	327.1
125°	360.1	359.8	359.6	359.3	359.6	359.8	360.1	360.3	360.6	360.8	361.1
127.5°	392.7	392.5	392.3	392.1	392.3	392.5	392.7	392.9	393.1	393.4	393.6
130°	415.0	414.5	414.0	413.5	414.0	414.5	415.0	415.5	415.9	416.2	416.4
132.5°	436.9	436.7	436.5	436.3	436.5	436.7	436.9	437.1	437.4	437.6	437.9
135°	468.8	468.4	468.1	467.7	468.1	468.4	468.8	469.2	469.5	469.8	470.0
137.5°	500.4	500.5	500.6	500.7	500.6	500.5	500.4	500.3	500.5	500.8	501.1
140°	521.1	521.0	520.9	520.7	520.9	521.0	521.1	521.2	521.4	521.5	521.6
142.5°	540.9	540.9	540.8	540.8	540.8	540.9	540.9	540.9	540.9	541.0	541.0
145°	569.2	568.8	568.4	568.1	568.4	568.8	569.2	569.6	569.8	570.0	570.1
147.5°	596.1	595.9	595.8	595.7	595.8	595.9	596.1	596.2	596.3	596.4	596.5
150°	612.9	612.8	612.7	612.6	612.7	612.8	612.9	613.1	613.1	613.1	613.1
152.5°	629.1	628.7	628.4	628.1	628.4	628.7	629.1	629.4	629.4	629.1	628.8
155°	651.1	650.6	650.1	649.6	650.1	650.6	651.1	651.7	651.7	651.1	650.6
157.5°	670.2	669.8	669.3	668.9	669.3	669.8	670.2	670.6	670.7	670.3	669.9
160°	681.8	681.1	680.5	679.9	680.5	681.1	681.8	682.4	682.5	682.1	681.8
162.5°	693.2	692.5	691.9	691.3	691.9	692.5	693.2	693.8	693.8	693.1	692.4
165°	707.6	707.1	706.6	706.1	706.6	707.1	707.6	708.1	708.0	707.2	706.5
167.5°	719.1	718.3	717.5	716.7	717.5	718.3	719.1	719.8	719.9	719.1	718.3
170°	725.3	724.4	723.5	722.6	723.5	724.4	725.3	726.2	726.2	725.5	724.7
172.5°	730.3	729.4	728.5	727.7	728.5	729.4	730.3	731.2	731.2	730.4	729.5
175°	735.6	734.7	733.8	732.9	733.8	734.7	735.6	736.4	736.4	735.6	734.7
177.5°	738.1	737.3	736.4	735.6	736.4	737.3	738.1	738.9	738.9	738.2	737.5
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1227.3	1229.0	1235.8	1242.2	1249.8	1255.4	1259.2	1263.4	1272.4	1279.6	1286.4
5°	1149.8	1152.5	1166.3	1175.9	1192.4	1206.7	1217.9	1230.1	1244.5	1264.2	1282.3
7.5°	1081.7	1091.5	1106.6	1122.2	1139.0	1157.8	1174.2	1192.6	1217.4	1244.4	1272.3
10°	1042.9	1054.1	1070.1	1088.1	1104.1	1125.9	1146.1	1167.9	1196.1	1229.1	1262.1
12.5°	1004.2	1022.6	1034.7	1056.2	1073.5	1091.4	1112.9	1141.5	1174.4	1209.1	1248.9
15°	955.7	965.8	989.2	1000.9	1025.4	1053.0	1074.3	1103.0	1134.9	1180.7	1225.4
17.5°	899.8	913.1	931.7	954.0	982.1	1003.7	1030.2	1059.7	1099.9	1145.4	1201.3
20°	863.2	874.3	897.2	921.7	951.5	974.3	1002.5	1031.2	1072.7	1121.1	1179.6
22.5°	830.4	841.2	865.3	888.1	917.0	945.0	974.4	1007.8	1047.6	1098.6	1158.3
25°	779.7	794.0	815.3	838.7	866.4	898.3	930.2	960.0	1002.5	1056.2	1120.1
27.5°	734.7	746.2	761.6	788.2	819.6	850.4	882.1	919.5	960.4	1017.2	1083.5
30°	705.7	716.4	731.8	756.3	785.5	818.5	851.5	887.6	930.2	986.6	1054.1
32.5°	682.8	690.9	704.6	726.5	753.2	787.9	820.4	857.9	902.5	958.1	1023.9
35°	648.8	655.8	661.1	681.8	705.7	737.7	770.6	810.5	853.6	906.3	972.2
37.5°	615.5	617.9	625.7	639.3	662.5	691.8	722.4	761.7	805.8	859.3	918.8
40°	595.1	596.2	601.0	613.7	634.0	661.6	691.4	730.2	772.2	822.8	881.8
42.5°	575.1	574.5	578.9	587.8	606.7	631.8	661.2	696.6	738.6	785.3	840.9
45°	543.5	543.5	542.5	549.9	565.3	589.8	614.3	648.3	683.4	729.2	776.0
47.5°	510.6	507.6	508.5	512.4	525.3	545.5	570.1	598.0	629.0	667.7	708.7
50°	489.3	485.0	483.4	487.7	499.4	516.9	540.3	564.8	594.1	628.1	663.2
52.5°	465.9	461.6	458.8	461.7	472.6	488.9	510.1	531.6	557.9	585.6	616.0
55°	429.7	424.9	423.3	424.4	432.4	445.1	463.2	482.9	502.6	525.5	546.7
57.5°	394.1	386.2	384.7	384.2	389.7	401.4	416.5	433.6	447.9	461.7	484.4
60°	370.7	361.1	357.9	357.4	361.7	371.2	385.1	402.1	412.2	421.7	441.4
62.5°	345.6	336.4	329.4	330.2	334.0	343.1	355.3	367.6	374.3	384.7	398.0
65°	306.9	295.2	289.9	288.3	290.4	297.8	307.4	315.4	322.8	327.1	339.8
67.5°	268.2	258.4	250.5	248.6	247.6	252.7	260.6	265.4	270.7	274.4	282.0
70°	240.9	232.4	222.8	219.6	219.1	223.4	230.8	231.3	238.8	240.4	248.4
72.5°	214.1	203.5	196.9	193.7	191.5	195.3	200.2	201.6	205.6	208.5	212.6
75°	172.3	164.3	158.0	153.2	151.6	153.7	153.7	156.4	159.0	160.6	165.4
77.5°	135.6	126.5	118.9	116.2	114.2	112.9	114.0	115.6	114.3	117.1	118.2
80°	110.1	100.5	94.7	93.6	90.4	87.8	87.2	88.8	86.7	87.8	90.9
82.5°	85.0	78.8	72.5	71.5	67.4	66.1	65.5	64.6	64.6	64.4	65.0
85°	50.5	46.8	42.5	39.9	38.3	35.6	35.6	34.6	33.5	32.4	33.0
87.5°	23.1	22.1	19.8	18.3	17.2	15.3	15.1	13.5	12.8	12.1	11.4
90°	13.3	12.5	11.5	10.5	9.5	8.5	7.3	5.9	4.5	3.1	1.7
92.5°	23.0	22.6	21.9	21.2	20.5	19.7	18.6	17.0	15.4	13.8	12.2
95°	43.7	43.3	42.5	41.6	40.7	39.8	38.8	37.6	36.5	35.4	34.2
97.5°	69.0	68.6	67.5	66.5	65.4	64.4	63.4	62.5	61.6	60.7	59.8
100°	87.5	87.3	86.1	85.0	83.8	82.7	81.9	81.4	80.9	80.4	79.8
102.5°	106.8	106.4	105.4	104.3	103.3	102.3	101.6	101.4	101.2	101.0	100.8
105°	136.1	135.7	135.2	134.7	134.2	133.7	133.4	133.3	133.1	133.0	132.9
107.5°	167.9	167.6	167.5	167.4	167.3	167.3	167.2	167.0	166.8	166.7	166.5
110°	189.7	189.9	190.1	190.2	190.3	190.4	190.4	190.1	189.9	189.6	189.4



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	212.2	212.3	212.5	212.7	213.0	213.2	213.3	213.2	213.2	213.1	213.1
115°	247.4	247.5	247.8	248.0	248.3	248.5	248.7	248.7	248.7	248.7	248.7
117.5°	281.4	281.9	282.0	282.2	282.4	282.6	282.6	282.5	282.4	282.3	282.2
120°	304.5	305.1	305.5	305.9	306.3	306.7	306.6	306.1	305.6	305.1	304.6
122.5°	327.5	328.0	328.1	328.3	328.5	328.7	328.6	328.4	328.2	328.0	327.8
125°	361.3	361.6	361.7	361.9	362.0	362.1	362.2	362.2	362.2	362.2	362.2
127.5°	393.9	394.1	394.3	394.5	394.7	394.9	394.8	394.5	394.1	393.7	393.3
130°	416.7	416.9	416.9	416.9	416.9	416.9	416.7	416.4	416.0	415.6	415.2
132.5°	438.1	438.4	438.5	438.6	438.7	438.8	438.7	438.4	438.1	437.9	437.6
135°	470.3	470.5	470.5	470.5	470.5	470.5	470.2	469.4	468.6	467.9	467.1
137.5°	501.5	501.8	501.6	501.4	501.2	501.0	500.7	500.3	500.0	499.6	499.3
140°	521.7	521.9	521.9	521.9	521.9	521.9	521.7	521.5	521.2	521.0	520.7
142.5°	541.0	541.0	541.1	541.2	541.3	541.4	541.4	541.1	540.9	540.6	540.3
145°	570.2	570.3	570.2	570.1	570.0	569.8	569.5	569.0	568.5	568.0	567.5
147.5°	596.6	596.7	596.8	596.9	597.0	597.1	596.9	596.2	595.6	595.0	594.4
150°	613.1	613.1	613.1	613.1	613.1	613.1	612.9	612.4	611.9	611.4	610.8
152.5°	628.5	628.2	628.1	628.0	627.9	627.8	627.6	627.3	627.0	626.7	626.4
155°	650.1	649.6	649.8	649.9	650.0	650.1	650.2	650.2	650.2	650.2	650.2
157.5°	669.5	669.1	669.2	669.2	669.2	669.2	669.4	669.6	669.8	670.0	670.3
160°	681.4	681.0	681.1	681.3	681.4	681.5	681.6	681.8	681.9	682.0	682.1
162.5°	691.7	691.0	691.2	691.3	691.4	691.5	691.8	692.1	692.4	692.8	693.1
165°	705.7	705.0	705.2	705.5	705.7	706.0	706.3	706.7	707.0	707.4	707.8
167.5°	717.6	716.8	716.8	716.8	716.7	716.7	717.0	717.5	718.0	718.6	719.1
170°	724.0	723.2	723.1	722.9	722.8	722.7	722.9	723.6	724.2	724.9	725.5
172.5°	728.6	727.8	727.7	727.7	727.7	727.7	727.9	728.5	729.0	729.5	730.0
175°	733.8	732.9	733.0	733.2	733.3	733.4	733.8	734.4	735.1	735.7	736.3
177.5°	736.8	736.1	736.1	736.1	736.1	736.1	736.3	736.9	737.4	737.9	738.4
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1292.4	1296.6	1302.2	1311.5	1314.9	1319.2	1325.1	1324.7	1326.4	1332.8	1346.4
5°	1297.2	1313.6	1329.6	1348.7	1369.0	1382.2	1400.3	1411.5	1422.7	1437.0	1461.5
7.5°	1299.1	1325.2	1354.5	1388.1	1418.0	1452.5	1479.4	1504.7	1527.5	1557.9	1587.0
10°	1296.1	1331.2	1369.0	1411.5	1456.7	1495.0	1529.6	1568.9	1602.4	1639.1	1672.1
12.5°	1290.6	1332.9	1383.4	1431.1	1483.9	1540.5	1583.6	1623.4	1668.0	1710.2	1761.0
15°	1278.0	1336.0	1395.0	1457.8	1528.5	1593.9	1656.1	1707.7	1755.6	1818.9	1885.4
17.5°	1262.1	1324.6	1399.1	1475.0	1548.9	1623.7	1700.7	1778.3	1838.7	1917.3	1969.3
20°	1247.2	1319.5	1396.1	1486.5	1560.4	1653.5	1730.1	1805.1	1888.0	1966.2	2028.4
22.5°	1226.3	1305.5	1386.7	1476.7	1574.0	1667.1	1755.6	1837.0	1919.9	2004.9	2080.3
25°	1199.8	1271.6	1367.9	1470.0	1566.8	1667.8	1769.4	1871.5	1960.9	2050.8	2121.0
27.5°	1154.7	1245.4	1335.0	1440.4	1548.0	1662.3	1770.9	1877.8	1971.4	2045.3	2088.8
30°	1131.8	1210.5	1307.8	1413.6	1530.1	1653.0	1766.2	1871.0	1958.2	2017.3	2034.8
32.5°	1097.7	1179.0	1274.2	1383.8	1507.1	1633.4	1751.3	1850.2	1922.9	1953.9	1932.7
35°	1047.2	1120.6	1216.8	1329.1	1457.2	1591.8	1708.3	1791.8	1829.0	1799.7	1726.9
37.5°	986.6	1059.3	1156.0	1266.2	1398.8	1535.6	1640.9	1701.0	1688.7	1615.9	1507.3
40°	944.0	1012.1	1104.1	1223.2	1352.5	1489.7	1582.2	1614.7	1580.6	1476.4	1361.0
42.5°	896.8	963.2	1055.6	1170.5	1307.4	1433.9	1514.6	1517.2	1460.2	1335.6	1219.7
45°	824.9	888.2	975.4	1095.1	1221.6	1340.8	1393.9	1367.9	1262.6	1142.4	1025.9
47.5°	753.9	808.8	894.8	1008.4	1128.6	1228.9	1255.2	1208.3	1096.1	979.4	871.5
50°	702.0	757.3	838.2	946.7	1062.6	1149.3	1162.1	1099.8	989.8	872.2	787.7
52.5°	652.2	707.1	785.0	885.4	991.6	1069.7	1070.2	998.2	888.5	783.7	705.1
55°	579.2	628.6	698.8	788.7	883.4	944.5	929.7	855.2	760.0	669.1	600.4
57.5°	508.8	551.8	616.5	691.5	774.9	825.3	800.6	728.9	643.9	566.8	514.8
60°	463.2	504.2	559.5	630.2	700.4	739.8	716.4	651.5	573.3	511.1	465.9
62.5°	419.0	453.6	506.7	568.1	633.2	662.4	641.5	577.5	509.9	453.7	417.0
65°	356.3	384.5	427.1	479.7	527.1	552.0	534.5	474.9	423.3	382.9	353.7
67.5°	297.8	319.8	352.1	394.3	434.5	448.0	432.1	390.6	346.9	314.5	293.9
70°	257.4	278.2	305.3	337.7	372.8	387.2	371.2	338.2	302.6	272.8	252.6
72.5°	222.1	238.2	261.0	288.8	316.2	330.6	319.7	288.0	257.9	235.8	218.6
75°	169.1	183.0	198.9	218.6	239.9	249.4	239.9	218.1	197.3	180.8	168.6
77.5°	123.0	130.4	142.7	157.4	170.7	178.1	169.8	155.0	142.3	131.0	125.0
80°	93.6	98.9	107.4	119.1	128.2	135.1	129.8	117.5	107.4	100.0	97.3
82.5°	68.1	71.7	77.2	85.9	92.0	95.5	93.2	84.3	80.2	73.6	70.9
85°	33.5	35.6	39.4	42.0	47.3	47.9	48.4	44.7	41.0	39.4	37.2
87.5°	12.1	12.8	14.4	15.9	17.9	18.5	18.3	18.5	17.0	16.7	15.2
90°	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3	14.1
92.5°	13.8	15.4	17.0	18.6	19.7	20.5	21.2	21.9	22.6	23.0	23.5
95°	35.4	36.5	37.6	38.8	39.8	40.7	41.6	42.5	43.3	43.7	44.1
97.5°	60.7	61.6	62.5	63.4	64.4	65.4	66.5	67.5	68.6	69.0	69.5
100°	80.4	80.9	81.4	81.9	82.7	83.8	85.0	86.1	87.3	87.5	87.8
102.5°	101.0	101.2	101.4	101.6	102.3	103.3	104.3	105.4	106.4	106.8	107.1
105°	133.0	133.1	133.3	133.4	133.7	134.2	134.7	135.2	135.7	136.1	136.5
107.5°	166.7	166.8	167.0	167.2	167.3	167.3	167.4	167.5	167.6	167.9	168.3
110°	189.6	189.9	190.1	190.4	190.4	190.3	190.2	190.1	189.9	189.7	189.4



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	213.1	213.2	213.2	213.3	213.2	213.0	212.7	212.5	212.3	212.2	212.2
115°	248.7	248.7	248.7	248.7	248.5	248.3	248.0	247.8	247.5	247.4	247.3
117.5°	282.3	282.4	282.5	282.6	282.6	282.4	282.2	282.0	281.9	281.4	281.0
120°	305.1	305.6	306.1	306.6	306.7	306.3	305.9	305.5	305.1	304.5	303.9
122.5°	328.0	328.2	328.4	328.6	328.7	328.5	328.3	328.1	328.0	327.5	327.1
125°	362.2	362.2	362.2	362.2	362.1	362.0	361.9	361.7	361.6	361.3	361.1
127.5°	393.7	394.1	394.5	394.8	394.9	394.7	394.5	394.3	394.1	393.9	393.6
130°	415.6	416.0	416.4	416.7	416.9	416.9	416.9	416.9	416.9	416.7	416.4
132.5°	437.9	438.1	438.4	438.7	438.8	438.7	438.6	438.5	438.4	438.1	437.9
135°	467.9	468.6	469.4	470.2	470.5	470.5	470.5	470.5	470.5	470.3	470.0
137.5°	499.6	500.0	500.3	500.7	501.0	501.2	501.4	501.6	501.8	501.5	501.1
140°	521.0	521.2	521.5	521.7	521.9	521.9	521.9	521.9	521.9	521.7	521.6
142.5°	540.6	540.9	541.1	541.4	541.4	541.3	541.2	541.1	541.0	541.0	541.0
145°	568.0	568.5	569.0	569.5	569.8	570.0	570.1	570.2	570.3	570.2	570.1
147.5°	595.0	595.6	596.2	596.9	597.1	597.0	596.9	596.8	596.7	596.6	596.5
150°	611.4	611.9	612.4	612.9	613.1	613.1	613.1	613.1	613.1	613.1	613.1
152.5°	626.7	627.0	627.3	627.6	627.8	627.9	628.0	628.1	628.2	628.5	628.8
155°	650.2	650.2	650.2	650.2	650.1	650.0	649.9	649.8	649.6	650.1	650.6
157.5°	670.0	669.8	669.6	669.4	669.2	669.2	669.2	669.2	669.1	669.5	669.9
160°	682.0	681.9	681.8	681.6	681.5	681.4	681.3	681.1	681.0	681.4	681.8
162.5°	692.8	692.4	692.1	691.8	691.5	691.4	691.3	691.2	691.0	691.7	692.4
165°	707.4	707.0	706.7	706.3	706.0	705.7	705.5	705.2	705.0	705.7	706.5
167.5°	718.6	718.0	717.5	717.0	716.7	716.7	716.8	716.8	716.8	717.6	718.3
170°	724.9	724.2	723.6	722.9	722.7	722.8	722.9	723.1	723.2	724.0	724.7
172.5°	729.5	729.0	728.5	727.9	727.7	727.7	727.7	727.7	727.8	728.6	729.5
175°	735.7	735.1	734.4	733.8	733.4	733.3	733.2	733.0	732.9	733.8	734.7
177.5°	737.9	737.4	736.9	736.3	736.1	736.1	736.1	736.1	736.1	736.8	737.5
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1353.2	1354.1	1357.9	1360.9	1361.7	1366.0	1366.4
5°	1472.1	1481.2	1498.7	1500.3	1503.0	1516.8	1506.2
7.5°	1611.5	1634.4	1649.8	1663.3	1668.2	1674.2	1673.0
10°	1700.8	1734.9	1751.9	1779.0	1780.1	1787.0	1782.7
12.5°	1790.6	1830.2	1861.2	1866.2	1889.0	1892.5	1898.5
15°	1917.8	1959.8	2002.9	2018.3	2049.7	2057.2	2068.9
17.5°	2037.4	2080.3	2110.5	2150.4	2163.3	2180.5	2168.8
20°	2102.9	2149.7	2188.0	2219.4	2232.7	2242.2	2241.2
22.5°	2142.5	2189.7	2220.7	2244.5	2256.9	2261.0	2260.7
25°	2167.2	2194.4	2203.9	2213.0	2199.2	2194.4	2196.5
27.5°	2098.3	2091.3	2066.3	2033.5	1999.5	1972.5	1957.8
30°	2003.4	1962.0	1924.2	1858.2	1824.2	1804.0	1785.9
32.5°	1869.0	1803.3	1730.6	1670.2	1631.5	1601.5	1597.0
35°	1638.6	1539.7	1450.9	1376.9	1338.6	1306.2	1298.7
37.5°	1393.1	1290.3	1210.4	1145.3	1104.1	1081.2	1059.8
40°	1230.1	1141.9	1063.1	1007.8	976.5	960.0	946.7
42.5°	1104.6	1024.0	945.7	903.6	875.2	865.1	857.3
45°	931.2	856.3	802.0	770.1	753.6	736.6	728.6
47.5°	792.4	731.4	695.6	668.5	650.9	640.8	635.7
50°	713.7	663.7	631.8	611.1	595.1	587.1	582.9
52.5°	643.9	602.9	576.1	559.6	548.8	542.9	541.2
55°	554.7	523.3	506.3	492.0	484.0	478.7	476.5
57.5°	482.2	458.0	444.2	432.4	429.3	424.8	423.3
60°	434.5	415.9	404.2	396.2	393.6	388.2	389.3
62.5°	392.4	377.2	367.2	362.6	359.1	354.6	356.1
65°	331.9	320.7	315.4	311.1	306.9	304.2	306.3
67.5°	278.5	270.8	263.6	261.1	259.0	258.6	256.3
70°	243.6	237.2	230.8	229.2	229.2	227.1	226.6
72.5°	210.0	205.3	201.0	199.9	198.2	199.0	196.8
75°	162.2	158.5	156.9	155.3	154.8	154.8	153.2
77.5°	119.9	117.1	114.6	114.6	112.6	111.9	111.7
80°	90.9	89.9	87.8	87.8	86.7	87.2	86.2
82.5°	68.4	66.9	66.5	65.6	64.1	64.2	63.2
85°	36.7	35.1	34.6	33.0	31.9	33.0	31.9
87.5°	15.7	15.5	15.1	14.3	14.0	14.0	12.8
90°	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	24.0	24.4	24.7	24.9	25.0	25.2	25.3
95°	44.5	44.9	45.1	45.1	45.1	45.1	45.1
97.5°	69.9	70.4	70.6	70.6	70.6	70.6	70.6
100°	88.0	88.3	88.4	88.4	88.4	88.4	88.4
102.5°	107.5	107.8	108.1	108.2	108.3	108.4	108.5
105°	136.9	137.3	137.6	138.0	138.4	138.8	139.2
107.5°	168.6	169.0	169.2	169.1	169.1	169.1	169.1
110°	189.2	188.9	189.0	189.4	189.7	190.1	190.5



TEST NUMBER: P332590

CATALOG NUMBER: S124DIP-S795D590U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	212.1	212.1	212.1	212.2	212.2	212.3	212.4
115°	247.2	247.0	246.9	246.8	246.6	246.5	246.4
117.5°	280.6	280.1	279.8	279.5	279.3	279.0	278.8
120°	303.2	302.6	302.4	302.7	302.9	303.2	303.4
122.5°	326.7	326.2	325.8	325.3	324.9	324.4	324.0
125°	360.8	360.6	360.3	360.1	359.8	359.6	359.3
127.5°	393.4	393.1	392.9	392.7	392.5	392.3	392.1
130°	416.2	415.9	415.5	415.0	414.5	414.0	413.5
132.5°	437.6	437.4	437.1	436.9	436.7	436.5	436.3
135°	469.8	469.5	469.2	468.8	468.4	468.1	467.7
137.5°	500.8	500.5	500.3	500.4	500.5	500.6	500.7
140°	521.5	521.4	521.2	521.1	521.0	520.9	520.7
142.5°	541.0	540.9	540.9	540.9	540.9	540.8	540.8
145°	570.0	569.8	569.6	569.2	568.8	568.4	568.1
147.5°	596.4	596.3	596.2	596.1	595.9	595.8	595.7
150°	613.1	613.1	613.1	612.9	612.8	612.7	612.6
152.5°	629.1	629.4	629.4	629.1	628.7	628.4	628.1
155°	651.1	651.7	651.7	651.1	650.6	650.1	649.6
157.5°	670.3	670.7	670.6	670.2	669.8	669.3	668.9
160°	682.1	682.5	682.4	681.8	681.1	680.5	679.9
162.5°	693.1	693.8	693.8	693.2	692.5	691.9	691.3
165°	707.2	708.0	708.1	707.6	707.1	706.6	706.1
167.5°	719.1	719.9	719.8	719.1	718.3	717.5	716.7
170°	725.5	726.2	726.2	725.3	724.4	723.5	722.6
172.5°	730.4	731.2	731.2	730.3	729.4	728.5	727.7
175°	735.6	736.4	736.4	735.6	734.7	733.8	732.9
177.5°	738.2	738.9	738.9	738.1	737.3	736.4	735.6
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5

(END OF REPORT)