

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332599

Luminaire Tested: **S124DIP-S795D810U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332599  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S795D810U835-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6349.8 lumens  
Efficiency: N/A  
Efficacy: 138.3 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	55	52	48	46	45	40
3	83	73	66	60	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	49	53	48	43	46	41	38	39	36	33	30
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	26	23	20
8	55	43	35	30	51	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10365	10365	10365	10365
5°	12206	10391	9172	10391
10°	14614	10346	8257	10346
15°	17291	10242	7583	10242
20°	19254	10134	6981	10134
25°	19565	9977	6566	9977
30°	16648	9826	6435	9826
35°	12799	9581	6436	9581
40°	9977	9293	6558	9293
45°	8318	8859	6667	8859
50°	7321	8329	6894	8329
55°	6707	7695	7171	7695
60°	6286	7127	7505	7127
65°	5851	6491	7782	6491
70°	5349	5863	7959	5863
75°	4779	5159	7863	5159
80°	4007	4226	7615	4226
85°	2955	3057	7290	3057



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.1	2.0
10°-20°	385.5	6.1
20°-30°	611.3	9.6
30°-40°	680.3	10.7
40°-50°	619.3	9.8
50°-60°	506.1	8.0
60°-70°	361.3	5.7
70°-80°	198.9	3.1
80°-90°	57.3	0.9
90°-100°	66.7	1.1
100°-110°	197.5	3.1
110°-120°	335.2	5.3
120°-130°	442.0	7.0
130°-140°	496.4	7.8
140°-150°	487.8	7.7
150°-160°	410.3	6.5
160°-170°	273.0	4.3
170°-180°	95.6	1.5
0°-30°	1121.9	17.7
0°-40°	1802.3	28.4
0°-60°	2927.7	46.1
0°-90°	3545.2	55.8
90°-120°	599.4	9.4
90°-150°	2025.7	31.9
90°-180°	2805.0	44.2
0°-180°	6349.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1506	1282	1132	1282	1506	153
15°	2069	1225	907	1225	2069	585
25°	2196	1120	737	1120	2196	968
35°	1299	972	653	972	1299	824
45°	729	776	584	776	729	574
55°	476	547	510	547	476	430
65°	306	340	407	340	306	303
75°	153	165	252	165	153	163
85°	32	33	79	33	32	39
90°	24	2	24	2	24	13
95°	62	47	62	47	62	64
105°	191	182	191	182	191	201
115°	338	341	338	341	338	334
125°	492	496	492	496	492	439
135°	641	640	641	640	641	495
145°	779	778	779	778	779	487
155°	890	891	890	891	890	410
165°	968	970	968	970	968	273
175°	1005	1009	1005	1009	1005	95
180°	1011	1011	1011	1011	1011	



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1366.4	1366.0	1361.7	1360.9	1357.9	1354.1	1353.2	1346.4	1332.8	1326.4	1324.7
5°	1506.2	1516.8	1503.0	1500.3	1498.7	1481.2	1472.1	1461.5	1437.0	1422.7	1411.5
7.5°	1673.0	1674.2	1668.2	1663.3	1649.8	1634.4	1611.5	1587.0	1557.9	1527.5	1504.7
10°	1782.7	1787.0	1780.1	1779.0	1751.9	1734.9	1700.8	1672.1	1639.1	1602.4	1568.9
12.5°	1898.5	1892.5	1889.0	1866.2	1861.2	1830.2	1790.6	1761.0	1710.2	1668.0	1623.4
15°	2068.9	2057.2	2049.7	2018.3	2002.9	1959.8	1917.8	1885.4	1818.9	1755.6	1707.7
17.5°	2168.8	2180.5	2163.3	2150.4	2110.5	2080.3	2037.4	1969.3	1917.3	1838.7	1778.3
20°	2241.2	2242.2	2232.7	2219.4	2188.0	2149.7	2102.9	2028.4	1966.2	1888.0	1805.1
22.5°	2260.7	2261.0	2256.9	2244.5	2220.7	2189.7	2142.5	2080.3	2004.9	1919.9	1837.0
25°	2196.5	2194.4	2199.2	2213.0	2203.9	2194.4	2167.2	2121.0	2050.8	1960.9	1871.5
27.5°	1957.8	1972.5	1999.5	2033.5	2066.3	2091.3	2098.3	2088.8	2045.3	1971.4	1877.8
30°	1785.9	1804.0	1824.2	1858.2	1924.2	1962.0	2003.4	2034.8	2017.3	1958.2	1871.0
32.5°	1597.0	1601.5	1631.5	1670.2	1730.6	1803.3	1869.0	1932.7	1953.9	1922.9	1850.2
35°	1298.7	1306.2	1338.6	1376.9	1450.9	1539.7	1638.6	1726.9	1799.7	1829.0	1791.8
37.5°	1059.8	1081.2	1104.1	1145.3	1210.4	1290.3	1393.1	1507.3	1615.9	1688.7	1701.0
40°	946.7	960.0	976.5	1007.8	1063.1	1141.9	1230.1	1361.0	1476.4	1580.6	1614.7
42.5°	857.3	865.1	875.2	903.6	945.7	1024.0	1104.6	1219.7	1335.6	1460.2	1517.2
45°	728.6	736.6	753.6	770.1	802.0	856.3	931.2	1025.9	1142.4	1262.6	1367.9
47.5°	635.7	640.8	650.9	668.5	695.6	731.4	792.4	871.5	979.4	1096.1	1208.3
50°	582.9	587.1	595.1	611.1	631.8	663.7	713.7	787.7	872.2	989.8	1099.8
52.5°	541.2	542.9	548.8	559.6	576.1	602.9	643.9	705.1	783.7	888.5	998.2
55°	476.5	478.7	484.0	492.0	506.3	523.3	554.7	600.4	669.1	760.0	855.2
57.5°	423.3	424.8	429.3	432.4	444.2	458.0	482.2	514.8	566.8	643.9	728.9
60°	389.3	388.2	393.6	396.2	404.2	415.9	434.5	465.9	511.1	573.3	651.5
62.5°	356.1	354.6	359.1	362.6	367.2	377.2	392.4	417.0	453.7	509.9	577.5
65°	306.3	304.2	306.9	311.1	315.4	320.7	331.9	353.7	382.9	423.3	474.9
67.5°	256.3	258.6	259.0	261.1	263.6	270.8	278.5	293.9	314.5	346.9	390.6
70°	226.6	227.1	229.2	229.2	230.8	237.2	243.6	252.6	272.8	302.6	338.2
72.5°	196.8	199.0	198.2	199.9	201.0	205.3	210.0	218.6	235.8	257.9	288.0
75°	153.2	154.8	154.8	155.3	156.9	158.5	162.2	168.6	180.8	197.3	218.1
77.5°	111.7	111.9	112.6	114.6	114.6	117.1	119.9	125.0	131.0	142.3	155.0
80°	86.2	87.2	86.7	87.8	87.8	89.9	90.9	97.3	100.0	107.4	117.5
82.5°	63.2	64.2	64.1	65.6	66.5	66.9	68.4	70.9	73.6	80.2	84.3
85°	31.9	33.0	31.9	33.0	34.6	35.1	36.7	37.2	39.4	41.0	44.7
87.5°	14.1	15.3	15.2	15.5	16.3	16.6	16.8	16.2	17.7	17.9	19.3
90°	23.5	23.1	22.8	22.4	22.1	21.4	20.3	19.3	18.2	17.2	15.8
92.5°	34.7	34.5	34.3	34.1	33.9	33.5	32.8	32.2	31.6	31.0	30.0
95°	61.8	61.8	61.8	61.8	61.8	61.5	61.0	60.5	59.9	59.4	58.2
97.5°	96.8	96.8	96.8	96.8	96.8	96.5	95.8	95.2	94.6	94.0	92.5
100°	121.2	121.2	121.2	121.2	121.2	121.0	120.7	120.3	120.0	119.6	118.0
102.5°	148.7	148.6	148.4	148.3	148.1	147.8	147.3	146.9	146.4	145.9	144.5
105°	190.8	190.2	189.7	189.2	188.7	188.1	187.6	187.1	186.6	186.1	185.4
107.5°	231.7	231.8	231.8	231.8	231.9	231.6	231.1	230.7	230.2	229.7	229.6
110°	261.1	260.6	260.1	259.6	259.0	258.9	259.3	259.6	260.0	260.3	260.5



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	291.1	291.0	290.9	290.8	290.7	290.7	290.8	290.8	290.9	291.0	291.3
115°	337.7	337.9	338.1	338.3	338.4	338.6	338.8	338.9	339.1	339.3	339.6
117.5°	382.1	382.5	382.8	383.2	383.5	384.0	384.6	385.2	385.8	386.4	386.6
120°	415.9	415.6	415.2	414.9	414.5	414.8	415.6	416.5	417.4	418.3	418.8
122.5°	444.1	444.7	445.3	445.9	446.6	447.2	447.8	448.3	448.9	449.5	449.8
125°	492.5	492.9	493.2	493.6	493.9	494.3	494.6	495.0	495.3	495.7	495.8
127.5°	537.4	537.7	538.0	538.2	538.5	538.8	539.2	539.5	539.9	540.2	540.5
130°	566.8	567.5	568.2	568.9	569.6	570.1	570.4	570.8	571.1	571.5	571.5
132.5°	598.1	598.3	598.6	598.9	599.2	599.5	599.8	600.2	600.5	600.9	601.0
135°	641.1	641.6	642.1	642.6	643.1	643.6	643.9	644.3	644.6	645.0	645.0
137.5°	686.3	686.1	686.0	685.9	685.8	686.0	686.5	686.9	687.4	687.8	687.5
140°	713.8	713.9	714.1	714.3	714.5	714.6	714.8	715.0	715.2	715.3	715.3
142.5°	741.3	741.3	741.4	741.4	741.4	741.5	741.5	741.5	741.6	741.6	741.7
145°	778.7	779.2	779.7	780.2	780.7	781.1	781.3	781.4	781.6	781.8	781.6
147.5°	816.5	816.7	816.8	817.0	817.2	817.3	817.5	817.6	817.8	817.9	818.0
150°	839.6	839.8	840.0	840.2	840.3	840.4	840.4	840.4	840.4	840.4	840.4
152.5°	860.9	861.4	861.8	862.3	862.7	862.7	862.3	861.9	861.5	861.1	860.9
155°	890.5	891.1	891.8	892.5	893.2	893.2	892.5	891.8	891.1	890.5	890.6
157.5°	916.9	917.5	918.1	918.7	919.2	919.3	918.8	918.2	917.7	917.2	917.2
160°	931.9	932.8	933.6	934.5	935.4	935.5	935.0	934.5	934.0	933.5	933.6
162.5°	947.5	948.4	949.3	950.1	951.0	951.0	950.0	949.1	948.2	947.2	947.4
165°	967.9	968.5	969.2	969.9	970.6	970.5	969.4	968.4	967.3	966.3	966.6
167.5°	982.4	983.5	984.5	985.6	986.7	986.7	985.7	984.6	983.6	982.5	982.5
170°	990.5	991.7	993.0	994.2	995.4	995.5	994.4	993.4	992.3	991.3	991.1
172.5°	997.4	998.6	999.8	1001.1	1002.3	1002.3	1001.1	999.9	998.7	997.6	997.5
175°	1004.6	1005.8	1007.0	1008.2	1009.5	1009.5	1008.2	1007.0	1005.8	1004.6	1004.8
177.5°	1008.3	1009.5	1010.6	1011.7	1012.8	1012.9	1011.9	1010.9	1009.9	1009.0	1009.0
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1325.1	1319.2	1314.9	1311.5	1302.2	1296.6	1292.4	1286.4	1279.6	1272.4	1263.4
5°	1400.3	1382.2	1369.0	1348.7	1329.6	1313.6	1297.2	1282.3	1264.2	1244.5	1230.1
7.5°	1479.4	1452.5	1418.0	1388.1	1354.5	1325.2	1299.1	1272.3	1244.4	1217.4	1192.6
10°	1529.6	1495.0	1456.7	1411.5	1369.0	1331.2	1296.1	1262.1	1229.1	1196.1	1167.9
12.5°	1583.6	1540.5	1483.9	1431.1	1383.4	1332.9	1290.6	1248.9	1209.1	1174.4	1141.5
15°	1656.1	1593.9	1528.5	1457.8	1395.0	1336.0	1278.0	1225.4	1180.7	1134.9	1103.0
17.5°	1700.7	1623.7	1548.9	1475.0	1399.1	1324.6	1262.1	1201.3	1145.4	1099.9	1059.7
20°	1730.1	1653.5	1560.4	1486.5	1396.1	1319.5	1247.2	1179.6	1121.1	1072.7	1031.2
22.5°	1755.6	1667.1	1574.0	1476.7	1386.7	1305.5	1226.3	1158.3	1098.6	1047.6	1007.8
25°	1769.4	1667.8	1566.8	1470.0	1367.9	1271.6	1199.8	1120.1	1056.2	1002.5	960.0
27.5°	1770.9	1662.3	1548.0	1440.4	1335.0	1245.4	1154.7	1083.5	1017.2	960.4	919.5
30°	1766.2	1653.0	1530.1	1413.6	1307.8	1210.5	1131.8	1054.1	986.6	930.2	887.6
32.5°	1751.3	1633.4	1507.1	1383.8	1274.2	1179.0	1097.7	1023.9	958.1	902.5	857.9
35°	1708.3	1591.8	1457.2	1329.1	1216.8	1120.6	1047.2	972.2	906.3	853.6	810.5
37.5°	1640.9	1535.6	1398.8	1266.2	1156.0	1059.3	986.6	918.8	859.3	805.8	761.7
40°	1582.2	1489.7	1352.5	1223.2	1104.1	1012.1	944.0	881.8	822.8	772.2	730.2
42.5°	1514.6	1433.9	1307.4	1170.5	1055.6	963.2	896.8	840.9	785.3	738.6	696.6
45°	1393.9	1340.8	1221.6	1095.1	975.4	888.2	824.9	776.0	729.2	683.4	648.3
47.5°	1255.2	1228.9	1128.6	1008.4	894.8	808.8	753.9	708.7	667.7	629.0	598.0
50°	1162.1	1149.3	1062.6	946.7	838.2	757.3	702.0	663.2	628.1	594.1	564.8
52.5°	1070.2	1069.7	991.6	885.4	785.0	707.1	652.2	616.0	585.6	557.9	531.6
55°	929.7	944.5	883.4	788.7	698.8	628.6	579.2	546.7	525.5	502.6	482.9
57.5°	800.6	825.3	774.9	691.5	616.5	551.8	508.8	484.4	461.7	447.9	433.6
60°	716.4	739.8	700.4	630.2	559.5	504.2	463.2	441.4	421.7	412.2	402.1
62.5°	641.5	662.4	633.2	568.1	506.7	453.6	419.0	398.0	384.7	374.3	367.6
65°	534.5	552.0	527.1	479.7	427.1	384.5	356.3	339.8	327.1	322.8	315.4
67.5°	432.1	448.0	434.5	394.3	352.1	319.8	297.8	282.0	274.4	270.7	265.4
70°	371.2	387.2	372.8	337.7	305.3	278.2	257.4	248.4	240.4	238.8	231.3
72.5°	319.7	330.6	316.2	288.8	261.0	238.2	222.1	212.6	208.5	205.6	201.6
75°	239.9	249.4	239.9	218.6	198.9	183.0	169.1	165.4	160.6	159.0	156.4
77.5°	169.8	178.1	170.7	157.4	142.7	130.4	123.0	118.2	117.1	114.3	115.6
80°	129.8	135.1	128.2	119.1	107.4	98.9	93.6	90.9	87.8	86.7	88.8
82.5°	93.2	95.5	92.0	85.9	77.2	71.7	68.1	65.0	64.4	64.6	64.6
85°	48.4	47.9	47.3	42.0	39.4	35.6	33.5	33.0	32.4	33.5	34.6
87.5°	19.1	19.2	18.5	16.5	14.8	13.1	12.3	11.5	12.3	13.1	14.0
90°	14.4	13.0	11.6	10.0	8.1	6.2	4.3	2.3	4.3	6.2	8.1
92.5°	29.0	28.0	27.1	25.5	23.3	21.1	18.9	16.7	18.9	21.1	23.3
95°	57.0	55.8	54.6	53.2	51.6	50.0	48.5	46.9	48.5	50.0	51.6
97.5°	91.1	89.7	88.3	86.9	85.7	84.4	83.2	81.9	83.2	84.4	85.7
100°	116.5	114.9	113.4	112.2	111.5	110.8	110.1	109.5	110.1	110.8	111.5
102.5°	143.0	141.6	140.2	139.3	139.1	138.8	138.5	138.2	138.5	138.8	139.1
105°	184.7	184.0	183.3	182.9	182.7	182.5	182.3	182.2	182.3	182.5	182.7
107.5°	229.5	229.4	229.3	229.1	228.9	228.7	228.5	228.3	228.5	228.7	228.9
110°	260.7	260.9	261.0	260.9	260.6	260.2	259.9	259.6	259.9	260.2	260.6





TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	291.6	291.9	292.2	292.4	292.3	292.2	292.1	292.1	292.1	292.2	292.3
115°	340.0	340.3	340.7	340.9	340.9	340.9	340.9	340.9	340.9	340.9	340.9
117.5°	386.8	387.1	387.3	387.4	387.2	387.1	387.0	386.8	387.0	387.1	387.2
120°	419.3	419.8	420.3	420.3	419.6	418.9	418.2	417.5	418.2	418.9	419.6
122.5°	450.0	450.3	450.5	450.5	450.2	449.9	449.6	449.4	449.6	449.9	450.2
125°	496.0	496.2	496.3	496.4	496.4	496.4	496.4	496.4	496.4	496.4	496.4
127.5°	540.8	541.0	541.3	541.2	540.7	540.2	539.6	539.1	539.6	540.2	540.7
130°	571.5	571.5	571.5	571.2	570.7	570.2	569.7	569.1	569.7	570.2	570.7
132.5°	601.2	601.3	601.4	601.3	600.9	600.6	600.2	599.8	600.2	600.6	600.9
135°	645.0	645.0	645.0	644.5	643.4	642.4	641.3	640.3	641.3	642.4	643.4
137.5°	687.3	687.0	686.7	686.3	685.8	685.3	684.9	684.4	684.9	685.3	685.8
140°	715.3	715.3	715.3	715.2	714.8	714.5	714.1	713.8	714.1	714.5	714.8
142.5°	741.9	742.0	742.2	742.1	741.7	741.4	741.0	740.7	741.0	741.4	741.7
145°	781.4	781.3	781.1	780.7	780.0	779.3	778.6	777.9	778.6	779.3	780.0
147.5°	818.2	818.3	818.5	818.1	817.3	816.4	815.6	814.8	815.6	816.4	817.3
150°	840.4	840.4	840.4	840.1	839.4	838.7	838.0	837.3	838.0	838.7	839.4
152.5°	860.8	860.6	860.5	860.2	859.8	859.4	859.0	858.6	859.0	859.4	859.8
155°	890.8	891.0	891.1	891.2	891.2	891.2	891.2	891.2	891.2	891.2	891.2
157.5°	917.3	917.3	917.3	917.5	917.8	918.1	918.4	918.8	918.4	918.1	917.8
160°	933.8	934.0	934.1	934.3	934.5	934.7	934.8	935.0	934.8	934.7	934.5
162.5°	947.6	947.7	947.9	948.2	948.7	949.1	949.6	950.0	949.6	949.1	948.7
165°	967.0	967.3	967.7	968.1	968.6	969.2	969.7	970.2	969.7	969.2	968.6
167.5°	982.5	982.4	982.4	982.8	983.5	984.2	984.9	985.7	984.9	984.2	983.5
170°	991.0	990.8	990.6	991.0	991.8	992.7	993.6	994.4	993.6	992.7	991.8
172.5°	997.5	997.5	997.4	997.8	998.5	999.2	1000.0	1000.7	1000.0	999.2	998.5
175°	1004.9	1005.1	1005.3	1005.8	1006.7	1007.5	1008.4	1009.3	1008.4	1007.5	1006.7
177.5°	1009.0	1009.0	1009.0	1009.3	1010.0	1010.7	1011.4	1012.1	1011.4	1010.7	1010.0
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1259.2	1255.4	1249.8	1242.2	1235.8	1229.0	1227.3	1224.7	1229.8	1225.6	1224.3
5°	1217.9	1206.7	1192.4	1175.9	1166.3	1152.5	1149.8	1144.5	1139.2	1138.7	1133.3
7.5°	1174.2	1157.8	1139.0	1122.2	1106.6	1091.5	1081.7	1079.5	1071.7	1067.1	1061.8
10°	1146.1	1125.9	1104.1	1088.1	1070.1	1054.1	1042.9	1036.6	1031.2	1025.4	1020.1
12.5°	1112.9	1091.4	1073.5	1056.2	1034.7	1022.6	1004.2	993.2	992.1	992.2	978.4
15°	1074.3	1053.0	1025.4	1000.9	989.2	965.8	955.7	942.9	935.0	927.0	920.6
17.5°	1030.2	1003.7	982.1	954.0	931.7	913.1	899.8	892.1	880.1	868.8	860.6
20°	1002.5	974.3	951.5	921.7	897.2	874.3	863.2	852.5	843.5	833.9	824.9
22.5°	974.4	945.0	917.0	888.1	865.3	841.2	830.4	815.9	807.3	802.0	793.0
25°	930.2	898.3	866.4	838.7	815.3	794.0	779.7	768.5	758.9	754.7	748.8
27.5°	882.1	850.4	819.6	788.2	761.6	746.2	734.7	726.3	720.7	715.1	712.5
30°	851.5	818.5	785.5	756.3	731.8	716.4	705.7	699.9	695.6	693.0	690.3
32.5°	820.4	787.9	753.2	726.5	704.6	690.9	682.8	676.9	674.8	673.8	672.9
35°	770.6	737.7	705.7	681.8	661.1	655.8	648.8	645.7	644.6	648.3	649.9
37.5°	722.4	691.8	662.5	639.3	625.7	617.9	615.5	615.7	619.5	622.8	626.6
40°	691.4	661.6	634.0	613.7	601.0	596.2	595.1	597.8	602.0	605.8	610.0
42.5°	661.2	631.8	606.7	587.8	578.9	574.5	575.1	577.8	583.7	588.3	594.7
45°	614.3	589.8	565.3	549.9	542.5	543.5	543.5	548.3	554.2	561.1	568.0
47.5°	570.1	545.5	525.3	512.4	508.5	507.6	510.6	516.8	525.2	533.8	543.4
50°	540.3	516.9	499.4	487.7	483.4	485.0	489.3	495.1	505.2	515.9	526.0
52.5°	510.1	488.9	472.6	461.7	458.8	461.6	465.9	475.1	484.0	495.5	507.7
55°	463.2	445.1	432.4	424.4	423.3	424.9	429.7	439.8	452.6	467.0	478.7
57.5°	416.5	401.4	389.7	384.2	384.7	386.2	394.1	406.1	419.7	435.0	450.1
60°	385.1	371.2	361.7	357.4	357.9	361.1	370.7	381.9	398.9	413.8	429.7
62.5°	355.3	343.1	334.0	330.2	329.4	336.4	345.6	357.2	374.2	390.8	408.0
65°	307.4	297.8	290.4	288.3	289.9	295.2	306.9	322.3	336.7	354.2	372.3
67.5°	260.6	252.7	247.6	248.6	250.5	258.4	268.2	281.4	297.7	315.9	333.8
70°	230.8	223.4	219.1	219.6	222.8	232.4	240.9	254.2	271.8	290.4	305.3
72.5°	200.2	195.3	191.5	193.7	196.9	203.5	214.1	227.4	242.8	260.2	275.9
75°	153.7	153.7	151.6	153.2	158.0	164.3	172.3	186.1	201.6	215.4	228.2
77.5°	114.0	112.9	114.2	116.2	118.9	126.5	135.6	145.5	157.1	170.9	181.5
80°	87.2	87.8	90.4	93.6	94.7	100.5	110.1	119.1	128.2	139.9	150.0
82.5°	65.5	66.1	67.4	71.5	72.5	78.8	85.0	94.0	102.2	110.1	118.5
85°	35.6	35.6	38.3	39.9	42.5	46.8	50.5	55.8	63.3	68.6	76.6
87.5°	15.6	15.9	17.9	19.1	20.6	23.0	24.1	29.0	30.9	33.2	37.2
90°	10.0	11.6	13.0	14.4	15.8	17.2	18.2	19.3	20.3	21.4	22.1
92.5°	25.5	27.1	28.0	29.0	30.0	31.0	31.6	32.2	32.8	33.5	33.9
95°	53.2	54.6	55.8	57.0	58.2	59.4	59.9	60.5	61.0	61.5	61.8
97.5°	86.9	88.3	89.7	91.1	92.5	94.0	94.6	95.2	95.8	96.5	96.8
100°	112.2	113.4	114.9	116.5	118.0	119.6	120.0	120.3	120.7	121.0	121.2
102.5°	139.3	140.2	141.6	143.0	144.5	145.9	146.4	146.9	147.3	147.8	148.1
105°	182.9	183.3	184.0	184.7	185.4	186.1	186.6	187.1	187.6	188.1	188.7
107.5°	229.1	229.3	229.4	229.5	229.6	229.7	230.2	230.7	231.1	231.6	231.9
110°	260.9	261.0	260.9	260.7	260.5	260.3	260.0	259.6	259.3	258.9	259.0



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	292.4	292.2	291.9	291.6	291.3	291.0	290.9	290.8	290.8	290.7	290.7
115°	340.9	340.7	340.3	340.0	339.6	339.3	339.1	338.9	338.8	338.6	338.4
117.5°	387.4	387.3	387.1	386.8	386.6	386.4	385.8	385.2	384.6	384.0	383.5
120°	420.3	420.3	419.8	419.3	418.8	418.3	417.4	416.5	415.6	414.8	414.5
122.5°	450.5	450.5	450.3	450.0	449.8	449.5	448.9	448.3	447.8	447.2	446.6
125°	496.4	496.3	496.2	496.0	495.8	495.7	495.3	495.0	494.6	494.3	493.9
127.5°	541.2	541.3	541.0	540.8	540.5	540.2	539.9	539.5	539.2	538.8	538.5
130°	571.2	571.5	571.5	571.5	571.5	571.5	571.1	570.8	570.4	570.1	569.6
132.5°	601.3	601.4	601.3	601.2	601.0	600.9	600.5	600.2	599.8	599.5	599.2
135°	644.5	645.0	645.0	645.0	645.0	645.0	644.6	644.3	643.9	643.6	643.1
137.5°	686.3	686.7	687.0	687.3	687.5	687.8	687.4	686.9	686.5	686.0	685.8
140°	715.2	715.3	715.3	715.3	715.3	715.3	715.2	715.0	714.8	714.6	714.5
142.5°	742.1	742.2	742.0	741.9	741.7	741.6	741.6	741.5	741.5	741.5	741.4
145°	780.7	781.1	781.3	781.4	781.6	781.8	781.6	781.4	781.3	781.1	780.7
147.5°	818.1	818.5	818.3	818.2	818.0	817.9	817.8	817.6	817.5	817.3	817.2
150°	840.1	840.4	840.4	840.4	840.4	840.4	840.4	840.4	840.4	840.4	840.3
152.5°	860.2	860.5	860.6	860.8	860.9	861.1	861.5	861.9	862.3	862.7	862.7
155°	891.2	891.1	891.0	890.8	890.6	890.5	891.1	891.8	892.5	893.2	893.2
157.5°	917.5	917.3	917.3	917.3	917.2	917.2	917.7	918.2	918.8	919.3	919.2
160°	934.3	934.1	934.0	933.8	933.6	933.5	934.0	934.5	935.0	935.5	935.4
162.5°	948.2	947.9	947.7	947.6	947.4	947.2	948.2	949.1	950.0	951.0	951.0
165°	968.1	967.7	967.3	967.0	966.6	966.3	967.3	968.4	969.4	970.5	970.6
167.5°	982.8	982.4	982.4	982.5	982.5	982.5	983.6	984.6	985.7	986.7	986.7
170°	991.0	990.6	990.8	991.0	991.1	991.3	992.3	993.4	994.4	995.5	995.4
172.5°	997.8	997.4	997.5	997.5	997.5	997.6	998.7	999.9	1001.1	1002.3	1002.3
175°	1005.8	1005.3	1005.1	1004.9	1004.8	1004.6	1005.8	1007.0	1008.2	1009.5	1009.5
177.5°	1009.3	1009.0	1009.0	1009.0	1009.0	1009.0	1009.9	1010.9	1011.9	1012.9	1012.8
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1223.4	1222.6	1219.6	1219.2	1219.6	1222.6	1223.4	1224.3	1225.6	1229.8	1224.7
5°	1130.2	1127.5	1125.9	1131.8	1125.9	1127.5	1130.2	1133.3	1138.7	1139.2	1144.5
7.5°	1059.8	1057.7	1053.0	1051.6	1053.0	1057.7	1059.8	1061.8	1067.1	1071.7	1079.5
10°	1014.7	1012.6	1008.4	1007.3	1008.4	1012.6	1014.7	1020.1	1025.4	1031.2	1036.6
12.5°	971.3	967.1	966.2	967.3	966.2	967.1	971.3	978.4	992.2	992.1	993.2
15°	913.7	911.6	905.7	907.3	905.7	911.6	913.7	920.6	927.0	935.0	942.9
17.5°	856.9	854.3	847.2	853.5	847.2	854.3	856.9	860.6	868.8	880.1	892.1
20°	821.2	816.9	813.2	812.6	813.2	816.9	821.2	824.9	833.9	843.5	852.5
22.5°	787.1	783.3	783.0	779.5	783.0	783.3	787.1	793.0	802.0	807.3	815.9
25°	744.6	740.9	739.8	737.1	739.8	740.9	744.6	748.8	754.7	758.9	768.5
27.5°	711.9	710.1	708.2	709.0	708.2	710.1	711.9	712.5	715.1	720.7	726.3
30°	691.9	691.4	690.3	690.3	690.3	691.4	691.9	690.3	693.0	695.6	699.9
32.5°	675.3	675.2	675.9	675.9	675.9	675.2	675.3	672.9	673.8	674.8	676.9
35°	652.0	653.6	654.7	653.1	654.7	653.6	652.0	649.9	648.3	644.6	645.7
37.5°	631.0	632.6	634.1	635.9	634.1	632.6	631.0	626.6	622.8	619.5	615.7
40°	614.8	618.5	619.6	622.3	619.6	618.5	614.8	610.0	605.8	602.0	597.8
42.5°	599.5	603.6	606.4	606.9	606.4	603.6	599.5	594.7	588.3	583.7	577.8
45°	576.0	580.2	584.0	584.0	584.0	580.2	576.0	568.0	561.1	554.2	548.3
47.5°	551.6	557.8	561.5	562.5	561.5	557.8	551.6	543.4	533.8	525.2	516.8
50°	535.0	542.5	546.2	548.9	546.2	542.5	535.0	526.0	515.9	505.2	495.1
52.5°	518.9	526.3	531.3	532.7	531.3	526.3	518.9	507.7	495.5	484.0	475.1
55°	490.9	501.5	507.4	509.5	507.4	501.5	490.9	478.7	467.0	452.6	439.8
57.5°	464.5	474.3	481.1	482.7	481.1	474.3	464.5	450.1	435.0	419.7	406.1
60°	444.1	454.7	463.2	464.8	463.2	454.7	444.1	429.7	413.8	398.9	381.9
62.5°	423.2	434.3	442.0	446.1	442.0	434.3	423.2	408.0	390.8	374.2	357.2
65°	387.2	398.3	405.8	407.4	405.8	398.3	387.2	372.3	354.2	336.7	322.3
67.5°	347.8	359.0	363.9	367.0	363.9	359.0	347.8	333.8	315.9	297.7	281.4
70°	320.2	329.2	334.5	337.2	334.5	329.2	320.2	305.3	290.4	271.8	254.2
72.5°	288.7	298.1	304.3	304.8	304.3	298.1	288.7	275.9	260.2	242.8	227.4
75°	240.4	248.9	252.1	252.1	252.1	248.9	240.4	228.2	215.4	201.6	186.1
77.5°	190.3	194.7	198.7	199.5	198.7	194.7	190.3	181.5	170.9	157.1	145.5
80°	158.0	160.6	163.8	163.8	163.8	160.6	158.0	150.0	139.9	128.2	119.1
82.5°	124.8	127.0	130.2	129.8	130.2	127.0	124.8	118.5	110.1	102.2	94.0
85°	75.5	80.3	79.8	78.7	79.8	80.3	75.5	76.6	68.6	63.3	55.8
87.5°	38.5	39.0	40.4	41.3	40.4	39.0	38.5	37.2	33.2	30.9	29.0
90°	22.4	22.8	23.1	23.5	23.1	22.8	22.4	22.1	21.4	20.3	19.3
92.5°	34.1	34.3	34.5	34.7	34.5	34.3	34.1	33.9	33.5	32.8	32.2
95°	61.8	61.8	61.8	61.8	61.8	61.8	61.8	61.8	61.5	61.0	60.5
97.5°	96.8	96.8	96.8	96.8	96.8	96.8	96.8	96.8	96.5	95.8	95.2
100°	121.2	121.2	121.2	121.2	121.2	121.2	121.2	121.2	121.0	120.7	120.3
102.5°	148.3	148.4	148.6	148.7	148.6	148.4	148.3	148.1	147.8	147.3	146.9
105°	189.2	189.7	190.2	190.8	190.2	189.7	189.2	188.7	188.1	187.6	187.1
107.5°	231.8	231.8	231.8	231.7	231.8	231.8	231.8	231.9	231.6	231.1	230.7
110°	259.6	260.1	260.6	261.1	260.6	260.1	259.6	259.0	258.9	259.3	259.6



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	290.8	290.9	291.0	291.1	291.0	290.9	290.8	290.7	290.7	290.8	290.8
115°	338.3	338.1	337.9	337.7	337.9	338.1	338.3	338.4	338.6	338.8	338.9
117.5°	383.2	382.8	382.5	382.1	382.5	382.8	383.2	383.5	384.0	384.6	385.2
120°	414.9	415.2	415.6	415.9	415.6	415.2	414.9	414.5	414.8	415.6	416.5
122.5°	445.9	445.3	444.7	444.1	444.7	445.3	445.9	446.6	447.2	447.8	448.3
125°	493.6	493.2	492.9	492.5	492.9	493.2	493.6	493.9	494.3	494.6	495.0
127.5°	538.2	538.0	537.7	537.4	537.7	538.0	538.2	538.5	538.8	539.2	539.5
130°	568.9	568.2	567.5	566.8	567.5	568.2	568.9	569.6	570.1	570.4	570.8
132.5°	598.9	598.6	598.3	598.1	598.3	598.6	598.9	599.2	599.5	599.8	600.2
135°	642.6	642.1	641.6	641.1	641.6	642.1	642.6	643.1	643.6	643.9	644.3
137.5°	685.9	686.0	686.1	686.3	686.1	686.0	685.9	685.8	686.0	686.5	686.9
140°	714.3	714.1	713.9	713.8	713.9	714.1	714.3	714.5	714.6	714.8	715.0
142.5°	741.4	741.4	741.3	741.3	741.3	741.4	741.4	741.4	741.5	741.5	741.5
145°	780.2	779.7	779.2	778.7	779.2	779.7	780.2	780.7	781.1	781.3	781.4
147.5°	817.0	816.8	816.7	816.5	816.7	816.8	817.0	817.2	817.3	817.5	817.6
150°	840.2	840.0	839.8	839.6	839.8	840.0	840.2	840.3	840.4	840.4	840.4
152.5°	862.3	861.8	861.4	860.9	861.4	861.8	862.3	862.7	862.7	862.3	861.9
155°	892.5	891.8	891.1	890.5	891.1	891.8	892.5	893.2	893.2	892.5	891.8
157.5°	918.7	918.1	917.5	916.9	917.5	918.1	918.7	919.2	919.3	918.8	918.2
160°	934.5	933.6	932.8	931.9	932.8	933.6	934.5	935.4	935.5	935.0	934.5
162.5°	950.1	949.3	948.4	947.5	948.4	949.3	950.1	951.0	951.0	950.0	949.1
165°	969.9	969.2	968.5	967.9	968.5	969.2	969.9	970.6	970.5	969.4	968.4
167.5°	985.6	984.5	983.5	982.4	983.5	984.5	985.6	986.7	986.7	985.7	984.6
170°	994.2	993.0	991.7	990.5	991.7	993.0	994.2	995.4	995.5	994.4	993.4
172.5°	1001.1	999.8	998.6	997.4	998.6	999.8	1001.1	1002.3	1002.3	1001.1	999.9
175°	1008.2	1007.0	1005.8	1004.6	1005.8	1007.0	1008.2	1009.5	1009.5	1008.2	1007.0
177.5°	1011.7	1010.6	1009.5	1008.3	1009.5	1010.6	1011.7	1012.8	1012.9	1011.9	1010.9
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1227.3	1229.0	1235.8	1242.2	1249.8	1255.4	1259.2	1263.4	1272.4	1279.6	1286.4
5°	1149.8	1152.5	1166.3	1175.9	1192.4	1206.7	1217.9	1230.1	1244.5	1264.2	1282.3
7.5°	1081.7	1091.5	1106.6	1122.2	1139.0	1157.8	1174.2	1192.6	1217.4	1244.4	1272.3
10°	1042.9	1054.1	1070.1	1088.1	1104.1	1125.9	1146.1	1167.9	1196.1	1229.1	1262.1
12.5°	1004.2	1022.6	1034.7	1056.2	1073.5	1091.4	1112.9	1141.5	1174.4	1209.1	1248.9
15°	955.7	965.8	989.2	1000.9	1025.4	1053.0	1074.3	1103.0	1134.9	1180.7	1225.4
17.5°	899.8	913.1	931.7	954.0	982.1	1003.7	1030.2	1059.7	1099.9	1145.4	1201.3
20°	863.2	874.3	897.2	921.7	951.5	974.3	1002.5	1031.2	1072.7	1121.1	1179.6
22.5°	830.4	841.2	865.3	888.1	917.0	945.0	974.4	1007.8	1047.6	1098.6	1158.3
25°	779.7	794.0	815.3	838.7	866.4	898.3	930.2	960.0	1002.5	1056.2	1120.1
27.5°	734.7	746.2	761.6	788.2	819.6	850.4	882.1	919.5	960.4	1017.2	1083.5
30°	705.7	716.4	731.8	756.3	785.5	818.5	851.5	887.6	930.2	986.6	1054.1
32.5°	682.8	690.9	704.6	726.5	753.2	787.9	820.4	857.9	902.5	958.1	1023.9
35°	648.8	655.8	661.1	681.8	705.7	737.7	770.6	810.5	853.6	906.3	972.2
37.5°	615.5	617.9	625.7	639.3	662.5	691.8	722.4	761.7	805.8	859.3	918.8
40°	595.1	596.2	601.0	613.7	634.0	661.6	691.4	730.2	772.2	822.8	881.8
42.5°	575.1	574.5	578.9	587.8	606.7	631.8	661.2	696.6	738.6	785.3	840.9
45°	543.5	543.5	542.5	549.9	565.3	589.8	614.3	648.3	683.4	729.2	776.0
47.5°	510.6	507.6	508.5	512.4	525.3	545.5	570.1	598.0	629.0	667.7	708.7
50°	489.3	485.0	483.4	487.7	499.4	516.9	540.3	564.8	594.1	628.1	663.2
52.5°	465.9	461.6	458.8	461.7	472.6	488.9	510.1	531.6	557.9	585.6	616.0
55°	429.7	424.9	423.3	424.4	432.4	445.1	463.2	482.9	502.6	525.5	546.7
57.5°	394.1	386.2	384.7	384.2	389.7	401.4	416.5	433.6	447.9	461.7	484.4
60°	370.7	361.1	357.9	357.4	361.7	371.2	385.1	402.1	412.2	421.7	441.4
62.5°	345.6	336.4	329.4	330.2	334.0	343.1	355.3	367.6	374.3	384.7	398.0
65°	306.9	295.2	289.9	288.3	290.4	297.8	307.4	315.4	322.8	327.1	339.8
67.5°	268.2	258.4	250.5	248.6	247.6	252.7	260.6	265.4	270.7	274.4	282.0
70°	240.9	232.4	222.8	219.6	219.1	223.4	230.8	231.3	238.8	240.4	248.4
72.5°	214.1	203.5	196.9	193.7	191.5	195.3	200.2	201.6	205.6	208.5	212.6
75°	172.3	164.3	158.0	153.2	151.6	153.7	153.7	156.4	159.0	160.6	165.4
77.5°	135.6	126.5	118.9	116.2	114.2	112.9	114.0	115.6	114.3	117.1	118.2
80°	110.1	100.5	94.7	93.6	90.4	87.8	87.2	88.8	86.7	87.8	90.9
82.5°	85.0	78.8	72.5	71.5	67.4	66.1	65.5	64.6	64.6	64.4	65.0
85°	50.5	46.8	42.5	39.9	38.3	35.6	35.6	34.6	33.5	32.4	33.0
87.5°	24.1	23.0	20.6	19.1	17.9	15.9	15.6	14.0	13.1	12.3	11.5
90°	18.2	17.2	15.8	14.4	13.0	11.6	10.0	8.1	6.2	4.3	2.3
92.5°	31.6	31.0	30.0	29.0	28.0	27.1	25.5	23.3	21.1	18.9	16.7
95°	59.9	59.4	58.2	57.0	55.8	54.6	53.2	51.6	50.0	48.5	46.9
97.5°	94.6	94.0	92.5	91.1	89.7	88.3	86.9	85.7	84.4	83.2	81.9
100°	120.0	119.6	118.0	116.5	114.9	113.4	112.2	111.5	110.8	110.1	109.5
102.5°	146.4	145.9	144.5	143.0	141.6	140.2	139.3	139.1	138.8	138.5	138.2
105°	186.6	186.1	185.4	184.7	184.0	183.3	182.9	182.7	182.5	182.3	182.2
107.5°	230.2	229.7	229.6	229.5	229.4	229.3	229.1	228.9	228.7	228.5	228.3
110°	260.0	260.3	260.5	260.7	260.9	261.0	260.9	260.6	260.2	259.9	259.6



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	290.9	291.0	291.3	291.6	291.9	292.2	292.4	292.3	292.2	292.1	292.1
115°	339.1	339.3	339.6	340.0	340.3	340.7	340.9	340.9	340.9	340.9	340.9
117.5°	385.8	386.4	386.6	386.8	387.1	387.3	387.4	387.2	387.1	387.0	386.8
120°	417.4	418.3	418.8	419.3	419.8	420.3	420.3	419.6	418.9	418.2	417.5
122.5°	448.9	449.5	449.8	450.0	450.3	450.5	450.5	450.2	449.9	449.6	449.4
125°	495.3	495.7	495.8	496.0	496.2	496.3	496.4	496.4	496.4	496.4	496.4
127.5°	539.9	540.2	540.5	540.8	541.0	541.3	541.2	540.7	540.2	539.6	539.1
130°	571.1	571.5	571.5	571.5	571.5	571.5	571.2	570.7	570.2	569.7	569.1
132.5°	600.5	600.9	601.0	601.2	601.3	601.4	601.3	600.9	600.6	600.2	599.8
135°	644.6	645.0	645.0	645.0	645.0	645.0	644.5	643.4	642.4	641.3	640.3
137.5°	687.4	687.8	687.5	687.3	687.0	686.7	686.3	685.8	685.3	684.9	684.4
140°	715.2	715.3	715.3	715.3	715.3	715.3	715.2	714.8	714.5	714.1	713.8
142.5°	741.6	741.6	741.7	741.9	742.0	742.2	742.1	741.7	741.4	741.0	740.7
145°	781.6	781.8	781.6	781.4	781.3	781.1	780.7	780.0	779.3	778.6	777.9
147.5°	817.8	817.9	818.0	818.2	818.3	818.5	818.1	817.3	816.4	815.6	814.8
150°	840.4	840.4	840.4	840.4	840.4	840.4	840.1	839.4	838.7	838.0	837.3
152.5°	861.5	861.1	860.9	860.8	860.6	860.5	860.2	859.8	859.4	859.0	858.6
155°	891.1	890.5	890.6	890.8	891.0	891.1	891.2	891.2	891.2	891.2	891.2
157.5°	917.7	917.2	917.2	917.3	917.3	917.3	917.5	917.8	918.1	918.4	918.8
160°	934.0	933.5	933.6	933.8	934.0	934.1	934.3	934.5	934.7	934.8	935.0
162.5°	948.2	947.2	947.4	947.6	947.7	947.9	948.2	948.7	949.1	949.6	950.0
165°	967.3	966.3	966.6	967.0	967.3	967.7	968.1	968.6	969.2	969.7	970.2
167.5°	983.6	982.5	982.5	982.5	982.4	982.4	982.8	983.5	984.2	984.9	985.7
170°	992.3	991.3	991.1	991.0	990.8	990.6	991.0	991.8	992.7	993.6	994.4
172.5°	998.7	997.6	997.5	997.5	997.5	997.4	997.8	998.5	999.2	1000.0	1000.7
175°	1005.8	1004.6	1004.8	1004.9	1005.1	1005.3	1005.8	1006.7	1007.5	1008.4	1009.3
177.5°	1009.9	1009.0	1009.0	1009.0	1009.0	1009.0	1009.3	1010.0	1010.7	1011.4	1012.1
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1292.4	1296.6	1302.2	1311.5	1314.9	1319.2	1325.1	1324.7	1326.4	1332.8	1346.4
5°	1297.2	1313.6	1329.6	1348.7	1369.0	1382.2	1400.3	1411.5	1422.7	1437.0	1461.5
7.5°	1299.1	1325.2	1354.5	1388.1	1418.0	1452.5	1479.4	1504.7	1527.5	1557.9	1587.0
10°	1296.1	1331.2	1369.0	1411.5	1456.7	1495.0	1529.6	1568.9	1602.4	1639.1	1672.1
12.5°	1290.6	1332.9	1383.4	1431.1	1483.9	1540.5	1583.6	1623.4	1668.0	1710.2	1761.0
15°	1278.0	1336.0	1395.0	1457.8	1528.5	1593.9	1656.1	1707.7	1755.6	1818.9	1885.4
17.5°	1262.1	1324.6	1399.1	1475.0	1548.9	1623.7	1700.7	1778.3	1838.7	1917.3	1969.3
20°	1247.2	1319.5	1396.1	1486.5	1560.4	1653.5	1730.1	1805.1	1888.0	1966.2	2028.4
22.5°	1226.3	1305.5	1386.7	1476.7	1574.0	1667.1	1755.6	1837.0	1919.9	2004.9	2080.3
25°	1199.8	1271.6	1367.9	1470.0	1566.8	1667.8	1769.4	1871.5	1960.9	2050.8	2121.0
27.5°	1154.7	1245.4	1335.0	1440.4	1548.0	1662.3	1770.9	1877.8	1971.4	2045.3	2088.8
30°	1131.8	1210.5	1307.8	1413.6	1530.1	1653.0	1766.2	1871.0	1958.2	2017.3	2034.8
32.5°	1097.7	1179.0	1274.2	1383.8	1507.1	1633.4	1751.3	1850.2	1922.9	1953.9	1932.7
35°	1047.2	1120.6	1216.8	1329.1	1457.2	1591.8	1708.3	1791.8	1829.0	1799.7	1726.9
37.5°	986.6	1059.3	1156.0	1266.2	1398.8	1535.6	1640.9	1701.0	1688.7	1615.9	1507.3
40°	944.0	1012.1	1104.1	1223.2	1352.5	1489.7	1582.2	1614.7	1580.6	1476.4	1361.0
42.5°	896.8	963.2	1055.6	1170.5	1307.4	1433.9	1514.6	1517.2	1460.2	1335.6	1219.7
45°	824.9	888.2	975.4	1095.1	1221.6	1340.8	1393.9	1367.9	1262.6	1142.4	1025.9
47.5°	753.9	808.8	894.8	1008.4	1128.6	1228.9	1255.2	1208.3	1096.1	979.4	871.5
50°	702.0	757.3	838.2	946.7	1062.6	1149.3	1162.1	1099.8	989.8	872.2	787.7
52.5°	652.2	707.1	785.0	885.4	991.6	1069.7	1070.2	998.2	888.5	783.7	705.1
55°	579.2	628.6	698.8	788.7	883.4	944.5	929.7	855.2	760.0	669.1	600.4
57.5°	508.8	551.8	616.5	691.5	774.9	825.3	800.6	728.9	643.9	566.8	514.8
60°	463.2	504.2	559.5	630.2	700.4	739.8	716.4	651.5	573.3	511.1	465.9
62.5°	419.0	453.6	506.7	568.1	633.2	662.4	641.5	577.5	509.9	453.7	417.0
65°	356.3	384.5	427.1	479.7	527.1	552.0	534.5	474.9	423.3	382.9	353.7
67.5°	297.8	319.8	352.1	394.3	434.5	448.0	432.1	390.6	346.9	314.5	293.9
70°	257.4	278.2	305.3	337.7	372.8	387.2	371.2	338.2	302.6	272.8	252.6
72.5°	222.1	238.2	261.0	288.8	316.2	330.6	319.7	288.0	257.9	235.8	218.6
75°	169.1	183.0	198.9	218.6	239.9	249.4	239.9	218.1	197.3	180.8	168.6
77.5°	123.0	130.4	142.7	157.4	170.7	178.1	169.8	155.0	142.3	131.0	125.0
80°	93.6	98.9	107.4	119.1	128.2	135.1	129.8	117.5	107.4	100.0	97.3
82.5°	68.1	71.7	77.2	85.9	92.0	95.5	93.2	84.3	80.2	73.6	70.9
85°	33.5	35.6	39.4	42.0	47.3	47.9	48.4	44.7	41.0	39.4	37.2
87.5°	12.3	13.1	14.8	16.5	18.5	19.2	19.1	19.3	17.9	17.7	16.2
90°	4.3	6.2	8.1	10.0	11.6	13.0	14.4	15.8	17.2	18.2	19.3
92.5°	18.9	21.1	23.3	25.5	27.1	28.0	29.0	30.0	31.0	31.6	32.2
95°	48.5	50.0	51.6	53.2	54.6	55.8	57.0	58.2	59.4	59.9	60.5
97.5°	83.2	84.4	85.7	86.9	88.3	89.7	91.1	92.5	94.0	94.6	95.2
100°	110.1	110.8	111.5	112.2	113.4	114.9	116.5	118.0	119.6	120.0	120.3
102.5°	138.5	138.8	139.1	139.3	140.2	141.6	143.0	144.5	145.9	146.4	146.9
105°	182.3	182.5	182.7	182.9	183.3	184.0	184.7	185.4	186.1	186.6	187.1
107.5°	228.5	228.7	228.9	229.1	229.3	229.4	229.5	229.6	229.7	230.2	230.7
110°	259.9	260.2	260.6	260.9	261.0	260.9	260.7	260.5	260.3	260.0	259.6





TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	292.1	292.2	292.3	292.4	292.2	291.9	291.6	291.3	291.0	290.9	290.8
115°	340.9	340.9	340.9	340.9	340.7	340.3	340.0	339.6	339.3	339.1	338.9
117.5°	387.0	387.1	387.2	387.4	387.3	387.1	386.8	386.6	386.4	385.8	385.2
120°	418.2	418.9	419.6	420.3	420.3	419.8	419.3	418.8	418.3	417.4	416.5
122.5°	449.6	449.9	450.2	450.5	450.5	450.3	450.0	449.8	449.5	448.9	448.3
125°	496.4	496.4	496.4	496.4	496.3	496.2	496.0	495.8	495.7	495.3	495.0
127.5°	539.6	540.2	540.7	541.2	541.3	541.0	540.8	540.5	540.2	539.9	539.5
130°	569.7	570.2	570.7	571.2	571.5	571.5	571.5	571.5	571.5	571.1	570.8
132.5°	600.2	600.6	600.9	601.3	601.4	601.3	601.2	601.0	600.9	600.5	600.2
135°	641.3	642.4	643.4	644.5	645.0	645.0	645.0	645.0	645.0	644.6	644.3
137.5°	684.9	685.3	685.8	686.3	686.7	687.0	687.3	687.5	687.8	687.4	686.9
140°	714.1	714.5	714.8	715.2	715.3	715.3	715.3	715.3	715.3	715.2	715.0
142.5°	741.0	741.4	741.7	742.1	742.2	742.0	741.9	741.7	741.6	741.6	741.5
145°	778.6	779.3	780.0	780.7	781.1	781.3	781.4	781.6	781.8	781.6	781.4
147.5°	815.6	816.4	817.3	818.1	818.5	818.3	818.2	818.0	817.9	817.8	817.6
150°	838.0	838.7	839.4	840.1	840.4	840.4	840.4	840.4	840.4	840.4	840.4
152.5°	859.0	859.4	859.8	860.2	860.5	860.6	860.8	860.9	861.1	861.5	861.9
155°	891.2	891.2	891.2	891.2	891.1	891.0	890.8	890.6	890.5	891.1	891.8
157.5°	918.4	918.1	917.8	917.5	917.3	917.3	917.3	917.2	917.2	917.7	918.2
160°	934.8	934.7	934.5	934.3	934.1	934.0	933.8	933.6	933.5	934.0	934.5
162.5°	949.6	949.1	948.7	948.2	947.9	947.7	947.6	947.4	947.2	948.2	949.1
165°	969.7	969.2	968.6	968.1	967.7	967.3	967.0	966.6	966.3	967.3	968.4
167.5°	984.9	984.2	983.5	982.8	982.4	982.4	982.5	982.5	982.5	983.6	984.6
170°	993.6	992.7	991.8	991.0	990.6	990.8	991.0	991.1	991.3	992.3	993.4
172.5°	1000.0	999.2	998.5	997.8	997.4	997.5	997.5	997.5	997.6	998.7	999.9
175°	1008.4	1007.5	1006.7	1005.8	1005.3	1005.1	1004.9	1004.8	1004.6	1005.8	1007.0
177.5°	1011.4	1010.7	1010.0	1009.3	1009.0	1009.0	1009.0	1009.0	1009.0	1009.9	1010.9
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1353.2	1354.1	1357.9	1360.9	1361.7	1366.0	1366.4
5°	1472.1	1481.2	1498.7	1500.3	1503.0	1516.8	1506.2
7.5°	1611.5	1634.4	1649.8	1663.3	1668.2	1674.2	1673.0
10°	1700.8	1734.9	1751.9	1779.0	1780.1	1787.0	1782.7
12.5°	1790.6	1830.2	1861.2	1866.2	1889.0	1892.5	1898.5
15°	1917.8	1959.8	2002.9	2018.3	2049.7	2057.2	2068.9
17.5°	2037.4	2080.3	2110.5	2150.4	2163.3	2180.5	2168.8
20°	2102.9	2149.7	2188.0	2219.4	2232.7	2242.2	2241.2
22.5°	2142.5	2189.7	2220.7	2244.5	2256.9	2261.0	2260.7
25°	2167.2	2194.4	2203.9	2213.0	2199.2	2194.4	2196.5
27.5°	2098.3	2091.3	2066.3	2033.5	1999.5	1972.5	1957.8
30°	2003.4	1962.0	1924.2	1858.2	1824.2	1804.0	1785.9
32.5°	1869.0	1803.3	1730.6	1670.2	1631.5	1601.5	1597.0
35°	1638.6	1539.7	1450.9	1376.9	1338.6	1306.2	1298.7
37.5°	1393.1	1290.3	1210.4	1145.3	1104.1	1081.2	1059.8
40°	1230.1	1141.9	1063.1	1007.8	976.5	960.0	946.7
42.5°	1104.6	1024.0	945.7	903.6	875.2	865.1	857.3
45°	931.2	856.3	802.0	770.1	753.6	736.6	728.6
47.5°	792.4	731.4	695.6	668.5	650.9	640.8	635.7
50°	713.7	663.7	631.8	611.1	595.1	587.1	582.9
52.5°	643.9	602.9	576.1	559.6	548.8	542.9	541.2
55°	554.7	523.3	506.3	492.0	484.0	478.7	476.5
57.5°	482.2	458.0	444.2	432.4	429.3	424.8	423.3
60°	434.5	415.9	404.2	396.2	393.6	388.2	389.3
62.5°	392.4	377.2	367.2	362.6	359.1	354.6	356.1
65°	331.9	320.7	315.4	311.1	306.9	304.2	306.3
67.5°	278.5	270.8	263.6	261.1	259.0	258.6	256.3
70°	243.6	237.2	230.8	229.2	229.2	227.1	226.6
72.5°	210.0	205.3	201.0	199.9	198.2	199.0	196.8
75°	162.2	158.5	156.9	155.3	154.8	154.8	153.2
77.5°	119.9	117.1	114.6	114.6	112.6	111.9	111.7
80°	90.9	89.9	87.8	87.8	86.7	87.2	86.2
82.5°	68.4	66.9	66.5	65.6	64.1	64.2	63.2
85°	36.7	35.1	34.6	33.0	31.9	33.0	31.9
87.5°	16.8	16.6	16.3	15.5	15.2	15.3	14.1
90°	20.3	21.4	22.1	22.4	22.8	23.1	23.5
92.5°	32.8	33.5	33.9	34.1	34.3	34.5	34.7
95°	61.0	61.5	61.8	61.8	61.8	61.8	61.8
97.5°	95.8	96.5	96.8	96.8	96.8	96.8	96.8
100°	120.7	121.0	121.2	121.2	121.2	121.2	121.2
102.5°	147.3	147.8	148.1	148.3	148.4	148.6	148.7
105°	187.6	188.1	188.7	189.2	189.7	190.2	190.8
107.5°	231.1	231.6	231.9	231.8	231.8	231.8	231.7
110°	259.3	258.9	259.0	259.6	260.1	260.6	261.1



TEST NUMBER: P332599

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	290.8	290.7	290.7	290.8	290.9	291.0	291.1
115°	338.8	338.6	338.4	338.3	338.1	337.9	337.7
117.5°	384.6	384.0	383.5	383.2	382.8	382.5	382.1
120°	415.6	414.8	414.5	414.9	415.2	415.6	415.9
122.5°	447.8	447.2	446.6	445.9	445.3	444.7	444.1
125°	494.6	494.3	493.9	493.6	493.2	492.9	492.5
127.5°	539.2	538.8	538.5	538.2	538.0	537.7	537.4
130°	570.4	570.1	569.6	568.9	568.2	567.5	566.8
132.5°	599.8	599.5	599.2	598.9	598.6	598.3	598.1
135°	643.9	643.6	643.1	642.6	642.1	641.6	641.1
137.5°	686.5	686.0	685.8	685.9	686.0	686.1	686.3
140°	714.8	714.6	714.5	714.3	714.1	713.9	713.8
142.5°	741.5	741.5	741.4	741.4	741.4	741.3	741.3
145°	781.3	781.1	780.7	780.2	779.7	779.2	778.7
147.5°	817.5	817.3	817.2	817.0	816.8	816.7	816.5
150°	840.4	840.4	840.3	840.2	840.0	839.8	839.6
152.5°	862.3	862.7	862.7	862.3	861.8	861.4	860.9
155°	892.5	893.2	893.2	892.5	891.8	891.1	890.5
157.5°	918.8	919.3	919.2	918.7	918.1	917.5	916.9
160°	935.0	935.5	935.4	934.5	933.6	932.8	931.9
162.5°	950.0	951.0	951.0	950.1	949.3	948.4	947.5
165°	969.4	970.5	970.6	969.9	969.2	968.5	967.9
167.5°	985.7	986.7	986.7	985.6	984.5	983.5	982.4
170°	994.4	995.5	995.4	994.2	993.0	991.7	990.5
172.5°	1001.1	1002.3	1002.3	1001.1	999.8	998.6	997.4
175°	1008.2	1009.5	1009.5	1008.2	1007.0	1005.8	1004.6
177.5°	1011.9	1012.9	1012.8	1011.7	1010.6	1009.5	1008.3
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8

(END OF REPORT)