

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332600

Luminaire Tested: **S124DIP-S795D810U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332600  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S795D810U835-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6439.0 lumens  
Efficiency: N/A  
Efficacy: 140.3 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	73	71	65	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	52	48	46	44	40
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	31	28	25	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10365	10365	10365	10365
5°	12206	10391	9172	10391
10°	14614	10346	8257	10346
15°	17291	10242	7583	10242
20°	19254	10134	6981	10134
25°	19565	9977	6566	9977
30°	16648	9826	6435	9826
35°	12799	9581	6436	9581
40°	9977	9293	6558	9293
45°	8318	8859	6667	8859
50°	7321	8329	6894	8329
55°	6707	7695	7171	7695
60°	6286	7127	7505	7127
65°	5851	6491	7782	6491
70°	5349	5863	7959	5863
75°	4779	5159	7863	5159
80°	4007	4226	7615	4226
85°	2955	3057	7290	3057



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.1	1.9
10°-20°	385.5	6.0
20°-30°	611.3	9.5
30°-40°	680.3	10.6
40°-50°	619.3	9.6
50°-60°	506.1	7.9
60°-70°	361.3	5.6
70°-80°	198.9	3.1
80°-90°	56.5	0.9
90°-100°	287.5	4.5
100°-110°	598.3	9.3
110°-120°	535.9	8.3
120°-130°	450.8	7.0
130°-140°	375.9	5.8
140°-150°	287.1	4.5
150°-160°	201.8	3.1
160°-170°	118.7	1.8
170°-180°	38.6	0.6
0°-30°	1121.9	17.4
0°-40°	1802.3	28.0
0°-60°	2927.7	45.5
0°-90°	3544.4	55.0
90°-120°	1421.6	22.1
90°-150°	2535.4	39.4
90°-180°	2895.0	45.0
0°-180°	6439.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1506	1282	1132	1282	1506	153
15°	2069	1225	907	1225	2069	585
25°	2196	1120	737	1120	2196	968
35°	1299	972	653	972	1299	824
45°	729	776	584	776	729	574
55°	476	547	510	547	476	430
65°	306	340	407	340	306	303
75°	153	165	252	165	153	163
85°	32	33	79	33	32	39
90°	16	1	16	1	16	14
95°	191	26	191	26	191	296
105°	1100	92	1100	92	1100	1088
115°	1056	161	1056	161	1056	1049
125°	843	224	843	224	843	766
135°	754	267	754	267	754	582
145°	615	307	615	307	615	390
155°	515	350	515	350	515	240
165°	450	381	450	381	450	129
175°	405	397	405	397	405	39
180°	398	398	398	398	398	



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1366.4	1366.0	1361.7	1360.9	1357.9	1354.1	1353.2	1346.4	1332.8	1326.4	1324.7
5°	1506.2	1516.8	1503.0	1500.3	1498.7	1481.2	1472.1	1461.5	1437.0	1422.7	1411.5
7.5°	1673.0	1674.2	1668.2	1663.3	1649.8	1634.4	1611.5	1587.0	1557.9	1527.5	1504.7
10°	1782.7	1787.0	1780.1	1779.0	1751.9	1734.9	1700.8	1672.1	1639.1	1602.4	1568.9
12.5°	1898.5	1892.5	1889.0	1866.2	1861.2	1830.2	1790.6	1761.0	1710.2	1668.0	1623.4
15°	2068.9	2057.2	2049.7	2018.3	2002.9	1959.8	1917.8	1885.4	1818.9	1755.6	1707.7
17.5°	2168.8	2180.5	2163.3	2150.4	2110.5	2080.3	2037.4	1969.3	1917.3	1838.7	1778.3
20°	2241.2	2242.2	2232.7	2219.4	2188.0	2149.7	2102.9	2028.4	1966.2	1888.0	1805.1
22.5°	2260.7	2261.0	2256.9	2244.5	2220.7	2189.7	2142.5	2080.3	2004.9	1919.9	1837.0
25°	2196.5	2194.4	2199.2	2213.0	2203.9	2194.4	2167.2	2121.0	2050.8	1960.9	1871.5
27.5°	1957.8	1972.5	1999.5	2033.5	2066.3	2091.3	2098.3	2088.8	2045.3	1971.4	1877.8
30°	1785.9	1804.0	1824.2	1858.2	1924.2	1962.0	2003.4	2034.8	2017.3	1958.2	1871.0
32.5°	1597.0	1601.5	1631.5	1670.2	1730.6	1803.3	1869.0	1932.7	1953.9	1922.9	1850.2
35°	1298.7	1306.2	1338.6	1376.9	1450.9	1539.7	1638.6	1726.9	1799.7	1829.0	1791.8
37.5°	1059.8	1081.2	1104.1	1145.3	1210.4	1290.3	1393.1	1507.3	1615.9	1688.7	1701.0
40°	946.7	960.0	976.5	1007.8	1063.1	1141.9	1230.1	1361.0	1476.4	1580.6	1614.7
42.5°	857.3	865.1	875.2	903.6	945.7	1024.0	1104.6	1219.7	1335.6	1460.2	1517.2
45°	728.6	736.6	753.6	770.1	802.0	856.3	931.2	1025.9	1142.4	1262.6	1367.9
47.5°	635.7	640.8	650.9	668.5	695.6	731.4	792.4	871.5	979.4	1096.1	1208.3
50°	582.9	587.1	595.1	611.1	631.8	663.7	713.7	787.7	872.2	989.8	1099.8
52.5°	541.2	542.9	548.8	559.6	576.1	602.9	643.9	705.1	783.7	888.5	998.2
55°	476.5	478.7	484.0	492.0	506.3	523.3	554.7	600.4	669.1	760.0	855.2
57.5°	423.3	424.8	429.3	432.4	444.2	458.0	482.2	514.8	566.8	643.9	728.9
60°	389.3	388.2	393.6	396.2	404.2	415.9	434.5	465.9	511.1	573.3	651.5
62.5°	356.1	354.6	359.1	362.6	367.2	377.2	392.4	417.0	453.7	509.9	577.5
65°	306.3	304.2	306.9	311.1	315.4	320.7	331.9	353.7	382.9	423.3	474.9
67.5°	256.3	258.6	259.0	261.1	263.6	270.8	278.5	293.9	314.5	346.9	390.6
70°	226.6	227.1	229.2	229.2	230.8	237.2	243.6	252.6	272.8	302.6	338.2
72.5°	196.8	199.0	198.2	199.9	201.0	205.3	210.0	218.6	235.8	257.9	288.0
75°	153.2	154.8	154.8	155.3	156.9	158.5	162.2	168.6	180.8	197.3	218.1
77.5°	111.7	111.9	112.6	114.6	114.6	117.1	119.9	125.0	131.0	142.3	155.0
80°	86.2	87.2	86.7	87.8	87.8	89.9	90.9	97.3	100.0	107.4	117.5
82.5°	63.2	64.2	64.1	65.6	66.5	66.9	68.4	70.9	73.6	80.2	84.3
85°	31.9	33.0	31.9	33.0	34.6	35.1	36.7	37.2	39.4	41.0	44.7
87.5°	12.6	13.9	14.1	14.3	15.0	15.5	15.7	15.2	16.7	17.3	18.7
90°	16.4	16.4	17.2	16.4	15.6	15.6	14.9	14.1	13.3	14.1	12.5
92.5°	60.2	60.2	62.9	67.1	76.3	92.0	115.6	153.6	206.6	248.0	217.1
95°	190.8	201.0	215.0	239.3	277.6	353.4	458.2	579.4	655.3	637.3	480.9
97.5°	510.0	526.2	549.7	596.8	652.9	734.5	811.0	856.0	823.2	671.2	450.1
100°	717.0	723.3	746.7	794.4	862.5	920.3	958.6	943.0	828.8	628.7	408.2
102.5°	897.2	902.2	926.9	961.5	1003.2	1027.3	1016.2	938.6	781.9	575.5	380.0
105°	1100.2	1104.9	1115.8	1122.1	1120.5	1088.4	1011.0	875.8	696.7	512.9	355.8
107.5°	1175.5	1173.5	1165.7	1147.9	1109.2	1039.5	930.5	786.5	627.9	477.9	351.4
110°	1176.8	1169.8	1155.7	1122.8	1067.3	981.3	867.9	732.7	593.5	466.0	352.6



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1139.9	1128.5	1108.8	1069.0	1006.0	920.0	812.9	693.3	574.1	460.4	356.4
115°	1056.4	1050.1	1025.1	978.2	916.4	841.3	749.9	653.7	555.9	457.4	363.6
117.5°	971.8	966.9	941.6	902.2	849.5	785.8	713.9	634.3	547.8	456.6	371.3
120°	924.2	915.6	895.3	860.9	816.3	760.8	698.3	625.5	543.4	456.6	376.9
122.5°	886.7	878.1	860.9	831.5	793.8	745.2	688.2	618.0	538.4	456.0	382.5
125°	842.9	838.2	823.4	800.7	769.4	726.4	672.5	605.2	530.1	455.1	391.0
127.5°	817.3	812.6	800.1	779.9	748.5	707.6	653.8	589.6	519.0	453.4	397.7
130°	802.3	797.6	785.1	765.5	733.4	692.0	638.8	577.1	512.2	452.7	402.7
132.5°	785.4	780.7	768.8	746.7	715.3	673.9	621.9	563.9	505.9	452.1	407.1
135°	753.8	749.1	736.6	714.7	683.4	644.3	596.6	545.8	496.5	451.2	413.6
137.5°	714.7	709.0	698.7	677.1	647.9	612.6	572.4	529.4	488.4	451.0	417.5
140°	686.5	680.3	669.3	652.1	624.8	591.9	556.7	520.0	484.0	450.4	420.7
142.5°	656.5	652.1	642.4	626.5	602.2	573.8	543.6	511.2	480.3	450.4	423.2
145°	615.4	611.5	603.6	590.4	570.8	548.9	525.5	498.9	473.8	448.8	424.6
147.5°	578.9	577.5	571.6	560.2	545.8	528.6	509.8	488.7	468.1	446.0	425.4
150°	558.3	557.5	552.8	542.7	530.1	516.1	500.4	482.4	463.7	444.1	425.4
152.5°	539.5	538.7	535.9	527.6	517.0	505.4	491.0	475.6	458.7	441.0	424.1
155°	515.3	515.3	512.9	506.7	498.9	489.5	477.8	465.2	451.2	436.3	422.2
157.5°	494.0	494.0	492.6	487.9	482.0	474.5	464.6	454.1	443.5	431.5	420.2
160°	480.9	480.9	480.1	475.4	470.7	464.5	455.9	447.3	437.9	427.7	418.3
162.5°	468.4	469.0	468.2	463.5	460.1	454.5	447.7	440.4	432.9	424.0	416.5
165°	449.6	450.4	451.2	448.0	444.9	441.0	435.5	430.8	424.6	418.3	412.9
167.5°	434.7	435.4	435.5	433.5	431.9	429.6	425.2	421.6	417.1	412.7	409.1
170°	425.4	425.4	426.1	425.4	423.8	421.5	418.3	416.0	412.1	408.9	406.6
172.5°	416.0	417.2	418.0	417.2	416.3	414.6	412.7	411.0	407.7	405.2	404.1
175°	405.0	406.6	408.2	406.6	406.6	406.6	405.0	404.3	402.7	401.1	401.1
177.5°	398.6	399.9	401.1	400.5	401.1	400.5	400.5	399.9	399.2	398.6	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1325.1	1319.2	1314.9	1311.5	1302.2	1296.6	1292.4	1286.4	1279.6	1272.4	1263.4
5°	1400.3	1382.2	1369.0	1348.7	1329.6	1313.6	1297.2	1282.3	1264.2	1244.5	1230.1
7.5°	1479.4	1452.5	1418.0	1388.1	1354.5	1325.2	1299.1	1272.3	1244.4	1217.4	1192.6
10°	1529.6	1495.0	1456.7	1411.5	1369.0	1331.2	1296.1	1262.1	1229.1	1196.1	1167.9
12.5°	1583.6	1540.5	1483.9	1431.1	1383.4	1332.9	1290.6	1248.9	1209.1	1174.4	1141.5
15°	1656.1	1593.9	1528.5	1457.8	1395.0	1336.0	1278.0	1225.4	1180.7	1134.9	1103.0
17.5°	1700.7	1623.7	1548.9	1475.0	1399.1	1324.6	1262.1	1201.3	1145.4	1099.9	1059.7
20°	1730.1	1653.5	1560.4	1486.5	1396.1	1319.5	1247.2	1179.6	1121.1	1072.7	1031.2
22.5°	1755.6	1667.1	1574.0	1476.7	1386.7	1305.5	1226.3	1158.3	1098.6	1047.6	1007.8
25°	1769.4	1667.8	1566.8	1470.0	1367.9	1271.6	1199.8	1120.1	1056.2	1002.5	960.0
27.5°	1770.9	1662.3	1548.0	1440.4	1335.0	1245.4	1154.7	1083.5	1017.2	960.4	919.5
30°	1766.2	1653.0	1530.1	1413.6	1307.8	1210.5	1131.8	1054.1	986.6	930.2	887.6
32.5°	1751.3	1633.4	1507.1	1383.8	1274.2	1179.0	1097.7	1023.9	958.1	902.5	857.9
35°	1708.3	1591.8	1457.2	1329.1	1216.8	1120.6	1047.2	972.2	906.3	853.6	810.5
37.5°	1640.9	1535.6	1398.8	1266.2	1156.0	1059.3	986.6	918.8	859.3	805.8	761.7
40°	1582.2	1489.7	1352.5	1223.2	1104.1	1012.1	944.0	881.8	822.8	772.2	730.2
42.5°	1514.6	1433.9	1307.4	1170.5	1055.6	963.2	896.8	840.9	785.3	738.6	696.6
45°	1393.9	1340.8	1221.6	1095.1	975.4	888.2	824.9	776.0	729.2	683.4	648.3
47.5°	1255.2	1228.9	1128.6	1008.4	894.8	808.8	753.9	708.7	667.7	629.0	598.0
50°	1162.1	1149.3	1062.6	946.7	838.2	757.3	702.0	663.2	628.1	594.1	564.8
52.5°	1070.2	1069.7	991.6	885.4	785.0	707.1	652.2	616.0	585.6	557.9	531.6
55°	929.7	944.5	883.4	788.7	698.8	628.6	579.2	546.7	525.5	502.6	482.9
57.5°	800.6	825.3	774.9	691.5	616.5	551.8	508.8	484.4	461.7	447.9	433.6
60°	716.4	739.8	700.4	630.2	559.5	504.2	463.2	441.4	421.7	412.2	402.1
62.5°	641.5	662.4	633.2	568.1	506.7	453.6	419.0	398.0	384.7	374.3	367.6
65°	534.5	552.0	527.1	479.7	427.1	384.5	356.3	339.8	327.1	322.8	315.4
67.5°	432.1	448.0	434.5	394.3	352.1	319.8	297.8	282.0	274.4	270.7	265.4
70°	371.2	387.2	372.8	337.7	305.3	278.2	257.4	248.4	240.4	238.8	231.3
72.5°	319.7	330.6	316.2	288.8	261.0	238.2	222.1	212.6	208.5	205.6	201.6
75°	239.9	249.4	239.9	218.6	198.9	183.0	169.1	165.4	160.6	159.0	156.4
77.5°	169.8	178.1	170.7	157.4	142.7	130.4	123.0	118.2	117.1	114.3	115.6
80°	129.8	135.1	128.2	119.1	107.4	98.9	93.6	90.9	87.8	86.7	88.8
82.5°	93.2	95.5	92.0	85.9	77.2	71.7	68.1	65.0	64.4	64.6	64.6
85°	48.4	47.9	47.3	42.0	39.4	35.6	33.5	33.0	32.4	33.5	34.6
87.5°	18.4	18.8	17.4	15.7	14.3	12.9	12.0	11.2	12.0	12.9	13.4
90°	10.9	10.9	6.3	6.3	5.5	4.7	2.3	0.8	2.3	4.7	5.5
92.5°	157.9	97.3	57.5	41.3	29.9	20.3	13.0	8.9	13.0	20.3	29.9
95°	294.0	165.8	97.7	64.9	46.1	36.0	28.1	25.8	28.1	36.0	46.1
97.5°	264.3	158.4	106.0	78.5	62.4	53.0	46.3	46.3	46.3	53.0	62.4
100°	248.7	160.3	114.2	89.1	74.3	64.9	59.4	59.4	59.4	64.9	74.3
102.5°	244.3	166.5	124.8	101.0	86.8	78.0	73.2	71.9	73.2	78.0	86.8
105°	246.3	181.4	143.9	121.2	107.1	97.7	93.8	91.5	93.8	97.7	107.1
107.5°	257.9	198.8	164.4	142.0	128.5	118.5	114.6	113.1	114.6	118.5	128.5
110°	266.6	211.9	177.5	156.4	142.3	132.9	129.0	127.5	129.0	132.9	142.3





TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	276.0	224.4	191.3	170.1	156.1	147.3	142.8	141.2	142.8	147.3	156.1
115°	290.9	244.0	212.7	191.6	176.7	168.9	163.4	161.1	163.4	168.9	176.7
117.5°	306.0	262.9	233.2	211.3	197.4	188.8	183.9	181.7	183.9	188.8	197.4
120°	316.7	276.0	246.3	224.4	211.1	202.5	197.0	195.5	197.0	202.5	211.1
122.5°	326.7	288.5	258.8	237.5	223.0	215.0	209.6	208.0	209.6	215.0	223.0
125°	341.7	305.7	277.6	255.7	240.8	232.2	227.5	224.4	227.5	232.2	240.8
127.5°	354.7	321.7	294.5	272.4	256.9	247.1	241.5	239.0	241.5	247.1	256.9
130°	362.8	332.3	305.7	283.1	268.2	256.5	250.2	247.1	250.2	256.5	268.2
132.5°	370.9	341.1	314.5	293.1	277.0	265.9	257.7	255.2	257.7	265.9	277.0
135°	381.6	353.4	327.6	307.3	290.9	277.6	269.8	266.6	269.8	277.6	290.9
137.5°	389.1	362.8	338.7	319.3	302.3	289.6	281.0	278.1	281.0	289.6	302.3
140°	394.1	369.1	345.6	326.8	310.4	297.1	288.5	286.2	288.5	297.1	310.4
142.5°	397.8	374.7	351.9	333.7	317.9	305.3	297.3	294.9	297.3	305.3	317.9
145°	401.9	380.8	360.5	343.3	328.4	317.5	309.6	307.3	309.6	317.5	328.4
147.5°	405.5	387.1	368.0	352.5	340.1	328.9	322.0	321.2	322.0	328.9	340.1
150°	407.4	390.2	373.0	358.1	346.4	337.0	330.8	330.0	330.8	337.0	346.4
152.5°	408.6	392.7	377.4	363.8	353.3	344.5	338.3	338.1	338.3	344.5	353.3
155°	409.7	396.4	383.1	371.4	362.8	355.0	350.3	349.5	350.3	355.0	362.8
157.5°	409.7	399.1	387.8	378.6	371.1	365.0	360.6	360.6	360.6	365.0	371.1
160°	409.7	400.3	391.0	382.4	376.1	370.6	367.5	367.5	367.5	370.6	376.1
162.5°	409.7	401.6	392.8	386.1	380.5	375.6	373.1	373.8	373.1	375.6	380.5
165°	408.2	401.9	394.9	390.2	386.3	382.4	380.8	380.8	380.8	382.4	386.3
167.5°	406.3	401.8	396.6	393.0	390.8	387.8	387.1	387.8	387.1	387.8	390.8
170°	405.0	401.1	397.2	394.9	393.3	391.0	390.2	391.0	390.2	391.0	393.3
172.5°	403.8	400.5	397.8	396.1	395.2	393.5	393.3	394.1	393.3	393.5	395.2
175°	401.9	399.6	398.0	398.0	397.2	396.4	396.4	397.2	396.4	396.4	397.2
177.5°	399.9	398.6	398.0	398.0	398.0	397.4	398.0	398.6	398.0	397.4	398.0
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1259.2	1255.4	1249.8	1242.2	1235.8	1229.0	1227.3	1224.7	1229.8	1225.6	1224.3
5°	1217.9	1206.7	1192.4	1175.9	1166.3	1152.5	1149.8	1144.5	1139.2	1138.7	1133.3
7.5°	1174.2	1157.8	1139.0	1122.2	1106.6	1091.5	1081.7	1079.5	1071.7	1067.1	1061.8
10°	1146.1	1125.9	1104.1	1088.1	1070.1	1054.1	1042.9	1036.6	1031.2	1025.4	1020.1
12.5°	1112.9	1091.4	1073.5	1056.2	1034.7	1022.6	1004.2	993.2	992.1	992.2	978.4
15°	1074.3	1053.0	1025.4	1000.9	989.2	965.8	955.7	942.9	935.0	927.0	920.6
17.5°	1030.2	1003.7	982.1	954.0	931.7	913.1	899.8	892.1	880.1	868.8	860.6
20°	1002.5	974.3	951.5	921.7	897.2	874.3	863.2	852.5	843.5	833.9	824.9
22.5°	974.4	945.0	917.0	888.1	865.3	841.2	830.4	815.9	807.3	802.0	793.0
25°	930.2	898.3	866.4	838.7	815.3	794.0	779.7	768.5	758.9	754.7	748.8
27.5°	882.1	850.4	819.6	788.2	761.6	746.2	734.7	726.3	720.7	715.1	712.5
30°	851.5	818.5	785.5	756.3	731.8	716.4	705.7	699.9	695.6	693.0	690.3
32.5°	820.4	787.9	753.2	726.5	704.6	690.9	682.8	676.9	674.8	673.8	672.9
35°	770.6	737.7	705.7	681.8	661.1	655.8	648.8	645.7	644.6	648.3	649.9
37.5°	722.4	691.8	662.5	639.3	625.7	617.9	615.5	615.7	619.5	622.8	626.6
40°	691.4	661.6	634.0	613.7	601.0	596.2	595.1	597.8	602.0	605.8	610.0
42.5°	661.2	631.8	606.7	587.8	578.9	574.5	575.1	577.8	583.7	588.3	594.7
45°	614.3	589.8	565.3	549.9	542.5	543.5	543.5	548.3	554.2	561.1	568.0
47.5°	570.1	545.5	525.3	512.4	508.5	507.6	510.6	516.8	525.2	533.8	543.4
50°	540.3	516.9	499.4	487.7	483.4	485.0	489.3	495.1	505.2	515.9	526.0
52.5°	510.1	488.9	472.6	461.7	458.8	461.6	465.9	475.1	484.0	495.5	507.7
55°	463.2	445.1	432.4	424.4	423.3	424.9	429.7	439.8	452.6	467.0	478.7
57.5°	416.5	401.4	389.7	384.2	384.7	386.2	394.1	406.1	419.7	435.0	450.1
60°	385.1	371.2	361.7	357.4	357.9	361.1	370.7	381.9	398.9	413.8	429.7
62.5°	355.3	343.1	334.0	330.2	329.4	336.4	345.6	357.2	374.2	390.8	408.0
65°	307.4	297.8	290.4	288.3	289.9	295.2	306.9	322.3	336.7	354.2	372.3
67.5°	260.6	252.7	247.6	248.6	250.5	258.4	268.2	281.4	297.7	315.9	333.8
70°	230.8	223.4	219.1	219.6	222.8	232.4	240.9	254.2	271.8	290.4	305.3
72.5°	200.2	195.3	191.5	193.7	196.9	203.5	214.1	227.4	242.8	260.2	275.9
75°	153.7	153.7	151.6	153.2	158.0	164.3	172.3	186.1	201.6	215.4	228.2
77.5°	114.0	112.9	114.2	116.2	118.9	126.5	135.6	145.5	157.1	170.9	181.5
80°	87.2	87.8	90.4	93.6	94.7	100.5	110.1	119.1	128.2	139.9	150.0
82.5°	65.5	66.1	67.4	71.5	72.5	78.8	85.0	94.0	102.2	110.1	118.5
85°	35.6	35.6	38.3	39.9	42.5	46.8	50.5	55.8	63.3	68.6	76.6
87.5°	14.9	14.9	17.5	18.4	19.9	22.4	23.1	27.9	29.8	32.1	35.9
90°	6.3	6.3	10.9	10.9	12.5	14.1	13.3	14.1	14.9	15.6	15.6
92.5°	41.3	57.5	97.3	157.9	217.1	248.0	206.6	153.6	115.6	92.0	76.3
95°	64.9	97.7	165.8	294.0	480.9	637.3	655.3	579.4	458.2	353.4	277.6
97.5°	78.5	106.0	158.4	264.3	450.1	671.2	823.2	856.0	811.0	734.5	652.9
100°	89.1	114.2	160.3	248.7	408.2	628.7	828.8	943.0	958.6	920.3	862.5
102.5°	101.0	124.8	166.5	244.3	380.0	575.5	781.9	938.6	1016.2	1027.3	1003.2
105°	121.2	143.9	181.4	246.3	355.8	512.9	696.7	875.8	1011.0	1088.4	1120.5
107.5°	142.0	164.4	198.8	257.9	351.4	477.9	627.9	786.5	930.5	1039.5	1109.2
110°	156.4	177.5	211.9	266.6	352.6	466.0	593.5	732.7	867.9	981.3	1067.3



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.1	191.3	224.4	276.0	356.4	460.4	574.1	693.3	812.9	920.0	1006.0
115°	191.6	212.7	244.0	290.9	363.6	457.4	555.9	653.7	749.9	841.3	916.4
117.5°	211.3	233.2	262.9	306.0	371.3	456.6	547.8	634.3	713.9	785.8	849.5
120°	224.4	246.3	276.0	316.7	376.9	456.6	543.4	625.5	698.3	760.8	816.3
122.5°	237.5	258.8	288.5	326.7	382.5	456.0	538.4	618.0	688.2	745.2	793.8
125°	255.7	277.6	305.7	341.7	391.0	455.1	530.1	605.2	672.5	726.4	769.4
127.5°	272.4	294.5	321.7	354.7	397.7	453.4	519.0	589.6	653.8	707.6	748.5
130°	283.1	305.7	332.3	362.8	402.7	452.7	512.2	577.1	638.8	692.0	733.4
132.5°	293.1	314.5	341.1	370.9	407.1	452.1	505.9	563.9	621.9	673.9	715.3
135°	307.3	327.6	353.4	381.6	413.6	451.2	496.5	545.8	596.6	644.3	683.4
137.5°	319.3	338.7	362.8	389.1	417.5	451.0	488.4	529.4	572.4	612.6	647.9
140°	326.8	345.6	369.1	394.1	420.7	450.4	484.0	520.0	556.7	591.9	624.8
142.5°	333.7	351.9	374.7	397.8	423.2	450.4	480.3	511.2	543.6	573.8	602.2
145°	343.3	360.5	380.8	401.9	424.6	448.8	473.8	498.9	525.5	548.9	570.8
147.5°	352.5	368.0	387.1	405.5	425.4	446.0	468.1	488.7	509.8	528.6	545.8
150°	358.1	373.0	390.2	407.4	425.4	444.1	463.7	482.4	500.4	516.1	530.1
152.5°	363.8	377.4	392.7	408.6	424.1	441.0	458.7	475.6	491.0	505.4	517.0
155°	371.4	383.1	396.4	409.7	422.2	436.3	451.2	465.2	477.8	489.5	498.9
157.5°	378.6	387.8	399.1	409.7	420.2	431.5	443.5	454.1	464.6	474.5	482.0
160°	382.4	391.0	400.3	409.7	418.3	427.7	437.9	447.3	455.9	464.5	470.7
162.5°	386.1	392.8	401.6	409.7	416.5	424.0	432.9	440.4	447.7	454.5	460.1
165°	390.2	394.9	401.9	408.2	412.9	418.3	424.6	430.8	435.5	441.0	444.9
167.5°	393.0	396.6	401.8	406.3	409.1	412.7	417.1	421.6	425.2	429.6	431.9
170°	394.9	397.2	401.1	405.0	406.6	408.9	412.1	416.0	418.3	421.5	423.8
172.5°	396.1	397.8	400.5	403.8	404.1	405.2	407.7	411.0	412.7	414.6	416.3
175°	398.0	398.0	399.6	401.9	401.1	401.1	402.7	404.3	405.0	406.6	406.6
177.5°	398.0	398.0	398.6	399.9	398.6	398.6	399.2	399.9	400.5	400.5	401.1
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1223.4	1222.6	1219.6	1219.2	1219.6	1222.6	1223.4	1224.3	1225.6	1229.8	1224.7
5°	1130.2	1127.5	1125.9	1131.8	1125.9	1127.5	1130.2	1133.3	1138.7	1139.2	1144.5
7.5°	1059.8	1057.7	1053.0	1051.6	1053.0	1057.7	1059.8	1061.8	1067.1	1071.7	1079.5
10°	1014.7	1012.6	1008.4	1007.3	1008.4	1012.6	1014.7	1020.1	1025.4	1031.2	1036.6
12.5°	971.3	967.1	966.2	967.3	966.2	967.1	971.3	978.4	992.2	992.1	993.2
15°	913.7	911.6	905.7	907.3	905.7	911.6	913.7	920.6	927.0	935.0	942.9
17.5°	856.9	854.3	847.2	853.5	847.2	854.3	856.9	860.6	868.8	880.1	892.1
20°	821.2	816.9	813.2	812.6	813.2	816.9	821.2	824.9	833.9	843.5	852.5
22.5°	787.1	783.3	783.0	779.5	783.0	783.3	787.1	793.0	802.0	807.3	815.9
25°	744.6	740.9	739.8	737.1	739.8	740.9	744.6	748.8	754.7	758.9	768.5
27.5°	711.9	710.1	708.2	709.0	708.2	710.1	711.9	712.5	715.1	720.7	726.3
30°	691.9	691.4	690.3	690.3	690.3	691.4	691.9	690.3	693.0	695.6	699.9
32.5°	675.3	675.2	675.9	675.9	675.9	675.2	675.3	672.9	673.8	674.8	676.9
35°	652.0	653.6	654.7	653.1	654.7	653.6	652.0	649.9	648.3	644.6	645.7
37.5°	631.0	632.6	634.1	635.9	634.1	632.6	631.0	626.6	622.8	619.5	615.7
40°	614.8	618.5	619.6	622.3	619.6	618.5	614.8	610.0	605.8	602.0	597.8
42.5°	599.5	603.6	606.4	606.9	606.4	603.6	599.5	594.7	588.3	583.7	577.8
45°	576.0	580.2	584.0	584.0	584.0	580.2	576.0	568.0	561.1	554.2	548.3
47.5°	551.6	557.8	561.5	562.5	561.5	557.8	551.6	543.4	533.8	525.2	516.8
50°	535.0	542.5	546.2	548.9	546.2	542.5	535.0	526.0	515.9	505.2	495.1
52.5°	518.9	526.3	531.3	532.7	531.3	526.3	518.9	507.7	495.5	484.0	475.1
55°	490.9	501.5	507.4	509.5	507.4	501.5	490.9	478.7	467.0	452.6	439.8
57.5°	464.5	474.3	481.1	482.7	481.1	474.3	464.5	450.1	435.0	419.7	406.1
60°	444.1	454.7	463.2	464.8	463.2	454.7	444.1	429.7	413.8	398.9	381.9
62.5°	423.2	434.3	442.0	446.1	442.0	434.3	423.2	408.0	390.8	374.2	357.2
65°	387.2	398.3	405.8	407.4	405.8	398.3	387.2	372.3	354.2	336.7	322.3
67.5°	347.8	359.0	363.9	367.0	363.9	359.0	347.8	333.8	315.9	297.7	281.4
70°	320.2	329.2	334.5	337.2	334.5	329.2	320.2	305.3	290.4	271.8	254.2
72.5°	288.7	298.1	304.3	304.8	304.3	298.1	288.7	275.9	260.2	242.8	227.4
75°	240.4	248.9	252.1	252.1	252.1	248.9	240.4	228.2	215.4	201.6	186.1
77.5°	190.3	194.7	198.7	199.5	198.7	194.7	190.3	181.5	170.9	157.1	145.5
80°	158.0	160.6	163.8	163.8	163.8	160.6	158.0	150.0	139.9	128.2	119.1
82.5°	124.8	127.0	130.2	129.8	130.2	127.0	124.8	118.5	110.1	102.2	94.0
85°	75.5	80.3	79.8	78.7	79.8	80.3	75.5	76.6	68.6	63.3	55.8
87.5°	37.3	37.9	39.0	39.9	39.0	37.9	37.3	35.9	32.1	29.8	27.9
90°	16.4	17.2	16.4	16.4	16.4	17.2	16.4	15.6	15.6	14.9	14.1
92.5°	67.1	62.9	60.2	60.2	60.2	62.9	67.1	76.3	92.0	115.6	153.6
95°	239.3	215.0	201.0	190.8	201.0	215.0	239.3	277.6	353.4	458.2	579.4
97.5°	596.8	549.7	526.2	510.0	526.2	549.7	596.8	652.9	734.5	811.0	856.0
100°	794.4	746.7	723.3	717.0	723.3	746.7	794.4	862.5	920.3	958.6	943.0
102.5°	961.5	926.9	902.2	897.2	902.2	926.9	961.5	1003.2	1027.3	1016.2	938.6
105°	1122.1	1115.8	1104.9	1100.2	1104.9	1115.8	1122.1	1120.5	1088.4	1011.0	875.8
107.5°	1147.9	1165.7	1173.5	1175.5	1173.5	1165.7	1147.9	1109.2	1039.5	930.5	786.5
110°	1122.8	1155.7	1169.8	1176.8	1169.8	1155.7	1122.8	1067.3	981.3	867.9	732.7



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1069.0	1108.8	1128.5	1139.9	1128.5	1108.8	1069.0	1006.0	920.0	812.9	693.3
115°	978.2	1025.1	1050.1	1056.4	1050.1	1025.1	978.2	916.4	841.3	749.9	653.7
117.5°	902.2	941.6	966.9	971.8	966.9	941.6	902.2	849.5	785.8	713.9	634.3
120°	860.9	895.3	915.6	924.2	915.6	895.3	860.9	816.3	760.8	698.3	625.5
122.5°	831.5	860.9	878.1	886.7	878.1	860.9	831.5	793.8	745.2	688.2	618.0
125°	800.7	823.4	838.2	842.9	838.2	823.4	800.7	769.4	726.4	672.5	605.2
127.5°	779.9	800.1	812.6	817.3	812.6	800.1	779.9	748.5	707.6	653.8	589.6
130°	765.5	785.1	797.6	802.3	797.6	785.1	765.5	733.4	692.0	638.8	577.1
132.5°	746.7	768.8	780.7	785.4	780.7	768.8	746.7	715.3	673.9	621.9	563.9
135°	714.7	736.6	749.1	753.8	749.1	736.6	714.7	683.4	644.3	596.6	545.8
137.5°	677.1	698.7	709.0	714.7	709.0	698.7	677.1	647.9	612.6	572.4	529.4
140°	652.1	669.3	680.3	686.5	680.3	669.3	652.1	624.8	591.9	556.7	520.0
142.5°	626.5	642.4	652.1	656.5	652.1	642.4	626.5	602.2	573.8	543.6	511.2
145°	590.4	603.6	611.5	615.4	611.5	603.6	590.4	570.8	548.9	525.5	498.9
147.5°	560.2	571.6	577.5	578.9	577.5	571.6	560.2	545.8	528.6	509.8	488.7
150°	542.7	552.8	557.5	558.3	557.5	552.8	542.7	530.1	516.1	500.4	482.4
152.5°	527.6	535.9	538.7	539.5	538.7	535.9	527.6	517.0	505.4	491.0	475.6
155°	506.7	512.9	515.3	515.3	515.3	512.9	506.7	498.9	489.5	477.8	465.2
157.5°	487.9	492.6	494.0	494.0	494.0	492.6	487.9	482.0	474.5	464.6	454.1
160°	475.4	480.1	480.9	480.9	480.9	480.1	475.4	470.7	464.5	455.9	447.3
162.5°	463.5	468.2	469.0	468.4	469.0	468.2	463.5	460.1	454.5	447.7	440.4
165°	448.0	451.2	450.4	449.6	450.4	451.2	448.0	444.9	441.0	435.5	430.8
167.5°	433.5	435.5	435.4	434.7	435.4	435.5	433.5	431.9	429.6	425.2	421.6
170°	425.4	426.1	425.4	425.4	425.4	426.1	425.4	423.8	421.5	418.3	416.0
172.5°	417.2	418.0	417.2	416.0	417.2	418.0	417.2	416.3	414.6	412.7	411.0
175°	406.6	408.2	406.6	405.0	406.6	408.2	406.6	406.6	406.6	405.0	404.3
177.5°	400.5	401.1	399.9	398.6	399.9	401.1	400.5	401.1	400.5	400.5	399.9
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1227.3	1229.0	1235.8	1242.2	1249.8	1255.4	1259.2	1263.4	1272.4	1279.6	1286.4
5°	1149.8	1152.5	1166.3	1175.9	1192.4	1206.7	1217.9	1230.1	1244.5	1264.2	1282.3
7.5°	1081.7	1091.5	1106.6	1122.2	1139.0	1157.8	1174.2	1192.6	1217.4	1244.4	1272.3
10°	1042.9	1054.1	1070.1	1088.1	1104.1	1125.9	1146.1	1167.9	1196.1	1229.1	1262.1
12.5°	1004.2	1022.6	1034.7	1056.2	1073.5	1091.4	1112.9	1141.5	1174.4	1209.1	1248.9
15°	955.7	965.8	989.2	1000.9	1025.4	1053.0	1074.3	1103.0	1134.9	1180.7	1225.4
17.5°	899.8	913.1	931.7	954.0	982.1	1003.7	1030.2	1059.7	1099.9	1145.4	1201.3
20°	863.2	874.3	897.2	921.7	951.5	974.3	1002.5	1031.2	1072.7	1121.1	1179.6
22.5°	830.4	841.2	865.3	888.1	917.0	945.0	974.4	1007.8	1047.6	1098.6	1158.3
25°	779.7	794.0	815.3	838.7	866.4	898.3	930.2	960.0	1002.5	1056.2	1120.1
27.5°	734.7	746.2	761.6	788.2	819.6	850.4	882.1	919.5	960.4	1017.2	1083.5
30°	705.7	716.4	731.8	756.3	785.5	818.5	851.5	887.6	930.2	986.6	1054.1
32.5°	682.8	690.9	704.6	726.5	753.2	787.9	820.4	857.9	902.5	958.1	1023.9
35°	648.8	655.8	661.1	681.8	705.7	737.7	770.6	810.5	853.6	906.3	972.2
37.5°	615.5	617.9	625.7	639.3	662.5	691.8	722.4	761.7	805.8	859.3	918.8
40°	595.1	596.2	601.0	613.7	634.0	661.6	691.4	730.2	772.2	822.8	881.8
42.5°	575.1	574.5	578.9	587.8	606.7	631.8	661.2	696.6	738.6	785.3	840.9
45°	543.5	543.5	542.5	549.9	565.3	589.8	614.3	648.3	683.4	729.2	776.0
47.5°	510.6	507.6	508.5	512.4	525.3	545.5	570.1	598.0	629.0	667.7	708.7
50°	489.3	485.0	483.4	487.7	499.4	516.9	540.3	564.8	594.1	628.1	663.2
52.5°	465.9	461.6	458.8	461.7	472.6	488.9	510.1	531.6	557.9	585.6	616.0
55°	429.7	424.9	423.3	424.4	432.4	445.1	463.2	482.9	502.6	525.5	546.7
57.5°	394.1	386.2	384.7	384.2	389.7	401.4	416.5	433.6	447.9	461.7	484.4
60°	370.7	361.1	357.9	357.4	361.7	371.2	385.1	402.1	412.2	421.7	441.4
62.5°	345.6	336.4	329.4	330.2	334.0	343.1	355.3	367.6	374.3	384.7	398.0
65°	306.9	295.2	289.9	288.3	290.4	297.8	307.4	315.4	322.8	327.1	339.8
67.5°	268.2	258.4	250.5	248.6	247.6	252.7	260.6	265.4	270.7	274.4	282.0
70°	240.9	232.4	222.8	219.6	219.1	223.4	230.8	231.3	238.8	240.4	248.4
72.5°	214.1	203.5	196.9	193.7	191.5	195.3	200.2	201.6	205.6	208.5	212.6
75°	172.3	164.3	158.0	153.2	151.6	153.7	153.7	156.4	159.0	160.6	165.4
77.5°	135.6	126.5	118.9	116.2	114.2	112.9	114.0	115.6	114.3	117.1	118.2
80°	110.1	100.5	94.7	93.6	90.4	87.8	87.2	88.8	86.7	87.8	90.9
82.5°	85.0	78.8	72.5	71.5	67.4	66.1	65.5	64.6	64.6	64.4	65.0
85°	50.5	46.8	42.5	39.9	38.3	35.6	35.6	34.6	33.5	32.4	33.0
87.5°	23.1	22.4	19.9	18.4	17.5	14.9	14.9	13.4	12.9	12.0	11.2
90°	13.3	14.1	12.5	10.9	10.9	6.3	6.3	5.5	4.7	2.3	0.8
92.5°	206.6	248.0	217.1	157.9	97.3	57.5	41.3	29.9	20.3	13.0	8.9
95°	655.3	637.3	480.9	294.0	165.8	97.7	64.9	46.1	36.0	28.1	25.8
97.5°	823.2	671.2	450.1	264.3	158.4	106.0	78.5	62.4	53.0	46.3	46.3
100°	828.8	628.7	408.2	248.7	160.3	114.2	89.1	74.3	64.9	59.4	59.4
102.5°	781.9	575.5	380.0	244.3	166.5	124.8	101.0	86.8	78.0	73.2	71.9
105°	696.7	512.9	355.8	246.3	181.4	143.9	121.2	107.1	97.7	93.8	91.5
107.5°	627.9	477.9	351.4	257.9	198.8	164.4	142.0	128.5	118.5	114.6	113.1
110°	593.5	466.0	352.6	266.6	211.9	177.5	156.4	142.3	132.9	129.0	127.5



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	574.1	460.4	356.4	276.0	224.4	191.3	170.1	156.1	147.3	142.8	141.2
115°	555.9	457.4	363.6	290.9	244.0	212.7	191.6	176.7	168.9	163.4	161.1
117.5°	547.8	456.6	371.3	306.0	262.9	233.2	211.3	197.4	188.8	183.9	181.7
120°	543.4	456.6	376.9	316.7	276.0	246.3	224.4	211.1	202.5	197.0	195.5
122.5°	538.4	456.0	382.5	326.7	288.5	258.8	237.5	223.0	215.0	209.6	208.0
125°	530.1	455.1	391.0	341.7	305.7	277.6	255.7	240.8	232.2	227.5	224.4
127.5°	519.0	453.4	397.7	354.7	321.7	294.5	272.4	256.9	247.1	241.5	239.0
130°	512.2	452.7	402.7	362.8	332.3	305.7	283.1	268.2	256.5	250.2	247.1
132.5°	505.9	452.1	407.1	370.9	341.1	314.5	293.1	277.0	265.9	257.7	255.2
135°	496.5	451.2	413.6	381.6	353.4	327.6	307.3	290.9	277.6	269.8	266.6
137.5°	488.4	451.0	417.5	389.1	362.8	338.7	319.3	302.3	289.6	281.0	278.1
140°	484.0	450.4	420.7	394.1	369.1	345.6	326.8	310.4	297.1	288.5	286.2
142.5°	480.3	450.4	423.2	397.8	374.7	351.9	333.7	317.9	305.3	297.3	294.9
145°	473.8	448.8	424.6	401.9	380.8	360.5	343.3	328.4	317.5	309.6	307.3
147.5°	468.1	446.0	425.4	405.5	387.1	368.0	352.5	340.1	328.9	322.0	321.2
150°	463.7	444.1	425.4	407.4	390.2	373.0	358.1	346.4	337.0	330.8	330.0
152.5°	458.7	441.0	424.1	408.6	392.7	377.4	363.8	353.3	344.5	338.3	338.1
155°	451.2	436.3	422.2	409.7	396.4	383.1	371.4	362.8	355.0	350.3	349.5
157.5°	443.5	431.5	420.2	409.7	399.1	387.8	378.6	371.1	365.0	360.6	360.6
160°	437.9	427.7	418.3	409.7	400.3	391.0	382.4	376.1	370.6	367.5	367.5
162.5°	432.9	424.0	416.5	409.7	401.6	392.8	386.1	380.5	375.6	373.1	373.8
165°	424.6	418.3	412.9	408.2	401.9	394.9	390.2	386.3	382.4	380.8	380.8
167.5°	417.1	412.7	409.1	406.3	401.8	396.6	393.0	390.8	387.8	387.1	387.8
170°	412.1	408.9	406.6	405.0	401.1	397.2	394.9	393.3	391.0	390.2	391.0
172.5°	407.7	405.2	404.1	403.8	400.5	397.8	396.1	395.2	393.5	393.3	394.1
175°	402.7	401.1	401.1	401.9	399.6	398.0	398.0	397.2	396.4	396.4	397.2
177.5°	399.2	398.6	398.6	399.9	398.6	398.0	398.0	398.0	397.4	398.0	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1292.4	1296.6	1302.2	1311.5	1314.9	1319.2	1325.1	1324.7	1326.4	1332.8	1346.4
5°	1297.2	1313.6	1329.6	1348.7	1369.0	1382.2	1400.3	1411.5	1422.7	1437.0	1461.5
7.5°	1299.1	1325.2	1354.5	1388.1	1418.0	1452.5	1479.4	1504.7	1527.5	1557.9	1587.0
10°	1296.1	1331.2	1369.0	1411.5	1456.7	1495.0	1529.6	1568.9	1602.4	1639.1	1672.1
12.5°	1290.6	1332.9	1383.4	1431.1	1483.9	1540.5	1583.6	1623.4	1668.0	1710.2	1761.0
15°	1278.0	1336.0	1395.0	1457.8	1528.5	1593.9	1656.1	1707.7	1755.6	1818.9	1885.4
17.5°	1262.1	1324.6	1399.1	1475.0	1548.9	1623.7	1700.7	1778.3	1838.7	1917.3	1969.3
20°	1247.2	1319.5	1396.1	1486.5	1560.4	1653.5	1730.1	1805.1	1888.0	1966.2	2028.4
22.5°	1226.3	1305.5	1386.7	1476.7	1574.0	1667.1	1755.6	1837.0	1919.9	2004.9	2080.3
25°	1199.8	1271.6	1367.9	1470.0	1566.8	1667.8	1769.4	1871.5	1960.9	2050.8	2121.0
27.5°	1154.7	1245.4	1335.0	1440.4	1548.0	1662.3	1770.9	1877.8	1971.4	2045.3	2088.8
30°	1131.8	1210.5	1307.8	1413.6	1530.1	1653.0	1766.2	1871.0	1958.2	2017.3	2034.8
32.5°	1097.7	1179.0	1274.2	1383.8	1507.1	1633.4	1751.3	1850.2	1922.9	1953.9	1932.7
35°	1047.2	1120.6	1216.8	1329.1	1457.2	1591.8	1708.3	1791.8	1829.0	1799.7	1726.9
37.5°	986.6	1059.3	1156.0	1266.2	1398.8	1535.6	1640.9	1701.0	1688.7	1615.9	1507.3
40°	944.0	1012.1	1104.1	1223.2	1352.5	1489.7	1582.2	1614.7	1580.6	1476.4	1361.0
42.5°	896.8	963.2	1055.6	1170.5	1307.4	1433.9	1514.6	1517.2	1460.2	1335.6	1219.7
45°	824.9	888.2	975.4	1095.1	1221.6	1340.8	1393.9	1367.9	1262.6	1142.4	1025.9
47.5°	753.9	808.8	894.8	1008.4	1128.6	1228.9	1255.2	1208.3	1096.1	979.4	871.5
50°	702.0	757.3	838.2	946.7	1062.6	1149.3	1162.1	1099.8	989.8	872.2	787.7
52.5°	652.2	707.1	785.0	885.4	991.6	1069.7	1070.2	998.2	888.5	783.7	705.1
55°	579.2	628.6	698.8	788.7	883.4	944.5	929.7	855.2	760.0	669.1	600.4
57.5°	508.8	551.8	616.5	691.5	774.9	825.3	800.6	728.9	643.9	566.8	514.8
60°	463.2	504.2	559.5	630.2	700.4	739.8	716.4	651.5	573.3	511.1	465.9
62.5°	419.0	453.6	506.7	568.1	633.2	662.4	641.5	577.5	509.9	453.7	417.0
65°	356.3	384.5	427.1	479.7	527.1	552.0	534.5	474.9	423.3	382.9	353.7
67.5°	297.8	319.8	352.1	394.3	434.5	448.0	432.1	390.6	346.9	314.5	293.9
70°	257.4	278.2	305.3	337.7	372.8	387.2	371.2	338.2	302.6	272.8	252.6
72.5°	222.1	238.2	261.0	288.8	316.2	330.6	319.7	288.0	257.9	235.8	218.6
75°	169.1	183.0	198.9	218.6	239.9	249.4	239.9	218.1	197.3	180.8	168.6
77.5°	123.0	130.4	142.7	157.4	170.7	178.1	169.8	155.0	142.3	131.0	125.0
80°	93.6	98.9	107.4	119.1	128.2	135.1	129.8	117.5	107.4	100.0	97.3
82.5°	68.1	71.7	77.2	85.9	92.0	95.5	93.2	84.3	80.2	73.6	70.9
85°	33.5	35.6	39.4	42.0	47.3	47.9	48.4	44.7	41.0	39.4	37.2
87.5°	12.0	12.9	14.3	15.7	17.4	18.8	18.4	18.7	17.3	16.7	15.2
90°	2.3	4.7	5.5	6.3	6.3	10.9	10.9	12.5	14.1	13.3	14.1
92.5°	13.0	20.3	29.9	41.3	57.5	97.3	157.9	217.1	248.0	206.6	153.6
95°	28.1	36.0	46.1	64.9	97.7	165.8	294.0	480.9	637.3	655.3	579.4
97.5°	46.3	53.0	62.4	78.5	106.0	158.4	264.3	450.1	671.2	823.2	856.0
100°	59.4	64.9	74.3	89.1	114.2	160.3	248.7	408.2	628.7	828.8	943.0
102.5°	73.2	78.0	86.8	101.0	124.8	166.5	244.3	380.0	575.5	781.9	938.6
105°	93.8	97.7	107.1	121.2	143.9	181.4	246.3	355.8	512.9	696.7	875.8
107.5°	114.6	118.5	128.5	142.0	164.4	198.8	257.9	351.4	477.9	627.9	786.5
110°	129.0	132.9	142.3	156.4	177.5	211.9	266.6	352.6	466.0	593.5	732.7





TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	142.8	147.3	156.1	170.1	191.3	224.4	276.0	356.4	460.4	574.1	693.3
115°	163.4	168.9	176.7	191.6	212.7	244.0	290.9	363.6	457.4	555.9	653.7
117.5°	183.9	188.8	197.4	211.3	233.2	262.9	306.0	371.3	456.6	547.8	634.3
120°	197.0	202.5	211.1	224.4	246.3	276.0	316.7	376.9	456.6	543.4	625.5
122.5°	209.6	215.0	223.0	237.5	258.8	288.5	326.7	382.5	456.0	538.4	618.0
125°	227.5	232.2	240.8	255.7	277.6	305.7	341.7	391.0	455.1	530.1	605.2
127.5°	241.5	247.1	256.9	272.4	294.5	321.7	354.7	397.7	453.4	519.0	589.6
130°	250.2	256.5	268.2	283.1	305.7	332.3	362.8	402.7	452.7	512.2	577.1
132.5°	257.7	265.9	277.0	293.1	314.5	341.1	370.9	407.1	452.1	505.9	563.9
135°	269.8	277.6	290.9	307.3	327.6	353.4	381.6	413.6	451.2	496.5	545.8
137.5°	281.0	289.6	302.3	319.3	338.7	362.8	389.1	417.5	451.0	488.4	529.4
140°	288.5	297.1	310.4	326.8	345.6	369.1	394.1	420.7	450.4	484.0	520.0
142.5°	297.3	305.3	317.9	333.7	351.9	374.7	397.8	423.2	450.4	480.3	511.2
145°	309.6	317.5	328.4	343.3	360.5	380.8	401.9	424.6	448.8	473.8	498.9
147.5°	322.0	328.9	340.1	352.5	368.0	387.1	405.5	425.4	446.0	468.1	488.7
150°	330.8	337.0	346.4	358.1	373.0	390.2	407.4	425.4	444.1	463.7	482.4
152.5°	338.3	344.5	353.3	363.8	377.4	392.7	408.6	424.1	441.0	458.7	475.6
155°	350.3	355.0	362.8	371.4	383.1	396.4	409.7	422.2	436.3	451.2	465.2
157.5°	360.6	365.0	371.1	378.6	387.8	399.1	409.7	420.2	431.5	443.5	454.1
160°	367.5	370.6	376.1	382.4	391.0	400.3	409.7	418.3	427.7	437.9	447.3
162.5°	373.1	375.6	380.5	386.1	392.8	401.6	409.7	416.5	424.0	432.9	440.4
165°	380.8	382.4	386.3	390.2	394.9	401.9	408.2	412.9	418.3	424.6	430.8
167.5°	387.1	387.8	390.8	393.0	396.6	401.8	406.3	409.1	412.7	417.1	421.6
170°	390.2	391.0	393.3	394.9	397.2	401.1	405.0	406.6	408.9	412.1	416.0
172.5°	393.3	393.5	395.2	396.1	397.8	400.5	403.8	404.1	405.2	407.7	411.0
175°	396.4	396.4	397.2	398.0	398.0	399.6	401.9	401.1	401.1	402.7	404.3
177.5°	398.0	397.4	398.0	398.0	398.0	398.6	399.9	398.6	398.6	399.2	399.9
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1353.2	1354.1	1357.9	1360.9	1361.7	1366.0	1366.4
5°	1472.1	1481.2	1498.7	1500.3	1503.0	1516.8	1506.2
7.5°	1611.5	1634.4	1649.8	1663.3	1668.2	1674.2	1673.0
10°	1700.8	1734.9	1751.9	1779.0	1780.1	1787.0	1782.7
12.5°	1790.6	1830.2	1861.2	1866.2	1889.0	1892.5	1898.5
15°	1917.8	1959.8	2002.9	2018.3	2049.7	2057.2	2068.9
17.5°	2037.4	2080.3	2110.5	2150.4	2163.3	2180.5	2168.8
20°	2102.9	2149.7	2188.0	2219.4	2232.7	2242.2	2241.2
22.5°	2142.5	2189.7	2220.7	2244.5	2256.9	2261.0	2260.7
25°	2167.2	2194.4	2203.9	2213.0	2199.2	2194.4	2196.5
27.5°	2098.3	2091.3	2066.3	2033.5	1999.5	1972.5	1957.8
30°	2003.4	1962.0	1924.2	1858.2	1824.2	1804.0	1785.9
32.5°	1869.0	1803.3	1730.6	1670.2	1631.5	1601.5	1597.0
35°	1638.6	1539.7	1450.9	1376.9	1338.6	1306.2	1298.7
37.5°	1393.1	1290.3	1210.4	1145.3	1104.1	1081.2	1059.8
40°	1230.1	1141.9	1063.1	1007.8	976.5	960.0	946.7
42.5°	1104.6	1024.0	945.7	903.6	875.2	865.1	857.3
45°	931.2	856.3	802.0	770.1	753.6	736.6	728.6
47.5°	792.4	731.4	695.6	668.5	650.9	640.8	635.7
50°	713.7	663.7	631.8	611.1	595.1	587.1	582.9
52.5°	643.9	602.9	576.1	559.6	548.8	542.9	541.2
55°	554.7	523.3	506.3	492.0	484.0	478.7	476.5
57.5°	482.2	458.0	444.2	432.4	429.3	424.8	423.3
60°	434.5	415.9	404.2	396.2	393.6	388.2	389.3
62.5°	392.4	377.2	367.2	362.6	359.1	354.6	356.1
65°	331.9	320.7	315.4	311.1	306.9	304.2	306.3
67.5°	278.5	270.8	263.6	261.1	259.0	258.6	256.3
70°	243.6	237.2	230.8	229.2	229.2	227.1	226.6
72.5°	210.0	205.3	201.0	199.9	198.2	199.0	196.8
75°	162.2	158.5	156.9	155.3	154.8	154.8	153.2
77.5°	119.9	117.1	114.6	114.6	112.6	111.9	111.7
80°	90.9	89.9	87.8	87.8	86.7	87.2	86.2
82.5°	68.4	66.9	66.5	65.6	64.1	64.2	63.2
85°	36.7	35.1	34.6	33.0	31.9	33.0	31.9
87.5°	15.7	15.5	15.0	14.3	14.1	13.9	12.6
90°	14.9	15.6	15.6	16.4	17.2	16.4	16.4
92.5°	115.6	92.0	76.3	67.1	62.9	60.2	60.2
95°	458.2	353.4	277.6	239.3	215.0	201.0	190.8
97.5°	811.0	734.5	652.9	596.8	549.7	526.2	510.0
100°	958.6	920.3	862.5	794.4	746.7	723.3	717.0
102.5°	1016.2	1027.3	1003.2	961.5	926.9	902.2	897.2
105°	1011.0	1088.4	1120.5	1122.1	1115.8	1104.9	1100.2
107.5°	930.5	1039.5	1109.2	1147.9	1165.7	1173.5	1175.5
110°	867.9	981.3	1067.3	1122.8	1155.7	1169.8	1176.8



TEST NUMBER: P332600

CATALOG NUMBER: S124DIP-S795D810U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	812.9	920.0	1006.0	1069.0	1108.8	1128.5	1139.9
115°	749.9	841.3	916.4	978.2	1025.1	1050.1	1056.4
117.5°	713.9	785.8	849.5	902.2	941.6	966.9	971.8
120°	698.3	760.8	816.3	860.9	895.3	915.6	924.2
122.5°	688.2	745.2	793.8	831.5	860.9	878.1	886.7
125°	672.5	726.4	769.4	800.7	823.4	838.2	842.9
127.5°	653.8	707.6	748.5	779.9	800.1	812.6	817.3
130°	638.8	692.0	733.4	765.5	785.1	797.6	802.3
132.5°	621.9	673.9	715.3	746.7	768.8	780.7	785.4
135°	596.6	644.3	683.4	714.7	736.6	749.1	753.8
137.5°	572.4	612.6	647.9	677.1	698.7	709.0	714.7
140°	556.7	591.9	624.8	652.1	669.3	680.3	686.5
142.5°	543.6	573.8	602.2	626.5	642.4	652.1	656.5
145°	525.5	548.9	570.8	590.4	603.6	611.5	615.4
147.5°	509.8	528.6	545.8	560.2	571.6	577.5	578.9
150°	500.4	516.1	530.1	542.7	552.8	557.5	558.3
152.5°	491.0	505.4	517.0	527.6	535.9	538.7	539.5
155°	477.8	489.5	498.9	506.7	512.9	515.3	515.3
157.5°	464.6	474.5	482.0	487.9	492.6	494.0	494.0
160°	455.9	464.5	470.7	475.4	480.1	480.9	480.9
162.5°	447.7	454.5	460.1	463.5	468.2	469.0	468.4
165°	435.5	441.0	444.9	448.0	451.2	450.4	449.6
167.5°	425.2	429.6	431.9	433.5	435.5	435.4	434.7
170°	418.3	421.5	423.8	425.4	426.1	425.4	425.4
172.5°	412.7	414.6	416.3	417.2	418.0	417.2	416.0
175°	405.0	406.6	406.6	406.6	408.2	406.6	405.0
177.5°	400.5	400.5	401.1	400.5	401.1	399.9	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0

(END OF REPORT)