

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832459

Luminaire Tested: S123RDP-S340D835-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-2019  
 Report Number: P832459  
 Test Lab: INNOVATION CENTER  
 Issue Date: 05/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: NEO-RAY  
 Catalog Number: S123RDP-S340D835-4F0-1E-UDD-G  
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE  
 DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -  
 Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 1472.9 lumens  
 Efficiency: N/A  
 Efficacy: 118.8 lumens/watt  
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
 CIE Type: Direct


Input Watts (W): 12.4  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832459

CATALOG NUMBER: S123RDP-S340D835-4F0-1E-UDD-G

### Luminous Intensity Polar Plot



TEST NUMBER: P832459

CATALOG NUMBER: S123RDP-S340D835-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59				
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53				
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47				
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43				
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39				
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	11958	11958	11958	11958	11958
5°	14199	13746	12034	9728	9031
10°	12865	13962	11973	7794	6686
15°	8857	11972	11847	6370	5289
20°	6161	9216	11609	5371	4648
25°	4696	7024	11263	4774	4284
30°	4088	5615	10829	4432	3969
35°	3753	4737	10217	4144	3681
40°	3424	4231	9414	3863	3417
45°	3092	3870	8549	3596	3154
50°	2807	3570	7529	3332	2830
55°	2539	3278	6548	3078	2428
60°	2275	2982	5688	2794	2295
65°	2099	2646	4895	2511	2170
70°	1706	2285	4271	2272	1762
75°	1497	1817	3618	1884	1551
80°	1358	1537	2963	1581	1469
85°	1235	1346	2248	1433	1346

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 9021 cd/sqm

TEST NUMBER: P832459  
 CATALOG NUMBER: S123RDP-S340D835-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.3	6.9
10°-20°	234.3	15.9
20°-30°	268.8	18.3
30°-40°	265.0	18.0
40°-50°	233.7	15.9
50°-60°	179.8	12.2
60°-70°	118.2	8.0
70°-80°	57.4	3.9
80°-90°	14.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	604.4	41.0
0°-40°	869.4	59.0
0°-60°	1282.9	87.1
0°-90°	1472.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1472.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1111	1111	1111	1111	1111	
5°	1314	1272	1114	900	836	120
15°	795	1074	1063	572	475	224
25°	395	591	948	402	361	187
35°	286	360	778	315	280	178
45°	203	254	562	236	207	158
55°	135	175	349	164	129	121
65°	82	104	192	99	85	81
75°	36	44	87	45	37	39
85°	10	11	18	12	11	11
90°	0	0	0	0	0	

TEST NUMBER: P832459

CATALOG NUMBER: S123RDP-S340D835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9
2.5°	1231.2	1227.3	1223.4	1222.3	1221.2	1217.5	1213.9	1205.7	1197.5	1189.0	1180.6
5°	1314.1	1314.5	1315.0	1313.8	1312.7	1307.9	1303.1	1293.1	1283.1	1272.2	1261.2
7.5°	1288.6	1295.9	1303.1	1304.5	1305.9	1309.5	1313.2	1310.9	1308.6	1304.5	1300.4
10°	1177.0	1176.5	1176.1	1184.3	1192.5	1216.8	1241.2	1253.7	1266.2	1277.4	1288.6
12.5°	994.8	995.5	996.1	1023.0	1049.9	1072.9	1095.9	1127.8	1159.7	1194.1	1228.4
15°	794.8	806.0	817.1	841.1	865.0	899.6	934.2	977.0	1019.8	1074.3	1128.7
17.5°	652.7	657.5	662.3	685.3	708.3	741.1	773.9	822.4	870.9	941.0	1011.2
20°	537.9	542.3	546.6	563.2	579.8	611.3	642.7	688.9	735.2	804.6	874.1
22.5°	449.1	457.5	466.0	477.1	488.3	511.1	533.8	581.0	628.1	691.4	754.7
25°	395.4	399.2	403.1	412.7	422.2	444.1	466.0	497.2	528.4	591.4	654.5
27.5°	358.9	360.1	361.2	368.3	375.3	389.4	403.6	432.5	461.4	513.3	565.3
30°	328.9	330.9	333.0	338.4	343.9	354.1	364.4	384.9	405.4	451.8	498.3
32.5°	305.6	306.8	307.9	312.5	317.0	324.5	332.0	348.2	364.4	399.9	435.4
35°	285.6	285.8	286.0	289.5	292.9	300.2	307.5	320.9	334.3	360.5	386.7
37.5°	262.8	264.4	266.0	268.5	271.0	277.4	283.8	294.7	305.6	327.3	348.9
40°	243.7	245.1	246.4	249.4	252.3	257.3	262.4	272.4	282.4	301.1	319.8
42.5°	224.6	225.5	226.4	229.3	232.3	238.4	244.6	252.6	260.5	276.0	291.5
45°	203.1	205.4	207.7	210.9	214.1	219.3	224.6	232.8	241.0	254.2	267.4
47.5°	185.4	186.5	187.7	190.4	193.1	199.5	205.9	213.2	220.5	232.8	245.1
50°	167.6	168.1	168.5	171.0	173.5	179.2	184.9	193.4	201.8	213.2	224.6
52.5°	150.8	151.9	153.0	155.5	158.1	161.9	165.8	174.5	183.1	194.3	205.4
55°	135.3	136.0	136.6	138.5	140.3	144.8	149.4	156.9	164.4	174.7	184.9
57.5°	120.7	121.6	122.5	123.9	125.3	129.4	133.5	140.1	146.7	156.9	167.2
60°	105.7	106.8	107.9	109.5	111.1	114.3	117.5	123.4	129.4	138.5	147.6
62.5°	94.7	95.0	95.2	96.6	97.9	100.2	102.5	107.3	112.0	121.2	130.3
65°	82.4	83.1	83.8	84.5	85.2	87.0	88.8	92.9	97.0	103.9	110.7
67.5°	69.7	70.4	71.1	72.2	73.3	74.9	76.5	79.3	82.0	88.4	94.7
70°	54.2	54.2	54.2	56.0	57.8	60.6	63.3	65.4	67.4	72.6	77.9
72.5°	44.2	44.4	44.6	44.9	45.1	46.7	48.3	51.7	55.1	58.3	61.5
75°	36.0	36.2	36.4	36.7	36.9	37.3	37.8	38.9	40.1	43.7	47.4
77.5°	28.7	28.9	29.2	29.4	29.6	30.1	30.5	31.0	31.4	32.8	34.2
80°	21.9	22.1	22.3	22.5	22.8	23.0	23.2	23.7	24.1	24.8	25.5
82.5°	15.9	15.9	15.9	15.9	15.9	16.4	16.9	16.9	16.9	17.3	17.8
85°	10.0	10.0	10.0	10.2	10.5	10.5	10.5	10.7	10.9	10.9	10.9
87.5°	4.6	4.3	4.1	4.3	4.6	4.6	4.6	4.8	5.0	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832459

CATALOG NUMBER: S123RDP-S340D835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9
2.5°	1179.5	1178.3	1167.4	1156.5	1145.8	1135.1	1127.1	1119.1	1105.7	1092.3	1083.8
5°	1252.6	1243.9	1226.6	1209.3	1183.4	1157.4	1135.5	1113.7	1085.9	1058.1	1034.9
7.5°	1293.3	1286.3	1265.3	1244.4	1210.0	1175.6	1141.4	1107.3	1066.3	1025.3	990.2
10°	1294.5	1300.4	1283.1	1265.8	1227.1	1188.4	1141.9	1095.4	1040.3	985.2	939.9
12.5°	1254.0	1279.5	1275.8	1272.2	1232.8	1193.4	1136.9	1080.4	1012.8	945.1	888.4
15°	1178.1	1227.5	1242.1	1256.7	1224.1	1191.5	1127.3	1063.1	983.6	904.1	839.0
17.5°	1080.4	1149.6	1188.1	1226.6	1202.9	1179.3	1108.9	1038.5	949.0	859.5	788.7
20°	964.7	1055.4	1115.7	1176.1	1167.4	1158.8	1086.1	1013.5	916.9	820.3	743.6
22.5°	850.4	946.0	1029.4	1112.7	1121.6	1130.5	1057.2	983.8	878.2	772.5	694.4
25°	751.8	849.0	948.3	1047.6	1067.7	1087.7	1018.0	948.3	838.8	729.2	651.6
27.5°	657.7	750.2	859.5	968.8	1005.3	1041.7	977.9	914.2	800.1	686.0	608.5
30°	581.0	663.6	775.2	886.8	937.6	988.4	929.9	871.3	758.2	645.0	569.1
32.5°	509.5	583.5	695.5	807.6	866.6	925.5	875.0	824.4	715.6	606.7	531.8
35°	453.0	519.3	623.8	728.3	794.4	860.4	819.0	777.5	671.2	564.8	494.0
37.5°	404.5	460.0	558.2	656.4	726.5	796.6	762.0	727.4	627.4	527.5	460.5
40°	364.4	409.0	500.4	591.7	660.5	729.2	699.6	670.0	580.5	491.0	428.4
42.5°	330.0	368.5	450.5	532.5	595.5	658.6	639.0	619.5	538.4	457.3	399.2
45°	299.7	332.0	404.2	476.4	534.5	592.6	577.1	561.6	491.7	421.8	368.5
47.5°	272.8	300.6	365.1	429.5	481.7	533.8	519.5	505.1	447.3	389.4	340.9
50°	248.2	271.9	325.7	379.4	426.3	473.2	461.4	449.6	401.7	353.9	312.0
52.5°	225.0	244.6	292.9	341.2	379.0	416.8	407.7	398.5	361.7	324.8	286.7
55°	202.9	220.9	261.7	302.4	334.8	367.1	358.0	348.9	320.2	291.5	258.0
57.5°	182.9	198.6	231.6	264.6	290.4	316.1	311.8	307.5	283.5	259.6	232.1
60°	161.7	175.8	204.3	232.8	253.5	274.2	269.2	264.2	247.1	230.0	206.3
62.5°	142.8	155.3	178.1	200.9	217.7	234.6	230.9	227.3	214.3	201.3	181.7
65°	123.0	135.3	153.7	172.2	185.4	198.6	195.4	192.2	182.4	172.6	156.9
67.5°	105.0	115.2	131.2	147.1	156.0	164.9	163.1	161.2	153.7	146.2	133.9
70°	86.8	95.7	108.9	122.1	128.2	134.4	135.1	135.7	128.9	122.1	113.0
72.5°	68.6	75.6	87.9	100.2	105.0	109.8	109.5	109.3	105.2	101.1	92.9
75°	52.6	57.8	67.4	77.0	81.1	85.2	86.1	87.0	83.1	79.3	74.7
77.5°	37.8	41.4	48.7	56.0	60.6	65.1	65.6	66.0	64.2	62.4	58.1
80°	26.6	27.8	32.3	36.9	41.7	46.5	47.1	47.8	46.0	44.2	41.4
82.5°	18.4	19.1	20.7	22.3	26.2	30.1	31.0	31.9	31.0	30.1	27.1
85°	11.2	11.4	12.1	12.8	14.6	16.4	17.3	18.2	17.8	17.3	15.7
87.5°	5.0	5.0	5.2	5.5	5.9	6.4	7.5	8.7	8.0	7.3	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832459

CATALOG NUMBER: S123RDP-S340D835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9	1110.9
2.5°	1075.4	1062.4	1049.4	1040.1	1030.8	1019.1	1007.5	1007.1	1006.6	998.0	989.3
5°	1011.6	989.1	966.5	944.4	922.4	900.3	878.2	873.2	868.2	860.6	853.1
7.5°	955.2	919.2	883.2	854.9	826.7	804.6	782.5	767.5	752.5	740.8	729.2
10°	894.6	849.9	805.3	771.1	737.0	713.1	689.1	671.8	654.5	646.3	638.1
12.5°	831.7	783.2	734.7	701.2	667.7	639.0	610.3	594.6	578.9	567.5	556.1
15°	773.9	721.7	669.6	634.0	598.5	571.6	544.8	529.0	513.3	501.9	490.6
17.5°	717.8	665.2	612.6	576.6	540.7	516.3	491.9	476.7	461.4	454.3	447.3
20°	666.8	613.8	560.7	526.8	492.8	468.9	445.0	436.8	428.6	422.0	415.4
22.5°	616.3	565.3	514.2	481.7	449.1	431.8	414.5	407.9	401.3	396.3	391.3
25°	573.9	523.1	472.3	443.9	415.4	402.0	388.5	384.2	379.9	374.9	369.9
27.5°	531.1	482.8	434.5	411.8	389.0	378.1	367.1	361.7	356.2	352.1	348.0
30°	493.3	448.7	404.0	385.1	366.2	356.6	347.1	341.2	335.2	331.4	327.5
32.5°	456.9	417.2	377.6	361.4	345.3	335.9	326.6	320.9	315.2	310.6	306.1
35°	423.1	388.8	354.4	339.6	324.8	315.4	306.1	300.4	294.7	290.1	285.6
37.5°	393.5	362.3	331.1	317.2	303.4	295.2	287.0	281.0	275.1	270.3	265.5
40°	365.8	338.2	310.6	297.2	283.8	274.9	266.0	260.8	255.5	251.2	246.9
42.5°	341.2	315.9	290.6	277.4	264.2	255.8	247.3	241.2	235.0	232.5	230.0
45°	315.2	292.9	270.6	257.8	245.1	236.2	227.3	222.0	216.8	214.5	212.3
47.5°	292.4	271.7	251.0	238.4	225.9	217.9	210.0	205.9	201.8	198.6	195.4
50°	270.1	250.1	230.0	217.9	205.9	199.0	192.2	187.2	182.2	179.9	177.6
52.5°	248.7	230.5	212.3	200.0	187.7	181.1	174.5	170.1	165.8	161.0	156.2
55°	224.6	208.6	192.7	181.7	170.8	164.0	157.1	152.1	147.1	142.1	137.1
57.5°	204.5	188.8	173.1	163.3	153.5	146.9	140.3	134.8	129.4	125.3	121.2
60°	182.6	169.0	155.3	145.8	136.2	129.8	123.4	118.2	113.0	110.9	108.9
62.5°	162.2	149.4	136.6	128.2	119.8	113.6	107.5	104.1	100.7	99.3	97.9
65°	141.2	130.3	119.3	111.6	103.9	98.6	93.4	91.8	90.2	89.0	87.9
67.5°	121.6	112.3	102.9	96.1	89.3	85.6	82.0	80.2	78.3	77.0	75.6
70°	103.9	95.7	87.5	81.5	75.6	72.2	68.8	67.2	65.6	63.1	60.6
72.5°	84.7	78.3	72.0	67.4	62.9	59.9	56.9	53.7	50.6	48.3	46.0
75°	70.1	63.8	57.4	53.1	48.7	45.3	41.9	40.8	39.6	38.9	38.3
77.5°	53.7	48.3	42.8	39.4	36.0	34.4	32.8	32.1	31.4	31.2	31.0
80°	38.7	34.2	29.6	27.8	26.0	25.5	25.1	24.6	24.1	23.9	23.7
82.5°	24.1	21.9	19.6	19.1	18.7	18.4	18.2	18.0	17.8	17.5	17.3
85°	14.1	13.2	12.3	12.1	11.8	11.6	11.4	11.4	11.4	11.4	11.4
87.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.7	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P832459

CATALOG NUMBER: S123RDP-S340D835-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1110.9	1110.9	1110.9	1110.9
2.5°	987.0	984.8	983.8	982.9
5°	846.1	839.0	837.4	835.8
7.5°	726.3	723.3	713.5	703.7
10°	629.0	619.9	615.8	611.7
12.5°	547.7	539.3	537.9	536.6
15°	484.6	478.7	476.7	474.6
17.5°	443.2	439.1	436.6	434.1
20°	412.4	409.5	407.7	405.8
22.5°	389.0	386.7	385.3	384.0
25°	366.4	363.0	361.9	360.7
27.5°	345.0	342.1	340.9	339.8
30°	325.0	322.5	320.9	319.3
32.5°	303.1	300.2	299.3	298.3
35°	283.8	281.9	281.0	280.1
37.5°	263.3	261.0	259.6	258.3
40°	245.7	244.6	243.9	243.2
42.5°	228.0	225.9	225.7	225.5
45°	210.2	208.2	207.7	207.2
47.5°	193.6	191.8	191.5	191.3
50°	175.1	172.6	170.8	169.0
52.5°	154.0	151.7	150.1	148.5
55°	134.6	132.1	130.7	129.4
57.5°	120.0	118.9	118.2	117.5
60°	108.2	107.5	107.0	106.6
62.5°	97.2	96.6	96.6	96.6
65°	87.2	86.5	85.9	85.2
67.5°	74.2	72.9	72.6	72.4
70°	58.5	56.5	56.3	56.0
72.5°	45.8	45.5	45.1	44.6
75°	37.8	37.3	37.3	37.3
77.5°	30.5	30.1	30.1	30.1
80°	23.5	23.2	23.5	23.7
82.5°	17.3	17.3	17.1	16.9
85°	11.2	10.9	10.9	10.9
87.5°	5.5	5.5	5.5	5.5
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832459

CATALOG NUMBER: S123RDP-S340D835-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.33	14.78	13.69	15.09	15.41	17.99	19.45	18.36	19.76	20.07
	3H	14.59	15.89	14.97	16.22	16.58	19.53	20.83	19.91	21.16	21.53
	4H	15.00	16.22	15.40	16.57	16.95	20.05	21.27	20.45	21.62	22.00
	6H	15.31	16.43	15.72	16.80	17.19	20.39	21.51	20.80	21.88	22.27
	8H	15.41	16.48	15.84	16.87	17.27	20.48	21.55	20.91	21.94	22.35
	12H	15.48	16.51	15.91	16.89	17.32	20.53	21.56	20.96	21.94	22.37
4H	2H	14.12	15.34	14.52	15.69	16.07	18.05	19.27	18.46	19.62	20.00
	3H	15.54	16.55	15.95	16.95	17.35	19.76	20.77	20.17	21.17	21.58
	4H	16.02	16.92	16.45	17.34	17.78	20.39	21.30	20.82	21.72	22.16
	6H	16.41	17.20	16.87	17.64	18.11	20.86	21.65	21.32	22.09	22.55
	8H	16.55	17.28	17.01	17.73	18.20	21.00	21.74	21.47	22.18	22.65
	12H	16.65	17.31	17.13	17.79	18.26	21.09	21.74	21.57	22.22	22.70
8H	4H	16.37	17.11	16.84	17.55	18.02	20.40	21.13	20.86	21.58	22.05
	6H	16.85	17.46	17.35	17.95	18.43	20.92	21.52	21.41	22.01	22.49
	8H	17.05	17.59	17.56	18.10	18.59	21.10	21.64	21.62	22.16	22.64
	12H	17.21	17.69	17.72	18.18	18.75	21.24	21.72	21.76	22.22	22.78
12H	4H	16.41	17.06	16.89	17.54	18.01	20.38	21.03	20.86	21.51	21.98
	6H	16.91	17.45	17.43	17.97	18.46	20.89	21.43	21.41	21.94	22.43
	8H	17.16	17.64	17.67	18.13	18.70	21.11	21.59	21.62	22.08	22.65