

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832473

Luminaire Tested: S123RDP-S560D935-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832473
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S560D935-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 2084.9 lumens
 Efficiency: N/A
 Efficacy: 106.4 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct


Input Watts (W): 19.6
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832473

CATALOG NUMBER: S123RDP-S560D935-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832473

CATALOG NUMBER: S123RDP-S560D935-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			87	
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76			76	
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			67	
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59			59	
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53			53	
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47			47	
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43			43	
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39			39	
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36	
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33			33	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	16926	16926	16926	16926	16926
5°	20097	19457	17033	13769	12783
10°	18209	19762	16948	11032	9464
15°	12538	16945	16769	9016	7486
20°	8722	13046	16432	7602	6581
25°	6646	9943	15942	6758	6064
30°	5786	7950	15330	6274	5618
35°	5311	6706	14462	5867	5210
40°	4846	5989	13326	5467	4838
45°	4376	5477	12102	5089	4466
50°	3974	5052	10655	4717	4006
55°	3594	4641	9269	4356	3436
60°	3221	4219	8049	3955	3249
65°	2972	3744	6930	3556	3072
70°	2414	3235	6046	3216	2496
75°	2117	2574	5120	2670	2200
80°	1915	2176	4197	2238	2077
85°	1754	1914	3186	2025	1914

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 12769 cd/sqm

TEST NUMBER: P832473

CATALOG NUMBER: S123RDP-S560D935-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.3	6.9
10°-20°	331.7	15.9
20°-30°	380.5	18.3
30°-40°	375.1	18.0
40°-50°	330.8	15.9
50°-60°	254.5	12.2
60°-70°	167.3	8.0
70°-80°	81.3	3.9
80°-90°	20.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	855.5	41.0
0°-40°	1230.6	59.0
0°-60°	1815.9	87.1
0°-90°	2084.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2084.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1572	1572	1572	1572	1572	
5°	1860	1801	1576	1274	1183	170
15°	1125	1521	1505	809	672	318
25°	560	837	1342	569	511	264
35°	404	510	1101	446	396	252
45°	288	360	795	334	293	223
55°	192	247	494	232	183	172
65°	117	147	272	140	121	114
75°	51	62	123	64	53	55
85°	14	16	26	16	16	16
90°	0	0	0	0	0	

TEST NUMBER: P832473

CATALOG NUMBER: S123RDP-S560D935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5
2.5°	1742.7	1737.2	1731.7	1730.1	1728.5	1723.4	1718.2	1706.6	1695.0	1683.1	1671.1
5°	1860.0	1860.7	1861.3	1859.7	1858.1	1851.3	1844.6	1830.4	1816.2	1800.7	1785.3
7.5°	1823.9	1834.3	1844.6	1846.5	1848.4	1853.6	1858.8	1855.5	1852.3	1846.5	1840.7
10°	1666.0	1665.3	1664.7	1676.3	1687.9	1722.4	1756.9	1774.6	1792.3	1808.1	1823.9
12.5°	1408.1	1409.1	1410.0	1448.1	1486.1	1518.7	1551.2	1596.4	1641.5	1690.2	1738.8
15°	1125.1	1140.9	1156.6	1190.5	1224.3	1273.3	1322.3	1382.9	1443.6	1520.6	1597.6
17.5°	923.9	930.7	937.4	970.0	1002.6	1049.0	1095.4	1164.1	1232.7	1332.0	1431.3
20°	761.4	767.6	773.7	797.2	820.7	865.2	909.7	975.2	1040.6	1138.9	1237.2
22.5°	635.7	647.6	659.6	675.4	691.2	723.4	755.6	822.4	889.1	978.7	1068.3
25°	559.6	565.1	570.6	584.1	597.7	628.6	659.6	703.7	747.9	837.2	926.5
27.5°	508.0	509.7	511.3	521.3	531.3	551.2	571.2	612.2	653.1	726.6	800.1
30°	465.5	468.4	471.3	479.0	486.8	501.3	515.8	544.8	573.8	639.6	705.3
32.5°	432.6	434.2	435.8	442.3	448.7	459.4	470.0	492.9	515.8	566.1	616.4
35°	404.2	404.6	404.9	409.7	414.6	424.9	435.2	454.2	473.2	510.3	547.4
37.5°	372.0	374.3	376.5	380.1	383.6	392.6	401.7	417.1	432.6	463.2	493.9
40°	344.9	346.9	348.8	353.0	357.2	364.3	371.4	385.5	399.7	426.2	452.6
42.5°	317.9	319.1	320.4	324.6	328.8	337.5	346.2	357.5	368.8	390.7	412.6
45°	287.5	290.8	294.0	298.5	303.0	310.4	317.9	329.5	341.1	359.8	378.5
47.5°	262.4	264.0	265.6	269.5	273.4	282.4	291.4	301.7	312.0	329.5	346.9
50°	237.3	237.9	238.6	242.1	245.6	253.7	261.8	273.7	285.6	301.7	317.9
52.5°	213.4	215.0	216.6	220.2	223.7	229.2	234.7	246.9	259.2	275.0	290.8
55°	191.5	192.5	193.4	196.0	198.6	205.0	211.5	222.1	232.7	247.3	261.8
57.5°	170.9	172.1	173.4	175.4	177.3	183.1	188.9	198.3	207.6	222.1	236.6
60°	149.6	151.2	152.8	155.1	157.3	161.8	166.3	174.7	183.1	196.0	208.9
62.5°	134.1	134.4	134.7	136.7	138.6	141.8	145.1	151.8	158.6	171.5	184.4
65°	116.7	117.7	118.6	119.6	120.6	123.1	125.7	131.5	137.3	147.0	156.7
67.5°	98.6	99.6	100.6	102.2	103.8	106.1	108.3	112.2	116.1	125.1	134.1
70°	76.7	76.7	76.7	79.3	81.9	85.7	89.6	92.5	95.4	102.8	110.2
72.5°	62.5	62.9	63.2	63.5	63.8	66.1	68.3	73.2	78.0	82.5	87.0
75°	50.9	51.3	51.6	51.9	52.2	52.9	53.5	55.1	56.7	61.9	67.1
77.5°	40.6	40.9	41.3	41.6	41.9	42.6	43.2	43.8	44.5	46.4	48.4
80°	30.9	31.3	31.6	31.9	32.2	32.6	32.9	33.5	34.2	35.1	36.1
82.5°	22.6	22.6	22.6	22.6	22.6	23.2	23.9	23.9	23.9	24.5	25.1
85°	14.2	14.2	14.2	14.5	14.8	14.8	14.8	15.2	15.5	15.5	15.5
87.5°	6.4	6.1	5.8	6.1	6.4	6.4	6.4	6.8	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832473

CATALOG NUMBER: S123RDP-S560D935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5
2.5°	1669.5	1667.9	1652.4	1637.0	1621.8	1606.7	1595.4	1584.1	1565.1	1546.1	1534.1
5°	1773.0	1760.8	1736.3	1711.8	1675.0	1638.3	1607.3	1576.4	1537.0	1497.7	1464.8
7.5°	1830.7	1820.7	1791.1	1761.4	1712.7	1664.0	1615.7	1567.3	1509.3	1451.3	1401.6
10°	1832.3	1840.7	1816.2	1791.7	1736.9	1682.1	1616.3	1550.6	1472.6	1394.6	1330.4
12.5°	1774.9	1811.0	1805.9	1800.7	1745.0	1689.2	1609.2	1529.3	1433.6	1337.8	1257.5
15°	1667.6	1737.5	1758.2	1778.8	1732.7	1686.6	1595.7	1504.8	1392.3	1279.8	1187.6
17.5°	1529.3	1627.3	1681.8	1736.3	1702.7	1669.2	1569.6	1470.0	1343.3	1216.6	1116.4
20°	1365.5	1493.8	1579.3	1664.7	1652.4	1640.2	1537.4	1434.5	1297.8	1161.2	1052.5
22.5°	1203.7	1339.1	1457.1	1575.1	1587.6	1600.2	1496.4	1392.6	1243.0	1093.5	982.9
25°	1064.1	1201.8	1342.3	1482.9	1511.2	1539.6	1441.0	1342.3	1187.3	1032.2	922.3
27.5°	931.0	1061.9	1216.6	1371.3	1422.9	1474.5	1384.2	1294.0	1132.5	971.0	861.4
30°	822.4	939.4	1097.3	1255.3	1327.2	1399.1	1316.2	1233.4	1073.2	912.9	805.6
32.5°	721.1	825.9	984.5	1143.1	1226.6	1310.1	1238.5	1167.0	1012.9	858.8	752.7
35°	641.2	735.0	883.0	1030.9	1124.4	1217.9	1159.2	1100.6	950.0	799.5	699.2
37.5°	572.5	651.2	790.1	929.1	1028.3	1127.6	1078.6	1029.6	888.1	746.6	651.8
40°	515.8	579.0	708.2	837.5	934.9	1032.2	990.3	948.4	821.7	695.0	606.4
42.5°	467.1	521.6	637.6	753.7	843.0	932.3	904.6	876.8	762.1	647.3	565.1
45°	424.2	470.0	572.2	674.4	756.6	838.8	816.9	795.0	696.0	597.0	521.6
47.5°	386.2	425.5	516.8	608.0	681.8	755.6	735.3	715.0	633.1	551.2	482.6
50°	351.4	384.9	461.0	537.1	603.5	669.9	653.1	636.3	568.7	501.0	441.6
52.5°	318.5	346.2	414.6	482.9	536.4	589.9	577.0	564.1	511.9	459.7	405.9
55°	287.2	312.7	370.4	428.1	473.9	519.7	506.8	493.9	453.2	412.6	365.2
57.5°	258.9	281.1	327.8	374.6	411.0	447.4	441.3	435.2	401.3	367.5	328.5
60°	228.9	248.9	289.2	329.5	358.8	388.1	381.0	373.9	349.8	325.6	292.1
62.5°	202.1	219.9	252.1	284.3	308.2	332.0	326.9	321.7	303.3	285.0	257.2
65°	174.1	191.5	217.6	243.7	262.4	281.1	276.6	272.1	258.2	244.4	222.1
67.5°	148.6	163.1	185.7	208.2	220.8	233.4	230.8	228.2	217.6	207.0	189.6
70°	122.8	135.4	154.1	172.8	181.5	190.2	191.2	192.1	182.5	172.8	159.9
72.5°	97.0	107.0	124.4	141.8	148.6	155.4	155.1	154.7	148.9	143.1	131.5
75°	74.5	81.9	95.4	109.0	114.8	120.6	121.9	123.1	117.7	112.2	105.7
77.5°	53.5	58.7	69.0	79.3	85.7	92.2	92.8	93.5	90.9	88.3	82.2
80°	37.7	39.3	45.8	52.2	59.0	65.8	66.7	67.7	65.1	62.5	58.7
82.5°	26.1	27.1	29.3	31.6	37.1	42.6	43.8	45.1	43.8	42.6	38.4
85°	15.8	16.1	17.1	18.1	20.6	23.2	24.5	25.8	25.1	24.5	22.2
87.5°	7.1	7.1	7.4	7.7	8.4	9.0	10.6	12.2	11.3	10.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832473

CATALOG NUMBER: S123RDP-S560D935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5	1572.5
2.5°	1522.2	1503.8	1485.5	1472.2	1459.0	1442.6	1426.1	1425.5	1424.9	1412.6	1400.4
5°	1431.9	1400.0	1368.1	1336.8	1305.6	1274.3	1243.0	1235.9	1228.9	1218.2	1207.6
7.5°	1352.0	1301.1	1250.1	1210.2	1170.2	1138.9	1107.6	1086.4	1065.1	1048.7	1032.2
10°	1266.3	1203.1	1139.9	1091.5	1043.2	1009.3	975.5	951.0	926.5	914.9	903.3
12.5°	1177.3	1108.6	1039.9	992.6	945.2	904.6	863.9	841.7	819.5	803.3	787.2
15°	1095.4	1021.6	947.8	897.5	847.2	809.1	771.1	748.9	726.6	710.5	694.4
17.5°	1016.1	941.6	867.2	816.2	765.3	730.8	696.3	674.7	653.1	643.1	633.1
20°	943.9	868.8	793.7	745.6	697.6	663.7	629.9	618.3	606.7	597.3	588.0
22.5°	872.3	800.1	727.9	681.8	635.7	611.2	586.7	577.4	568.0	560.9	553.8
25°	812.4	740.5	668.6	628.3	588.0	569.0	550.0	543.8	537.7	530.6	523.5
27.5°	751.8	683.4	615.1	582.8	550.6	535.1	519.7	511.9	504.2	498.4	492.6
30°	698.2	635.1	571.9	545.1	518.4	504.8	491.3	482.9	474.5	469.0	463.6
32.5°	646.7	590.6	534.5	511.6	488.7	475.5	462.3	454.2	446.2	439.7	433.3
35°	599.0	550.3	501.6	480.6	459.7	446.5	433.3	425.2	417.1	410.7	404.2
37.5°	557.0	512.9	468.7	449.1	429.4	417.8	406.2	397.8	389.4	382.6	375.9
40°	517.7	478.7	439.7	420.7	401.7	389.1	376.5	369.1	361.7	355.6	349.4
42.5°	482.9	447.1	411.3	392.6	373.9	362.0	350.1	341.4	332.7	329.1	325.6
45°	446.2	414.6	383.0	364.9	346.9	334.3	321.7	314.3	306.9	303.7	300.4
47.5°	413.9	384.6	355.2	337.5	319.8	308.5	297.2	291.4	285.6	281.1	276.6
50°	382.3	354.0	325.6	308.5	291.4	281.7	272.1	265.0	257.9	254.7	251.4
52.5°	352.0	326.2	300.4	283.0	265.6	256.3	246.9	240.8	234.7	227.9	221.1
55°	317.9	295.3	272.7	257.2	241.8	232.1	222.4	215.3	208.2	201.2	194.1
57.5°	289.5	267.2	245.0	231.1	217.3	207.9	198.6	190.8	183.1	177.3	171.5
60°	258.5	239.2	219.9	206.3	192.8	183.7	174.7	167.3	159.9	157.0	154.1
62.5°	229.5	211.5	193.4	181.5	169.6	160.9	152.2	147.3	142.5	140.6	138.6
65°	199.9	184.4	168.9	158.0	147.0	139.6	132.2	129.9	127.7	126.0	124.4
67.5°	172.1	158.9	145.7	136.0	126.4	121.2	116.1	113.5	110.9	109.0	107.0
70°	147.0	135.4	123.8	115.4	107.0	102.2	97.4	95.1	92.8	89.3	85.7
72.5°	119.9	110.9	101.9	95.4	89.0	84.8	80.6	76.1	71.6	68.3	65.1
75°	99.3	90.3	81.2	75.1	69.0	64.2	59.3	57.7	56.1	55.1	54.2
77.5°	76.1	68.3	60.6	55.8	50.9	48.7	46.4	45.5	44.5	44.2	43.8
80°	54.8	48.4	41.9	39.3	36.7	36.1	35.5	34.8	34.2	33.8	33.5
82.5°	34.2	30.9	27.7	27.1	26.4	26.1	25.8	25.5	25.1	24.8	24.5
85°	20.0	18.7	17.4	17.1	16.8	16.4	16.1	16.1	16.1	16.1	16.1
87.5°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.1	7.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832473

CATALOG NUMBER: S123RDP-S560D935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1572.5	1572.5	1572.5	1572.5
2.5°	1397.1	1393.9	1392.6	1391.3
5°	1197.6	1187.6	1185.3	1183.1
7.5°	1028.0	1023.8	1010.0	996.1
10°	890.4	877.5	871.7	865.9
12.5°	775.3	763.4	761.4	759.5
15°	686.0	677.6	674.7	671.8
17.5°	627.3	621.5	618.0	614.4
20°	583.8	579.6	577.0	574.5
22.5°	550.6	547.4	545.4	543.5
25°	518.7	513.8	512.2	510.6
27.5°	488.4	484.2	482.6	481.0
30°	460.0	456.5	454.2	452.0
32.5°	429.1	424.9	423.6	422.3
35°	401.7	399.1	397.8	396.5
37.5°	372.7	369.4	367.5	365.6
40°	347.8	346.2	345.3	344.3
42.5°	322.7	319.8	319.5	319.1
45°	297.5	294.6	294.0	293.4
47.5°	274.0	271.4	271.1	270.8
50°	247.9	244.4	241.8	239.2
52.5°	217.9	214.7	212.4	210.2
55°	190.5	187.0	185.0	183.1
57.5°	169.9	168.3	167.3	166.3
60°	153.1	152.2	151.5	150.9
62.5°	137.6	136.7	136.7	136.7
65°	123.5	122.5	121.5	120.6
67.5°	105.1	103.2	102.8	102.5
70°	82.8	79.9	79.6	79.3
72.5°	64.8	64.5	63.8	63.2
75°	53.5	52.9	52.9	52.9
77.5°	43.2	42.6	42.6	42.6
80°	33.2	32.9	33.2	33.5
82.5°	24.5	24.5	24.2	23.9
85°	15.8	15.5	15.5	15.5
87.5°	7.7	7.7	7.7	7.7
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832473

CATALOG NUMBER: S123RDP-S560D935-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.53	15.99	14.90	16.30	16.62	19.20	20.65	19.56	20.97	21.28
	3H	15.80	17.10	16.18	17.43	17.79	20.74	22.04	21.12	22.37	22.73
	4H	16.21	17.43	16.61	17.78	18.16	21.26	22.48	21.66	22.83	23.21
	6H	16.52	17.64	16.93	18.01	18.40	21.60	22.72	22.01	23.09	23.48
	8H	16.62	17.69	17.05	18.08	18.48	21.69	22.76	22.12	23.15	23.55
	12H	16.69	17.71	17.12	18.09	18.52	21.74	22.77	22.17	23.15	23.58
4H	2H	15.33	16.55	15.73	16.90	17.28	19.26	20.48	19.66	20.83	21.21
	3H	16.75	17.76	17.16	18.16	18.56	20.97	21.98	21.38	22.38	22.78
	4H	17.22	18.13	17.66	18.55	18.99	21.60	22.51	22.03	22.92	23.36
	6H	17.62	18.41	18.08	18.85	19.31	22.07	22.85	22.53	23.30	23.76
	8H	17.76	18.49	18.22	18.94	19.40	22.21	22.94	22.67	23.39	23.86
	12H	17.86	18.51	18.34	18.99	19.46	22.30	22.95	22.78	23.43	23.90
8H	4H	17.58	18.31	18.04	18.76	19.23	21.61	22.34	22.07	22.79	23.26
	6H	18.06	18.67	18.56	19.16	19.64	22.12	22.73	22.62	23.22	23.70
	8H	18.25	18.80	18.77	19.31	19.80	22.31	22.85	22.83	23.36	23.85
	12H	18.42	18.90	18.93	19.39	19.96	22.45	22.93	22.96	23.42	23.99
12H	4H	17.62	18.27	18.10	18.75	19.22	21.58	22.24	22.07	22.72	23.19
	6H	18.12	18.66	18.64	19.17	19.66	22.10	22.64	22.61	23.15	23.64
	8H	18.36	18.84	18.88	19.34	19.90	22.32	22.80	22.83	23.29	23.86