

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832451

Luminaire Tested: S123RDP-S1165D840-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832451
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S1165D840-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 5018.0 lumens
 Efficiency: N/A
 Efficacy: 118.9 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct


Input Watts (W): 42.2
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832451

CATALOG NUMBER: S123RDP-S1165D840-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832451

CATALOG NUMBER: S123RDP-S1165D840-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59				
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53				
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47				
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43				
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39				
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	40739	40739	40739	40739	40739
5°	48372	46830	40995	33140	30767
10°	43827	47566	40791	26552	22778
15°	30175	40783	40360	21702	18018
20°	20992	31400	39550	18299	15837
25°	15997	23931	38371	16264	14596
30°	13926	19132	36896	15101	13520
35°	12786	16139	34807	14121	12540
40°	11665	14412	32073	13159	11643
45°	10535	13181	29125	12248	10749
50°	9562	12161	25648	11355	9640
55°	8649	11168	22308	10483	8270
60°	7750	10155	19375	9522	7817
65°	7154	9011	16677	8558	7391
70°	5813	7789	14552	7742	6008
75°	5099	6197	12327	6421	5290
80°	4618	5244	10098	5387	5002
85°	4211	4594	7669	4891	4594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 30731 cd/sqm

TEST NUMBER: P832451

CATALOG NUMBER: S123RDP-S1165D840-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.0	6.9
10°-20°	798.3	15.9
20°-30°	915.9	18.3
30°-40°	902.8	18.0
40°-50°	796.1	15.9
50°-60°	612.5	12.2
60°-70°	402.7	8.0
70°-80°	195.6	3.9
80°-90°	49.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2059.1	41.0
0°-40°	2961.9	59.0
0°-60°	4370.5	87.1
0°-90°	5018.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5018.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3785	3785	3785	3785	3785	
5°	4477	4334	3794	3067	2848	409
15°	2708	3660	3622	1948	1617	764
25°	1347	2015	3231	1369	1229	636
35°	973	1228	2649	1075	954	607
45°	692	866	1913	805	706	537
55°	461	595	1189	559	441	413
65°	281	354	655	336	290	275
75°	123	149	296	154	127	132
85°	34	37	62	40	37	38
90°	0	0	0	0	0	

TEST NUMBER: P832451

CATALOG NUMBER: S123RDP-S1165D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	4194.4	4181.2	4168.0	4164.2	4160.3	4147.9	4135.5	4107.5	4079.6	4050.9	4022.2
5°	4476.8	4478.4	4479.9	4476.1	4472.2	4455.9	4439.6	4405.5	4371.3	4334.1	4296.8
7.5°	4389.9	4414.8	4439.6	4444.3	4448.9	4461.3	4473.7	4466.0	4458.2	4444.3	4430.3
10°	4009.8	4008.2	4006.7	4034.6	4062.5	4145.5	4228.6	4271.2	4313.9	4351.9	4389.9
12.5°	3389.1	3391.4	3393.7	3485.3	3576.8	3655.2	3733.5	3842.2	3950.8	4067.9	4185.1
15°	2707.8	2745.8	2783.9	2865.3	2946.8	3064.7	3182.7	3328.5	3474.4	3659.8	3845.3
17.5°	2223.7	2240.0	2256.3	2334.6	2413.0	2524.7	2636.4	2801.7	2967.0	3205.9	3444.9
20°	1832.6	1847.4	1862.1	1918.8	1975.4	2082.5	2189.5	2347.0	2504.5	2741.2	2977.8
22.5°	1530.0	1558.7	1587.5	1625.5	1663.5	1741.1	1818.7	1979.3	2139.9	2355.6	2571.3
25°	1346.9	1360.1	1373.3	1405.9	1438.5	1513.0	1587.5	1693.8	1800.0	2015.0	2229.9
27.5°	1222.8	1226.7	1230.5	1254.6	1278.7	1326.8	1374.9	1473.4	1571.9	1748.8	1925.7
30°	1120.4	1127.4	1134.3	1153.0	1171.6	1206.5	1241.4	1311.2	1381.1	1539.3	1697.6
32.5°	1041.2	1045.1	1049.0	1064.5	1080.0	1105.6	1131.2	1186.3	1241.4	1362.4	1483.5
35°	973.0	973.7	974.5	986.1	997.8	1022.6	1047.4	1093.2	1139.0	1228.2	1317.4
37.5°	895.4	900.8	906.2	914.8	923.3	945.0	966.7	1004.0	1041.2	1114.9	1188.7
40°	830.2	834.8	839.5	849.6	859.7	876.7	893.8	928.0	962.1	1025.7	1089.3
42.5°	765.0	768.1	771.2	781.3	791.4	812.3	833.3	860.5	887.6	940.4	993.1
45°	692.1	699.8	707.6	718.5	729.3	747.2	765.0	793.0	820.9	865.9	910.9
47.5°	631.6	635.4	639.3	648.6	657.9	679.7	701.4	726.2	751.1	793.0	834.8
50°	571.0	572.6	574.2	582.7	591.2	610.6	630.0	658.7	687.4	726.2	765.0
52.5°	513.6	517.5	521.4	529.9	538.5	551.7	564.8	594.3	623.8	661.8	699.8
55°	460.9	463.2	465.5	471.7	477.9	493.5	509.0	534.6	560.2	595.1	630.0
57.5°	411.2	414.3	417.4	422.1	426.7	440.7	454.7	477.2	499.7	534.6	569.5
60°	360.0	363.9	367.8	373.2	378.6	389.5	400.4	420.5	440.7	471.7	502.8
62.5°	322.8	323.5	324.3	329.0	333.6	341.4	349.1	365.4	381.7	412.8	443.8
65°	280.9	283.2	285.5	287.9	290.2	296.4	302.6	316.6	330.5	353.8	377.1
67.5°	237.4	239.7	242.1	246.0	249.8	255.3	260.7	270.0	279.3	301.0	322.8
70°	184.7	184.7	184.7	190.9	197.1	206.4	215.7	222.7	229.7	247.5	265.4
72.5°	150.5	151.3	152.1	152.8	153.6	159.1	164.5	176.1	187.8	198.6	209.5
75°	122.6	123.4	124.1	124.9	125.7	127.2	128.8	132.7	136.6	149.0	161.4
77.5°	97.8	98.5	99.3	100.1	100.9	102.4	104.0	105.5	107.1	111.7	116.4
80°	74.5	75.3	76.0	76.8	77.6	78.4	79.1	80.7	82.2	84.6	86.9
82.5°	54.3	54.3	54.3	54.3	54.3	55.9	57.4	57.4	57.4	59.0	60.5
85°	34.1	34.1	34.1	34.9	35.7	35.7	35.7	36.5	37.2	37.2	37.2
87.5°	15.5	14.7	14.0	14.7	15.5	15.5	15.5	16.3	17.1	17.1	17.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832451

CATALOG NUMBER: S123RDP-S1165D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	4018.3	4014.4	3977.2	3939.9	3903.5	3867.0	3839.8	3812.7	3766.9	3721.1	3692.4
5°	4267.4	4237.9	4178.9	4119.9	4031.5	3943.0	3868.5	3794.1	3699.4	3604.7	3525.6
7.5°	4406.2	4382.2	4310.8	4239.4	4122.3	4005.1	3888.7	3772.3	3632.7	3493.0	3373.5
10°	4410.1	4430.3	4371.3	4312.4	4180.5	4048.6	3890.3	3732.0	3544.2	3356.5	3202.1
12.5°	4272.0	4358.9	4346.5	4334.1	4199.8	4065.6	3873.2	3680.8	3450.3	3219.9	3026.7
15°	4013.6	4182.0	4231.7	4281.3	4170.4	4059.4	3840.6	3621.8	3351.0	3080.3	2858.3
17.5°	3680.8	3916.7	4047.8	4178.9	4098.2	4017.5	3777.8	3538.0	3233.1	2928.2	2686.9
20°	3286.6	3595.4	3801.0	4006.7	3977.2	3947.7	3700.2	3452.7	3123.7	2794.7	2533.3
22.5°	2897.1	3223.0	3507.0	3791.0	3821.2	3851.5	3601.6	3351.8	2991.8	2631.8	2365.7
25°	2561.2	2892.5	3230.8	3569.1	3637.3	3705.6	3468.2	3230.8	2857.6	2484.4	2219.8
27.5°	2240.7	2555.8	2928.2	3300.6	3424.7	3548.9	3331.6	3114.4	2725.7	2337.0	2073.2
30°	1979.3	2260.9	2641.1	3021.3	3194.3	3367.3	3167.9	2968.5	2582.9	2197.3	1938.9
32.5°	1735.6	1987.8	2369.5	2751.3	2952.2	3153.2	2980.9	2808.7	2437.8	2066.9	1811.7
35°	1543.2	1769.0	2125.1	2481.3	2706.3	2931.3	2790.1	2648.9	2286.5	1924.2	1682.9
37.5°	1378.0	1567.3	1901.7	2236.1	2475.1	2714.0	2596.1	2478.2	2137.6	1796.9	1568.8
40°	1241.4	1393.5	1704.6	2015.7	2250.1	2484.4	2383.5	2282.6	1977.7	1672.8	1459.4
42.5°	1124.3	1255.4	1534.7	1814.0	2028.9	2243.9	2177.1	2110.4	1834.2	1558.0	1360.1
45°	1021.1	1131.2	1377.2	1623.1	1821.0	2018.8	1966.1	1913.3	1675.1	1436.9	1255.4
47.5°	929.5	1024.2	1243.7	1463.3	1641.0	1818.7	1769.8	1720.9	1523.8	1326.8	1161.5
50°	845.7	926.4	1109.5	1292.6	1452.5	1612.3	1571.9	1531.6	1368.7	1205.7	1063.0
52.5°	766.6	833.3	997.8	1162.3	1291.1	1419.9	1388.8	1357.8	1232.1	1106.4	976.8
55°	691.3	752.6	891.5	1030.4	1140.5	1250.7	1219.7	1188.7	1090.9	993.1	879.1
57.5°	623.0	676.6	789.1	901.6	989.2	1076.9	1062.2	1047.4	966.0	884.5	790.6
60°	550.9	599.0	696.0	793.0	863.6	934.2	917.1	900.0	841.8	783.6	702.9
62.5°	486.5	529.2	606.7	684.3	741.7	799.2	786.7	774.3	730.1	685.9	619.2
65°	419.0	460.9	523.7	586.6	631.6	676.6	665.7	654.8	621.5	588.1	534.6
67.5°	357.7	392.6	446.9	501.2	531.5	561.7	555.5	549.3	523.7	498.1	456.2
70°	295.6	325.9	370.9	415.9	436.8	457.8	460.1	462.4	439.1	415.9	384.8
72.5°	233.5	257.6	299.5	341.4	357.7	374.0	373.2	372.4	358.5	344.5	316.6
75°	179.2	197.1	229.7	262.2	276.2	290.2	293.3	296.4	283.2	270.0	254.5
77.5°	128.8	141.2	166.0	190.9	206.4	221.9	223.5	225.0	218.8	212.6	197.8
80°	90.8	94.7	110.2	125.7	142.0	158.3	160.6	162.9	156.7	150.5	141.2
82.5°	62.8	65.2	70.6	76.0	89.2	102.4	105.5	108.6	105.5	102.4	92.3
85°	38.0	38.8	41.1	43.4	49.7	55.9	59.0	62.1	60.5	59.0	53.5
87.5°	17.1	17.1	17.8	18.6	20.2	21.7	25.6	29.5	27.2	24.8	22.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832451

CATALOG NUMBER: S123RDP-S1165D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8	3784.8
2.5°	3663.7	3619.5	3575.3	3543.5	3511.6	3472.1	3432.5	3431.0	3429.4	3399.9	3370.4
5°	3446.5	3369.7	3292.8	3217.6	3142.3	3067.1	2991.8	2974.7	2957.7	2932.1	2906.5
7.5°	3254.0	3131.5	3008.9	2912.7	2816.5	2741.2	2665.9	2614.7	2563.5	2523.9	2484.4
10°	3047.7	2895.6	2743.5	2627.1	2510.8	2429.3	2347.8	2288.9	2229.9	2202.0	2174.0
12.5°	2833.5	2668.3	2503.0	2388.9	2274.9	2177.1	2079.4	2025.8	1972.3	1933.5	1894.7
15°	2636.4	2458.8	2281.1	2160.1	2039.0	1947.5	1855.9	1802.4	1748.8	1710.0	1671.2
17.5°	2445.6	2266.4	2087.1	1964.5	1841.9	1758.9	1675.9	1623.9	1571.9	1547.9	1523.8
20°	2271.8	2091.0	1910.2	1794.6	1679.0	1597.5	1516.1	1488.1	1460.2	1437.7	1415.2
22.5°	2099.5	1925.7	1751.9	1641.0	1530.0	1471.1	1412.1	1389.6	1367.1	1350.0	1333.0
25°	1955.2	1782.2	1609.2	1512.2	1415.2	1369.4	1323.7	1308.9	1294.2	1277.1	1260.0
27.5°	1809.4	1644.9	1480.4	1402.8	1325.2	1288.0	1250.7	1232.1	1213.5	1199.5	1185.5
30°	1680.6	1528.5	1376.4	1312.0	1247.6	1215.0	1182.4	1162.3	1142.1	1128.9	1115.7
32.5°	1556.4	1421.4	1286.4	1231.3	1176.2	1144.4	1112.6	1093.2	1073.8	1058.3	1042.8
35°	1441.6	1324.4	1207.3	1156.8	1106.4	1074.6	1042.8	1023.4	1004.0	988.5	973.0
37.5°	1340.7	1234.4	1128.1	1080.8	1033.5	1005.5	977.6	957.4	937.3	921.0	904.7
40°	1246.1	1152.2	1058.3	1012.5	966.7	936.5	906.2	888.4	870.5	855.8	841.1
42.5°	1162.3	1076.1	990.0	945.0	900.0	871.3	842.6	821.7	800.7	792.2	783.6
45°	1073.8	997.8	921.7	878.3	834.8	804.6	774.3	756.5	738.6	730.9	723.1
47.5°	996.2	925.6	855.0	812.3	769.7	742.5	715.4	701.4	687.4	676.6	665.7
50°	920.2	851.9	783.6	742.5	701.4	678.1	654.8	637.8	620.7	612.9	605.2
52.5°	847.3	785.2	723.1	681.2	639.3	616.8	594.3	579.6	564.8	548.5	532.3
55°	765.0	710.7	656.4	619.2	581.9	558.6	535.4	518.3	501.2	484.2	467.1
57.5°	696.7	643.2	589.7	556.3	522.9	500.4	477.9	459.3	440.7	426.7	412.8
60°	622.3	575.7	529.2	496.6	464.0	442.3	420.5	402.7	384.8	377.9	370.9
62.5°	552.4	509.0	465.5	436.8	408.1	387.2	366.2	354.6	342.9	338.3	333.6
65°	481.0	443.8	406.6	380.2	353.8	336.0	318.1	312.7	307.2	303.4	299.5
67.5°	414.3	382.5	350.7	327.4	304.1	291.7	279.3	273.1	266.9	262.2	257.6
70°	353.8	325.9	297.9	277.8	257.6	246.0	234.3	228.9	223.5	214.9	206.4
72.5°	288.6	266.9	245.2	229.7	214.1	204.1	194.0	183.1	172.2	164.5	156.7
75°	239.0	217.2	195.5	180.8	166.0	154.4	142.8	138.9	135.0	132.7	130.3
77.5°	183.1	164.5	145.9	134.2	122.6	117.2	111.7	109.4	107.1	106.3	105.5
80°	131.9	116.4	100.9	94.7	88.5	86.9	85.3	83.8	82.2	81.5	80.7
82.5°	82.2	74.5	66.7	65.2	63.6	62.8	62.1	61.3	60.5	59.7	59.0
85°	48.1	45.0	41.9	41.1	40.3	39.6	38.8	38.8	38.8	38.8	38.8
87.5°	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.2	19.4	18.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832451

CATALOG NUMBER: S123RDP-S1165D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3784.8	3784.8	3784.8	3784.8
2.5°	3362.7	3354.9	3351.8	3348.7
5°	2882.4	2858.3	2852.9	2847.5
7.5°	2474.3	2464.2	2430.8	2397.5
10°	2143.0	2112.0	2098.0	2084.0
12.5°	1866.0	1837.3	1832.6	1828.0
15°	1651.1	1630.9	1623.9	1616.9
17.5°	1509.9	1495.9	1487.4	1478.8
20°	1405.1	1395.0	1388.8	1382.6
22.5°	1325.2	1317.4	1312.8	1308.1
25°	1248.4	1236.8	1232.9	1229.0
27.5°	1175.5	1165.4	1161.5	1157.6
30°	1107.2	1098.6	1093.2	1087.8
32.5°	1032.7	1022.6	1019.5	1016.4
35°	966.7	960.5	957.4	954.3
37.5°	896.9	889.2	884.5	879.9
40°	837.2	833.3	831.0	828.6
42.5°	776.7	769.7	768.9	768.1
45°	716.1	709.2	707.6	706.1
47.5°	659.5	653.3	652.5	651.7
50°	596.7	588.1	581.9	575.7
52.5°	524.5	516.7	511.3	505.9
55°	458.5	450.0	445.4	440.7
57.5°	408.9	405.0	402.7	400.4
60°	368.5	366.2	364.7	363.1
62.5°	331.3	329.0	329.0	329.0
65°	297.2	294.8	292.5	290.2
67.5°	252.9	248.3	247.5	246.7
70°	199.4	192.4	191.6	190.9
72.5°	156.0	155.2	153.6	152.1
75°	128.8	127.2	127.2	127.2
77.5°	104.0	102.4	102.4	102.4
80°	79.9	79.1	79.9	80.7
82.5°	59.0	59.0	58.2	57.4
85°	38.0	37.2	37.2	37.2
87.5°	18.6	18.6	18.6	18.6
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832451

CATALOG NUMBER: S123RDP-S1165D840-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.59	19.04	17.95	19.35	19.67	22.25	23.70	22.61	24.02	24.33
	3H	18.85	20.15	19.23	20.48	20.84	23.79	25.09	24.17	25.42	25.78
	4H	19.26	20.48	19.66	20.83	21.21	24.31	25.53	24.71	25.88	26.26
	6H	19.57	20.69	19.98	21.06	21.45	24.65	25.77	25.06	26.14	26.53
	8H	19.67	20.74	20.10	21.13	21.53	24.74	25.81	25.17	26.20	26.61
	12H	19.74	20.76	20.17	21.15	21.58	24.79	25.82	25.22	26.20	26.63
4H	2H	18.38	19.60	18.78	19.95	20.33	22.31	23.53	22.71	23.88	24.26
	3H	19.80	20.81	20.21	21.21	21.61	24.02	25.03	24.43	25.43	25.83
	4H	20.27	21.18	20.71	21.60	22.04	24.65	25.56	25.08	25.97	26.41
	6H	20.67	21.46	21.13	21.90	22.37	25.12	25.91	25.58	26.35	26.81
	8H	20.81	21.54	21.27	21.99	22.46	25.26	25.99	25.72	26.44	26.91
	12H	20.91	21.56	21.39	22.04	22.52	25.35	26.00	25.83	26.48	26.96
8H	4H	20.63	21.36	21.09	21.81	22.28	24.66	25.39	25.12	25.84	26.31
	6H	21.11	21.72	21.61	22.21	22.69	25.17	25.78	25.67	26.27	26.75
	8H	21.31	21.85	21.82	22.36	22.85	25.36	25.90	25.88	26.41	26.90
	12H	21.47	21.95	21.98	22.44	23.01	25.50	25.98	26.02	26.47	27.04
12H	4H	20.67	21.32	21.15	21.80	22.27	24.64	25.29	25.12	25.77	26.24
	6H	21.17	21.71	21.69	22.23	22.72	25.15	25.69	25.67	26.20	26.69
	8H	21.42	21.90	21.93	22.39	22.96	25.37	25.85	25.88	26.34	26.91