

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832460

Luminaire Tested: S123RDP-S340D840-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832460
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S340D840-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 1487.5 lumens
 Efficiency: N/A
 Efficacy: 120.0 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct


Input Watts (W): 12.4
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832460

CATALOG NUMBER: S123RDP-S340D840-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832460

CATALOG NUMBER: S123RDP-S340D840-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59				
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53				
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47				
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43				
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39				
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	12076	12076	12076	12076	12076
5°	14338	13881	12151	9823	9121
10°	12991	14100	12091	7871	6753
15°	8945	12090	11964	6433	5341
20°	6222	9308	11724	5424	4694
25°	4742	7094	11374	4821	4327
30°	4128	5671	10936	4477	4007
35°	3790	4784	10318	4185	3717
40°	3458	4272	9507	3901	3451
45°	3124	3908	8634	3631	3186
50°	2835	3605	7603	3366	2858
55°	2563	3310	6611	3108	2451
60°	2297	3010	5744	2822	2316
65°	2122	2672	4944	2537	2190
70°	1721	2310	4315	2294	1781
75°	1510	1838	3656	1905	1568
80°	1370	1556	2994	1599	1481
85°	1247	1359	2272	1445	1359

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 9109 cd/sqm

TEST NUMBER: P832460

CATALOG NUMBER: S123RDP-S340D840-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	6.9
10°-20°	236.6	15.9
20°-30°	271.5	18.3
30°-40°	267.6	18.0
40°-50°	236.0	15.9
50°-60°	181.6	12.2
60°-70°	119.4	8.0
70°-80°	58.0	3.9
80°-90°	14.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.4	41.0
0°-40°	878.0	59.0
0°-60°	1295.5	87.1
0°-90°	1487.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1487.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1122	1122	1122	1122	1122	
5°	1327	1285	1125	909	844	121
15°	803	1085	1074	577	479	227
25°	399	597	958	406	364	189
35°	288	364	785	318	283	180
45°	205	257	567	238	209	159
55°	137	176	352	166	131	123
65°	83	105	194	100	86	82
75°	36	44	88	46	38	39
85°	10	11	18	12	11	11
90°	0	0	0	0	0	

TEST NUMBER: P832460

CATALOG NUMBER: S123RDP-S340D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1243.3	1239.4	1235.5	1234.4	1233.2	1229.5	1225.8	1217.6	1209.3	1200.8	1192.3
5°	1327.0	1327.5	1328.0	1326.8	1325.7	1320.8	1316.0	1305.9	1295.8	1284.7	1273.7
7.5°	1301.3	1308.6	1316.0	1317.4	1318.8	1322.4	1326.1	1323.8	1321.5	1317.4	1313.2
10°	1188.6	1188.1	1187.7	1195.9	1204.2	1228.8	1253.4	1266.1	1278.7	1290.0	1301.3
12.5°	1004.6	1005.3	1006.0	1033.1	1060.3	1083.5	1106.7	1138.9	1171.1	1205.8	1240.6
15°	802.7	813.9	825.2	849.4	873.5	908.5	943.4	986.7	1029.9	1084.9	1139.8
17.5°	659.1	664.0	668.8	692.0	715.3	748.4	781.5	830.5	879.5	950.3	1021.2
20°	543.2	547.6	552.0	568.8	585.6	617.3	649.0	695.7	742.4	812.6	882.7
22.5°	453.5	462.0	470.6	481.8	493.1	516.1	539.1	586.7	634.3	698.2	762.2
25°	399.3	403.2	407.1	416.7	426.4	448.5	470.6	502.1	533.6	597.3	661.0
27.5°	362.5	363.6	364.8	371.9	379.0	393.3	407.5	436.7	466.0	518.4	570.8
30°	332.1	334.2	336.2	341.8	347.3	357.6	368.0	388.7	409.4	456.3	503.2
32.5°	308.6	309.8	310.9	315.5	320.1	327.7	335.3	351.7	368.0	403.9	439.7
35°	288.4	288.6	288.9	292.3	295.8	303.1	310.5	324.1	337.6	364.1	390.5
37.5°	265.4	267.0	268.6	271.2	273.7	280.1	286.6	297.6	308.6	330.5	352.3
40°	246.1	247.5	248.8	251.8	254.8	259.9	264.9	275.1	285.2	304.0	322.9
42.5°	226.8	227.7	228.6	231.6	234.6	240.8	247.0	255.1	263.1	278.7	294.4
45°	205.2	207.5	209.8	213.0	216.2	221.5	226.8	235.0	243.3	256.7	270.0
47.5°	187.2	188.4	189.5	192.3	195.0	201.5	207.9	215.3	222.6	235.0	247.5
50°	169.3	169.7	170.2	172.7	175.3	181.0	186.8	195.3	203.8	215.3	226.8
52.5°	152.3	153.4	154.6	157.1	159.6	163.5	167.4	176.2	184.9	196.2	207.5
55°	136.6	137.3	138.0	139.8	141.7	146.3	150.9	158.5	166.1	176.4	186.8
57.5°	121.9	122.8	123.7	125.1	126.5	130.6	134.8	141.4	148.1	158.5	168.8
60°	106.7	107.9	109.0	110.6	112.2	115.5	118.7	124.7	130.6	139.8	149.0
62.5°	95.7	95.9	96.1	97.5	98.9	101.2	103.5	108.3	113.2	122.4	131.6
65°	83.3	83.9	84.6	85.3	86.0	87.9	89.7	93.8	98.0	104.9	111.8
67.5°	70.4	71.1	71.8	72.9	74.1	75.7	77.3	80.0	82.8	89.2	95.7
70°	54.7	54.7	54.7	56.6	58.4	61.2	63.9	66.0	68.1	73.4	78.7
72.5°	44.6	44.8	45.1	45.3	45.5	47.1	48.8	52.2	55.7	58.9	62.1
75°	36.3	36.6	36.8	37.0	37.3	37.7	38.2	39.3	40.5	44.2	47.8
77.5°	29.0	29.2	29.4	29.7	29.9	30.4	30.8	31.3	31.7	33.1	34.5
80°	22.1	22.3	22.5	22.8	23.0	23.2	23.5	23.9	24.4	25.1	25.8
82.5°	16.1	16.1	16.1	16.1	16.1	16.6	17.0	17.0	17.0	17.5	17.9
85°	10.1	10.1	10.1	10.3	10.6	10.6	10.6	10.8	11.0	11.0	11.0
87.5°	4.6	4.4	4.1	4.4	4.6	4.6	4.6	4.8	5.1	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832460

CATALOG NUMBER: S123RDP-S340D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1191.1	1190.0	1178.9	1167.9	1157.1	1146.3	1138.2	1130.2	1116.6	1103.0	1094.5
5°	1264.9	1256.2	1238.7	1221.2	1195.0	1168.8	1146.7	1124.6	1096.6	1068.5	1045.1
7.5°	1306.1	1299.0	1277.8	1256.7	1221.9	1187.2	1152.7	1118.2	1076.8	1035.4	1000.0
10°	1307.3	1313.2	1295.8	1278.3	1239.2	1200.1	1153.2	1106.2	1050.6	994.9	949.2
12.5°	1266.3	1292.1	1288.4	1284.7	1244.9	1205.1	1148.1	1091.1	1022.8	954.5	897.2
15°	1189.7	1239.6	1254.4	1269.1	1236.2	1203.3	1138.4	1073.6	993.3	913.1	847.3
17.5°	1091.1	1161.0	1199.9	1238.7	1214.8	1190.9	1119.8	1048.8	958.4	868.0	796.5
20°	974.2	1065.8	1126.7	1187.7	1178.9	1170.2	1096.8	1023.5	925.9	828.4	750.9
22.5°	858.8	955.4	1039.6	1123.7	1132.7	1141.7	1067.6	993.6	886.8	780.1	701.2
25°	759.2	857.4	957.7	1058.0	1078.2	1098.4	1028.1	957.7	847.1	736.4	658.0
27.5°	664.2	757.6	868.0	978.4	1015.2	1052.0	987.6	923.2	808.0	692.7	614.5
30°	586.7	670.2	782.9	895.6	946.9	998.2	939.0	879.9	765.6	651.3	574.7
32.5°	514.5	589.2	702.4	815.5	875.1	934.7	883.6	832.6	722.6	612.7	537.0
35°	457.4	524.4	629.9	735.5	802.2	868.9	827.0	785.2	677.8	570.4	498.8
37.5°	408.5	464.6	563.7	662.8	733.7	804.5	769.5	734.6	633.6	532.7	465.0
40°	368.0	413.1	505.3	597.5	667.0	736.4	706.5	676.6	586.2	495.9	432.6
42.5°	333.3	372.1	454.9	537.7	601.4	665.1	645.4	625.6	543.7	461.8	403.2
45°	302.7	335.3	408.2	481.1	539.8	598.4	582.8	567.2	496.5	425.9	372.1
47.5°	275.5	303.6	368.7	433.8	486.4	539.1	524.6	510.1	451.7	393.3	344.3
50°	250.7	274.6	328.9	383.2	430.5	477.9	466.0	454.0	405.7	357.4	315.1
52.5°	227.2	247.0	295.8	344.5	382.7	420.9	411.7	402.5	365.2	328.0	289.6
55°	204.9	223.1	264.3	305.4	338.1	370.7	361.5	352.3	323.4	294.4	260.6
57.5°	184.7	200.6	233.9	267.2	293.2	319.2	314.9	310.5	286.3	262.2	234.4
60°	163.3	177.6	206.3	235.0	256.0	276.9	271.8	266.8	249.5	232.3	208.4
62.5°	144.2	156.9	179.9	202.9	219.9	236.9	233.2	229.5	216.4	203.3	183.5
65°	124.2	136.6	155.2	173.9	187.2	200.6	197.3	194.1	184.2	174.3	158.5
67.5°	106.0	116.4	132.5	148.6	157.5	166.5	164.7	162.8	155.2	147.7	135.2
70°	87.6	96.6	109.9	123.3	129.5	135.7	136.4	137.1	130.2	123.3	114.1
72.5°	69.2	76.4	88.8	101.2	106.0	110.9	110.6	110.4	106.3	102.1	93.8
75°	53.1	58.4	68.1	77.7	81.9	86.0	86.9	87.9	83.9	80.0	75.4
77.5°	38.2	41.9	49.2	56.6	61.2	65.8	66.2	66.7	64.9	63.0	58.6
80°	26.9	28.1	32.7	37.3	42.1	46.9	47.6	48.3	46.5	44.6	41.9
82.5°	18.6	19.3	20.9	22.5	26.4	30.4	31.3	32.2	31.3	30.4	27.4
85°	11.3	11.5	12.2	12.9	14.7	16.6	17.5	18.4	17.9	17.5	15.9
87.5°	5.1	5.1	5.3	5.5	6.0	6.4	7.6	8.7	8.0	7.4	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832460

CATALOG NUMBER: S123RDP-S340D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9	1121.9
2.5°	1086.0	1072.9	1059.8	1050.4	1040.9	1029.2	1017.5	1017.0	1016.6	1007.8	999.1
5°	1021.6	998.8	976.1	953.8	931.5	909.1	886.8	881.8	876.7	869.1	861.5
7.5°	964.6	928.2	891.9	863.4	834.9	812.6	790.2	775.1	759.9	748.2	736.4
10°	903.4	858.3	813.2	778.7	744.2	720.1	695.9	678.5	661.0	652.7	644.4
12.5°	839.9	790.9	741.9	708.1	674.3	645.4	616.4	600.5	584.6	573.1	561.6
15°	781.5	728.8	676.2	640.3	604.4	577.3	550.1	534.3	518.4	506.9	495.4
17.5°	724.9	671.8	618.7	582.3	546.0	521.4	496.8	481.4	466.0	458.8	451.7
20°	673.4	619.8	566.2	532.0	497.7	473.5	449.4	441.1	432.8	426.2	419.5
22.5°	622.4	570.8	519.3	486.4	453.5	436.1	418.6	411.9	405.2	400.2	395.1
25°	579.6	528.3	477.0	448.2	419.5	405.9	392.4	388.0	383.6	378.6	373.5
27.5°	536.3	487.6	438.8	415.8	392.8	381.8	370.7	365.2	359.7	355.6	351.4
30°	498.2	453.1	408.0	388.9	369.8	360.2	350.5	344.5	338.5	334.6	330.7
32.5°	461.4	421.3	381.3	365.0	348.7	339.2	329.8	324.1	318.3	313.7	309.1
35°	427.3	392.6	357.9	342.9	328.0	318.5	309.1	303.4	297.6	293.0	288.4
37.5°	397.4	365.9	334.4	320.4	306.3	298.1	289.8	283.8	277.8	273.0	268.2
40°	369.4	341.5	313.7	300.1	286.6	277.6	268.6	263.3	258.0	253.7	249.3
42.5°	344.5	319.0	293.5	280.1	266.8	258.3	249.8	243.6	237.3	234.8	232.3
45°	318.3	295.8	273.2	260.3	247.5	238.5	229.5	224.2	218.9	216.6	214.4
47.5°	295.3	274.4	253.4	240.8	228.1	220.1	212.1	207.9	203.8	200.6	197.3
50°	272.8	252.5	232.3	220.1	207.9	201.0	194.1	189.1	184.0	181.7	179.4
52.5°	251.1	232.7	214.4	201.9	189.5	182.8	176.2	171.8	167.4	162.6	157.8
55°	226.8	210.7	194.6	183.5	172.5	165.6	158.7	153.6	148.6	143.5	138.5
57.5°	206.5	190.7	174.8	164.9	155.0	148.3	141.7	136.2	130.6	126.5	122.4
60°	184.5	170.7	156.9	147.2	137.5	131.1	124.7	119.4	114.1	112.0	109.9
62.5°	163.8	150.9	138.0	129.5	121.0	114.8	108.6	105.1	101.7	100.3	98.9
65°	142.6	131.6	120.5	112.7	104.9	99.6	94.3	92.7	91.1	89.9	88.8
67.5°	122.8	113.4	104.0	97.1	90.2	86.5	82.8	81.0	79.1	77.7	76.4
70°	104.9	96.6	88.3	82.3	76.4	72.9	69.5	67.8	66.2	63.7	61.2
72.5°	85.6	79.1	72.7	68.1	63.5	60.5	57.5	54.3	51.1	48.8	46.5
75°	70.8	64.4	58.0	53.6	49.2	45.8	42.3	41.2	40.0	39.3	38.6
77.5°	54.3	48.8	43.2	39.8	36.3	34.7	33.1	32.4	31.7	31.5	31.3
80°	39.1	34.5	29.9	28.1	26.2	25.8	25.3	24.8	24.4	24.1	23.9
82.5°	24.4	22.1	19.8	19.3	18.9	18.6	18.4	18.2	17.9	17.7	17.5
85°	14.3	13.3	12.4	12.2	12.0	11.7	11.5	11.5	11.5	11.5	11.5
87.5°	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	5.7	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832460

CATALOG NUMBER: S123RDP-S340D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1121.9	1121.9	1121.9	1121.9
2.5°	996.8	994.5	993.6	992.6
5°	854.4	847.3	845.7	844.1
7.5°	733.4	730.4	720.6	710.7
10°	635.2	626.0	621.9	617.8
12.5°	553.1	544.6	543.2	541.9
15°	489.4	483.4	481.4	479.3
17.5°	447.6	443.4	440.9	438.4
20°	416.5	413.5	411.7	409.8
22.5°	392.8	390.5	389.1	387.8
25°	370.1	366.6	365.5	364.3
27.5°	348.4	345.4	344.3	343.1
30°	328.2	325.7	324.1	322.4
32.5°	306.1	303.1	302.2	301.3
35°	286.6	284.7	283.8	282.9
37.5°	265.9	263.6	262.2	260.8
40°	248.2	247.0	246.3	245.6
42.5°	230.2	228.1	227.9	227.7
45°	212.3	210.2	209.8	209.3
47.5°	195.5	193.7	193.4	193.2
50°	176.9	174.3	172.5	170.7
52.5°	155.5	153.2	151.6	150.0
55°	135.9	133.4	132.0	130.6
57.5°	121.2	120.1	119.4	118.7
60°	109.2	108.6	108.1	107.6
62.5°	98.2	97.5	97.5	97.5
65°	88.1	87.4	86.7	86.0
67.5°	75.0	73.6	73.4	73.1
70°	59.1	57.0	56.8	56.6
72.5°	46.2	46.0	45.5	45.1
75°	38.2	37.7	37.7	37.7
77.5°	30.8	30.4	30.4	30.4
80°	23.7	23.5	23.7	23.9
82.5°	17.5	17.5	17.2	17.0
85°	11.3	11.0	11.0	11.0
87.5°	5.5	5.5	5.5	5.5
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832460

CATALOG NUMBER: S123RDP-S340D840-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.36	14.82	13.72	15.13	15.44	18.03	19.48	18.39	19.79	20.11
	3H	14.62	15.93	15.00	16.25	16.62	19.57	20.87	19.95	21.20	21.56
	4H	15.03	16.25	15.43	16.60	16.98	20.08	21.30	20.48	21.65	22.03
	6H	15.34	16.47	15.75	16.83	17.23	20.42	21.55	20.84	21.92	22.31
	8H	15.45	16.52	15.87	16.91	17.31	20.52	21.59	20.95	21.98	22.38
	12H	15.52	16.54	15.95	16.92	17.35	20.57	21.59	21.00	21.98	22.40
4H	2H	14.15	15.37	14.55	15.72	16.10	18.09	19.31	18.49	19.66	20.04
	3H	15.57	16.58	15.98	16.98	17.38	19.80	20.81	20.21	21.21	21.61
	4H	16.05	16.96	16.48	17.37	17.81	20.43	21.33	20.86	21.75	22.19
	6H	16.45	17.23	16.91	17.68	18.14	20.89	21.68	21.35	22.13	22.59
	8H	16.58	17.32	17.05	17.76	18.23	21.04	21.77	21.50	22.22	22.68
	12H	16.69	17.34	17.17	17.82	18.29	21.13	21.78	21.61	22.26	22.73
8H	4H	16.40	17.14	16.87	17.58	18.05	20.43	21.17	20.90	21.61	22.08
	6H	16.89	17.49	17.39	17.99	18.47	20.95	21.56	21.45	22.05	22.53
	8H	17.08	17.62	17.60	18.14	18.63	21.14	21.68	21.65	22.19	22.68
	12H	17.25	17.73	17.76	18.22	18.79	21.28	21.76	21.79	22.25	22.82
12H	4H	16.44	17.10	16.93	17.58	18.05	20.41	21.07	20.90	21.55	22.02
	6H	16.95	17.49	17.46	18.00	18.49	20.93	21.47	21.44	21.98	22.47
	8H	17.19	17.67	17.70	18.16	18.73	21.15	21.62	21.66	22.12	22.68