

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333006

Luminaire Tested: **S124RDIP-S1195D1035U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333006  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1195D1035U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8950.7 lumens  
Efficiency: N/A  
Efficacy: 134.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333006

CATALOG NUMBER: S124RDIP-S1195D1035U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333006

CATALOG NUMBER: S124RDIP-S1195D1035U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54					54			
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46					46			
2	90	83	77	72	84	77	72	68	66	62	59	56	54	51	47	45	43	39					39			
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	39	37	33					33			
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29					29			
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25					25			
6	64	52	44	38	59	49	42	36	42	37	33	37	32	29	31	28	25	22					22			
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20					20			
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18					18			
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16					16			
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15					15			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16835	16835	16835
5°	16874	16667	16771
10°	16768	16467	16467
15°	16575	16121	16002
20°	16311	15667	15378
25°	15973	15134	14750
30°	15645	14573	13962
35°	15281	13991	13172
40°	14842	13328	12318
45°	14439	12670	11449
50°	13978	11912	10528
55°	13485	11125	9529
60°	12943	10261	8507
65°	12445	9181	7503
70°	11722	7990	6371
75°	10808	6625	5181
80°	9428	5049	4751
85°	7984	4585	4289



TEST NUMBER: P333006

CATALOG NUMBER: S124RDIP-S1195D1035U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.9	2.2
10°-20°	546.3	6.1
20°-30°	788.8	8.8
30°-40°	894.2	10.0
40°-50°	863.5	9.6
50°-60°	718.0	8.0
60°-70°	495.8	5.5
70°-80°	251.3	2.8
80°-90°	68.3	0.8
90°-100°	45.7	0.5
100°-110°	291.1	3.3
110°-120°	556.8	6.2
120°-130°	706.8	7.9
130°-140°	756.2	8.4
140°-150°	707.2	7.9
150°-160°	570.3	6.4
160°-170°	367.8	4.1
170°-180°	126.8	1.4
0°-30°	1531.0	17.1
0°-40°	2425.2	27.1
0°-60°	4006.7	44.8
0°-90°	4822.1	53.9
90°-120°	893.5	10.0
90°-150°	3063.7	34.2
90°-180°	4129.0	46.1
0°-180°	8950.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2057	2072	2070	197
15°	1983	1967	1929	1925	1915	559
25°	1793	1762	1699	1672	1656	826
35°	1550	1498	1420	1367	1336	968
45°	1265	1204	1110	1034	1003	975
55°	958	892	790	710	677	857
65°	652	581	481	415	393	643
75°	346	287	212	177	166	366
85°	86	56	50	46	46	97
90°	3	14	22	28	30	7
95°	55	23	22	28	29	71
105°	300	306	312	318	284	314
115°	561	564	563	565	565	552
125°	789	792	791	794	795	704
135°	978	978	981	983	985	753
145°	1128	1131	1131	1132	1134	705
155°	1237	1238	1235	1238	1236	570
165°	1305	1300	1300	1307	1299	369
175°	1335	1329	1330	1338	1327	127
180°	1335	1335	1335	1335	1335	



TEST NUMBER: P333006

CATALOG NUMBER: S124RDIP-S1195D1035U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2090.5	2089.4	2088.3	2087.1	2086.0	2083.9	2080.8	2077.6	2074.5	2071.4	2074.5
5°	2082.2	2080.8	2079.4	2078.0	2076.6	2073.7	2069.5	2065.2	2061.0	2056.7	2060.2
7.5°	2063.4	2061.9	2060.4	2058.9	2057.4	2053.9	2048.4	2042.9	2037.3	2031.8	2034.1
10°	2045.5	2043.7	2042.0	2040.2	2038.4	2034.3	2028.0	2021.6	2015.2	2008.8	2010.2
12.5°	2022.5	2020.5	2018.4	2016.3	2014.3	2009.5	2002.0	1994.5	1986.9	1979.4	1980.3
15°	1983.2	1980.0	1976.9	1973.7	1970.5	1964.4	1955.6	1946.7	1937.8	1928.9	1928.2
17.5°	1935.7	1931.0	1926.4	1921.8	1917.2	1909.6	1898.9	1888.3	1877.6	1867.0	1865.0
20°	1898.6	1894.0	1889.4	1884.8	1880.2	1871.8	1859.8	1847.7	1835.6	1823.6	1820.7
22.5°	1857.7	1852.6	1847.4	1842.2	1837.0	1828.0	1815.0	1802.1	1789.2	1776.3	1772.0
25°	1793.2	1786.8	1780.4	1774.1	1767.7	1757.2	1742.7	1728.1	1713.6	1699.0	1693.0
27.5°	1725.5	1717.5	1709.5	1701.5	1693.4	1681.7	1666.1	1650.6	1635.0	1619.5	1612.0
30°	1678.3	1669.4	1660.5	1651.6	1642.8	1630.0	1613.3	1596.6	1580.0	1563.3	1554.4
32.5°	1628.4	1618.4	1608.4	1598.4	1588.4	1574.8	1557.5	1540.3	1523.0	1505.8	1495.5
35°	1550.5	1539.1	1527.8	1516.4	1505.1	1490.5	1472.8	1455.1	1437.3	1419.6	1407.5
37.5°	1467.2	1455.4	1443.7	1432.0	1420.3	1404.6	1385.0	1365.3	1345.7	1326.0	1312.5
40°	1408.4	1396.7	1385.0	1373.3	1361.5	1345.6	1325.4	1305.1	1284.9	1264.7	1249.8
42.5°	1352.2	1339.9	1327.6	1315.3	1303.1	1286.4	1265.3	1244.2	1223.2	1202.1	1186.9
45°	1264.7	1251.5	1238.4	1225.3	1212.2	1194.9	1173.7	1152.4	1131.1	1109.8	1092.4
47.5°	1174.3	1160.7	1147.2	1133.6	1120.1	1102.2	1080.1	1057.9	1035.8	1013.7	995.6
50°	1113.0	1099.1	1085.3	1071.5	1057.6	1039.3	1016.6	993.9	971.2	948.5	930.8
52.5°	1050.4	1036.8	1023.3	1009.7	996.2	977.7	954.5	931.2	907.9	884.6	866.6
55°	958.1	943.9	929.7	915.5	901.3	882.7	859.6	836.6	813.5	790.4	772.0
57.5°	866.7	852.0	837.2	822.5	807.7	789.0	766.3	743.5	720.8	698.1	679.4
60°	801.6	787.4	773.2	759.0	744.8	726.4	703.7	681.0	658.2	635.5	617.1
62.5°	742.8	728.1	713.3	698.6	683.8	664.8	641.5	618.2	594.9	571.7	554.6
65°	651.5	636.2	621.0	605.7	590.5	571.5	548.8	526.1	503.4	480.6	465.4
67.5°	556.6	542.0	527.4	512.8	498.2	480.3	459.2	438.2	417.1	396.0	382.9
70°	496.6	481.7	466.8	451.9	437.0	419.4	399.2	379.0	358.8	338.5	326.8
72.5°	432.7	419.3	405.8	392.3	378.8	362.5	343.4	324.3	305.2	286.1	276.1
75°	346.5	333.4	320.2	307.1	294.0	279.1	262.4	245.7	229.1	212.4	204.2
77.5°	259.0	247.9	236.7	225.6	214.4	202.1	188.6	175.2	161.7	148.2	143.4
80°	202.8	192.5	182.2	171.9	161.6	151.2	140.5	129.9	119.2	108.6	107.5
82.5°	154.3	144.8	135.4	125.9	116.5	108.7	102.6	96.5	90.4	84.3	83.5
85°	86.2	79.1	72.0	64.9	57.8	53.8	52.7	51.6	50.6	49.5	48.8
87.5°	30.0	28.2	26.4	24.6	22.8	22.0	22.1	22.1	22.2	22.3	22.3
90°	3.0	5.4	7.9	10.3	12.8	14.9	16.6	18.4	20.2	22.0	23.3
92.5°	12.6	12.7	12.8	13.0	13.1	14.1	15.8	17.6	19.4	21.2	22.5
95°	54.9	47.4	39.8	32.3	24.7	21.1	21.3	21.5	21.7	22.0	23.3
97.5°	116.6	121.3	126.0	130.7	135.4	125.4	100.6	75.9	51.1	26.4	26.5
100°	163.7	167.7	171.7	175.7	179.7	166.4	135.8	105.2	74.5	43.9	40.2
102.5°	216.4	219.4	222.3	225.2	228.1	227.6	223.6	219.6	215.6	211.6	170.9
105°	300.5	301.8	303.1	304.5	305.8	307.0	308.1	309.2	310.4	311.5	313.5
107.5°	378.5	379.2	379.9	380.5	381.2	382.3	383.8	385.3	386.8	388.3	389.3
110°	431.3	431.9	432.6	433.2	433.9	434.9	436.2	437.6	438.9	440.2	440.7



TEST NUMBER: P333006

CATALOG NUMBER: S124RDIP-S1195D1035U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	482.4	483.6	484.8	486.0	487.2	488.1	488.7	489.3	489.9	490.5	490.5
115°	561.0	561.7	562.4	563.0	563.7	563.9	563.7	563.5	563.2	563.0	563.5
117.5°	631.9	632.8	633.7	634.6	635.5	636.1	636.6	637.1	637.6	638.1	638.0
120°	679.8	680.7	681.6	682.5	683.4	683.7	683.5	683.3	683.0	682.8	683.3
122.5°	724.5	725.1	725.6	726.1	726.7	727.1	727.4	727.7	728.0	728.3	728.6
125°	788.6	789.5	790.4	791.3	792.2	792.4	792.0	791.5	791.1	790.6	791.3
127.5°	849.3	849.5	849.8	850.0	850.2	850.8	851.9	852.9	853.9	854.9	854.8
130°	888.5	888.7	888.9	889.1	889.3	889.8	890.5	891.1	891.8	892.5	892.7
132.5°	924.4	924.8	925.2	925.6	926.0	926.6	927.5	928.3	929.1	930.0	930.2
135°	978.3	978.1	977.9	977.6	977.4	977.7	978.6	979.5	980.4	981.3	981.7
137.5°	1026.0	1026.1	1026.2	1026.3	1026.4	1026.9	1027.9	1028.9	1029.8	1030.8	1031.3
140°	1057.2	1057.6	1058.1	1058.5	1058.9	1059.4	1059.8	1060.3	1060.7	1061.2	1061.8
142.5°	1085.1	1085.9	1086.7	1087.5	1088.3	1088.8	1089.1	1089.4	1089.6	1089.9	1090.4
145°	1128.0	1128.7	1129.4	1130.0	1130.7	1131.0	1131.0	1131.0	1131.0	1131.0	1131.3
147.5°	1162.2	1163.4	1164.7	1165.9	1167.2	1167.7	1167.4	1167.2	1167.0	1166.8	1167.0
150°	1186.9	1187.8	1188.7	1189.6	1190.5	1190.8	1190.6	1190.4	1190.2	1189.9	1189.9
152.5°	1207.7	1208.4	1209.1	1209.8	1210.5	1210.7	1210.3	1209.9	1209.5	1209.1	1209.5
155°	1236.9	1237.1	1237.3	1237.5	1237.7	1237.5	1236.9	1236.2	1235.5	1234.9	1235.7
157.5°	1261.4	1261.3	1261.1	1261.0	1260.9	1260.4	1259.7	1258.9	1258.2	1257.4	1258.6
160°	1275.8	1275.1	1274.5	1273.8	1273.1	1272.7	1272.5	1272.2	1272.0	1271.8	1273.1
162.5°	1288.6	1287.7	1286.9	1286.0	1285.2	1284.7	1284.4	1284.2	1284.0	1283.8	1285.1
165°	1304.7	1303.6	1302.5	1301.4	1300.3	1299.7	1299.7	1299.7	1299.7	1299.7	1301.5
167.5°	1317.5	1316.4	1315.2	1314.1	1312.9	1312.3	1312.1	1312.0	1311.9	1311.7	1313.7
170°	1324.7	1323.4	1322.0	1320.7	1319.4	1318.8	1319.0	1319.3	1319.5	1319.7	1321.5
172.5°	1329.5	1328.2	1326.8	1325.5	1324.2	1323.6	1323.8	1324.1	1324.3	1324.5	1326.3
175°	1334.7	1333.4	1332.0	1330.7	1329.4	1328.8	1329.0	1329.3	1329.5	1329.7	1331.7
177.5°	1337.1	1335.8	1334.6	1333.4	1332.1	1331.7	1332.0	1332.4	1332.7	1333.1	1334.5
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7



TEST NUMBER: P333006

CATALOG NUMBER: S124RDIP-S1195D1035U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4	2085.4
2.5°	2077.6	2080.8	2083.9	2085.3	2085.0	2084.7	2084.4	2084.2
5°	2063.8	2067.3	2070.9	2072.3	2071.6	2070.9	2070.2	2069.5
7.5°	2036.3	2038.6	2040.9	2041.4	2040.3	2039.2	2038.0	2036.9
10°	2011.6	2013.0	2014.5	2014.5	2013.0	2011.6	2010.2	2008.8
12.5°	1981.1	1982.0	1982.8	1982.2	1980.3	1978.3	1976.3	1974.3
15°	1927.5	1926.8	1926.1	1924.5	1922.0	1919.5	1917.1	1914.6
17.5°	1863.0	1861.0	1859.0	1856.2	1852.4	1848.6	1844.9	1841.1
20°	1817.9	1815.0	1812.2	1808.5	1803.9	1799.3	1794.6	1790.0
22.5°	1767.8	1763.5	1759.3	1755.3	1751.5	1747.7	1744.0	1740.2
25°	1686.9	1680.9	1674.9	1670.1	1666.5	1663.0	1659.4	1655.9
27.5°	1604.6	1597.1	1589.7	1583.4	1578.3	1573.2	1568.1	1563.0
30°	1545.5	1536.7	1527.8	1520.5	1514.8	1509.2	1503.5	1497.8
32.5°	1485.2	1474.9	1464.6	1456.8	1451.4	1446.0	1440.6	1435.2
35°	1395.4	1383.4	1371.3	1362.1	1355.7	1349.3	1342.9	1336.5
37.5°	1299.0	1285.5	1272.1	1262.1	1255.7	1249.3	1243.0	1236.6
40°	1234.9	1220.0	1205.1	1194.4	1188.0	1181.6	1175.3	1168.9
42.5°	1171.7	1156.5	1141.3	1130.4	1123.7	1117.1	1110.4	1103.7
45°	1075.0	1057.6	1040.2	1028.3	1022.0	1015.6	1009.2	1002.8
47.5°	977.6	959.6	941.6	929.0	922.0	915.0	907.9	900.9
50°	913.0	895.3	877.5	865.3	858.6	851.8	845.1	838.3
52.5°	848.6	830.6	812.5	800.0	793.0	786.0	778.9	771.9
55°	753.5	735.1	716.6	704.0	697.3	690.5	683.8	677.0
57.5°	660.7	641.9	623.2	611.3	606.2	601.0	595.9	590.8
60°	598.6	580.2	561.7	549.7	544.0	538.3	532.6	526.9
62.5°	537.6	520.6	503.5	492.7	488.2	483.7	479.1	474.6
65°	450.1	434.9	419.6	409.8	405.6	401.3	397.1	392.8
67.5°	369.8	356.6	343.5	334.6	329.9	325.2	320.5	315.8
70°	315.1	303.4	291.7	284.1	280.5	277.0	273.4	269.9
72.5°	266.1	256.1	246.1	239.5	236.2	233.0	229.7	226.4
75°	196.1	187.9	179.7	174.6	172.5	170.3	168.2	166.1
77.5°	138.7	133.9	129.2	126.5	125.8	125.2	124.6	123.9
80°	106.5	105.4	104.3	103.6	103.3	102.9	102.6	102.2
82.5°	82.8	82.0	81.2	80.6	80.3	79.9	79.6	79.2
85°	48.1	47.4	46.7	46.3	46.3	46.3	46.3	46.3
87.5°	22.2	22.2	22.2	22.4	22.8	23.1	23.5	23.9
90°	24.6	26.0	27.3	28.2	28.6	29.1	29.5	29.9
92.5°	23.8	25.2	26.5	27.2	27.3	27.4	27.5	27.6
95°	24.6	26.0	27.3	28.1	28.3	28.5	28.7	28.9
97.5°	26.6	26.8	26.9	27.1	27.3	27.5	27.7	28.0
100°	36.4	32.6	28.8	27.1	27.3	27.5	27.7	28.0
102.5°	130.3	89.6	48.9	28.6	28.6	28.7	28.7	28.8
105°	315.5	317.4	319.4	316.5	308.5	300.5	292.5	284.5
107.5°	390.3	391.3	392.2	393.1	394.0	394.8	395.7	396.5
110°	441.1	441.6	442.0	442.6	443.2	443.9	444.6	445.2





TEST NUMBER: P333006

CATALOG NUMBER: S124RDIP-S1195D1035U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	490.4	490.3	490.2	490.6	491.4	492.3	493.1	493.9
115°	563.9	564.4	564.8	565.0	565.0	565.0	565.0	565.0
117.5°	637.9	637.8	637.7	637.7	637.6	637.5	637.4	637.3
120°	683.7	684.1	684.6	684.6	684.1	683.7	683.3	682.8
122.5°	728.9	729.1	729.4	729.3	728.9	728.4	728.0	727.5
125°	792.0	792.6	793.3	793.7	794.0	794.2	794.4	794.6
127.5°	854.7	854.5	854.4	854.2	854.1	853.9	853.7	853.5
130°	892.9	893.1	893.3	893.5	893.5	893.5	893.5	893.5
132.5°	930.4	930.7	930.9	930.9	930.7	930.5	930.4	930.2
135°	982.2	982.6	983.1	983.5	984.0	984.4	984.8	985.3
137.5°	1031.8	1032.3	1032.8	1032.9	1032.8	1032.7	1032.5	1032.4
140°	1062.5	1063.2	1063.8	1064.3	1064.5	1064.7	1064.9	1065.2
142.5°	1090.9	1091.4	1091.9	1092.1	1092.2	1092.2	1092.3	1092.3
145°	1131.5	1131.7	1131.9	1132.3	1132.7	1133.1	1133.6	1134.0
147.5°	1167.1	1167.3	1167.5	1167.7	1167.9	1168.1	1168.4	1168.6
150°	1189.9	1189.9	1189.9	1190.0	1190.3	1190.5	1190.7	1190.9
152.5°	1209.8	1210.2	1210.5	1210.6	1210.5	1210.4	1210.2	1210.1
155°	1236.6	1237.5	1238.4	1238.5	1237.9	1237.2	1236.5	1235.9
157.5°	1259.7	1260.9	1262.0	1262.0	1260.9	1259.7	1258.6	1257.4
160°	1274.5	1275.8	1277.1	1277.1	1275.8	1274.5	1273.1	1271.8
162.5°	1286.4	1287.8	1289.1	1289.0	1287.5	1286.0	1284.5	1283.0
165°	1303.3	1305.1	1306.8	1306.7	1304.7	1302.7	1300.7	1298.7
167.5°	1315.6	1317.6	1319.5	1319.4	1317.2	1315.0	1312.7	1310.5
170°	1323.3	1325.0	1326.8	1326.6	1324.4	1322.2	1319.9	1317.7
172.5°	1328.1	1329.8	1331.6	1331.3	1328.9	1326.5	1324.1	1321.7
175°	1333.7	1335.7	1337.7	1337.3	1334.7	1332.0	1329.4	1326.7
177.5°	1335.9	1337.3	1338.8	1338.4	1336.3	1334.2	1332.0	1329.9
180°	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7	1334.7

(END OF REPORT)