

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832469

Luminaire Tested: S123RDP-S560D840-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832469
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S560D840-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 2445.4 lumens
 Efficiency: N/A
 Efficacy: 124.8 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct

Input Watts (W): 19.6
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832469
CATALOG NUMBER: S123RDP-S560D840-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832469

CATALOG NUMBER: S123RDP-S560D840-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59				
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53				
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47				
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43				
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39				
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	19853	19853	19853	19853	19853
5°	23573	22821	19977	16149	14993
10°	21357	23180	19878	12939	11100
15°	14705	19875	19668	10575	8781
20°	10230	15301	19274	8917	7718
25°	7796	11662	18699	7926	7113
30°	6786	9324	17980	7359	6589
35°	6230	7864	16962	6882	6112
40°	5685	7024	15631	6413	5674
45°	5135	6424	14193	5969	5238
50°	4660	5926	12499	5534	4699
55°	4215	5442	10871	5108	4031
60°	3776	4949	9442	4639	3810
65°	3487	4391	8127	4169	3601
70°	2832	3795	7091	3773	2927
75°	2483	3019	6005	3127	2578
80°	2250	2554	4922	2622	2436
85°	2050	2235	3730	2384	2235

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 14976 cd/sqm

TEST NUMBER: P832469

CATALOG NUMBER: S123RDP-S560D840-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.1	6.9
10°-20°	389.0	15.9
20°-30°	446.3	18.3
30°-40°	439.9	18.0
40°-50°	388.0	15.9
50°-60°	298.5	12.2
60°-70°	196.2	8.0
70°-80°	95.3	3.9
80°-90°	24.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1003.5	41.0
0°-40°	1443.4	59.0
0°-60°	2129.8	87.1
0°-90°	2445.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2445.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1844	1844	1844	1844	1844	
5°	2182	2112	1849	1495	1388	199
15°	1320	1784	1765	949	788	372
25°	656	982	1574	667	599	310
35°	474	598	1291	524	465	296
45°	337	422	932	392	344	262
55°	225	290	579	272	215	201
65°	137	172	319	164	141	134
75°	60	73	144	75	62	64
85°	17	18	30	19	18	19
90°	0	0	0	0	0	

TEST NUMBER: P832469

CATALOG NUMBER: S123RDP-S560D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4
2.5°	2044.0	2037.6	2031.2	2029.3	2027.4	2021.3	2015.3	2001.7	1988.1	1974.1	1960.1
5°	2181.7	2182.4	2183.2	2181.3	2179.4	2171.4	2163.5	2146.9	2130.2	2112.1	2093.9
7.5°	2139.3	2151.4	2163.5	2165.8	2168.0	2174.1	2180.1	2176.4	2172.6	2165.8	2159.0
10°	1954.0	1953.3	1952.5	1966.1	1979.7	2020.2	2060.7	2081.5	2102.2	2120.8	2139.3
12.5°	1651.6	1652.7	1653.8	1698.4	1743.1	1781.2	1819.4	1872.4	1925.3	1982.4	2039.5
15°	1319.6	1338.1	1356.6	1396.3	1436.0	1493.5	1551.0	1622.1	1693.1	1783.5	1873.9
17.5°	1083.6	1091.6	1099.5	1137.7	1175.9	1230.3	1284.8	1365.3	1445.9	1562.3	1678.8
20°	893.1	900.3	907.4	935.0	962.6	1014.8	1067.0	1143.8	1220.5	1335.8	1451.2
22.5°	745.6	759.6	773.6	792.1	810.7	848.5	886.3	964.5	1042.8	1147.9	1253.0
25°	656.4	662.8	669.2	685.1	701.0	737.3	773.6	825.4	877.2	981.9	1086.7
27.5°	595.9	597.8	599.7	611.4	623.1	646.6	670.0	718.0	766.0	852.2	938.5
30°	546.0	549.4	552.8	561.9	570.9	587.9	605.0	639.0	673.0	750.2	827.3
32.5°	507.4	509.3	511.2	518.8	526.3	538.8	551.3	578.1	605.0	663.9	722.9
35°	474.1	474.5	474.9	480.6	486.2	498.3	510.4	532.7	555.1	598.5	642.0
37.5°	436.3	439.0	441.6	445.8	449.9	460.5	471.1	489.3	507.4	543.3	579.3
40°	404.6	406.8	409.1	414.0	418.9	427.3	435.6	452.2	468.8	499.9	530.9
42.5°	372.8	374.3	375.8	380.7	385.7	395.9	406.1	419.3	432.5	458.3	484.0
45°	337.3	341.0	344.8	350.1	355.4	364.1	372.8	386.4	400.0	422.0	443.9
47.5°	307.8	309.7	311.6	316.1	320.6	331.2	341.8	353.9	366.0	386.4	406.8
50°	278.3	279.0	279.8	284.0	288.1	297.6	307.0	321.0	335.0	353.9	372.8
52.5°	250.3	252.2	254.1	258.2	262.4	268.8	275.3	289.6	304.0	322.5	341.0
55°	224.6	225.7	226.9	229.9	232.9	240.5	248.0	260.5	273.0	290.0	307.0
57.5°	200.4	201.9	203.4	205.7	208.0	214.8	221.6	232.5	243.5	260.5	277.5
60°	175.4	177.3	179.2	181.9	184.5	189.8	195.1	204.9	214.8	229.9	245.0
62.5°	157.3	157.7	158.0	160.3	162.6	166.4	170.1	178.1	186.0	201.2	216.3
65°	136.9	138.0	139.1	140.3	141.4	144.4	147.5	154.3	161.1	172.4	183.8
67.5°	115.7	116.8	118.0	119.9	121.7	124.4	127.0	131.6	136.1	146.7	157.3
70°	90.0	90.0	90.0	93.0	96.0	100.6	105.1	108.5	111.9	120.6	129.3
72.5°	73.4	73.7	74.1	74.5	74.9	77.5	80.2	85.8	91.5	96.8	102.1
75°	59.7	60.1	60.5	60.9	61.3	62.0	62.8	64.7	66.5	72.6	78.6
77.5°	47.6	48.0	48.4	48.8	49.2	49.9	50.7	51.4	52.2	54.4	56.7
80°	36.3	36.7	37.1	37.4	37.8	38.2	38.6	39.3	40.1	41.2	42.3
82.5°	26.5	26.5	26.5	26.5	26.5	27.2	28.0	28.0	28.0	28.7	29.5
85°	16.6	16.6	16.6	17.0	17.4	17.4	17.4	17.8	18.1	18.1	18.1
87.5°	7.6	7.2	6.8	7.2	7.6	7.6	7.6	7.9	8.3	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832469

CATALOG NUMBER: S123RDP-S560D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4
2.5°	1958.2	1956.3	1938.2	1920.0	1902.2	1884.5	1871.2	1858.0	1835.7	1813.4	1799.4
5°	2079.6	2065.2	2036.5	2007.7	1964.6	1921.5	1885.2	1848.9	1802.8	1756.7	1718.1
7.5°	2147.2	2135.5	2100.7	2066.0	2008.9	1951.8	1895.0	1838.3	1770.3	1702.2	1644.0
10°	2149.1	2159.0	2130.2	2101.5	2037.2	1972.9	1895.8	1818.7	1727.2	1635.7	1560.4
12.5°	2081.8	2124.2	2118.1	2112.1	2046.7	1981.3	1887.5	1793.7	1681.4	1569.1	1475.0
15°	1955.9	2038.0	2062.2	2086.4	2032.3	1978.2	1871.6	1765.0	1633.0	1501.1	1392.9
17.5°	1793.7	1908.7	1972.6	2036.5	1997.1	1957.8	1841.0	1724.1	1575.6	1427.0	1309.4
20°	1601.6	1752.1	1852.3	1952.5	1938.2	1923.8	1803.2	1682.6	1522.2	1361.9	1234.5
22.5°	1411.8	1570.6	1709.0	1847.4	1862.2	1876.9	1755.2	1633.4	1458.0	1282.5	1152.8
25°	1248.1	1409.6	1574.4	1739.3	1772.5	1805.8	1690.1	1574.4	1392.6	1210.7	1081.8
27.5°	1092.0	1245.5	1427.0	1608.4	1668.9	1729.4	1623.6	1517.7	1328.3	1138.8	1010.3
30°	964.5	1101.8	1287.1	1472.3	1556.6	1641.0	1543.8	1446.6	1258.7	1070.8	944.9
32.5°	845.8	968.7	1154.7	1340.8	1438.7	1536.6	1452.7	1368.7	1188.0	1007.3	882.9
35°	752.0	862.1	1035.6	1209.2	1318.8	1428.5	1359.7	1290.8	1114.3	937.7	820.1
37.5°	671.5	763.8	926.7	1089.7	1206.1	1322.6	1265.1	1207.7	1041.7	875.7	764.5
40°	605.0	679.1	830.7	982.3	1096.5	1210.7	1161.5	1112.4	963.8	815.2	711.2
42.5°	547.9	611.8	747.9	884.0	988.7	1093.5	1061.0	1028.4	893.8	759.2	662.8
45°	497.6	551.3	671.1	791.0	887.4	983.8	958.1	932.4	816.3	700.2	611.8
47.5°	453.0	499.1	606.1	713.1	799.7	886.3	862.5	838.6	742.6	646.6	566.0
50°	412.1	451.5	540.7	629.9	707.8	785.7	766.0	746.4	667.0	587.6	518.0
52.5°	373.6	406.1	486.2	566.4	629.2	691.9	676.8	661.7	600.4	539.2	476.0
55°	336.9	366.8	434.4	502.1	555.8	609.5	594.4	579.3	531.6	484.0	428.4
57.5°	303.6	329.7	384.5	439.4	482.1	524.8	517.6	510.4	470.7	431.0	385.3
60°	268.5	291.9	339.2	386.4	420.8	455.2	446.9	438.6	410.2	381.9	342.6
62.5°	237.1	257.9	295.7	333.5	361.5	389.4	383.4	377.3	355.8	334.2	301.7
65°	204.2	224.6	255.2	285.8	307.8	329.7	324.4	319.1	302.9	286.6	260.5
67.5°	174.3	191.3	217.8	244.3	259.0	273.7	270.7	267.7	255.2	242.7	222.3
70°	144.1	158.8	180.7	202.7	212.9	223.1	224.2	225.3	214.0	202.7	187.5
72.5°	113.8	125.5	145.9	166.4	174.3	182.2	181.9	181.5	174.7	167.9	154.3
75°	87.3	96.0	111.9	127.8	134.6	141.4	142.9	144.4	138.0	131.6	124.0
77.5°	62.8	68.8	80.9	93.0	100.6	108.1	108.9	109.6	106.6	103.6	96.4
80°	44.2	46.1	53.7	61.3	69.2	77.1	78.3	79.4	76.4	73.4	68.8
82.5°	30.6	31.8	34.4	37.1	43.5	49.9	51.4	52.9	51.4	49.9	45.0
85°	18.5	18.9	20.0	21.2	24.2	27.2	28.7	30.2	29.5	28.7	26.1
87.5°	8.3	8.3	8.7	9.1	9.8	10.6	12.5	14.4	13.2	12.1	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832469

CATALOG NUMBER: S123RDP-S560D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4	1844.4
2.5°	1785.4	1763.8	1742.3	1726.8	1711.3	1692.0	1672.7	1672.0	1671.2	1656.8	1642.5
5°	1679.5	1642.1	1604.7	1568.0	1531.3	1494.6	1458.0	1449.6	1441.3	1428.8	1416.4
7.5°	1585.8	1526.0	1466.3	1419.4	1372.5	1335.8	1299.2	1274.2	1249.3	1230.0	1210.7
10°	1485.2	1411.1	1337.0	1280.3	1223.5	1183.8	1144.1	1115.4	1086.7	1073.1	1059.4
12.5°	1380.8	1300.3	1219.8	1164.2	1108.6	1061.0	1013.3	987.2	961.1	942.2	923.3
15°	1284.8	1198.2	1111.6	1052.6	993.7	949.0	904.4	878.3	852.2	833.3	814.4
17.5°	1191.8	1104.4	1017.1	957.4	897.6	857.2	816.7	791.4	766.0	754.3	742.6
20°	1107.1	1019.0	930.9	874.6	818.2	778.5	738.8	725.2	711.6	700.6	689.7
22.5°	1023.1	938.5	853.8	799.7	745.6	716.9	688.1	677.2	666.2	657.9	649.6
25°	952.8	868.5	784.2	736.9	689.7	667.4	645.0	637.9	630.7	622.4	614.0
27.5°	881.7	801.6	721.4	683.6	645.8	627.7	609.5	600.4	591.4	584.5	577.7
30°	819.0	744.9	670.8	639.4	608.0	592.1	576.2	566.4	556.6	550.1	543.7
32.5°	758.5	692.7	626.9	600.0	573.2	557.7	542.2	532.7	523.3	515.7	508.2
35°	702.5	645.4	588.3	563.8	539.2	523.7	508.2	498.7	489.3	481.7	474.1
37.5°	653.4	601.6	549.8	526.7	503.6	490.0	476.4	466.6	456.7	448.8	440.9
40°	607.2	561.5	515.7	493.4	471.1	456.4	441.6	432.9	424.2	417.0	409.9
42.5°	566.4	524.4	482.5	460.5	438.6	424.6	410.6	400.4	390.2	386.0	381.9
45°	523.3	486.2	449.2	428.0	406.8	392.1	377.3	368.6	360.0	356.2	352.4
47.5°	485.5	451.1	416.7	395.9	375.1	361.8	348.6	341.8	335.0	329.7	324.4
50°	448.4	415.2	381.9	361.8	341.8	330.5	319.1	310.8	302.5	298.7	294.9
52.5°	412.9	382.6	352.4	332.0	311.6	300.6	289.6	282.4	275.3	267.3	259.4
55°	372.8	346.3	319.9	301.7	283.6	272.2	260.9	252.6	244.3	235.9	227.6
57.5°	339.5	313.4	287.4	271.1	254.8	243.9	232.9	223.8	214.8	208.0	201.2
60°	303.2	280.6	257.9	242.0	226.1	215.5	204.9	196.2	187.5	184.1	180.7
62.5°	269.2	248.0	226.9	212.9	198.9	188.7	178.5	172.8	167.1	164.9	162.6
65°	234.4	216.3	198.1	185.3	172.4	163.7	155.0	152.4	149.7	147.8	145.9
67.5°	201.9	186.4	170.9	159.6	148.2	142.2	136.1	133.1	130.1	127.8	125.5
70°	172.4	158.8	145.2	135.4	125.5	119.9	114.2	111.5	108.9	104.7	100.6
72.5°	140.7	130.1	119.5	111.9	104.4	99.4	94.5	89.2	83.9	80.2	76.4
75°	116.5	105.9	95.3	88.1	80.9	75.2	69.6	67.7	65.8	64.7	63.5
77.5°	89.2	80.2	71.1	65.4	59.7	57.1	54.4	53.3	52.2	51.8	51.4
80°	64.3	56.7	49.2	46.1	43.1	42.3	41.6	40.8	40.1	39.7	39.3
82.5°	40.1	36.3	32.5	31.8	31.0	30.6	30.2	29.9	29.5	29.1	28.7
85°	23.4	21.9	20.4	20.0	19.7	19.3	18.9	18.9	18.9	18.9	18.9
87.5°	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.5	9.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832469

CATALOG NUMBER: S123RDP-S560D840-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1844.4	1844.4	1844.4	1844.4
2.5°	1638.7	1634.9	1633.4	1631.9
5°	1404.7	1392.9	1390.3	1387.6
7.5°	1205.8	1200.9	1184.6	1168.3
10°	1044.3	1029.2	1022.4	1015.6
12.5°	909.3	895.3	893.1	890.8
15°	804.6	794.8	791.4	788.0
17.5°	735.8	729.0	724.8	720.7
20°	684.7	679.8	676.8	673.8
22.5°	645.8	642.0	639.7	637.5
25°	608.4	602.7	600.8	598.9
27.5°	572.8	567.9	566.0	564.1
30°	539.6	535.4	532.7	530.1
32.5°	503.3	498.3	496.8	495.3
35°	471.1	468.1	466.6	465.1
37.5°	437.1	433.3	431.0	428.8
40°	408.0	406.1	404.9	403.8
42.5°	378.5	375.1	374.7	374.3
45°	349.0	345.6	344.8	344.1
47.5°	321.4	318.4	318.0	317.6
50°	290.8	286.6	283.6	280.6
52.5°	255.6	251.8	249.2	246.5
55°	223.5	219.3	217.0	214.8
57.5°	199.3	197.4	196.2	195.1
60°	179.6	178.5	177.7	177.0
62.5°	161.4	160.3	160.3	160.3
65°	144.8	143.7	142.5	141.4
67.5°	123.3	121.0	120.6	120.2
70°	97.2	93.8	93.4	93.0
72.5°	76.0	75.6	74.9	74.1
75°	62.8	62.0	62.0	62.0
77.5°	50.7	49.9	49.9	49.9
80°	38.9	38.6	38.9	39.3
82.5°	28.7	28.7	28.4	28.0
85°	18.5	18.1	18.1	18.1
87.5°	9.1	9.1	9.1	9.1
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832469

CATALOG NUMBER: S123RDP-S560D840-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.09	16.54	15.45	16.86	17.17	19.75	21.21	20.12	21.52	21.84
	3H	16.35	17.65	16.73	17.98	18.35	21.29	22.60	21.67	22.92	23.29
	4H	16.76	17.98	17.16	18.33	18.71	21.81	23.03	22.21	23.38	23.76
	6H	17.07	18.20	17.48	18.56	18.96	22.15	23.28	22.56	23.64	24.04
	8H	17.17	18.24	17.60	18.63	19.04	22.25	23.32	22.67	23.71	24.11
	12H	17.24	18.27	17.67	18.65	19.08	22.30	23.32	22.73	23.70	24.13
4H	2H	15.88	17.10	16.28	17.45	17.83	19.82	21.04	20.22	21.39	21.77
	3H	17.30	18.31	17.71	18.71	19.11	21.52	22.53	21.94	22.94	23.34
	4H	17.78	18.68	18.21	19.10	19.54	22.15	23.06	22.59	23.48	23.92
	6H	18.18	18.96	18.63	19.41	19.87	22.62	23.41	23.08	23.85	24.31
	8H	18.31	19.05	18.78	19.49	19.96	22.76	23.50	23.23	23.94	24.41
	12H	18.41	19.07	18.90	19.55	20.02	22.85	23.51	23.33	23.99	24.46
8H	4H	18.13	18.87	18.60	19.31	19.78	22.16	22.90	22.63	23.34	23.81
	6H	18.62	19.22	19.11	19.71	20.19	22.68	23.28	23.18	23.77	24.25
	8H	18.81	19.35	19.33	19.86	20.35	22.86	23.41	23.38	23.92	24.41
	12H	18.97	19.45	19.49	19.95	20.51	23.01	23.48	23.52	23.98	24.54
12H	4H	18.17	18.82	18.65	19.30	19.78	22.14	22.79	22.62	23.27	23.74
	6H	18.67	19.22	19.19	19.73	20.22	22.65	23.19	23.17	23.71	24.20
	8H	18.92	19.40	19.43	19.89	20.46	22.87	23.35	23.38	23.84	24.41