

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831754

Luminaire Tested: S123DP-S560D940-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831754
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, -)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DP-S560D940-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2313.8 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831754

CATALOG NUMBER: S123DP-S560D940-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831754

CATALOG NUMBER: S123DP-S560D940-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88				86	
2	101	94	88	82	99	92	86	81	88	84	80	85	81	78	82	79	76				74	
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66				64	
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	62	58				56	
5	80	68	60	54	78	67	59	54	65	58	53	63	57	52	61	56	52				50	
6	74	62	54	48	73	61	53	48	60	53	47	58	52	47	56	51	47				45	
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42				40	
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	39				37	
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35				34	
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33				31	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	15493	15493	15493	15493	15493
5°	19594	18493	15632	12597	11575
10°	19783	20382	15527	10041	8775
15°	14900	18923	15422	8504	7421
20°	10381	15313	15224	7436	6740
25°	7917	11776	14890	6842	6322
30°	6848	9355	14353	6421	5986
35°	6355	7899	13736	6117	5749
40°	6015	7086	12867	5828	5668
45°	5815	6558	11764	5602	5632
50°	5715	6141	10458	5397	5603
55°	5502	5834	9175	5202	5628
60°	5307	5507	7907	5018	5535
65°	4984	5196	6821	4824	5428
70°	4604	4803	5800	4497	5108
75°	4167	4304	4974	4180	4666
80°	3434	3769	3936	3645	3936
85°	2717	3051	2890	3088	3137

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 13431 cd/sqm



TEST NUMBER: P831754

CATALOG NUMBER: S123DP-S560D940-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.1	5.9
10°-20°	338.5	14.6
20°-30°	400.8	17.3
30°-40°	403.0	17.4
40°-50°	369.8	16.0
50°-60°	305.2	13.2
60°-70°	215.9	9.3
70°-80°	115.2	5.0
80°-90°	29.2	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	875.4	37.8
0°-40°	1278.4	55.3
0°-60°	1953.4	84.4
0°-90°	2313.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2313.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1439	1439	1439	1439	1439	
5°	1813	1712	1447	1166	1071	173
15°	1337	1698	1384	763	666	369
25°	667	992	1254	576	532	315
35°	484	601	1045	466	438	304
45°	382	431	773	368	370	296
55°	293	311	489	277	300	262
65°	196	204	268	189	213	194
75°	100	104	120	100	112	105
85°	22	25	23	25	25	26
90°	0	0	0	0	0	



TEST NUMBER: P831754

CATALOG NUMBER: S123DP-S560D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1622.3	1620.7	1619.0	1610.6	1602.3	1598.3	1594.3	1582.3	1570.2	1556.9	1543.5
5°	1813.4	1818.0	1822.7	1817.4	1812.0	1795.7	1779.3	1757.6	1735.9	1711.5	1687.1
7.5°	1901.5	1904.2	1906.9	1903.5	1900.2	1895.8	1891.5	1872.1	1852.8	1827.7	1802.7
10°	1810.0	1816.0	1822.0	1835.1	1848.1	1862.8	1877.5	1874.8	1872.1	1864.8	1857.4
12.5°	1609.0	1616.3	1623.7	1649.7	1675.8	1709.2	1742.6	1771.3	1800.0	1820.0	1840.1
15°	1337.1	1357.5	1377.9	1401.6	1425.3	1474.4	1523.5	1583.9	1644.4	1698.1	1751.9
17.5°	1101.4	1109.1	1116.7	1142.1	1167.5	1229.3	1291.1	1360.8	1430.6	1519.8	1609.0
20°	906.3	913.4	920.4	953.8	987.2	1035.6	1084.0	1162.5	1241.0	1336.8	1432.6
22.5°	761.4	772.4	783.4	802.1	820.9	867.3	913.7	983.5	1053.3	1159.1	1265.0
25°	666.6	674.6	682.6	693.9	705.3	742.4	779.4	836.9	894.3	991.5	1088.7
27.5°	601.8	605.1	608.5	619.8	631.2	655.2	679.3	728.7	778.1	860.6	943.1
30°	551.0	553.4	555.7	565.7	575.7	592.1	608.5	644.2	679.9	752.7	825.5
32.5°	515.6	517.3	519.0	526.6	534.3	546.0	557.7	583.7	609.8	669.9	730.0
35°	483.6	484.6	485.6	491.2	496.9	505.6	514.3	534.0	553.7	601.1	648.5
37.5°	455.5	456.8	458.2	461.5	464.9	472.5	480.2	495.9	511.6	548.0	584.4
40°	428.1	430.5	432.8	435.1	437.5	443.8	450.2	462.2	474.2	504.3	534.3
42.5°	404.7	407.1	409.4	410.4	411.4	415.1	418.8	429.8	440.8	463.2	485.6
45°	382.0	383.0	384.0	385.0	386.0	389.1	392.1	401.7	411.4	430.8	450.2
47.5°	361.3	361.3	361.3	362.0	362.7	365.3	368.0	375.0	382.0	397.1	412.1
50°	341.3	341.3	341.3	340.3	339.3	341.0	342.6	348.0	353.3	366.7	380.0
52.5°	317.3	317.3	317.3	317.6	317.9	317.9	317.9	322.6	327.3	339.3	351.3
55°	293.2	294.5	295.9	294.9	293.9	294.5	295.2	298.2	301.2	310.9	320.6
57.5°	269.2	269.8	270.5	270.2	269.8	270.2	270.5	273.2	275.8	283.2	290.5
60°	246.5	246.5	246.5	245.8	245.1	245.8	246.5	247.8	249.1	255.8	262.5
62.5°	221.1	221.4	221.7	222.1	222.4	221.7	221.1	222.7	224.4	229.4	234.4
65°	195.7	196.0	196.4	197.4	198.4	197.7	197.0	198.7	200.4	204.0	207.7
67.5°	173.0	172.3	171.7	172.0	172.3	173.3	174.3	174.7	175.0	179.0	183.0
70°	146.3	146.9	147.6	147.3	146.9	147.3	147.6	148.6	149.6	152.6	155.6
72.5°	122.2	122.6	122.9	122.9	122.9	123.6	124.2	125.2	126.2	127.9	129.6
75°	100.2	100.2	100.2	100.9	101.5	101.9	102.2	102.2	102.2	103.5	104.9
77.5°	76.1	77.8	79.5	79.1	78.8	79.5	80.1	81.2	82.2	82.8	83.5
80°	55.4	55.4	55.4	55.8	56.1	57.1	58.1	58.8	59.4	60.8	62.1
82.5°	35.4	35.7	36.1	37.1	38.1	38.7	39.4	40.4	41.4	41.4	41.4
85°	22.0	21.4	20.7	21.4	22.0	22.7	23.4	23.7	24.0	24.7	25.4
87.5°	10.7	10.7	10.7	10.7	10.7	11.0	11.4	11.4	11.4	11.4	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P831754

CATALOG NUMBER: S123DP-S560D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1539.5	1535.5	1520.8	1506.1	1489.4	1472.7	1460.4	1448.0	1429.6	1411.3	1396.2
5°	1668.4	1649.7	1618.7	1587.6	1545.5	1503.4	1475.1	1446.7	1408.6	1370.5	1340.1
7.5°	1770.6	1738.5	1695.1	1651.7	1596.6	1541.5	1489.4	1437.3	1379.2	1321.1	1273.7
10°	1835.7	1814.0	1763.9	1713.8	1640.0	1566.2	1493.4	1420.6	1345.8	1271.0	1208.2
12.5°	1842.1	1844.1	1798.0	1751.9	1668.4	1584.9	1496.4	1407.9	1313.8	1219.6	1146.5
15°	1786.3	1820.7	1795.3	1769.9	1685.8	1601.6	1492.8	1383.9	1275.4	1166.8	1082.3
17.5°	1682.8	1756.6	1760.3	1763.9	1679.8	1595.6	1475.1	1354.5	1231.6	1108.7	1019.9
20°	1541.5	1650.4	1687.8	1725.2	1656.7	1588.3	1458.7	1329.1	1191.5	1053.9	960.8
22.5°	1397.3	1529.5	1598.0	1666.4	1615.7	1564.9	1427.0	1289.1	1143.8	998.5	904.0
25°	1232.9	1377.2	1482.4	1587.6	1556.5	1525.5	1389.6	1253.7	1099.0	944.4	847.9
27.5°	1089.7	1236.3	1363.2	1490.1	1483.4	1476.7	1341.8	1206.9	1048.6	890.3	797.1
30°	962.1	1098.7	1240.6	1382.6	1398.9	1415.3	1285.0	1154.8	996.2	837.5	747.7
32.5°	849.2	968.5	1120.7	1273.0	1305.1	1337.1	1219.6	1102.0	945.1	788.1	701.6
35°	756.7	864.9	1017.2	1169.5	1209.6	1249.6	1147.5	1045.3	892.3	739.4	656.9
37.5°	674.9	765.4	914.0	1062.6	1111.7	1160.8	1069.3	977.8	834.5	691.3	615.5
40°	607.1	679.9	816.5	953.1	1009.9	1066.6	991.2	915.7	779.8	643.9	574.1
42.5°	550.4	615.1	739.0	862.9	917.4	971.8	908.0	844.2	723.3	602.4	538.7
45°	501.9	553.7	666.2	778.8	830.5	882.3	827.5	772.8	666.2	559.7	500.3
47.5°	456.5	500.9	597.1	693.3	739.4	785.5	742.7	700.0	609.8	519.6	465.9
50°	415.8	451.5	535.7	619.8	659.9	700.0	662.2	624.5	550.4	476.2	429.5
52.5°	380.4	409.4	479.9	550.4	584.7	619.1	586.8	554.4	495.6	436.8	396.1
55°	345.3	370.0	431.1	492.2	515.6	539.0	514.0	488.9	441.5	394.1	359.7
57.5°	312.6	334.6	384.7	434.8	452.8	470.9	448.2	425.5	389.7	354.0	325.3
60°	280.5	298.6	340.3	382.0	393.1	404.1	385.7	367.3	342.3	317.3	291.5
62.5°	250.8	267.2	298.2	329.3	336.6	344.0	329.9	315.9	296.9	277.8	257.8
65°	220.1	232.4	257.8	283.2	287.9	292.5	280.2	267.8	253.5	239.1	224.4
67.5°	191.7	200.4	221.1	241.8	242.1	242.4	232.4	222.4	214.4	206.4	194.7
70°	164.0	172.3	186.0	199.7	200.0	200.4	192.4	184.3	178.3	172.3	163.6
72.5°	135.6	141.6	151.9	162.3	161.6	161.0	156.0	150.9	146.3	141.6	135.3
75°	109.9	114.9	121.9	128.9	126.9	124.9	122.2	119.6	115.5	111.5	107.5
77.5°	86.5	89.5	93.5	97.5	96.2	94.8	92.5	90.2	87.2	84.2	82.5
80°	63.5	64.8	67.5	70.1	69.5	68.8	66.1	63.5	62.8	62.1	59.8
82.5°	43.1	44.7	45.4	46.1	45.8	45.4	43.4	41.4	40.7	40.1	39.7
85°	25.7	26.0	26.4	26.7	25.7	24.7	24.0	23.4	23.4	23.4	23.0
87.5°	11.7	12.0	12.0	12.0	11.7	11.4	10.7	10.0	10.4	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P831754

CATALOG NUMBER: S123DP-S560D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1381.2	1368.2	1355.2	1345.2	1335.1	1318.1	1301.1	1297.1	1293.1	1287.4	1281.7
5°	1309.8	1277.7	1245.6	1216.9	1188.2	1165.8	1143.4	1128.8	1114.1	1103.4	1092.7
7.5°	1226.3	1178.2	1130.1	1096.0	1062.0	1029.6	997.2	986.8	976.5	962.4	948.4
10°	1145.5	1092.4	1039.3	994.8	950.4	918.7	887.0	874.3	861.6	843.9	826.2
12.5°	1073.3	1015.2	957.1	912.4	867.6	836.9	806.2	787.8	769.4	759.4	749.4
15°	997.8	935.7	873.6	832.2	790.8	763.1	735.4	719.3	703.3	693.6	683.9
17.5°	931.1	869.6	808.2	768.4	728.7	703.3	677.9	663.9	649.9	642.5	635.2
20°	867.6	807.5	747.4	708.6	669.9	649.2	628.5	619.5	610.5	604.5	598.4
22.5°	809.5	750.4	691.3	658.2	625.2	608.5	591.8	585.4	579.1	574.1	569.1
25°	751.4	698.6	645.9	617.8	589.8	576.1	562.4	556.0	549.7	544.7	539.7
27.5°	704.0	653.5	603.1	579.1	555.0	544.3	533.7	528.6	523.6	519.0	514.3
30°	657.9	612.8	567.7	547.0	526.3	516.6	506.9	501.9	496.9	492.6	488.2
32.5°	615.1	576.4	537.7	518.6	499.6	491.6	483.6	477.5	471.5	468.2	464.9
35°	574.4	539.7	504.9	489.2	473.5	465.5	457.5	452.5	447.5	444.8	442.2
37.5°	539.7	508.6	477.5	462.5	447.5	439.8	432.1	427.8	423.4	422.4	421.4
40°	504.3	477.5	450.8	436.1	421.4	414.8	408.1	405.4	402.7	402.1	401.4
42.5°	474.9	448.8	422.8	409.4	396.1	390.4	384.7	383.4	382.0	383.0	384.0
45°	440.8	419.1	397.4	385.0	372.7	368.0	363.3	362.3	361.3	363.3	365.3
47.5°	412.1	392.1	372.0	360.3	348.6	345.3	342.0	341.6	341.3	344.0	346.6
50°	382.7	363.3	344.0	334.6	325.3	322.3	319.3	320.3	321.3	325.6	329.9
52.5°	355.3	337.3	319.3	310.6	301.9	299.9	297.9	300.2	302.6	307.2	311.9
55°	325.3	308.9	292.5	285.9	279.2	277.2	275.2	279.9	284.5	288.9	293.2
57.5°	296.5	282.2	267.8	261.8	255.8	255.5	255.1	259.5	263.8	268.5	273.2
60°	265.8	253.8	241.8	237.1	232.4	233.1	233.8	238.8	243.8	247.5	251.1
62.5°	237.8	227.8	217.7	213.4	209.1	210.7	212.4	217.4	222.4	226.8	231.1
65°	209.7	201.4	193.0	190.0	187.0	189.4	191.7	196.0	200.4	203.4	206.4
67.5°	183.0	176.0	169.0	166.6	164.3	166.6	169.0	173.3	177.7	180.7	183.7
70°	155.0	149.3	143.6	141.9	140.3	142.9	145.6	149.3	152.9	156.0	159.0
72.5°	128.9	124.6	120.2	119.9	119.6	121.9	124.2	127.9	131.6	133.6	135.6
75°	103.5	101.2	98.8	98.5	98.2	100.5	102.9	104.9	106.9	108.5	110.2
77.5°	80.8	78.8	76.8	77.1	77.5	79.1	80.8	82.8	84.8	85.8	86.8
80°	57.4	56.8	56.1	56.8	57.4	58.8	60.1	61.4	62.8	63.5	64.1
82.5°	39.4	38.7	38.1	39.1	40.1	41.1	42.1	43.1	44.1	44.4	44.7
85°	22.7	23.7	24.7	24.7	24.7	25.0	25.4	25.7	26.0	25.7	25.4
87.5°	10.7	11.0	11.4	11.4	11.4	11.7	12.0	12.0	12.0	11.7	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P831754

CATALOG NUMBER: S123DP-S560D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1439.3	1439.3	1439.3	1439.3
2.5°	1279.4	1277.0	1267.7	1258.3
5°	1084.7	1076.7	1074.0	1071.3
7.5°	947.8	947.1	933.1	919.0
10°	827.2	828.2	815.5	802.8
12.5°	741.0	732.7	731.7	730.7
15°	676.3	668.6	667.2	665.9
17.5°	630.5	625.8	624.5	623.2
20°	595.8	593.1	590.8	588.4
22.5°	565.7	562.4	560.4	558.4
25°	536.7	533.7	533.0	532.3
27.5°	510.6	506.9	506.9	506.9
30°	485.9	483.6	482.6	481.6
32.5°	462.9	460.9	460.9	460.9
35°	441.1	440.1	438.8	437.5
37.5°	421.4	421.4	420.8	420.1
40°	402.4	403.4	403.4	403.4
42.5°	385.0	386.0	386.0	386.0
45°	367.0	368.7	369.3	370.0
47.5°	349.3	352.0	352.7	353.3
50°	331.9	334.0	334.3	334.6
52.5°	314.2	316.6	318.3	319.9
55°	295.5	297.9	298.9	299.9
57.5°	275.5	277.8	278.2	278.5
60°	253.5	255.8	256.5	257.1
62.5°	232.4	233.8	234.4	235.1
65°	208.4	210.4	211.7	213.1
67.5°	185.3	187.0	187.0	187.0
70°	159.6	160.3	161.3	162.3
72.5°	135.9	136.3	136.3	136.3
75°	110.9	111.5	111.9	112.2
77.5°	87.2	87.5	87.5	87.5
80°	63.8	63.5	63.5	63.5
82.5°	43.7	42.7	42.7	42.7
85°	25.0	24.7	25.0	25.4
87.5°	11.4	11.4	11.4	11.4
90°	0.0	0.0	0.0	0.0



TEST NUMBER: P831754

CATALOG NUMBER: S123DP-S560D940-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.00	18.51	17.37	18.82	19.14	19.24	20.75	19.60	21.06	21.38
	3H	18.69	20.05	19.07	20.38	20.74	20.71	22.06	21.08	22.39	22.75
	4H	19.30	20.57	19.70	20.92	21.30	21.18	22.46	21.58	22.80	23.18
	6H	19.70	20.87	20.11	21.24	21.63	21.49	22.67	21.90	23.03	23.42
	8H	19.81	20.93	20.24	21.32	21.72	21.57	22.69	22.00	23.08	23.48
	12H	19.88	20.95	20.31	21.33	21.76	21.61	22.68	22.04	23.06	23.49
4H	2H	17.65	18.92	18.05	19.27	19.65	19.47	20.75	19.87	21.09	21.47
	3H	19.53	20.59	19.94	20.99	21.39	21.14	22.20	21.55	22.60	23.00
	4H	20.25	21.20	20.68	21.62	22.06	21.75	22.70	22.18	23.12	23.56
	6H	20.76	21.59	21.22	22.03	22.49	22.19	23.02	22.65	23.46	23.92
	8H	20.91	21.68	21.37	22.13	22.59	22.31	23.09	22.78	23.53	24.00
	12H	21.00	21.70	21.49	22.17	22.65	22.39	23.08	22.87	23.56	24.03
8H	4H	20.56	21.34	21.03	21.78	22.25	21.90	22.68	22.37	23.12	23.59
	6H	21.17	21.81	21.67	22.31	22.78	22.43	23.07	22.92	23.56	24.04
	8H	21.38	21.96	21.90	22.47	22.96	22.61	23.18	23.12	23.69	24.18
	12H	21.54	22.04	22.05	22.53	23.10	22.74	23.25	23.25	23.74	24.30
12H	4H	20.59	21.28	21.07	21.76	22.23	21.91	22.60	22.39	23.08	23.55
	6H	21.23	21.80	21.74	22.31	22.80	22.44	23.02	22.96	23.53	24.02
	8H	21.49	22.00	22.00	22.49	23.05	22.67	23.18	23.18	23.67	24.24