

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832456

Luminaire Tested: S123RDP-S1165D940-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-2019  
 Report Number: P832456  
 Test Lab: INNOVATION CENTER  
 Issue Date: 05/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: NEO-RAY  
 Catalog Number: S123RDP-S1165D940-4F0-1E-UDD-G  
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE  
 DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -  
 Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 4430.9 lumens  
 Efficiency: N/A  
 Efficacy: 105.0 lumens/watt  
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
 CIE Type: Direct


Input Watts (W): 42.2  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832456

CATALOG NUMBER: S123RDP-S1165D940-4F0-1E-UDD-G

### Luminous Intensity Polar Plot



TEST NUMBER: P832456

CATALOG NUMBER: S123RDP-S1165D940-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			87	
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76			76	
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			67	
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59			59	
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53			53	
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47			47	
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43			43	
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39			39	
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36	
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33			33	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	35972	35972	35972	35972	35972
5°	42712	41351	36199	29262	27167
10°	38699	42001	36018	23446	20113
15°	26644	36012	35638	19163	15911
20°	18536	27726	34922	16158	13985
25°	14125	21131	33882	14361	12889
30°	12296	16894	32579	13335	11938
35°	11289	14251	30734	12469	11073
40°	10301	12726	28322	11619	10281
45°	9302	11639	25718	10816	9490
50°	8443	10739	22647	10027	8512
55°	7638	9862	19697	9257	7302
60°	6844	8966	17108	8407	6902
65°	6316	7957	14727	7554	6525
70°	5133	6877	12850	6836	5303
75°	4500	5469	10884	5669	4675
80°	4079	4630	8920	4754	4420
85°	3717	4063	6768	4310	4063

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 27136 cd/sqm

TEST NUMBER: P832456

CATALOG NUMBER: S123RDP-S1165D940-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	304.6	6.9
10°-20°	704.9	15.9
20°-30°	808.7	18.3
30°-40°	797.1	18.0
40°-50°	703.0	15.9
50°-60°	540.8	12.2
60°-70°	355.6	8.0
70°-80°	172.7	3.9
80°-90°	43.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1818.2	41.0
0°-40°	2615.4	59.0
0°-60°	3859.1	87.1
0°-90°	4430.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4430.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3342	3342	3342	3342	3342	
5°	3953	3827	3350	2708	2514	361
15°	2391	3232	3198	1720	1428	675
25°	1189	1779	2853	1209	1085	562
35°	859	1084	2339	949	843	536
45°	611	765	1690	710	623	474
55°	407	526	1050	493	389	365
65°	248	312	578	297	256	243
75°	108	132	262	136	112	116
85°	30	33	55	35	33	34
90°	0	0	0	0	0	

TEST NUMBER: P832456

CATALOG NUMBER: S123RDP-S1165D940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9
2.5°	3703.7	3692.0	3680.4	3676.9	3673.5	3662.6	3651.6	3626.9	3602.3	3576.9	3551.6
5°	3953.0	3954.4	3955.8	3952.4	3948.9	3934.5	3920.2	3890.0	3859.9	3827.0	3794.1
7.5°	3876.3	3898.2	3920.2	3924.3	3928.4	3939.3	3950.3	3943.5	3936.6	3924.3	3911.9
10°	3540.6	3539.2	3537.9	3562.5	3587.2	3660.5	3733.8	3771.5	3809.2	3842.7	3876.3
12.5°	2992.5	2994.6	2996.6	3077.5	3158.3	3227.5	3296.7	3392.6	3488.5	3592.0	3695.4
15°	2391.0	2424.6	2458.1	2530.1	2602.0	2706.2	2810.3	2939.1	3067.9	3231.6	3395.4
17.5°	1963.5	1977.9	1992.3	2061.5	2130.7	2229.3	2328.0	2473.9	2619.8	2830.8	3041.9
20°	1618.2	1631.2	1644.2	1694.3	1744.3	1838.8	1933.4	2072.4	2211.5	2420.5	2629.4
22.5°	1351.0	1376.4	1401.7	1435.3	1468.9	1537.4	1605.9	1747.7	1889.5	2080.0	2270.4
25°	1189.3	1201.0	1212.6	1241.4	1270.2	1336.0	1401.7	1495.6	1589.4	1779.2	1969.0
27.5°	1079.7	1083.1	1086.6	1107.8	1129.0	1171.5	1214.0	1301.0	1388.0	1544.2	1700.4
30°	989.3	995.5	1001.6	1018.1	1034.5	1065.3	1096.2	1157.8	1219.5	1359.2	1499.0
32.5°	919.4	922.8	926.3	940.0	953.7	976.3	998.9	1047.5	1096.2	1203.0	1309.9
35°	859.1	859.8	860.5	870.8	881.0	903.0	924.9	965.3	1005.7	1084.5	1163.3
37.5°	790.6	795.4	800.2	807.7	815.3	834.5	853.6	886.5	919.4	984.5	1049.6
40°	733.1	737.2	741.3	750.2	759.1	774.2	789.2	819.4	849.5	905.7	961.9
42.5°	675.5	678.3	681.0	689.9	698.8	717.3	735.8	759.8	783.8	830.3	876.9
45°	611.1	618.0	624.8	634.4	644.0	659.8	675.5	700.2	724.8	764.6	804.3
47.5°	557.7	561.1	564.5	572.7	581.0	600.2	619.3	641.3	663.2	700.2	737.2
50°	504.2	505.6	507.0	514.5	522.0	539.2	556.3	581.7	607.0	641.3	675.5
52.5°	453.5	457.0	460.4	467.9	475.5	487.1	498.8	524.8	550.8	584.4	618.0
55°	407.0	409.0	411.1	416.5	422.0	435.7	449.4	472.0	494.6	525.5	556.3
57.5°	363.1	365.8	368.6	372.7	376.8	389.1	401.5	421.3	441.2	472.0	502.9
60°	317.9	321.3	324.7	329.5	334.3	343.9	353.5	371.3	389.1	416.5	443.9
62.5°	285.0	285.7	286.4	290.5	294.6	301.4	308.3	322.7	337.1	364.5	391.9
65°	248.0	250.1	252.1	254.2	256.2	261.7	267.2	279.5	291.9	312.4	333.0
67.5°	209.6	211.7	213.8	217.2	220.6	225.4	230.2	238.4	246.6	265.8	285.0
70°	163.1	163.1	163.1	168.5	174.0	182.2	190.5	196.6	202.8	218.5	234.3
72.5°	132.9	133.6	134.3	135.0	135.7	140.4	145.2	155.5	165.8	175.4	185.0
75°	108.2	108.9	109.6	110.3	111.0	112.4	113.7	117.2	120.6	131.5	142.5
77.5°	86.3	87.0	87.7	88.4	89.1	90.4	91.8	93.2	94.5	98.7	102.8
80°	65.8	66.5	67.1	67.8	68.5	69.2	69.9	71.3	72.6	74.7	76.7
82.5°	48.0	48.0	48.0	48.0	48.0	49.3	50.7	50.7	50.7	52.1	53.4
85°	30.1	30.1	30.1	30.8	31.5	31.5	31.5	32.2	32.9	32.9	32.9
87.5°	13.7	13.0	12.3	13.0	13.7	13.7	13.7	14.4	15.1	15.1	15.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832456

CATALOG NUMBER: S123RDP-S1165D940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9
2.5°	3548.1	3544.7	3511.8	3479.0	3446.8	3414.6	3390.6	3366.6	3326.2	3285.8	3260.4
5°	3768.1	3742.0	3690.0	3637.9	3559.8	3481.7	3415.9	3350.2	3266.6	3183.0	3113.1
7.5°	3890.7	3869.5	3806.4	3743.4	3640.0	3536.5	3433.7	3331.0	3207.7	3084.3	2978.8
10°	3894.1	3911.9	3859.9	3807.8	3691.3	3574.9	3435.1	3295.3	3129.6	2963.8	2827.4
12.5°	3772.2	3848.9	3837.9	3827.0	3708.5	3589.9	3420.0	3250.1	3046.7	2843.2	2672.6
15°	3544.0	3692.7	3736.6	3780.4	3682.4	3584.5	3391.3	3198.1	2959.0	2719.9	2523.9
17.5°	3250.1	3458.4	3574.2	3690.0	3618.7	3547.5	3335.8	3124.1	2854.8	2585.6	2372.5
20°	2902.1	3174.8	3356.3	3537.9	3511.8	3485.8	3267.3	3048.7	2758.2	2467.7	2236.9
22.5°	2558.2	2845.9	3096.7	3347.4	3374.1	3400.9	3180.2	2959.6	2641.8	2323.9	2088.9
25°	2261.5	2554.1	2852.8	3151.5	3211.8	3272.1	3062.4	2852.8	2523.2	2193.7	1960.1
27.5°	1978.6	2256.7	2585.6	2914.4	3024.0	3133.7	2941.8	2750.0	2406.8	2063.5	1830.6
30°	1747.7	1996.4	2332.1	2667.8	2820.6	2973.3	2797.3	2621.2	2280.7	1940.2	1712.1
32.5°	1532.6	1755.2	2092.3	2429.4	2606.8	2784.3	2632.2	2480.1	2152.6	1825.1	1599.7
35°	1362.7	1562.0	1876.5	2191.0	2389.6	2588.3	2463.6	2338.9	2019.0	1699.1	1486.0
37.5°	1216.7	1383.9	1679.2	1974.5	2185.5	2396.5	2292.4	2188.2	1887.5	1586.7	1385.3
40°	1096.2	1230.4	1505.2	1779.9	1986.8	2193.7	2104.6	2015.6	1746.3	1477.1	1288.7
42.5°	992.7	1108.5	1355.1	1601.8	1791.5	1981.3	1922.4	1863.5	1619.6	1375.7	1201.0
45°	901.6	998.9	1216.1	1433.2	1607.9	1782.6	1736.1	1689.5	1479.1	1268.8	1108.5
47.5°	820.8	904.3	1098.2	1292.1	1449.0	1605.9	1562.7	1519.6	1345.5	1171.5	1025.6
50°	746.8	818.0	979.7	1141.4	1282.5	1423.6	1388.0	1352.4	1208.5	1064.7	938.6
52.5°	676.9	735.8	881.0	1026.3	1140.0	1253.7	1226.3	1198.9	1087.9	977.0	862.5
55°	610.4	664.5	787.2	909.8	1007.1	1104.4	1077.0	1049.6	963.3	876.9	776.2
57.5°	550.1	597.4	696.7	796.1	873.5	950.9	937.9	924.9	853.0	781.0	698.1
60°	486.4	528.9	614.5	700.2	762.5	824.9	809.8	794.7	743.3	692.0	620.7
62.5°	429.6	467.2	535.8	604.3	655.0	705.7	694.7	683.7	644.7	605.6	546.7
65°	370.0	407.0	462.4	517.9	557.7	597.4	587.8	578.2	548.8	519.3	472.0
67.5°	315.8	346.7	394.6	442.6	469.3	496.0	490.5	485.1	462.4	439.8	402.8
70°	261.0	287.7	327.5	367.2	385.7	404.2	406.3	408.3	387.8	367.2	339.8
72.5°	206.2	227.5	264.4	301.4	315.8	330.2	329.5	328.8	316.5	304.2	279.5
75°	158.3	174.0	202.8	231.6	243.9	256.2	259.0	261.7	250.1	238.4	224.7
77.5°	113.7	124.7	146.6	168.5	182.2	195.9	197.3	198.7	193.2	187.7	174.7
80°	80.2	83.6	97.3	111.0	125.4	139.8	141.8	143.9	138.4	132.9	124.7
82.5°	55.5	57.5	62.3	67.1	78.8	90.4	93.2	95.9	93.2	90.4	81.5
85°	33.6	34.3	36.3	38.4	43.8	49.3	52.1	54.8	53.4	52.1	47.3
87.5°	15.1	15.1	15.8	16.4	17.8	19.2	22.6	26.0	24.0	21.9	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832456

CATALOG NUMBER: S123RDP-S1165D940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9
2.5°	3235.1	3196.0	3157.0	3128.9	3100.8	3065.8	3030.9	3029.5	3028.2	3002.1	2976.1
5°	3043.2	2975.4	2907.6	2841.1	2774.7	2708.2	2641.8	2626.7	2611.6	2589.0	2566.4
7.5°	2873.3	2765.1	2656.8	2571.9	2486.9	2420.5	2354.0	2308.8	2263.6	2228.6	2193.7
10°	2691.1	2556.8	2422.5	2319.8	2217.0	2145.1	2073.1	2021.1	1969.0	1944.3	1919.7
12.5°	2502.0	2356.1	2210.1	2109.4	2008.7	1922.4	1836.1	1788.8	1741.5	1707.3	1673.0
15°	2328.0	2171.1	2014.2	1907.3	1800.5	1719.6	1638.8	1591.5	1544.2	1510.0	1475.7
17.5°	2159.4	2001.2	1842.9	1734.7	1626.4	1553.1	1479.8	1433.9	1388.0	1366.8	1345.5
20°	2006.0	1846.4	1686.7	1584.6	1482.6	1410.6	1338.7	1314.0	1289.4	1269.5	1249.6
22.5°	1853.9	1700.4	1547.0	1449.0	1351.0	1299.0	1246.9	1227.0	1207.2	1192.1	1177.0
25°	1726.5	1573.7	1420.9	1335.3	1249.6	1209.2	1168.8	1155.8	1142.8	1127.7	1112.6
27.5°	1597.7	1452.4	1307.2	1238.7	1170.2	1137.3	1104.4	1087.9	1071.5	1059.2	1046.8
30°	1483.9	1349.7	1215.4	1158.5	1101.6	1072.9	1044.1	1026.3	1008.5	996.8	985.2
32.5°	1374.3	1255.1	1135.9	1087.3	1038.6	1010.5	982.4	965.3	948.2	934.5	920.8
35°	1272.9	1169.5	1066.0	1021.5	977.0	948.9	920.8	903.7	886.5	872.8	859.1
37.5°	1183.9	1090.0	996.1	954.3	912.6	887.9	863.2	845.4	827.6	813.2	798.8
40°	1100.3	1017.4	934.5	894.1	853.6	826.9	800.2	784.4	768.7	755.7	742.7
42.5°	1026.3	950.2	874.2	834.5	794.7	769.4	744.0	725.5	707.0	699.5	692.0
45°	948.2	881.0	813.9	775.5	737.2	710.5	683.7	668.0	652.2	645.4	638.5
47.5°	879.7	817.3	755.0	717.3	679.6	655.6	631.7	619.3	607.0	597.4	587.8
50°	812.5	752.2	692.0	655.6	619.3	598.8	578.2	563.2	548.1	541.2	534.4
52.5°	748.1	693.3	638.5	601.5	564.5	544.7	524.8	511.8	498.8	484.4	470.0
55°	675.5	627.6	579.6	546.7	513.8	493.3	472.7	457.6	442.6	427.5	412.4
57.5°	615.2	568.0	520.7	491.2	461.8	441.9	422.0	405.6	389.1	376.8	364.5
60°	549.5	508.3	467.2	438.5	409.7	390.5	371.3	355.6	339.8	333.6	327.5
62.5°	487.8	449.4	411.1	385.7	360.4	341.9	323.4	313.1	302.8	298.7	294.6
65°	424.8	391.9	359.0	335.7	312.4	296.6	280.9	276.1	271.3	267.9	264.4
67.5°	365.8	337.8	309.7	289.1	268.6	257.6	246.6	241.2	235.7	231.6	227.5
70°	312.4	287.7	263.1	245.3	227.5	217.2	206.9	202.1	197.3	189.8	182.2
72.5°	254.9	235.7	216.5	202.8	189.1	180.2	171.3	161.7	152.1	145.2	138.4
75°	211.0	191.8	172.6	159.6	146.6	136.3	126.1	122.6	119.2	117.2	115.1
77.5°	161.7	145.2	128.8	118.5	108.2	103.5	98.7	96.6	94.5	93.9	93.2
80°	116.5	102.8	89.1	83.6	78.1	76.7	75.4	74.0	72.6	71.9	71.3
82.5°	72.6	65.8	58.9	57.5	56.2	55.5	54.8	54.1	53.4	52.8	52.1
85°	42.5	39.7	37.0	36.3	35.6	34.9	34.3	34.3	34.3	34.3	34.3
87.5°	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.1	16.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P832456

CATALOG NUMBER: S123RDP-S1165D940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	3341.9	3341.9	3341.9	3341.9
2.5°	2969.2	2962.4	2959.6	2956.9
5°	2545.2	2523.9	2519.1	2514.3
7.5°	2184.8	2175.9	2146.4	2117.0
10°	1892.3	1864.9	1852.5	1840.2
12.5°	1647.7	1622.3	1618.2	1614.1
15°	1457.9	1440.1	1433.9	1427.8
17.5°	1333.2	1320.9	1313.3	1305.8
20°	1240.7	1231.8	1226.3	1220.9
22.5°	1170.2	1163.3	1159.2	1155.1
25°	1102.3	1092.1	1088.6	1085.2
27.5°	1037.9	1029.0	1025.6	1022.2
30°	977.6	970.1	965.3	960.5
32.5°	911.9	903.0	900.2	897.5
35°	853.6	848.2	845.4	842.7
37.5°	792.0	785.1	781.0	776.9
40°	739.2	735.8	733.7	731.7
42.5°	685.8	679.6	678.9	678.3
45°	632.4	626.2	624.8	623.4
47.5°	582.3	576.9	576.2	575.5
50°	526.8	519.3	513.8	508.3
52.5°	463.1	456.3	451.5	446.7
55°	404.9	397.4	393.2	389.1
57.5°	361.0	357.6	355.6	353.5
60°	325.4	323.4	322.0	320.6
62.5°	292.5	290.5	290.5	290.5
65°	262.4	260.3	258.3	256.2
67.5°	223.3	219.2	218.5	217.9
70°	176.1	169.9	169.2	168.5
72.5°	137.7	137.0	135.7	134.3
75°	113.7	112.4	112.4	112.4
77.5°	91.8	90.4	90.4	90.4
80°	70.6	69.9	70.6	71.3
82.5°	52.1	52.1	51.4	50.7
85°	33.6	32.9	32.9	32.9
87.5°	16.4	16.4	16.4	16.4
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832456

CATALOG NUMBER: S123RDP-S1165D940-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.15	18.61	17.52	18.92	19.24	21.82	23.27	22.18	23.59	23.90
	3H	18.42	19.72	18.79	20.05	20.41	23.36	24.66	23.74	24.99	25.35
	4H	18.82	20.04	19.23	20.39	20.77	23.87	25.09	24.28	25.44	25.82
	6H	19.13	20.26	19.55	20.63	21.02	24.22	25.34	24.63	25.71	26.10
	8H	19.24	20.31	19.67	20.70	21.10	24.31	25.38	24.74	25.77	26.17
	12H	19.31	20.33	19.74	20.71	21.14	24.36	25.38	24.79	25.77	26.20
4H	2H	17.94	19.16	18.35	19.51	19.89	21.88	23.10	22.28	23.45	23.83
	3H	19.36	20.37	19.78	20.78	21.18	23.59	24.60	24.00	25.00	25.40
	4H	19.84	20.75	20.27	21.17	21.61	24.22	25.13	24.65	25.54	25.98
	6H	20.24	21.03	20.70	21.47	21.93	24.69	25.47	25.15	25.92	26.38
	8H	20.37	21.11	20.84	21.56	22.02	24.83	25.56	25.29	26.01	26.48
	12H	20.48	21.13	20.96	21.61	22.08	24.92	25.57	25.40	26.05	26.52
8H	4H	20.20	20.93	20.66	21.38	21.84	24.23	24.96	24.69	25.41	25.87
	6H	20.68	21.29	21.18	21.78	22.26	24.74	25.35	25.24	25.84	26.32
	8H	20.87	21.42	21.39	21.93	22.42	24.93	25.47	25.45	25.98	26.47
	12H	21.04	21.52	21.55	22.01	22.58	25.07	25.55	25.58	26.04	26.61
12H	4H	20.23	20.89	20.72	21.37	21.84	24.20	24.86	24.69	25.34	25.81
	6H	20.74	21.28	21.26	21.79	22.28	24.72	25.26	25.23	25.77	26.26
	8H	20.98	21.46	21.50	21.96	22.52	24.94	25.42	25.45	25.91	26.48