

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332881

Luminaire Tested: **S124RDIP-S350D810U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332881
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D810U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4235.8 lumens
Efficiency: N/A
Efficacy: 135.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332881

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332881

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	79	69	62	57	71	63	57	52	51	46	43	39	37	34	29	27	26	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	15	14	11
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4991	4991	4991
5°	5002	4941	4971
10°	4970	4882	4882
15°	4914	4779	4743
20°	4835	4643	4558
25°	4735	4486	4372
30°	4638	4320	4139
35°	4529	4147	3905
40°	4400	3951	3652
45°	4280	3756	3394
50°	4143	3532	3121
55°	3997	3298	2825
60°	3836	3042	2522
65°	3689	2722	2223
70°	3474	2367	1888
75°	3203	1965	1535
80°	2794	1497	1409
85°	2371	1362	1269



TEST NUMBER: P332881

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	1.4
10°-20°	161.9	3.8
20°-30°	233.8	5.5
30°-40°	265.1	6.3
40°-50°	255.9	6.0
50°-60°	212.8	5.0
60°-70°	147.0	3.5
70°-80°	74.5	1.8
80°-90°	22.1	0.5
90°-100°	66.7	1.6
100°-110°	197.5	4.7
110°-120°	335.2	7.9
120°-130°	442.0	10.4
130°-140°	496.4	11.7
140°-150°	487.8	11.5
150°-160°	410.3	9.7
160°-170°	273.0	6.4
170°-180°	95.6	2.3
0°-30°	453.8	10.7
0°-40°	718.9	17.0
0°-60°	1187.7	28.0
0°-90°	1431.3	33.8
90°-120°	599.4	14.2
90°-150°	2025.7	47.8
90°-180°	2805.0	66.2
0°-180°	4235.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	618	618	618	618	618	
5°	617	615	610	614	613	59
15°	588	583	572	571	568	166
25°	532	522	504	496	491	245
35°	460	444	421	405	396	287
45°	375	357	329	307	297	289
55°	284	264	234	211	201	254
65°	193	172	142	123	116	191
75°	103	85	63	53	49	108
85°	26	16	15	14	14	29
90°	2	11	17	22	24	4
95°	47	54	59	62	62	52
105°	182	183	186	188	191	193
115°	341	341	339	338	338	336
125°	496	496	496	494	492	442
135°	640	645	645	643	641	495
145°	778	781	782	781	779	487
155°	891	891	890	893	890	410
165°	970	968	966	971	968	273
175°	1009	1006	1005	1010	1005	96
180°	1011	1011	1011	1011	1011	



TEST NUMBER: P332881

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	619.7	619.3	619.0	618.7	618.3	617.7	616.8	615.9	614.9	614.0	614.9
5°	617.2	616.8	616.4	616.0	615.5	614.7	613.4	612.2	610.9	609.7	610.7
7.5°	611.6	611.2	610.8	610.3	609.9	608.8	607.2	605.5	603.9	602.3	602.9
10°	606.3	605.8	605.3	604.8	604.2	603.0	601.1	599.2	597.3	595.5	595.9
12.5°	599.5	598.9	598.3	597.7	597.1	595.7	593.4	591.2	589.0	586.7	587.0
15°	587.9	586.9	586.0	585.0	584.1	582.3	579.7	577.0	574.4	571.8	571.6
17.5°	573.8	572.4	571.0	569.7	568.3	566.0	562.9	559.7	556.6	553.4	552.8
20°	562.8	561.4	560.1	558.7	557.3	554.9	551.3	547.7	544.1	540.5	539.7
22.5°	550.7	549.1	547.6	546.1	544.5	541.8	538.0	534.2	530.4	526.5	525.3
25°	531.6	529.7	527.8	525.9	524.0	520.9	516.6	512.3	507.9	503.6	501.8
27.5°	511.5	509.1	506.7	504.4	502.0	498.5	493.9	489.3	484.7	480.1	477.8
30°	497.5	494.8	492.2	489.6	487.0	483.2	478.2	473.3	468.3	463.4	460.8
32.5°	482.7	479.7	476.8	473.8	470.8	466.8	461.7	456.6	451.5	446.4	443.3
35°	459.6	456.2	452.9	449.5	446.1	441.8	436.6	431.3	426.1	420.8	417.2
37.5°	434.9	431.4	428.0	424.5	421.0	416.4	410.5	404.7	398.9	393.1	389.1
40°	417.5	414.0	410.5	407.1	403.6	398.9	392.9	386.9	380.9	374.9	370.5
42.5°	400.8	397.2	393.5	389.9	386.3	381.3	375.1	368.8	362.6	356.3	351.8
45°	374.9	371.0	367.1	363.2	359.3	354.2	347.9	341.6	335.3	329.0	323.8
47.5°	348.1	344.1	340.1	336.0	332.0	326.7	320.2	313.6	307.0	300.5	295.1
50°	329.9	325.8	321.7	317.6	313.5	308.1	301.4	294.6	287.9	281.2	275.9
52.5°	311.4	307.3	303.3	299.3	295.3	289.8	282.9	276.0	269.1	262.2	256.9
55°	284.0	279.8	275.6	271.4	267.2	261.6	254.8	248.0	241.1	234.3	228.8
57.5°	256.9	252.5	248.2	243.8	239.4	233.9	227.1	220.4	213.7	206.9	201.4
60°	237.6	233.4	229.2	225.0	220.8	215.3	208.6	201.8	195.1	188.4	182.9
62.5°	220.2	215.8	211.4	207.1	202.7	197.1	190.2	183.3	176.4	169.5	164.4
65°	193.1	188.6	184.1	179.6	175.0	169.4	162.7	155.9	149.2	142.5	138.0
67.5°	165.0	160.7	156.3	152.0	147.7	142.4	136.1	129.9	123.6	117.4	113.5
70°	147.2	142.8	138.4	134.0	129.5	124.3	118.3	112.3	106.3	100.3	96.9
72.5°	128.3	124.3	120.3	116.3	112.3	107.5	101.8	96.1	90.5	84.8	81.9
75°	102.7	98.8	94.9	91.0	87.1	82.7	77.8	72.8	67.9	63.0	60.5
77.5°	76.8	73.5	70.2	66.9	63.6	59.9	55.9	51.9	47.9	43.9	42.5
80°	60.1	57.1	54.0	51.0	47.9	44.8	41.7	38.5	35.3	32.2	31.9
82.5°	45.7	42.9	40.1	37.3	34.5	32.2	30.4	28.6	26.8	25.0	24.8
85°	25.6	23.5	21.4	19.2	17.1	15.9	15.6	15.3	15.0	14.7	14.5
87.5°	9.2	8.9	8.6	8.3	8.0	8.0	8.2	8.4	8.5	8.7	8.9
90°	2.3	4.3	6.2	8.1	10.0	11.6	13.0	14.4	15.8	17.2	18.2
92.5°	16.7	18.9	21.1	23.3	25.5	27.1	28.0	29.0	30.0	31.0	31.6
95°	46.9	48.5	50.0	51.6	53.2	54.6	55.8	57.0	58.2	59.4	59.9
97.5°	81.9	83.2	84.4	85.7	86.9	88.3	89.7	91.1	92.5	94.0	94.6
100°	109.5	110.1	110.8	111.5	112.2	113.4	114.9	116.5	118.0	119.6	120.0
102.5°	138.2	138.5	138.8	139.1	139.3	140.2	141.6	143.0	144.5	145.9	146.4
105°	182.2	182.3	182.5	182.7	182.9	183.3	184.0	184.7	185.4	186.1	186.6
107.5°	228.3	228.5	228.7	228.9	229.1	229.3	229.4	229.5	229.6	229.7	230.2
110°	259.6	259.9	260.2	260.6	260.9	261.0	260.9	260.7	260.5	260.3	260.0



TEST NUMBER: P332881

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.1	292.1	292.2	292.3	292.4	292.2	291.9	291.6	291.3	291.0	290.9
115°	340.9	340.9	340.9	340.9	340.9	340.7	340.3	340.0	339.6	339.3	339.1
117.5°	386.8	387.0	387.1	387.2	387.4	387.3	387.1	386.8	386.6	386.4	385.8
120°	417.5	418.2	418.9	419.6	420.3	420.3	419.8	419.3	418.8	418.3	417.4
122.5°	449.4	449.6	449.9	450.2	450.5	450.5	450.3	450.0	449.8	449.5	448.9
125°	496.4	496.4	496.4	496.4	496.4	496.3	496.2	496.0	495.8	495.7	495.3
127.5°	539.1	539.6	540.2	540.7	541.2	541.3	541.0	540.8	540.5	540.2	539.9
130°	569.1	569.7	570.2	570.7	571.2	571.5	571.5	571.5	571.5	571.5	571.1
132.5°	599.8	600.2	600.6	600.9	601.3	601.4	601.3	601.2	601.0	600.9	600.5
135°	640.3	641.3	642.4	643.4	644.5	645.0	645.0	645.0	645.0	645.0	644.6
137.5°	684.4	684.9	685.3	685.8	686.3	686.7	687.0	687.3	687.5	687.8	687.4
140°	713.8	714.1	714.5	714.8	715.2	715.3	715.3	715.3	715.3	715.3	715.2
142.5°	740.7	741.0	741.4	741.7	742.1	742.2	742.0	741.9	741.7	741.6	741.6
145°	777.9	778.6	779.3	780.0	780.7	781.1	781.3	781.4	781.6	781.8	781.6
147.5°	814.8	815.6	816.4	817.3	818.1	818.5	818.3	818.2	818.0	817.9	817.8
150°	837.3	838.0	838.7	839.4	840.1	840.4	840.4	840.4	840.4	840.4	840.4
152.5°	858.6	859.0	859.4	859.8	860.2	860.5	860.6	860.8	860.9	861.1	861.5
155°	891.2	891.2	891.2	891.2	891.2	891.1	891.0	890.8	890.6	890.5	891.1
157.5°	918.8	918.4	918.1	917.8	917.5	917.3	917.3	917.3	917.2	917.2	917.7
160°	935.0	934.8	934.7	934.5	934.3	934.1	934.0	933.8	933.6	933.5	934.0
162.5°	950.0	949.6	949.1	948.7	948.2	947.9	947.7	947.6	947.4	947.2	948.2
165°	970.2	969.7	969.2	968.6	968.1	967.7	967.3	967.0	966.6	966.3	967.3
167.5°	985.7	984.9	984.2	983.5	982.8	982.4	982.4	982.5	982.5	982.5	983.6
170°	994.4	993.6	992.7	991.8	991.0	990.6	990.8	991.0	991.1	991.3	992.3
172.5°	1000.7	1000.0	999.2	998.5	997.8	997.4	997.5	997.5	997.5	997.6	998.7
175°	1009.3	1008.4	1007.5	1006.7	1005.8	1005.3	1005.1	1004.9	1004.8	1004.6	1005.8
177.5°	1012.1	1011.4	1010.7	1010.0	1009.3	1009.0	1009.0	1009.0	1009.0	1009.0	1009.9
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332881

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	618.2	618.2	618.2	618.2	618.2	618.2	618.2	618.2
2.5°	615.9	616.8	617.7	618.1	618.0	618.0	617.9	617.8
5°	611.8	612.8	613.9	614.3	614.1	613.9	613.6	613.4
7.5°	603.6	604.3	605.0	605.1	604.8	604.5	604.1	603.8
10°	596.3	596.7	597.1	597.1	596.7	596.3	595.9	595.5
12.5°	587.2	587.5	587.8	587.6	587.0	586.4	585.8	585.2
15°	571.4	571.2	570.9	570.5	569.7	569.0	568.3	567.5
17.5°	552.2	551.7	551.1	550.2	549.1	548.0	546.9	545.8
20°	538.9	538.0	537.2	536.1	534.7	533.3	532.0	530.6
22.5°	524.0	522.7	521.5	520.3	519.2	518.1	517.0	515.8
25°	500.0	498.3	496.5	495.1	494.0	492.9	491.9	490.8
27.5°	475.6	473.4	471.2	469.4	467.8	466.3	464.8	463.3
30°	458.1	455.5	452.9	450.7	449.0	447.4	445.7	444.0
32.5°	440.3	437.2	434.2	431.8	430.2	428.6	427.0	425.4
35°	413.6	410.1	406.5	403.8	401.9	400.0	398.1	396.2
37.5°	385.1	381.1	377.1	374.1	372.2	370.3	368.4	366.5
40°	366.0	361.6	357.2	354.1	352.2	350.3	348.4	346.5
42.5°	347.3	342.8	338.3	335.1	333.1	331.1	329.1	327.2
45°	318.7	313.5	308.3	304.8	302.9	301.0	299.1	297.3
47.5°	289.8	284.4	279.1	275.4	273.3	271.2	269.1	267.1
50°	270.6	265.4	260.1	256.5	254.5	252.5	250.5	248.5
52.5°	251.5	246.2	240.9	237.1	235.1	233.0	230.9	228.8
55°	223.4	217.9	212.4	208.7	206.7	204.7	202.7	200.7
57.5°	195.8	190.3	184.7	181.2	179.7	178.2	176.6	175.1
60°	177.4	172.0	166.5	162.9	161.2	159.6	157.9	156.2
62.5°	159.4	154.3	149.3	146.1	144.7	143.4	142.0	140.7
65°	133.4	128.9	124.4	121.5	120.2	119.0	117.7	116.4
67.5°	109.6	105.7	101.8	99.2	97.8	96.4	95.0	93.6
70°	93.4	89.9	86.5	84.2	83.1	82.1	81.0	80.0
72.5°	78.9	75.9	73.0	71.0	70.0	69.1	68.1	67.1
75°	58.1	55.7	53.3	51.8	51.1	50.5	49.9	49.2
77.5°	41.1	39.7	38.3	37.5	37.3	37.1	36.9	36.7
80°	31.6	31.2	30.9	30.7	30.6	30.5	30.4	30.3
82.5°	24.5	24.3	24.1	23.9	23.8	23.7	23.6	23.5
85°	14.3	14.0	13.8	13.7	13.7	13.7	13.7	13.7
87.5°	9.0	9.1	9.2	9.4	9.5	9.7	9.8	10.0
90°	19.3	20.3	21.4	22.1	22.4	22.8	23.1	23.5
92.5°	32.2	32.8	33.5	33.9	34.1	34.3	34.5	34.7
95°	60.5	61.0	61.5	61.8	61.8	61.8	61.8	61.8
97.5°	95.2	95.8	96.5	96.8	96.8	96.8	96.8	96.8
100°	120.3	120.7	121.0	121.2	121.2	121.2	121.2	121.2
102.5°	146.9	147.3	147.8	148.1	148.3	148.4	148.6	148.7
105°	187.1	187.6	188.1	188.7	189.2	189.7	190.2	190.8
107.5°	230.7	231.1	231.6	231.9	231.8	231.8	231.8	231.7
110°	259.6	259.3	258.9	259.0	259.6	260.1	260.6	261.1



TEST NUMBER: P332881

CATALOG NUMBER: S124RDIP-S350D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	290.8	290.8	290.7	290.7	290.8	290.9	291.0	291.1
115°	338.9	338.8	338.6	338.4	338.3	338.1	337.9	337.7
117.5°	385.2	384.6	384.0	383.5	383.2	382.8	382.5	382.1
120°	416.5	415.6	414.8	414.5	414.9	415.2	415.6	415.9
122.5°	448.3	447.8	447.2	446.6	445.9	445.3	444.7	444.1
125°	495.0	494.6	494.3	493.9	493.6	493.2	492.9	492.5
127.5°	539.5	539.2	538.8	538.5	538.2	538.0	537.7	537.4
130°	570.8	570.4	570.1	569.6	568.9	568.2	567.5	566.8
132.5°	600.2	599.8	599.5	599.2	598.9	598.6	598.3	598.1
135°	644.3	643.9	643.6	643.1	642.6	642.1	641.6	641.1
137.5°	686.9	686.5	686.0	685.8	685.9	686.0	686.1	686.3
140°	715.0	714.8	714.6	714.5	714.3	714.1	713.9	713.8
142.5°	741.5	741.5	741.5	741.4	741.4	741.4	741.3	741.3
145°	781.4	781.3	781.1	780.7	780.2	779.7	779.2	778.7
147.5°	817.6	817.5	817.3	817.2	817.0	816.8	816.7	816.5
150°	840.4	840.4	840.4	840.3	840.2	840.0	839.8	839.6
152.5°	861.9	862.3	862.7	862.7	862.3	861.8	861.4	860.9
155°	891.8	892.5	893.2	893.2	892.5	891.8	891.1	890.5
157.5°	918.2	918.8	919.3	919.2	918.7	918.1	917.5	916.9
160°	934.5	935.0	935.5	935.4	934.5	933.6	932.8	931.9
162.5°	949.1	950.0	951.0	951.0	950.1	949.3	948.4	947.5
165°	968.4	969.4	970.5	970.6	969.9	969.2	968.5	967.9
167.5°	984.6	985.7	986.7	986.7	985.6	984.5	983.5	982.4
170°	993.4	994.4	995.5	995.4	994.2	993.0	991.7	990.5
172.5°	999.9	1001.1	1002.3	1002.3	1001.1	999.8	998.6	997.4
175°	1007.0	1008.2	1009.5	1009.5	1008.2	1007.0	1005.8	1004.6
177.5°	1010.9	1011.9	1012.9	1012.8	1011.7	1010.6	1009.5	1008.3
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8

(END OF REPORT)