

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832474

Luminaire Tested: S123RDP-S560D940-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832474
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S560D940-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 2159.3 lumens
 Efficiency: N/A
 Efficacy: 110.2 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct


Input Watts (W): 19.6
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832474

CATALOG NUMBER: S123RDP-S560D940-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832474

CATALOG NUMBER: S123RDP-S560D940-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59				
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53				
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47				
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43				
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39				
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	17530	17530	17530	17530	17530
5°	20815	20151	17640	14260	13239
10°	18859	20467	17552	11425	9802
15°	12985	17549	17367	9338	7754
20°	9033	13511	17018	7874	6814
25°	6884	10297	16511	6999	6280
30°	5992	8233	15877	6498	5818
35°	5502	6945	14977	6076	5397
40°	5019	6202	13801	5663	5011
45°	4533	5672	12533	5270	4625
50°	4114	5233	11035	4886	4148
55°	3721	4806	9599	4511	3558
60°	3335	4370	8338	4097	3363
65°	3079	3876	7177	3683	3181
70°	2502	3352	6263	3330	2584
75°	2196	2666	5303	2761	2279
80°	1990	2256	4345	2318	2151
85°	1815	1976	3298	2100	1976

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 13224 cd/sqm

TEST NUMBER: P832474

CATALOG NUMBER: S123RDP-S560D940-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.4	6.9
10°-20°	343.5	15.9
20°-30°	394.1	18.3
30°-40°	388.5	18.0
40°-50°	342.6	15.9
50°-60°	263.5	12.2
60°-70°	173.3	8.0
70°-80°	84.2	3.9
80°-90°	21.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	886.1	41.0
0°-40°	1274.5	59.0
0°-60°	1880.6	87.1
0°-90°	2159.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2159.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1629	1629	1629	1629	1629	
5°	1926	1865	1633	1320	1225	176
15°	1165	1575	1558	838	696	329
25°	580	867	1390	589	529	274
35°	419	528	1140	462	411	261
45°	298	373	823	346	304	231
55°	198	256	512	240	190	178
65°	121	152	282	145	125	118
75°	53	64	128	66	55	57
85°	15	16	27	17	16	17
90°	0	0	0	0	0	

TEST NUMBER: P832474

CATALOG NUMBER: S123RDP-S560D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6
2.5°	1804.9	1799.2	1793.5	1791.8	1790.2	1784.8	1779.5	1767.5	1755.5	1743.1	1730.8
5°	1926.4	1927.1	1927.7	1926.1	1924.4	1917.4	1910.4	1895.7	1881.0	1865.0	1848.9
7.5°	1889.0	1899.7	1910.4	1912.4	1914.4	1919.7	1925.1	1921.7	1918.4	1912.4	1906.4
10°	1725.4	1724.7	1724.1	1736.1	1748.1	1783.8	1819.6	1837.9	1856.3	1872.6	1889.0
12.5°	1458.3	1459.3	1460.3	1499.7	1539.1	1572.8	1606.6	1653.3	1700.0	1750.4	1800.9
15°	1165.2	1181.5	1197.9	1233.0	1268.0	1318.8	1369.5	1432.3	1495.0	1574.8	1654.6
17.5°	956.9	963.9	970.9	1004.6	1038.3	1086.4	1134.5	1205.6	1276.7	1379.5	1482.4
20°	788.6	794.9	801.3	825.6	850.0	896.1	942.2	1009.9	1077.7	1179.5	1281.4
22.5°	658.4	670.7	683.1	699.4	715.8	749.2	782.6	851.7	920.8	1013.6	1106.4
25°	579.6	585.3	590.9	605.0	619.0	651.0	683.1	728.8	774.6	867.0	959.5
27.5°	526.2	527.8	529.5	539.9	550.2	570.9	591.6	634.0	676.4	752.5	828.7
30°	482.1	485.1	488.1	496.1	504.1	519.2	534.2	564.2	594.3	662.4	730.5
32.5°	448.0	449.7	451.4	458.1	464.7	475.8	486.8	510.5	534.2	586.3	638.3
35°	418.7	419.0	419.3	424.3	429.3	440.0	450.7	470.4	490.1	528.5	566.9
37.5°	385.3	387.6	390.0	393.6	397.3	406.6	416.0	432.0	448.0	479.8	511.5
40°	357.2	359.2	361.2	365.6	369.9	377.3	384.6	399.3	414.0	441.4	468.7
42.5°	329.2	330.5	331.9	336.2	340.5	349.6	358.6	370.3	381.9	404.6	427.3
45°	297.8	301.1	304.5	309.2	313.8	321.5	329.2	341.2	353.2	372.6	392.0
47.5°	271.8	273.4	275.1	279.1	283.1	292.5	301.8	312.5	323.2	341.2	359.2
50°	245.7	246.4	247.1	250.7	254.4	262.8	271.1	283.5	295.8	312.5	329.2
52.5°	221.0	222.7	224.4	228.0	231.7	237.4	243.1	255.7	268.4	284.8	301.1
55°	198.3	199.3	200.3	203.0	205.7	212.3	219.0	230.0	241.0	256.1	271.1
57.5°	176.9	178.3	179.6	181.6	183.6	189.6	195.6	205.3	215.0	230.0	245.1
60°	154.9	156.6	158.3	160.6	162.9	167.6	172.3	181.0	189.6	203.0	216.3
62.5°	138.9	139.2	139.6	141.6	143.6	146.9	150.2	157.2	164.3	177.6	191.0
65°	120.9	121.9	122.9	123.9	124.9	127.5	130.2	136.2	142.2	152.2	162.3
67.5°	102.2	103.2	104.2	105.8	107.5	109.8	112.2	116.2	120.2	129.5	138.9
70°	79.5	79.5	79.5	82.1	84.8	88.8	92.8	95.8	98.8	106.5	114.2
72.5°	64.8	65.1	65.4	65.8	66.1	68.4	70.8	75.8	80.8	85.5	90.1
75°	52.8	53.1	53.4	53.8	54.1	54.8	55.4	57.1	58.8	64.1	69.4
77.5°	42.1	42.4	42.7	43.1	43.4	44.1	44.7	45.4	46.1	48.1	50.1
80°	32.1	32.4	32.7	33.1	33.4	33.7	34.1	34.7	35.4	36.4	37.4
82.5°	23.4	23.4	23.4	23.4	23.4	24.0	24.7	24.7	24.7	25.4	26.0
85°	14.7	14.7	14.7	15.0	15.4	15.4	15.4	15.7	16.0	16.0	16.0
87.5°	6.7	6.3	6.0	6.3	6.7	6.7	6.7	7.0	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832474

CATALOG NUMBER: S123RDP-S560D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6
2.5°	1729.1	1727.4	1711.4	1695.4	1679.7	1664.0	1652.3	1640.6	1620.9	1601.2	1588.9
5°	1836.3	1823.6	1798.2	1772.8	1734.8	1696.7	1664.6	1632.6	1591.9	1551.1	1517.1
7.5°	1896.0	1885.7	1854.9	1824.2	1773.8	1723.4	1673.3	1623.2	1563.2	1503.1	1451.6
10°	1897.7	1906.4	1881.0	1855.6	1798.9	1742.1	1674.0	1605.9	1525.1	1444.3	1377.9
12.5°	1838.3	1875.6	1870.3	1865.0	1807.2	1749.4	1666.6	1583.9	1484.7	1385.5	1302.4
15°	1727.1	1799.5	1820.9	1842.3	1794.5	1746.8	1652.6	1558.5	1442.0	1325.4	1230.0
17.5°	1583.9	1685.3	1741.8	1798.2	1763.5	1728.7	1625.6	1522.4	1391.2	1260.0	1156.2
20°	1414.2	1547.1	1635.6	1724.1	1711.4	1698.7	1592.2	1485.7	1344.1	1202.6	1090.1
22.5°	1246.6	1386.9	1509.1	1631.3	1644.3	1657.3	1549.8	1442.3	1287.4	1132.5	1018.0
25°	1102.1	1244.6	1390.2	1535.8	1565.2	1594.5	1492.4	1390.2	1229.6	1069.0	955.2
27.5°	964.2	1099.7	1260.0	1420.3	1473.7	1527.1	1433.6	1340.1	1172.9	1005.6	892.1
30°	851.7	972.9	1136.5	1300.1	1374.5	1449.0	1363.2	1277.4	1111.4	945.5	834.3
32.5°	746.9	855.4	1019.6	1183.9	1270.4	1356.8	1282.7	1208.6	1049.0	889.4	779.6
35°	664.1	761.2	914.5	1067.7	1164.5	1261.3	1200.6	1139.8	983.9	828.0	724.2
37.5°	592.9	674.4	818.3	962.2	1065.0	1167.9	1117.1	1066.4	919.8	773.2	675.1
40°	534.2	599.6	733.5	867.4	968.2	1069.0	1025.6	982.2	851.0	719.8	628.0
42.5°	483.8	540.2	660.4	780.6	873.1	965.5	936.8	908.1	789.3	670.4	585.3
45°	439.4	486.8	592.6	698.4	783.6	868.7	846.0	823.3	720.8	618.3	540.2
47.5°	400.0	440.7	535.2	629.7	706.1	782.6	761.5	740.5	655.7	570.9	499.8
50°	363.9	398.6	477.4	556.2	625.0	693.8	676.4	659.0	588.9	518.8	457.4
52.5°	329.9	358.6	429.3	500.1	555.5	611.0	597.6	584.3	530.2	476.1	420.3
55°	297.5	323.8	383.6	443.4	490.8	538.2	524.8	511.5	469.4	427.3	378.3
57.5°	268.1	291.1	339.5	388.0	425.7	463.4	457.1	450.7	415.7	380.6	340.2
60°	237.0	257.7	299.5	341.2	371.6	402.0	394.6	387.3	362.2	337.2	302.5
62.5°	209.3	227.7	261.1	294.5	319.2	343.9	338.5	333.2	314.2	295.1	266.4
65°	180.3	198.3	225.4	252.4	271.8	291.1	286.5	281.8	267.4	253.1	230.0
67.5°	153.9	168.9	192.3	215.7	228.7	241.7	239.0	236.4	225.4	214.3	196.3
70°	127.2	140.2	159.6	179.0	188.0	197.0	198.0	199.0	189.0	179.0	165.6
72.5°	100.5	110.8	128.9	146.9	153.9	160.9	160.6	160.3	154.2	148.2	136.2
75°	77.1	84.8	98.8	112.8	118.9	124.9	126.2	127.5	121.9	116.2	109.5
77.5°	55.4	60.8	71.4	82.1	88.8	95.5	96.2	96.8	94.1	91.5	85.1
80°	39.1	40.7	47.4	54.1	61.1	68.1	69.1	70.1	67.4	64.8	60.8
82.5°	27.0	28.0	30.4	32.7	38.4	44.1	45.4	46.7	45.4	44.1	39.7
85°	16.4	16.7	17.7	18.7	21.4	24.0	25.4	26.7	26.0	25.4	23.0
87.5°	7.3	7.3	7.7	8.0	8.7	9.3	11.0	12.7	11.7	10.7	9.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832474

CATALOG NUMBER: S123RDP-S560D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6
2.5°	1576.5	1557.5	1538.4	1524.8	1511.1	1494.0	1477.0	1476.3	1475.7	1463.0	1450.3
5°	1483.0	1450.0	1416.9	1384.5	1352.1	1319.8	1287.4	1280.0	1272.7	1261.7	1250.7
7.5°	1400.2	1347.5	1294.7	1253.3	1211.9	1179.5	1147.2	1125.1	1103.1	1086.1	1069.0
10°	1311.4	1246.0	1180.5	1130.5	1080.4	1045.3	1010.3	984.9	959.5	947.5	935.5
12.5°	1219.3	1148.2	1077.0	1028.0	978.9	936.8	894.8	871.7	848.7	832.0	815.3
15°	1134.5	1058.0	981.6	929.5	877.4	838.0	798.6	775.6	752.5	735.8	719.1
17.5°	1052.3	975.2	898.1	845.3	792.6	756.9	721.1	698.8	676.4	666.1	655.7
20°	977.6	899.8	822.0	772.2	722.5	687.4	652.4	640.4	628.3	618.7	609.0
22.5°	903.4	828.7	753.9	706.1	658.4	633.0	607.6	598.0	588.3	580.9	573.6
25°	841.3	766.9	692.4	650.7	609.0	589.3	569.6	563.2	556.9	549.5	542.2
27.5°	778.6	707.8	637.0	603.6	570.2	554.2	538.2	530.2	522.2	516.2	510.1
30°	723.1	657.7	592.3	564.6	536.9	522.8	508.8	500.1	491.4	485.8	480.1
32.5°	669.7	611.6	553.5	529.8	506.1	492.4	478.8	470.4	462.1	455.4	448.7
35°	620.3	569.9	519.5	497.8	476.1	462.4	448.7	440.4	432.0	425.3	418.7
37.5°	576.9	531.2	485.4	465.1	444.7	432.7	420.7	412.0	403.3	396.3	389.3
40°	536.2	495.8	455.4	435.7	416.0	403.0	390.0	382.3	374.6	368.3	361.9
42.5°	500.1	463.1	426.0	406.6	387.3	374.9	362.6	353.6	344.5	340.9	337.2
45°	462.1	429.3	396.6	377.9	359.2	346.2	333.2	325.5	317.8	314.5	311.2
47.5°	428.7	398.3	367.9	349.6	331.2	319.5	307.8	301.8	295.8	291.1	286.5
50°	396.0	366.6	337.2	319.5	301.8	291.8	281.8	274.4	267.1	263.8	260.4
52.5°	364.6	337.9	311.2	293.1	275.1	265.4	255.7	249.4	243.1	236.0	229.0
55°	329.2	305.8	282.4	266.4	250.4	240.4	230.4	223.0	215.7	208.3	201.0
57.5°	299.8	276.8	253.7	239.4	225.0	215.3	205.7	197.6	189.6	183.6	177.6
60°	267.8	247.7	227.7	213.7	199.7	190.3	181.0	173.3	165.6	162.6	159.6
62.5°	237.7	219.0	200.3	188.0	175.6	166.6	157.6	152.6	147.6	145.6	143.6
65°	207.0	191.0	174.9	163.6	152.2	144.6	136.9	134.5	132.2	130.5	128.9
67.5°	178.3	164.6	150.9	140.9	130.9	125.5	120.2	117.5	114.8	112.8	110.8
70°	152.2	140.2	128.2	119.5	110.8	105.8	100.8	98.5	96.2	92.5	88.8
72.5°	124.2	114.8	105.5	98.8	92.1	87.8	83.5	78.8	74.1	70.8	67.4
75°	102.8	93.5	84.1	77.8	71.4	66.4	61.4	59.8	58.1	57.1	56.1
77.5°	78.8	70.8	62.8	57.8	52.8	50.4	48.1	47.1	46.1	45.7	45.4
80°	56.8	50.1	43.4	40.7	38.1	37.4	36.7	36.1	35.4	35.1	34.7
82.5°	35.4	32.1	28.7	28.0	27.4	27.0	26.7	26.4	26.0	25.7	25.4
85°	20.7	19.4	18.0	17.7	17.4	17.0	16.7	16.7	16.7	16.7	16.7
87.5°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.3	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832474

CATALOG NUMBER: S123RDP-S560D940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1628.6	1628.6	1628.6	1628.6
2.5°	1447.0	1443.6	1442.3	1441.0
5°	1240.3	1230.0	1227.6	1225.3
7.5°	1064.7	1060.4	1046.0	1031.6
10°	922.1	908.8	902.8	896.8
12.5°	802.9	790.6	788.6	786.6
15°	710.5	701.8	698.8	695.8
17.5°	649.7	643.7	640.0	636.3
20°	604.6	600.3	597.6	594.9
22.5°	570.2	566.9	564.9	562.9
25°	537.2	532.2	530.5	528.8
27.5°	505.8	501.5	499.8	498.1
30°	476.4	472.8	470.4	468.1
32.5°	444.4	440.0	438.7	437.4
35°	416.0	413.3	412.0	410.7
37.5°	385.9	382.6	380.6	378.6
40°	360.2	358.6	357.6	356.6
42.5°	334.2	331.2	330.9	330.5
45°	308.2	305.2	304.5	303.8
47.5°	283.8	281.1	280.8	280.4
50°	256.7	253.1	250.4	247.7
52.5°	225.7	222.4	220.0	217.7
55°	197.3	193.6	191.6	189.6
57.5°	175.9	174.3	173.3	172.3
60°	158.6	157.6	156.9	156.2
62.5°	142.6	141.6	141.6	141.6
65°	127.9	126.9	125.9	124.9
67.5°	108.8	106.8	106.5	106.2
70°	85.8	82.8	82.5	82.1
72.5°	67.1	66.8	66.1	65.4
75°	55.4	54.8	54.8	54.8
77.5°	44.7	44.1	44.1	44.1
80°	34.4	34.1	34.4	34.7
82.5°	25.4	25.4	25.0	24.7
85°	16.4	16.0	16.0	16.0
87.5°	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832474

CATALOG NUMBER: S123RDP-S560D940-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.66	16.11	15.02	16.42	16.74	19.32	20.78	19.68	21.09	21.40
	3H	15.92	17.22	16.30	17.55	17.91	20.86	22.16	21.24	22.49	22.86
	4H	16.33	17.55	16.73	17.90	18.28	21.38	22.60	21.78	22.95	23.33
	6H	16.64	17.76	17.05	18.13	18.52	21.72	22.84	22.13	23.21	23.60
	8H	16.74	17.81	17.17	18.20	18.61	21.81	22.88	22.24	23.27	23.68
	12H	16.81	17.84	17.24	18.22	18.65	21.86	22.89	22.29	23.27	23.70
4H	2H	15.45	16.67	15.85	17.02	17.40	19.38	20.60	19.78	20.95	21.33
	3H	16.87	17.88	17.28	18.28	18.68	21.09	22.10	21.50	22.50	22.91
	4H	17.34	18.25	17.78	18.67	19.11	21.72	22.63	22.15	23.04	23.48
	6H	17.74	18.53	18.20	18.98	19.44	22.19	22.98	22.65	23.42	23.88
	8H	17.88	18.61	18.34	19.06	19.53	22.33	23.07	22.80	23.51	23.98
	12H	17.98	18.64	18.47	19.12	19.59	22.42	23.07	22.90	23.55	24.03
8H	4H	17.70	18.43	18.16	18.88	19.35	21.73	22.46	22.19	22.91	23.38
	6H	18.18	18.79	18.68	19.28	19.76	22.25	22.85	22.74	23.34	23.82
	8H	18.38	18.92	18.90	19.43	19.92	22.43	22.97	22.95	23.48	23.97
	12H	18.54	19.02	19.06	19.52	20.08	22.57	23.05	23.09	23.54	24.11
12H	4H	17.74	18.39	18.22	18.87	19.34	21.71	22.36	22.19	22.84	23.31
	6H	18.24	18.79	18.76	19.30	19.79	22.22	22.76	22.74	23.27	23.76
	8H	18.49	18.97	19.00	19.46	20.03	22.44	22.92	22.95	23.41	23.98