

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832461

Luminaire Tested: S123RDP-S340D850-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832461
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S340D850-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 1633.5 lumens
 Efficiency: N/A
 Efficacy: 131.7 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct

Input Watts (W): 12.4
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832461
CATALOG NUMBER: S123RDP-S340D850-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832461

CATALOG NUMBER: S123RDP-S340D850-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59				
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53				
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47				
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43				
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39				
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	13261	13261	13261	13261	13261
5°	15746	15244	13344	10788	10015
10°	14267	15483	13278	8643	7415
15°	9823	13277	13138	7064	5865
20°	6834	10221	12874	5956	5156
25°	5208	7790	12491	5295	4752
30°	4533	6228	12010	4916	4401
35°	4162	5253	11331	4596	4083
40°	3797	4692	10442	4283	3790
45°	3430	4291	9481	3987	3498
50°	3113	3959	8349	3696	3138
55°	2815	3635	7261	3412	2693
60°	2523	3307	6308	3100	2545
65°	2328	2934	5430	2786	2407
70°	1891	2537	4736	2521	1954
75°	1659	2017	4013	2092	1722
80°	1500	1705	3285	1754	1630
85°	1371	1494	2495	1593	1494

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 10004 cd/sqm

TEST NUMBER: P832461
 CATALOG NUMBER: S123RDP-S340D850-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.3	6.9
10°-20°	259.9	15.9
20°-30°	298.1	18.3
30°-40°	293.9	18.0
40°-50°	259.2	15.9
50°-60°	199.4	12.2
60°-70°	131.1	8.0
70°-80°	63.7	3.9
80°-90°	16.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.3	41.0
0°-40°	964.2	59.0
0°-60°	1422.7	87.1
0°-90°	1633.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1633.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1232	1232	1232	1232	1232	
5°	1457	1411	1235	998	927	133
15°	882	1191	1179	634	526	249
25°	438	656	1052	446	400	207
35°	317	400	862	350	311	197
45°	225	282	623	262	230	175
55°	150	194	387	182	144	135
65°	91	115	213	109	94	90
75°	40	48	96	50	41	43
85°	11	12	20	13	12	13
90°	0	0	0	0	0	

TEST NUMBER: P832461

CATALOG NUMBER: S123RDP-S340D850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0
2.5°	1365.4	1361.1	1356.8	1355.5	1354.3	1350.2	1346.2	1337.1	1328.0	1318.6	1309.3
5°	1457.3	1457.8	1458.3	1457.1	1455.8	1450.5	1445.2	1434.1	1423.0	1410.8	1398.7
7.5°	1429.0	1437.1	1445.2	1446.7	1448.2	1452.3	1456.3	1453.8	1451.2	1446.7	1442.2
10°	1305.3	1304.8	1304.3	1313.3	1322.4	1349.5	1376.5	1390.4	1404.3	1416.6	1429.0
12.5°	1103.2	1104.0	1104.7	1134.5	1164.3	1189.8	1215.3	1250.7	1286.1	1324.2	1362.3
15°	881.5	893.8	906.2	932.7	959.2	997.6	1036.0	1083.5	1131.0	1191.4	1251.7
17.5°	723.9	729.2	734.5	760.0	785.5	821.9	858.2	912.0	965.8	1043.6	1121.4
20°	596.6	601.4	606.2	624.6	643.0	677.9	712.7	764.0	815.3	892.3	969.4
22.5°	498.1	507.4	516.8	529.1	541.5	566.8	592.0	644.3	696.6	766.8	837.0
25°	438.5	442.7	447.0	457.7	468.3	492.5	516.8	551.4	586.0	655.9	725.9
27.5°	398.0	399.3	400.6	408.4	416.2	431.9	447.5	479.6	511.7	569.3	626.9
30°	364.7	367.0	369.3	375.3	381.4	392.7	404.1	426.8	449.6	501.1	552.6
32.5°	338.9	340.2	341.5	346.5	351.6	359.9	368.2	386.2	404.1	443.5	482.9
35°	316.7	317.0	317.2	321.0	324.8	332.9	341.0	355.9	370.8	399.8	428.9
37.5°	291.5	293.2	295.0	297.8	300.6	307.6	314.7	326.8	338.9	362.9	386.9
40°	270.2	271.8	273.3	276.6	279.8	285.4	291.0	302.1	313.2	333.9	354.6
42.5°	249.0	250.0	251.1	254.3	257.6	264.4	271.3	280.1	288.9	306.1	323.3
45°	225.3	227.8	230.3	233.9	237.4	243.2	249.0	258.1	267.2	281.9	296.5
47.5°	205.6	206.9	208.1	211.1	214.2	221.2	228.3	236.4	244.5	258.1	271.8
50°	185.9	186.4	186.9	189.7	192.5	198.8	205.1	214.4	223.8	236.4	249.0
52.5°	167.2	168.5	169.7	172.5	175.3	179.6	183.9	193.5	203.1	215.4	227.8
55°	150.0	150.8	151.5	153.6	155.6	160.6	165.7	174.0	182.4	193.7	205.1
57.5°	133.9	134.9	135.9	137.4	138.9	143.5	148.0	155.3	162.7	174.0	185.4
60°	117.2	118.5	119.7	121.5	123.3	126.8	130.3	136.9	143.5	153.6	163.7
62.5°	105.1	105.3	105.6	107.1	108.6	111.1	113.7	119.0	124.3	134.4	144.5
65°	91.4	92.2	92.9	93.7	94.5	96.5	98.5	103.0	107.6	115.2	122.7
67.5°	77.3	78.0	78.8	80.1	81.3	83.1	84.9	87.9	90.9	98.0	105.1
70°	60.1	60.1	60.1	62.1	64.2	67.2	70.2	72.5	74.8	80.6	86.4
72.5°	49.0	49.3	49.5	49.8	50.0	51.8	53.5	57.3	61.1	64.7	68.2
75°	39.9	40.2	40.4	40.7	40.9	41.4	41.9	43.2	44.5	48.5	52.5
77.5°	31.8	32.1	32.3	32.6	32.8	33.3	33.8	34.3	34.9	36.4	37.9
80°	24.2	24.5	24.8	25.0	25.3	25.5	25.8	26.3	26.8	27.5	28.3
82.5°	17.7	17.7	17.7	17.7	17.7	18.2	18.7	18.7	18.7	19.2	19.7
85°	11.1	11.1	11.1	11.4	11.6	11.6	11.6	11.9	12.1	12.1	12.1
87.5°	5.1	4.8	4.5	4.8	5.1	5.1	5.1	5.3	5.6	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832461

CATALOG NUMBER: S123RDP-S340D850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0
2.5°	1308.0	1306.8	1294.7	1282.5	1270.7	1258.8	1250.0	1241.1	1226.2	1211.3	1202.0
5°	1389.1	1379.5	1360.3	1341.1	1312.3	1283.5	1259.3	1235.0	1204.2	1173.4	1147.7
7.5°	1434.3	1426.5	1403.3	1380.0	1341.9	1303.7	1265.9	1228.0	1182.5	1137.1	1098.2
10°	1435.6	1442.2	1423.0	1403.8	1360.8	1317.9	1266.4	1214.8	1153.7	1092.6	1042.3
12.5°	1390.6	1418.9	1414.9	1410.8	1367.1	1323.4	1260.8	1198.2	1123.2	1048.2	985.3
15°	1306.5	1361.3	1377.5	1393.7	1357.5	1321.4	1250.2	1179.0	1090.8	1002.7	930.5
17.5°	1198.2	1275.0	1317.6	1360.3	1334.1	1307.8	1229.7	1151.7	1052.4	953.2	874.6
20°	1069.9	1170.4	1237.3	1304.3	1294.7	1285.1	1204.5	1123.9	1016.8	909.7	824.6
22.5°	943.1	1049.2	1141.6	1234.0	1243.9	1253.7	1172.4	1091.1	973.9	856.7	770.1
25°	833.7	941.6	1051.7	1161.8	1184.0	1206.3	1129.0	1051.7	930.2	808.7	722.6
27.5°	729.4	832.0	953.2	1074.4	1114.8	1155.2	1084.5	1013.8	887.3	760.7	674.9
30°	644.3	736.0	859.7	983.5	1039.8	1096.1	1031.2	966.3	840.8	715.3	631.2
32.5°	565.0	647.1	771.3	895.6	961.0	1026.4	970.4	914.3	793.6	672.8	589.7
35°	502.4	575.9	691.8	807.7	881.0	954.2	908.2	862.3	744.3	626.4	547.8
37.5°	448.6	510.2	619.0	727.9	805.7	883.5	845.1	806.7	695.8	584.9	510.7
40°	404.1	453.6	554.9	656.2	732.4	808.7	775.9	743.1	643.8	544.5	475.1
42.5°	366.0	408.7	499.6	590.5	660.5	730.4	708.7	687.0	597.1	507.2	442.7
45°	332.4	368.2	448.3	528.4	592.8	657.2	640.0	622.8	545.3	467.8	408.7
47.5°	302.6	333.4	404.9	476.3	534.2	592.0	576.1	560.2	496.0	431.9	378.1
50°	275.3	301.6	361.2	420.8	472.8	524.8	511.7	498.6	445.5	392.5	346.0
52.5°	249.5	271.3	324.8	378.3	420.3	462.2	452.1	442.0	401.1	360.2	318.0
55°	225.0	245.0	290.2	335.4	371.3	407.1	397.0	386.9	355.1	323.3	286.2
57.5°	202.8	220.2	256.9	293.5	322.0	350.6	345.8	341.0	314.4	287.9	257.4
60°	179.3	195.0	226.6	258.1	281.1	304.1	298.5	293.0	274.0	255.1	228.8
62.5°	158.4	172.3	197.5	222.8	241.5	260.1	256.1	252.1	237.7	223.3	201.5
65°	136.4	150.0	170.5	190.9	205.6	220.2	216.7	213.2	202.3	191.4	174.0
67.5°	116.4	127.8	145.5	163.2	173.0	182.9	180.8	178.8	170.5	162.1	148.5
70°	96.2	106.1	120.7	135.4	142.2	149.0	149.8	150.5	143.0	135.4	125.3
72.5°	76.0	83.9	97.5	111.1	116.4	121.7	121.5	121.2	116.7	112.1	103.0
75°	58.3	64.2	74.8	85.4	89.9	94.5	95.5	96.5	92.2	87.9	82.8
77.5°	41.9	46.0	54.0	62.1	67.2	72.2	72.7	73.2	71.2	69.2	64.4
80°	29.6	30.8	35.9	40.9	46.2	51.5	52.3	53.0	51.0	49.0	46.0
82.5°	20.5	21.2	23.0	24.8	29.0	33.3	34.3	35.4	34.3	33.3	30.1
85°	12.4	12.6	13.4	14.1	16.2	18.2	19.2	20.2	19.7	19.2	17.4
87.5°	5.6	5.6	5.8	6.1	6.6	7.1	8.3	9.6	8.8	8.1	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832461

CATALOG NUMBER: S123RDP-S340D850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0	1232.0
2.5°	1192.6	1178.2	1163.8	1153.5	1143.1	1130.2	1117.4	1116.8	1116.3	1106.7	1097.1
5°	1121.9	1096.9	1071.9	1047.4	1022.9	998.4	973.9	968.3	962.8	954.4	946.1
7.5°	1059.3	1019.4	979.5	948.1	916.8	892.3	867.8	851.1	834.5	821.6	808.7
10°	992.1	942.6	893.1	855.2	817.3	790.8	764.3	745.1	725.9	716.8	707.7
12.5°	922.4	868.6	814.8	777.7	740.5	708.7	676.9	659.5	642.0	629.4	616.8
15°	858.2	800.4	742.5	703.1	663.7	633.9	604.1	586.7	569.3	556.7	544.0
17.5°	796.1	737.7	679.4	639.5	599.6	572.6	545.5	528.6	511.7	503.9	496.0
20°	739.5	680.7	621.8	584.2	546.6	520.0	493.5	484.4	475.3	468.0	460.7
22.5°	683.4	626.9	570.3	534.2	498.1	478.9	459.7	452.3	445.0	439.5	433.9
25°	636.5	580.1	523.8	492.3	460.7	445.8	430.9	426.1	421.3	415.7	410.2
27.5°	589.0	535.4	481.9	456.6	431.4	419.3	407.1	401.1	395.0	390.5	385.9
30°	547.1	497.6	448.1	427.1	406.1	395.5	384.9	378.3	371.8	367.5	363.2
32.5°	506.6	462.7	418.8	400.8	382.9	372.5	362.2	355.9	349.6	344.5	339.4
35°	469.3	431.1	393.0	376.6	360.2	349.8	339.4	333.1	326.8	321.8	316.7
37.5°	436.4	401.8	367.2	351.8	336.4	327.3	318.2	311.7	305.1	299.8	294.5
40°	405.6	375.1	344.5	329.6	314.7	304.8	295.0	289.2	283.4	278.6	273.8
42.5°	378.3	350.3	322.3	307.6	293.0	283.6	274.3	267.5	260.6	257.9	255.1
45°	349.6	324.8	300.0	285.9	271.8	261.9	252.1	246.3	240.4	237.9	235.4
47.5°	324.3	301.3	278.3	264.4	250.5	241.7	232.9	228.3	223.8	220.2	216.7
50°	299.5	277.3	255.1	241.7	228.3	220.7	213.2	207.6	202.1	199.5	197.0
52.5°	275.8	255.6	235.4	221.8	208.1	200.8	193.5	188.7	183.9	178.6	173.3
55°	249.0	231.4	213.7	201.5	189.4	181.8	174.3	168.7	163.2	157.6	152.0
57.5°	226.8	209.4	192.0	181.1	170.2	162.9	155.6	149.5	143.5	138.9	134.4
60°	202.6	187.4	172.3	161.6	151.0	144.0	136.9	131.1	125.3	123.0	120.7
62.5°	179.8	165.7	151.5	142.2	132.8	126.0	119.2	115.4	111.6	110.1	108.6
65°	156.6	144.5	132.3	123.8	115.2	109.4	103.6	101.8	100.0	98.8	97.5
67.5°	134.9	124.5	114.2	106.6	99.0	95.0	90.9	88.9	86.9	85.4	83.9
70°	115.2	106.1	97.0	90.4	83.9	80.1	76.3	74.5	72.7	70.0	67.2
72.5°	94.0	86.9	79.8	74.8	69.7	66.4	63.1	59.6	56.1	53.5	51.0
75°	77.8	70.7	63.6	58.8	54.0	50.3	46.5	45.2	43.9	43.2	42.4
77.5°	59.6	53.5	47.5	43.7	39.9	38.1	36.4	35.6	34.9	34.6	34.3
80°	42.9	37.9	32.8	30.8	28.8	28.3	27.8	27.3	26.8	26.5	26.3
82.5°	26.8	24.2	21.7	21.2	20.7	20.5	20.2	20.0	19.7	19.4	19.2
85°	15.7	14.6	13.6	13.4	13.1	12.9	12.6	12.6	12.6	12.6	12.6
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.3	6.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832461

CATALOG NUMBER: S123RDP-S340D850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1232.0	1232.0	1232.0	1232.0
2.5°	1094.6	1092.1	1091.1	1090.1
5°	938.3	930.5	928.7	926.9
7.5°	805.4	802.2	791.3	780.4
10°	697.6	687.5	682.9	678.4
12.5°	607.4	598.1	596.6	595.0
15°	537.5	530.9	528.6	526.3
17.5°	491.5	486.9	484.2	481.4
20°	457.4	454.1	452.1	450.1
22.5°	431.4	428.9	427.3	425.8
25°	406.4	402.6	401.3	400.1
27.5°	382.6	379.4	378.1	376.8
30°	360.4	357.6	355.9	354.1
32.5°	336.2	332.9	331.9	330.9
35°	314.7	312.7	311.7	310.7
37.5°	292.0	289.4	287.9	286.4
40°	272.5	271.3	270.5	269.7
42.5°	252.8	250.5	250.3	250.0
45°	233.1	230.8	230.3	229.8
47.5°	214.7	212.7	212.4	212.2
50°	194.2	191.4	189.4	187.4
52.5°	170.7	168.2	166.4	164.7
55°	149.3	146.5	145.0	143.5
57.5°	133.1	131.8	131.1	130.3
60°	120.0	119.2	118.7	118.2
62.5°	107.8	107.1	107.1	107.1
65°	96.7	96.0	95.2	94.5
67.5°	82.3	80.8	80.6	80.3
70°	64.9	62.6	62.4	62.1
72.5°	50.8	50.5	50.0	49.5
75°	41.9	41.4	41.4	41.4
77.5°	33.8	33.3	33.3	33.3
80°	26.0	25.8	26.0	26.3
82.5°	19.2	19.2	18.9	18.7
85°	12.4	12.1	12.1	12.1
87.5°	6.1	6.1	6.1	6.1
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832461

CATALOG NUMBER: S123RDP-S340D850-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.69	15.14	14.05	15.46	15.77	18.35	19.81	18.72	20.12	20.43
	3H	14.95	16.25	15.33	16.58	16.94	19.89	21.19	20.27	21.52	21.89
	4H	15.36	16.58	15.76	16.93	17.31	20.41	21.63	20.81	21.98	22.36
	6H	15.67	16.79	16.08	17.16	17.55	20.75	21.87	21.16	22.24	22.63
	8H	15.77	16.84	16.20	17.23	17.63	20.84	21.91	21.27	22.30	22.71
	12H	15.84	16.86	16.27	17.25	17.68	20.89	21.92	21.32	22.30	22.73
4H	2H	14.48	15.70	14.88	16.05	16.43	18.41	19.63	18.82	19.98	20.36
	3H	15.90	16.91	16.31	17.31	17.71	20.12	21.13	20.53	21.53	21.94
	4H	16.38	17.28	16.81	17.70	18.14	20.75	21.66	21.18	22.08	22.52
	6H	16.77	17.56	17.23	18.00	18.47	21.22	22.01	21.68	22.45	22.91
	8H	16.91	17.64	17.37	18.09	18.56	21.36	22.10	21.83	22.54	23.01
	12H	17.01	17.67	17.49	18.15	18.62	21.45	22.10	21.93	22.58	23.06
8H	4H	16.73	17.47	17.20	17.91	18.38	20.76	21.49	21.22	21.94	22.41
	6H	17.21	17.82	17.71	18.31	18.79	21.28	21.88	21.77	22.37	22.85
	8H	17.41	17.95	17.92	18.46	18.95	21.46	22.00	21.98	22.52	23.00
	12H	17.57	18.05	18.08	18.54	19.11	21.60	22.08	22.12	22.57	23.14
12H	4H	16.77	17.42	17.25	17.90	18.37	20.74	21.39	21.22	21.87	22.34
	6H	17.27	17.82	17.79	18.33	18.82	21.25	21.79	21.77	22.30	22.79
	8H	17.52	18.00	18.03	18.49	19.06	21.47	21.95	21.98	22.44	23.01