

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832470

Luminaire Tested: S123RDP-S560D850-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832470
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S560D850-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 2685.4 lumens
 Efficiency: N/A
 Efficacy: 137.0 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct

Input Watts (W): 19.6
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832470
CATALOG NUMBER: S123RDP-S560D850-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832470

CATALOG NUMBER: S123RDP-S560D850-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59				
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53				
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47				
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43				
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39				
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	21801	21801	21801	21801	21801
5°	25887	25061	21939	17735	16466
10°	23455	25456	21829	14210	12190
15°	16148	21826	21599	11614	9643
20°	11234	16804	21165	9793	8475
25°	8561	12807	20535	8704	7811
30°	7452	10239	19745	8081	7235
35°	6842	8637	18628	7557	6711
40°	6243	7713	17165	7043	6232
45°	5638	7054	15586	6555	5751
50°	5117	6507	13725	6077	5159
55°	4628	5977	11937	5611	4425
60°	4148	5436	10370	5096	4183
65°	3828	4821	8925	4579	3955
70°	3109	4170	7789	4142	3213
75°	2728	3315	6596	3435	2832
80°	2473	2808	5405	2882	2678
85°	2260	2458	4100	2618	2458

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 16446 cd/sqm

TEST NUMBER: P832470

CATALOG NUMBER: S123RDP-S560D850-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	6.9
10°-20°	427.2	15.9
20°-30°	490.1	18.3
30°-40°	483.1	18.0
40°-50°	426.0	15.9
50°-60°	327.8	12.2
60°-70°	215.5	8.0
70°-80°	104.7	3.9
80°-90°	26.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1102.0	41.0
0°-40°	1585.1	59.0
0°-60°	2338.9	87.1
0°-90°	2685.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2685.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2025	2025	2025	2025	2025	
5°	2396	2319	2030	1641	1524	219
15°	1449	1959	1938	1042	865	409
25°	721	1078	1729	733	658	340
35°	521	657	1418	575	511	325
45°	370	463	1024	431	378	288
55°	247	318	636	299	236	221
65°	150	189	350	180	155	147
75°	66	80	159	83	68	71
85°	18	20	33	21	20	21
90°	0	0	0	0	0	

TEST NUMBER: P832470

CATALOG NUMBER: S123RDP-S560D850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4
2.5°	2244.7	2237.6	2230.6	2228.5	2226.4	2219.8	2213.1	2198.2	2183.2	2167.9	2152.5
5°	2395.8	2396.6	2397.5	2395.4	2393.3	2384.6	2375.9	2357.6	2339.3	2319.4	2299.5
7.5°	2349.3	2362.6	2375.9	2378.4	2380.9	2387.5	2394.2	2390.0	2385.8	2378.4	2370.9
10°	2145.9	2145.0	2144.2	2159.1	2174.1	2218.5	2262.9	2285.8	2308.6	2329.0	2349.3
12.5°	1813.7	1814.9	1816.2	1865.2	1914.2	1956.1	1998.0	2056.2	2114.3	2177.0	2239.7
15°	1449.1	1469.5	1489.8	1533.4	1577.0	1640.1	1703.2	1781.3	1859.4	1958.6	2057.8
17.5°	1190.0	1198.7	1207.5	1249.4	1291.3	1351.1	1410.9	1499.4	1587.8	1715.7	1843.6
20°	980.7	988.6	996.5	1026.8	1057.1	1114.4	1171.7	1256.0	1340.3	1467.0	1593.6
22.5°	818.8	834.2	849.5	869.9	890.2	931.8	973.3	1059.2	1145.2	1260.6	1376.0
25°	720.8	727.9	734.9	752.4	769.8	809.7	849.5	906.4	963.3	1078.3	1193.3
27.5°	654.4	656.5	658.5	671.4	684.3	710.0	735.8	788.5	841.2	935.9	1030.6
30°	599.6	603.3	607.1	617.0	627.0	645.7	664.4	701.7	739.1	823.8	908.5
32.5°	557.2	559.3	561.4	569.7	578.0	591.7	605.4	634.9	664.4	729.1	793.9
35°	520.7	521.1	521.5	527.7	534.0	547.3	560.5	585.0	609.5	657.3	705.0
37.5°	479.2	482.1	485.0	489.5	494.1	505.7	517.4	537.3	557.2	596.7	636.1
40°	444.3	446.8	449.3	454.7	460.1	469.2	478.3	496.6	514.9	548.9	583.0
42.5°	409.4	411.1	412.7	418.1	423.5	434.7	445.9	460.5	475.0	503.2	531.5
45°	370.4	374.5	378.7	384.5	390.3	399.9	409.4	424.4	439.3	463.4	487.5
47.5°	338.0	340.1	342.1	347.1	352.1	363.7	375.4	388.6	401.9	424.4	446.8
50°	305.6	306.4	307.3	311.8	316.4	326.8	337.2	352.5	367.9	388.6	409.4
52.5°	274.9	277.0	279.0	283.6	288.2	295.2	302.3	318.1	333.8	354.2	374.5
55°	246.6	247.9	249.1	252.5	255.8	264.1	272.4	286.1	299.8	318.5	337.2
57.5°	220.1	221.7	223.4	225.9	228.4	235.8	243.3	255.4	267.4	286.1	304.8
60°	192.7	194.7	196.8	199.7	202.6	208.4	214.3	225.0	235.8	252.5	269.1
62.5°	172.7	173.1	173.6	176.1	178.5	182.7	186.8	195.6	204.3	220.9	237.5
65°	150.3	151.6	152.8	154.0	155.3	158.6	161.9	169.4	176.9	189.3	201.8
67.5°	127.1	128.3	129.5	131.6	133.7	136.6	139.5	144.5	149.5	161.1	172.7
70°	98.8	98.8	98.8	102.1	105.5	110.4	115.4	119.2	122.9	132.5	142.0
72.5°	80.6	81.0	81.4	81.8	82.2	85.1	88.0	94.3	100.5	106.3	112.1
75°	65.6	66.0	66.4	66.9	67.3	68.1	68.9	71.0	73.1	79.7	86.4
77.5°	52.3	52.7	53.1	53.6	54.0	54.8	55.6	56.5	57.3	59.8	62.3
80°	39.9	40.3	40.7	41.1	41.5	41.9	42.4	43.2	44.0	45.3	46.5
82.5°	29.1	29.1	29.1	29.1	29.1	29.9	30.7	30.7	30.7	31.6	32.4
85°	18.3	18.3	18.3	18.7	19.1	19.1	19.1	19.5	19.9	19.9	19.9
87.5°	8.3	7.9	7.5	7.9	8.3	8.3	8.3	8.7	9.1	9.1	9.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832470

CATALOG NUMBER: S123RDP-S560D850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4
2.5°	2150.4	2148.3	2128.4	2108.5	2089.0	2069.5	2054.9	2040.4	2015.9	1991.4	1976.0
5°	2283.7	2267.9	2236.4	2204.8	2157.5	2110.1	2070.3	2030.4	1979.8	1929.1	1886.8
7.5°	2358.0	2345.2	2307.0	2268.8	2206.1	2143.4	2081.1	2018.8	1944.1	1869.3	1805.4
10°	2360.1	2370.9	2339.3	2307.8	2237.2	2166.6	2081.9	1997.2	1896.7	1796.2	1713.6
12.5°	2286.2	2332.7	2326.1	2319.4	2247.6	2175.7	2072.8	1969.8	1846.5	1723.2	1619.8
15°	2147.9	2238.0	2264.6	2291.2	2231.8	2172.4	2055.3	1938.2	1793.3	1648.4	1529.7
17.5°	1969.8	2096.0	2166.2	2236.4	2193.2	2150.0	2021.7	1893.4	1730.2	1567.0	1437.9
20°	1758.9	1924.1	2034.2	2144.2	2128.4	2112.6	1980.2	1847.7	1671.7	1495.6	1355.7
22.5°	1550.4	1724.8	1876.8	2028.8	2045.0	2061.1	1927.4	1793.7	1601.1	1408.4	1266.0
25°	1370.6	1547.9	1729.0	1910.0	1946.5	1983.1	1856.0	1729.0	1529.3	1329.5	1187.9
27.5°	1199.2	1367.7	1567.0	1766.3	1832.8	1899.2	1783.0	1666.7	1458.7	1250.6	1109.5
30°	1059.2	1209.9	1413.4	1616.9	1709.5	1802.1	1695.3	1588.6	1382.3	1175.9	1037.6
32.5°	928.8	1063.8	1268.1	1472.4	1579.9	1687.5	1595.3	1503.1	1304.6	1106.1	969.5
35°	825.9	946.7	1137.3	1327.9	1448.3	1568.7	1493.1	1417.6	1223.7	1029.7	900.6
37.5°	737.4	838.7	1017.7	1196.7	1324.5	1452.4	1389.3	1326.2	1143.9	961.6	839.6
40°	664.4	745.7	912.2	1078.7	1204.1	1329.5	1275.6	1221.6	1058.4	895.2	781.0
42.5°	601.7	671.8	821.3	970.8	1085.8	1200.8	1165.1	1129.4	981.6	833.8	727.9
45°	546.4	605.4	737.0	868.6	974.5	1080.4	1052.2	1023.9	896.5	769.0	671.8
47.5°	497.4	548.1	665.6	783.1	878.2	973.3	947.1	921.0	815.5	710.0	621.6
50°	452.6	495.8	593.8	691.8	777.3	862.8	841.2	819.6	732.4	645.3	568.9
52.5°	410.2	445.9	534.0	622.0	690.9	759.9	743.2	726.6	659.4	592.1	522.8
55°	370.0	402.8	477.1	551.4	610.4	669.3	652.7	636.1	583.8	531.5	470.4
57.5°	333.4	362.1	422.3	482.5	529.4	576.3	568.4	560.5	516.9	473.3	423.1
60°	294.8	320.5	372.5	424.4	462.1	499.9	490.8	481.7	450.5	419.4	376.2
62.5°	260.3	283.2	324.7	366.2	396.9	427.7	421.0	414.4	390.7	367.1	331.3
65°	224.2	246.6	280.3	313.9	338.0	362.1	356.3	350.4	332.6	314.7	286.1
67.5°	191.4	210.1	239.2	268.2	284.4	300.6	297.3	294.0	280.3	266.6	244.1
70°	158.2	174.4	198.5	222.6	233.8	245.0	246.2	247.5	235.0	222.6	205.9
72.5°	125.0	137.9	160.3	182.7	191.4	200.1	199.7	199.3	191.8	184.4	169.4
75°	95.9	105.5	122.9	140.3	147.8	155.3	157.0	158.6	151.6	144.5	136.2
77.5°	68.9	75.6	88.9	102.1	110.4	118.8	119.6	120.4	117.1	113.8	105.9
80°	48.6	50.7	59.0	67.3	76.0	84.7	86.0	87.2	83.9	80.6	75.6
82.5°	33.6	34.9	37.8	40.7	47.8	54.8	56.5	58.1	56.5	54.8	49.4
85°	20.3	20.8	22.0	23.3	26.6	29.9	31.6	33.2	32.4	31.6	28.7
87.5°	9.1	9.1	9.6	10.0	10.8	11.6	13.7	15.8	14.5	13.3	12.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832470

CATALOG NUMBER: S123RDP-S560D850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4
2.5°	1960.7	1937.0	1913.3	1896.3	1879.3	1858.1	1836.9	1836.1	1835.3	1819.5	1803.7
5°	1844.4	1803.3	1762.2	1721.9	1681.6	1641.4	1601.1	1592.0	1582.8	1569.1	1555.4
7.5°	1741.4	1675.8	1610.2	1558.7	1507.2	1467.0	1426.7	1399.3	1371.9	1350.7	1329.5
10°	1631.0	1549.6	1468.2	1405.9	1343.6	1300.1	1256.5	1224.9	1193.3	1178.4	1163.4
12.5°	1516.4	1427.9	1339.5	1278.5	1217.4	1165.1	1112.8	1084.1	1055.5	1034.7	1014.0
15°	1410.9	1315.8	1220.7	1156.0	1091.2	1042.2	993.2	964.6	935.9	915.1	894.4
17.5°	1308.8	1212.9	1116.9	1051.3	985.7	941.3	896.9	869.1	841.2	828.4	815.5
20°	1215.8	1119.0	1022.3	960.4	898.5	854.9	811.3	796.4	781.4	769.4	757.4
22.5°	1123.6	1030.6	937.6	878.2	818.8	787.3	755.7	743.7	731.6	722.5	713.3
25°	1046.4	953.8	861.2	809.3	757.4	732.9	708.4	700.5	692.6	683.5	674.3
27.5°	968.3	880.3	792.2	750.7	709.2	689.3	669.3	659.4	649.4	641.9	634.5
30°	899.4	818.0	736.6	702.1	667.7	650.2	632.8	622.0	611.2	604.1	597.1
32.5°	832.9	760.7	688.4	659.0	629.5	612.4	595.4	585.0	574.7	566.4	558.1
35°	771.5	708.8	646.1	619.1	592.1	575.1	558.1	547.7	537.3	529.0	520.7
37.5°	717.5	660.6	603.7	578.4	553.1	538.1	523.2	512.4	501.6	492.9	484.1
40°	666.8	616.6	566.4	541.9	517.4	501.2	485.0	475.4	465.9	458.0	450.1
42.5°	622.0	575.9	529.8	505.7	481.7	466.3	450.9	439.7	428.5	423.9	419.4
45°	574.7	534.0	493.3	470.0	446.8	430.6	414.4	404.8	395.3	391.1	387.0
47.5°	533.1	495.4	457.6	434.7	411.9	397.4	382.8	375.4	367.9	362.1	356.3
50°	492.5	455.9	419.4	397.4	375.4	362.9	350.4	341.3	332.2	328.0	323.9
52.5°	453.4	420.2	387.0	364.6	342.1	330.1	318.1	310.2	302.3	293.6	284.8
55°	409.4	380.3	351.3	331.3	311.4	299.0	286.5	277.4	268.2	259.1	250.0
57.5°	372.9	344.2	315.6	297.7	279.9	267.8	255.8	245.8	235.8	228.4	220.9
60°	333.0	308.1	283.2	265.7	248.3	236.7	225.0	215.5	205.9	202.2	198.5
62.5°	295.6	272.4	249.1	233.8	218.4	207.2	196.0	189.8	183.5	181.0	178.5
65°	257.4	237.5	217.6	203.5	189.3	179.8	170.2	167.3	164.4	162.4	160.3
67.5°	221.7	204.7	187.7	175.2	162.8	156.1	149.5	146.2	142.8	140.3	137.9
70°	189.3	174.4	159.4	148.6	137.9	131.6	125.4	122.5	119.6	115.0	110.4
72.5°	154.5	142.8	131.2	122.9	114.6	109.2	103.8	98.0	92.2	88.0	83.9
75°	127.9	116.3	104.6	96.7	88.9	82.6	76.4	74.3	72.2	71.0	69.8
77.5°	98.0	88.0	78.1	71.8	65.6	62.7	59.8	58.5	57.3	56.9	56.5
80°	70.6	62.3	54.0	50.7	47.3	46.5	45.7	44.8	44.0	43.6	43.2
82.5°	44.0	39.9	35.7	34.9	34.0	33.6	33.2	32.8	32.4	32.0	31.6
85°	25.7	24.1	22.4	22.0	21.6	21.2	20.8	20.8	20.8	20.8	20.8
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.4	10.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832470

CATALOG NUMBER: S123RDP-S560D850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2025.4	2025.4	2025.4	2025.4
2.5°	1799.6	1795.4	1793.7	1792.1
5°	1542.5	1529.7	1526.8	1523.9
7.5°	1324.1	1318.7	1300.9	1283.0
10°	1146.8	1130.2	1122.8	1115.3
12.5°	998.6	983.2	980.7	978.3
15°	883.6	872.8	869.1	865.3
17.5°	808.0	800.5	796.0	791.4
20°	752.0	746.6	743.2	739.9
22.5°	709.2	705.0	702.6	700.1
25°	668.1	661.9	659.8	657.7
27.5°	629.1	623.7	621.6	619.5
30°	592.5	588.0	585.0	582.1
32.5°	552.7	547.3	545.6	543.9
35°	517.4	514.0	512.4	510.7
37.5°	480.0	475.8	473.3	470.9
40°	448.0	445.9	444.7	443.5
42.5°	415.6	411.9	411.5	411.1
45°	383.2	379.5	378.7	377.8
47.5°	352.9	349.6	349.2	348.8
50°	319.3	314.7	311.4	308.1
52.5°	280.7	276.5	273.6	270.7
55°	245.4	240.8	238.3	235.8
57.5°	218.8	216.7	215.5	214.3
60°	197.2	196.0	195.2	194.3
62.5°	177.3	176.1	176.1	176.1
65°	159.0	157.8	156.5	155.3
67.5°	135.4	132.9	132.5	132.0
70°	106.7	103.0	102.6	102.1
72.5°	83.5	83.0	82.2	81.4
75°	68.9	68.1	68.1	68.1
77.5°	55.6	54.8	54.8	54.8
80°	42.8	42.4	42.8	43.2
82.5°	31.6	31.6	31.1	30.7
85°	20.3	19.9	19.9	19.9
87.5°	10.0	10.0	10.0	10.0
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832470

CATALOG NUMBER: S123RDP-S560D850-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.41	16.87	15.78	17.18	17.50	20.08	21.53	20.44	21.85	22.16
	3H	16.68	17.98	17.05	18.31	18.67	21.62	22.92	22.00	23.25	23.61
	4H	17.09	18.31	17.49	18.65	19.03	22.14	23.36	22.54	23.70	24.08
	6H	17.40	18.52	17.81	18.89	19.28	22.48	23.60	22.89	23.97	24.36
	8H	17.50	18.57	17.93	18.96	19.36	22.57	23.64	23.00	24.03	24.43
	12H	17.57	18.59	18.00	18.98	19.40	22.62	23.64	23.05	24.03	24.46
4H	2H	16.21	17.43	16.61	17.77	18.15	20.14	21.36	20.54	21.71	22.09
	3H	17.62	18.63	18.04	19.04	19.44	21.85	22.86	22.26	23.26	23.66
	4H	18.10	19.01	18.53	19.43	19.87	22.48	23.39	22.91	23.80	24.24
	6H	18.50	19.29	18.96	19.73	20.19	22.95	23.73	23.41	24.18	24.64
	8H	18.64	19.37	19.10	19.82	20.28	23.09	23.82	23.55	24.27	24.74
	12H	18.74	19.39	19.22	19.87	20.35	23.18	23.83	23.66	24.31	24.78
8H	4H	18.46	19.19	18.92	19.64	20.11	22.49	23.22	22.95	23.67	24.13
	6H	18.94	19.55	19.44	20.04	20.52	23.00	23.61	23.50	24.10	24.58
	8H	19.14	19.68	19.65	20.19	20.68	23.19	23.73	23.71	24.24	24.73
	12H	19.30	19.78	19.81	20.27	20.84	23.33	23.81	23.84	24.30	24.87
12H	4H	18.50	19.15	18.98	19.63	20.10	22.46	23.12	22.95	23.60	24.07
	6H	19.00	19.54	19.52	20.05	20.54	22.98	23.52	23.49	24.03	24.52
	8H	19.25	19.72	19.76	20.22	20.78	23.20	23.68	23.71	24.17	24.74