

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332952

Luminaire Tested: **S124RDIP-S795D1205U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020


**Test Information**

Test Method: LM-79-08  
Report Number: P332952  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S795D1205U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8019.5 lumens  
Efficiency: N/A  
Efficacy: 140.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332952

CATALOG NUMBER: S124RDIP-S795D1205U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332952

CATALOG NUMBER: S124RDIP-S795D1205U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																				
1	96	92	88	84	87	84	80	78	68	66	64	55	53	52	42	41	40	34																				
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	35	34	29																				
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25																				
4	73	63	55	49	66	57	51	46	47	42	39	38	35	32	30	27	25	21																				
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19																				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20	17																				
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	17	15																				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13																				
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11215	11215	11215
5°	11240	11102	11171
10°	11170	10969	10969
15°	11041	10739	10659
20°	10865	10436	10244
25°	10640	10081	9825
30°	10421	9707	9300
35°	10178	9319	8774
40°	9887	8878	8205
45°	9618	8440	7626
50°	9311	7935	7013
55°	8983	7410	6348
60°	8622	6835	5667
65°	8290	6117	4999
70°	7808	5323	4244
75°	7199	4414	3450
80°	6281	3361	3166
85°	5317	3057	2853



TEST NUMBER: P332952

CATALOG NUMBER: S124RDIP-S795D1205U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.5	1.6
10°-20°	363.9	4.5
20°-30°	525.5	6.6
30°-40°	595.6	7.4
40°-50°	575.2	7.2
50°-60°	478.3	6.0
60°-70°	330.3	4.1
70°-80°	167.4	2.1
80°-90°	47.4	0.6
90°-100°	53.1	0.7
100°-110°	338.8	4.2
110°-120°	648.1	8.1
120°-130°	822.7	10.3
130°-140°	880.2	11.0
140°-150°	823.1	10.3
150°-160°	663.8	8.3
160°-170°	428.1	5.3
170°-180°	147.6	1.8
0°-30°	1019.8	12.7
0°-40°	1615.5	20.1
0°-60°	2668.9	33.3
0°-90°	3214.0	40.1
90°-120°	1040.0	13.0
90°-150°	3566.1	44.5
90°-180°	4806.0	59.9
0°-180°	8019.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1389	1389	1389	1389	1389	
5°	1387	1382	1370	1380	1378	132
15°	1321	1311	1285	1282	1275	372
25°	1194	1174	1132	1114	1103	550
35°	1033	998	946	910	890	645
45°	842	802	739	689	668	649
55°	638	594	526	473	451	571
65°	434	387	320	276	262	428
75°	231	191	142	118	111	244
85°	57	37	33	31	31	65
90°	4	16	26	32	35	6
95°	64	27	26	32	34	82
105°	350	357	362	370	331	366
115°	653	656	655	658	658	642
125°	918	922	920	924	925	819
135°	1139	1138	1142	1145	1147	877
145°	1313	1316	1316	1318	1320	820
155°	1440	1441	1437	1442	1438	663
165°	1519	1513	1513	1521	1512	429
175°	1554	1547	1548	1557	1544	148
180°	1554	1554	1554	1554	1554	



TEST NUMBER: P332952

CATALOG NUMBER: S124RDIP-S795D1205U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1392.6	1391.8	1391.0	1390.3	1389.5	1388.1	1386.0	1384.0	1381.9	1379.8	1381.9
5°	1387.0	1386.1	1385.1	1384.2	1383.2	1381.4	1378.5	1375.7	1372.8	1370.0	1372.4
7.5°	1374.5	1373.5	1372.5	1371.5	1370.5	1368.2	1364.5	1360.8	1357.1	1353.4	1354.9
10°	1362.6	1361.4	1360.2	1359.0	1357.8	1355.1	1350.9	1346.6	1342.4	1338.1	1339.0
12.5°	1347.2	1345.9	1344.5	1343.1	1341.8	1338.6	1333.6	1328.5	1323.5	1318.5	1319.1
15°	1321.1	1319.0	1316.8	1314.7	1312.6	1308.6	1302.6	1296.7	1290.8	1284.9	1284.4
17.5°	1289.4	1286.3	1283.2	1280.2	1277.1	1272.0	1264.9	1257.8	1250.7	1243.6	1242.3
20°	1264.7	1261.6	1258.6	1255.5	1252.4	1246.9	1238.8	1230.8	1222.7	1214.7	1212.8
22.5°	1237.5	1234.0	1230.6	1227.1	1223.7	1217.6	1209.0	1200.4	1191.8	1183.2	1180.4
25°	1194.5	1190.2	1186.0	1181.7	1177.5	1170.5	1160.8	1151.1	1141.4	1131.7	1127.7
27.5°	1149.4	1144.1	1138.7	1133.4	1128.0	1120.2	1109.8	1099.5	1089.1	1078.8	1073.8
30°	1117.9	1112.0	1106.1	1100.2	1094.3	1085.8	1074.7	1063.6	1052.4	1041.3	1035.4
32.5°	1084.7	1078.1	1071.4	1064.7	1058.1	1049.0	1037.5	1026.0	1014.5	1003.0	996.2
35°	1032.8	1025.3	1017.7	1010.1	1002.6	992.9	981.1	969.2	957.4	945.6	937.6
37.5°	977.3	969.5	961.7	953.9	946.1	935.7	922.6	909.5	896.4	883.3	874.3
40°	938.2	930.4	922.6	914.8	907.0	896.3	882.8	869.4	855.9	842.4	832.5
42.5°	900.7	892.5	884.4	876.2	868.0	856.9	842.9	828.8	814.8	800.7	790.6
45°	842.4	833.7	824.9	816.2	807.4	796.0	781.8	767.6	753.4	739.3	727.7
47.5°	782.2	773.2	764.2	755.1	746.1	734.2	719.5	704.7	690.0	675.2	663.2
50°	741.4	732.2	722.9	713.7	704.5	692.3	677.2	662.1	646.9	631.8	620.0
52.5°	699.7	690.7	681.6	672.6	663.6	651.3	635.8	620.3	604.8	589.3	577.3
55°	638.2	628.7	619.3	609.8	600.4	588.0	572.6	557.2	541.9	526.5	514.2
57.5°	577.4	567.5	557.7	547.9	538.0	525.5	510.4	495.3	480.2	465.0	452.6
60°	534.0	524.5	515.1	505.6	496.1	483.9	468.7	453.6	438.5	423.3	411.0
62.5°	494.8	485.0	475.2	465.3	455.5	442.8	427.3	411.8	396.3	380.8	369.4
65°	434.0	423.8	413.6	403.5	393.3	380.7	365.5	350.4	335.3	320.2	310.0
67.5°	370.8	361.1	351.3	341.6	331.8	320.0	305.9	291.9	277.8	263.8	255.0
70°	330.8	320.9	310.9	301.0	291.1	279.4	265.9	252.4	239.0	225.5	217.7
72.5°	288.3	279.3	270.3	261.3	252.3	241.5	228.8	216.0	203.3	190.6	183.9
75°	230.8	222.1	213.3	204.6	195.8	185.9	174.8	163.7	152.6	141.5	136.0
77.5°	172.5	165.1	157.7	150.3	142.8	134.6	125.7	116.7	107.7	98.7	95.5
80°	135.1	128.2	121.4	114.5	107.7	100.7	93.6	86.5	79.4	72.3	71.6
82.5°	102.8	96.5	90.2	83.9	77.6	72.4	68.4	64.3	60.2	56.2	55.6
85°	57.4	52.7	48.0	43.3	38.5	35.8	35.1	34.4	33.7	33.0	32.5
87.5°	20.3	19.3	18.4	17.4	16.5	16.1	16.4	16.6	16.8	17.0	17.1
90°	3.5	6.3	9.2	12.0	14.8	17.3	19.4	21.4	23.5	25.6	27.1
92.5°	14.6	14.8	15.0	15.1	15.3	16.4	18.4	20.5	22.6	24.6	26.2
95°	63.9	55.1	46.3	37.6	28.8	24.5	24.8	25.0	25.3	25.6	27.1
97.5°	135.7	141.2	146.7	152.1	157.6	145.9	117.1	88.3	59.5	30.7	30.8
100°	190.6	195.2	199.9	204.5	209.2	193.7	158.0	122.4	86.8	51.1	46.7
102.5°	251.9	255.3	258.7	262.1	265.5	264.9	260.3	255.6	251.0	246.3	199.0
105°	349.7	351.3	352.8	354.4	355.9	357.4	358.7	359.9	361.2	362.5	364.9
107.5°	440.6	441.4	442.2	442.9	443.7	445.0	446.7	448.5	450.2	452.0	453.1
110°	502.0	502.7	503.5	504.3	505.1	506.2	507.8	509.3	510.9	512.4	512.9



TEST NUMBER: P332952

CATALOG NUMBER: S124RDIP-S795D1205U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	561.5	562.9	564.2	565.6	567.0	568.1	568.8	569.5	570.3	571.0	570.9
115°	653.0	653.8	654.6	655.3	656.1	656.4	656.1	655.9	655.6	655.3	655.9
117.5°	735.5	736.5	737.6	738.6	739.6	740.4	741.0	741.6	742.2	742.7	742.6
120°	791.3	792.3	793.4	794.4	795.4	795.8	795.6	795.3	795.0	794.8	795.3
122.5°	843.3	844.0	844.6	845.2	845.8	846.3	846.7	847.0	847.4	847.8	848.1
125°	917.9	919.0	920.0	921.0	922.1	922.3	921.8	921.3	920.8	920.3	921.0
127.5°	988.6	988.8	989.1	989.4	989.6	990.3	991.5	992.7	993.9	995.1	994.9
130°	1034.1	1034.4	1034.7	1034.9	1035.2	1035.7	1036.5	1037.2	1038.0	1038.8	1039.0
132.5°	1076.0	1076.4	1076.9	1077.4	1077.8	1078.6	1079.5	1080.5	1081.5	1082.5	1082.7
135°	1138.7	1138.5	1138.2	1137.9	1137.7	1138.1	1139.1	1140.1	1141.2	1142.2	1142.7
137.5°	1194.3	1194.4	1194.5	1194.6	1194.7	1195.3	1196.4	1197.6	1198.7	1199.8	1200.4
140°	1230.5	1231.0	1231.5	1232.1	1232.6	1233.1	1233.6	1234.1	1234.6	1235.2	1235.9
142.5°	1263.0	1264.0	1264.9	1265.8	1266.8	1267.4	1267.7	1268.0	1268.3	1268.6	1269.2
145°	1313.0	1313.8	1314.6	1315.3	1316.1	1316.5	1316.5	1316.5	1316.5	1316.5	1316.8
147.5°	1352.7	1354.2	1355.6	1357.1	1358.5	1359.1	1358.9	1358.6	1358.3	1358.1	1358.3
150°	1381.6	1382.6	1383.6	1384.7	1385.7	1386.1	1385.8	1385.6	1385.3	1385.0	1385.0
152.5°	1405.7	1406.6	1407.4	1408.2	1409.0	1409.2	1408.8	1408.3	1407.8	1407.4	1407.8
155°	1439.7	1439.9	1440.2	1440.4	1440.7	1440.4	1439.7	1438.9	1438.1	1437.3	1438.4
157.5°	1468.2	1468.1	1467.9	1467.8	1467.6	1467.1	1466.2	1465.4	1464.5	1463.6	1464.9
160°	1485.0	1484.2	1483.4	1482.7	1481.9	1481.4	1481.1	1480.8	1480.6	1480.3	1481.9
162.5°	1499.8	1498.9	1497.9	1496.9	1495.9	1495.3	1495.0	1494.8	1494.5	1494.3	1495.8
165°	1518.7	1517.4	1516.1	1514.8	1513.5	1512.9	1512.9	1512.9	1512.9	1512.9	1514.9
167.5°	1533.5	1532.2	1530.9	1529.5	1528.2	1527.4	1527.3	1527.1	1527.0	1526.8	1529.1
170°	1541.9	1540.4	1538.8	1537.3	1535.7	1535.1	1535.3	1535.6	1535.8	1536.1	1538.2
172.5°	1547.5	1545.9	1544.4	1542.8	1541.3	1540.6	1540.9	1541.2	1541.4	1541.7	1543.7
175°	1553.5	1552.0	1550.4	1548.9	1547.3	1546.7	1546.9	1547.2	1547.5	1547.7	1550.0
177.5°	1556.3	1554.9	1553.4	1552.0	1550.5	1550.0	1550.4	1550.8	1551.3	1551.7	1553.3
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5



TEST NUMBER: P332952

CATALOG NUMBER: S124RDIP-S795D1205U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2	1389.2
2.5°	1384.0	1386.0	1388.1	1389.1	1388.9	1388.7	1388.5	1388.3
5°	1374.7	1377.1	1379.5	1380.4	1379.9	1379.5	1379.0	1378.5
7.5°	1356.4	1358.0	1359.5	1359.8	1359.1	1358.3	1357.6	1356.8
10°	1340.0	1340.9	1341.9	1341.9	1340.9	1340.0	1339.0	1338.1
12.5°	1319.7	1320.2	1320.8	1320.4	1319.1	1317.8	1316.4	1315.1
15°	1284.0	1283.5	1283.0	1282.0	1280.3	1278.6	1277.0	1275.3
17.5°	1241.0	1239.7	1238.3	1236.4	1233.9	1231.4	1228.9	1226.4
20°	1210.9	1209.0	1207.1	1204.7	1201.6	1198.5	1195.4	1192.4
22.5°	1177.6	1174.7	1171.9	1169.2	1166.7	1164.2	1161.7	1159.2
25°	1123.7	1119.7	1115.7	1112.5	1110.1	1107.8	1105.4	1103.0
27.5°	1068.8	1063.9	1058.9	1054.7	1051.3	1047.9	1044.5	1041.1
30°	1029.5	1023.6	1017.7	1012.8	1009.1	1005.3	1001.5	997.7
32.5°	989.3	982.5	975.6	970.4	966.8	963.2	959.6	956.0
35°	929.5	921.5	913.5	907.3	903.1	898.8	894.5	890.3
37.5°	865.3	856.3	847.3	840.7	836.5	832.2	828.0	823.7
40°	822.6	812.6	802.7	795.6	791.4	787.1	782.9	778.6
42.5°	780.5	770.4	760.3	753.0	748.5	744.1	739.7	735.2
45°	716.1	704.5	692.9	685.0	680.7	676.5	672.2	668.0
47.5°	651.2	639.2	627.2	618.8	614.2	609.5	604.8	600.1
50°	608.2	596.4	584.5	576.4	571.9	567.4	562.9	558.4
52.5°	565.3	553.3	541.2	532.9	528.2	523.5	518.9	514.2
55°	501.9	489.6	477.4	469.0	464.5	460.0	455.5	451.0
57.5°	440.1	427.6	415.1	407.2	403.8	400.4	397.0	393.6
60°	398.8	386.5	374.2	366.1	362.4	358.6	354.8	351.0
62.5°	358.1	346.8	335.4	328.2	325.2	322.2	319.1	316.1
65°	299.8	289.7	279.5	273.0	270.2	267.3	264.5	261.7
67.5°	246.3	237.6	228.8	222.9	219.8	216.6	213.5	210.4
70°	209.9	202.1	194.3	189.2	186.9	184.5	182.1	179.8
72.5°	177.3	170.6	163.9	159.5	157.4	155.2	153.0	150.8
75°	130.6	125.2	119.7	116.3	114.9	113.5	112.0	110.6
77.5°	92.4	89.2	86.0	84.2	83.8	83.4	83.0	82.5
80°	70.9	70.2	69.5	69.0	68.8	68.5	68.3	68.1
82.5°	55.1	54.6	54.1	53.7	53.5	53.2	53.0	52.8
85°	32.0	31.6	31.1	30.8	30.8	30.8	30.8	30.8
87.5°	17.3	17.4	17.5	17.7	18.0	18.3	18.6	18.9
90°	28.7	30.2	31.8	32.8	33.3	33.8	34.3	34.9
92.5°	27.7	29.3	30.8	31.7	31.8	31.9	32.0	32.1
95°	28.7	30.2	31.8	32.7	32.9	33.2	33.4	33.7
97.5°	31.0	31.1	31.3	31.5	31.8	32.0	32.3	32.5
100°	42.3	38.0	33.6	31.5	31.8	32.0	32.3	32.5
102.5°	151.6	104.3	56.9	33.3	33.3	33.4	33.4	33.5
105°	367.2	369.5	371.8	368.3	359.0	349.7	340.5	331.2
107.5°	454.3	455.4	456.5	457.6	458.6	459.6	460.5	461.5
110°	513.5	514.0	514.5	515.1	515.9	516.7	517.5	518.2





TEST NUMBER: P332952

CATALOG NUMBER: S124RDIP-S795D1205U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	570.8	570.7	570.6	571.0	572.0	573.0	574.0	574.9
115°	656.4	656.9	657.4	657.7	657.7	657.7	657.7	657.7
117.5°	742.5	742.4	742.3	742.2	742.1	742.0	741.9	741.8
120°	795.8	796.3	796.8	796.8	796.3	795.8	795.3	794.8
122.5°	848.4	848.7	849.0	848.9	848.4	847.9	847.3	846.8
125°	921.8	922.6	923.4	923.9	924.1	924.4	924.7	924.9
127.5°	994.8	994.6	994.5	994.3	994.1	993.9	993.7	993.5
130°	1039.3	1039.6	1039.8	1039.9	1039.9	1039.9	1039.9	1039.9
132.5°	1083.0	1083.3	1083.5	1083.5	1083.3	1083.1	1082.9	1082.7
135°	1143.2	1143.7	1144.3	1144.8	1145.3	1145.8	1146.3	1146.8
137.5°	1201.0	1201.5	1202.1	1202.3	1202.2	1202.0	1201.8	1201.7
140°	1236.7	1237.5	1238.3	1238.8	1239.0	1239.3	1239.5	1239.8
142.5°	1269.8	1270.3	1270.9	1271.2	1271.3	1271.3	1271.4	1271.4
145°	1317.0	1317.3	1317.5	1317.9	1318.4	1318.9	1319.5	1320.0
147.5°	1358.5	1358.7	1358.9	1359.1	1359.4	1359.7	1359.9	1360.2
150°	1385.0	1385.0	1385.0	1385.2	1385.4	1385.7	1386.0	1386.2
152.5°	1408.2	1408.6	1409.0	1409.1	1409.0	1408.8	1408.7	1408.5
155°	1439.4	1440.4	1441.5	1441.6	1440.8	1440.0	1439.3	1438.5
157.5°	1466.3	1467.6	1469.0	1469.0	1467.6	1466.3	1464.9	1463.6
160°	1483.4	1485.0	1486.5	1486.5	1485.0	1483.4	1481.9	1480.3
162.5°	1497.4	1498.9	1500.5	1500.4	1498.6	1496.9	1495.1	1493.3
165°	1517.0	1519.1	1521.1	1521.0	1518.7	1516.3	1514.0	1511.7
167.5°	1531.4	1533.6	1535.9	1535.7	1533.2	1530.6	1528.0	1525.4
170°	1540.2	1542.3	1544.4	1544.1	1541.5	1538.9	1536.4	1533.8
172.5°	1545.8	1547.9	1549.9	1549.6	1546.8	1544.0	1541.2	1538.4
175°	1552.4	1554.7	1557.0	1556.6	1553.5	1550.4	1547.3	1544.2
177.5°	1555.0	1556.6	1558.3	1557.9	1555.4	1552.9	1550.4	1548.0
180°	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5	1553.5

(END OF REPORT)