

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332652-935

Luminaire Tested: **S124DIP-S1020D1035U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332652-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1020D1035U935-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7522.3 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	58	56	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11599	11599	11599	11599
5°	13661	11629	10264	11629
10°	16356	11579	9241	11579
15°	19351	11462	8487	11462
20°	21549	11342	7814	11342
25°	21896	11166	7349	11166
30°	18632	10997	7202	10997
35°	14325	10723	7203	10723
40°	11166	10400	7339	10400
45°	9310	9914	7462	9914
50°	8194	9323	7714	9323
55°	7506	8612	8025	8612
60°	7035	7976	8399	7976
65°	6550	7265	8709	7265
70°	5986	6559	8908	6559
75°	5346	5774	8799	5774
80°	4482	4733	8522	4733
85°	3307	3418	8160	3418



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.0	1.9
10°-20°	431.5	5.7
20°-30°	684.2	9.1
30°-40°	761.4	10.1
40°-50°	693.1	9.2
50°-60°	566.4	7.5
60°-70°	404.3	5.4
70°-80°	222.6	3.0
80°-90°	64.1	0.9
90°-100°	39.3	0.5
100°-110°	250.6	3.3
110°-120°	479.4	6.4
120°-130°	608.6	8.1
130°-140°	651.1	8.7
140°-150°	608.9	8.1
150°-160°	491.0	6.5
160°-170°	316.7	4.2
170°-180°	109.2	1.5
0°-30°	1255.6	16.7
0°-40°	2017.1	26.8
0°-60°	3276.5	43.6
0°-90°	3967.6	52.7
90°-120°	769.3	10.2
90°-150°	2637.9	35.1
90°-180°	3555.0	47.3
0°-180°	7522.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1437	1437	1437	1437	1437	
5°	1686	1435	1267	1435	1686	171
15°	2315	1371	1016	1371	2315	654
25°	2458	1254	825	1254	2458	1084
35°	1454	1088	731	1088	1454	923
45°	816	868	654	868	816	642
55°	533	612	570	612	533	482
65°	343	380	456	380	343	339
75°	171	185	282	185	171	182
85°	36	37	88	37	36	44
90°	26	3	26	3	26	12
95°	25	47	25	47	25	20
105°	245	259	245	259	245	214
115°	486	483	486	483	486	482
125°	684	679	684	679	684	609
135°	848	842	848	842	848	653
145°	976	971	976	971	976	610
155°	1064	1065	1064	1065	1064	491
165°	1118	1123	1118	1123	1118	316
175°	1142	1149	1142	1149	1142	109
180°	1149	1149	1149	1149	1149	



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1529.2	1528.8	1524.0	1523.0	1519.7	1515.4	1514.5	1506.8	1491.6	1484.5	1482.6
5°	1685.7	1697.5	1682.0	1679.1	1677.3	1657.7	1647.5	1635.6	1608.3	1592.2	1579.7
7.5°	1872.3	1873.7	1867.0	1861.5	1846.3	1829.2	1803.5	1776.2	1743.5	1709.6	1683.9
10°	1995.2	1999.9	1992.2	1991.0	1960.7	1941.6	1903.5	1871.4	1834.4	1793.4	1755.9
12.5°	2124.7	2118.0	2114.1	2088.6	2083.0	2048.2	2004.0	1970.9	1914.0	1866.7	1816.8
15°	2315.4	2302.3	2294.0	2258.8	2241.6	2193.4	2146.3	2110.1	2035.7	1964.8	1911.2
17.5°	2427.2	2440.4	2421.1	2406.7	2362.1	2328.2	2280.2	2204.0	2145.8	2057.8	1990.2
20°	2508.3	2509.4	2498.7	2483.8	2448.7	2405.9	2353.5	2270.1	2200.5	2113.0	2020.2
22.5°	2530.1	2530.4	2525.8	2511.9	2485.4	2450.6	2397.8	2328.2	2243.9	2148.7	2055.9
25°	2458.2	2455.8	2461.3	2476.7	2466.6	2455.8	2425.5	2373.7	2295.2	2194.5	2094.6
27.5°	2191.1	2207.5	2237.7	2275.9	2312.6	2340.5	2348.4	2337.8	2289.1	2206.3	2101.6
30°	1998.7	2019.0	2041.6	2079.7	2153.4	2195.7	2242.2	2277.3	2257.6	2191.6	2094.0
32.5°	1787.3	1792.3	1825.9	1869.2	1936.8	2018.1	2091.7	2163.0	2186.7	2152.1	2070.6
35°	1453.5	1461.8	1498.1	1541.0	1623.8	1723.1	1833.8	1932.7	2014.2	2046.9	2005.3
37.5°	1186.1	1210.0	1235.7	1281.8	1354.6	1444.1	1559.1	1687.0	1808.5	1889.9	1903.8
40°	1059.5	1074.4	1092.8	1127.9	1189.8	1277.9	1376.7	1523.2	1652.3	1769.0	1807.1
42.5°	959.5	968.2	979.5	1011.2	1058.4	1146.0	1236.2	1365.0	1494.7	1634.2	1698.1
45°	815.5	824.4	843.4	861.9	897.6	958.3	1042.2	1148.1	1278.5	1413.1	1530.9
47.5°	711.4	717.1	728.4	748.2	778.5	818.6	886.8	975.3	1096.1	1226.8	1352.3
50°	652.4	657.1	666.1	683.9	707.1	742.8	798.7	881.5	976.1	1107.7	1230.9
52.5°	605.7	607.6	614.2	626.3	644.7	674.8	720.7	789.1	877.1	994.4	1117.1
55°	533.3	535.7	541.7	550.6	566.6	585.7	620.8	672.0	748.8	850.6	957.1
57.5°	473.8	475.4	480.4	483.9	497.1	512.6	539.6	576.2	634.4	720.7	815.8
60°	435.7	434.5	440.5	443.4	452.4	465.5	486.3	521.4	572.0	641.6	729.1
62.5°	398.6	396.9	401.9	405.8	411.0	422.1	439.1	466.7	507.7	570.7	646.3
65°	342.9	340.4	343.5	348.2	352.9	359.0	371.4	395.8	428.5	473.8	531.5
67.5°	286.9	289.4	289.9	292.2	295.0	303.1	311.7	328.9	352.0	388.2	437.1
70°	253.6	254.2	256.6	256.6	258.3	265.4	272.6	282.8	305.3	338.7	378.6
72.5°	220.2	222.7	221.8	223.7	225.0	229.7	235.0	244.6	263.9	288.7	322.4
75°	171.4	173.2	173.2	173.8	175.6	177.4	181.5	188.6	202.3	220.8	244.0
77.5°	125.0	125.3	126.1	128.2	128.2	131.0	134.1	139.9	146.6	159.3	173.4
80°	96.4	97.6	97.0	98.2	98.2	100.6	101.8	108.9	111.9	120.2	131.6
82.5°	70.7	71.9	71.8	73.4	74.4	74.9	76.5	79.4	82.4	89.7	94.4
85°	35.7	36.9	35.7	36.9	38.7	39.3	41.1	41.7	44.1	45.8	50.0
87.5°	15.7	17.0	16.9	17.3	18.2	18.5	18.8	18.1	19.7	20.0	21.6
90°	25.7	25.4	25.1	24.6	24.3	23.5	22.4	21.2	20.1	18.9	17.4
92.5°	23.8	23.7	23.6	23.5	23.4	22.8	21.7	20.5	19.4	18.3	16.7
95°	24.9	24.7	24.5	24.4	24.2	23.5	22.4	21.2	20.1	18.9	18.7
97.5°	24.1	23.8	23.7	23.5	23.3	23.2	23.1	22.9	22.8	22.7	44.0
100°	24.1	23.8	23.7	23.5	23.3	24.8	28.1	31.3	34.6	37.8	64.1
102.5°	24.8	24.7	24.7	24.6	24.6	42.1	77.1	112.2	147.1	182.2	185.6
105°	245.0	251.8	258.7	265.6	272.5	275.0	273.3	271.6	269.9	268.2	267.3
107.5°	341.4	340.7	339.9	339.2	338.5	337.7	336.9	336.0	335.2	334.3	333.0
110°	383.3	382.8	382.2	381.6	381.1	380.6	380.2	379.8	379.4	379.0	377.9



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	425.2	424.6	423.9	423.1	422.4	422.1	422.1	422.2	422.3	422.3	421.8
115°	486.5	486.5	486.5	486.5	486.5	486.3	485.9	485.5	485.2	484.7	484.9
117.5°	548.7	548.8	548.9	549.0	549.1	549.1	549.1	549.2	549.3	549.4	549.0
120°	587.9	588.3	588.7	589.0	589.4	589.4	589.0	588.7	588.3	587.9	588.1
122.5°	626.4	626.8	627.2	627.6	627.9	628.0	627.8	627.6	627.3	627.1	626.8
125°	684.2	684.0	683.8	683.6	683.4	683.0	682.4	681.9	681.3	680.7	681.1
127.5°	734.9	735.0	735.2	735.4	735.5	735.6	735.7	735.9	736.0	736.1	735.2
130°	769.3	769.3	769.3	769.3	769.3	769.1	769.0	768.8	768.6	768.4	767.8
132.5°	800.9	801.1	801.2	801.3	801.5	801.5	801.3	801.1	800.9	800.7	800.0
135°	848.3	847.9	847.6	847.2	846.8	846.4	846.0	845.7	845.2	844.9	844.1
137.5°	888.9	889.0	889.2	889.2	889.3	889.2	888.8	888.4	887.9	887.5	886.7
140°	917.1	916.9	916.7	916.5	916.4	915.9	915.4	914.8	914.2	913.7	913.3
142.5°	940.5	940.5	940.4	940.4	940.3	940.1	939.7	939.3	938.8	938.4	938.1
145°	976.4	976.0	975.6	975.3	974.9	974.6	974.4	974.2	974.0	973.8	973.8
147.5°	1006.2	1006.0	1005.7	1005.6	1005.4	1005.2	1005.0	1004.9	1004.8	1004.6	1004.8
150°	1025.4	1025.2	1025.0	1024.8	1024.6	1024.5	1024.5	1024.5	1024.5	1024.5	1024.8
152.5°	1041.9	1042.0	1042.2	1042.2	1042.3	1042.2	1042.0	1041.6	1041.4	1041.0	1041.4
155°	1064.1	1064.6	1065.2	1065.8	1066.3	1066.3	1065.5	1064.7	1063.9	1063.2	1063.8
157.5°	1082.6	1083.7	1084.6	1085.6	1086.6	1086.6	1085.6	1084.6	1083.7	1082.6	1083.3
160°	1095.0	1096.1	1097.3	1098.5	1099.6	1099.6	1098.5	1097.3	1096.1	1095.0	1095.2
162.5°	1104.7	1106.0	1107.2	1108.5	1109.8	1109.9	1108.8	1107.6	1106.5	1105.4	1105.5
165°	1118.2	1119.9	1121.6	1123.3	1125.1	1125.2	1123.7	1122.1	1120.6	1119.0	1119.0
167.5°	1128.3	1130.2	1132.2	1134.1	1136.0	1136.1	1134.5	1132.7	1131.1	1129.4	1129.5
170°	1134.5	1136.4	1138.4	1140.3	1142.2	1142.4	1140.8	1139.4	1137.8	1136.3	1136.1
172.5°	1138.0	1140.1	1142.1	1144.2	1146.2	1146.5	1145.0	1143.5	1141.9	1140.4	1140.2
175°	1142.3	1144.6	1146.9	1149.2	1151.4	1151.8	1150.0	1148.3	1146.6	1144.9	1144.7
177.5°	1145.0	1146.9	1148.7	1150.6	1152.4	1152.7	1151.4	1150.2	1149.0	1147.8	1147.5
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1483.1	1476.4	1471.6	1467.8	1457.3	1451.1	1446.4	1439.7	1432.1	1424.0	1414.0
5°	1567.2	1547.0	1532.1	1509.5	1488.1	1470.2	1451.7	1435.0	1414.8	1392.8	1376.7
7.5°	1655.6	1625.6	1587.0	1553.5	1515.9	1483.2	1453.9	1423.8	1392.7	1362.4	1334.7
10°	1711.8	1673.2	1630.3	1579.7	1532.1	1489.8	1450.5	1412.5	1375.5	1338.6	1307.1
12.5°	1772.3	1724.1	1660.8	1601.6	1548.3	1491.8	1444.3	1397.7	1353.1	1314.3	1277.6
15°	1853.5	1783.8	1710.6	1631.5	1561.3	1495.2	1430.3	1371.4	1321.4	1270.1	1234.5
17.5°	1903.4	1817.2	1733.5	1650.8	1565.7	1482.5	1412.5	1344.5	1281.9	1231.1	1186.0
20°	1936.2	1850.5	1746.4	1663.6	1562.5	1476.7	1395.8	1320.2	1254.7	1200.6	1154.1
22.5°	1964.8	1865.8	1761.6	1652.7	1552.0	1461.0	1372.4	1296.4	1229.5	1172.4	1127.9
25°	1980.3	1866.6	1753.5	1645.2	1530.9	1423.1	1342.8	1253.5	1182.1	1122.0	1074.4
27.5°	1981.9	1860.4	1732.4	1612.1	1494.1	1393.8	1292.4	1212.5	1138.4	1074.9	1029.2
30°	1976.7	1849.9	1712.4	1582.1	1463.6	1354.7	1266.6	1179.7	1104.1	1041.0	993.4
32.5°	1960.1	1828.0	1686.7	1548.8	1426.0	1319.5	1228.6	1145.9	1072.2	1010.0	960.1
35°	1911.9	1781.5	1630.9	1487.5	1361.8	1254.1	1172.0	1088.0	1014.3	955.3	907.1
37.5°	1836.5	1718.6	1565.6	1417.1	1293.7	1185.5	1104.1	1028.3	961.7	901.9	852.5
40°	1770.7	1667.2	1513.6	1369.0	1235.7	1132.7	1056.5	986.9	920.8	864.3	817.3
42.5°	1695.1	1604.8	1463.2	1309.9	1181.4	1078.0	1003.7	941.2	878.9	826.6	779.6
45°	1560.0	1500.6	1367.2	1225.5	1091.7	994.0	923.2	868.4	816.1	764.8	725.6
47.5°	1404.8	1375.3	1263.1	1128.5	1001.4	905.2	843.8	793.2	747.3	703.9	669.3
50°	1300.5	1286.2	1189.2	1059.5	938.1	847.6	785.7	742.3	702.9	664.9	632.1
52.5°	1197.7	1197.2	1109.7	990.9	878.6	791.4	730.0	689.4	655.3	624.4	595.0
55°	1040.4	1057.1	988.7	882.7	782.1	703.5	648.2	611.9	588.1	562.5	540.4
57.5°	896.0	923.7	867.2	773.9	690.0	617.6	569.4	542.1	516.8	501.3	485.3
60°	801.8	827.9	783.9	705.3	626.2	564.3	518.4	494.0	472.0	461.3	450.0
62.5°	718.0	741.3	708.7	635.8	567.1	507.6	468.9	445.5	430.6	418.9	411.4
65°	598.2	617.9	589.9	536.9	477.9	430.3	398.8	380.3	366.1	361.3	352.9
67.5°	483.5	501.4	486.3	441.3	394.0	358.0	333.3	315.6	307.1	303.0	297.0
70°	415.4	433.3	417.2	378.0	341.6	311.3	288.1	277.9	269.1	267.3	258.9
72.5°	357.8	370.0	354.0	323.2	292.1	266.6	248.6	238.0	233.3	230.1	225.6
75°	268.5	279.1	268.5	244.6	222.6	204.7	189.2	185.1	179.8	178.0	175.0
77.5°	190.0	199.2	191.1	176.2	159.7	145.9	137.6	132.2	131.0	127.9	129.4
80°	145.3	151.2	143.4	133.4	120.2	110.7	104.8	101.8	98.2	97.0	99.4
82.5°	104.3	106.9	103.0	96.2	86.4	80.2	76.2	72.8	72.0	72.2	72.2
85°	54.2	53.6	53.0	47.0	44.1	39.9	37.5	36.9	36.3	37.5	38.7
87.5°	21.3	21.4	20.7	18.4	16.5	14.7	13.8	12.9	13.8	14.7	15.6
90°	15.8	14.3	12.8	11.0	8.9	6.8	4.6	2.6	4.6	6.8	8.9
92.5°	15.2	13.6	12.1	11.3	11.2	11.0	10.9	10.8	10.9	11.0	11.2
95°	18.5	18.3	18.2	21.3	27.8	34.3	40.8	47.3	40.8	34.3	27.8
97.5°	65.3	86.6	108.0	116.6	112.5	108.5	104.4	100.4	104.4	108.5	112.5
100°	90.6	116.9	143.3	154.7	151.3	147.8	144.4	140.9	144.4	147.8	151.3
102.5°	189.1	192.5	196.0	196.4	193.9	191.4	188.9	186.3	188.9	191.4	193.9
105°	266.2	265.3	264.3	263.3	262.2	261.0	259.8	258.7	259.8	261.0	262.2
107.5°	331.7	330.5	329.2	328.2	327.6	327.1	326.5	325.9	326.5	327.1	327.6
110°	376.8	375.6	374.4	373.6	373.0	372.5	371.9	371.3	371.9	372.5	373.0



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	421.3	420.8	420.3	419.5	418.4	417.4	416.4	415.3	416.4	417.4	418.4
115°	485.2	485.3	485.5	485.3	484.7	484.2	483.6	483.0	483.6	484.2	484.7
117.5°	548.5	548.1	547.7	547.2	546.4	545.6	544.8	544.1	544.8	545.6	546.4
120°	588.3	588.5	588.7	588.4	587.6	586.9	586.1	585.3	586.1	586.9	587.6
122.5°	626.5	626.3	626.0	625.7	625.2	624.7	624.3	623.8	624.3	624.7	625.2
125°	681.5	681.9	682.3	682.1	681.3	680.5	679.8	679.0	679.8	680.5	681.3
127.5°	734.3	733.5	732.5	732.0	731.8	731.7	731.4	731.2	731.4	731.7	731.8
130°	767.2	766.7	766.1	765.7	765.5	765.3	765.2	765.0	765.2	765.3	765.5
132.5°	799.3	798.6	797.8	797.3	796.9	796.6	796.3	795.9	796.3	796.6	796.9
135°	843.3	842.6	841.8	841.5	841.7	842.0	842.1	842.3	842.1	842.0	841.7
137.5°	885.9	885.0	884.2	883.7	883.6	883.6	883.5	883.4	883.5	883.6	883.6
140°	912.9	912.5	912.1	911.7	911.4	911.0	910.6	910.2	910.6	911.0	911.4
142.5°	938.0	937.7	937.5	937.0	936.3	935.6	935.0	934.3	935.0	935.6	936.3
145°	973.8	973.8	973.8	973.5	972.9	972.4	971.8	971.2	971.8	972.4	972.9
147.5°	1005.0	1005.1	1005.4	1005.0	1003.8	1002.8	1001.7	1000.7	1001.7	1002.8	1003.8
150°	1024.9	1025.1	1025.3	1025.0	1024.2	1023.5	1022.7	1021.9	1022.7	1023.5	1024.2
152.5°	1041.7	1042.1	1042.4	1042.2	1041.6	1041.0	1040.4	1039.8	1040.4	1041.0	1041.6
155°	1064.4	1065.0	1065.5	1065.7	1065.5	1065.3	1065.1	1065.0	1065.1	1065.3	1065.5
157.5°	1083.9	1084.6	1085.2	1085.6	1085.7	1085.8	1086.0	1086.1	1086.0	1085.8	1085.7
160°	1095.4	1095.6	1095.8	1096.1	1096.7	1097.3	1097.9	1098.5	1097.9	1097.3	1096.7
162.5°	1105.7	1105.9	1106.1	1106.6	1107.2	1108.0	1108.7	1109.5	1108.7	1108.0	1107.2
165°	1119.0	1119.0	1119.0	1119.6	1120.5	1121.5	1122.4	1123.3	1122.4	1121.5	1120.5
167.5°	1129.6	1129.7	1129.9	1130.4	1131.4	1132.4	1133.4	1134.4	1133.4	1132.4	1131.4
170°	1135.9	1135.7	1135.5	1136.0	1137.1	1138.2	1139.4	1140.6	1139.4	1138.2	1137.1
172.5°	1140.1	1139.8	1139.6	1140.1	1141.3	1142.4	1143.6	1144.7	1143.6	1142.4	1141.3
175°	1144.5	1144.3	1144.1	1144.6	1145.7	1146.9	1148.1	1149.2	1148.1	1146.9	1145.7
177.5°	1147.2	1146.9	1146.6	1146.9	1148.1	1149.1	1150.1	1151.2	1150.1	1149.1	1148.1
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1409.2	1405.0	1398.8	1390.2	1383.0	1375.4	1373.6	1370.6	1376.4	1371.6	1370.2
5°	1363.0	1350.6	1334.5	1316.0	1305.3	1289.9	1286.9	1280.9	1275.0	1274.4	1268.4
7.5°	1314.1	1295.8	1274.7	1255.9	1238.5	1221.6	1210.6	1208.2	1199.4	1194.2	1188.3
10°	1282.7	1260.1	1235.7	1217.8	1197.6	1179.7	1167.3	1160.1	1154.1	1147.5	1141.6
12.5°	1245.5	1221.5	1201.4	1182.1	1158.0	1144.4	1123.9	1111.5	1110.3	1110.4	1094.9
15°	1202.3	1178.5	1147.5	1120.2	1107.1	1080.9	1069.6	1055.3	1046.4	1037.4	1030.4
17.5°	1153.0	1123.3	1099.2	1067.7	1042.7	1021.8	1007.0	998.4	985.0	972.3	963.2
20°	1122.0	1090.5	1064.8	1031.5	1004.1	978.5	966.0	954.2	944.0	933.3	923.2
22.5°	1090.5	1057.6	1026.2	993.9	968.5	941.4	929.4	913.2	903.5	897.6	887.4
25°	1041.0	1005.3	969.6	938.7	912.5	888.6	872.6	860.1	849.4	844.6	838.1
27.5°	987.2	951.7	917.2	882.1	852.4	835.1	822.3	812.8	806.7	800.3	797.4
30°	953.0	916.0	879.2	846.4	819.0	801.8	789.9	783.3	778.5	775.6	772.6
32.5°	918.2	881.8	842.9	813.0	788.5	773.2	764.1	757.6	755.2	754.1	753.0
35°	862.5	825.5	789.9	763.1	739.9	733.9	726.2	722.6	721.4	725.6	727.4
37.5°	808.6	774.3	741.4	715.4	700.3	691.6	688.9	689.1	693.3	697.0	701.3
40°	773.8	740.5	709.5	686.9	672.6	667.3	666.1	669.0	673.8	678.0	682.7
42.5°	739.9	707.1	679.0	657.8	647.8	642.9	643.7	646.6	653.3	658.4	665.6
45°	687.5	660.1	632.7	615.4	607.1	608.3	608.3	613.6	620.2	627.9	635.7
47.5°	638.1	610.4	588.0	573.4	569.1	568.1	571.4	578.4	587.8	597.4	608.2
50°	604.8	578.5	558.9	545.8	541.1	542.9	547.6	554.1	565.4	577.4	588.7
52.5°	570.9	547.1	528.9	516.8	513.4	516.7	521.4	531.8	541.7	554.5	568.2
55°	518.4	498.2	483.9	475.0	473.8	475.6	481.0	492.2	506.5	522.6	535.7
57.5°	466.1	449.3	436.2	430.0	430.6	432.2	441.1	454.5	469.8	486.9	503.8
60°	430.9	415.4	404.8	400.0	400.5	404.2	414.8	427.4	446.4	463.0	481.0
62.5°	397.6	384.0	373.8	369.5	368.7	376.5	386.8	399.8	418.8	437.4	456.7
65°	344.1	333.3	325.0	322.6	324.4	330.4	343.5	360.7	376.8	396.4	416.6
67.5°	291.6	282.8	277.2	278.2	280.3	289.1	300.1	315.0	333.2	353.5	373.6
70°	258.3	249.9	245.2	245.8	249.4	260.1	269.7	284.5	304.2	325.0	341.6
72.5°	224.0	218.5	214.3	216.8	220.3	227.7	239.6	254.5	271.8	291.2	308.8
75°	172.0	172.0	169.6	171.4	176.8	183.9	192.9	208.4	225.6	241.1	255.4
77.5°	127.6	126.3	127.9	130.0	133.1	141.5	151.8	162.8	175.8	191.3	203.1
80°	97.6	98.2	101.2	104.8	106.0	112.5	123.2	133.4	143.4	156.5	167.8
82.5°	73.4	74.0	75.5	80.0	81.2	88.3	95.1	105.2	114.4	123.2	132.6
85°	39.9	39.9	42.9	44.6	47.6	52.3	56.6	62.5	70.9	76.8	85.7
87.5°	17.4	17.8	20.0	21.3	23.0	25.7	26.9	32.4	34.4	37.1	41.5
90°	11.0	12.8	14.3	15.8	17.4	18.9	20.1	21.2	22.4	23.5	24.3
92.5°	11.3	12.1	13.6	15.2	16.7	18.3	19.4	20.5	21.7	22.8	23.4
95°	21.3	18.2	18.3	18.5	18.7	18.9	20.1	21.2	22.4	23.5	24.2
97.5°	116.6	108.0	86.6	65.3	44.0	22.7	22.8	22.9	23.1	23.2	23.3
100°	154.7	143.3	116.9	90.6	64.1	37.8	34.6	31.3	28.1	24.8	23.3
102.5°	196.4	196.0	192.5	189.1	185.6	182.2	147.1	112.2	77.1	42.1	24.6
105°	263.3	264.3	265.3	266.2	267.3	268.2	269.9	271.6	273.3	275.0	272.5
107.5°	328.2	329.2	330.5	331.7	333.0	334.3	335.2	336.0	336.9	337.7	338.5
110°	373.6	374.4	375.6	376.8	377.9	379.0	379.4	379.8	380.2	380.6	381.1



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	419.5	420.3	420.8	421.3	421.8	422.3	422.3	422.2	422.1	422.1	422.4
115°	485.3	485.5	485.3	485.2	484.9	484.7	485.2	485.5	485.9	486.3	486.5
117.5°	547.2	547.7	548.1	548.5	549.0	549.4	549.3	549.2	549.1	549.1	549.1
120°	588.4	588.7	588.5	588.3	588.1	587.9	588.3	588.7	589.0	589.4	589.4
122.5°	625.7	626.0	626.3	626.5	626.8	627.1	627.3	627.6	627.8	628.0	627.9
125°	682.1	682.3	681.9	681.5	681.1	680.7	681.3	681.9	682.4	683.0	683.4
127.5°	732.0	732.5	733.5	734.3	735.2	736.1	736.0	735.9	735.7	735.6	735.5
130°	765.7	766.1	766.7	767.2	767.8	768.4	768.6	768.8	769.0	769.1	769.3
132.5°	797.3	797.8	798.6	799.3	800.0	800.7	800.9	801.1	801.3	801.5	801.5
135°	841.5	841.8	842.6	843.3	844.1	844.9	845.2	845.7	846.0	846.4	846.8
137.5°	883.7	884.2	885.0	885.9	886.7	887.5	887.9	888.4	888.8	889.2	889.3
140°	911.7	912.1	912.5	912.9	913.3	913.7	914.2	914.8	915.4	915.9	916.4
142.5°	937.0	937.5	937.7	938.0	938.1	938.4	938.8	939.3	939.7	940.1	940.3
145°	973.5	973.8	973.8	973.8	973.8	973.8	974.0	974.2	974.4	974.6	974.9
147.5°	1005.0	1005.4	1005.1	1005.0	1004.8	1004.6	1004.8	1004.9	1005.0	1005.2	1005.4
150°	1025.0	1025.3	1025.1	1024.9	1024.8	1024.5	1024.5	1024.5	1024.5	1024.5	1024.6
152.5°	1042.2	1042.4	1042.1	1041.7	1041.4	1041.0	1041.4	1041.6	1042.0	1042.2	1042.3
155°	1065.7	1065.5	1065.0	1064.4	1063.8	1063.2	1063.9	1064.7	1065.5	1066.3	1066.3
157.5°	1085.6	1085.2	1084.6	1083.9	1083.3	1082.6	1083.7	1084.6	1085.6	1086.6	1086.6
160°	1096.1	1095.8	1095.6	1095.4	1095.2	1095.0	1096.1	1097.3	1098.5	1099.6	1099.6
162.5°	1106.6	1106.1	1105.9	1105.7	1105.5	1105.4	1106.5	1107.6	1108.8	1109.9	1109.8
165°	1119.6	1119.0	1119.0	1119.0	1119.0	1119.0	1120.6	1122.1	1123.7	1125.2	1125.1
167.5°	1130.4	1129.9	1129.7	1129.6	1129.5	1129.4	1131.1	1132.7	1134.5	1136.1	1136.0
170°	1136.0	1135.5	1135.7	1135.9	1136.1	1136.3	1137.8	1139.4	1140.8	1142.4	1142.2
172.5°	1140.1	1139.6	1139.8	1140.1	1140.2	1140.4	1141.9	1143.5	1145.0	1146.5	1146.2
175°	1144.6	1144.1	1144.3	1144.5	1144.7	1144.9	1146.6	1148.3	1150.0	1151.8	1151.4
177.5°	1146.9	1146.6	1146.9	1147.2	1147.5	1147.8	1149.0	1150.2	1151.4	1152.7	1152.4
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1369.2	1368.3	1364.9	1364.5	1364.9	1368.3	1369.2	1370.2	1371.6	1376.4	1370.6
5°	1264.8	1261.9	1260.1	1266.6	1260.1	1261.9	1264.8	1268.4	1274.4	1275.0	1280.9
7.5°	1186.1	1183.8	1178.5	1176.9	1178.5	1183.8	1186.1	1188.3	1194.2	1199.4	1208.2
10°	1135.7	1133.2	1128.5	1127.3	1128.5	1133.2	1135.7	1141.6	1147.5	1154.1	1160.1
12.5°	1087.1	1082.4	1081.4	1082.5	1081.4	1082.4	1087.1	1094.9	1110.4	1110.3	1111.5
15°	1022.6	1020.2	1013.7	1015.5	1013.7	1020.2	1022.6	1030.4	1037.4	1046.4	1055.3
17.5°	959.0	956.1	948.2	955.2	948.2	956.1	959.0	963.2	972.3	985.0	998.4
20°	919.0	914.2	910.1	909.5	910.1	914.2	919.0	923.2	933.3	944.0	954.2
22.5°	880.9	876.7	876.2	872.4	876.2	876.7	880.9	887.4	897.6	903.5	913.2
25°	833.3	829.1	827.9	825.0	827.9	829.1	833.3	838.1	844.6	849.4	860.1
27.5°	796.8	794.7	792.6	793.5	792.6	794.7	796.8	797.4	800.3	806.7	812.8
30°	774.4	773.8	772.6	772.6	772.6	773.8	774.4	772.6	775.6	778.5	783.3
32.5°	755.8	755.7	756.4	756.4	756.4	755.7	755.8	753.0	754.1	755.2	757.6
35°	729.7	731.5	732.7	730.9	732.7	731.5	729.7	727.4	725.6	721.4	722.6
37.5°	706.2	707.9	709.6	711.6	709.6	707.9	706.2	701.3	697.0	693.3	689.1
40°	688.0	692.2	693.4	696.4	693.4	692.2	688.0	682.7	678.0	673.8	669.0
42.5°	670.9	675.5	678.6	679.2	678.6	675.5	670.9	665.6	658.4	653.3	646.6
45°	644.6	649.4	653.6	653.6	653.6	649.4	644.6	635.7	627.9	620.2	613.6
47.5°	617.3	624.2	628.4	629.5	628.4	624.2	617.3	608.2	597.4	587.8	578.4
50°	598.8	607.1	611.3	614.2	611.3	607.1	598.8	588.7	577.4	565.4	554.1
52.5°	580.7	589.0	594.6	596.2	594.6	589.0	580.7	568.2	554.5	541.7	531.8
55°	549.4	561.3	567.8	570.2	567.8	561.3	549.4	535.7	522.6	506.5	492.2
57.5°	519.9	530.8	538.5	540.2	538.5	530.8	519.9	503.8	486.9	469.8	454.5
60°	497.0	508.9	518.4	520.2	518.4	508.9	497.0	481.0	463.0	446.4	427.4
62.5°	473.6	486.0	494.6	499.3	494.6	486.0	473.6	456.7	437.4	418.8	399.8
65°	433.3	445.8	454.2	455.9	454.2	445.8	433.3	416.6	396.4	376.8	360.7
67.5°	389.3	401.7	407.3	410.7	407.3	401.7	389.3	373.6	353.5	333.2	315.0
70°	358.3	368.4	374.4	377.4	374.4	368.4	358.3	341.6	325.0	304.2	284.5
72.5°	323.0	333.6	340.6	341.2	340.6	333.6	323.0	308.8	291.2	271.8	254.5
75°	269.1	278.5	282.1	282.1	282.1	278.5	269.1	255.4	241.1	225.6	208.4
77.5°	212.9	217.8	222.4	223.3	222.4	217.8	212.9	203.1	191.3	175.8	162.8
80°	176.8	179.8	183.3	183.3	183.3	179.8	176.8	167.8	156.5	143.4	133.4
82.5°	139.7	142.2	145.7	145.3	145.7	142.2	139.7	132.6	123.2	114.4	105.2
85°	84.6	89.9	89.3	88.1	89.3	89.9	84.6	85.7	76.8	70.9	62.5
87.5°	43.0	43.6	45.1	46.1	45.1	43.6	43.0	41.5	37.1	34.4	32.4
90°	24.6	25.1	25.4	25.7	25.4	25.1	24.6	24.3	23.5	22.4	21.2
92.5°	23.5	23.6	23.7	23.8	23.7	23.6	23.5	23.4	22.8	21.7	20.5
95°	24.4	24.5	24.7	24.9	24.7	24.5	24.4	24.2	23.5	22.4	21.2
97.5°	23.5	23.7	23.8	24.1	23.8	23.7	23.5	23.3	23.2	23.1	22.9
100°	23.5	23.7	23.8	24.1	23.8	23.7	23.5	23.3	24.8	28.1	31.3
102.5°	24.6	24.7	24.7	24.8	24.7	24.7	24.6	24.6	42.1	77.1	112.2
105°	265.6	258.7	251.8	245.0	251.8	258.7	265.6	272.5	275.0	273.3	271.6
107.5°	339.2	339.9	340.7	341.4	340.7	339.9	339.2	338.5	337.7	336.9	336.0
110°	381.6	382.2	382.8	383.3	382.8	382.2	381.6	381.1	380.6	380.2	379.8



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	423.1	423.9	424.6	425.2	424.6	423.9	423.1	422.4	422.1	422.1	422.2
115°	486.5	486.5	486.5	486.5	486.5	486.5	486.5	486.5	486.3	485.9	485.5
117.5°	549.0	548.9	548.8	548.7	548.8	548.9	549.0	549.1	549.1	549.1	549.2
120°	589.0	588.7	588.3	587.9	588.3	588.7	589.0	589.4	589.4	589.0	588.7
122.5°	627.6	627.2	626.8	626.4	626.8	627.2	627.6	627.9	628.0	627.8	627.6
125°	683.6	683.8	684.0	684.2	684.0	683.8	683.6	683.4	683.0	682.4	681.9
127.5°	735.4	735.2	735.0	734.9	735.0	735.2	735.4	735.5	735.6	735.7	735.9
130°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.1	769.0	768.8
132.5°	801.3	801.2	801.1	800.9	801.1	801.2	801.3	801.5	801.5	801.3	801.1
135°	847.2	847.6	847.9	848.3	847.9	847.6	847.2	846.8	846.4	846.0	845.7
137.5°	889.2	889.2	889.0	888.9	889.0	889.2	889.2	889.3	889.2	888.8	888.4
140°	916.5	916.7	916.9	917.1	916.9	916.7	916.5	916.4	915.9	915.4	914.8
142.5°	940.4	940.4	940.5	940.5	940.5	940.4	940.4	940.3	940.1	939.7	939.3
145°	975.3	975.6	976.0	976.4	976.0	975.6	975.3	974.9	974.6	974.4	974.2
147.5°	1005.6	1005.7	1006.0	1006.2	1006.0	1005.7	1005.6	1005.4	1005.2	1005.0	1004.9
150°	1024.8	1025.0	1025.2	1025.4	1025.2	1025.0	1024.8	1024.6	1024.5	1024.5	1024.5
152.5°	1042.2	1042.2	1042.0	1041.9	1042.0	1042.2	1042.2	1042.3	1042.2	1042.0	1041.6
155°	1065.8	1065.2	1064.6	1064.1	1064.6	1065.2	1065.8	1066.3	1066.3	1065.5	1064.7
157.5°	1085.6	1084.6	1083.7	1082.6	1083.7	1084.6	1085.6	1086.6	1086.6	1085.6	1084.6
160°	1098.5	1097.3	1096.1	1095.0	1096.1	1097.3	1098.5	1099.6	1099.6	1098.5	1097.3
162.5°	1108.5	1107.2	1106.0	1104.7	1106.0	1107.2	1108.5	1109.8	1109.9	1108.8	1107.6
165°	1123.3	1121.6	1119.9	1118.2	1119.9	1121.6	1123.3	1125.1	1125.2	1123.7	1122.1
167.5°	1134.1	1132.2	1130.2	1128.3	1130.2	1132.2	1134.1	1136.0	1136.1	1134.5	1132.7
170°	1140.3	1138.4	1136.4	1134.5	1136.4	1138.4	1140.3	1142.2	1142.4	1140.8	1139.4
172.5°	1144.2	1142.1	1140.1	1138.0	1140.1	1142.1	1144.2	1146.2	1146.5	1145.0	1143.5
175°	1149.2	1146.9	1144.6	1142.3	1144.6	1146.9	1149.2	1151.4	1151.8	1150.0	1148.3
177.5°	1150.6	1148.7	1146.9	1145.0	1146.9	1148.7	1150.6	1152.4	1152.7	1151.4	1150.2
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1373.6	1375.4	1383.0	1390.2	1398.8	1405.0	1409.2	1414.0	1424.0	1432.1	1439.7
5°	1286.9	1289.9	1305.3	1316.0	1334.5	1350.6	1363.0	1376.7	1392.8	1414.8	1435.0
7.5°	1210.6	1221.6	1238.5	1255.9	1274.7	1295.8	1314.1	1334.7	1362.4	1392.7	1423.8
10°	1167.3	1179.7	1197.6	1217.8	1235.7	1260.1	1282.7	1307.1	1338.6	1375.5	1412.5
12.5°	1123.9	1144.4	1158.0	1182.1	1201.4	1221.5	1245.5	1277.6	1314.3	1353.1	1397.7
15°	1069.6	1080.9	1107.1	1120.2	1147.5	1178.5	1202.3	1234.5	1270.1	1321.4	1371.4
17.5°	1007.0	1021.8	1042.7	1067.7	1099.2	1123.3	1153.0	1186.0	1231.1	1281.9	1344.5
20°	966.0	978.5	1004.1	1031.5	1064.8	1090.5	1122.0	1154.1	1200.6	1254.7	1320.2
22.5°	929.4	941.4	968.5	993.9	1026.2	1057.6	1090.5	1127.9	1172.4	1229.5	1296.4
25°	872.6	888.6	912.5	938.7	969.6	1005.3	1041.0	1074.4	1122.0	1182.1	1253.5
27.5°	822.3	835.1	852.4	882.1	917.2	951.7	987.2	1029.2	1074.9	1138.4	1212.5
30°	789.9	801.8	819.0	846.4	879.2	916.0	953.0	993.4	1041.0	1104.1	1179.7
32.5°	764.1	773.2	788.5	813.0	842.9	881.8	918.2	960.1	1010.0	1072.2	1145.9
35°	726.2	733.9	739.9	763.1	789.9	825.5	862.5	907.1	955.3	1014.3	1088.0
37.5°	688.9	691.6	700.3	715.4	741.4	774.3	808.6	852.5	901.9	961.7	1028.3
40°	666.1	667.3	672.6	686.9	709.5	740.5	773.8	817.3	864.3	920.8	986.9
42.5°	643.7	642.9	647.8	657.8	679.0	707.1	739.9	779.6	826.6	878.9	941.2
45°	608.3	608.3	607.1	615.4	632.7	660.1	687.5	725.6	764.8	816.1	868.4
47.5°	571.4	568.1	569.1	573.4	588.0	610.4	638.1	669.3	703.9	747.3	793.2
50°	547.6	542.9	541.1	545.8	558.9	578.5	604.8	632.1	664.9	702.9	742.3
52.5°	521.4	516.7	513.4	516.8	528.9	547.1	570.9	595.0	624.4	655.3	689.4
55°	481.0	475.6	473.8	475.0	483.9	498.2	518.4	540.4	562.5	588.1	611.9
57.5°	441.1	432.2	430.6	430.0	436.2	449.3	466.1	485.3	501.3	516.8	542.1
60°	414.8	404.2	400.5	400.0	404.8	415.4	430.9	450.0	461.3	472.0	494.0
62.5°	386.8	376.5	368.7	369.5	373.8	384.0	397.6	411.4	418.9	430.6	445.5
65°	343.5	330.4	324.4	322.6	325.0	333.3	344.1	352.9	361.3	366.1	380.3
67.5°	300.1	289.1	280.3	278.2	277.2	282.8	291.6	297.0	303.0	307.1	315.6
70°	269.7	260.1	249.4	245.8	245.2	249.9	258.3	258.9	267.3	269.1	277.9
72.5°	239.6	227.7	220.3	216.8	214.3	218.5	224.0	225.6	230.1	233.3	238.0
75°	192.9	183.9	176.8	171.4	169.6	172.0	172.0	175.0	178.0	179.8	185.1
77.5°	151.8	141.5	133.1	130.0	127.9	126.3	127.6	129.4	127.9	131.0	132.2
80°	123.2	112.5	106.0	104.8	101.2	98.2	97.6	99.4	97.0	98.2	101.8
82.5°	95.1	88.3	81.2	80.0	75.5	74.0	73.4	72.2	72.2	72.0	72.8
85°	56.6	52.3	47.6	44.6	42.9	39.9	39.9	38.7	37.5	36.3	36.9
87.5°	26.9	25.7	23.0	21.3	20.0	17.8	17.4	15.6	14.7	13.8	12.9
90°	20.1	18.9	17.4	15.8	14.3	12.8	11.0	8.9	6.8	4.6	2.6
92.5°	19.4	18.3	16.7	15.2	13.6	12.1	11.3	11.2	11.0	10.9	10.8
95°	20.1	18.9	18.7	18.5	18.3	18.2	21.3	27.8	34.3	40.8	47.3
97.5°	22.8	22.7	44.0	65.3	86.6	108.0	116.6	112.5	108.5	104.4	100.4
100°	34.6	37.8	64.1	90.6	116.9	143.3	154.7	151.3	147.8	144.4	140.9
102.5°	147.1	182.2	185.6	189.1	192.5	196.0	196.4	193.9	191.4	188.9	186.3
105°	269.9	268.2	267.3	266.2	265.3	264.3	263.3	262.2	261.0	259.8	258.7
107.5°	335.2	334.3	333.0	331.7	330.5	329.2	328.2	327.6	327.1	326.5	325.9
110°	379.4	379.0	377.9	376.8	375.6	374.4	373.6	373.0	372.5	371.9	371.3



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	422.3	422.3	421.8	421.3	420.8	420.3	419.5	418.4	417.4	416.4	415.3
115°	485.2	484.7	484.9	485.2	485.3	485.5	485.3	484.7	484.2	483.6	483.0
117.5°	549.3	549.4	549.0	548.5	548.1	547.7	547.2	546.4	545.6	544.8	544.1
120°	588.3	587.9	588.1	588.3	588.5	588.7	588.4	587.6	586.9	586.1	585.3
122.5°	627.3	627.1	626.8	626.5	626.3	626.0	625.7	625.2	624.7	624.3	623.8
125°	681.3	680.7	681.1	681.5	681.9	682.3	682.1	681.3	680.5	679.8	679.0
127.5°	736.0	736.1	735.2	734.3	733.5	732.5	732.0	731.8	731.7	731.4	731.2
130°	768.6	768.4	767.8	767.2	766.7	766.1	765.7	765.5	765.3	765.2	765.0
132.5°	800.9	800.7	800.0	799.3	798.6	797.8	797.3	796.9	796.6	796.3	795.9
135°	845.2	844.9	844.1	843.3	842.6	841.8	841.5	841.7	842.0	842.1	842.3
137.5°	887.9	887.5	886.7	885.9	885.0	884.2	883.7	883.6	883.6	883.5	883.4
140°	914.2	913.7	913.3	912.9	912.5	912.1	911.7	911.4	911.0	910.6	910.2
142.5°	938.8	938.4	938.1	938.0	937.7	937.5	937.0	936.3	935.6	935.0	934.3
145°	974.0	973.8	973.8	973.8	973.8	973.8	973.5	972.9	972.4	971.8	971.2
147.5°	1004.8	1004.6	1004.8	1005.0	1005.1	1005.4	1005.0	1003.8	1002.8	1001.7	1000.7
150°	1024.5	1024.5	1024.8	1024.9	1025.1	1025.3	1025.0	1024.2	1023.5	1022.7	1021.9
152.5°	1041.4	1041.0	1041.4	1041.7	1042.1	1042.4	1042.2	1041.6	1041.0	1040.4	1039.8
155°	1063.9	1063.2	1063.8	1064.4	1065.0	1065.5	1065.7	1065.5	1065.3	1065.1	1065.0
157.5°	1083.7	1082.6	1083.3	1083.9	1084.6	1085.2	1085.6	1085.7	1085.8	1086.0	1086.1
160°	1096.1	1095.0	1095.2	1095.4	1095.6	1095.8	1096.1	1096.7	1097.3	1097.9	1098.5
162.5°	1106.5	1105.4	1105.5	1105.7	1105.9	1106.1	1106.6	1107.2	1108.0	1108.7	1109.5
165°	1120.6	1119.0	1119.0	1119.0	1119.0	1119.0	1119.6	1120.5	1121.5	1122.4	1123.3
167.5°	1131.1	1129.4	1129.5	1129.6	1129.7	1129.9	1130.4	1131.4	1132.4	1133.4	1134.4
170°	1137.8	1136.3	1136.1	1135.9	1135.7	1135.5	1136.0	1137.1	1138.2	1139.4	1140.6
172.5°	1141.9	1140.4	1140.2	1140.1	1139.8	1139.6	1140.1	1141.3	1142.4	1143.6	1144.7
175°	1146.6	1144.9	1144.7	1144.5	1144.3	1144.1	1144.6	1145.7	1146.9	1148.1	1149.2
177.5°	1149.0	1147.8	1147.5	1147.2	1146.9	1146.6	1146.9	1148.1	1149.1	1150.1	1151.2
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1446.4	1451.1	1457.3	1467.8	1471.6	1476.4	1483.1	1482.6	1484.5	1491.6	1506.8
5°	1451.7	1470.2	1488.1	1509.5	1532.1	1547.0	1567.2	1579.7	1592.2	1608.3	1635.6
7.5°	1453.9	1483.2	1515.9	1553.5	1587.0	1625.6	1655.6	1683.9	1709.6	1743.5	1776.2
10°	1450.5	1489.8	1532.1	1579.7	1630.3	1673.2	1711.8	1755.9	1793.4	1834.4	1871.4
12.5°	1444.3	1491.8	1548.3	1601.6	1660.8	1724.1	1772.3	1816.8	1866.7	1914.0	1970.9
15°	1430.3	1495.2	1561.3	1631.5	1710.6	1783.8	1853.5	1911.2	1964.8	2035.7	2110.1
17.5°	1412.5	1482.5	1565.7	1650.8	1733.5	1817.2	1903.4	1990.2	2057.8	2145.8	2204.0
20°	1395.8	1476.7	1562.5	1663.6	1746.4	1850.5	1936.2	2020.2	2113.0	2200.5	2270.1
22.5°	1372.4	1461.0	1552.0	1652.7	1761.6	1865.8	1964.8	2055.9	2148.7	2243.9	2328.2
25°	1342.8	1423.1	1530.9	1645.2	1753.5	1866.6	1980.3	2094.6	2194.5	2295.2	2373.7
27.5°	1292.4	1393.8	1494.1	1612.1	1732.4	1860.4	1981.9	2101.6	2206.3	2289.1	2337.8
30°	1266.6	1354.7	1463.6	1582.1	1712.4	1849.9	1976.7	2094.0	2191.6	2257.6	2277.3
32.5°	1228.6	1319.5	1426.0	1548.8	1686.7	1828.0	1960.1	2070.6	2152.1	2186.7	2163.0
35°	1172.0	1254.1	1361.8	1487.5	1630.9	1781.5	1911.9	2005.3	2046.9	2014.2	1932.7
37.5°	1104.1	1185.5	1293.7	1417.1	1565.6	1718.6	1836.5	1903.8	1889.9	1808.5	1687.0
40°	1056.5	1132.7	1235.7	1369.0	1513.6	1667.2	1770.7	1807.1	1769.0	1652.3	1523.2
42.5°	1003.7	1078.0	1181.4	1309.9	1463.2	1604.8	1695.1	1698.1	1634.2	1494.7	1365.0
45°	923.2	994.0	1091.7	1225.5	1367.2	1500.6	1560.0	1530.9	1413.1	1278.5	1148.1
47.5°	843.8	905.2	1001.4	1128.5	1263.1	1375.3	1404.8	1352.3	1226.8	1096.1	975.3
50°	785.7	847.6	938.1	1059.5	1189.2	1286.2	1300.5	1230.9	1107.7	976.1	881.5
52.5°	730.0	791.4	878.6	990.9	1109.7	1197.2	1197.7	1117.1	994.4	877.1	789.1
55°	648.2	703.5	782.1	882.7	988.7	1057.1	1040.4	957.1	850.6	748.8	672.0
57.5°	569.4	617.6	690.0	773.9	867.2	923.7	896.0	815.8	720.7	634.4	576.2
60°	518.4	564.3	626.2	705.3	783.9	827.9	801.8	729.1	641.6	572.0	521.4
62.5°	468.9	507.6	567.1	635.8	708.7	741.3	718.0	646.3	570.7	507.7	466.7
65°	398.8	430.3	477.9	536.9	589.9	617.9	598.2	531.5	473.8	428.5	395.8
67.5°	333.3	358.0	394.0	441.3	486.3	501.4	483.5	437.1	388.2	352.0	328.9
70°	288.1	311.3	341.6	378.0	417.2	433.3	415.4	378.6	338.7	305.3	282.8
72.5°	248.6	266.6	292.1	323.2	354.0	370.0	357.8	322.4	288.7	263.9	244.6
75°	189.2	204.7	222.6	244.6	268.5	279.1	268.5	244.0	220.8	202.3	188.6
77.5°	137.6	145.9	159.7	176.2	191.1	199.2	190.0	173.4	159.3	146.6	139.9
80°	104.8	110.7	120.2	133.4	143.4	151.2	145.3	131.6	120.2	111.9	108.9
82.5°	76.2	80.2	86.4	96.2	103.0	106.9	104.3	94.4	89.7	82.4	79.4
85°	37.5	39.9	44.1	47.0	53.0	53.6	54.2	50.0	45.8	44.1	41.7
87.5°	13.8	14.7	16.5	18.4	20.7	21.4	21.3	21.6	20.0	19.7	18.1
90°	4.6	6.8	8.9	11.0	12.8	14.3	15.8	17.4	18.9	20.1	21.2
92.5°	10.9	11.0	11.2	11.3	12.1	13.6	15.2	16.7	18.3	19.4	20.5
95°	40.8	34.3	27.8	21.3	18.2	18.3	18.5	18.7	18.9	20.1	21.2
97.5°	104.4	108.5	112.5	116.6	108.0	86.6	65.3	44.0	22.7	22.8	22.9
100°	144.4	147.8	151.3	154.7	143.3	116.9	90.6	64.1	37.8	34.6	31.3
102.5°	188.9	191.4	193.9	196.4	196.0	192.5	189.1	185.6	182.2	147.1	112.2
105°	259.8	261.0	262.2	263.3	264.3	265.3	266.2	267.3	268.2	269.9	271.6
107.5°	326.5	327.1	327.6	328.2	329.2	330.5	331.7	333.0	334.3	335.2	336.0
110°	371.9	372.5	373.0	373.6	374.4	375.6	376.8	377.9	379.0	379.4	379.8



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	416.4	417.4	418.4	419.5	420.3	420.8	421.3	421.8	422.3	422.3	422.2
115°	483.6	484.2	484.7	485.3	485.5	485.3	485.2	484.9	484.7	485.2	485.5
117.5°	544.8	545.6	546.4	547.2	547.7	548.1	548.5	549.0	549.4	549.3	549.2
120°	586.1	586.9	587.6	588.4	588.7	588.5	588.3	588.1	587.9	588.3	588.7
122.5°	624.3	624.7	625.2	625.7	626.0	626.3	626.5	626.8	627.1	627.3	627.6
125°	679.8	680.5	681.3	682.1	682.3	681.9	681.5	681.1	680.7	681.3	681.9
127.5°	731.4	731.7	731.8	732.0	732.5	733.5	734.3	735.2	736.1	736.0	735.9
130°	765.2	765.3	765.5	765.7	766.1	766.7	767.2	767.8	768.4	768.6	768.8
132.5°	796.3	796.6	796.9	797.3	797.8	798.6	799.3	800.0	800.7	800.9	801.1
135°	842.1	842.0	841.7	841.5	841.8	842.6	843.3	844.1	844.9	845.2	845.7
137.5°	883.5	883.6	883.6	883.7	884.2	885.0	885.9	886.7	887.5	887.9	888.4
140°	910.6	911.0	911.4	911.7	912.1	912.5	912.9	913.3	913.7	914.2	914.8
142.5°	935.0	935.6	936.3	937.0	937.5	937.7	938.0	938.1	938.4	938.8	939.3
145°	971.8	972.4	972.9	973.5	973.8	973.8	973.8	973.8	973.8	974.0	974.2
147.5°	1001.7	1002.8	1003.8	1005.0	1005.4	1005.1	1005.0	1004.8	1004.6	1004.8	1004.9
150°	1022.7	1023.5	1024.2	1025.0	1025.3	1025.1	1024.9	1024.8	1024.5	1024.5	1024.5
152.5°	1040.4	1041.0	1041.6	1042.2	1042.4	1042.1	1041.7	1041.4	1041.0	1041.4	1041.6
155°	1065.1	1065.3	1065.5	1065.7	1065.5	1065.0	1064.4	1063.8	1063.2	1063.9	1064.7
157.5°	1086.0	1085.8	1085.7	1085.6	1085.2	1084.6	1083.9	1083.3	1082.6	1083.7	1084.6
160°	1097.9	1097.3	1096.7	1096.1	1095.8	1095.6	1095.4	1095.2	1095.0	1096.1	1097.3
162.5°	1108.7	1108.0	1107.2	1106.6	1106.1	1105.9	1105.7	1105.5	1105.4	1106.5	1107.6
165°	1122.4	1121.5	1120.5	1119.6	1119.0	1119.0	1119.0	1119.0	1119.0	1120.6	1122.1
167.5°	1133.4	1132.4	1131.4	1130.4	1129.9	1129.7	1129.6	1129.5	1129.4	1131.1	1132.7
170°	1139.4	1138.2	1137.1	1136.0	1135.5	1135.7	1135.9	1136.1	1136.3	1137.8	1139.4
172.5°	1143.6	1142.4	1141.3	1140.1	1139.6	1139.8	1140.1	1140.2	1140.4	1141.9	1143.5
175°	1148.1	1146.9	1145.7	1144.6	1144.1	1144.3	1144.5	1144.7	1144.9	1146.6	1148.3
177.5°	1150.1	1149.1	1148.1	1146.9	1146.6	1146.9	1147.2	1147.5	1147.8	1149.0	1150.2
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1514.5	1515.4	1519.7	1523.0	1524.0	1528.8	1529.2
5°	1647.5	1657.7	1677.3	1679.1	1682.0	1697.5	1685.7
7.5°	1803.5	1829.2	1846.3	1861.5	1867.0	1873.7	1872.3
10°	1903.5	1941.6	1960.7	1991.0	1992.2	1999.9	1995.2
12.5°	2004.0	2048.2	2083.0	2088.6	2114.1	2118.0	2124.7
15°	2146.3	2193.4	2241.6	2258.8	2294.0	2302.3	2315.4
17.5°	2280.2	2328.2	2362.1	2406.7	2421.1	2440.4	2427.2
20°	2353.5	2405.9	2448.7	2483.8	2498.7	2509.4	2508.3
22.5°	2397.8	2450.6	2485.4	2511.9	2525.8	2530.4	2530.1
25°	2425.5	2455.8	2466.6	2476.7	2461.3	2455.8	2458.2
27.5°	2348.4	2340.5	2312.6	2275.9	2237.7	2207.5	2191.1
30°	2242.2	2195.7	2153.4	2079.7	2041.6	2019.0	1998.7
32.5°	2091.7	2018.1	1936.8	1869.2	1825.9	1792.3	1787.3
35°	1833.8	1723.1	1623.8	1541.0	1498.1	1461.8	1453.5
37.5°	1559.1	1444.1	1354.6	1281.8	1235.7	1210.0	1186.1
40°	1376.7	1277.9	1189.8	1127.9	1092.8	1074.4	1059.5
42.5°	1236.2	1146.0	1058.4	1011.2	979.5	968.2	959.5
45°	1042.2	958.3	897.6	861.9	843.4	824.4	815.5
47.5°	886.8	818.6	778.5	748.2	728.4	717.1	711.4
50°	798.7	742.8	707.1	683.9	666.1	657.1	652.4
52.5°	720.7	674.8	644.7	626.3	614.2	607.6	605.7
55°	620.8	585.7	566.6	550.6	541.7	535.7	533.3
57.5°	539.6	512.6	497.1	483.9	480.4	475.4	473.8
60°	486.3	465.5	452.4	443.4	440.5	434.5	435.7
62.5°	439.1	422.1	411.0	405.8	401.9	396.9	398.6
65°	371.4	359.0	352.9	348.2	343.5	340.4	342.9
67.5°	311.7	303.1	295.0	292.2	289.9	289.4	286.9
70°	272.6	265.4	258.3	256.6	256.6	254.2	253.6
72.5°	235.0	229.7	225.0	223.7	221.8	222.7	220.2
75°	181.5	177.4	175.6	173.8	173.2	173.2	171.4
77.5°	134.1	131.0	128.2	128.2	126.1	125.3	125.0
80°	101.8	100.6	98.2	98.2	97.0	97.6	96.4
82.5°	76.5	74.9	74.4	73.4	71.8	71.9	70.7
85°	41.1	39.3	38.7	36.9	35.7	36.9	35.7
87.5°	18.8	18.5	18.2	17.3	16.9	17.0	15.7
90°	22.4	23.5	24.3	24.6	25.1	25.4	25.7
92.5°	21.7	22.8	23.4	23.5	23.6	23.7	23.8
95°	22.4	23.5	24.2	24.4	24.5	24.7	24.9
97.5°	23.1	23.2	23.3	23.5	23.7	23.8	24.1
100°	28.1	24.8	23.3	23.5	23.7	23.8	24.1
102.5°	77.1	42.1	24.6	24.6	24.7	24.7	24.8
105°	273.3	275.0	272.5	265.6	258.7	251.8	245.0
107.5°	336.9	337.7	338.5	339.2	339.9	340.7	341.4
110°	380.2	380.6	381.1	381.6	382.2	382.8	383.3



TEST NUMBER: P332652-935

CATALOG NUMBER: S124DIP-S1020D1035U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	422.1	422.1	422.4	423.1	423.9	424.6	425.2
115°	485.9	486.3	486.5	486.5	486.5	486.5	486.5
117.5°	549.1	549.1	549.1	549.0	548.9	548.8	548.7
120°	589.0	589.4	589.4	589.0	588.7	588.3	587.9
122.5°	627.8	628.0	627.9	627.6	627.2	626.8	626.4
125°	682.4	683.0	683.4	683.6	683.8	684.0	684.2
127.5°	735.7	735.6	735.5	735.4	735.2	735.0	734.9
130°	769.0	769.1	769.3	769.3	769.3	769.3	769.3
132.5°	801.3	801.5	801.5	801.3	801.2	801.1	800.9
135°	846.0	846.4	846.8	847.2	847.6	847.9	848.3
137.5°	888.8	889.2	889.3	889.2	889.2	889.0	888.9
140°	915.4	915.9	916.4	916.5	916.7	916.9	917.1
142.5°	939.7	940.1	940.3	940.4	940.4	940.5	940.5
145°	974.4	974.6	974.9	975.3	975.6	976.0	976.4
147.5°	1005.0	1005.2	1005.4	1005.6	1005.7	1006.0	1006.2
150°	1024.5	1024.5	1024.6	1024.8	1025.0	1025.2	1025.4
152.5°	1042.0	1042.2	1042.3	1042.2	1042.2	1042.0	1041.9
155°	1065.5	1066.3	1066.3	1065.8	1065.2	1064.6	1064.1
157.5°	1085.6	1086.6	1086.6	1085.6	1084.6	1083.7	1082.6
160°	1098.5	1099.6	1099.6	1098.5	1097.3	1096.1	1095.0
162.5°	1108.8	1109.9	1109.8	1108.5	1107.2	1106.0	1104.7
165°	1123.7	1125.2	1125.1	1123.3	1121.6	1119.9	1118.2
167.5°	1134.5	1136.1	1136.0	1134.1	1132.2	1130.2	1128.3
170°	1140.8	1142.4	1142.2	1140.3	1138.4	1136.4	1134.5
172.5°	1145.0	1146.5	1146.2	1144.2	1142.1	1140.1	1138.0
175°	1150.0	1151.8	1151.4	1149.2	1146.9	1144.6	1142.3
177.5°	1151.4	1152.7	1152.4	1150.6	1148.7	1146.9	1145.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2

(END OF REPORT)