

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832466

Luminaire Tested: S123RDP-S340D950-4F0-1E-UDD-G

Issue Date: 05/03/2024

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P832466
 Test Lab: INNOVATION CENTER
 Issue Date: 05/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: NEO-RAY
 Catalog Number: S123RDP-S340D950-4F0-1E-UDD-G
 Description: DEFINE 3 DIRECT PENDANT LED LUMINAIRE
 DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC

Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 1405.2 lumens
 Efficiency: N/A
 Efficacy: 113.3 lumens/watt
 Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
 Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
 CIE Type: Direct

Input Watts (W): 12.4
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P832466
CATALOG NUMBER: S123RDP-S340D950-4F0-1E-UDD-G

Luminous Intensity Polar Plot



TEST NUMBER: P832466

CATALOG NUMBER: S123RDP-S340D950-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59				
5	82	70	62	56	80	69	62	56	67	61	56	65	60	55	63	58	54	53				
6	76	64	56	51	74	63	56	50	62	55	50	60	54	50	59	53	49	47				
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43				
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39				
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36				
10	60	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	11408	11408	11408	11408	11408
5°	13545	13113	11479	9280	8616
10°	12272	13319	11423	7436	6379
15°	8450	11420	11302	6077	5046
20°	5879	8793	11074	5125	4435
25°	4480	6701	10745	4555	4087
30°	3899	5358	10332	4228	3786
35°	3581	4519	9746	3954	3511
40°	3267	4036	8982	3684	3260
45°	2950	3691	8156	3430	3009
50°	2678	3406	7182	3180	2699
55°	2423	3126	6247	2935	2316
60°	2170	2844	5425	2665	2189
65°	2004	2524	4671	2397	2071
70°	1627	2181	4076	2168	1681
75°	1426	1734	3452	1797	1481
80°	1296	1469	2827	1506	1401
85°	1186	1284	2149	1371	1284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8605 cd/sqm

TEST NUMBER: P832466
 CATALOG NUMBER: S123RDP-S340D950-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	6.9
10°-20°	223.5	15.9
20°-30°	256.5	18.3
30°-40°	252.8	18.0
40°-50°	222.9	15.9
50°-60°	171.5	12.2
60°-70°	112.8	8.0
70°-80°	54.8	3.9
80°-90°	13.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	576.6	41.0
0°-40°	829.4	59.0
0°-60°	1223.8	87.1
0°-90°	1405.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1405.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1060	1060	1060	1060	1060	
5°	1254	1214	1062	859	797	115
15°	758	1025	1014	545	453	214
25°	377	564	905	384	344	178
35°	272	344	742	301	267	170
45°	194	242	536	225	198	150
55°	129	167	333	156	123	116
65°	79	99	183	94	81	77
75°	34	42	83	43	36	37
85°	10	10	17	11	10	11
90°	0	0	0	0	0	

TEST NUMBER: P832466

CATALOG NUMBER: S123RDP-S340D950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1174.5	1170.8	1167.2	1166.1	1165.0	1161.5	1158.0	1150.2	1142.4	1134.3	1126.3
5°	1253.6	1254.1	1254.5	1253.4	1252.3	1247.8	1243.2	1233.6	1224.1	1213.6	1203.2
7.5°	1229.3	1236.2	1243.2	1244.5	1245.8	1249.3	1252.8	1250.6	1248.4	1244.5	1240.6
10°	1122.8	1122.4	1122.0	1129.8	1137.6	1160.9	1184.1	1196.1	1208.0	1218.6	1229.3
12.5°	949.0	949.7	950.3	976.0	1001.6	1023.5	1045.5	1075.9	1106.3	1139.1	1171.9
15°	758.3	768.9	779.6	802.4	825.2	858.2	891.2	932.1	972.9	1024.8	1076.8
17.5°	622.7	627.2	631.8	653.8	675.7	707.0	738.3	784.5	830.8	897.7	964.7
20°	513.2	517.3	521.4	537.3	553.2	583.1	613.1	657.2	701.3	767.6	833.9
22.5°	428.4	436.5	444.5	455.2	465.8	487.5	509.3	554.2	599.2	659.6	720.0
25°	377.2	380.9	384.6	393.7	402.8	423.7	444.5	474.3	504.1	564.2	624.4
27.5°	342.4	343.5	344.6	351.3	358.1	371.5	385.0	412.6	440.2	489.7	539.3
30°	313.7	315.7	317.6	322.9	328.1	337.8	347.6	367.2	386.7	431.1	475.4
32.5°	291.6	292.7	293.7	298.1	302.4	309.6	316.8	332.2	347.6	381.5	415.4
35°	272.5	272.7	272.9	276.1	279.4	286.4	293.3	306.1	318.9	343.9	368.9
37.5°	250.7	252.2	253.8	256.2	258.5	264.6	270.7	281.1	291.6	312.2	332.9
40°	232.5	233.8	235.1	237.9	240.7	245.5	250.3	259.9	269.4	287.2	305.0
42.5°	214.2	215.1	216.0	218.8	221.6	227.5	233.3	240.9	248.6	263.3	278.1
45°	193.8	196.0	198.1	201.2	204.2	209.2	214.2	222.0	229.9	242.5	255.1
47.5°	176.9	177.9	179.0	181.6	184.2	190.3	196.4	203.4	210.3	222.0	233.8
50°	159.9	160.3	160.8	163.2	165.6	171.0	176.4	184.5	192.5	203.4	214.2
52.5°	143.8	144.9	146.0	148.4	150.8	154.5	158.2	166.4	174.7	185.3	196.0
55°	129.1	129.7	130.4	132.1	133.8	138.2	142.5	149.7	156.9	166.6	176.4
57.5°	115.2	116.0	116.9	118.2	119.5	123.4	127.3	133.6	139.9	149.7	159.5
60°	100.8	101.9	103.0	104.5	106.0	109.1	112.1	117.8	123.4	132.1	140.8
62.5°	90.4	90.6	90.8	92.1	93.4	95.6	97.8	102.3	106.9	115.6	124.3
65°	78.7	79.3	80.0	80.6	81.3	83.0	84.7	88.6	92.6	99.1	105.6
67.5°	66.5	67.1	67.8	68.9	70.0	71.5	73.0	75.6	78.2	84.3	90.4
70°	51.7	51.7	51.7	53.4	55.2	57.8	60.4	62.4	64.3	69.3	74.3
72.5°	42.1	42.4	42.6	42.8	43.0	44.5	46.1	49.3	52.6	55.6	58.7
75°	34.3	34.5	34.8	35.0	35.2	35.6	36.1	37.2	38.2	41.7	45.2
77.5°	27.4	27.6	27.8	28.0	28.2	28.7	29.1	29.5	30.0	31.3	32.6
80°	20.9	21.1	21.3	21.5	21.7	21.9	22.2	22.6	23.0	23.7	24.3
82.5°	15.2	15.2	15.2	15.2	15.2	15.6	16.1	16.1	16.1	16.5	16.9
85°	9.6	9.6	9.6	9.8	10.0	10.0	10.0	10.2	10.4	10.4	10.4
87.5°	4.3	4.1	3.9	4.1	4.3	4.3	4.3	4.6	4.8	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832466

CATALOG NUMBER: S123RDP-S340D950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1125.2	1124.1	1113.7	1103.3	1093.1	1082.9	1075.3	1067.6	1054.8	1042.0	1034.0
5°	1195.0	1186.7	1170.2	1153.7	1128.9	1104.1	1083.3	1062.4	1035.9	1009.4	987.3
7.5°	1233.9	1227.1	1207.1	1187.1	1154.3	1121.5	1088.9	1056.3	1017.2	978.1	944.7
10°	1234.9	1240.6	1224.1	1207.6	1170.6	1133.7	1089.4	1045.1	992.5	939.9	896.7
12.5°	1196.3	1220.6	1217.1	1213.6	1176.1	1138.5	1084.6	1030.7	966.2	901.7	847.6
15°	1123.9	1171.1	1185.0	1198.9	1167.8	1136.7	1075.5	1014.2	938.4	862.5	800.4
17.5°	1030.7	1096.8	1133.5	1170.2	1147.6	1125.0	1057.9	990.7	905.3	820.0	752.4
20°	920.3	1006.8	1064.4	1122.0	1113.7	1105.5	1036.1	966.8	874.7	782.6	709.4
22.5°	811.3	902.5	982.0	1061.6	1070.0	1078.5	1008.6	938.6	837.8	737.0	662.4
25°	717.2	810.0	904.7	999.4	1018.5	1037.7	971.2	904.7	800.2	695.7	621.6
27.5°	627.5	715.7	820.0	924.3	959.0	993.8	932.9	872.1	763.3	654.4	580.5
30°	554.2	633.1	739.6	846.0	894.5	942.9	887.1	831.3	723.3	615.3	542.9
32.5°	486.0	556.6	663.5	770.4	826.7	883.0	834.7	786.5	682.7	578.8	507.3
35°	432.1	495.4	595.1	694.8	757.8	820.8	781.3	741.7	640.3	538.8	471.3
37.5°	385.9	438.9	532.5	626.2	693.1	760.0	727.0	693.9	598.6	503.2	439.3
40°	347.6	390.2	477.3	564.5	630.1	695.7	667.4	639.2	553.8	468.4	408.7
42.5°	314.8	351.5	429.8	508.0	568.2	628.3	609.6	591.0	513.6	436.3	380.9
45°	285.9	316.8	385.6	454.5	509.9	565.3	550.6	535.8	469.1	402.4	351.5
47.5°	260.3	286.8	348.3	409.8	459.5	509.3	495.6	481.9	426.7	371.5	325.2
50°	236.8	259.4	310.7	362.0	406.7	451.5	440.2	428.9	383.3	337.6	297.7
52.5°	214.7	233.3	279.4	325.5	361.5	397.6	388.9	380.2	345.0	309.8	273.5
55°	193.6	210.7	249.6	288.5	319.4	350.2	341.5	332.9	305.5	278.1	246.2
57.5°	174.5	189.5	221.0	252.5	277.0	301.6	297.4	293.3	270.5	247.7	221.4
60°	154.3	167.7	194.9	222.0	241.8	261.6	256.8	252.0	235.7	219.4	196.8
62.5°	136.2	148.2	169.9	191.6	207.7	223.8	220.3	216.8	204.4	192.1	173.4
65°	117.3	129.1	146.7	164.3	176.9	189.5	186.4	183.4	174.0	164.7	149.7
67.5°	100.2	109.9	125.1	140.4	148.8	157.3	155.6	153.8	146.7	139.5	127.8
70°	82.8	91.3	103.9	116.5	122.3	128.2	128.8	129.5	123.0	116.5	107.8
72.5°	65.4	72.1	83.9	95.6	100.2	104.7	104.5	104.3	100.4	96.5	88.6
75°	50.2	55.2	64.3	73.4	77.3	81.3	82.1	83.0	79.3	75.6	71.3
77.5°	36.1	39.5	46.5	53.4	57.8	62.1	62.6	63.0	61.3	59.5	55.4
80°	25.4	26.5	30.9	35.2	39.8	44.3	45.0	45.6	43.9	42.1	39.5
82.5°	17.6	18.3	19.8	21.3	25.0	28.7	29.5	30.4	29.5	28.7	25.9
85°	10.6	10.9	11.5	12.2	13.9	15.6	16.5	17.4	16.9	16.5	15.0
87.5°	4.8	4.8	5.0	5.2	5.6	6.1	7.2	8.3	7.6	7.0	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832466

CATALOG NUMBER: S123RDP-S340D950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1025.9	1013.5	1001.2	992.3	983.3	972.3	961.2	960.8	960.3	952.1	943.8
5°	965.1	943.6	922.1	901.0	879.9	858.9	837.8	833.0	828.2	821.0	813.9
7.5°	911.2	876.9	842.6	815.6	788.7	767.6	746.5	732.2	717.8	706.8	695.7
10°	853.4	810.8	768.3	735.7	703.1	680.3	657.4	640.9	624.4	616.6	608.8
12.5°	793.5	747.2	700.9	669.0	637.0	609.6	582.3	567.3	552.3	541.4	530.6
15°	738.3	688.5	638.8	604.9	571.0	545.3	519.7	504.7	489.7	478.9	468.0
17.5°	684.8	634.6	584.4	550.1	515.8	492.5	469.3	454.7	440.2	433.4	426.7
20°	636.2	585.5	534.9	502.5	470.2	447.4	424.5	416.7	408.9	402.6	396.3
22.5°	587.9	539.3	490.6	459.5	428.4	411.9	395.4	389.1	382.8	378.0	373.3
25°	547.5	499.1	450.6	423.5	396.3	383.5	370.7	366.5	362.4	357.6	352.8
27.5°	506.7	460.6	414.5	392.8	371.1	360.7	350.2	345.0	339.8	335.9	332.0
30°	470.6	428.0	385.4	367.4	349.4	340.2	331.1	325.5	319.8	316.1	312.4
32.5°	435.8	398.0	360.2	344.8	329.4	320.5	311.6	306.1	300.7	296.4	292.0
35°	403.7	370.9	338.1	323.9	309.8	300.9	292.0	286.6	281.1	276.8	272.5
37.5°	375.4	345.7	315.9	302.7	289.4	281.6	273.8	268.1	262.5	257.9	253.3
40°	348.9	322.6	296.4	283.5	270.7	262.2	253.8	248.8	243.8	239.6	235.5
42.5°	325.5	301.3	277.2	264.6	252.0	244.0	236.0	230.1	224.2	221.8	219.4
45°	300.7	279.4	258.1	245.9	233.8	225.3	216.8	211.8	206.8	204.7	202.5
47.5°	279.0	259.2	239.4	227.5	215.5	207.9	200.3	196.4	192.5	189.5	186.4
50°	257.7	238.6	219.4	207.9	196.4	189.9	183.4	178.6	173.8	171.6	169.5
52.5°	237.3	219.9	202.5	190.8	179.0	172.7	166.4	162.3	158.2	153.6	149.0
55°	214.2	199.0	183.8	173.4	162.9	156.4	149.9	145.1	140.4	135.6	130.8
57.5°	195.1	180.1	165.1	155.8	146.4	140.1	133.8	128.6	123.4	119.5	115.6
60°	174.2	161.2	148.2	139.1	129.9	123.8	117.8	112.8	107.8	105.8	103.9
62.5°	154.7	142.5	130.4	122.3	114.3	108.4	102.5	99.3	96.0	94.7	93.4
65°	134.7	124.3	113.8	106.5	99.1	94.1	89.1	87.6	86.0	85.0	83.9
67.5°	116.0	107.1	98.2	91.7	85.2	81.7	78.2	76.5	74.7	73.4	72.1
70°	99.1	91.3	83.4	77.8	72.1	68.9	65.6	64.1	62.6	60.2	57.8
72.5°	80.8	74.7	68.7	64.3	60.0	57.1	54.3	51.3	48.2	46.1	43.9
75°	66.9	60.8	54.8	50.6	46.5	43.2	40.0	38.9	37.8	37.2	36.5
77.5°	51.3	46.1	40.8	37.6	34.3	32.8	31.3	30.6	30.0	29.8	29.5
80°	36.9	32.6	28.2	26.5	24.8	24.3	23.9	23.5	23.0	22.8	22.6
82.5°	23.0	20.9	18.7	18.3	17.8	17.6	17.4	17.2	16.9	16.7	16.5
85°	13.5	12.6	11.7	11.5	11.3	11.1	10.9	10.9	10.9	10.9	10.9
87.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.4	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P832466

CATALOG NUMBER: S123RDP-S340D950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1059.8	1059.8	1059.8	1059.8
2.5°	941.6	939.5	938.6	937.7
5°	807.1	800.4	798.9	797.4
7.5°	692.9	690.0	680.7	671.4
10°	600.1	591.4	587.5	583.6
12.5°	522.5	514.5	513.2	511.9
15°	462.3	456.7	454.7	452.8
17.5°	422.8	418.9	416.5	414.1
20°	393.5	390.6	388.9	387.2
22.5°	371.1	368.9	367.6	366.3
25°	349.6	346.3	345.2	344.1
27.5°	329.2	326.3	325.2	324.2
30°	310.0	307.6	306.1	304.6
32.5°	289.2	286.4	285.5	284.6
35°	270.7	269.0	268.1	267.2
37.5°	251.2	249.0	247.7	246.4
40°	234.4	233.3	232.7	232.0
42.5°	217.5	215.5	215.3	215.1
45°	200.5	198.6	198.1	197.7
47.5°	184.7	182.9	182.7	182.5
50°	167.1	164.7	162.9	161.2
52.5°	146.9	144.7	143.2	141.7
55°	128.4	126.0	124.7	123.4
57.5°	114.5	113.4	112.8	112.1
60°	103.2	102.5	102.1	101.7
62.5°	92.8	92.1	92.1	92.1
65°	83.2	82.6	81.9	81.3
67.5°	70.8	69.5	69.3	69.1
70°	55.8	53.9	53.7	53.4
72.5°	43.7	43.5	43.0	42.6
75°	36.1	35.6	35.6	35.6
77.5°	29.1	28.7	28.7	28.7
80°	22.4	22.2	22.4	22.6
82.5°	16.5	16.5	16.3	16.1
85°	10.6	10.4	10.4	10.4
87.5°	5.2	5.2	5.2	5.2
90°	0.0	0.0	0.0	0.0

TEST NUMBER: P832466

CATALOG NUMBER: S123RDP-S340D950-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.16	14.62	13.53	14.93	15.25	17.83	19.28	18.19	19.60	19.91
	3H	14.42	15.73	14.80	16.06	16.42	19.37	20.67	19.75	21.00	21.36
	4H	14.83	16.05	15.23	16.40	16.78	19.88	21.11	20.29	21.45	21.83
	6H	15.14	16.27	15.56	16.64	17.03	20.23	21.35	20.64	21.72	22.11
	8H	15.25	16.32	15.68	16.71	17.11	20.32	21.39	20.75	21.78	22.18
	12H	15.32	16.34	15.75	16.72	17.15	20.37	21.39	20.80	21.78	22.21
4H	2H	13.96	15.18	14.36	15.52	15.90	17.89	19.11	18.29	19.46	19.84
	3H	15.37	16.38	15.79	16.79	17.19	19.60	20.61	20.01	21.01	21.41
	4H	15.85	16.76	16.28	17.18	17.62	20.23	21.14	20.66	21.55	21.99
	6H	16.25	17.04	16.71	17.48	17.94	20.70	21.48	21.16	21.93	22.39
	8H	16.39	17.12	16.85	17.57	18.03	20.84	21.57	21.30	22.02	22.49
	12H	16.49	17.14	16.97	17.62	18.10	20.93	21.58	21.41	22.06	22.53
8H	4H	16.21	16.94	16.67	17.39	17.86	20.24	20.97	20.70	21.42	21.88
	6H	16.69	17.30	17.19	17.79	18.27	20.75	21.36	21.25	21.85	22.33
	8H	16.89	17.43	17.40	17.94	18.43	20.94	21.48	21.46	21.99	22.48
	12H	17.05	17.53	17.56	18.02	18.59	21.08	21.56	21.59	22.05	22.62
12H	4H	16.25	16.90	16.73	17.38	17.85	20.21	20.87	20.70	21.35	21.82
	6H	16.75	17.29	17.27	17.80	18.29	20.73	21.27	21.24	21.78	22.27
	8H	17.00	17.47	17.51	17.97	18.53	20.95	21.42	21.46	21.92	22.48