

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334620

Luminaire Tested: **S123IP-S365U835-4F0-1E-UDD-4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P334620  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123IP-S365U835-4F0-1E-UDD-4  
Description: DEFINE 3 INDIRECT LED LUMINAIRE, BATWING OPTIC  
PENDANT MOUNT, 365 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1314.1 lumens  
Efficiency: N/A  
Efficacy: 115.3 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 11.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P334620  
CATALOG NUMBER: S123IP-S365U835-4F0-1E-UDD-4

### Luminous Intensity Polar Plot





TEST NUMBER: P334620

CATALOG NUMBER: S123IP-S365U835-4F0-1E-UDD-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P334620

CATALOG NUMBER: S123IP-S365U835-4F0-1E-UDD-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.0	0.1
90°-100°	94.7	7.2
100°-110°	277.3	21.1
110°-120°	270.8	20.6
120°-130°	215.7	16.4
130°-140°	170.2	12.9
140°-150°	126.9	9.7
150°-160°	88.5	6.7
160°-170°	52.0	4.0
170°-180°	16.9	1.3
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.0	0.1
90°-120°	642.9	48.9
90°-150°	1155.7	87.9
90°-180°	1313.0	99.9
0°-180°	1314.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	4	9	10	10	1
95°	12	39	210	61	41	13
105°	41	61	284	497	450	44
115°	72	90	217	477	547	72
125°	101	119	203	368	431	89
135°	118	141	200	303	350	91
145°	135	154	198	248	273	84
155°	153	165	191	217	226	70
165°	167	172	183	194	198	47
175°	174	174	176	178	178	17
180°	175	175	175	175	175	



TEST NUMBER: P334620

CATALOG NUMBER: S123IP-S365U835-4F0-1E-UDD-4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.7	1.4	2.1	3.2	3.9	4.6	5.7	6.7	7.8	8.8	8.5
92.5°	5.3	7.8	11.3	14.5	18.0	24.4	35.7	54.4	72.8	65.7	49.1
95°	12.0	13.1	17.0	23.0	32.2	45.9	76.0	128.6	186.6	209.6	170.0
97.5°	19.1	19.4	22.6	27.9	37.1	52.3	82.0	143.1	240.7	322.3	333.2
100°	26.2	26.5	29.0	33.9	42.4	56.2	80.9	133.2	226.2	334.7	404.3
102.5°	33.6	34.3	36.4	41.0	48.4	60.8	82.3	124.7	205.0	311.7	407.8
105°	41.0	42.1	44.2	48.4	55.1	66.1	85.2	121.6	188.4	284.1	385.5
107.5°	48.8	49.8	51.9	56.2	62.5	72.8	89.8	120.9	176.3	259.7	353.7
110°	57.2	58.3	60.1	64.0	70.0	79.9	95.8	122.6	170.0	239.6	324.1



TEST NUMBER: P334620

CATALOG NUMBER: S123IP-S365U835-4F0-1E-UDD-4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	65.0	66.1	67.8	71.7	77.7	87.3	101.8	126.2	166.4	226.2	298.3
115°	72.4	73.9	76.0	79.5	85.5	95.1	108.5	130.0	166.1	217.3	278.5
117.5°	79.9	81.6	83.4	86.6	93.3	102.1	115.6	135.0	166.4	211.3	265.4
120°	87.6	88.7	90.5	94.0	100.7	109.5	122.3	140.6	167.9	207.4	255.5
122.5°	94.4	95.4	97.2	101.1	107.4	117.0	129.3	145.9	170.3	205.0	247.4
125°	100.7	101.4	103.5	107.4	114.1	123.7	136.1	151.6	172.8	202.8	240.7
127.5°	105.7	106.7	109.2	113.1	120.5	130.0	142.1	156.2	175.6	201.8	234.3
130°	110.3	111.3	114.5	118.7	126.2	135.7	147.4	160.8	178.5	200.7	229.3
132.5°	113.8	115.2	118.7	124.0	131.5	140.6	152.0	165.0	180.6	200.4	224.8
135°	118.0	119.4	123.3	128.6	136.1	145.6	156.5	168.6	182.7	200.0	220.9
137.5°	121.9	123.3	127.2	132.9	140.3	149.1	159.7	171.4	184.1	199.3	217.3
140°	125.8	127.6	131.1	136.8	143.8	152.7	162.9	173.5	185.5	199.0	214.1
142.5°	130.0	131.5	135.3	140.3	147.4	155.5	165.4	175.6	186.6	198.2	211.3
145°	134.6	135.7	138.9	144.2	150.2	158.3	167.5	177.0	186.9	197.5	208.8
147.5°	139.2	139.9	143.1	147.7	153.7	160.8	169.3	178.1	186.9	196.5	206.4
150°	143.8	144.2	147.0	151.6	156.5	162.9	171.0	178.5	186.9	195.1	203.9
152.5°	148.4	148.4	151.2	155.1	159.4	165.4	172.1	179.2	185.9	193.3	201.1
155°	153.0	153.0	155.1	158.7	162.6	167.5	173.5	179.2	185.2	191.2	198.2
157.5°	156.5	156.9	158.7	161.8	165.4	169.3	174.2	179.5	184.1	189.4	195.1
160°	160.8	160.8	162.2	165.0	167.5	171.0	175.3	179.5	183.4	187.3	191.9
162.5°	164.0	164.0	165.0	167.1	169.3	172.1	175.6	179.2	182.0	185.2	188.7
165°	167.1	166.8	167.5	169.3	170.7	173.2	176.0	178.5	180.6	183.1	185.9
167.5°	169.6	169.3	169.6	171.0	172.1	173.9	176.0	178.1	179.2	180.9	183.1
170°	171.7	171.0	171.4	172.4	173.2	173.9	175.6	177.0	177.8	178.8	180.6
172.5°	173.2	172.8	172.8	173.5	173.9	174.2	175.6	176.7	176.7	177.0	178.1
175°	174.2	173.9	173.5	174.2	174.2	174.6	175.3	176.0	175.6	175.6	176.3
177.5°	174.9	174.6	174.2	174.6	174.6	174.6	174.9	175.6	174.9	174.6	174.9
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P334620

CATALOG NUMBER: S123IP-S365U835-4F0-1E-UDD-4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	8.8	9.2	9.5	10.2	9.9	10.2	10.6	10.2
92.5°	35.0	27.2	23.7	21.2	20.5	19.1	19.4	18.7
95°	127.2	86.2	67.5	54.8	48.1	44.9	42.4	41.0
97.5°	292.2	220.5	173.9	133.6	109.9	96.5	88.0	84.1
100°	416.6	388.0	346.7	296.5	260.8	235.0	221.2	221.6
102.5°	458.0	464.0	444.2	417.0	391.2	372.1	361.2	350.9
105°	459.4	494.7	501.4	492.3	476.0	462.6	451.3	449.5
107.5°	438.2	493.7	521.2	530.8	528.7	522.3	517.7	513.8
110°	405.0	470.0	514.5	539.3	549.2	552.0	551.3	550.6





TEST NUMBER: P334620

CATALOG NUMBER: S123IP-S365U835-4F0-1E-UDD-4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	372.1	438.9	490.1	523.7	543.9	554.1	557.6	558.0
115°	343.8	405.3	457.3	495.8	522.3	537.8	544.9	546.7
117.5°	321.9	376.4	424.1	464.0	491.6	508.9	519.5	521.9
120°	305.3	353.0	395.4	431.1	459.0	478.8	487.3	489.4
122.5°	292.2	334.3	372.8	405.3	429.4	446.7	456.2	459.0
125°	280.9	319.5	353.4	381.7	404.3	419.8	428.7	431.1
127.5°	270.7	305.7	336.8	362.9	383.4	396.8	405.0	407.1
130°	261.1	293.0	321.6	345.6	364.3	377.1	384.5	387.3
132.5°	252.3	280.9	307.1	329.7	347.0	359.7	366.1	367.9
135°	244.5	269.6	292.6	312.7	330.1	340.7	347.0	349.5
137.5°	237.1	258.3	278.8	296.8	311.7	322.6	327.9	330.1
140°	230.8	248.8	265.7	280.9	294.4	304.3	309.9	309.6
142.5°	224.8	239.6	253.7	266.4	277.4	285.9	290.8	290.5
145°	220.2	231.8	243.1	253.4	262.2	269.6	272.5	273.2
147.5°	216.3	225.8	235.4	242.8	249.8	255.1	258.0	258.3
150°	212.0	220.2	227.6	234.3	239.6	243.5	245.6	245.6
152.5°	208.1	214.9	221.2	226.5	230.4	233.9	235.0	235.0
155°	204.3	209.9	215.2	219.4	222.6	225.5	226.2	226.5
157.5°	200.0	205.0	209.2	212.7	215.6	217.7	218.4	218.4
160°	196.5	200.4	203.9	206.4	208.8	211.0	211.0	210.6
162.5°	192.2	195.4	198.6	200.7	202.1	203.9	203.9	203.5
165°	188.7	190.8	193.3	195.1	196.5	197.9	197.5	197.5
167.5°	185.5	187.3	188.7	190.1	190.8	191.9	191.5	191.5
170°	182.3	183.4	184.8	185.5	185.9	186.6	186.2	186.2
172.5°	179.5	180.2	181.3	181.6	181.6	182.3	181.6	181.3
175°	177.0	177.4	178.1	178.1	178.1	178.5	178.1	177.8
177.5°	175.3	175.6	176.0	176.0	175.6	176.0	175.3	175.3
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6

(END OF REPORT)