

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332667-935

Luminaire Tested: **S124DIP-S1020D1205U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332667-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D1205U935-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7953.8 lumens  
Efficiency: N/A  
Efficacy: 121.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332667-935

CATALOG NUMBER: S124DIP-S1020D1205U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332667-935

CATALOG NUMBER: S124DIP-S1020D1205U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	34
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16	13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11994	11994	11994
5°	12030	11885	11972
10°	11954	11788	11847
15°	11810	11621	11651
20°	11618	11413	11424
25°	11399	11176	11144
30°	11130	10897	10797
35°	10852	10606	10465
40°	10564	10275	10086
45°	10261	9949	9758
50°	9928	9658	9359
55°	9568	9282	8981
60°	9206	8861	8591
65°	8800	8458	8118
70°	8344	7924	7615
75°	7648	7277	7093
80°	6811	6527	6365
85°	5956	5734	5622



TEST NUMBER: P332667-935

CATALOG NUMBER: S124DIP-S1020D1205U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.9	1.8
10°-20°	394.2	5.0
20°-30°	580.2	7.3
30°-40°	674.5	8.5
40°-50°	674.5	8.5
50°-60°	590.0	7.4
60°-70°	438.2	5.5
70°-80°	248.9	3.1
80°-90°	75.7	1.0
90°-100°	45.8	0.6
100°-110°	291.7	3.7
110°-120°	558.0	7.0
120°-130°	708.4	8.9
130°-140°	757.9	9.5
140°-150°	708.7	8.9
150°-160°	571.5	7.2
160°-170°	368.6	4.6
170°-180°	127.0	1.6
0°-30°	1114.3	14.0
0°-40°	1788.8	22.5
0°-60°	3053.4	38.4
0°-90°	3816.3	48.0
90°-120°	895.4	11.3
90°-150°	3070.4	38.6
90°-180°	4138.0	52.0
0°-180°	7953.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1486	1486	1486	1486	1486	
5°	1484	1479	1467	1479	1477	141
15°	1413	1408	1390	1397	1394	398
25°	1280	1271	1255	1256	1251	588
35°	1101	1092	1076	1068	1062	688
45°	899	890	871	859	855	693
55°	680	675	660	646	638	609
65°	461	454	443	431	425	456
75°	245	239	233	229	227	261
85°	64	64	62	62	61	71
90°	3	14	22	28	30	6
95°	55	23	22	28	29	71
105°	301	307	312	319	285	315
115°	562	565	564	566	566	553
125°	790	794	792	795	796	705
135°	980	980	983	985	987	755
145°	1130	1133	1134	1135	1136	706
155°	1240	1240	1238	1241	1238	571
165°	1308	1303	1303	1310	1302	369
175°	1338	1332	1333	1340	1330	127
180°	1338	1338	1338	1338	1338	



TEST NUMBER: P332667-935

CATALOG NUMBER: S124DIP-S1020D1205U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1489.4	1488.8	1488.2	1487.5	1486.9	1485.4	1483.1	1480.7	1478.4	1476.1	1478.3
5°	1484.5	1483.4	1482.4	1481.3	1480.2	1478.3	1475.3	1472.4	1469.6	1466.6	1469.6
7.5°	1470.7	1469.6	1468.5	1467.5	1466.5	1464.3	1461.0	1457.8	1454.6	1451.4	1453.7
10°	1458.3	1457.2	1456.1	1455.1	1454.1	1451.8	1448.4	1444.9	1441.5	1438.0	1440.1
12.5°	1442.1	1441.1	1439.9	1438.9	1437.9	1435.5	1431.8	1428.2	1424.5	1420.9	1423.2
15°	1413.1	1412.0	1410.9	1409.9	1408.8	1406.3	1402.3	1398.4	1394.4	1390.4	1392.0
17.5°	1378.0	1376.7	1375.4	1374.1	1372.8	1370.2	1366.4	1362.7	1358.9	1355.2	1356.2
20°	1352.3	1351.0	1349.7	1348.3	1347.0	1344.4	1340.4	1336.4	1332.5	1328.5	1329.3
22.5°	1324.7	1322.9	1321.2	1319.5	1317.8	1314.8	1310.9	1306.9	1303.0	1299.0	1300.5
25°	1279.7	1277.9	1276.0	1274.1	1272.3	1269.5	1265.8	1262.1	1258.4	1254.7	1255.0
27.5°	1228.3	1226.4	1224.4	1222.5	1220.6	1218.0	1214.5	1211.1	1207.6	1204.2	1203.6
30°	1194.0	1191.9	1189.7	1187.7	1185.5	1182.8	1179.3	1175.9	1172.4	1169.0	1167.9
32.5°	1157.8	1155.9	1154.0	1152.1	1150.2	1147.4	1143.8	1140.1	1136.4	1132.8	1131.5
35°	1101.1	1099.3	1097.4	1095.6	1093.7	1091.0	1087.3	1083.6	1079.9	1076.2	1074.3
37.5°	1041.4	1039.7	1038.0	1036.3	1034.6	1031.8	1027.8	1023.8	1019.9	1015.9	1013.9
40°	1002.4	1000.2	998.1	996.0	993.9	990.8	986.9	982.9	979.0	975.0	972.3
42.5°	960.4	959.2	957.9	956.7	955.4	952.5	948.1	943.7	939.4	935.0	931.9
45°	898.8	896.9	895.1	893.2	891.4	888.3	884.1	879.9	875.6	871.4	868.5
47.5°	834.2	833.0	831.7	830.4	829.1	826.6	822.7	818.7	814.9	810.9	807.6
50°	790.5	789.4	788.3	787.3	786.2	783.9	780.2	776.4	772.7	769.0	765.3
52.5°	747.6	746.3	745.0	743.8	742.5	739.9	736.0	732.1	728.1	724.3	721.0
55°	679.8	678.9	678.1	677.3	676.6	674.3	670.6	666.9	663.2	659.5	656.3
57.5°	615.0	614.1	613.2	612.3	611.4	609.1	605.5	601.8	598.1	594.5	591.5
60°	570.2	568.9	567.6	566.3	564.9	562.6	559.1	555.7	552.2	548.8	546.4
62.5°	526.4	525.3	524.2	523.1	521.9	519.6	515.9	512.3	508.6	505.0	502.8
65°	460.7	459.3	458.1	456.8	455.4	453.4	450.7	448.2	445.5	442.8	440.2
67.5°	394.5	393.3	392.1	390.9	389.6	387.8	385.2	382.7	380.1	377.6	375.1
70°	353.5	351.7	349.8	348.0	346.1	344.1	342.1	339.9	337.9	335.7	333.6
72.5°	309.8	307.9	306.1	304.2	302.4	300.6	298.9	297.2	295.5	293.8	292.1
75°	245.2	243.9	242.5	241.3	240.0	238.6	237.3	236.0	234.6	233.3	232.3
77.5°	183.6	183.0	182.4	181.8	181.2	180.4	179.2	178.1	176.8	175.7	175.4
80°	146.5	145.6	144.8	144.0	143.3	142.6	142.1	141.5	141.0	140.4	139.9
82.5°	110.2	109.9	109.5	109.1	108.7	108.5	108.4	108.3	108.2	108.1	107.8
85°	64.3	64.3	64.3	64.3	64.3	64.1	63.5	62.9	62.4	61.9	61.9
87.5°	25.4	25.7	25.9	26.2	26.4	26.7	26.9	26.9	27.1	27.3	27.6
90°	3.0	5.4	7.9	10.3	12.7	14.9	16.7	18.4	20.2	22.0	23.3
92.5°	12.6	12.7	12.9	13.0	13.2	14.1	15.8	17.7	19.5	21.2	22.6
95°	55.0	47.4	39.9	32.4	24.8	21.1	21.4	21.5	21.8	22.0	23.3
97.5°	116.8	121.6	126.3	131.0	135.7	125.6	100.8	76.0	51.2	26.4	26.5
100°	164.1	168.1	172.1	176.1	180.1	166.8	136.0	105.4	74.7	44.0	40.2
102.5°	216.9	219.8	222.7	225.7	228.6	228.1	224.1	220.1	216.1	212.1	171.3
105°	301.1	302.5	303.8	305.1	306.4	307.7	308.8	309.9	311.0	312.1	314.2
107.5°	379.4	380.0	380.7	381.3	382.0	383.1	384.6	386.2	387.6	389.2	390.1
110°	432.2	432.8	433.5	434.2	434.9	435.8	437.2	438.5	439.9	441.2	441.6



TEST NUMBER: P332667-935

CATALOG NUMBER: S124DIP-S1020D1205U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.5	484.7	485.8	487.0	488.2	489.1	489.7	490.3	491.0	491.6	491.5
115°	562.2	562.9	563.6	564.2	564.9	565.2	564.9	564.7	564.5	564.2	564.7
117.5°	633.3	634.1	635.1	635.9	636.8	637.5	638.0	638.5	639.0	639.5	639.4
120°	681.3	682.2	683.1	684.0	684.8	685.2	685.0	684.8	684.5	684.3	684.8
122.5°	726.1	726.7	727.2	727.7	728.2	728.7	729.0	729.3	729.6	730.0	730.2
125°	790.3	791.3	792.1	793.0	793.9	794.1	793.7	793.2	792.8	792.4	793.0
127.5°	851.2	851.4	851.6	851.9	852.0	852.6	853.7	854.7	855.7	856.8	856.6
130°	890.4	890.6	890.9	891.0	891.3	891.7	892.4	893.0	893.7	894.4	894.6
132.5°	926.4	926.8	927.2	927.6	928.0	928.7	929.4	930.3	931.2	932.0	932.2
135°	980.4	980.2	980.0	979.7	979.6	979.9	980.8	981.6	982.6	983.4	983.9
137.5°	1028.3	1028.4	1028.5	1028.6	1028.6	1029.2	1030.1	1031.1	1032.1	1033.0	1033.5
140°	1059.5	1059.9	1060.3	1060.8	1061.3	1061.7	1062.1	1062.6	1063.0	1063.5	1064.1
142.5°	1087.4	1088.3	1089.1	1089.9	1090.7	1091.2	1091.5	1091.7	1092.0	1092.3	1092.8
145°	1130.5	1131.2	1131.9	1132.5	1133.2	1133.5	1133.5	1133.5	1133.5	1133.5	1133.8
147.5°	1164.7	1166.0	1167.2	1168.5	1169.7	1170.2	1170.0	1169.8	1169.5	1169.3	1169.5
150°	1189.6	1190.4	1191.3	1192.2	1193.1	1193.4	1193.2	1193.0	1192.7	1192.5	1192.5
152.5°	1210.3	1211.1	1211.8	1212.5	1213.1	1213.3	1213.0	1212.5	1212.1	1211.8	1212.1
155°	1239.6	1239.8	1240.0	1240.2	1240.4	1240.2	1239.6	1238.9	1238.2	1237.5	1238.5
157.5°	1264.1	1264.0	1263.9	1263.8	1263.6	1263.2	1262.4	1261.7	1260.9	1260.2	1261.3
160°	1278.6	1277.9	1277.2	1276.6	1275.9	1275.5	1275.2	1275.0	1274.8	1274.5	1275.9
162.5°	1291.3	1290.6	1289.7	1288.8	1288.0	1287.5	1287.2	1287.0	1286.8	1286.6	1287.9
165°	1307.6	1306.5	1305.4	1304.2	1303.1	1302.6	1302.6	1302.6	1302.6	1302.6	1304.3
167.5°	1320.3	1319.2	1318.1	1316.9	1315.8	1315.1	1315.0	1314.8	1314.7	1314.6	1316.6
170°	1327.6	1326.3	1324.9	1323.6	1322.2	1321.7	1321.9	1322.2	1322.3	1322.6	1324.4
172.5°	1332.4	1331.0	1329.7	1328.4	1327.1	1326.5	1326.7	1327.0	1327.1	1327.4	1329.1
175°	1337.6	1336.3	1334.9	1333.6	1332.2	1331.7	1331.9	1332.1	1332.4	1332.6	1334.6
177.5°	1340.0	1338.8	1337.5	1336.3	1335.0	1334.6	1334.9	1335.2	1335.7	1336.0	1337.4
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332667-935

CATALOG NUMBER: S124DIP-S1020D1205U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1480.3	1482.5	1484.6	1485.6	1485.3	1485.1	1484.9	1484.7
5°	1472.4	1475.3	1478.3	1479.5	1478.9	1478.3	1477.8	1477.3
7.5°	1456.0	1458.4	1460.7	1461.7	1461.4	1461.0	1460.7	1460.4
10°	1442.3	1444.4	1446.5	1447.3	1446.7	1446.2	1445.7	1445.2
12.5°	1425.6	1427.9	1430.2	1431.0	1430.3	1429.5	1428.7	1428.1
15°	1393.6	1395.2	1396.8	1397.1	1396.4	1395.6	1394.8	1394.0
17.5°	1357.2	1358.2	1359.2	1359.4	1358.9	1358.4	1357.9	1357.3
20°	1330.1	1330.9	1331.7	1331.8	1331.3	1330.8	1330.2	1329.7
22.5°	1301.8	1303.3	1304.7	1304.9	1304.0	1303.0	1302.1	1301.1
25°	1255.3	1255.5	1255.8	1255.3	1254.3	1253.3	1252.2	1251.1
27.5°	1203.0	1202.3	1201.7	1200.8	1199.4	1198.1	1196.7	1195.4
30°	1166.9	1165.8	1164.8	1163.6	1162.3	1160.9	1159.6	1158.3
32.5°	1130.2	1129.0	1127.7	1126.4	1125.1	1123.8	1122.5	1121.1
35°	1072.5	1070.6	1068.8	1067.1	1065.8	1064.5	1063.2	1061.9
37.5°	1011.8	1009.9	1007.9	1006.0	1004.3	1002.5	1000.7	999.0
40°	969.7	967.0	964.4	962.4	961.0	959.8	958.5	957.1
42.5°	928.8	925.7	922.6	920.7	919.8	918.9	918.0	917.1
45°	865.6	862.6	859.7	857.9	857.1	856.4	855.5	854.7
47.5°	804.3	801.1	797.8	795.1	793.2	791.1	789.1	787.1
50°	761.6	757.9	754.2	751.6	749.9	748.4	746.8	745.2
52.5°	717.7	714.4	711.1	708.5	706.5	704.5	702.5	700.4
55°	653.2	650.0	646.8	644.5	642.8	641.3	639.6	638.1
57.5°	588.5	585.5	582.5	580.1	578.6	577.1	575.6	574.0
60°	544.1	541.7	539.2	537.4	536.1	534.8	533.5	532.1
62.5°	500.7	498.4	496.3	494.6	493.3	491.9	490.6	489.3
65°	437.6	434.9	432.2	430.2	429.0	427.7	426.3	425.0
67.5°	372.6	370.0	367.5	366.0	365.6	365.2	364.9	364.5
70°	331.5	329.3	327.3	325.8	325.0	324.2	323.4	322.6
72.5°	290.4	288.7	287.1	285.8	285.0	284.2	283.4	282.6
75°	231.2	230.1	229.1	228.4	228.2	227.9	227.6	227.4
77.5°	175.0	174.8	174.4	173.9	173.2	172.5	171.9	171.2
80°	139.4	138.9	138.4	137.9	137.7	137.4	137.2	136.9
82.5°	107.5	107.1	106.9	106.5	106.2	106.0	105.7	105.5
85°	61.9	61.9	61.9	61.7	61.5	61.2	61.0	60.7
87.5°	27.8	28.1	28.3	28.5	28.6	28.7	28.8	28.8
90°	24.7	26.0	27.4	28.2	28.7	29.1	29.5	30.0
92.5°	23.8	25.2	26.5	27.3	27.4	27.5	27.6	27.6
95°	24.7	26.0	27.4	28.2	28.3	28.6	28.8	29.0
97.5°	26.7	26.8	26.9	27.1	27.4	27.6	27.8	28.0
100°	36.4	32.7	28.9	27.1	27.4	27.6	27.8	28.0
102.5°	130.5	89.8	49.0	28.7	28.7	28.8	28.8	28.8
105°	316.2	318.1	320.1	317.1	309.1	301.1	293.2	285.2
107.5°	391.2	392.1	393.0	394.0	394.9	395.7	396.5	397.4
110°	442.1	442.6	443.0	443.5	444.2	444.9	445.6	446.2





TEST NUMBER: P332667-935

CATALOG NUMBER: S124DIP-S1020D1205U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	491.5	491.4	491.3	491.6	492.5	493.4	494.2	495.0
115°	565.2	565.6	566.0	566.3	566.3	566.3	566.3	566.3
117.5°	639.3	639.2	639.1	639.0	638.9	638.9	638.8	638.7
120°	685.2	685.6	686.0	686.0	685.6	685.2	684.8	684.3
122.5°	730.5	730.7	731.0	730.9	730.5	730.0	729.5	729.1
125°	793.7	794.4	795.0	795.5	795.7	795.9	796.2	796.3
127.5°	856.5	856.4	856.3	856.1	855.9	855.7	855.6	855.4
130°	894.8	895.1	895.3	895.4	895.4	895.4	895.4	895.4
132.5°	932.5	932.7	932.9	932.9	932.7	932.5	932.4	932.2
135°	984.3	984.7	985.2	985.7	986.1	986.5	987.0	987.4
137.5°	1034.1	1034.5	1035.0	1035.2	1035.1	1034.9	1034.7	1034.7
140°	1064.8	1065.5	1066.2	1066.6	1066.8	1067.0	1067.2	1067.5
142.5°	1093.3	1093.7	1094.2	1094.5	1094.6	1094.6	1094.7	1094.7
145°	1133.9	1134.2	1134.4	1134.7	1135.1	1135.6	1136.1	1136.5
147.5°	1169.7	1169.8	1170.0	1170.2	1170.4	1170.7	1170.9	1171.1
150°	1192.5	1192.5	1192.5	1192.7	1192.8	1193.1	1193.3	1193.5
152.5°	1212.5	1212.8	1213.1	1213.2	1213.1	1213.0	1212.9	1212.7
155°	1239.3	1240.2	1241.1	1241.2	1240.5	1239.8	1239.2	1238.5
157.5°	1262.5	1263.6	1264.8	1264.8	1263.6	1262.5	1261.3	1260.2
160°	1277.2	1278.6	1279.9	1279.9	1278.6	1277.2	1275.9	1274.5
162.5°	1289.3	1290.6	1291.9	1291.8	1290.3	1288.8	1287.3	1285.7
165°	1306.1	1307.9	1309.7	1309.6	1307.6	1305.5	1303.6	1301.6
167.5°	1318.5	1320.4	1322.4	1322.2	1320.1	1317.8	1315.6	1313.4
170°	1326.1	1327.9	1329.7	1329.5	1327.2	1325.0	1322.8	1320.6
172.5°	1330.9	1332.7	1334.5	1334.2	1331.8	1329.4	1327.0	1324.6
175°	1336.6	1338.6	1340.6	1340.2	1337.6	1334.9	1332.2	1329.6
177.5°	1338.9	1340.2	1341.7	1341.4	1339.2	1337.0	1334.9	1332.8
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6

(END OF REPORT)