

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332654-927

Luminaire Tested: **S124DIP-S1020D1035U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332654-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D1035U927-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6577.3 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	74	71	65	63	61	54	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	39	35	33	29
5	70	58	50	44	65	54	47	42	47	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	29	36	30	26	31	26	23	27	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10672	10672	10672	10672
5°	12568	10699	9444	10699
10°	15048	10653	8502	10653
15°	17804	10546	7809	10546
20°	19826	10436	7189	10436
25°	20147	10273	6762	10273
30°	17143	10118	6626	10118
35°	13180	9866	6628	9866
40°	10273	9569	6752	9569
45°	8566	9122	6865	9122
50°	7538	8577	7097	8577
55°	6906	7924	7385	7924
60°	6471	7340	7727	7340
65°	6025	6684	8013	6684
70°	5507	6035	8195	6035
75°	4919	5312	8097	5312
80°	4124	4351	7843	4351
85°	3047	3149	7503	3149



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.8	2.0
10°-20°	397.0	6.0
20°-30°	629.5	9.6
30°-40°	700.6	10.7
40°-50°	637.7	9.7
50°-60°	521.1	7.9
60°-70°	372.0	5.7
70°-80°	204.9	3.1
80°-90°	58.2	0.9
90°-100°	290.8	4.4
100°-110°	605.1	9.2
110°-120°	542.0	8.2
120°-130°	455.9	6.9
130°-140°	380.1	5.8
140°-150°	290.4	4.4
150°-160°	204.1	3.1
160°-170°	120.1	1.8
170°-180°	39.1	0.6
0°-30°	1155.3	17.6
0°-40°	1855.8	28.2
0°-60°	3014.6	45.8
0°-90°	3649.7	55.5
90°-120°	1437.9	21.9
90°-150°	2564.4	39.0
90°-180°	2928.0	44.5
0°-180°	6577.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1322	1322	1322	1322	1322	
5°	1551	1320	1165	1320	1551	158
15°	2130	1262	934	1262	2130	602
25°	2262	1153	759	1153	2262	997
35°	1337	1001	672	1001	1337	849
45°	750	799	601	799	750	591
55°	491	563	525	563	491	443
65°	315	350	420	350	315	312
75°	158	170	260	170	158	168
85°	33	34	81	34	33	40
90°	17	1	17	1	17	15
95°	193	26	193	26	193	299
105°	1113	92	1113	92	1113	1100
115°	1068	163	1068	163	1068	1061
125°	852	227	852	227	852	775
135°	762	270	762	270	762	588
145°	622	311	622	311	622	395
155°	521	354	521	354	521	243
165°	455	385	455	385	455	130
175°	410	402	410	402	410	40
180°	402	402	402	402	402	



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1407.0	1406.6	1402.2	1401.3	1398.2	1394.3	1393.4	1386.4	1372.4	1365.8	1364.1
5°	1550.9	1561.9	1547.6	1544.9	1543.3	1525.2	1515.8	1504.9	1479.7	1464.9	1453.4
7.5°	1722.7	1723.9	1717.8	1712.7	1698.8	1683.0	1659.4	1634.2	1604.2	1573.0	1549.4
10°	1835.7	1840.1	1833.0	1831.8	1804.0	1786.4	1751.4	1721.8	1687.8	1650.0	1615.6
12.5°	1954.9	1948.7	1945.1	1921.7	1916.5	1884.5	1843.8	1813.4	1761.0	1717.5	1671.6
15°	2130.3	2118.3	2110.6	2078.3	2062.4	2018.1	1974.8	1941.4	1873.0	1807.8	1758.5
17.5°	2233.2	2245.4	2227.6	2214.3	2173.3	2142.1	2097.9	2027.8	1974.3	1893.3	1831.1
20°	2307.8	2308.8	2299.0	2285.3	2253.0	2213.6	2165.4	2088.7	2024.7	1944.1	1858.7
22.5°	2327.9	2328.1	2323.9	2311.1	2286.7	2254.7	2206.1	2142.1	2064.5	1977.0	1891.6
25°	2261.8	2259.5	2264.5	2278.7	2269.4	2259.5	2231.7	2184.0	2111.7	2019.1	1927.1
27.5°	2015.9	2031.1	2058.9	2094.0	2127.7	2153.5	2160.7	2150.9	2106.1	2030.0	1933.6
30°	1839.0	1857.6	1878.4	1913.4	1981.3	2020.2	2063.0	2095.2	2077.2	2016.4	1926.6
32.5°	1644.5	1649.1	1680.0	1719.8	1782.0	1856.8	1924.5	1990.1	2011.9	1980.1	1905.1
35°	1337.4	1345.0	1378.4	1417.8	1494.0	1585.4	1687.3	1778.2	1853.2	1883.3	1845.0
37.5°	1091.3	1113.3	1136.9	1179.3	1246.3	1328.6	1434.5	1552.1	1664.0	1738.8	1751.6
40°	974.8	988.5	1005.4	1037.8	1094.7	1175.8	1266.7	1401.4	1520.3	1627.6	1662.6
42.5°	882.8	890.8	901.2	930.4	973.8	1054.4	1137.4	1255.9	1375.2	1503.6	1562.3
45°	750.3	758.5	776.0	793.0	825.9	881.7	958.9	1056.4	1176.3	1300.1	1408.5
47.5°	654.5	659.8	670.2	688.4	716.3	753.1	815.9	897.4	1008.5	1128.7	1244.2
50°	600.2	604.6	612.8	629.2	650.6	683.4	734.9	811.0	898.1	1019.1	1132.5
52.5°	557.3	559.0	565.1	576.2	593.2	620.8	663.1	726.0	807.0	914.9	1027.8
55°	490.7	492.9	498.4	506.6	521.3	538.8	571.2	618.3	689.0	782.6	880.6
57.5°	435.9	437.4	442.0	445.2	457.4	471.7	496.5	530.1	583.7	663.1	750.6
60°	400.8	399.8	405.3	408.0	416.2	428.3	447.4	479.7	526.2	590.3	670.8
62.5°	366.7	365.2	369.8	373.4	378.1	388.4	404.0	429.4	467.1	525.1	594.6
65°	315.4	313.2	316.0	320.4	324.7	330.3	341.7	364.2	394.3	435.9	489.0
67.5°	264.0	266.3	266.7	268.9	271.4	278.8	286.8	302.6	323.8	357.2	402.2
70°	233.3	233.9	236.1	236.1	237.7	244.2	250.8	260.2	280.9	311.6	348.3
72.5°	202.6	204.9	204.1	205.8	207.0	211.4	216.2	225.1	242.8	265.6	296.6
75°	157.7	159.4	159.4	159.9	161.5	163.2	167.0	173.6	186.2	203.2	224.5
77.5°	115.0	115.3	116.0	118.0	118.0	120.6	123.4	128.7	134.9	146.6	159.5
80°	88.7	89.8	89.3	90.4	90.4	92.5	93.6	100.2	103.0	110.6	121.0
82.5°	65.0	66.1	66.1	67.6	68.4	68.9	70.4	73.0	75.8	82.5	86.8
85°	32.9	34.0	32.9	34.0	35.6	36.1	37.8	38.3	40.6	42.1	46.0
87.5°	13.0	14.3	14.4	14.7	15.4	15.8	16.2	15.5	17.1	17.7	19.2
90°	16.6	16.6	17.4	16.6	15.8	15.8	15.1	14.3	13.5	14.3	12.7
92.5°	60.9	60.9	63.6	67.9	77.2	93.0	116.9	155.3	209.0	250.9	219.5
95°	193.0	203.3	217.5	242.0	280.7	357.4	463.4	586.0	662.7	644.5	486.4
97.5°	515.8	532.3	556.0	603.6	660.4	742.9	820.2	865.9	832.6	678.8	455.2
100°	725.2	731.5	755.3	803.5	872.3	930.8	969.6	953.8	838.3	635.8	412.8
102.5°	907.4	912.5	937.5	972.4	1014.6	1039.0	1027.8	949.4	790.8	582.1	384.4
105°	1112.7	1117.5	1128.5	1134.9	1133.3	1100.8	1022.5	885.7	704.6	518.8	359.8
107.5°	1189.0	1186.9	1179.0	1160.9	1121.9	1051.4	941.1	795.4	635.0	483.4	355.4
110°	1190.3	1183.1	1168.9	1135.7	1079.5	992.5	877.8	741.0	600.2	471.3	356.6



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1152.9	1141.4	1121.4	1081.2	1017.5	930.5	822.1	701.2	580.7	465.6	360.4
115°	1068.4	1062.1	1036.8	989.4	926.9	851.0	758.4	661.2	562.3	462.6	367.7
117.5°	982.9	977.9	952.4	912.5	859.2	794.8	722.1	641.5	554.1	461.8	375.5
120°	934.8	926.1	905.5	870.7	825.6	769.5	706.2	632.6	549.6	461.8	381.2
122.5°	896.8	888.1	870.7	841.0	802.9	753.7	696.1	625.1	544.5	461.2	386.9
125°	852.5	847.8	832.7	809.8	778.2	734.7	680.1	612.1	536.2	460.3	395.5
127.5°	826.6	821.8	809.2	788.8	757.0	715.7	661.3	596.3	525.0	458.5	402.2
130°	811.4	806.7	794.0	774.2	741.8	699.9	646.1	583.7	518.0	457.9	407.3
132.5°	794.3	789.6	777.5	755.3	723.5	681.5	629.1	570.4	511.7	457.2	411.7
135°	762.4	757.6	745.0	722.9	691.2	651.6	603.4	552.0	502.2	456.3	418.4
137.5°	722.9	717.2	706.7	684.8	655.3	619.6	578.9	535.4	493.9	456.1	422.3
140°	694.3	688.0	677.0	659.6	631.8	598.7	563.1	525.9	489.6	455.5	425.5
142.5°	664.0	659.6	649.7	633.6	609.1	580.4	549.8	517.1	485.8	455.5	428.0
145°	622.4	618.5	610.5	597.1	577.3	555.2	531.5	504.5	479.3	453.9	429.4
147.5°	585.5	584.2	578.1	566.6	552.0	534.6	515.6	494.2	473.4	451.1	430.2
150°	564.7	563.9	559.1	548.8	536.2	522.0	506.1	488.0	469.0	449.2	430.2
152.5°	545.7	544.9	542.0	533.7	522.9	511.2	496.6	481.0	463.9	446.0	429.0
155°	521.2	521.2	518.8	512.5	504.5	495.0	483.2	470.6	456.3	441.3	427.1
157.5°	499.6	499.6	498.2	493.5	487.5	479.9	469.9	459.3	448.5	436.4	425.0
160°	486.4	486.4	485.6	480.9	476.1	469.8	461.1	452.3	442.9	432.6	423.1
162.5°	473.7	474.4	473.6	468.8	465.3	459.6	452.8	445.4	437.8	428.8	421.2
165°	454.7	455.5	456.3	453.1	450.0	446.0	440.5	435.8	429.4	423.1	417.6
167.5°	439.7	440.4	440.5	438.5	436.9	434.5	430.1	426.4	421.8	417.4	413.8
170°	430.2	430.2	431.0	430.2	428.6	426.3	423.1	420.7	416.8	413.6	411.2
172.5°	420.7	422.0	422.8	422.0	421.0	419.3	417.4	415.7	412.3	409.8	408.7
175°	409.6	411.2	412.8	411.2	411.2	411.2	409.6	408.8	407.3	405.7	405.7
177.5°	403.1	404.4	405.7	405.0	405.7	405.0	405.0	404.4	403.8	403.1	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1364.5	1358.4	1354.0	1350.5	1340.8	1335.1	1330.8	1324.6	1317.6	1310.2	1301.0
5°	1441.9	1423.3	1409.6	1388.9	1369.1	1352.7	1335.7	1320.3	1301.7	1281.5	1266.7
7.5°	1523.3	1495.6	1460.2	1429.3	1394.7	1364.6	1337.7	1310.0	1281.4	1253.5	1228.0
10°	1575.0	1539.4	1500.0	1453.4	1409.6	1370.7	1334.6	1299.6	1265.6	1231.6	1202.6
12.5°	1630.6	1586.3	1528.0	1473.6	1424.5	1372.5	1328.9	1285.9	1245.0	1209.3	1175.4
15°	1705.3	1641.2	1573.9	1501.1	1436.5	1375.7	1316.0	1261.8	1215.8	1168.6	1135.8
17.5°	1751.3	1672.0	1595.0	1518.9	1440.6	1364.0	1299.6	1237.0	1179.4	1132.7	1091.2
20°	1781.5	1702.6	1606.8	1530.7	1437.6	1358.7	1284.2	1214.7	1154.4	1104.6	1061.8
22.5°	1807.8	1716.7	1620.8	1520.6	1427.9	1344.3	1262.7	1192.8	1131.2	1078.7	1037.8
25°	1822.0	1717.4	1613.4	1513.7	1408.5	1309.4	1235.5	1153.3	1087.6	1032.3	988.5
27.5°	1823.5	1711.7	1593.9	1483.2	1374.7	1282.4	1189.1	1115.6	1047.4	989.0	946.9
30°	1818.7	1702.1	1575.6	1455.6	1346.6	1246.4	1165.4	1085.4	1015.9	957.8	914.0
32.5°	1803.4	1681.9	1551.9	1425.0	1312.0	1214.0	1130.4	1054.3	986.5	929.3	883.4
35°	1759.0	1639.1	1500.6	1368.6	1253.0	1153.9	1078.3	1001.1	933.2	878.9	834.6
37.5°	1689.7	1581.3	1440.4	1303.9	1190.3	1090.8	1015.9	946.1	884.9	829.8	784.3
40°	1629.2	1533.9	1392.7	1259.6	1136.9	1042.2	972.1	908.0	847.2	795.2	751.9
42.5°	1559.6	1476.5	1346.2	1205.2	1087.0	991.8	923.4	865.9	808.7	760.6	717.3
45°	1435.4	1380.6	1257.9	1127.6	1004.4	914.6	849.4	799.0	750.8	703.7	667.6
47.5°	1292.5	1265.4	1162.1	1038.3	921.4	832.8	776.3	729.8	687.5	647.6	615.8
50°	1196.6	1183.4	1094.2	974.8	863.1	779.8	722.9	682.9	646.7	611.7	581.6
52.5°	1101.9	1101.5	1021.0	911.7	808.3	728.2	671.6	634.3	602.9	574.5	547.4
55°	957.3	972.6	909.7	812.1	719.6	647.3	596.4	563.0	541.1	517.5	497.3
57.5°	824.4	849.9	797.9	712.0	634.9	568.2	523.9	498.8	475.5	461.2	446.5
60°	737.7	761.8	721.3	649.0	576.2	519.2	477.0	454.6	434.3	424.5	414.0
62.5°	660.6	682.1	652.0	585.0	521.8	467.0	431.4	409.9	396.2	385.4	378.5
65°	550.4	568.5	542.7	494.0	439.7	395.9	366.9	349.9	336.8	332.4	324.7
67.5°	444.9	461.4	447.4	406.0	362.5	329.4	306.7	290.3	282.6	278.8	273.3
70°	382.2	398.7	383.9	347.8	314.3	286.5	265.1	255.7	247.6	245.9	238.2
72.5°	329.2	340.4	325.7	297.4	268.8	245.3	228.7	219.0	214.7	211.8	207.6
75°	247.0	256.8	247.0	225.1	204.8	188.4	174.1	170.3	165.4	163.7	161.0
77.5°	174.8	183.3	175.8	162.1	146.9	134.3	126.6	121.7	120.6	117.7	119.1
80°	133.6	139.1	132.0	122.7	110.6	101.9	96.4	93.6	90.4	89.3	91.4
82.5°	95.9	98.4	94.7	88.5	79.5	73.8	70.1	66.9	66.2	66.5	66.5
85°	49.8	49.3	48.7	43.3	40.6	36.7	34.5	34.0	33.4	34.5	35.6
87.5°	18.9	19.3	17.9	16.2	14.7	13.2	12.3	11.6	12.3	13.2	13.8
90°	11.1	11.1	6.3	6.3	5.5	4.8	2.4	0.8	2.4	4.8	5.5
92.5°	159.8	98.4	58.2	41.7	30.2	20.6	13.2	9.0	13.2	20.6	30.2
95°	297.4	167.6	98.9	65.7	46.7	36.4	28.4	26.1	28.4	36.4	46.7
97.5°	267.3	160.3	107.3	79.4	63.1	53.6	46.8	46.8	46.8	53.6	63.1
100°	251.5	162.2	115.5	90.2	75.1	65.7	60.1	60.1	60.1	65.7	75.1
102.5°	247.1	168.4	126.2	102.2	87.8	78.9	74.0	72.7	74.0	78.9	87.8
105°	249.1	183.5	145.5	122.6	108.4	98.9	94.9	92.5	94.9	98.9	108.4
107.5°	260.8	201.1	166.2	143.6	130.0	119.9	116.0	114.4	116.0	119.9	130.0
110°	269.7	214.3	179.5	158.2	143.9	134.4	130.5	128.9	130.5	134.4	143.9





TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	279.2	227.0	193.5	172.1	157.9	149.0	144.4	142.8	144.4	149.0	157.9
115°	294.2	246.8	215.1	193.8	178.7	170.8	165.2	163.0	165.2	170.8	178.7
117.5°	309.5	265.9	235.8	213.7	199.6	190.9	186.0	183.8	186.0	190.9	199.6
120°	320.3	279.2	249.1	227.0	213.5	204.9	199.3	197.7	199.3	204.9	213.5
122.5°	330.4	291.8	261.7	240.3	225.5	217.5	211.9	210.4	211.9	217.5	225.5
125°	345.6	309.2	280.7	258.6	243.6	234.9	230.1	227.0	230.1	234.9	243.6
127.5°	358.7	325.3	297.9	275.5	259.8	249.9	244.2	241.7	244.2	249.9	259.8
130°	366.9	336.1	309.2	286.3	271.2	259.4	253.1	249.9	253.1	259.4	271.2
132.5°	375.2	345.0	318.1	296.4	280.1	268.9	260.6	258.1	260.6	268.9	280.1
135°	386.0	357.4	331.4	310.8	294.2	280.7	272.8	269.7	272.8	280.7	294.2
137.5°	393.6	366.9	342.6	323.0	305.7	292.9	284.2	281.2	284.2	292.9	305.7
140°	398.5	373.3	349.6	330.6	313.9	300.6	291.8	289.5	291.8	300.6	313.9
142.5°	402.3	379.0	355.8	337.5	321.5	308.7	300.7	298.3	300.7	308.7	321.5
145°	406.5	385.2	364.6	347.2	332.2	321.1	313.1	310.8	313.1	321.1	332.2
147.5°	410.1	391.5	372.2	356.5	344.0	332.6	325.7	324.9	325.7	332.6	344.0
150°	412.0	394.7	377.2	362.2	350.4	340.9	334.5	333.7	334.5	340.9	350.4
152.5°	413.3	397.2	381.7	367.9	357.3	348.5	342.1	342.0	342.1	348.5	357.3
155°	414.4	400.9	387.5	375.7	366.9	359.0	354.3	353.5	354.3	359.0	366.9
157.5°	414.4	403.6	392.3	382.9	375.3	369.2	364.7	364.7	364.7	369.2	375.3
160°	414.4	404.9	395.5	386.7	380.4	374.9	371.7	371.7	371.7	374.9	380.4
162.5°	414.4	406.2	397.4	390.5	384.8	379.9	377.4	378.0	377.4	379.9	384.8
165°	412.8	406.5	399.3	394.7	390.7	386.7	385.2	385.2	385.2	386.7	390.7
167.5°	410.9	406.3	401.1	397.5	395.3	392.3	391.5	392.3	391.5	392.3	395.3
170°	409.6	405.7	401.7	399.3	397.8	395.5	394.7	395.5	394.7	395.5	397.8
172.5°	408.4	405.0	402.3	400.6	399.7	397.9	397.8	398.5	397.8	397.9	399.7
175°	406.5	404.1	402.5	402.5	401.7	400.9	400.9	401.7	400.9	400.9	401.7
177.5°	404.4	403.1	402.5	402.5	402.5	401.9	402.5	403.1	402.5	401.9	402.5
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1296.6	1292.7	1287.0	1279.1	1272.5	1265.5	1263.8	1261.1	1266.4	1261.9	1260.7
5°	1254.1	1242.6	1227.8	1210.9	1200.9	1186.8	1184.0	1178.5	1173.1	1172.5	1167.0
7.5°	1209.1	1192.2	1172.8	1155.6	1139.6	1123.9	1113.8	1111.6	1103.5	1098.8	1093.3
10°	1180.2	1159.4	1136.9	1120.5	1101.8	1085.4	1074.0	1067.4	1061.8	1055.8	1050.4
12.5°	1146.0	1123.9	1105.3	1087.6	1065.5	1053.0	1034.0	1022.6	1021.6	1021.7	1007.4
15°	1106.2	1084.3	1055.8	1030.6	1018.6	994.5	984.1	971.0	962.7	954.5	948.0
17.5°	1060.8	1033.5	1011.3	982.4	959.3	940.2	926.5	918.6	906.3	894.6	886.2
20°	1032.3	1003.3	979.7	949.0	923.8	900.3	888.8	877.9	868.5	858.7	849.4
22.5°	1003.4	973.0	944.2	914.4	891.0	866.2	855.1	840.2	831.3	825.9	816.5
25°	957.8	925.0	892.1	863.6	839.6	817.6	802.9	791.3	781.5	777.1	771.1
27.5°	908.3	875.7	843.9	811.6	784.3	768.3	756.5	747.8	742.2	736.3	733.6
30°	876.8	842.8	808.9	778.7	753.5	737.7	726.7	720.7	716.3	713.6	710.8
32.5°	844.8	811.3	775.5	748.1	725.5	711.4	703.1	697.0	694.8	693.9	692.8
35°	793.5	759.5	726.7	702.1	680.7	675.3	668.1	664.8	663.8	667.6	669.2
37.5°	743.9	712.4	682.1	658.2	644.3	636.3	633.8	634.0	637.9	641.3	645.2
40°	711.9	681.3	652.8	632.0	618.9	613.9	612.8	615.5	620.0	623.8	628.1
42.5°	680.8	650.6	624.7	605.2	596.0	591.5	592.2	594.9	601.1	605.8	612.4
45°	632.6	607.4	582.2	566.3	558.6	559.7	559.7	564.6	570.6	577.7	584.9
47.5°	587.1	561.7	541.0	527.6	523.6	522.7	525.8	532.2	540.8	549.6	559.6
50°	556.4	532.3	514.2	502.2	497.8	499.5	503.8	509.8	520.2	531.2	541.6
52.5°	525.3	503.4	486.6	475.5	472.4	475.4	479.7	489.3	498.4	510.2	522.8
55°	477.0	458.4	445.2	437.0	435.9	437.6	442.5	452.9	466.0	480.9	492.9
57.5°	428.9	413.4	401.3	395.6	396.2	397.7	405.8	418.2	432.2	448.0	463.5
60°	396.5	382.2	372.4	368.0	368.5	371.9	381.7	393.2	410.7	426.0	442.5
62.5°	365.8	353.3	343.9	340.0	339.2	346.4	355.8	367.8	385.3	402.4	420.2
65°	316.6	306.7	299.0	296.8	298.5	304.0	316.0	331.8	346.7	364.7	383.3
67.5°	268.3	260.2	255.0	256.0	257.9	266.0	276.2	289.8	306.6	325.3	343.7
70°	237.7	230.0	225.6	226.2	229.5	239.3	248.1	261.7	279.9	299.0	314.3
72.5°	206.1	201.1	197.2	199.5	202.7	209.5	220.5	234.2	250.1	267.9	284.1
75°	158.3	158.3	156.1	157.7	162.6	169.2	177.4	191.7	207.6	221.8	235.0
77.5°	117.4	116.2	117.6	119.6	122.5	130.2	139.7	149.8	161.8	176.0	186.9
80°	89.8	90.4	93.1	96.4	97.5	103.5	113.4	122.7	132.0	144.0	154.4
82.5°	67.5	68.0	69.5	73.6	74.7	81.2	87.5	96.8	105.3	113.4	122.0
85°	36.7	36.7	39.5	41.0	43.8	48.2	52.0	57.5	65.2	70.7	78.8
87.5°	15.3	15.3	18.0	18.9	20.5	23.0	23.7	28.7	30.6	33.0	36.9
90°	6.3	6.3	11.1	11.1	12.7	14.3	13.5	14.3	15.1	15.8	15.8
92.5°	41.7	58.2	98.4	159.8	219.5	250.9	209.0	155.3	116.9	93.0	77.2
95°	65.7	98.9	167.6	297.4	486.4	644.5	662.7	586.0	463.4	357.4	280.7
97.5°	79.4	107.3	160.3	267.3	455.2	678.8	832.6	865.9	820.2	742.9	660.4
100°	90.2	115.5	162.2	251.5	412.8	635.8	838.3	953.8	969.6	930.8	872.3
102.5°	102.2	126.2	168.4	247.1	384.4	582.1	790.8	949.4	1027.8	1039.0	1014.6
105°	122.6	145.5	183.5	249.1	359.8	518.8	704.6	885.7	1022.5	1100.8	1133.3
107.5°	143.6	166.2	201.1	260.8	355.4	483.4	635.0	795.4	941.1	1051.4	1121.9
110°	158.2	179.5	214.3	269.7	356.6	471.3	600.2	741.0	877.8	992.5	1079.5



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	172.1	193.5	227.0	279.2	360.4	465.6	580.7	701.2	822.1	930.5	1017.5
115°	193.8	215.1	246.8	294.2	367.7	462.6	562.3	661.2	758.4	851.0	926.9
117.5°	213.7	235.8	265.9	309.5	375.5	461.8	554.1	641.5	722.1	794.8	859.2
120°	227.0	249.1	279.2	320.3	381.2	461.8	549.6	632.6	706.2	769.5	825.6
122.5°	240.3	261.7	291.8	330.4	386.9	461.2	544.5	625.1	696.1	753.7	802.9
125°	258.6	280.7	309.2	345.6	395.5	460.3	536.2	612.1	680.1	734.7	778.2
127.5°	275.5	297.9	325.3	358.7	402.2	458.5	525.0	596.3	661.3	715.7	757.0
130°	286.3	309.2	336.1	366.9	407.3	457.9	518.0	583.7	646.1	699.9	741.8
132.5°	296.4	318.1	345.0	375.2	411.7	457.2	511.7	570.4	629.1	681.5	723.5
135°	310.8	331.4	357.4	386.0	418.4	456.3	502.2	552.0	603.4	651.6	691.2
137.5°	323.0	342.6	366.9	393.6	422.3	456.1	493.9	535.4	578.9	619.6	655.3
140°	330.6	349.6	373.3	398.5	425.5	455.5	489.6	525.9	563.1	598.7	631.8
142.5°	337.5	355.8	379.0	402.3	428.0	455.5	485.8	517.1	549.8	580.4	609.1
145°	347.2	364.6	385.2	406.5	429.4	453.9	479.3	504.5	531.5	555.2	577.3
147.5°	356.5	372.2	391.5	410.1	430.2	451.1	473.4	494.2	515.6	534.6	552.0
150°	362.2	377.2	394.7	412.0	430.2	449.2	469.0	488.0	506.1	522.0	536.2
152.5°	367.9	381.7	397.2	413.3	429.0	446.0	463.9	481.0	496.6	511.2	522.9
155°	375.7	387.5	400.9	414.4	427.1	441.3	456.3	470.6	483.2	495.0	504.5
157.5°	382.9	392.3	403.6	414.4	425.0	436.4	448.5	459.3	469.9	479.9	487.5
160°	386.7	395.5	404.9	414.4	423.1	432.6	442.9	452.3	461.1	469.8	476.1
162.5°	390.5	397.4	406.2	414.4	421.2	428.8	437.8	445.4	452.8	459.6	465.3
165°	394.7	399.3	406.5	412.8	417.6	423.1	429.4	435.8	440.5	446.0	450.0
167.5°	397.5	401.1	406.3	410.9	413.8	417.4	421.8	426.4	430.1	434.5	436.9
170°	399.3	401.7	405.7	409.6	411.2	413.6	416.8	420.7	423.1	426.3	428.6
172.5°	400.6	402.3	405.0	408.4	408.7	409.8	412.3	415.7	417.4	419.3	421.0
175°	402.5	402.5	404.1	406.5	405.7	405.7	407.3	408.8	409.6	411.2	411.2
177.5°	402.5	402.5	403.1	404.4	403.1	403.1	403.8	404.4	405.0	405.0	405.7
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1259.8	1258.9	1255.8	1255.5	1255.8	1258.9	1259.8	1260.7	1261.9	1266.4	1261.1
5°	1163.7	1161.0	1159.4	1165.4	1159.4	1161.0	1163.7	1167.0	1172.5	1173.1	1178.5
7.5°	1091.3	1089.2	1084.3	1082.8	1084.3	1089.2	1091.3	1093.3	1098.8	1103.5	1111.6
10°	1044.9	1042.7	1038.3	1037.2	1038.3	1042.7	1044.9	1050.4	1055.8	1061.8	1067.4
12.5°	1000.2	995.9	995.0	996.0	995.0	995.9	1000.2	1007.4	1021.7	1021.6	1022.6
15°	940.9	938.7	932.6	934.3	932.6	938.7	940.9	948.0	954.5	962.7	971.0
17.5°	882.3	879.7	872.4	878.8	872.4	879.7	882.3	886.2	894.6	906.3	918.6
20°	845.6	841.1	837.3	836.8	837.3	841.1	845.6	849.4	858.7	868.5	877.9
22.5°	810.5	806.6	806.2	802.6	806.2	806.6	810.5	816.5	825.9	831.3	840.2
25°	766.7	762.9	761.8	759.1	761.8	762.9	766.7	771.1	777.1	781.5	791.3
27.5°	733.1	731.2	729.2	730.1	729.2	731.2	733.1	733.6	736.3	742.2	747.8
30°	712.5	711.9	710.8	710.8	710.8	711.9	712.5	710.8	713.6	716.3	720.7
32.5°	695.4	695.3	695.9	695.9	695.9	695.3	695.4	692.8	693.9	694.8	697.0
35°	671.4	673.0	674.1	672.5	674.1	673.0	671.4	669.2	667.6	663.8	664.8
37.5°	649.7	651.3	652.9	654.7	652.9	651.3	649.7	645.2	641.3	637.9	634.0
40°	633.0	636.9	638.0	640.7	638.0	636.9	633.0	628.1	623.8	620.0	615.5
42.5°	617.3	621.5	624.4	625.0	624.4	621.5	617.3	612.4	605.8	601.1	594.9
45°	593.1	597.5	601.3	601.3	601.3	597.5	593.1	584.9	577.7	570.6	564.6
47.5°	568.0	574.3	578.2	579.2	578.2	574.3	568.0	559.6	549.6	540.8	532.2
50°	551.0	558.6	562.4	565.1	562.4	558.6	551.0	541.6	531.2	520.2	509.8
52.5°	534.2	541.9	547.1	548.5	547.1	541.9	534.2	522.8	510.2	498.4	489.3
55°	505.5	516.4	522.4	524.7	522.4	516.4	505.5	492.9	480.9	466.0	452.9
57.5°	478.3	488.4	495.4	497.0	495.4	488.4	478.3	463.5	448.0	432.2	418.2
60°	457.2	468.3	477.0	478.6	477.0	468.3	457.2	442.5	426.0	410.7	393.2
62.5°	435.8	447.2	455.1	459.4	455.1	447.2	435.8	420.2	402.4	385.3	367.8
65°	398.7	410.2	417.9	419.5	417.9	410.2	398.7	383.3	364.7	346.7	331.8
67.5°	358.1	369.6	374.7	377.9	374.7	369.6	358.1	343.7	325.3	306.6	289.8
70°	329.7	339.0	344.4	347.2	344.4	339.0	329.7	314.3	299.0	279.9	261.7
72.5°	297.2	307.0	313.4	313.9	313.4	307.0	297.2	284.1	267.9	250.1	234.2
75°	247.6	256.3	259.6	259.6	259.6	256.3	247.6	235.0	221.8	207.6	191.7
77.5°	195.9	200.4	204.6	205.5	204.6	200.4	195.9	186.9	176.0	161.8	149.8
80°	162.6	165.4	168.7	168.7	168.7	165.4	162.6	154.4	144.0	132.0	122.7
82.5°	128.5	130.8	134.0	133.6	134.0	130.8	128.5	122.0	113.4	105.3	96.8
85°	77.8	82.7	82.1	81.0	82.1	82.7	77.8	78.8	70.7	65.2	57.5
87.5°	38.3	39.0	40.1	41.0	40.1	39.0	38.3	36.9	33.0	30.6	28.7
90°	16.6	17.4	16.6	16.6	16.6	17.4	16.6	15.8	15.8	15.1	14.3
92.5°	67.9	63.6	60.9	60.9	60.9	63.6	67.9	77.2	93.0	116.9	155.3
95°	242.0	217.5	203.3	193.0	203.3	217.5	242.0	280.7	357.4	463.4	586.0
97.5°	603.6	556.0	532.3	515.8	532.3	556.0	603.6	660.4	742.9	820.2	865.9
100°	803.5	755.3	731.5	725.2	731.5	755.3	803.5	872.3	930.8	969.6	953.8
102.5°	972.4	937.5	912.5	907.4	912.5	937.5	972.4	1014.6	1039.0	1027.8	949.4
105°	1134.9	1128.5	1117.5	1112.7	1117.5	1128.5	1134.9	1133.3	1100.8	1022.5	885.7
107.5°	1160.9	1179.0	1186.9	1189.0	1186.9	1179.0	1160.9	1121.9	1051.4	941.1	795.4
110°	1135.7	1168.9	1183.1	1190.3	1183.1	1168.9	1135.7	1079.5	992.5	877.8	741.0



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1081.2	1121.4	1141.4	1152.9	1141.4	1121.4	1081.2	1017.5	930.5	822.1	701.2
115°	989.4	1036.8	1062.1	1068.4	1062.1	1036.8	989.4	926.9	851.0	758.4	661.2
117.5°	912.5	952.4	977.9	982.9	977.9	952.4	912.5	859.2	794.8	722.1	641.5
120°	870.7	905.5	926.1	934.8	926.1	905.5	870.7	825.6	769.5	706.2	632.6
122.5°	841.0	870.7	888.1	896.8	888.1	870.7	841.0	802.9	753.7	696.1	625.1
125°	809.8	832.7	847.8	852.5	847.8	832.7	809.8	778.2	734.7	680.1	612.1
127.5°	788.8	809.2	821.8	826.6	821.8	809.2	788.8	757.0	715.7	661.3	596.3
130°	774.2	794.0	806.7	811.4	806.7	794.0	774.2	741.8	699.9	646.1	583.7
132.5°	755.3	777.5	789.6	794.3	789.6	777.5	755.3	723.5	681.5	629.1	570.4
135°	722.9	745.0	757.6	762.4	757.6	745.0	722.9	691.2	651.6	603.4	552.0
137.5°	684.8	706.7	717.2	722.9	717.2	706.7	684.8	655.3	619.6	578.9	535.4
140°	659.6	677.0	688.0	694.3	688.0	677.0	659.6	631.8	598.7	563.1	525.9
142.5°	633.6	649.7	659.6	664.0	659.6	649.7	633.6	609.1	580.4	549.8	517.1
145°	597.1	610.5	618.5	622.4	618.5	610.5	597.1	577.3	555.2	531.5	504.5
147.5°	566.6	578.1	584.2	585.5	584.2	578.1	566.6	552.0	534.6	515.6	494.2
150°	548.8	559.1	563.9	564.7	563.9	559.1	548.8	536.2	522.0	506.1	488.0
152.5°	533.7	542.0	544.9	545.7	544.9	542.0	533.7	522.9	511.2	496.6	481.0
155°	512.5	518.8	521.2	521.2	521.2	518.8	512.5	504.5	495.0	483.2	470.6
157.5°	493.5	498.2	499.6	499.6	499.6	498.2	493.5	487.5	479.9	469.9	459.3
160°	480.9	485.6	486.4	486.4	486.4	485.6	480.9	476.1	469.8	461.1	452.3
162.5°	468.8	473.6	474.4	473.7	474.4	473.6	468.8	465.3	459.6	452.8	445.4
165°	453.1	456.3	455.5	454.7	455.5	456.3	453.1	450.0	446.0	440.5	435.8
167.5°	438.5	440.5	440.4	439.7	440.4	440.5	438.5	436.9	434.5	430.1	426.4
170°	430.2	431.0	430.2	430.2	430.2	431.0	430.2	428.6	426.3	423.1	420.7
172.5°	422.0	422.8	422.0	420.7	422.0	422.8	422.0	421.0	419.3	417.4	415.7
175°	411.2	412.8	411.2	409.6	411.2	412.8	411.2	411.2	411.2	409.6	408.8
177.5°	405.0	405.7	404.4	403.1	404.4	405.7	405.0	405.7	405.0	405.0	404.4
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1263.8	1265.5	1272.5	1279.1	1287.0	1292.7	1296.6	1301.0	1310.2	1317.6	1324.6
5°	1184.0	1186.8	1200.9	1210.9	1227.8	1242.6	1254.1	1266.7	1281.5	1301.7	1320.3
7.5°	1113.8	1123.9	1139.6	1155.6	1172.8	1192.2	1209.1	1228.0	1253.5	1281.4	1310.0
10°	1074.0	1085.4	1101.8	1120.5	1136.9	1159.4	1180.2	1202.6	1231.6	1265.6	1299.6
12.5°	1034.0	1053.0	1065.5	1087.6	1105.3	1123.9	1146.0	1175.4	1209.3	1245.0	1285.9
15°	984.1	994.5	1018.6	1030.6	1055.8	1084.3	1106.2	1135.8	1168.6	1215.8	1261.8
17.5°	926.5	940.2	959.3	982.4	1011.3	1033.5	1060.8	1091.2	1132.7	1179.4	1237.0
20°	888.8	900.3	923.8	949.0	979.7	1003.3	1032.3	1061.8	1104.6	1154.4	1214.7
22.5°	855.1	866.2	891.0	914.4	944.2	973.0	1003.4	1037.8	1078.7	1131.2	1192.8
25°	802.9	817.6	839.6	863.6	892.1	925.0	957.8	988.5	1032.3	1087.6	1153.3
27.5°	756.5	768.3	784.3	811.6	843.9	875.7	908.3	946.9	989.0	1047.4	1115.6
30°	726.7	737.7	753.5	778.7	808.9	842.8	876.8	914.0	957.8	1015.9	1085.4
32.5°	703.1	711.4	725.5	748.1	775.5	811.3	844.8	883.4	929.3	986.5	1054.3
35°	668.1	675.3	680.7	702.1	726.7	759.5	793.5	834.6	878.9	933.2	1001.1
37.5°	633.8	636.3	644.3	658.2	682.1	712.4	743.9	784.3	829.8	884.9	946.1
40°	612.8	613.9	618.9	632.0	652.8	681.3	711.9	751.9	795.2	847.2	908.0
42.5°	592.2	591.5	596.0	605.2	624.7	650.6	680.8	717.3	760.6	808.7	865.9
45°	559.7	559.7	558.6	566.3	582.2	607.4	632.6	667.6	703.7	750.8	799.0
47.5°	525.8	522.7	523.6	527.6	541.0	561.7	587.1	615.8	647.6	687.5	729.8
50°	503.8	499.5	497.8	502.2	514.2	532.3	556.4	581.6	611.7	646.7	682.9
52.5°	479.7	475.4	472.4	475.5	486.6	503.4	525.3	547.4	574.5	602.9	634.3
55°	442.5	437.6	435.9	437.0	445.2	458.4	477.0	497.3	517.5	541.1	563.0
57.5°	405.8	397.7	396.2	395.6	401.3	413.4	428.9	446.5	461.2	475.5	498.8
60°	381.7	371.9	368.5	368.0	372.4	382.2	396.5	414.0	424.5	434.3	454.6
62.5°	355.8	346.4	339.2	340.0	343.9	353.3	365.8	378.5	385.4	396.2	409.9
65°	316.0	304.0	298.5	296.8	299.0	306.7	316.6	324.7	332.4	336.8	349.9
67.5°	276.2	266.0	257.9	256.0	255.0	260.2	268.3	273.3	278.8	282.6	290.3
70°	248.1	239.3	229.5	226.2	225.6	230.0	237.7	238.2	245.9	247.6	255.7
72.5°	220.5	209.5	202.7	199.5	197.2	201.1	206.1	207.6	211.8	214.7	219.0
75°	177.4	169.2	162.6	157.7	156.1	158.3	158.3	161.0	163.7	165.4	170.3
77.5°	139.7	130.2	122.5	119.6	117.6	116.2	117.4	119.1	117.7	120.6	121.7
80°	113.4	103.5	97.5	96.4	93.1	90.4	89.8	91.4	89.3	90.4	93.6
82.5°	87.5	81.2	74.7	73.6	69.5	68.0	67.5	66.5	66.5	66.2	66.9
85°	52.0	48.2	43.8	41.0	39.5	36.7	36.7	35.6	34.5	33.4	34.0
87.5°	23.7	23.0	20.5	18.9	18.0	15.3	15.3	13.8	13.2	12.3	11.6
90°	13.5	14.3	12.7	11.1	11.1	6.3	6.3	5.5	4.8	2.4	0.8
92.5°	209.0	250.9	219.5	159.8	98.4	58.2	41.7	30.2	20.6	13.2	9.0
95°	662.7	644.5	486.4	297.4	167.6	98.9	65.7	46.7	36.4	28.4	26.1
97.5°	832.6	678.8	455.2	267.3	160.3	107.3	79.4	63.1	53.6	46.8	46.8
100°	838.3	635.8	412.8	251.5	162.2	115.5	90.2	75.1	65.7	60.1	60.1
102.5°	790.8	582.1	384.4	247.1	168.4	126.2	102.2	87.8	78.9	74.0	72.7
105°	704.6	518.8	359.8	249.1	183.5	145.5	122.6	108.4	98.9	94.9	92.5
107.5°	635.0	483.4	355.4	260.8	201.1	166.2	143.6	130.0	119.9	116.0	114.4
110°	600.2	471.3	356.6	269.7	214.3	179.5	158.2	143.9	134.4	130.5	128.9



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	580.7	465.6	360.4	279.2	227.0	193.5	172.1	157.9	149.0	144.4	142.8
115°	562.3	462.6	367.7	294.2	246.8	215.1	193.8	178.7	170.8	165.2	163.0
117.5°	554.1	461.8	375.5	309.5	265.9	235.8	213.7	199.6	190.9	186.0	183.8
120°	549.6	461.8	381.2	320.3	279.2	249.1	227.0	213.5	204.9	199.3	197.7
122.5°	544.5	461.2	386.9	330.4	291.8	261.7	240.3	225.5	217.5	211.9	210.4
125°	536.2	460.3	395.5	345.6	309.2	280.7	258.6	243.6	234.9	230.1	227.0
127.5°	525.0	458.5	402.2	358.7	325.3	297.9	275.5	259.8	249.9	244.2	241.7
130°	518.0	457.9	407.3	366.9	336.1	309.2	286.3	271.2	259.4	253.1	249.9
132.5°	511.7	457.2	411.7	375.2	345.0	318.1	296.4	280.1	268.9	260.6	258.1
135°	502.2	456.3	418.4	386.0	357.4	331.4	310.8	294.2	280.7	272.8	269.7
137.5°	493.9	456.1	422.3	393.6	366.9	342.6	323.0	305.7	292.9	284.2	281.2
140°	489.6	455.5	425.5	398.5	373.3	349.6	330.6	313.9	300.6	291.8	289.5
142.5°	485.8	455.5	428.0	402.3	379.0	355.8	337.5	321.5	308.7	300.7	298.3
145°	479.3	453.9	429.4	406.5	385.2	364.6	347.2	332.2	321.1	313.1	310.8
147.5°	473.4	451.1	430.2	410.1	391.5	372.2	356.5	344.0	332.6	325.7	324.9
150°	469.0	449.2	430.2	412.0	394.7	377.2	362.2	350.4	340.9	334.5	333.7
152.5°	463.9	446.0	429.0	413.3	397.2	381.7	367.9	357.3	348.5	342.1	342.0
155°	456.3	441.3	427.1	414.4	400.9	387.5	375.7	366.9	359.0	354.3	353.5
157.5°	448.5	436.4	425.0	414.4	403.6	392.3	382.9	375.3	369.2	364.7	364.7
160°	442.9	432.6	423.1	414.4	404.9	395.5	386.7	380.4	374.9	371.7	371.7
162.5°	437.8	428.8	421.2	414.4	406.2	397.4	390.5	384.8	379.9	377.4	378.0
165°	429.4	423.1	417.6	412.8	406.5	399.3	394.7	390.7	386.7	385.2	385.2
167.5°	421.8	417.4	413.8	410.9	406.3	401.1	397.5	395.3	392.3	391.5	392.3
170°	416.8	413.6	411.2	409.6	405.7	401.7	399.3	397.8	395.5	394.7	395.5
172.5°	412.3	409.8	408.7	408.4	405.0	402.3	400.6	399.7	397.9	397.8	398.5
175°	407.3	405.7	405.7	406.5	404.1	402.5	402.5	401.7	400.9	400.9	401.7
177.5°	403.8	403.1	403.1	404.4	403.1	402.5	402.5	402.5	401.9	402.5	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1330.8	1335.1	1340.8	1350.5	1354.0	1358.4	1364.5	1364.1	1365.8	1372.4	1386.4
5°	1335.7	1352.7	1369.1	1388.9	1409.6	1423.3	1441.9	1453.4	1464.9	1479.7	1504.9
7.5°	1337.7	1364.6	1394.7	1429.3	1460.2	1495.6	1523.3	1549.4	1573.0	1604.2	1634.2
10°	1334.6	1370.7	1409.6	1453.4	1500.0	1539.4	1575.0	1615.6	1650.0	1687.8	1721.8
12.5°	1328.9	1372.5	1424.5	1473.6	1528.0	1586.3	1630.6	1671.6	1717.5	1761.0	1813.4
15°	1316.0	1375.7	1436.5	1501.1	1573.9	1641.2	1705.3	1758.5	1807.8	1873.0	1941.4
17.5°	1299.6	1364.0	1440.6	1518.9	1595.0	1672.0	1751.3	1831.1	1893.3	1974.3	2027.8
20°	1284.2	1358.7	1437.6	1530.7	1606.8	1702.6	1781.5	1858.7	1944.1	2024.7	2088.7
22.5°	1262.7	1344.3	1427.9	1520.6	1620.8	1716.7	1807.8	1891.6	1977.0	2064.5	2142.1
25°	1235.5	1309.4	1408.5	1513.7	1613.4	1717.4	1822.0	1927.1	2019.1	2111.7	2184.0
27.5°	1189.1	1282.4	1374.7	1483.2	1593.9	1711.7	1823.5	1933.6	2030.0	2106.1	2150.9
30°	1165.4	1246.4	1346.6	1455.6	1575.6	1702.1	1818.7	1926.6	2016.4	2077.2	2095.2
32.5°	1130.4	1214.0	1312.0	1425.0	1551.9	1681.9	1803.4	1905.1	1980.1	2011.9	1990.1
35°	1078.3	1153.9	1253.0	1368.6	1500.6	1639.1	1759.0	1845.0	1883.3	1853.2	1778.2
37.5°	1015.9	1090.8	1190.3	1303.9	1440.4	1581.3	1689.7	1751.6	1738.8	1664.0	1552.1
40°	972.1	1042.2	1136.9	1259.6	1392.7	1533.9	1629.2	1662.6	1627.6	1520.3	1401.4
42.5°	923.4	991.8	1087.0	1205.2	1346.2	1476.5	1559.6	1562.3	1503.6	1375.2	1255.9
45°	849.4	914.6	1004.4	1127.6	1257.9	1380.6	1435.4	1408.5	1300.1	1176.3	1056.4
47.5°	776.3	832.8	921.4	1038.3	1162.1	1265.4	1292.5	1244.2	1128.7	1008.5	897.4
50°	722.9	779.8	863.1	974.8	1094.2	1183.4	1196.6	1132.5	1019.1	898.1	811.0
52.5°	671.6	728.2	808.3	911.7	1021.0	1101.5	1101.9	1027.8	914.9	807.0	726.0
55°	596.4	647.3	719.6	812.1	909.7	972.6	957.3	880.6	782.6	689.0	618.3
57.5°	523.9	568.2	634.9	712.0	797.9	849.9	824.4	750.6	663.1	583.7	530.1
60°	477.0	519.2	576.2	649.0	721.3	761.8	737.7	670.8	590.3	526.2	479.7
62.5°	431.4	467.0	521.8	585.0	652.0	682.1	660.6	594.6	525.1	467.1	429.4
65°	366.9	395.9	439.7	494.0	542.7	568.5	550.4	489.0	435.9	394.3	364.2
67.5°	306.7	329.4	362.5	406.0	447.4	461.4	444.9	402.2	357.2	323.8	302.6
70°	265.1	286.5	314.3	347.8	383.9	398.7	382.2	348.3	311.6	280.9	260.2
72.5°	228.7	245.3	268.8	297.4	325.7	340.4	329.2	296.6	265.6	242.8	225.1
75°	174.1	188.4	204.8	225.1	247.0	256.8	247.0	224.5	203.2	186.2	173.6
77.5°	126.6	134.3	146.9	162.1	175.8	183.3	174.8	159.5	146.6	134.9	128.7
80°	96.4	101.9	110.6	122.7	132.0	139.1	133.6	121.0	110.6	103.0	100.2
82.5°	70.1	73.8	79.5	88.5	94.7	98.4	95.9	86.8	82.5	75.8	73.0
85°	34.5	36.7	40.6	43.3	48.7	49.3	49.8	46.0	42.1	40.6	38.3
87.5°	12.3	13.2	14.7	16.2	17.9	19.3	18.9	19.2	17.7	17.1	15.5
90°	2.4	4.8	5.5	6.3	6.3	11.1	11.1	12.7	14.3	13.5	14.3
92.5°	13.2	20.6	30.2	41.7	58.2	98.4	159.8	219.5	250.9	209.0	155.3
95°	28.4	36.4	46.7	65.7	98.9	167.6	297.4	486.4	644.5	662.7	586.0
97.5°	46.8	53.6	63.1	79.4	107.3	160.3	267.3	455.2	678.8	832.6	865.9
100°	60.1	65.7	75.1	90.2	115.5	162.2	251.5	412.8	635.8	838.3	953.8
102.5°	74.0	78.9	87.8	102.2	126.2	168.4	247.1	384.4	582.1	790.8	949.4
105°	94.9	98.9	108.4	122.6	145.5	183.5	249.1	359.8	518.8	704.6	885.7
107.5°	116.0	119.9	130.0	143.6	166.2	201.1	260.8	355.4	483.4	635.0	795.4
110°	130.5	134.4	143.9	158.2	179.5	214.3	269.7	356.6	471.3	600.2	741.0





TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	149.0	157.9	172.1	193.5	227.0	279.2	360.4	465.6	580.7	701.2
115°	165.2	170.8	178.7	193.8	215.1	246.8	294.2	367.7	462.6	562.3	661.2
117.5°	186.0	190.9	199.6	213.7	235.8	265.9	309.5	375.5	461.8	554.1	641.5
120°	199.3	204.9	213.5	227.0	249.1	279.2	320.3	381.2	461.8	549.6	632.6
122.5°	211.9	217.5	225.5	240.3	261.7	291.8	330.4	386.9	461.2	544.5	625.1
125°	230.1	234.9	243.6	258.6	280.7	309.2	345.6	395.5	460.3	536.2	612.1
127.5°	244.2	249.9	259.8	275.5	297.9	325.3	358.7	402.2	458.5	525.0	596.3
130°	253.1	259.4	271.2	286.3	309.2	336.1	366.9	407.3	457.9	518.0	583.7
132.5°	260.6	268.9	280.1	296.4	318.1	345.0	375.2	411.7	457.2	511.7	570.4
135°	272.8	280.7	294.2	310.8	331.4	357.4	386.0	418.4	456.3	502.2	552.0
137.5°	284.2	292.9	305.7	323.0	342.6	366.9	393.6	422.3	456.1	493.9	535.4
140°	291.8	300.6	313.9	330.6	349.6	373.3	398.5	425.5	455.5	489.6	525.9
142.5°	300.7	308.7	321.5	337.5	355.8	379.0	402.3	428.0	455.5	485.8	517.1
145°	313.1	321.1	332.2	347.2	364.6	385.2	406.5	429.4	453.9	479.3	504.5
147.5°	325.7	332.6	344.0	356.5	372.2	391.5	410.1	430.2	451.1	473.4	494.2
150°	334.5	340.9	350.4	362.2	377.2	394.7	412.0	430.2	449.2	469.0	488.0
152.5°	342.1	348.5	357.3	367.9	381.7	397.2	413.3	429.0	446.0	463.9	481.0
155°	354.3	359.0	366.9	375.7	387.5	400.9	414.4	427.1	441.3	456.3	470.6
157.5°	364.7	369.2	375.3	382.9	392.3	403.6	414.4	425.0	436.4	448.5	459.3
160°	371.7	374.9	380.4	386.7	395.5	404.9	414.4	423.1	432.6	442.9	452.3
162.5°	377.4	379.9	384.8	390.5	397.4	406.2	414.4	421.2	428.8	437.8	445.4
165°	385.2	386.7	390.7	394.7	399.3	406.5	412.8	417.6	423.1	429.4	435.8
167.5°	391.5	392.3	395.3	397.5	401.1	406.3	410.9	413.8	417.4	421.8	426.4
170°	394.7	395.5	397.8	399.3	401.7	405.7	409.6	411.2	413.6	416.8	420.7
172.5°	397.8	397.9	399.7	400.6	402.3	405.0	408.4	408.7	409.8	412.3	415.7
175°	400.9	400.9	401.7	402.5	402.5	404.1	406.5	405.7	405.7	407.3	408.8
177.5°	402.5	401.9	402.5	402.5	402.5	403.1	404.4	403.1	403.1	403.8	404.4
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5	402.5



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1393.4	1394.3	1398.2	1401.3	1402.2	1406.6	1407.0
5°	1515.8	1525.2	1543.3	1544.9	1547.6	1561.9	1550.9
7.5°	1659.4	1683.0	1698.8	1712.7	1717.8	1723.9	1722.7
10°	1751.4	1786.4	1804.0	1831.8	1833.0	1840.1	1835.7
12.5°	1843.8	1884.5	1916.5	1921.7	1945.1	1948.7	1954.9
15°	1974.8	2018.1	2062.4	2078.3	2110.6	2118.3	2130.3
17.5°	2097.9	2142.1	2173.3	2214.3	2227.6	2245.4	2233.2
20°	2165.4	2213.6	2253.0	2285.3	2299.0	2308.8	2307.8
22.5°	2206.1	2254.7	2286.7	2311.1	2323.9	2328.1	2327.9
25°	2231.7	2259.5	2269.4	2278.7	2264.5	2259.5	2261.8
27.5°	2160.7	2153.5	2127.7	2094.0	2058.9	2031.1	2015.9
30°	2063.0	2020.2	1981.3	1913.4	1878.4	1857.6	1839.0
32.5°	1924.5	1856.8	1782.0	1719.8	1680.0	1649.1	1644.5
35°	1687.3	1585.4	1494.0	1417.8	1378.4	1345.0	1337.4
37.5°	1434.5	1328.6	1246.3	1179.3	1136.9	1113.3	1091.3
40°	1266.7	1175.8	1094.7	1037.8	1005.4	988.5	974.8
42.5°	1137.4	1054.4	973.8	930.4	901.2	890.8	882.8
45°	958.9	881.7	825.9	793.0	776.0	758.5	750.3
47.5°	815.9	753.1	716.3	688.4	670.2	659.8	654.5
50°	734.9	683.4	650.6	629.2	612.8	604.6	600.2
52.5°	663.1	620.8	593.2	576.2	565.1	559.0	557.3
55°	571.2	538.8	521.3	506.6	498.4	492.9	490.7
57.5°	496.5	471.7	457.4	445.2	442.0	437.4	435.9
60°	447.4	428.3	416.2	408.0	405.3	399.8	400.8
62.5°	404.0	388.4	378.1	373.4	369.8	365.2	366.7
65°	341.7	330.3	324.7	320.4	316.0	313.2	315.4
67.5°	286.8	278.8	271.4	268.9	266.7	266.3	264.0
70°	250.8	244.2	237.7	236.1	236.1	233.9	233.3
72.5°	216.2	211.4	207.0	205.8	204.1	204.9	202.6
75°	167.0	163.2	161.5	159.9	159.4	159.4	157.7
77.5°	123.4	120.6	118.0	118.0	116.0	115.3	115.0
80°	93.6	92.5	90.4	90.4	89.3	89.8	88.7
82.5°	70.4	68.9	68.4	67.6	66.1	66.1	65.0
85°	37.8	36.1	35.6	34.0	32.9	34.0	32.9
87.5°	16.2	15.8	15.4	14.7	14.4	14.3	13.0
90°	15.1	15.8	15.8	16.6	17.4	16.6	16.6
92.5°	116.9	93.0	77.2	67.9	63.6	60.9	60.9
95°	463.4	357.4	280.7	242.0	217.5	203.3	193.0
97.5°	820.2	742.9	660.4	603.6	556.0	532.3	515.8
100°	969.6	930.8	872.3	803.5	755.3	731.5	725.2
102.5°	1027.8	1039.0	1014.6	972.4	937.5	912.5	907.4
105°	1022.5	1100.8	1133.3	1134.9	1128.5	1117.5	1112.7
107.5°	941.1	1051.4	1121.9	1160.9	1179.0	1186.9	1189.0
110°	877.8	992.5	1079.5	1135.7	1168.9	1183.1	1190.3



TEST NUMBER: P332654-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	822.1	930.5	1017.5	1081.2	1121.4	1141.4	1152.9
115°	758.4	851.0	926.9	989.4	1036.8	1062.1	1068.4
117.5°	722.1	794.8	859.2	912.5	952.4	977.9	982.9
120°	706.2	769.5	825.6	870.7	905.5	926.1	934.8
122.5°	696.1	753.7	802.9	841.0	870.7	888.1	896.8
125°	680.1	734.7	778.2	809.8	832.7	847.8	852.5
127.5°	661.3	715.7	757.0	788.8	809.2	821.8	826.6
130°	646.1	699.9	741.8	774.2	794.0	806.7	811.4
132.5°	629.1	681.5	723.5	755.3	777.5	789.6	794.3
135°	603.4	651.6	691.2	722.9	745.0	757.6	762.4
137.5°	578.9	619.6	655.3	684.8	706.7	717.2	722.9
140°	563.1	598.7	631.8	659.6	677.0	688.0	694.3
142.5°	549.8	580.4	609.1	633.6	649.7	659.6	664.0
145°	531.5	555.2	577.3	597.1	610.5	618.5	622.4
147.5°	515.6	534.6	552.0	566.6	578.1	584.2	585.5
150°	506.1	522.0	536.2	548.8	559.1	563.9	564.7
152.5°	496.6	511.2	522.9	533.7	542.0	544.9	545.7
155°	483.2	495.0	504.5	512.5	518.8	521.2	521.2
157.5°	469.9	479.9	487.5	493.5	498.2	499.6	499.6
160°	461.1	469.8	476.1	480.9	485.6	486.4	486.4
162.5°	452.8	459.6	465.3	468.8	473.6	474.4	473.7
165°	440.5	446.0	450.0	453.1	456.3	455.5	454.7
167.5°	430.1	434.5	436.9	438.5	440.5	440.4	439.7
170°	423.1	426.3	428.6	430.2	431.0	430.2	430.2
172.5°	417.4	419.3	421.0	422.0	422.8	422.0	420.7
175°	409.6	411.2	411.2	411.2	412.8	411.2	409.6
177.5°	405.0	405.0	405.7	405.0	405.7	404.4	403.1
180°	402.5	402.5	402.5	402.5	402.5	402.5	402.5

(END OF REPORT)