

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332627-935

Luminaire Tested: **S124DIP-S1020D365U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332627-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1020D365U935-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5091.7 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	100	96	92	99	96	92	89	87	85	82	80	78	76	73	71	70	66
2	95	88	82	76	91	84	78	74	77	73	69	71	67	64	65	62	59	56
3	87	78	70	64	83	74	68	62	68	63	58	63	58	54	58	54	51	48
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	52	48	44	41
5	74	62	53	47	70	59	52	46	55	48	44	51	45	41	47	42	39	36
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	43	38	34	32
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	31	28
8	59	46	38	33	56	45	37	32	41	35	30	39	33	29	36	31	28	25
9	55	42	35	29	52	41	34	29	38	32	27	36	30	26	33	28	25	23
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11599	11599	11599	11599
5°	13661	11629	10264	11629
10°	16356	11579	9241	11579
15°	19351	11462	8487	11462
20°	21549	11342	7814	11342
25°	21896	11166	7349	11166
30°	18632	10997	7202	10997
35°	14325	10723	7203	10723
40°	11166	10400	7339	10400
45°	9310	9914	7462	9914
50°	8194	9323	7714	9323
55°	7506	8612	8025	8612
60°	7035	7976	8399	7976
65°	6550	7265	8709	7265
70°	5986	6559	8908	6559
75°	5346	5774	8799	5774
80°	4482	4733	8522	4733
85°	3307	3418	8160	3418



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.0	2.7
10°-20°	431.5	8.5
20°-30°	684.2	13.4
30°-40°	761.4	15.0
40°-50°	693.1	13.6
50°-60°	566.4	11.1
60°-70°	404.3	7.9
70°-80°	222.6	4.4
80°-90°	61.7	1.2
90°-100°	111.9	2.2
100°-110°	232.8	4.6
110°-120°	208.5	4.1
120°-130°	175.4	3.4
130°-140°	146.3	2.9
140°-150°	111.7	2.2
150°-160°	78.5	1.5
160°-170°	46.2	0.9
170°-180°	15.0	0.3
0°-30°	1255.6	24.7
0°-40°	2017.1	39.6
0°-60°	3276.5	64.4
0°-90°	3965.2	77.9
90°-120°	553.3	10.9
90°-150°	986.7	19.4
90°-180°	1126.0	22.1
0°-180°	5091.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1437	1437	1437	1437	1437	
5°	1686	1435	1267	1435	1686	171
15°	2315	1371	1016	1371	2315	654
25°	2458	1254	825	1254	2458	1084
35°	1454	1088	731	1088	1454	923
45°	816	868	654	868	816	642
55°	533	612	570	612	533	482
65°	343	380	456	380	343	339
75°	171	185	282	185	171	182
85°	36	37	88	37	36	44
90°	6	0	6	0	6	7
95°	74	10	74	10	74	115
105°	428	36	428	36	428	423
115°	411	63	411	63	411	408
125°	328	87	328	87	328	298
135°	293	104	293	104	293	226
145°	239	120	239	120	239	152
155°	200	136	200	136	200	94
165°	175	148	175	148	175	50
175°	158	154	158	154	158	15
180°	155	155	155	155	155	



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1529.2	1528.8	1524.0	1523.0	1519.7	1515.4	1514.5	1506.8	1491.6	1484.5	1482.6
5°	1685.7	1697.5	1682.0	1679.1	1677.3	1657.7	1647.5	1635.6	1608.3	1592.2	1579.7
7.5°	1872.3	1873.7	1867.0	1861.5	1846.3	1829.2	1803.5	1776.2	1743.5	1709.6	1683.9
10°	1995.2	1999.9	1992.2	1991.0	1960.7	1941.6	1903.5	1871.4	1834.4	1793.4	1755.9
12.5°	2124.7	2118.0	2114.1	2088.6	2083.0	2048.2	2004.0	1970.9	1914.0	1866.7	1816.8
15°	2315.4	2302.3	2294.0	2258.8	2241.6	2193.4	2146.3	2110.1	2035.7	1964.8	1911.2
17.5°	2427.2	2440.4	2421.1	2406.7	2362.1	2328.2	2280.2	2204.0	2145.8	2057.8	1990.2
20°	2508.3	2509.4	2498.7	2483.8	2448.7	2405.9	2353.5	2270.1	2200.5	2113.0	2020.2
22.5°	2530.1	2530.4	2525.8	2511.9	2485.4	2450.6	2397.8	2328.2	2243.9	2148.7	2055.9
25°	2458.2	2455.8	2461.3	2476.7	2466.6	2455.8	2425.5	2373.7	2295.2	2194.5	2094.6
27.5°	2191.1	2207.5	2237.7	2275.9	2312.6	2340.5	2348.4	2337.8	2289.1	2206.3	2101.6
30°	1998.7	2019.0	2041.6	2079.7	2153.4	2195.7	2242.2	2277.3	2257.6	2191.6	2094.0
32.5°	1787.3	1792.3	1825.9	1869.2	1936.8	2018.1	2091.7	2163.0	2186.7	2152.1	2070.6
35°	1453.5	1461.8	1498.1	1541.0	1623.8	1723.1	1833.8	1932.7	2014.2	2046.9	2005.3
37.5°	1186.1	1210.0	1235.7	1281.8	1354.6	1444.1	1559.1	1687.0	1808.5	1889.9	1903.8
40°	1059.5	1074.4	1092.8	1127.9	1189.8	1277.9	1376.7	1523.2	1652.3	1769.0	1807.1
42.5°	959.5	968.2	979.5	1011.2	1058.4	1146.0	1236.2	1365.0	1494.7	1634.2	1698.1
45°	815.5	824.4	843.4	861.9	897.6	958.3	1042.2	1148.1	1278.5	1413.1	1530.9
47.5°	711.4	717.1	728.4	748.2	778.5	818.6	886.8	975.3	1096.1	1226.8	1352.3
50°	652.4	657.1	666.1	683.9	707.1	742.8	798.7	881.5	976.1	1107.7	1230.9
52.5°	605.7	607.6	614.2	626.3	644.7	674.8	720.7	789.1	877.1	994.4	1117.1
55°	533.3	535.7	541.7	550.6	566.6	585.7	620.8	672.0	748.8	850.6	957.1
57.5°	473.8	475.4	480.4	483.9	497.1	512.6	539.6	576.2	634.4	720.7	815.8
60°	435.7	434.5	440.5	443.4	452.4	465.5	486.3	521.4	572.0	641.6	729.1
62.5°	398.6	396.9	401.9	405.8	411.0	422.1	439.1	466.7	507.7	570.7	646.3
65°	342.9	340.4	343.5	348.2	352.9	359.0	371.4	395.8	428.5	473.8	531.5
67.5°	286.9	289.4	289.9	292.2	295.0	303.1	311.7	328.9	352.0	388.2	437.1
70°	253.6	254.2	256.6	256.6	258.3	265.4	272.6	282.8	305.3	338.7	378.6
72.5°	220.2	222.7	221.8	223.7	225.0	229.7	235.0	244.6	263.9	288.7	322.4
75°	171.4	173.2	173.2	173.8	175.6	177.4	181.5	188.6	202.3	220.8	244.0
77.5°	125.0	125.3	126.1	128.2	128.2	131.0	134.1	139.9	146.6	159.3	173.4
80°	96.4	97.6	97.0	98.2	98.2	100.6	101.8	108.9	111.9	120.2	131.6
82.5°	70.7	71.9	71.8	73.4	74.4	74.9	76.5	79.4	82.4	89.7	94.4
85°	35.7	36.9	35.7	36.9	38.7	39.3	41.1	41.7	44.1	45.8	50.0
87.5°	11.8	13.2	13.3	13.7	14.6	15.1	15.4	14.9	16.8	17.3	19.0
90°	6.4	6.4	6.7	6.4	6.1	6.1	5.8	5.5	5.2	5.5	4.9
92.5°	23.4	23.4	24.5	26.1	29.7	35.8	44.9	59.8	80.4	96.5	84.5
95°	74.2	78.2	83.7	93.1	108.1	137.5	178.3	225.5	255.0	248.0	187.2
97.5°	198.5	204.8	214.0	232.2	254.1	285.9	315.6	333.1	320.4	261.2	175.1
100°	279.1	281.5	290.6	309.2	335.6	358.2	373.1	367.0	322.5	244.7	158.9
102.5°	349.1	351.1	360.8	374.2	390.4	399.8	395.5	365.3	304.3	223.9	147.9
105°	428.2	430.0	434.2	436.7	436.1	423.6	393.5	340.8	271.1	199.6	138.4
107.5°	457.4	456.7	453.7	446.7	431.7	404.5	362.1	306.1	244.4	186.0	136.7
110°	458.0	455.2	449.8	437.0	415.3	381.9	337.8	285.2	231.0	181.3	137.2



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	443.6	439.2	431.5	416.0	391.5	358.0	316.3	269.8	223.4	179.2	138.7
115°	411.1	408.7	398.9	380.6	356.6	327.4	291.8	254.4	216.4	178.1	141.5
117.5°	378.2	376.3	366.4	351.1	330.6	305.8	277.8	246.8	213.2	177.7	144.5
120°	359.7	356.4	348.4	335.0	317.7	296.1	271.7	243.4	211.5	177.7	146.7
122.5°	345.1	341.7	335.0	323.6	308.9	290.0	267.9	240.5	209.6	177.5	148.9
125°	328.0	326.2	320.5	311.6	299.5	282.7	261.7	235.6	206.3	177.1	152.1
127.5°	318.1	316.2	311.3	303.5	291.3	275.4	254.4	229.5	202.0	176.4	154.8
130°	312.2	310.4	305.5	297.9	285.4	269.3	248.7	224.5	199.3	176.2	156.7
132.5°	305.7	303.8	299.2	290.6	278.4	262.3	242.0	219.5	196.9	176.0	158.4
135°	293.3	291.5	286.6	278.1	266.0	250.7	232.2	212.4	193.2	175.6	161.0
137.5°	278.1	276.0	271.9	263.6	252.1	238.4	222.7	206.0	190.1	175.6	162.5
140°	267.2	264.8	260.5	253.8	243.1	230.3	216.6	202.3	188.4	175.3	163.7
142.5°	255.5	253.8	250.0	243.8	234.4	223.3	211.5	199.0	186.9	175.3	164.7
145°	239.4	238.0	234.9	229.7	222.1	213.6	204.5	194.2	184.4	174.7	165.2
147.5°	225.3	224.7	222.5	218.0	212.4	205.7	198.4	190.2	182.2	173.6	165.6
150°	217.2	217.0	215.2	211.2	206.3	200.9	194.8	187.8	180.5	172.8	165.6
152.5°	210.0	209.7	208.5	205.3	201.2	196.7	191.1	185.1	178.5	171.6	165.1
155°	200.5	200.5	199.6	197.2	194.2	190.5	185.9	181.1	175.6	169.8	164.4
157.5°	192.3	192.3	191.7	189.9	187.6	184.7	180.8	176.8	172.6	167.9	163.5
160°	187.2	187.2	186.8	185.0	183.2	180.7	177.4	174.1	170.4	166.4	162.8
162.5°	182.3	182.5	182.2	180.4	179.1	176.8	174.3	171.4	168.5	165.0	162.0
165°	175.0	175.3	175.6	174.4	173.1	171.6	169.5	167.6	165.2	162.8	160.7
167.5°	169.2	169.4	169.5	168.7	168.1	167.2	165.5	164.1	162.3	160.6	159.2
170°	165.6	165.6	165.8	165.6	165.0	164.0	162.8	161.9	160.4	159.1	158.3
172.5°	161.9	162.4	162.6	162.4	162.0	161.4	160.6	160.0	158.7	157.6	157.3
175°	157.6	158.3	158.9	158.3	158.3	158.3	157.6	157.3	156.7	156.1	156.1
177.5°	155.2	155.6	156.1	155.8	156.1	155.8	155.8	155.6	155.4	155.2	155.2
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1483.1	1476.4	1471.6	1467.8	1457.3	1451.1	1446.4	1439.7	1432.1	1424.0	1414.0
5°	1567.2	1547.0	1532.1	1509.5	1488.1	1470.2	1451.7	1435.0	1414.8	1392.8	1376.7
7.5°	1655.6	1625.6	1587.0	1553.5	1515.9	1483.2	1453.9	1423.8	1392.7	1362.4	1334.7
10°	1711.8	1673.2	1630.3	1579.7	1532.1	1489.8	1450.5	1412.5	1375.5	1338.6	1307.1
12.5°	1772.3	1724.1	1660.8	1601.6	1548.3	1491.8	1444.3	1397.7	1353.1	1314.3	1277.6
15°	1853.5	1783.8	1710.6	1631.5	1561.3	1495.2	1430.3	1371.4	1321.4	1270.1	1234.5
17.5°	1903.4	1817.2	1733.5	1650.8	1565.7	1482.5	1412.5	1344.5	1281.9	1231.1	1186.0
20°	1936.2	1850.5	1746.4	1663.6	1562.5	1476.7	1395.8	1320.2	1254.7	1200.6	1154.1
22.5°	1964.8	1865.8	1761.6	1652.7	1552.0	1461.0	1372.4	1296.4	1229.5	1172.4	1127.9
25°	1980.3	1866.6	1753.5	1645.2	1530.9	1423.1	1342.8	1253.5	1182.1	1122.0	1074.4
27.5°	1981.9	1860.4	1732.4	1612.1	1494.1	1393.8	1292.4	1212.5	1138.4	1074.9	1029.2
30°	1976.7	1849.9	1712.4	1582.1	1463.6	1354.7	1266.6	1179.7	1104.1	1041.0	993.4
32.5°	1960.1	1828.0	1686.7	1548.8	1426.0	1319.5	1228.6	1145.9	1072.2	1010.0	960.1
35°	1911.9	1781.5	1630.9	1487.5	1361.8	1254.1	1172.0	1088.0	1014.3	955.3	907.1
37.5°	1836.5	1718.6	1565.6	1417.1	1293.7	1185.5	1104.1	1028.3	961.7	901.9	852.5
40°	1770.7	1667.2	1513.6	1369.0	1235.7	1132.7	1056.5	986.9	920.8	864.3	817.3
42.5°	1695.1	1604.8	1463.2	1309.9	1181.4	1078.0	1003.7	941.2	878.9	826.6	779.6
45°	1560.0	1500.6	1367.2	1225.5	1091.7	994.0	923.2	868.4	816.1	764.8	725.6
47.5°	1404.8	1375.3	1263.1	1128.5	1001.4	905.2	843.8	793.2	747.3	703.9	669.3
50°	1300.5	1286.2	1189.2	1059.5	938.1	847.6	785.7	742.3	702.9	664.9	632.1
52.5°	1197.7	1197.2	1109.7	990.9	878.6	791.4	730.0	689.4	655.3	624.4	595.0
55°	1040.4	1057.1	988.7	882.7	782.1	703.5	648.2	611.9	588.1	562.5	540.4
57.5°	896.0	923.7	867.2	773.9	690.0	617.6	569.4	542.1	516.8	501.3	485.3
60°	801.8	827.9	783.9	705.3	626.2	564.3	518.4	494.0	472.0	461.3	450.0
62.5°	718.0	741.3	708.7	635.8	567.1	507.6	468.9	445.5	430.6	418.9	411.4
65°	598.2	617.9	589.9	536.9	477.9	430.3	398.8	380.3	366.1	361.3	352.9
67.5°	483.5	501.4	486.3	441.3	394.0	358.0	333.3	315.6	307.1	303.0	297.0
70°	415.4	433.3	417.2	378.0	341.6	311.3	288.1	277.9	269.1	267.3	258.9
72.5°	357.8	370.0	354.0	323.2	292.1	266.6	248.6	238.0	233.3	230.1	225.6
75°	268.5	279.1	268.5	244.6	222.6	204.7	189.2	185.1	179.8	178.0	175.0
77.5°	190.0	199.2	191.1	176.2	159.7	145.9	137.6	132.2	131.0	127.9	129.4
80°	145.3	151.2	143.4	133.4	120.2	110.7	104.8	101.8	98.2	97.0	99.4
82.5°	104.3	106.9	103.0	96.2	86.4	80.2	76.2	72.8	72.0	72.2	72.2
85°	54.2	53.6	53.0	47.0	44.1	39.9	37.5	36.9	36.3	37.5	38.7
87.5°	18.9	19.5	18.6	16.7	15.2	13.7	13.0	12.4	13.0	13.7	14.2
90°	4.2	4.2	2.4	2.4	2.2	1.8	0.9	0.3	0.9	1.8	2.2
92.5°	61.5	37.9	22.4	16.1	11.6	7.9	5.1	3.4	5.1	7.9	11.6
95°	114.4	64.5	38.1	25.2	18.0	14.0	10.9	10.1	10.9	14.0	18.0
97.5°	102.9	61.6	41.2	30.6	24.3	20.7	18.0	18.0	18.0	20.7	24.3
100°	96.8	62.4	44.4	34.7	28.9	25.2	23.2	23.2	23.2	25.2	28.9
102.5°	95.1	64.8	48.6	39.3	33.8	30.4	28.5	28.0	28.5	30.4	33.8
105°	95.8	70.6	56.0	47.2	41.7	38.1	36.5	35.6	36.5	38.1	41.7
107.5°	100.4	77.3	64.0	55.3	50.0	46.1	44.6	44.0	44.6	46.1	50.0
110°	103.8	82.5	69.1	60.9	55.4	51.7	50.2	49.6	50.2	51.7	55.4



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	107.5	87.3	74.4	66.2	60.7	57.3	55.5	54.9	55.5	57.3	60.7
115°	113.2	95.0	82.7	74.6	68.8	65.7	63.6	62.7	63.6	65.7	68.8
117.5°	119.1	102.3	90.7	82.2	76.8	73.4	71.5	70.7	71.5	73.4	76.8
120°	123.2	107.5	95.8	87.3	82.1	78.8	76.7	76.1	76.7	78.8	82.1
122.5°	127.2	112.3	100.7	92.5	86.8	83.7	81.5	80.9	81.5	83.7	86.8
125°	132.9	119.0	108.1	99.5	93.8	90.4	88.5	87.3	88.5	90.4	93.8
127.5°	138.0	125.2	114.6	106.0	100.0	96.2	93.9	93.0	93.9	96.2	100.0
130°	141.2	129.3	119.0	110.1	104.4	99.8	97.4	96.2	97.4	99.8	104.4
132.5°	144.4	132.8	122.3	114.1	107.8	103.5	100.3	99.4	100.3	103.5	107.8
135°	148.5	137.5	127.5	119.6	113.2	108.1	105.0	103.8	105.0	108.1	113.2
137.5°	151.4	141.2	131.8	124.2	117.6	112.7	109.3	108.2	109.3	112.7	117.6
140°	153.3	143.6	134.5	127.2	120.8	115.6	112.3	111.4	112.3	115.6	120.8
142.5°	154.8	145.9	136.9	129.8	123.7	118.8	115.7	114.8	115.7	118.8	123.7
145°	156.4	148.2	140.3	133.6	127.8	123.6	120.5	119.6	120.5	123.6	127.8
147.5°	157.8	150.6	143.2	137.2	132.3	128.0	125.3	125.0	125.3	128.0	132.3
150°	158.5	151.9	145.2	139.4	134.8	131.1	128.7	128.4	128.7	131.1	134.8
152.5°	159.0	152.8	146.9	141.5	137.5	134.1	131.6	131.6	131.6	134.1	137.5
155°	159.5	154.3	149.1	144.6	141.2	138.2	136.3	136.0	136.3	138.2	141.2
157.5°	159.5	155.3	150.9	147.3	144.4	142.1	140.3	140.3	140.3	142.1	144.4
160°	159.5	155.8	152.1	148.8	146.4	144.2	143.0	143.0	143.0	144.2	146.4
162.5°	159.5	156.3	152.9	150.2	148.1	146.2	145.3	145.4	145.3	146.2	148.1
165°	158.9	156.4	153.7	151.9	150.3	148.8	148.2	148.2	148.2	148.8	150.3
167.5°	158.1	156.4	154.4	152.9	152.1	150.9	150.6	150.9	150.6	150.9	152.1
170°	157.6	156.1	154.5	153.7	153.1	152.1	151.9	152.1	151.9	152.1	153.1
172.5°	157.1	155.8	154.8	154.1	153.8	153.1	153.1	153.3	153.1	153.1	153.8
175°	156.4	155.5	154.9	154.9	154.5	154.3	154.3	154.5	154.3	154.3	154.5
177.5°	155.6	155.2	154.9	154.9	154.9	154.6	154.9	155.2	154.9	154.6	154.9
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1409.2	1405.0	1398.8	1390.2	1383.0	1375.4	1373.6	1370.6	1376.4	1371.6	1370.2
5°	1363.0	1350.6	1334.5	1316.0	1305.3	1289.9	1286.9	1280.9	1275.0	1274.4	1268.4
7.5°	1314.1	1295.8	1274.7	1255.9	1238.5	1221.6	1210.6	1208.2	1199.4	1194.2	1188.3
10°	1282.7	1260.1	1235.7	1217.8	1197.6	1179.7	1167.3	1160.1	1154.1	1147.5	1141.6
12.5°	1245.5	1221.5	1201.4	1182.1	1158.0	1144.4	1123.9	1111.5	1110.3	1110.4	1094.9
15°	1202.3	1178.5	1147.5	1120.2	1107.1	1080.9	1069.6	1055.3	1046.4	1037.4	1030.4
17.5°	1153.0	1123.3	1099.2	1067.7	1042.7	1021.8	1007.0	998.4	985.0	972.3	963.2
20°	1122.0	1090.5	1064.8	1031.5	1004.1	978.5	966.0	954.2	944.0	933.3	923.2
22.5°	1090.5	1057.6	1026.2	993.9	968.5	941.4	929.4	913.2	903.5	897.6	887.4
25°	1041.0	1005.3	969.6	938.7	912.5	888.6	872.6	860.1	849.4	844.6	838.1
27.5°	987.2	951.7	917.2	882.1	852.4	835.1	822.3	812.8	806.7	800.3	797.4
30°	953.0	916.0	879.2	846.4	819.0	801.8	789.9	783.3	778.5	775.6	772.6
32.5°	918.2	881.8	842.9	813.0	788.5	773.2	764.1	757.6	755.2	754.1	753.0
35°	862.5	825.5	789.9	763.1	739.9	733.9	726.2	722.6	721.4	725.6	727.4
37.5°	808.6	774.3	741.4	715.4	700.3	691.6	688.9	689.1	693.3	697.0	701.3
40°	773.8	740.5	709.5	686.9	672.6	667.3	666.1	669.0	673.8	678.0	682.7
42.5°	739.9	707.1	679.0	657.8	647.8	642.9	643.7	646.6	653.3	658.4	665.6
45°	687.5	660.1	632.7	615.4	607.1	608.3	608.3	613.6	620.2	627.9	635.7
47.5°	638.1	610.4	588.0	573.4	569.1	568.1	571.4	578.4	587.8	597.4	608.2
50°	604.8	578.5	558.9	545.8	541.1	542.9	547.6	554.1	565.4	577.4	588.7
52.5°	570.9	547.1	528.9	516.8	513.4	516.7	521.4	531.8	541.7	554.5	568.2
55°	518.4	498.2	483.9	475.0	473.8	475.6	481.0	492.2	506.5	522.6	535.7
57.5°	466.1	449.3	436.2	430.0	430.6	432.2	441.1	454.5	469.8	486.9	503.8
60°	430.9	415.4	404.8	400.0	400.5	404.2	414.8	427.4	446.4	463.0	481.0
62.5°	397.6	384.0	373.8	369.5	368.7	376.5	386.8	399.8	418.8	437.4	456.7
65°	344.1	333.3	325.0	322.6	324.4	330.4	343.5	360.7	376.8	396.4	416.6
67.5°	291.6	282.8	277.2	278.2	280.3	289.1	300.1	315.0	333.2	353.5	373.6
70°	258.3	249.9	245.2	245.8	249.4	260.1	269.7	284.5	304.2	325.0	341.6
72.5°	224.0	218.5	214.3	216.8	220.3	227.7	239.6	254.5	271.8	291.2	308.8
75°	172.0	172.0	169.6	171.4	176.8	183.9	192.9	208.4	225.6	241.1	255.4
77.5°	127.6	126.3	127.9	130.0	133.1	141.5	151.8	162.8	175.8	191.3	203.1
80°	97.6	98.2	101.2	104.8	106.0	112.5	123.2	133.4	143.4	156.5	167.8
82.5°	73.4	74.0	75.5	80.0	81.2	88.3	95.1	105.2	114.4	123.2	132.6
85°	39.9	39.9	42.9	44.6	47.6	52.3	56.6	62.5	70.9	76.8	85.7
87.5°	15.8	15.8	18.0	18.9	20.5	23.0	23.8	29.2	31.2	33.6	37.9
90°	2.4	2.4	4.2	4.2	4.9	5.5	5.2	5.5	5.8	6.1	6.1
92.5°	16.1	22.4	37.9	61.5	84.5	96.5	80.4	59.8	44.9	35.8	29.7
95°	25.2	38.1	64.5	114.4	187.2	248.0	255.0	225.5	178.3	137.5	108.1
97.5°	30.6	41.2	61.6	102.9	175.1	261.2	320.4	333.1	315.6	285.9	254.1
100°	34.7	44.4	62.4	96.8	158.9	244.7	322.5	367.0	373.1	358.2	335.6
102.5°	39.3	48.6	64.8	95.1	147.9	223.9	304.3	365.3	395.5	399.8	390.4
105°	47.2	56.0	70.6	95.8	138.4	199.6	271.1	340.8	393.5	423.6	436.1
107.5°	55.3	64.0	77.3	100.4	136.7	186.0	244.4	306.1	362.1	404.5	431.7
110°	60.9	69.1	82.5	103.8	137.2	181.3	231.0	285.2	337.8	381.9	415.3



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	66.2	74.4	87.3	107.5	138.7	179.2	223.4	269.8	316.3	358.0	391.5
115°	74.6	82.7	95.0	113.2	141.5	178.1	216.4	254.4	291.8	327.4	356.6
117.5°	82.2	90.7	102.3	119.1	144.5	177.7	213.2	246.8	277.8	305.8	330.6
120°	87.3	95.8	107.5	123.2	146.7	177.7	211.5	243.4	271.7	296.1	317.7
122.5°	92.5	100.7	112.3	127.2	148.9	177.5	209.6	240.5	267.9	290.0	308.9
125°	99.5	108.1	119.0	132.9	152.1	177.1	206.3	235.6	261.7	282.7	299.5
127.5°	106.0	114.6	125.2	138.0	154.8	176.4	202.0	229.5	254.4	275.4	291.3
130°	110.1	119.0	129.3	141.2	156.7	176.2	199.3	224.5	248.7	269.3	285.4
132.5°	114.1	122.3	132.8	144.4	158.4	176.0	196.9	219.5	242.0	262.3	278.4
135°	119.6	127.5	137.5	148.5	161.0	175.6	193.2	212.4	232.2	250.7	266.0
137.5°	124.2	131.8	141.2	151.4	162.5	175.6	190.1	206.0	222.7	238.4	252.1
140°	127.2	134.5	143.6	153.3	163.7	175.3	188.4	202.3	216.6	230.3	243.1
142.5°	129.8	136.9	145.9	154.8	164.7	175.3	186.9	199.0	211.5	223.3	234.4
145°	133.6	140.3	148.2	156.4	165.2	174.7	184.4	194.2	204.5	213.6	222.1
147.5°	137.2	143.2	150.6	157.8	165.6	173.6	182.2	190.2	198.4	205.7	212.4
150°	139.4	145.2	151.9	158.5	165.6	172.8	180.5	187.8	194.8	200.9	206.3
152.5°	141.5	146.9	152.8	159.0	165.1	171.6	178.5	185.1	191.1	196.7	201.2
155°	144.6	149.1	154.3	159.5	164.4	169.8	175.6	181.1	185.9	190.5	194.2
157.5°	147.3	150.9	155.3	159.5	163.5	167.9	172.6	176.8	180.8	184.7	187.6
160°	148.8	152.1	155.8	159.5	162.8	166.4	170.4	174.1	177.4	180.7	183.2
162.5°	150.2	152.9	156.3	159.5	162.0	165.0	168.5	171.4	174.3	176.8	179.1
165°	151.9	153.7	156.4	158.9	160.7	162.8	165.2	167.6	169.5	171.6	173.1
167.5°	152.9	154.4	156.4	158.1	159.2	160.6	162.3	164.1	165.5	167.2	168.1
170°	153.7	154.5	156.1	157.6	158.3	159.1	160.4	161.9	162.8	164.0	165.0
172.5°	154.1	154.8	155.8	157.1	157.3	157.6	158.7	160.0	160.6	161.4	162.0
175°	154.9	154.9	155.5	156.4	156.1	156.1	156.7	157.3	157.6	158.3	158.3
177.5°	154.9	154.9	155.2	155.6	155.2	155.2	155.4	155.6	155.8	155.8	156.1
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1369.2	1368.3	1364.9	1364.5	1364.9	1368.3	1369.2	1370.2	1371.6	1376.4	1370.6
5°	1264.8	1261.9	1260.1	1266.6	1260.1	1261.9	1264.8	1268.4	1274.4	1275.0	1280.9
7.5°	1186.1	1183.8	1178.5	1176.9	1178.5	1183.8	1186.1	1188.3	1194.2	1199.4	1208.2
10°	1135.7	1133.2	1128.5	1127.3	1128.5	1133.2	1135.7	1141.6	1147.5	1154.1	1160.1
12.5°	1087.1	1082.4	1081.4	1082.5	1081.4	1082.4	1087.1	1094.9	1110.4	1110.3	1111.5
15°	1022.6	1020.2	1013.7	1015.5	1013.7	1020.2	1022.6	1030.4	1037.4	1046.4	1055.3
17.5°	959.0	956.1	948.2	955.2	948.2	956.1	959.0	963.2	972.3	985.0	998.4
20°	919.0	914.2	910.1	909.5	910.1	914.2	919.0	923.2	933.3	944.0	954.2
22.5°	880.9	876.7	876.2	872.4	876.2	876.7	880.9	887.4	897.6	903.5	913.2
25°	833.3	829.1	827.9	825.0	827.9	829.1	833.3	838.1	844.6	849.4	860.1
27.5°	796.8	794.7	792.6	793.5	792.6	794.7	796.8	797.4	800.3	806.7	812.8
30°	774.4	773.8	772.6	772.6	772.6	773.8	774.4	772.6	775.6	778.5	783.3
32.5°	755.8	755.7	756.4	756.4	756.4	755.7	755.8	753.0	754.1	755.2	757.6
35°	729.7	731.5	732.7	730.9	732.7	731.5	729.7	727.4	725.6	721.4	722.6
37.5°	706.2	707.9	709.6	711.6	709.6	707.9	706.2	701.3	697.0	693.3	689.1
40°	688.0	692.2	693.4	696.4	693.4	692.2	688.0	682.7	678.0	673.8	669.0
42.5°	670.9	675.5	678.6	679.2	678.6	675.5	670.9	665.6	658.4	653.3	646.6
45°	644.6	649.4	653.6	653.6	653.6	649.4	644.6	635.7	627.9	620.2	613.6
47.5°	617.3	624.2	628.4	629.5	628.4	624.2	617.3	608.2	597.4	587.8	578.4
50°	598.8	607.1	611.3	614.2	611.3	607.1	598.8	588.7	577.4	565.4	554.1
52.5°	580.7	589.0	594.6	596.2	594.6	589.0	580.7	568.2	554.5	541.7	531.8
55°	549.4	561.3	567.8	570.2	567.8	561.3	549.4	535.7	522.6	506.5	492.2
57.5°	519.9	530.8	538.5	540.2	538.5	530.8	519.9	503.8	486.9	469.8	454.5
60°	497.0	508.9	518.4	520.2	518.4	508.9	497.0	481.0	463.0	446.4	427.4
62.5°	473.6	486.0	494.6	499.3	494.6	486.0	473.6	456.7	437.4	418.8	399.8
65°	433.3	445.8	454.2	455.9	454.2	445.8	433.3	416.6	396.4	376.8	360.7
67.5°	389.3	401.7	407.3	410.7	407.3	401.7	389.3	373.6	353.5	333.2	315.0
70°	358.3	368.4	374.4	377.4	374.4	368.4	358.3	341.6	325.0	304.2	284.5
72.5°	323.0	333.6	340.6	341.2	340.6	333.6	323.0	308.8	291.2	271.8	254.5
75°	269.1	278.5	282.1	282.1	282.1	278.5	269.1	255.4	241.1	225.6	208.4
77.5°	212.9	217.8	222.4	223.3	222.4	217.8	212.9	203.1	191.3	175.8	162.8
80°	176.8	179.8	183.3	183.3	183.3	179.8	176.8	167.8	156.5	143.4	133.4
82.5°	139.7	142.2	145.7	145.3	145.7	142.2	139.7	132.6	123.2	114.4	105.2
85°	84.6	89.9	89.3	88.1	89.3	89.9	84.6	85.7	76.8	70.9	62.5
87.5°	39.3	40.0	41.2	42.2	41.2	40.0	39.3	37.9	33.6	31.2	29.2
90°	6.4	6.7	6.4	6.4	6.4	6.7	6.4	6.1	6.1	5.8	5.5
92.5°	26.1	24.5	23.4	23.4	23.4	24.5	26.1	29.7	35.8	44.9	59.8
95°	93.1	83.7	78.2	74.2	78.2	83.7	93.1	108.1	137.5	178.3	225.5
97.5°	232.2	214.0	204.8	198.5	204.8	214.0	232.2	254.1	285.9	315.6	333.1
100°	309.2	290.6	281.5	279.1	281.5	290.6	309.2	335.6	358.2	373.1	367.0
102.5°	374.2	360.8	351.1	349.1	351.1	360.8	374.2	390.4	399.8	395.5	365.3
105°	436.7	434.2	430.0	428.2	430.0	434.2	436.7	436.1	423.6	393.5	340.8
107.5°	446.7	453.7	456.7	457.4	456.7	453.7	446.7	431.7	404.5	362.1	306.1
110°	437.0	449.8	455.2	458.0	455.2	449.8	437.0	415.3	381.9	337.8	285.2



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	416.0	431.5	439.2	443.6	439.2	431.5	416.0	391.5	358.0	316.3	269.8
115°	380.6	398.9	408.7	411.1	408.7	398.9	380.6	356.6	327.4	291.8	254.4
117.5°	351.1	366.4	376.3	378.2	376.3	366.4	351.1	330.6	305.8	277.8	246.8
120°	335.0	348.4	356.4	359.7	356.4	348.4	335.0	317.7	296.1	271.7	243.4
122.5°	323.6	335.0	341.7	345.1	341.7	335.0	323.6	308.9	290.0	267.9	240.5
125°	311.6	320.5	326.2	328.0	326.2	320.5	311.6	299.5	282.7	261.7	235.6
127.5°	303.5	311.3	316.2	318.1	316.2	311.3	303.5	291.3	275.4	254.4	229.5
130°	297.9	305.5	310.4	312.2	310.4	305.5	297.9	285.4	269.3	248.7	224.5
132.5°	290.6	299.2	303.8	305.7	303.8	299.2	290.6	278.4	262.3	242.0	219.5
135°	278.1	286.6	291.5	293.3	291.5	286.6	278.1	266.0	250.7	232.2	212.4
137.5°	263.6	271.9	276.0	278.1	276.0	271.9	263.6	252.1	238.4	222.7	206.0
140°	253.8	260.5	264.8	267.2	264.8	260.5	253.8	243.1	230.3	216.6	202.3
142.5°	243.8	250.0	253.8	255.5	253.8	250.0	243.8	234.4	223.3	211.5	199.0
145°	229.7	234.9	238.0	239.4	238.0	234.9	229.7	222.1	213.6	204.5	194.2
147.5°	218.0	222.5	224.7	225.3	224.7	222.5	218.0	212.4	205.7	198.4	190.2
150°	211.2	215.2	217.0	217.2	217.0	215.2	211.2	206.3	200.9	194.8	187.8
152.5°	205.3	208.5	209.7	210.0	209.7	208.5	205.3	201.2	196.7	191.1	185.1
155°	197.2	199.6	200.5	200.5	200.5	199.6	197.2	194.2	190.5	185.9	181.1
157.5°	189.9	191.7	192.3	192.3	192.3	191.7	189.9	187.6	184.7	180.8	176.8
160°	185.0	186.8	187.2	187.2	187.2	186.8	185.0	183.2	180.7	177.4	174.1
162.5°	180.4	182.2	182.5	182.3	182.5	182.2	180.4	179.1	176.8	174.3	171.4
165°	174.4	175.6	175.3	175.0	175.3	175.6	174.4	173.1	171.6	169.5	167.6
167.5°	168.7	169.5	169.4	169.2	169.4	169.5	168.7	168.1	167.2	165.5	164.1
170°	165.6	165.8	165.6	165.6	165.6	165.8	165.6	165.0	164.0	162.8	161.9
172.5°	162.4	162.6	162.4	161.9	162.4	162.6	162.4	162.0	161.4	160.6	160.0
175°	158.3	158.9	158.3	157.6	158.3	158.9	158.3	158.3	158.3	157.6	157.3
177.5°	155.8	156.1	155.6	155.2	155.6	156.1	155.8	156.1	155.8	155.8	155.6
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1373.6	1375.4	1383.0	1390.2	1398.8	1405.0	1409.2	1414.0	1424.0	1432.1	1439.7
5°	1286.9	1289.9	1305.3	1316.0	1334.5	1350.6	1363.0	1376.7	1392.8	1414.8	1435.0
7.5°	1210.6	1221.6	1238.5	1255.9	1274.7	1295.8	1314.1	1334.7	1362.4	1392.7	1423.8
10°	1167.3	1179.7	1197.6	1217.8	1235.7	1260.1	1282.7	1307.1	1338.6	1375.5	1412.5
12.5°	1123.9	1144.4	1158.0	1182.1	1201.4	1221.5	1245.5	1277.6	1314.3	1353.1	1397.7
15°	1069.6	1080.9	1107.1	1120.2	1147.5	1178.5	1202.3	1234.5	1270.1	1321.4	1371.4
17.5°	1007.0	1021.8	1042.7	1067.7	1099.2	1123.3	1153.0	1186.0	1231.1	1281.9	1344.5
20°	966.0	978.5	1004.1	1031.5	1064.8	1090.5	1122.0	1154.1	1200.6	1254.7	1320.2
22.5°	929.4	941.4	968.5	993.9	1026.2	1057.6	1090.5	1127.9	1172.4	1229.5	1296.4
25°	872.6	888.6	912.5	938.7	969.6	1005.3	1041.0	1074.4	1122.0	1182.1	1253.5
27.5°	822.3	835.1	852.4	882.1	917.2	951.7	987.2	1029.2	1074.9	1138.4	1212.5
30°	789.9	801.8	819.0	846.4	879.2	916.0	953.0	993.4	1041.0	1104.1	1179.7
32.5°	764.1	773.2	788.5	813.0	842.9	881.8	918.2	960.1	1010.0	1072.2	1145.9
35°	726.2	733.9	739.9	763.1	789.9	825.5	862.5	907.1	955.3	1014.3	1088.0
37.5°	688.9	691.6	700.3	715.4	741.4	774.3	808.6	852.5	901.9	961.7	1028.3
40°	666.1	667.3	672.6	686.9	709.5	740.5	773.8	817.3	864.3	920.8	986.9
42.5°	643.7	642.9	647.8	657.8	679.0	707.1	739.9	779.6	826.6	878.9	941.2
45°	608.3	608.3	607.1	615.4	632.7	660.1	687.5	725.6	764.8	816.1	868.4
47.5°	571.4	568.1	569.1	573.4	588.0	610.4	638.1	669.3	703.9	747.3	793.2
50°	547.6	542.9	541.1	545.8	558.9	578.5	604.8	632.1	664.9	702.9	742.3
52.5°	521.4	516.7	513.4	516.8	528.9	547.1	570.9	595.0	624.4	655.3	689.4
55°	481.0	475.6	473.8	475.0	483.9	498.2	518.4	540.4	562.5	588.1	611.9
57.5°	441.1	432.2	430.6	430.0	436.2	449.3	466.1	485.3	501.3	516.8	542.1
60°	414.8	404.2	400.5	400.0	404.8	415.4	430.9	450.0	461.3	472.0	494.0
62.5°	386.8	376.5	368.7	369.5	373.8	384.0	397.6	411.4	418.9	430.6	445.5
65°	343.5	330.4	324.4	322.6	325.0	333.3	344.1	352.9	361.3	366.1	380.3
67.5°	300.1	289.1	280.3	278.2	277.2	282.8	291.6	297.0	303.0	307.1	315.6
70°	269.7	260.1	249.4	245.8	245.2	249.9	258.3	258.9	267.3	269.1	277.9
72.5°	239.6	227.7	220.3	216.8	214.3	218.5	224.0	225.6	230.1	233.3	238.0
75°	192.9	183.9	176.8	171.4	169.6	172.0	172.0	175.0	178.0	179.8	185.1
77.5°	151.8	141.5	133.1	130.0	127.9	126.3	127.6	129.4	127.9	131.0	132.2
80°	123.2	112.5	106.0	104.8	101.2	98.2	97.6	99.4	97.0	98.2	101.8
82.5°	95.1	88.3	81.2	80.0	75.5	74.0	73.4	72.2	72.2	72.0	72.8
85°	56.6	52.3	47.6	44.6	42.9	39.9	39.9	38.7	37.5	36.3	36.9
87.5°	23.8	23.0	20.5	18.9	18.0	15.8	15.8	14.2	13.7	13.0	12.4
90°	5.2	5.5	4.9	4.2	4.2	2.4	2.4	2.2	1.8	0.9	0.3
92.5°	80.4	96.5	84.5	61.5	37.9	22.4	16.1	11.6	7.9	5.1	3.4
95°	255.0	248.0	187.2	114.4	64.5	38.1	25.2	18.0	14.0	10.9	10.1
97.5°	320.4	261.2	175.1	102.9	61.6	41.2	30.6	24.3	20.7	18.0	18.0
100°	322.5	244.7	158.9	96.8	62.4	44.4	34.7	28.9	25.2	23.2	23.2
102.5°	304.3	223.9	147.9	95.1	64.8	48.6	39.3	33.8	30.4	28.5	28.0
105°	271.1	199.6	138.4	95.8	70.6	56.0	47.2	41.7	38.1	36.5	35.6
107.5°	244.4	186.0	136.7	100.4	77.3	64.0	55.3	50.0	46.1	44.6	44.0
110°	231.0	181.3	137.2	103.8	82.5	69.1	60.9	55.4	51.7	50.2	49.6



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	223.4	179.2	138.7	107.5	87.3	74.4	66.2	60.7	57.3	55.5	54.9
115°	216.4	178.1	141.5	113.2	95.0	82.7	74.6	68.8	65.7	63.6	62.7
117.5°	213.2	177.7	144.5	119.1	102.3	90.7	82.2	76.8	73.4	71.5	70.7
120°	211.5	177.7	146.7	123.2	107.5	95.8	87.3	82.1	78.8	76.7	76.1
122.5°	209.6	177.5	148.9	127.2	112.3	100.7	92.5	86.8	83.7	81.5	80.9
125°	206.3	177.1	152.1	132.9	119.0	108.1	99.5	93.8	90.4	88.5	87.3
127.5°	202.0	176.4	154.8	138.0	125.2	114.6	106.0	100.0	96.2	93.9	93.0
130°	199.3	176.2	156.7	141.2	129.3	119.0	110.1	104.4	99.8	97.4	96.2
132.5°	196.9	176.0	158.4	144.4	132.8	122.3	114.1	107.8	103.5	100.3	99.4
135°	193.2	175.6	161.0	148.5	137.5	127.5	119.6	113.2	108.1	105.0	103.8
137.5°	190.1	175.6	162.5	151.4	141.2	131.8	124.2	117.6	112.7	109.3	108.2
140°	188.4	175.3	163.7	153.3	143.6	134.5	127.2	120.8	115.6	112.3	111.4
142.5°	186.9	175.3	164.7	154.8	145.9	136.9	129.8	123.7	118.8	115.7	114.8
145°	184.4	174.7	165.2	156.4	148.2	140.3	133.6	127.8	123.6	120.5	119.6
147.5°	182.2	173.6	165.6	157.8	150.6	143.2	137.2	132.3	128.0	125.3	125.0
150°	180.5	172.8	165.6	158.5	151.9	145.2	139.4	134.8	131.1	128.7	128.4
152.5°	178.5	171.6	165.1	159.0	152.8	146.9	141.5	137.5	134.1	131.6	131.6
155°	175.6	169.8	164.4	159.5	154.3	149.1	144.6	141.2	138.2	136.3	136.0
157.5°	172.6	167.9	163.5	159.5	155.3	150.9	147.3	144.4	142.1	140.3	140.3
160°	170.4	166.4	162.8	159.5	155.8	152.1	148.8	146.4	144.2	143.0	143.0
162.5°	168.5	165.0	162.0	159.5	156.3	152.9	150.2	148.1	146.2	145.3	145.4
165°	165.2	162.8	160.7	158.9	156.4	153.7	151.9	150.3	148.8	148.2	148.2
167.5°	162.3	160.6	159.2	158.1	156.4	154.4	152.9	152.1	150.9	150.6	150.9
170°	160.4	159.1	158.3	157.6	156.1	154.5	153.7	153.1	152.1	151.9	152.1
172.5°	158.7	157.6	157.3	157.1	155.8	154.8	154.1	153.8	153.1	153.1	153.3
175°	156.7	156.1	156.1	156.4	155.5	154.9	154.9	154.5	154.3	154.3	154.5
177.5°	155.4	155.2	155.2	155.6	155.2	154.9	154.9	154.9	154.6	154.9	155.2
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1446.4	1451.1	1457.3	1467.8	1471.6	1476.4	1483.1	1482.6	1484.5	1491.6	1506.8
5°	1451.7	1470.2	1488.1	1509.5	1532.1	1547.0	1567.2	1579.7	1592.2	1608.3	1635.6
7.5°	1453.9	1483.2	1515.9	1553.5	1587.0	1625.6	1655.6	1683.9	1709.6	1743.5	1776.2
10°	1450.5	1489.8	1532.1	1579.7	1630.3	1673.2	1711.8	1755.9	1793.4	1834.4	1871.4
12.5°	1444.3	1491.8	1548.3	1601.6	1660.8	1724.1	1772.3	1816.8	1866.7	1914.0	1970.9
15°	1430.3	1495.2	1561.3	1631.5	1710.6	1783.8	1853.5	1911.2	1964.8	2035.7	2110.1
17.5°	1412.5	1482.5	1565.7	1650.8	1733.5	1817.2	1903.4	1990.2	2057.8	2145.8	2204.0
20°	1395.8	1476.7	1562.5	1663.6	1746.4	1850.5	1936.2	2020.2	2113.0	2200.5	2270.1
22.5°	1372.4	1461.0	1552.0	1652.7	1761.6	1865.8	1964.8	2055.9	2148.7	2243.9	2328.2
25°	1342.8	1423.1	1530.9	1645.2	1753.5	1866.6	1980.3	2094.6	2194.5	2295.2	2373.7
27.5°	1292.4	1393.8	1494.1	1612.1	1732.4	1860.4	1981.9	2101.6	2206.3	2289.1	2337.8
30°	1266.6	1354.7	1463.6	1582.1	1712.4	1849.9	1976.7	2094.0	2191.6	2257.6	2277.3
32.5°	1228.6	1319.5	1426.0	1548.8	1686.7	1828.0	1960.1	2070.6	2152.1	2186.7	2163.0
35°	1172.0	1254.1	1361.8	1487.5	1630.9	1781.5	1911.9	2005.3	2046.9	2014.2	1932.7
37.5°	1104.1	1185.5	1293.7	1417.1	1565.6	1718.6	1836.5	1903.8	1889.9	1808.5	1687.0
40°	1056.5	1132.7	1235.7	1369.0	1513.6	1667.2	1770.7	1807.1	1769.0	1652.3	1523.2
42.5°	1003.7	1078.0	1181.4	1309.9	1463.2	1604.8	1695.1	1698.1	1634.2	1494.7	1365.0
45°	923.2	994.0	1091.7	1225.5	1367.2	1500.6	1560.0	1530.9	1413.1	1278.5	1148.1
47.5°	843.8	905.2	1001.4	1128.5	1263.1	1375.3	1404.8	1352.3	1226.8	1096.1	975.3
50°	785.7	847.6	938.1	1059.5	1189.2	1286.2	1300.5	1230.9	1107.7	976.1	881.5
52.5°	730.0	791.4	878.6	990.9	1109.7	1197.2	1197.7	1117.1	994.4	877.1	789.1
55°	648.2	703.5	782.1	882.7	988.7	1057.1	1040.4	957.1	850.6	748.8	672.0
57.5°	569.4	617.6	690.0	773.9	867.2	923.7	896.0	815.8	720.7	634.4	576.2
60°	518.4	564.3	626.2	705.3	783.9	827.9	801.8	729.1	641.6	572.0	521.4
62.5°	468.9	507.6	567.1	635.8	708.7	741.3	718.0	646.3	570.7	507.7	466.7
65°	398.8	430.3	477.9	536.9	589.9	617.9	598.2	531.5	473.8	428.5	395.8
67.5°	333.3	358.0	394.0	441.3	486.3	501.4	483.5	437.1	388.2	352.0	328.9
70°	288.1	311.3	341.6	378.0	417.2	433.3	415.4	378.6	338.7	305.3	282.8
72.5°	248.6	266.6	292.1	323.2	354.0	370.0	357.8	322.4	288.7	263.9	244.6
75°	189.2	204.7	222.6	244.6	268.5	279.1	268.5	244.0	220.8	202.3	188.6
77.5°	137.6	145.9	159.7	176.2	191.1	199.2	190.0	173.4	159.3	146.6	139.9
80°	104.8	110.7	120.2	133.4	143.4	151.2	145.3	131.6	120.2	111.9	108.9
82.5°	76.2	80.2	86.4	96.2	103.0	106.9	104.3	94.4	89.7	82.4	79.4
85°	37.5	39.9	44.1	47.0	53.0	53.6	54.2	50.0	45.8	44.1	41.7
87.5°	13.0	13.7	15.2	16.7	18.6	19.5	18.9	19.0	17.3	16.8	14.9
90°	0.9	1.8	2.2	2.4	2.4	4.2	4.2	4.9	5.5	5.2	5.5
92.5°	5.1	7.9	11.6	16.1	22.4	37.9	61.5	84.5	96.5	80.4	59.8
95°	10.9	14.0	18.0	25.2	38.1	64.5	114.4	187.2	248.0	255.0	225.5
97.5°	18.0	20.7	24.3	30.6	41.2	61.6	102.9	175.1	261.2	320.4	333.1
100°	23.2	25.2	28.9	34.7	44.4	62.4	96.8	158.9	244.7	322.5	367.0
102.5°	28.5	30.4	33.8	39.3	48.6	64.8	95.1	147.9	223.9	304.3	365.3
105°	36.5	38.1	41.7	47.2	56.0	70.6	95.8	138.4	199.6	271.1	340.8
107.5°	44.6	46.1	50.0	55.3	64.0	77.3	100.4	136.7	186.0	244.4	306.1
110°	50.2	51.7	55.4	60.9	69.1	82.5	103.8	137.2	181.3	231.0	285.2



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	55.5	57.3	60.7	66.2	74.4	87.3	107.5	138.7	179.2	223.4	269.8
115°	63.6	65.7	68.8	74.6	82.7	95.0	113.2	141.5	178.1	216.4	254.4
117.5°	71.5	73.4	76.8	82.2	90.7	102.3	119.1	144.5	177.7	213.2	246.8
120°	76.7	78.8	82.1	87.3	95.8	107.5	123.2	146.7	177.7	211.5	243.4
122.5°	81.5	83.7	86.8	92.5	100.7	112.3	127.2	148.9	177.5	209.6	240.5
125°	88.5	90.4	93.8	99.5	108.1	119.0	132.9	152.1	177.1	206.3	235.6
127.5°	93.9	96.2	100.0	106.0	114.6	125.2	138.0	154.8	176.4	202.0	229.5
130°	97.4	99.8	104.4	110.1	119.0	129.3	141.2	156.7	176.2	199.3	224.5
132.5°	100.3	103.5	107.8	114.1	122.3	132.8	144.4	158.4	176.0	196.9	219.5
135°	105.0	108.1	113.2	119.6	127.5	137.5	148.5	161.0	175.6	193.2	212.4
137.5°	109.3	112.7	117.6	124.2	131.8	141.2	151.4	162.5	175.6	190.1	206.0
140°	112.3	115.6	120.8	127.2	134.5	143.6	153.3	163.7	175.3	188.4	202.3
142.5°	115.7	118.8	123.7	129.8	136.9	145.9	154.8	164.7	175.3	186.9	199.0
145°	120.5	123.6	127.8	133.6	140.3	148.2	156.4	165.2	174.7	184.4	194.2
147.5°	125.3	128.0	132.3	137.2	143.2	150.6	157.8	165.6	173.6	182.2	190.2
150°	128.7	131.1	134.8	139.4	145.2	151.9	158.5	165.6	172.8	180.5	187.8
152.5°	131.6	134.1	137.5	141.5	146.9	152.8	159.0	165.1	171.6	178.5	185.1
155°	136.3	138.2	141.2	144.6	149.1	154.3	159.5	164.4	169.8	175.6	181.1
157.5°	140.3	142.1	144.4	147.3	150.9	155.3	159.5	163.5	167.9	172.6	176.8
160°	143.0	144.2	146.4	148.8	152.1	155.8	159.5	162.8	166.4	170.4	174.1
162.5°	145.3	146.2	148.1	150.2	152.9	156.3	159.5	162.0	165.0	168.5	171.4
165°	148.2	148.8	150.3	151.9	153.7	156.4	158.9	160.7	162.8	165.2	167.6
167.5°	150.6	150.9	152.1	152.9	154.4	156.4	158.1	159.2	160.6	162.3	164.1
170°	151.9	152.1	153.1	153.7	154.5	156.1	157.6	158.3	159.1	160.4	161.9
172.5°	153.1	153.1	153.8	154.1	154.8	155.8	157.1	157.3	157.6	158.7	160.0
175°	154.3	154.3	154.5	154.9	154.9	155.5	156.4	156.1	156.1	156.7	157.3
177.5°	154.9	154.6	154.9	154.9	154.9	155.2	155.6	155.2	155.2	155.4	155.6
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8	1436.8
2.5°	1514.5	1515.4	1519.7	1523.0	1524.0	1528.8	1529.2
5°	1647.5	1657.7	1677.3	1679.1	1682.0	1697.5	1685.7
7.5°	1803.5	1829.2	1846.3	1861.5	1867.0	1873.7	1872.3
10°	1903.5	1941.6	1960.7	1991.0	1992.2	1999.9	1995.2
12.5°	2004.0	2048.2	2083.0	2088.6	2114.1	2118.0	2124.7
15°	2146.3	2193.4	2241.6	2258.8	2294.0	2302.3	2315.4
17.5°	2280.2	2328.2	2362.1	2406.7	2421.1	2440.4	2427.2
20°	2353.5	2405.9	2448.7	2483.8	2498.7	2509.4	2508.3
22.5°	2397.8	2450.6	2485.4	2511.9	2525.8	2530.4	2530.1
25°	2425.5	2455.8	2466.6	2476.7	2461.3	2455.8	2458.2
27.5°	2348.4	2340.5	2312.6	2275.9	2237.7	2207.5	2191.1
30°	2242.2	2195.7	2153.4	2079.7	2041.6	2019.0	1998.7
32.5°	2091.7	2018.1	1936.8	1869.2	1825.9	1792.3	1787.3
35°	1833.8	1723.1	1623.8	1541.0	1498.1	1461.8	1453.5
37.5°	1559.1	1444.1	1354.6	1281.8	1235.7	1210.0	1186.1
40°	1376.7	1277.9	1189.8	1127.9	1092.8	1074.4	1059.5
42.5°	1236.2	1146.0	1058.4	1011.2	979.5	968.2	959.5
45°	1042.2	958.3	897.6	861.9	843.4	824.4	815.5
47.5°	886.8	818.6	778.5	748.2	728.4	717.1	711.4
50°	798.7	742.8	707.1	683.9	666.1	657.1	652.4
52.5°	720.7	674.8	644.7	626.3	614.2	607.6	605.7
55°	620.8	585.7	566.6	550.6	541.7	535.7	533.3
57.5°	539.6	512.6	497.1	483.9	480.4	475.4	473.8
60°	486.3	465.5	452.4	443.4	440.5	434.5	435.7
62.5°	439.1	422.1	411.0	405.8	401.9	396.9	398.6
65°	371.4	359.0	352.9	348.2	343.5	340.4	342.9
67.5°	311.7	303.1	295.0	292.2	289.9	289.4	286.9
70°	272.6	265.4	258.3	256.6	256.6	254.2	253.6
72.5°	235.0	229.7	225.0	223.7	221.8	222.7	220.2
75°	181.5	177.4	175.6	173.8	173.2	173.2	171.4
77.5°	134.1	131.0	128.2	128.2	126.1	125.3	125.0
80°	101.8	100.6	98.2	98.2	97.0	97.6	96.4
82.5°	76.5	74.9	74.4	73.4	71.8	71.9	70.7
85°	41.1	39.3	38.7	36.9	35.7	36.9	35.7
87.5°	15.4	15.1	14.6	13.7	13.3	13.2	11.8
90°	5.8	6.1	6.1	6.4	6.7	6.4	6.4
92.5°	44.9	35.8	29.7	26.1	24.5	23.4	23.4
95°	178.3	137.5	108.1	93.1	83.7	78.2	74.2
97.5°	315.6	285.9	254.1	232.2	214.0	204.8	198.5
100°	373.1	358.2	335.6	309.2	290.6	281.5	279.1
102.5°	395.5	399.8	390.4	374.2	360.8	351.1	349.1
105°	393.5	423.6	436.1	436.7	434.2	430.0	428.2
107.5°	362.1	404.5	431.7	446.7	453.7	456.7	457.4
110°	337.8	381.9	415.3	437.0	449.8	455.2	458.0



TEST NUMBER: P332627-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	316.3	358.0	391.5	416.0	431.5	439.2	443.6
115°	291.8	327.4	356.6	380.6	398.9	408.7	411.1
117.5°	277.8	305.8	330.6	351.1	366.4	376.3	378.2
120°	271.7	296.1	317.7	335.0	348.4	356.4	359.7
122.5°	267.9	290.0	308.9	323.6	335.0	341.7	345.1
125°	261.7	282.7	299.5	311.6	320.5	326.2	328.0
127.5°	254.4	275.4	291.3	303.5	311.3	316.2	318.1
130°	248.7	269.3	285.4	297.9	305.5	310.4	312.2
132.5°	242.0	262.3	278.4	290.6	299.2	303.8	305.7
135°	232.2	250.7	266.0	278.1	286.6	291.5	293.3
137.5°	222.7	238.4	252.1	263.6	271.9	276.0	278.1
140°	216.6	230.3	243.1	253.8	260.5	264.8	267.2
142.5°	211.5	223.3	234.4	243.8	250.0	253.8	255.5
145°	204.5	213.6	222.1	229.7	234.9	238.0	239.4
147.5°	198.4	205.7	212.4	218.0	222.5	224.7	225.3
150°	194.8	200.9	206.3	211.2	215.2	217.0	217.2
152.5°	191.1	196.7	201.2	205.3	208.5	209.7	210.0
155°	185.9	190.5	194.2	197.2	199.6	200.5	200.5
157.5°	180.8	184.7	187.6	189.9	191.7	192.3	192.3
160°	177.4	180.7	183.2	185.0	186.8	187.2	187.2
162.5°	174.3	176.8	179.1	180.4	182.2	182.5	182.3
165°	169.5	171.6	173.1	174.4	175.6	175.3	175.0
167.5°	165.5	167.2	168.1	168.7	169.5	169.4	169.2
170°	162.8	164.0	165.0	165.6	165.8	165.6	165.6
172.5°	160.6	161.4	162.0	162.4	162.6	162.4	161.9
175°	157.6	158.3	158.3	158.3	158.9	158.3	157.6
177.5°	155.8	155.8	156.1	155.8	156.1	155.6	155.2
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9

(END OF REPORT)