

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332659-927

Luminaire Tested: **S124DIP-S1020D1035U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332659-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D1035U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6347.3 lumens  
Efficiency: N/A  
Efficacy: 104.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332659-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332659-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	53	51	46
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	38	34	32	28
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11035	11035	11035
5°	11068	10935	11015
10°	10999	10846	10900
15°	10866	10692	10719
20°	10689	10501	10510
25°	10488	10283	10253
30°	10241	10026	9934
35°	9984	9758	9629
40°	9720	9454	9280
45°	9442	9154	8978
50°	9134	8887	8611
55°	8802	8541	8263
60°	8472	8152	7905
65°	8097	7782	7469
70°	7678	7291	7006
75°	7037	6697	6525
80°	6267	6007	5858
85°	5483	5280	5169



TEST NUMBER: P332659-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.7	2.0
10°-20°	362.7	5.7
20°-30°	533.8	8.4
30°-40°	620.6	9.8
40°-50°	620.6	9.8
50°-60°	542.9	8.6
60°-70°	403.2	6.4
70°-80°	229.1	3.6
80°-90°	69.2	1.1
90°-100°	67.4	1.1
100°-110°	199.8	3.1
110°-120°	339.1	5.3
120°-130°	447.1	7.0
130°-140°	502.1	7.9
140°-150°	493.4	7.8
150°-160°	415.0	6.5
160°-170°	276.1	4.3
170°-180°	96.7	1.5
0°-30°	1025.2	16.2
0°-40°	1645.9	25.9
0°-60°	2809.4	44.3
0°-90°	3510.8	55.3
90°-120°	606.3	9.6
90°-150°	2048.8	32.3
90°-180°	2837.0	44.7
0°-180°	6347.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1367	1367	1367	1367	1367	
5°	1366	1361	1349	1361	1359	129
15°	1300	1295	1279	1285	1282	366
25°	1177	1169	1154	1155	1151	541
35°	1013	1005	990	983	977	633
45°	827	819	802	790	786	637
55°	625	621	607	594	587	560
65°	424	418	407	397	391	420
75°	226	220	215	210	209	240
85°	59	59	57	57	56	65
90°	2	11	17	22	24	6
95°	48	54	60	62	62	53
105°	184	185	188	191	193	196
115°	345	345	343	342	342	340
125°	502	502	501	500	498	447
135°	648	652	652	651	648	501
145°	787	790	791	790	788	492
155°	901	901	901	903	901	415
165°	981	979	977	982	979	276
175°	1021	1017	1016	1021	1016	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332659-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1370.4	1369.8	1369.2	1368.7	1368.1	1366.7	1364.5	1362.4	1360.3	1358.1	1360.1
5°	1365.8	1364.9	1363.9	1362.9	1361.9	1360.1	1357.4	1354.7	1352.1	1349.4	1352.1
7.5°	1353.1	1352.1	1351.1	1350.2	1349.2	1347.3	1344.3	1341.3	1338.3	1335.4	1337.5
10°	1341.7	1340.8	1339.7	1338.8	1337.8	1335.8	1332.6	1329.4	1326.3	1323.1	1325.0
12.5°	1326.8	1325.9	1324.8	1323.9	1322.9	1320.7	1317.4	1314.1	1310.7	1307.3	1309.5
15°	1300.1	1299.1	1298.1	1297.2	1296.2	1293.9	1290.2	1286.6	1282.9	1279.3	1280.7
17.5°	1267.9	1266.7	1265.4	1264.2	1263.1	1260.7	1257.2	1253.8	1250.3	1246.9	1247.8
20°	1244.2	1243.0	1241.8	1240.6	1239.4	1236.9	1233.3	1229.6	1226.0	1222.3	1223.1
22.5°	1218.9	1217.2	1215.6	1214.0	1212.4	1209.7	1206.1	1202.5	1198.8	1195.2	1196.5
25°	1177.4	1175.8	1174.0	1172.3	1170.6	1168.1	1164.7	1161.3	1157.9	1154.4	1154.7
27.5°	1130.1	1128.4	1126.6	1124.8	1123.1	1120.6	1117.5	1114.3	1111.1	1107.9	1107.4
30°	1098.6	1096.6	1094.6	1092.7	1090.8	1088.2	1085.1	1081.9	1078.7	1075.5	1074.6
32.5°	1065.2	1063.5	1061.8	1060.0	1058.3	1055.7	1052.3	1049.0	1045.6	1042.3	1041.1
35°	1013.1	1011.5	1009.7	1008.1	1006.3	1003.8	1000.4	997.0	993.6	990.1	988.4
37.5°	958.1	956.6	955.1	953.5	951.9	949.4	945.6	942.0	938.3	934.7	932.9
40°	922.3	920.3	918.3	916.4	914.4	911.6	908.0	904.4	900.7	897.1	894.6
42.5°	883.7	882.5	881.3	880.2	879.0	876.4	872.4	868.3	864.3	860.2	857.4
45°	827.0	825.2	823.6	821.8	820.1	817.3	813.4	809.5	805.6	801.8	799.1
47.5°	767.5	766.4	765.2	764.1	762.9	760.5	756.9	753.3	749.7	746.1	743.1
50°	727.3	726.3	725.3	724.4	723.3	721.2	717.8	714.4	711.0	707.6	704.2
52.5°	687.9	686.7	685.5	684.4	683.2	680.8	677.2	673.6	669.9	666.4	663.4
55°	625.4	624.6	623.9	623.2	622.5	620.4	617.0	613.6	610.2	606.8	603.9
57.5°	565.9	565.0	564.2	563.3	562.5	560.4	557.1	553.7	550.3	547.0	544.2
60°	524.7	523.4	522.2	521.0	519.8	517.6	514.4	511.3	508.1	504.9	502.7
62.5°	484.3	483.3	482.3	481.3	480.2	478.1	474.7	471.3	467.9	464.6	462.6
65°	423.9	422.6	421.4	420.3	419.0	417.2	414.7	412.3	409.9	407.4	405.0
67.5°	363.0	361.9	360.8	359.7	358.5	356.8	354.4	352.1	349.7	347.5	345.1
70°	325.3	323.6	321.9	320.2	318.5	316.6	314.7	312.8	310.9	308.9	306.9
72.5°	285.0	283.3	281.6	279.9	278.2	276.6	275.0	273.5	271.9	270.3	268.8
75°	225.6	224.4	223.2	222.0	220.8	219.5	218.3	217.1	215.9	214.7	213.7
77.5°	168.9	168.3	167.8	167.3	166.8	166.0	164.9	163.8	162.7	161.7	161.4
80°	134.8	134.0	133.2	132.5	131.8	131.2	130.7	130.2	129.8	129.2	128.7
82.5°	101.4	101.1	100.8	100.4	100.1	99.8	99.7	99.7	99.6	99.4	99.2
85°	59.2	59.2	59.2	59.2	59.2	58.9	58.4	57.9	57.4	57.0	57.0
87.5°	23.3	23.4	23.6	23.8	24.0	24.2	24.2	24.3	24.4	24.5	24.7
90°	2.4	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5
92.5°	17.0	19.2	21.3	23.5	25.7	27.4	28.4	29.3	30.3	31.3	31.9
95°	47.5	49.0	50.6	52.2	53.8	55.1	56.4	57.7	58.9	60.1	60.6
97.5°	82.9	84.1	85.4	86.7	87.9	89.3	90.7	92.1	93.6	95.1	95.7
100°	110.7	111.4	112.1	112.8	113.5	114.6	116.2	117.8	119.4	121.0	121.4
102.5°	139.8	140.1	140.4	140.6	140.9	141.8	143.2	144.7	146.1	147.6	148.1
105°	184.3	184.4	184.6	184.7	185.0	185.4	186.1	186.8	187.5	188.2	188.7
107.5°	230.9	231.1	231.3	231.6	231.7	231.9	232.0	232.1	232.2	232.3	232.8
110°	262.5	262.8	263.2	263.6	264.0	264.0	263.8	263.6	263.5	263.3	262.9



TEST NUMBER: P332659-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.4	295.5	295.6	295.6	295.7	295.6	295.2	294.9	294.6	294.3	294.2
115°	344.8	344.8	344.8	344.8	344.8	344.6	344.2	343.9	343.5	343.2	343.0
117.5°	391.3	391.4	391.5	391.7	391.8	391.7	391.5	391.3	391.0	390.8	390.1
120°	422.2	422.9	423.7	424.4	425.1	425.2	424.6	424.1	423.6	423.0	422.2
122.5°	454.5	454.8	455.0	455.3	455.6	455.7	455.4	455.1	454.9	454.6	454.1
125°	502.1	502.1	502.1	502.1	502.1	502.0	501.8	501.7	501.5	501.3	501.0
127.5°	545.3	545.8	546.3	546.8	547.4	547.5	547.2	546.9	546.7	546.4	546.1
130°	575.6	576.2	576.7	577.2	577.7	578.0	578.0	578.0	578.0	578.0	577.7
132.5°	606.7	607.0	607.4	607.8	608.2	608.3	608.2	608.0	607.8	607.8	607.4
135°	647.6	648.6	649.7	650.8	651.8	652.4	652.4	652.4	652.4	652.4	652.0
137.5°	692.2	692.7	693.2	693.6	694.2	694.5	694.8	695.1	695.4	695.7	695.2
140°	721.9	722.2	722.6	722.9	723.3	723.5	723.5	723.5	723.5	723.5	723.3
142.5°	749.1	749.5	749.8	750.2	750.5	750.6	750.5	750.4	750.2	750.0	750.0
145°	786.7	787.4	788.1	788.9	789.6	790.0	790.2	790.4	790.5	790.7	790.5
147.5°	824.1	824.9	825.8	826.6	827.4	827.8	827.7	827.5	827.4	827.3	827.1
150°	846.8	847.6	848.3	849.0	849.7	850.0	850.0	850.0	850.0	850.0	850.0
152.5°	868.4	868.8	869.2	869.7	870.1	870.3	870.4	870.6	870.8	870.8	871.3
155°	901.4	901.4	901.4	901.4	901.4	901.3	901.1	900.9	900.8	900.6	901.3
157.5°	929.2	928.9	928.6	928.3	928.0	927.8	927.7	927.7	927.7	927.6	928.2
160°	945.7	945.5	945.3	945.2	945.0	944.8	944.6	944.4	944.3	944.1	944.6
162.5°	960.8	960.4	960.0	959.5	959.0	958.7	958.5	958.4	958.2	958.0	958.9
165°	981.3	980.7	980.2	979.7	979.1	978.7	978.3	978.0	977.6	977.3	978.3
167.5°	997.0	996.2	995.5	994.7	994.0	993.6	993.6	993.7	993.7	993.8	994.8
170°	1005.8	1004.9	1004.0	1003.1	1002.3	1001.9	1002.1	1002.3	1002.4	1002.6	1003.7
172.5°	1012.1	1011.4	1010.7	1009.9	1009.2	1008.8	1008.8	1008.8	1008.9	1008.9	1010.1
175°	1020.8	1019.9	1019.1	1018.2	1017.3	1016.8	1016.6	1016.4	1016.2	1016.1	1017.3
177.5°	1023.7	1022.9	1022.2	1021.5	1020.8	1020.5	1020.5	1020.5	1020.5	1020.5	1021.4
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332659-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1362.0	1364.0	1366.0	1366.8	1366.6	1366.4	1366.2	1366.0
5°	1354.7	1357.4	1360.1	1361.2	1360.7	1360.2	1359.7	1359.2
7.5°	1339.7	1341.8	1343.9	1344.9	1344.6	1344.3	1343.9	1343.7
10°	1327.0	1329.0	1330.9	1331.6	1331.1	1330.6	1330.2	1329.7
12.5°	1311.6	1313.8	1315.9	1316.6	1316.0	1315.3	1314.5	1313.9
15°	1282.2	1283.7	1285.2	1285.5	1284.8	1284.0	1283.3	1282.5
17.5°	1248.7	1249.7	1250.5	1250.8	1250.3	1249.8	1249.4	1248.8
20°	1223.8	1224.6	1225.3	1225.3	1224.9	1224.4	1223.9	1223.4
22.5°	1197.8	1199.1	1200.4	1200.6	1199.8	1198.9	1198.0	1197.1
25°	1154.9	1155.2	1155.4	1155.0	1154.1	1153.1	1152.1	1151.1
27.5°	1106.8	1106.2	1105.6	1104.8	1103.5	1102.3	1101.1	1099.9
30°	1073.6	1072.6	1071.7	1070.6	1069.4	1068.1	1066.9	1065.7
32.5°	1039.9	1038.8	1037.6	1036.4	1035.1	1034.0	1032.8	1031.5
35°	986.7	985.0	983.3	981.8	980.6	979.5	978.2	977.0
37.5°	931.0	929.2	927.3	925.6	924.0	922.3	920.8	919.2
40°	892.2	889.7	887.3	885.5	884.2	883.0	881.9	880.6
42.5°	854.6	851.8	848.9	847.1	846.3	845.4	844.6	843.8
45°	796.4	793.7	791.0	789.3	788.6	787.9	787.1	786.4
47.5°	740.1	737.0	734.0	731.6	729.8	727.9	726.0	724.2
50°	700.8	697.4	694.0	691.5	690.0	688.6	687.1	685.6
52.5°	660.4	657.3	654.3	651.9	650.0	648.2	646.3	644.4
55°	600.9	598.0	595.1	592.9	591.4	590.0	588.5	587.1
57.5°	541.5	538.7	535.9	533.8	532.3	531.0	529.6	528.1
60°	500.6	498.4	496.1	494.5	493.2	492.0	490.8	489.6
62.5°	460.7	458.6	456.6	455.0	453.8	452.6	451.4	450.2
65°	402.6	400.1	397.7	395.9	394.7	393.5	392.2	391.0
67.5°	342.8	340.4	338.1	336.8	336.4	336.0	335.7	335.4
70°	305.0	303.0	301.1	299.8	299.0	298.3	297.5	296.8
72.5°	267.2	265.6	264.1	262.9	262.2	261.5	260.8	260.0
75°	212.7	211.8	210.8	210.2	209.9	209.7	209.5	209.2
77.5°	161.1	160.8	160.5	160.0	159.4	158.8	158.1	157.5
80°	128.3	127.8	127.3	126.9	126.7	126.4	126.2	126.0
82.5°	98.9	98.5	98.3	98.0	97.8	97.5	97.3	97.0
85°	57.0	57.0	57.0	56.8	56.6	56.3	56.1	55.8
87.5°	25.0	25.1	25.3	25.5	25.6	25.7	25.7	25.7
90°	19.5	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	32.6	33.2	33.8	34.3	34.5	34.7	34.9	35.1
95°	61.2	61.7	62.2	62.5	62.5	62.5	62.5	62.5
97.5°	96.3	97.0	97.6	97.9	97.9	97.9	97.9	97.9
100°	121.7	122.0	122.4	122.6	122.6	122.6	122.6	122.6
102.5°	148.5	149.0	149.5	149.8	150.0	150.1	150.3	150.4
105°	189.3	189.8	190.3	190.8	191.3	191.9	192.4	192.9
107.5°	233.3	233.8	234.2	234.5	234.5	234.4	234.4	234.3
110°	262.6	262.2	261.9	262.0	262.5	263.0	263.6	264.1





TEST NUMBER: P332659-927

CATALOG NUMBER: S124DIP-S1020D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.1	294.1	294.1	294.1	294.1	294.2	294.4	294.5
115°	342.8	342.6	342.5	342.3	342.1	341.9	341.7	341.6
117.5°	389.6	389.0	388.4	387.9	387.5	387.2	386.8	386.5
120°	421.3	420.4	419.5	419.2	419.6	419.9	420.3	420.6
122.5°	453.4	452.9	452.3	451.6	451.0	450.4	449.7	449.1
125°	500.6	500.3	499.9	499.6	499.2	498.8	498.5	498.1
127.5°	545.7	545.3	544.9	544.6	544.4	544.1	543.8	543.5
130°	577.3	576.9	576.6	576.1	575.4	574.6	573.9	573.2
132.5°	607.0	606.7	606.3	606.0	605.7	605.5	605.1	604.9
135°	651.6	651.3	650.9	650.5	650.0	649.4	648.9	648.4
137.5°	694.7	694.3	693.9	693.6	693.8	693.9	694.0	694.1
140°	723.2	722.9	722.8	722.6	722.5	722.2	722.1	721.9
142.5°	750.0	750.0	750.0	749.9	749.9	749.8	749.8	749.7
145°	790.4	790.2	790.0	789.6	789.1	788.6	788.1	787.5
147.5°	827.0	826.8	826.6	826.5	826.3	826.2	826.0	825.9
150°	850.0	850.0	850.0	849.9	849.8	849.5	849.4	849.2
152.5°	871.7	872.1	872.6	872.6	872.1	871.6	871.2	870.7
155°	902.1	902.7	903.4	903.4	902.7	902.1	901.3	900.6
157.5°	928.7	929.2	929.8	929.7	929.2	928.5	928.0	927.3
160°	945.2	945.7	946.2	946.0	945.2	944.3	943.4	942.5
162.5°	959.9	960.8	961.8	961.9	961.0	960.1	959.3	958.3
165°	979.5	980.5	981.5	981.7	981.0	980.3	979.6	978.9
167.5°	995.9	997.0	998.0	998.0	996.9	995.8	994.7	993.6
170°	1004.7	1005.8	1006.9	1006.7	1005.5	1004.2	1003.1	1001.8
172.5°	1011.3	1012.5	1013.8	1013.7	1012.5	1011.2	1010.0	1008.8
175°	1018.5	1019.8	1021.0	1021.0	1019.8	1018.5	1017.3	1016.1
177.5°	1022.5	1023.4	1024.5	1024.4	1023.3	1022.1	1021.0	1019.9
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4

(END OF REPORT)