

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332631-935

Luminaire Tested: **S124DIP-S1020D365U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332631-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D365U935-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5072.1 lumens  
Efficiency: N/A  
Efficacy: 116.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332631-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332631-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67	63
2	94	86	80	74	89	82	77	72	75	70	66	68	64	61	62	59	56	53
3	86	76	68	62	81	73	66	60	66	60	56	60	56	52	55	51	48	45
4	79	67	59	53	75	64	57	51	59	53	48	54	49	44	49	45	41	38
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	33
6	67	54	46	40	63	52	44	38	48	41	36	44	38	34	40	35	32	29
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28	26
8	58	45	37	31	55	43	35	30	40	33	29	37	31	27	34	29	25	23
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11994	11994	11994
5°	12030	11885	11972
10°	11954	11788	11847
15°	11810	11621	11651
20°	11618	11413	11424
25°	11399	11176	11144
30°	11130	10897	10797
35°	10852	10606	10465
40°	10564	10275	10086
45°	10261	9949	9758
50°	9928	9658	9359
55°	9568	9282	8981
60°	9206	8861	8591
65°	8800	8458	8118
70°	8344	7924	7615
75°	7648	7277	7093
80°	6811	6527	6365
85°	5956	5734	5622



TEST NUMBER: P332631-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.9	2.8
10°-20°	394.2	7.8
20°-30°	580.2	11.4
30°-40°	674.5	13.3
40°-50°	674.5	13.3
50°-60°	590.0	11.6
60°-70°	438.2	8.6
70°-80°	248.9	4.9
80°-90°	73.0	1.4
90°-100°	13.9	0.3
100°-110°	88.7	1.7
110°-120°	169.7	3.3
120°-130°	215.4	4.2
130°-140°	230.5	4.5
140°-150°	215.6	4.2
150°-160°	173.8	3.4
160°-170°	112.1	2.2
170°-180°	38.6	0.8
0°-30°	1114.3	22.0
0°-40°	1788.8	35.3
0°-60°	3053.4	60.2
0°-90°	3813.6	75.2
90°-120°	272.4	5.4
90°-150°	933.9	18.4
90°-180°	1258.0	24.8
0°-180°	5072.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1486	1486	1486	1486	1486	
5°	1484	1479	1467	1479	1477	141
15°	1413	1408	1390	1397	1394	398
25°	1280	1271	1255	1256	1251	588
35°	1101	1092	1076	1068	1062	688
45°	899	890	871	859	855	693
55°	680	675	660	646	638	609
65°	461	454	443	431	425	456
75°	245	239	233	229	227	261
85°	64	64	62	62	61	71
90°	1	4	7	8	9	4
95°	17	7	7	8	9	22
105°	92	93	95	97	87	96
115°	171	172	172	172	172	168
125°	240	242	241	242	242	215
135°	298	298	299	300	300	230
145°	344	345	345	345	346	215
155°	377	377	376	378	377	174
165°	398	396	396	398	396	112
175°	407	405	405	408	404	39
180°	407	407	407	407	407	



TEST NUMBER: P332631-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1489.4	1488.8	1488.2	1487.5	1486.9	1485.4	1483.1	1480.7	1478.4	1476.1	1478.3
5°	1484.5	1483.4	1482.4	1481.3	1480.2	1478.3	1475.3	1472.4	1469.6	1466.6	1469.6
7.5°	1470.7	1469.6	1468.5	1467.5	1466.5	1464.3	1461.0	1457.8	1454.6	1451.4	1453.7
10°	1458.3	1457.2	1456.1	1455.1	1454.1	1451.8	1448.4	1444.9	1441.5	1438.0	1440.1
12.5°	1442.1	1441.1	1439.9	1438.9	1437.9	1435.5	1431.8	1428.2	1424.5	1420.9	1423.2
15°	1413.1	1412.0	1410.9	1409.9	1408.8	1406.3	1402.3	1398.4	1394.4	1390.4	1392.0
17.5°	1378.0	1376.7	1375.4	1374.1	1372.8	1370.2	1366.4	1362.7	1358.9	1355.2	1356.2
20°	1352.3	1351.0	1349.7	1348.3	1347.0	1344.4	1340.4	1336.4	1332.5	1328.5	1329.3
22.5°	1324.7	1322.9	1321.2	1319.5	1317.8	1314.8	1310.9	1306.9	1303.0	1299.0	1300.5
25°	1279.7	1277.9	1276.0	1274.1	1272.3	1269.5	1265.8	1262.1	1258.4	1254.7	1255.0
27.5°	1228.3	1226.4	1224.4	1222.5	1220.6	1218.0	1214.5	1211.1	1207.6	1204.2	1203.6
30°	1194.0	1191.9	1189.7	1187.7	1185.5	1182.8	1179.3	1175.9	1172.4	1169.0	1167.9
32.5°	1157.8	1155.9	1154.0	1152.1	1150.2	1147.4	1143.8	1140.1	1136.4	1132.8	1131.5
35°	1101.1	1099.3	1097.4	1095.6	1093.7	1091.0	1087.3	1083.6	1079.9	1076.2	1074.3
37.5°	1041.4	1039.7	1038.0	1036.3	1034.6	1031.8	1027.8	1023.8	1019.9	1015.9	1013.9
40°	1002.4	1000.2	998.1	996.0	993.9	990.8	986.9	982.9	979.0	975.0	972.3
42.5°	960.4	959.2	957.9	956.7	955.4	952.5	948.1	943.7	939.4	935.0	931.9
45°	898.8	896.9	895.1	893.2	891.4	888.3	884.1	879.9	875.6	871.4	868.5
47.5°	834.2	833.0	831.7	830.4	829.1	826.6	822.7	818.7	814.9	810.9	807.6
50°	790.5	789.4	788.3	787.3	786.2	783.9	780.2	776.4	772.7	769.0	765.3
52.5°	747.6	746.3	745.0	743.8	742.5	739.9	736.0	732.1	728.1	724.3	721.0
55°	679.8	678.9	678.1	677.3	676.6	674.3	670.6	666.9	663.2	659.5	656.3
57.5°	615.0	614.1	613.2	612.3	611.4	609.1	605.5	601.8	598.1	594.5	591.5
60°	570.2	568.9	567.6	566.3	564.9	562.6	559.1	555.7	552.2	548.8	546.4
62.5°	526.4	525.3	524.2	523.1	521.9	519.6	515.9	512.3	508.6	505.0	502.8
65°	460.7	459.3	458.1	456.8	455.4	453.4	450.7	448.2	445.5	442.8	440.2
67.5°	394.5	393.3	392.1	390.9	389.6	387.8	385.2	382.7	380.1	377.6	375.1
70°	353.5	351.7	349.8	348.0	346.1	344.1	342.1	339.9	337.9	335.7	333.6
72.5°	309.8	307.9	306.1	304.2	302.4	300.6	298.9	297.2	295.5	293.8	292.1
75°	245.2	243.9	242.5	241.3	240.0	238.6	237.3	236.0	234.6	233.3	232.3
77.5°	183.6	183.0	182.4	181.8	181.2	180.4	179.2	178.1	176.8	175.7	175.4
80°	146.5	145.6	144.8	144.0	143.3	142.6	142.1	141.5	141.0	140.4	139.9
82.5°	110.2	109.9	109.5	109.1	108.7	108.5	108.4	108.3	108.2	108.1	107.8
85°	64.3	64.3	64.3	64.3	64.3	64.1	63.5	62.9	62.4	61.9	61.9
87.5°	25.0	24.9	24.8	24.8	24.7	24.6	24.5	24.4	24.3	24.2	24.3
90°	0.9	1.6	2.4	3.2	3.9	4.6	5.1	5.6	6.1	6.7	7.1
92.5°	3.9	3.9	3.9	4.0	4.0	4.3	4.8	5.3	5.9	6.5	6.9
95°	16.7	14.5	12.1	9.8	7.6	6.5	6.5	6.5	6.6	6.7	7.1
97.5°	35.6	36.9	38.4	39.9	41.2	38.2	30.7	23.2	15.6	8.0	8.1
100°	49.9	51.1	52.3	53.6	54.8	50.7	41.4	32.0	22.7	13.4	12.2
102.5°	66.0	66.9	67.8	68.6	69.6	69.4	68.2	67.0	65.7	64.5	52.1
105°	91.6	92.0	92.4	92.8	93.2	93.6	93.9	94.3	94.6	95.0	95.6
107.5°	115.4	115.5	115.8	116.0	116.2	116.5	117.0	117.4	117.9	118.4	118.6
110°	131.5	131.6	131.8	132.1	132.2	132.6	132.9	133.4	133.8	134.2	134.3



TEST NUMBER: P332631-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.1	147.4	147.7	148.1	148.5	148.8	149.0	149.1	149.3	149.6	149.5
115°	171.0	171.3	171.4	171.6	171.9	171.9	171.9	171.8	171.7	171.6	171.8
117.5°	192.6	192.9	193.1	193.5	193.7	193.9	194.1	194.2	194.3	194.5	194.5
120°	207.2	207.5	207.8	208.0	208.3	208.4	208.4	208.3	208.2	208.1	208.3
122.5°	220.8	221.0	221.2	221.4	221.5	221.6	221.7	221.8	221.9	222.1	222.1
125°	240.4	240.6	240.9	241.2	241.5	241.5	241.4	241.3	241.2	241.0	241.2
127.5°	258.9	259.0	259.0	259.1	259.2	259.3	259.7	259.9	260.3	260.6	260.5
130°	270.8	270.9	271.0	271.0	271.1	271.2	271.4	271.6	271.8	272.1	272.1
132.5°	281.8	281.9	282.0	282.1	282.2	282.4	282.7	282.9	283.2	283.4	283.5
135°	298.2	298.2	298.1	298.0	297.9	298.0	298.3	298.6	298.9	299.1	299.3
137.5°	312.7	312.8	312.8	312.8	312.9	313.1	313.3	313.6	313.9	314.2	314.4
140°	322.3	322.4	322.5	322.6	322.8	322.9	323.0	323.2	323.3	323.5	323.6
142.5°	330.8	331.0	331.2	331.5	331.7	331.9	332.0	332.1	332.2	332.3	332.3
145°	343.9	344.1	344.2	344.5	344.7	344.7	344.7	344.7	344.7	344.7	344.8
147.5°	354.2	354.6	355.0	355.4	355.8	355.9	355.9	355.8	355.7	355.7	355.7
150°	361.8	362.1	362.3	362.7	362.9	363.0	362.9	362.8	362.7	362.7	362.7
152.5°	368.2	368.3	368.6	368.8	369.0	369.0	368.9	368.8	368.7	368.6	368.7
155°	377.0	377.1	377.1	377.2	377.3	377.2	377.0	376.8	376.6	376.4	376.7
157.5°	384.5	384.4	384.4	384.4	384.4	384.2	384.0	383.7	383.5	383.3	383.7
160°	388.9	388.7	388.5	388.3	388.1	388.0	387.9	387.8	387.7	387.6	388.1
162.5°	392.8	392.5	392.3	392.0	391.8	391.6	391.5	391.4	391.4	391.3	391.8
165°	397.7	397.4	397.0	396.7	396.3	396.1	396.1	396.1	396.1	396.1	396.7
167.5°	401.6	401.2	400.9	400.5	400.2	400.0	399.9	399.9	399.8	399.8	400.5
170°	403.8	403.4	402.9	402.6	402.2	402.0	402.1	402.2	402.2	402.3	402.8
172.5°	405.3	404.8	404.4	404.1	403.6	403.5	403.6	403.6	403.6	403.7	404.2
175°	406.8	406.4	406.0	405.6	405.2	405.0	405.1	405.2	405.3	405.3	406.0
177.5°	407.6	407.2	406.8	406.4	406.0	405.9	406.0	406.1	406.2	406.3	406.8
180°	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8



TEST NUMBER: P332631-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1480.3	1482.5	1484.6	1485.6	1485.3	1485.1	1484.9	1484.7
5°	1472.4	1475.3	1478.3	1479.5	1478.9	1478.3	1477.8	1477.3
7.5°	1456.0	1458.4	1460.7	1461.7	1461.4	1461.0	1460.7	1460.4
10°	1442.3	1444.4	1446.5	1447.3	1446.7	1446.2	1445.7	1445.2
12.5°	1425.6	1427.9	1430.2	1431.0	1430.3	1429.5	1428.7	1428.1
15°	1393.6	1395.2	1396.8	1397.1	1396.4	1395.6	1394.8	1394.0
17.5°	1357.2	1358.2	1359.2	1359.4	1358.9	1358.4	1357.9	1357.3
20°	1330.1	1330.9	1331.7	1331.8	1331.3	1330.8	1330.2	1329.7
22.5°	1301.8	1303.3	1304.7	1304.9	1304.0	1303.0	1302.1	1301.1
25°	1255.3	1255.5	1255.8	1255.3	1254.3	1253.3	1252.2	1251.1
27.5°	1203.0	1202.3	1201.7	1200.8	1199.4	1198.1	1196.7	1195.4
30°	1166.9	1165.8	1164.8	1163.6	1162.3	1160.9	1159.6	1158.3
32.5°	1130.2	1129.0	1127.7	1126.4	1125.1	1123.8	1122.5	1121.1
35°	1072.5	1070.6	1068.8	1067.1	1065.8	1064.5	1063.2	1061.9
37.5°	1011.8	1009.9	1007.9	1006.0	1004.3	1002.5	1000.7	999.0
40°	969.7	967.0	964.4	962.4	961.0	959.8	958.5	957.1
42.5°	928.8	925.7	922.6	920.7	919.8	918.9	918.0	917.1
45°	865.6	862.6	859.7	857.9	857.1	856.4	855.5	854.7
47.5°	804.3	801.1	797.8	795.1	793.2	791.1	789.1	787.1
50°	761.6	757.9	754.2	751.6	749.9	748.4	746.8	745.2
52.5°	717.7	714.4	711.1	708.5	706.5	704.5	702.5	700.4
55°	653.2	650.0	646.8	644.5	642.8	641.3	639.6	638.1
57.5°	588.5	585.5	582.5	580.1	578.6	577.1	575.6	574.0
60°	544.1	541.7	539.2	537.4	536.1	534.8	533.5	532.1
62.5°	500.7	498.4	496.3	494.6	493.3	491.9	490.6	489.3
65°	437.6	434.9	432.2	430.2	429.0	427.7	426.3	425.0
67.5°	372.6	370.0	367.5	366.0	365.6	365.2	364.9	364.5
70°	331.5	329.3	327.3	325.8	325.0	324.2	323.4	322.6
72.5°	290.4	288.7	287.1	285.8	285.0	284.2	283.4	282.6
75°	231.2	230.1	229.1	228.4	228.2	227.9	227.6	227.4
77.5°	175.0	174.8	174.4	173.9	173.2	172.5	171.9	171.2
80°	139.4	138.9	138.4	137.9	137.7	137.4	137.2	136.9
82.5°	107.5	107.1	106.9	106.5	106.2	106.0	105.7	105.5
85°	61.9	61.9	61.9	61.7	61.5	61.2	61.0	60.7
87.5°	24.4	24.5	24.5	24.5	24.6	24.6	24.6	24.7
90°	7.5	7.9	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	7.2	7.7	8.1	8.3	8.4	8.4	8.4	8.4
95°	7.5	7.9	8.4	8.5	8.6	8.7	8.8	8.8
97.5°	8.1	8.2	8.2	8.3	8.4	8.4	8.4	8.5
100°	11.1	9.9	8.8	8.3	8.4	8.4	8.4	8.5
102.5°	39.7	27.3	14.9	8.7	8.7	8.7	8.8	8.8
105°	96.2	96.8	97.4	96.4	94.0	91.6	89.1	86.7
107.5°	119.0	119.2	119.6	119.9	120.1	120.4	120.6	120.9
110°	134.5	134.6	134.7	134.9	135.1	135.3	135.5	135.7





TEST NUMBER: P332631-935

CATALOG NUMBER: S124DIP-S1020D365U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	149.5	149.5	149.4	149.6	149.8	150.1	150.3	150.6
115°	171.9	172.0	172.2	172.2	172.2	172.2	172.2	172.2
117.5°	194.4	194.4	194.4	194.3	194.3	194.3	194.3	194.2
120°	208.4	208.5	208.7	208.7	208.5	208.4	208.3	208.1
122.5°	222.1	222.2	222.3	222.3	222.1	222.1	221.9	221.8
125°	241.4	241.6	241.8	241.9	242.0	242.1	242.1	242.2
127.5°	260.5	260.5	260.5	260.4	260.4	260.3	260.2	260.2
130°	272.2	272.2	272.3	272.3	272.3	272.3	272.3	272.3
132.5°	283.6	283.7	283.8	283.8	283.7	283.6	283.6	283.5
135°	299.4	299.5	299.6	299.8	299.9	300.1	300.2	300.3
137.5°	314.5	314.7	314.8	314.9	314.8	314.8	314.7	314.7
140°	323.8	324.1	324.3	324.4	324.5	324.5	324.6	324.7
142.5°	332.5	332.7	332.8	332.9	332.9	332.9	332.9	332.9
145°	344.9	345.0	345.0	345.1	345.3	345.4	345.5	345.7
147.5°	355.8	355.9	355.9	355.9	356.0	356.0	356.1	356.2
150°	362.7	362.7	362.7	362.7	362.8	362.9	362.9	363.0
152.5°	368.8	368.9	369.0	369.0	368.9	368.9	368.9	368.9
155°	376.9	377.2	377.5	377.5	377.3	377.1	376.9	376.7
157.5°	384.0	384.4	384.7	384.7	384.4	384.0	383.7	383.3
160°	388.5	388.9	389.3	389.3	388.9	388.5	388.1	387.6
162.5°	392.1	392.5	393.0	392.9	392.4	392.0	391.5	391.1
165°	397.3	397.8	398.4	398.3	397.7	397.1	396.5	395.9
167.5°	401.1	401.7	402.2	402.2	401.5	400.8	400.1	399.5
170°	403.4	403.9	404.4	404.3	403.7	403.0	402.3	401.7
172.5°	404.8	405.4	405.9	405.8	405.1	404.3	403.6	402.9
175°	406.6	407.2	407.8	407.7	406.8	406.0	405.2	404.4
177.5°	407.3	407.7	408.1	407.9	407.3	406.7	406.0	405.4
180°	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8

(END OF REPORT)