

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332640-935

Luminaire Tested: **S124DIP-S1020D590U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332640-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D590U935-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5845.5 lumens  
Efficiency: N/A  
Efficacy: 119.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332640-935

CATALOG NUMBER: S124DIP-S1020D590U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332640-935

CATALOG NUMBER: S124DIP-S1020D590U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	61	59	55
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	40	37	33
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	25
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11994	11994	11994
5°	12030	11885	11972
10°	11954	11788	11847
15°	11810	11621	11651
20°	11618	11413	11424
25°	11399	11176	11144
30°	11130	10897	10797
35°	10852	10606	10465
40°	10564	10275	10086
45°	10261	9949	9758
50°	9928	9658	9359
55°	9568	9282	8981
60°	9206	8861	8591
65°	8800	8458	8118
70°	8344	7924	7615
75°	7648	7277	7093
80°	6811	6527	6365
85°	5956	5734	5622



TEST NUMBER: P332640-935

CATALOG NUMBER: S124DIP-S1020D590U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.9	2.4
10°-20°	394.2	6.7
20°-30°	580.2	9.9
30°-40°	674.5	11.5
40°-50°	674.5	11.5
50°-60°	590.0	10.1
60°-70°	438.2	7.5
70°-80°	248.9	4.3
80°-90°	73.7	1.3
90°-100°	22.5	0.4
100°-110°	143.2	2.4
110°-120°	273.9	4.7
120°-130°	347.7	5.9
130°-140°	372.1	6.4
140°-150°	347.9	6.0
150°-160°	280.6	4.8
160°-170°	181.0	3.1
170°-180°	62.4	1.1
0°-30°	1114.3	19.1
0°-40°	1788.8	30.6
0°-60°	3053.4	52.2
0°-90°	3814.3	65.3
90°-120°	439.6	7.5
90°-150°	1507.3	25.8
90°-180°	2031.0	34.7
0°-180°	5845.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1486	1486	1486	1486	1486	
5°	1484	1479	1467	1479	1477	141
15°	1413	1408	1390	1397	1394	398
25°	1280	1271	1255	1256	1251	588
35°	1101	1092	1076	1068	1062	688
45°	899	890	871	859	855	693
55°	680	675	660	646	638	609
65°	461	454	443	431	425	456
75°	245	239	233	229	227	261
85°	64	64	62	62	61	71
90°	2	7	11	14	15	5
95°	27	11	11	14	14	35
105°	148	151	153	156	140	155
115°	276	277	277	278	278	272
125°	388	390	389	390	391	346
135°	481	481	483	484	485	371
145°	555	556	556	557	558	347
155°	609	609	608	609	608	280
165°	642	640	640	643	639	181
175°	657	654	654	658	653	63
180°	657	657	657	657	657	



TEST NUMBER: P332640-935

CATALOG NUMBER: S124DIP-S1020D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1489.4	1488.8	1488.2	1487.5	1486.9	1485.4	1483.1	1480.7	1478.4	1476.1	1478.3
5°	1484.5	1483.4	1482.4	1481.3	1480.2	1478.3	1475.3	1472.4	1469.6	1466.6	1469.6
7.5°	1470.7	1469.6	1468.5	1467.5	1466.5	1464.3	1461.0	1457.8	1454.6	1451.4	1453.7
10°	1458.3	1457.2	1456.1	1455.1	1454.1	1451.8	1448.4	1444.9	1441.5	1438.0	1440.1
12.5°	1442.1	1441.1	1439.9	1438.9	1437.9	1435.5	1431.8	1428.2	1424.5	1420.9	1423.2
15°	1413.1	1412.0	1410.9	1409.9	1408.8	1406.3	1402.3	1398.4	1394.4	1390.4	1392.0
17.5°	1378.0	1376.7	1375.4	1374.1	1372.8	1370.2	1366.4	1362.7	1358.9	1355.2	1356.2
20°	1352.3	1351.0	1349.7	1348.3	1347.0	1344.4	1340.4	1336.4	1332.5	1328.5	1329.3
22.5°	1324.7	1322.9	1321.2	1319.5	1317.8	1314.8	1310.9	1306.9	1303.0	1299.0	1300.5
25°	1279.7	1277.9	1276.0	1274.1	1272.3	1269.5	1265.8	1262.1	1258.4	1254.7	1255.0
27.5°	1228.3	1226.4	1224.4	1222.5	1220.6	1218.0	1214.5	1211.1	1207.6	1204.2	1203.6
30°	1194.0	1191.9	1189.7	1187.7	1185.5	1182.8	1179.3	1175.9	1172.4	1169.0	1167.9
32.5°	1157.8	1155.9	1154.0	1152.1	1150.2	1147.4	1143.8	1140.1	1136.4	1132.8	1131.5
35°	1101.1	1099.3	1097.4	1095.6	1093.7	1091.0	1087.3	1083.6	1079.9	1076.2	1074.3
37.5°	1041.4	1039.7	1038.0	1036.3	1034.6	1031.8	1027.8	1023.8	1019.9	1015.9	1013.9
40°	1002.4	1000.2	998.1	996.0	993.9	990.8	986.9	982.9	979.0	975.0	972.3
42.5°	960.4	959.2	957.9	956.7	955.4	952.5	948.1	943.7	939.4	935.0	931.9
45°	898.8	896.9	895.1	893.2	891.4	888.3	884.1	879.9	875.6	871.4	868.5
47.5°	834.2	833.0	831.7	830.4	829.1	826.6	822.7	818.7	814.9	810.9	807.6
50°	790.5	789.4	788.3	787.3	786.2	783.9	780.2	776.4	772.7	769.0	765.3
52.5°	747.6	746.3	745.0	743.8	742.5	739.9	736.0	732.1	728.1	724.3	721.0
55°	679.8	678.9	678.1	677.3	676.6	674.3	670.6	666.9	663.2	659.5	656.3
57.5°	615.0	614.1	613.2	612.3	611.4	609.1	605.5	601.8	598.1	594.5	591.5
60°	570.2	568.9	567.6	566.3	564.9	562.6	559.1	555.7	552.2	548.8	546.4
62.5°	526.4	525.3	524.2	523.1	521.9	519.6	515.9	512.3	508.6	505.0	502.8
65°	460.7	459.3	458.1	456.8	455.4	453.4	450.7	448.2	445.5	442.8	440.2
67.5°	394.5	393.3	392.1	390.9	389.6	387.8	385.2	382.7	380.1	377.6	375.1
70°	353.5	351.7	349.8	348.0	346.1	344.1	342.1	339.9	337.9	335.7	333.6
72.5°	309.8	307.9	306.1	304.2	302.4	300.6	298.9	297.2	295.5	293.8	292.1
75°	245.2	243.9	242.5	241.3	240.0	238.6	237.3	236.0	234.6	233.3	232.3
77.5°	183.6	183.0	182.4	181.8	181.2	180.4	179.2	178.1	176.8	175.7	175.4
80°	146.5	145.6	144.8	144.0	143.3	142.6	142.1	141.5	141.0	140.4	139.9
82.5°	110.2	109.9	109.5	109.1	108.7	108.5	108.4	108.3	108.2	108.1	107.8
85°	64.3	64.3	64.3	64.3	64.3	64.1	63.5	62.9	62.4	61.9	61.9
87.5°	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1
90°	1.5	2.7	3.9	5.1	6.3	7.3	8.2	9.0	9.9	10.8	11.5
92.5°	6.2	6.3	6.3	6.4	6.5	6.9	7.8	8.7	9.6	10.4	11.1
95°	27.0	23.3	19.6	15.8	12.1	10.3	10.5	10.6	10.7	10.8	11.5
97.5°	57.3	59.7	62.0	64.3	66.6	61.6	49.5	37.4	25.1	13.0	13.0
100°	80.5	82.5	84.5	86.4	88.4	81.9	66.8	51.7	36.7	21.6	19.7
102.5°	106.5	107.9	109.3	110.8	112.3	112.0	110.0	108.1	106.1	104.1	84.1
105°	147.8	148.5	149.1	149.8	150.4	151.0	151.6	152.1	152.7	153.3	154.2
107.5°	186.2	186.6	186.9	187.2	187.5	188.0	188.8	189.6	190.3	191.1	191.6
110°	212.2	212.5	212.8	213.2	213.4	214.0	214.6	215.2	215.9	216.6	216.8



TEST NUMBER: P332640-935

CATALOG NUMBER: S124DIP-S1020D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	237.3	237.9	238.5	239.1	239.7	240.1	240.4	240.7	241.1	241.3	241.3
115°	276.0	276.4	276.6	277.0	277.3	277.4	277.3	277.2	277.1	277.0	277.2
117.5°	310.9	311.3	311.8	312.2	312.6	313.0	313.2	313.5	313.7	313.9	313.9
120°	334.5	334.9	335.4	335.8	336.2	336.4	336.3	336.1	336.0	336.0	336.1
122.5°	356.5	356.7	357.0	357.2	357.5	357.7	357.9	358.0	358.2	358.3	358.4
125°	388.0	388.4	388.9	389.3	389.8	389.9	389.6	389.4	389.2	389.0	389.3
127.5°	417.8	417.9	418.1	418.2	418.3	418.6	419.1	419.6	420.1	420.6	420.5
130°	437.1	437.2	437.3	437.5	437.6	437.7	438.1	438.4	438.8	439.1	439.2
132.5°	454.8	455.0	455.2	455.4	455.6	455.9	456.3	456.7	457.1	457.5	457.6
135°	481.3	481.2	481.1	481.0	480.9	481.0	481.5	481.9	482.3	482.8	483.0
137.5°	504.8	504.8	504.9	504.9	505.0	505.2	505.7	506.2	506.7	507.1	507.4
140°	520.1	520.3	520.6	520.7	521.0	521.2	521.4	521.7	521.9	522.1	522.4
142.5°	533.9	534.3	534.7	535.0	535.5	535.7	535.8	536.0	536.1	536.2	536.5
145°	555.0	555.3	555.6	555.9	556.3	556.5	556.5	556.5	556.5	556.5	556.6
147.5°	571.8	572.4	573.0	573.6	574.2	574.5	574.4	574.3	574.1	574.0	574.1
150°	583.9	584.4	584.9	585.3	585.7	585.9	585.7	585.7	585.6	585.4	585.4
152.5°	594.2	594.5	594.9	595.2	595.6	595.6	595.5	595.3	595.0	594.9	595.0
155°	608.6	608.6	608.7	608.8	609.0	608.8	608.6	608.2	607.9	607.5	608.0
157.5°	620.6	620.5	620.4	620.4	620.4	620.1	619.7	619.4	619.0	618.6	619.2
160°	627.7	627.3	627.0	626.7	626.4	626.1	626.0	625.9	625.8	625.7	626.4
162.5°	634.0	633.5	633.1	632.7	632.3	632.1	631.9	631.8	631.7	631.6	632.2
165°	641.9	641.4	640.8	640.2	639.7	639.5	639.5	639.5	639.5	639.5	640.3
167.5°	648.2	647.6	647.0	646.5	645.9	645.6	645.6	645.5	645.4	645.3	646.4
170°	651.8	651.1	650.4	649.8	649.1	648.8	648.9	649.0	649.2	649.3	650.1
172.5°	654.1	653.4	652.8	652.1	651.5	651.2	651.3	651.4	651.5	651.6	652.6
175°	656.7	656.0	655.3	654.7	654.0	653.8	653.8	654.0	654.1	654.2	655.1
177.5°	657.8	657.2	656.6	656.0	655.4	655.1	655.3	655.5	655.7	655.8	656.6
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7



TEST NUMBER: P332640-935

CATALOG NUMBER: S124DIP-S1020D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1480.3	1482.5	1484.6	1485.6	1485.3	1485.1	1484.9	1484.7
5°	1472.4	1475.3	1478.3	1479.5	1478.9	1478.3	1477.8	1477.3
7.5°	1456.0	1458.4	1460.7	1461.7	1461.4	1461.0	1460.7	1460.4
10°	1442.3	1444.4	1446.5	1447.3	1446.7	1446.2	1445.7	1445.2
12.5°	1425.6	1427.9	1430.2	1431.0	1430.3	1429.5	1428.7	1428.1
15°	1393.6	1395.2	1396.8	1397.1	1396.4	1395.6	1394.8	1394.0
17.5°	1357.2	1358.2	1359.2	1359.4	1358.9	1358.4	1357.9	1357.3
20°	1330.1	1330.9	1331.7	1331.8	1331.3	1330.8	1330.2	1329.7
22.5°	1301.8	1303.3	1304.7	1304.9	1304.0	1303.0	1302.1	1301.1
25°	1255.3	1255.5	1255.8	1255.3	1254.3	1253.3	1252.2	1251.1
27.5°	1203.0	1202.3	1201.7	1200.8	1199.4	1198.1	1196.7	1195.4
30°	1166.9	1165.8	1164.8	1163.6	1162.3	1160.9	1159.6	1158.3
32.5°	1130.2	1129.0	1127.7	1126.4	1125.1	1123.8	1122.5	1121.1
35°	1072.5	1070.6	1068.8	1067.1	1065.8	1064.5	1063.2	1061.9
37.5°	1011.8	1009.9	1007.9	1006.0	1004.3	1002.5	1000.7	999.0
40°	969.7	967.0	964.4	962.4	961.0	959.8	958.5	957.1
42.5°	928.8	925.7	922.6	920.7	919.8	918.9	918.0	917.1
45°	865.6	862.6	859.7	857.9	857.1	856.4	855.5	854.7
47.5°	804.3	801.1	797.8	795.1	793.2	791.1	789.1	787.1
50°	761.6	757.9	754.2	751.6	749.9	748.4	746.8	745.2
52.5°	717.7	714.4	711.1	708.5	706.5	704.5	702.5	700.4
55°	653.2	650.0	646.8	644.5	642.8	641.3	639.6	638.1
57.5°	588.5	585.5	582.5	580.1	578.6	577.1	575.6	574.0
60°	544.1	541.7	539.2	537.4	536.1	534.8	533.5	532.1
62.5°	500.7	498.4	496.3	494.6	493.3	491.9	490.6	489.3
65°	437.6	434.9	432.2	430.2	429.0	427.7	426.3	425.0
67.5°	372.6	370.0	367.5	366.0	365.6	365.2	364.9	364.5
70°	331.5	329.3	327.3	325.8	325.0	324.2	323.4	322.6
72.5°	290.4	288.7	287.1	285.8	285.0	284.2	283.4	282.6
75°	231.2	230.1	229.1	228.4	228.2	227.9	227.6	227.4
77.5°	175.0	174.8	174.4	173.9	173.2	172.5	171.9	171.2
80°	139.4	138.9	138.4	137.9	137.7	137.4	137.2	136.9
82.5°	107.5	107.1	106.9	106.5	106.2	106.0	105.7	105.5
85°	61.9	61.9	61.9	61.7	61.5	61.2	61.0	60.7
87.5°	25.3	25.4	25.6	25.7	25.7	25.7	25.7	25.8
90°	12.1	12.7	13.4	13.9	14.1	14.3	14.6	14.7
92.5°	11.7	12.4	13.0	13.3	13.4	13.4	13.5	13.5
95°	12.1	12.7	13.4	13.8	13.9	14.0	14.1	14.2
97.5°	13.1	13.2	13.3	13.3	13.4	13.5	13.6	13.8
100°	17.9	16.0	14.2	13.3	13.4	13.5	13.6	13.8
102.5°	64.1	44.1	24.0	14.0	14.1	14.1	14.1	14.1
105°	155.2	156.2	157.1	155.7	151.8	147.8	143.9	140.0
107.5°	192.0	192.5	193.0	193.4	193.8	194.2	194.7	195.1
110°	217.1	217.2	217.5	217.7	218.1	218.3	218.7	219.0





TEST NUMBER: P332640-935

CATALOG NUMBER: S124DIP-S1020D590U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	241.3	241.3	241.2	241.3	241.8	242.2	242.6	243.0
115°	277.4	277.7	277.8	278.0	278.0	278.0	278.0	278.0
117.5°	313.8	313.8	313.7	313.7	313.7	313.7	313.6	313.6
120°	336.4	336.6	336.8	336.8	336.6	336.4	336.1	336.0
122.5°	358.6	358.7	358.9	358.8	358.6	358.3	358.2	357.9
125°	389.6	389.9	390.3	390.5	390.6	390.7	390.8	391.0
127.5°	420.5	420.4	420.3	420.3	420.2	420.1	420.0	419.9
130°	439.3	439.4	439.5	439.5	439.5	439.5	439.5	439.5
132.5°	457.8	457.9	458.0	458.0	457.9	457.8	457.7	457.6
135°	483.2	483.5	483.6	483.9	484.1	484.3	484.6	484.7
137.5°	507.6	507.9	508.1	508.2	508.2	508.1	508.0	507.9
140°	522.7	523.1	523.4	523.6	523.7	523.8	523.9	524.0
142.5°	536.7	536.9	537.2	537.4	537.4	537.4	537.4	537.4
145°	556.6	556.8	556.9	557.1	557.2	557.5	557.8	557.9
147.5°	574.2	574.3	574.4	574.5	574.6	574.7	574.8	574.9
150°	585.4	585.4	585.4	585.5	585.6	585.7	585.8	585.9
152.5°	595.2	595.4	595.6	595.6	595.6	595.5	595.4	595.4
155°	608.4	608.8	609.2	609.3	609.0	608.6	608.4	608.0
157.5°	619.7	620.4	620.9	620.9	620.4	619.7	619.2	618.6
160°	627.0	627.7	628.4	628.4	627.7	627.0	626.4	625.7
162.5°	632.9	633.5	634.2	634.2	633.4	632.7	632.0	631.2
165°	641.2	642.0	643.0	642.9	641.9	640.9	640.0	638.9
167.5°	647.3	648.2	649.2	649.1	648.1	647.0	645.8	644.8
170°	651.0	651.9	652.8	652.6	651.6	650.5	649.4	648.3
172.5°	653.4	654.3	655.1	655.0	653.8	652.6	651.4	650.2
175°	656.2	657.1	658.1	658.0	656.7	655.3	654.0	652.7
177.5°	657.3	658.0	658.7	658.5	657.5	656.4	655.3	654.3
180°	656.7	656.7	656.7	656.7	656.7	656.7	656.7	656.7

(END OF REPORT)