

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332649-935

Luminaire Tested: **S124DIP-S1020D810U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332649-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1020D810U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6599.2 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332649-935

CATALOG NUMBER: S124DIP-S1020D810U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332649-935

CATALOG NUMBER: S124DIP-S1020D810U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	99	95	91	88	93	89	85	82	77	74	72	66	64	62	56	55	53
2	91	83	77	72	84	78	72	67	67	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	44	41	38
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	32	29
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11994	11994	11994
5°	12030	11885	11972
10°	11954	11788	11847
15°	11810	11621	11651
20°	11618	11413	11424
25°	11399	11176	11144
30°	11130	10897	10797
35°	10852	10606	10465
40°	10564	10275	10086
45°	10261	9949	9758
50°	9928	9658	9359
55°	9568	9282	8981
60°	9206	8861	8591
65°	8800	8458	8118
70°	8344	7924	7615
75°	7648	7277	7093
80°	6811	6527	6365
85°	5956	5734	5622



TEST NUMBER: P332649-935

CATALOG NUMBER: S124DIP-S1020D810U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.9	2.1
10°-20°	394.2	6.0
20°-30°	580.2	8.8
30°-40°	674.5	10.2
40°-50°	674.5	10.2
50°-60°	590.0	8.9
60°-70°	438.2	6.6
70°-80°	248.9	3.8
80°-90°	74.4	1.1
90°-100°	30.8	0.5
100°-110°	196.3	3.0
110°-120°	375.5	5.7
120°-130°	476.7	7.2
130°-140°	510.0	7.7
140°-150°	476.9	7.2
150°-160°	384.6	5.8
160°-170°	248.0	3.8
170°-180°	85.5	1.3
0°-30°	1114.3	16.9
0°-40°	1788.8	27.1
0°-60°	3053.4	46.3
0°-90°	3815.0	57.8
90°-120°	602.6	9.1
90°-150°	2066.1	31.3
90°-180°	2784.0	42.2
0°-180°	6599.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1486	1486	1486	1486	1486	
5°	1484	1479	1467	1479	1477	141
15°	1413	1408	1390	1397	1394	398
25°	1280	1271	1255	1256	1251	588
35°	1101	1092	1076	1068	1062	688
45°	899	890	871	859	855	693
55°	680	675	660	646	638	609
65°	461	454	443	431	425	456
75°	245	239	233	229	227	261
85°	64	64	62	62	61	71
90°	2	9	15	19	20	5
95°	37	15	15	19	20	48
105°	203	207	210	214	192	212
115°	378	380	380	381	381	372
125°	532	534	533	535	536	475
135°	660	659	662	663	664	508
145°	761	763	763	763	765	475
155°	834	835	833	835	833	384
165°	880	877	876	881	876	249
175°	900	896	897	902	895	86
180°	900	900	900	900	900	



TEST NUMBER: P332649-935

CATALOG NUMBER: S124DIP-S1020D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1489.4	1488.8	1488.2	1487.5	1486.9	1485.4	1483.1	1480.7	1478.4	1476.1	1478.3
5°	1484.5	1483.4	1482.4	1481.3	1480.2	1478.3	1475.3	1472.4	1469.6	1466.6	1469.6
7.5°	1470.7	1469.6	1468.5	1467.5	1466.5	1464.3	1461.0	1457.8	1454.6	1451.4	1453.7
10°	1458.3	1457.2	1456.1	1455.1	1454.1	1451.8	1448.4	1444.9	1441.5	1438.0	1440.1
12.5°	1442.1	1441.1	1439.9	1438.9	1437.9	1435.5	1431.8	1428.2	1424.5	1420.9	1423.2
15°	1413.1	1412.0	1410.9	1409.9	1408.8	1406.3	1402.3	1398.4	1394.4	1390.4	1392.0
17.5°	1378.0	1376.7	1375.4	1374.1	1372.8	1370.2	1366.4	1362.7	1358.9	1355.2	1356.2
20°	1352.3	1351.0	1349.7	1348.3	1347.0	1344.4	1340.4	1336.4	1332.5	1328.5	1329.3
22.5°	1324.7	1322.9	1321.2	1319.5	1317.8	1314.8	1310.9	1306.9	1303.0	1299.0	1300.5
25°	1279.7	1277.9	1276.0	1274.1	1272.3	1269.5	1265.8	1262.1	1258.4	1254.7	1255.0
27.5°	1228.3	1226.4	1224.4	1222.5	1220.6	1218.0	1214.5	1211.1	1207.6	1204.2	1203.6
30°	1194.0	1191.9	1189.7	1187.7	1185.5	1182.8	1179.3	1175.9	1172.4	1169.0	1167.9
32.5°	1157.8	1155.9	1154.0	1152.1	1150.2	1147.4	1143.8	1140.1	1136.4	1132.8	1131.5
35°	1101.1	1099.3	1097.4	1095.6	1093.7	1091.0	1087.3	1083.6	1079.9	1076.2	1074.3
37.5°	1041.4	1039.7	1038.0	1036.3	1034.6	1031.8	1027.8	1023.8	1019.9	1015.9	1013.9
40°	1002.4	1000.2	998.1	996.0	993.9	990.8	986.9	982.9	979.0	975.0	972.3
42.5°	960.4	959.2	957.9	956.7	955.4	952.5	948.1	943.7	939.4	935.0	931.9
45°	898.8	896.9	895.1	893.2	891.4	888.3	884.1	879.9	875.6	871.4	868.5
47.5°	834.2	833.0	831.7	830.4	829.1	826.6	822.7	818.7	814.9	810.9	807.6
50°	790.5	789.4	788.3	787.3	786.2	783.9	780.2	776.4	772.7	769.0	765.3
52.5°	747.6	746.3	745.0	743.8	742.5	739.9	736.0	732.1	728.1	724.3	721.0
55°	679.8	678.9	678.1	677.3	676.6	674.3	670.6	666.9	663.2	659.5	656.3
57.5°	615.0	614.1	613.2	612.3	611.4	609.1	605.5	601.8	598.1	594.5	591.5
60°	570.2	568.9	567.6	566.3	564.9	562.6	559.1	555.7	552.2	548.8	546.4
62.5°	526.4	525.3	524.2	523.1	521.9	519.6	515.9	512.3	508.6	505.0	502.8
65°	460.7	459.3	458.1	456.8	455.4	453.4	450.7	448.2	445.5	442.8	440.2
67.5°	394.5	393.3	392.1	390.9	389.6	387.8	385.2	382.7	380.1	377.6	375.1
70°	353.5	351.7	349.8	348.0	346.1	344.1	342.1	339.9	337.9	335.7	333.6
72.5°	309.8	307.9	306.1	304.2	302.4	300.6	298.9	297.2	295.5	293.8	292.1
75°	245.2	243.9	242.5	241.3	240.0	238.6	237.3	236.0	234.6	233.3	232.3
77.5°	183.6	183.0	182.4	181.8	181.2	180.4	179.2	178.1	176.8	175.7	175.4
80°	146.5	145.6	144.8	144.0	143.3	142.6	142.1	141.5	141.0	140.4	139.9
82.5°	110.2	109.9	109.5	109.1	108.7	108.5	108.4	108.3	108.2	108.1	107.8
85°	64.3	64.3	64.3	64.3	64.3	64.1	63.5	62.9	62.4	61.9	61.9
87.5°	25.1	25.3	25.4	25.5	25.7	25.7	25.7	25.7	25.8	25.8	26.0
90°	2.0	3.7	5.3	7.0	8.6	10.0	11.2	12.4	13.6	14.8	15.7
92.5°	8.5	8.6	8.7	8.8	8.9	9.5	10.7	11.9	13.1	14.3	15.2
95°	37.0	31.9	26.9	21.8	16.7	14.2	14.4	14.6	14.6	14.8	15.7
97.5°	78.6	81.8	85.0	88.2	91.4	84.6	67.8	51.1	34.4	17.7	17.8
100°	110.4	113.1	115.8	118.5	121.1	112.2	91.5	70.9	50.3	29.6	27.0
102.5°	145.9	147.9	149.9	151.9	153.9	153.5	150.8	148.1	145.4	142.8	115.3
105°	202.6	203.5	204.4	205.3	206.2	207.1	207.8	208.5	209.3	210.0	211.4
107.5°	255.3	255.7	256.1	256.7	257.1	257.8	258.8	259.8	260.9	261.9	262.5
110°	290.8	291.3	291.7	292.1	292.7	293.3	294.2	295.1	296.0	296.9	297.2



TEST NUMBER: P332649-935

CATALOG NUMBER: S124DIP-S1020D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.3	326.1	326.9	327.7	328.6	329.2	329.6	329.9	330.4	330.8	330.8
115°	378.3	378.8	379.3	379.7	380.1	380.3	380.1	380.0	379.9	379.7	380.0
117.5°	426.1	426.7	427.3	427.9	428.5	429.0	429.3	429.6	430.0	430.3	430.2
120°	458.5	459.1	459.7	460.3	460.8	461.1	460.9	460.8	460.6	460.5	460.8
122.5°	488.6	489.0	489.3	489.7	490.1	490.3	490.5	490.8	490.9	491.2	491.4
125°	531.8	532.4	533.0	533.6	534.3	534.3	534.1	533.8	533.5	533.2	533.6
127.5°	572.7	572.9	573.1	573.3	573.3	573.8	574.5	575.1	575.8	576.5	576.4
130°	599.2	599.3	599.4	599.6	599.8	600.0	600.5	601.0	601.4	601.8	602.0
132.5°	623.4	623.6	624.0	624.2	624.5	624.9	625.4	626.0	626.5	627.2	627.3
135°	659.8	659.6	659.4	659.3	659.2	659.4	660.0	660.6	661.2	661.8	662.0
137.5°	691.9	692.0	692.1	692.1	692.2	692.5	693.2	693.9	694.5	695.2	695.5
140°	712.9	713.3	713.5	713.9	714.1	714.5	714.7	715.1	715.3	715.6	716.1
142.5°	731.8	732.3	732.9	733.4	733.9	734.3	734.4	734.7	734.9	735.0	735.4
145°	760.7	761.2	761.6	762.1	762.5	762.8	762.8	762.8	762.8	762.8	762.9
147.5°	783.8	784.6	785.4	786.3	787.1	787.5	787.3	787.1	787.0	786.9	787.0
150°	800.5	801.1	801.7	802.3	802.8	803.1	802.9	802.8	802.6	802.5	802.5
152.5°	814.4	814.9	815.4	815.9	816.4	816.5	816.2	816.0	815.6	815.4	815.6
155°	834.1	834.2	834.4	834.6	834.7	834.6	834.1	833.6	833.2	832.8	833.4
157.5°	850.7	850.6	850.5	850.4	850.3	850.0	849.5	849.0	848.5	848.0	848.8
160°	860.4	859.9	859.5	859.0	858.6	858.2	858.2	858.0	857.8	857.6	858.6
162.5°	869.0	868.4	867.8	867.3	866.7	866.3	866.2	866.1	865.9	865.7	866.7
165°	879.9	879.2	878.4	877.6	876.9	876.5	876.5	876.5	876.5	876.5	877.7
167.5°	888.5	887.7	886.9	886.1	885.4	884.9	884.8	884.8	884.7	884.6	885.9
170°	893.4	892.4	891.6	890.6	889.8	889.4	889.5	889.7	889.8	890.0	891.1
172.5°	896.6	895.7	894.8	893.9	893.0	892.6	892.8	892.9	893.0	893.2	894.4
175°	900.1	899.1	898.3	897.4	896.5	896.1	896.3	896.4	896.6	896.7	898.0
177.5°	901.7	900.9	900.0	899.1	898.4	898.0	898.3	898.5	898.8	899.0	899.9
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1



TEST NUMBER: P332649-935

CATALOG NUMBER: S124DIP-S1020D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7	1485.7
2.5°	1480.3	1482.5	1484.6	1485.6	1485.3	1485.1	1484.9	1484.7
5°	1472.4	1475.3	1478.3	1479.5	1478.9	1478.3	1477.8	1477.3
7.5°	1456.0	1458.4	1460.7	1461.7	1461.4	1461.0	1460.7	1460.4
10°	1442.3	1444.4	1446.5	1447.3	1446.7	1446.2	1445.7	1445.2
12.5°	1425.6	1427.9	1430.2	1431.0	1430.3	1429.5	1428.7	1428.1
15°	1393.6	1395.2	1396.8	1397.1	1396.4	1395.6	1394.8	1394.0
17.5°	1357.2	1358.2	1359.2	1359.4	1358.9	1358.4	1357.9	1357.3
20°	1330.1	1330.9	1331.7	1331.8	1331.3	1330.8	1330.2	1329.7
22.5°	1301.8	1303.3	1304.7	1304.9	1304.0	1303.0	1302.1	1301.1
25°	1255.3	1255.5	1255.8	1255.3	1254.3	1253.3	1252.2	1251.1
27.5°	1203.0	1202.3	1201.7	1200.8	1199.4	1198.1	1196.7	1195.4
30°	1166.9	1165.8	1164.8	1163.6	1162.3	1160.9	1159.6	1158.3
32.5°	1130.2	1129.0	1127.7	1126.4	1125.1	1123.8	1122.5	1121.1
35°	1072.5	1070.6	1068.8	1067.1	1065.8	1064.5	1063.2	1061.9
37.5°	1011.8	1009.9	1007.9	1006.0	1004.3	1002.5	1000.7	999.0
40°	969.7	967.0	964.4	962.4	961.0	959.8	958.5	957.1
42.5°	928.8	925.7	922.6	920.7	919.8	918.9	918.0	917.1
45°	865.6	862.6	859.7	857.9	857.1	856.4	855.5	854.7
47.5°	804.3	801.1	797.8	795.1	793.2	791.1	789.1	787.1
50°	761.6	757.9	754.2	751.6	749.9	748.4	746.8	745.2
52.5°	717.7	714.4	711.1	708.5	706.5	704.5	702.5	700.4
55°	653.2	650.0	646.8	644.5	642.8	641.3	639.6	638.1
57.5°	588.5	585.5	582.5	580.1	578.6	577.1	575.6	574.0
60°	544.1	541.7	539.2	537.4	536.1	534.8	533.5	532.1
62.5°	500.7	498.4	496.3	494.6	493.3	491.9	490.6	489.3
65°	437.6	434.9	432.2	430.2	429.0	427.7	426.3	425.0
67.5°	372.6	370.0	367.5	366.0	365.6	365.2	364.9	364.5
70°	331.5	329.3	327.3	325.8	325.0	324.2	323.4	322.6
72.5°	290.4	288.7	287.1	285.8	285.0	284.2	283.4	282.6
75°	231.2	230.1	229.1	228.4	228.2	227.9	227.6	227.4
77.5°	175.0	174.8	174.4	173.9	173.2	172.5	171.9	171.2
80°	139.4	138.9	138.4	137.9	137.7	137.4	137.2	136.9
82.5°	107.5	107.1	106.9	106.5	106.2	106.0	105.7	105.5
85°	61.9	61.9	61.9	61.7	61.5	61.2	61.0	60.7
87.5°	26.2	26.3	26.5	26.7	26.7	26.8	26.9	26.9
90°	16.6	17.5	18.4	19.0	19.3	19.6	19.9	20.2
92.5°	16.1	17.0	17.8	18.3	18.4	18.4	18.5	18.6
95°	16.6	17.5	18.4	18.9	19.1	19.2	19.4	19.5
97.5°	18.0	18.1	18.2	18.3	18.4	18.5	18.7	18.9
100°	24.5	22.0	19.5	18.3	18.4	18.5	18.7	18.9
102.5°	87.8	60.4	33.0	19.3	19.3	19.3	19.4	19.4
105°	212.8	214.0	215.4	213.4	208.0	202.6	197.3	191.8
107.5°	263.2	263.8	264.5	265.1	265.7	266.2	266.8	267.4
110°	297.5	297.8	298.1	298.4	298.9	299.4	299.8	300.2



TEST NUMBER: P332649-935

CATALOG NUMBER: S124DIP-S1020D810U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	330.7	330.6	330.5	330.8	331.4	332.0	332.5	333.1
115°	380.3	380.6	380.9	381.1	381.1	381.1	381.1	381.1
117.5°	430.2	430.2	430.1	430.0	430.0	429.9	429.8	429.8
120°	461.1	461.4	461.7	461.7	461.4	461.1	460.8	460.5
122.5°	491.5	491.7	491.9	491.8	491.5	491.2	490.9	490.6
125°	534.1	534.5	534.9	535.3	535.5	535.5	535.7	535.9
127.5°	576.4	576.3	576.2	576.1	575.9	575.8	575.8	575.6
130°	602.2	602.3	602.4	602.5	602.5	602.5	602.5	602.5
132.5°	627.5	627.6	627.8	627.8	627.7	627.5	627.4	627.3
135°	662.4	662.6	663.0	663.2	663.6	663.8	664.2	664.4
137.5°	695.8	696.1	696.5	696.5	696.5	696.4	696.3	696.2
140°	716.5	717.0	717.4	717.7	717.9	718.0	718.2	718.3
142.5°	735.6	736.0	736.3	736.5	736.5	736.6	736.6	736.6
145°	763.0	763.2	763.4	763.5	763.9	764.1	764.5	764.7
147.5°	787.1	787.2	787.3	787.5	787.6	787.7	787.9	788.1
150°	802.5	802.5	802.5	802.5	802.7	802.8	803.0	803.1
152.5°	815.9	816.1	816.3	816.4	816.3	816.2	816.1	816.1
155°	834.0	834.6	835.2	835.3	834.7	834.3	833.9	833.4
157.5°	849.5	850.3	851.1	851.1	850.3	849.5	848.8	848.0
160°	859.5	860.4	861.3	861.3	860.4	859.5	858.6	857.6
162.5°	867.5	868.4	869.4	869.3	868.2	867.2	866.3	865.2
165°	878.9	880.1	881.3	881.2	879.9	878.6	877.2	875.8
167.5°	887.3	888.6	889.8	889.8	888.3	886.7	885.3	883.8
170°	892.3	893.5	894.8	894.6	893.1	891.7	890.1	888.6
172.5°	895.6	896.8	898.0	897.8	896.2	894.6	892.9	891.3
175°	899.4	900.8	902.1	901.9	900.1	898.3	896.5	894.7
177.5°	901.0	901.9	902.8	902.6	901.1	899.7	898.3	896.8
180°	900.1	900.1	900.1	900.1	900.1	900.1	900.1	900.1

(END OF REPORT)