

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332713-935

Luminaire Tested: **S124DIP-S1195D1205U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332713-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1195D1205U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7995.4 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332713-935

CATALOG NUMBER: S124DIP-S1195D1205U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332713-935

CATALOG NUMBER: S124DIP-S1195D1205U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	94	91	87	92	88	84	81	76	73	71	64	62	61	54	52	51	46				
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28				
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24				
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21				
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13893	13726	13827
10°	13806	13615	13682
15°	13639	13422	13456
20°	13418	13181	13193
25°	13165	12908	12871
30°	12855	12585	12470
35°	12534	12249	12086
40°	12199	11866	11649
45°	11851	11490	11270
50°	11465	11154	10810
55°	11050	10719	10372
60°	10634	10233	9923
65°	10164	9769	9377
70°	9640	9151	8795
75°	8833	8406	8191
80°	7861	7541	7350
85°	6873	6623	6493



TEST NUMBER: P332713-935

CATALOG NUMBER: S124DIP-S1195D1205U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	2.0
10°-20°	455.3	5.7
20°-30°	670.1	8.4
30°-40°	779.0	9.7
40°-50°	779.1	9.7
50°-60°	681.5	8.5
60°-70°	506.1	6.3
70°-80°	287.5	3.6
80°-90°	86.8	1.1
90°-100°	85.3	1.1
100°-110°	252.7	3.2
110°-120°	428.9	5.4
120°-130°	565.6	7.1
130°-140°	635.2	7.9
140°-150°	624.2	7.8
150°-160°	525.0	6.6
160°-170°	349.3	4.4
170°-180°	122.3	1.5
0°-30°	1287.0	16.1
0°-40°	2066.0	25.8
0°-60°	3526.5	44.1
0°-90°	4406.9	55.1
90°-120°	767.0	9.6
90°-150°	2591.9	32.4
90°-180°	3588.0	44.9
0°-180°	7995.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1714	1708	1694	1708	1706	163
15°	1632	1626	1606	1613	1610	460
25°	1478	1468	1449	1450	1445	680
35°	1272	1262	1243	1233	1226	795
45°	1038	1028	1006	992	987	800
55°	785	780	762	746	737	703
65°	532	525	511	498	491	527
75°	283	276	270	264	263	301
85°	74	74	72	71	70	82
90°	3	14	22	28	30	8
95°	60	69	76	79	79	67
105°	233	234	238	241	244	247
115°	436	436	434	433	432	430
125°	635	635	634	632	630	566
135°	819	825	825	823	820	634
145°	995	999	1000	999	996	623
155°	1140	1140	1139	1143	1139	524
165°	1241	1238	1236	1242	1238	350
175°	1291	1287	1285	1292	1285	123
180°	1293	1293	1293	1293	1293	



TEST NUMBER: P332713-935

CATALOG NUMBER: S124DIP-S1195D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1720.2	1719.5	1718.7	1718.0	1717.3	1715.5	1712.9	1710.2	1707.5	1704.9	1707.3
5°	1714.4	1713.2	1712.0	1710.8	1709.6	1707.3	1703.9	1700.6	1697.2	1693.8	1697.2
7.5°	1698.5	1697.3	1696.1	1694.8	1693.6	1691.2	1687.4	1683.7	1680.0	1676.2	1679.0
10°	1684.2	1683.0	1681.8	1680.5	1679.3	1676.7	1672.8	1668.8	1664.8	1660.9	1663.3
12.5°	1665.5	1664.3	1663.0	1661.8	1660.6	1657.9	1653.7	1649.5	1645.3	1641.1	1643.7
15°	1631.9	1630.7	1629.5	1628.3	1627.0	1624.2	1619.5	1615.0	1610.4	1605.9	1607.7
17.5°	1591.6	1590.0	1588.5	1587.0	1585.4	1582.5	1578.1	1573.8	1569.5	1565.1	1566.3
20°	1561.9	1560.3	1558.8	1557.3	1555.7	1552.6	1548.1	1543.5	1539.0	1534.3	1535.2
22.5°	1529.9	1527.9	1526.0	1523.9	1521.9	1518.5	1514.0	1509.4	1504.9	1500.2	1501.9
25°	1478.0	1475.8	1473.7	1471.5	1469.4	1466.2	1461.9	1457.7	1453.4	1449.1	1449.4
27.5°	1418.6	1416.3	1414.2	1412.0	1409.8	1406.7	1402.7	1398.8	1394.8	1390.8	1390.1
30°	1379.0	1376.6	1374.1	1371.7	1369.2	1366.0	1362.0	1358.1	1354.1	1350.1	1348.9
32.5°	1337.2	1335.0	1332.8	1330.6	1328.4	1325.2	1320.9	1316.7	1312.5	1308.3	1306.8
35°	1271.8	1269.6	1267.5	1265.3	1263.2	1260.0	1255.7	1251.5	1247.2	1242.9	1240.7
37.5°	1202.7	1200.8	1198.9	1196.9	1194.9	1191.6	1187.1	1182.5	1177.8	1173.3	1171.0
40°	1157.6	1155.2	1152.7	1150.3	1147.9	1144.4	1139.8	1135.1	1130.6	1126.0	1122.9
42.5°	1109.2	1107.8	1106.3	1104.8	1103.4	1100.1	1095.0	1089.9	1084.9	1079.8	1076.2
45°	1038.0	1035.9	1033.7	1031.6	1029.5	1026.0	1021.1	1016.2	1011.2	1006.4	1003.1
47.5°	963.5	962.0	960.5	959.1	957.6	954.7	950.1	945.6	941.1	936.6	932.8
50°	912.9	911.7	910.4	909.2	908.0	905.3	901.0	896.7	892.4	888.1	883.9
52.5°	863.4	861.9	860.5	859.0	857.6	854.5	850.1	845.5	841.0	836.5	832.7
55°	785.1	784.1	783.3	782.3	781.4	778.8	774.5	770.3	765.9	761.6	758.0
57.5°	710.2	709.2	708.2	707.1	706.1	703.4	699.2	695.0	690.8	686.6	683.1
60°	658.6	657.0	655.5	654.0	652.5	649.7	645.8	641.8	637.7	633.8	631.0
62.5°	608.0	606.7	605.4	604.1	602.9	600.1	595.9	591.7	587.5	583.2	580.7
65°	532.1	530.5	529.0	527.4	526.0	523.7	520.6	517.5	514.5	511.4	508.4
67.5°	455.6	454.3	452.8	451.4	450.0	447.8	444.9	442.0	439.0	436.1	433.2
70°	408.4	406.2	404.1	401.9	399.8	397.5	395.0	392.6	390.1	387.7	385.3
72.5°	357.7	355.6	353.4	351.3	349.2	347.2	345.2	343.2	341.3	339.3	337.3
75°	283.2	281.7	280.2	278.6	277.1	275.6	274.1	272.5	271.0	269.5	268.3
77.5°	212.0	211.3	210.7	210.0	209.3	208.3	207.0	205.6	204.3	202.9	202.6
80°	169.1	168.2	167.3	166.3	165.5	164.7	164.1	163.4	162.8	162.2	161.6
82.5°	127.3	126.9	126.5	126.1	125.6	125.4	125.2	125.1	124.9	124.8	124.5
85°	74.2	74.2	74.2	74.2	74.2	74.0	73.4	72.8	72.1	71.5	71.5
87.5°	29.2	29.4	29.7	30.0	30.1	30.4	30.5	30.6	30.7	30.8	31.1
90°	3.0	5.4	7.9	10.3	12.7	14.9	16.7	18.4	20.2	22.0	23.3
92.5°	21.4	24.2	27.0	29.8	32.6	34.6	35.9	37.1	38.4	39.6	40.4
95°	60.0	62.0	64.1	66.0	68.0	69.8	71.4	72.9	74.5	76.0	76.7
97.5°	104.9	106.4	108.1	109.6	111.2	113.0	114.8	116.6	118.4	120.2	121.1
100°	140.1	140.9	141.8	142.7	143.6	145.1	147.1	149.0	151.0	153.1	153.5
102.5°	176.8	177.2	177.5	177.9	178.3	179.3	181.2	183.0	184.9	186.7	187.3
105°	233.1	233.3	233.5	233.8	233.9	234.5	235.4	236.3	237.2	238.1	238.8
107.5°	292.1	292.4	292.7	292.9	293.2	293.3	293.5	293.6	293.8	293.9	294.5
110°	332.1	332.5	332.9	333.5	333.9	334.0	333.8	333.6	333.3	333.1	332.7



TEST NUMBER: P332713-935

CATALOG NUMBER: S124DIP-S1195D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	373.7	373.8	373.9	374.0	374.1	373.9	373.5	373.2	372.7	372.3	372.2
115°	436.1	436.1	436.1	436.1	436.1	435.9	435.5	435.1	434.5	434.1	433.9
117.5°	495.0	495.2	495.3	495.5	495.7	495.6	495.2	495.0	494.6	494.4	493.6
120°	534.2	535.0	536.0	536.8	537.7	537.9	537.2	536.5	535.8	535.2	534.1
122.5°	575.0	575.3	575.7	576.0	576.4	576.4	576.1	575.8	575.5	575.1	574.5
125°	635.2	635.2	635.2	635.2	635.2	635.1	634.9	634.6	634.4	634.2	633.8
127.5°	689.8	690.5	691.1	691.8	692.5	692.7	692.2	691.9	691.6	691.2	690.8
130°	728.2	728.9	729.5	730.2	730.9	731.2	731.2	731.2	731.2	731.2	730.8
132.5°	767.4	767.9	768.4	768.9	769.4	769.6	769.4	769.2	769.0	768.9	768.4
135°	819.2	820.6	821.9	823.3	824.6	825.3	825.3	825.3	825.3	825.3	824.8
137.5°	875.6	876.3	876.9	877.5	878.1	878.7	879.0	879.3	879.7	880.0	879.5
140°	913.3	913.7	914.2	914.6	915.1	915.2	915.2	915.2	915.2	915.2	915.1
142.5°	947.7	948.1	948.6	949.0	949.5	949.6	949.4	949.3	949.1	948.9	948.8
145°	995.3	996.2	997.1	998.0	998.8	999.4	999.6	999.9	1000.1	1000.3	1000.1
147.5°	1042.5	1043.6	1044.7	1045.7	1046.8	1047.2	1047.1	1046.9	1046.7	1046.5	1046.4
150°	1071.3	1072.2	1073.2	1074.0	1074.9	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3
152.5°	1098.5	1099.1	1099.6	1100.1	1100.7	1101.0	1101.2	1101.4	1101.6	1101.7	1102.3
155°	1140.3	1140.3	1140.3	1140.3	1140.3	1140.2	1140.1	1139.8	1139.5	1139.4	1140.2
157.5°	1175.5	1175.2	1174.7	1174.4	1174.0	1173.7	1173.7	1173.6	1173.6	1173.5	1174.2
160°	1196.4	1196.2	1195.9	1195.7	1195.5	1195.2	1195.1	1194.8	1194.6	1194.4	1195.1
162.5°	1215.6	1215.0	1214.4	1213.8	1213.2	1212.9	1212.6	1212.5	1212.2	1211.9	1213.1
165°	1241.4	1240.7	1240.0	1239.4	1238.7	1238.1	1237.7	1237.3	1236.8	1236.4	1237.7
167.5°	1261.2	1260.2	1259.3	1258.4	1257.5	1257.0	1257.1	1257.1	1257.1	1257.1	1258.5
170°	1272.4	1271.3	1270.1	1269.0	1267.9	1267.5	1267.7	1267.9	1268.2	1268.4	1269.7
172.5°	1280.4	1279.4	1278.5	1277.6	1276.7	1276.2	1276.3	1276.3	1276.3	1276.4	1277.9
175°	1291.4	1290.3	1289.2	1288.1	1286.9	1286.2	1286.1	1285.8	1285.6	1285.4	1286.9
177.5°	1295.0	1294.1	1293.2	1292.4	1291.4	1291.0	1291.0	1291.0	1291.0	1291.0	1292.3
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4



TEST NUMBER: P332713-935

CATALOG NUMBER: S124DIP-S1195D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1709.7	1712.2	1714.6	1715.7	1715.5	1715.2	1714.9	1714.7
5°	1700.6	1703.9	1707.3	1708.7	1708.1	1707.4	1706.8	1706.2
7.5°	1681.6	1684.3	1687.0	1688.2	1687.8	1687.4	1687.0	1686.7
10°	1665.7	1668.2	1670.6	1671.5	1670.9	1670.3	1669.7	1669.0
12.5°	1646.4	1649.1	1651.8	1652.7	1651.8	1651.0	1650.1	1649.2
15°	1609.5	1611.4	1613.2	1613.6	1612.7	1611.8	1610.8	1610.0
17.5°	1567.5	1568.7	1569.8	1570.0	1569.4	1568.8	1568.2	1567.6
20°	1536.2	1537.1	1538.0	1538.2	1537.6	1537.0	1536.4	1535.7
22.5°	1503.6	1505.2	1506.8	1507.1	1506.1	1504.9	1503.8	1502.7
25°	1449.8	1450.0	1450.4	1449.8	1448.6	1447.4	1446.2	1445.0
27.5°	1389.3	1388.6	1387.8	1386.7	1385.2	1383.7	1382.2	1380.6
30°	1347.6	1346.4	1345.2	1343.8	1342.3	1340.8	1339.3	1337.7
32.5°	1305.4	1303.9	1302.4	1301.0	1299.4	1297.9	1296.4	1294.9
35°	1238.6	1236.5	1234.3	1232.5	1231.0	1229.4	1227.9	1226.4
37.5°	1168.6	1166.3	1164.0	1161.8	1159.9	1157.8	1155.8	1153.7
40°	1119.9	1116.8	1113.8	1111.5	1110.0	1108.5	1106.9	1105.4
42.5°	1072.7	1069.2	1065.7	1063.3	1062.3	1061.3	1060.2	1059.2
45°	999.7	996.3	993.0	990.8	989.9	988.9	988.1	987.1
47.5°	929.0	925.2	921.4	918.3	916.0	913.7	911.4	909.0
50°	879.6	875.3	871.1	868.0	866.2	864.4	862.5	860.7
52.5°	828.9	825.1	821.3	818.3	816.0	813.6	811.3	809.0
55°	754.3	750.7	747.0	744.2	742.4	740.6	738.7	736.9
57.5°	679.7	676.1	672.7	670.0	668.3	666.5	664.7	663.0
60°	628.3	625.6	622.8	620.7	619.1	617.6	616.1	614.6
62.5°	578.2	575.7	573.2	571.2	569.6	568.1	566.6	565.1
65°	505.3	502.3	499.2	497.0	495.4	493.9	492.3	490.9
67.5°	430.2	427.3	424.4	422.7	422.2	421.8	421.4	420.9
70°	382.8	380.4	377.9	376.3	375.3	374.4	373.5	372.6
72.5°	335.4	333.5	331.5	330.0	329.2	328.2	327.3	326.4
75°	267.0	265.8	264.6	263.8	263.6	263.2	262.9	262.6
77.5°	202.2	201.8	201.5	200.9	200.1	199.3	198.5	197.7
80°	161.0	160.4	159.8	159.4	159.0	158.7	158.4	158.1
82.5°	124.1	123.7	123.4	123.0	122.7	122.4	122.1	121.8
85°	71.5	71.5	71.5	71.4	71.0	70.7	70.4	70.1
87.5°	31.3	31.6	31.9	32.0	32.1	32.2	32.3	32.4
90°	24.7	26.0	27.4	28.2	28.7	29.1	29.5	30.0
92.5°	41.2	42.0	42.8	43.3	43.7	43.9	44.2	44.4
95°	77.3	78.0	78.7	79.0	79.0	79.0	79.0	79.0
97.5°	121.8	122.6	123.5	123.8	123.8	123.8	123.8	123.8
100°	153.9	154.4	154.8	155.1	155.1	155.1	155.1	155.1
102.5°	187.9	188.6	189.2	189.5	189.8	189.9	190.1	190.3
105°	239.4	240.0	240.7	241.4	242.1	242.7	243.4	244.1
107.5°	295.2	295.8	296.4	296.7	296.6	296.6	296.5	296.5
110°	332.2	331.7	331.3	331.4	332.1	332.8	333.5	334.1



TEST NUMBER: P332713-935

CATALOG NUMBER: S124DIP-S1195D1205U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	372.1	372.0	372.0	372.0	372.1	372.2	372.4	372.6
115°	433.7	433.4	433.3	433.0	432.8	432.6	432.4	432.1
117.5°	492.8	492.1	491.3	490.8	490.3	489.8	489.4	489.0
120°	533.0	531.8	530.7	530.4	530.8	531.2	531.8	532.2
122.5°	573.7	572.9	572.1	571.4	570.6	569.8	568.9	568.2
125°	633.3	632.8	632.4	632.0	631.5	631.1	630.6	630.2
127.5°	690.3	689.9	689.4	689.1	688.7	688.3	687.9	687.6
130°	730.3	729.9	729.4	728.8	727.9	727.0	726.1	725.2
132.5°	767.9	767.5	767.1	766.6	766.3	765.9	765.6	765.3
135°	824.4	823.9	823.5	822.9	822.3	821.6	820.9	820.3
137.5°	878.9	878.3	877.8	877.5	877.7	877.8	878.0	878.0
140°	914.8	914.6	914.4	914.2	914.0	913.7	913.5	913.3
142.5°	948.8	948.7	948.7	948.6	948.6	948.6	948.6	948.5
145°	999.9	999.6	999.4	998.9	998.3	997.6	997.0	996.3
147.5°	1046.2	1046.0	1045.8	1045.6	1045.4	1045.2	1044.9	1044.7
150°	1075.3	1075.3	1075.3	1075.2	1075.0	1074.8	1074.5	1074.4
152.5°	1102.8	1103.4	1103.9	1103.9	1103.3	1102.7	1102.1	1101.6
155°	1141.2	1142.0	1142.9	1142.9	1142.0	1141.2	1140.2	1139.4
157.5°	1174.9	1175.5	1176.2	1176.2	1175.4	1174.7	1173.9	1173.2
160°	1195.7	1196.4	1197.0	1196.8	1195.7	1194.6	1193.5	1192.4
162.5°	1214.4	1215.6	1216.8	1216.9	1215.7	1214.6	1213.5	1212.4
165°	1239.1	1240.4	1241.7	1241.9	1241.0	1240.2	1239.2	1238.4
167.5°	1259.8	1261.2	1262.5	1262.5	1261.1	1259.7	1258.4	1257.0
170°	1271.1	1272.4	1273.8	1273.6	1272.0	1270.5	1268.9	1267.4
172.5°	1279.4	1280.9	1282.5	1282.5	1280.8	1279.3	1277.7	1276.2
175°	1288.5	1290.0	1291.6	1291.6	1290.0	1288.5	1286.9	1285.4
177.5°	1293.5	1294.8	1296.0	1295.9	1294.4	1293.0	1291.6	1290.2
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4

(END OF REPORT)