

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332687-935

Luminaire Tested: **S124DIP-S1195D590U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332687-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1195D590U935-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6222.7 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332687-935

CATALOG NUMBER: S124DIP-S1195D590U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332687-935

CATALOG NUMBER: S124DIP-S1195D590U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	75	75	75	75	75	75	71		
1	102	98	94	90	97	93	89	86	83	81	78	75	72	71	66	65	63	63	63	63	63	63	63	60		
2	93	86	79	74	88	81	75	71	73	68	65	65	62	59	58	56	53	53	53	53	53	53	53	50		
3	85	75	68	61	80	71	65	59	64	59	54	58	54	50	52	48	45	45	45	45	45	45	45	42		
4	78	67	58	52	73	63	56	50	57	51	46	52	47	43	46	42	39	39	39	39	39	39	39	36		
5	72	60	51	45	68	57	49	43	51	45	40	46	41	37	42	38	34	34	34	34	34	34	34	31		
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30	30	30	30	30	30	30	28		
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	27	27	27	27	27	27	24		
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	27	24	24	24	24	24	24	24	22		
9	53	40	33	27	50	39	32	27	35	29	25	32	27	23	29	25	22	22	22	22	22	22	22	20		
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	20	20	20	20	20	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13852	13852	13852
5°	13893	13726	13827
10°	13806	13615	13682
15°	13639	13422	13456
20°	13418	13181	13193
25°	13165	12908	12871
30°	12855	12585	12470
35°	12534	12249	12086
40°	12199	11866	11649
45°	11851	11490	11270
50°	11465	11154	10810
55°	11050	10719	10372
60°	10634	10233	9923
65°	10164	9769	9377
70°	9640	9151	8795
75°	8833	8406	8191
80°	7861	7541	7350
85°	6873	6623	6493



TEST NUMBER: P332687-935

CATALOG NUMBER: S124DIP-S1195D590U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	2.6
10°-20°	455.3	7.3
20°-30°	670.1	10.8
30°-40°	779.0	12.5
40°-50°	779.1	12.5
50°-60°	681.5	11.0
60°-70°	506.1	8.1
70°-80°	287.5	4.6
80°-90°	84.4	1.4
90°-100°	180.6	2.9
100°-110°	375.8	6.0
110°-120°	336.6	5.4
120°-130°	283.1	4.6
130°-140°	236.1	3.8
140°-150°	180.4	2.9
150°-160°	126.8	2.0
160°-170°	74.6	1.2
170°-180°	24.3	0.4
0°-30°	1287.0	20.7
0°-40°	2066.0	33.2
0°-60°	3526.5	56.7
0°-90°	4404.4	70.8
90°-120°	893.0	14.4
90°-150°	1592.6	25.6
90°-180°	1818.0	29.2
0°-180°	6222.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1714	1708	1694	1708	1706	163
15°	1632	1626	1606	1613	1610	460
25°	1478	1468	1449	1450	1445	680
35°	1272	1262	1243	1233	1226	795
45°	1038	1028	1006	992	987	800
55°	785	780	762	746	737	703
65°	532	525	511	498	491	527
75°	283	276	270	264	263	301
85°	74	74	72	71	70	82
90°	0	4	9	10	10	5
95°	16	51	400	198	120	18
105°	57	83	322	694	691	61
115°	101	127	287	552	664	100
125°	141	168	286	470	529	125
135°	168	199	283	417	474	129
145°	193	221	282	352	386	121
155°	220	237	274	310	324	101
165°	239	247	263	278	282	68
175°	250	250	252	255	254	24
180°	250	250	250	250	250	



TEST NUMBER: P332687-935

CATALOG NUMBER: S124DIP-S1195D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1720.2	1719.5	1718.7	1718.0	1717.3	1715.5	1712.9	1710.2	1707.5	1704.9	1707.3
5°	1714.4	1713.2	1712.0	1710.8	1709.6	1707.3	1703.9	1700.6	1697.2	1693.8	1697.2
7.5°	1698.5	1697.3	1696.1	1694.8	1693.6	1691.2	1687.4	1683.7	1680.0	1676.2	1679.0
10°	1684.2	1683.0	1681.8	1680.5	1679.3	1676.7	1672.8	1668.8	1664.8	1660.9	1663.3
12.5°	1665.5	1664.3	1663.0	1661.8	1660.6	1657.9	1653.7	1649.5	1645.3	1641.1	1643.7
15°	1631.9	1630.7	1629.5	1628.3	1627.0	1624.2	1619.5	1615.0	1610.4	1605.9	1607.7
17.5°	1591.6	1590.0	1588.5	1587.0	1585.4	1582.5	1578.1	1573.8	1569.5	1565.1	1566.3
20°	1561.9	1560.3	1558.8	1557.3	1555.7	1552.6	1548.1	1543.5	1539.0	1534.3	1535.2
22.5°	1529.9	1527.9	1526.0	1523.9	1521.9	1518.5	1514.0	1509.4	1504.9	1500.2	1501.9
25°	1478.0	1475.8	1473.7	1471.5	1469.4	1466.2	1461.9	1457.7	1453.4	1449.1	1449.4
27.5°	1418.6	1416.3	1414.2	1412.0	1409.8	1406.7	1402.7	1398.8	1394.8	1390.8	1390.1
30°	1379.0	1376.6	1374.1	1371.7	1369.2	1366.0	1362.0	1358.1	1354.1	1350.1	1348.9
32.5°	1337.2	1335.0	1332.8	1330.6	1328.4	1325.2	1320.9	1316.7	1312.5	1308.3	1306.8
35°	1271.8	1269.6	1267.5	1265.3	1263.2	1260.0	1255.7	1251.5	1247.2	1242.9	1240.7
37.5°	1202.7	1200.8	1198.9	1196.9	1194.9	1191.6	1187.1	1182.5	1177.8	1173.3	1171.0
40°	1157.6	1155.2	1152.7	1150.3	1147.9	1144.4	1139.8	1135.1	1130.6	1126.0	1122.9
42.5°	1109.2	1107.8	1106.3	1104.8	1103.4	1100.1	1095.0	1089.9	1084.9	1079.8	1076.2
45°	1038.0	1035.9	1033.7	1031.6	1029.5	1026.0	1021.1	1016.2	1011.2	1006.4	1003.1
47.5°	963.5	962.0	960.5	959.1	957.6	954.7	950.1	945.6	941.1	936.6	932.8
50°	912.9	911.7	910.4	909.2	908.0	905.3	901.0	896.7	892.4	888.1	883.9
52.5°	863.4	861.9	860.5	859.0	857.6	854.5	850.1	845.5	841.0	836.5	832.7
55°	785.1	784.1	783.3	782.3	781.4	778.8	774.5	770.3	765.9	761.6	758.0
57.5°	710.2	709.2	708.2	707.1	706.1	703.4	699.2	695.0	690.8	686.6	683.1
60°	658.6	657.0	655.5	654.0	652.5	649.7	645.8	641.8	637.7	633.8	631.0
62.5°	608.0	606.7	605.4	604.1	602.9	600.1	595.9	591.7	587.5	583.2	580.7
65°	532.1	530.5	529.0	527.4	526.0	523.7	520.6	517.5	514.5	511.4	508.4
67.5°	455.6	454.3	452.8	451.4	450.0	447.8	444.9	442.0	439.0	436.1	433.2
70°	408.4	406.2	404.1	401.9	399.8	397.5	395.0	392.6	390.1	387.7	385.3
72.5°	357.7	355.6	353.4	351.3	349.2	347.2	345.2	343.2	341.3	339.3	337.3
75°	283.2	281.7	280.2	278.6	277.1	275.6	274.1	272.5	271.0	269.5	268.3
77.5°	212.0	211.3	210.7	210.0	209.3	208.3	207.0	205.6	204.3	202.9	202.6
80°	169.1	168.2	167.3	166.3	165.5	164.7	164.1	163.4	162.8	162.2	161.6
82.5°	127.3	126.9	126.5	126.1	125.6	125.4	125.2	125.1	124.9	124.8	124.5
85°	74.2	74.2	74.2	74.2	74.2	74.0	73.4	72.8	72.1	71.5	71.5
87.5°	28.7	28.7	28.7	28.6	28.4	28.2	28.5	28.2	28.2	28.2	28.1
90°	0.5	1.5	2.9	3.4	4.0	4.0	6.9	6.9	7.8	8.9	8.4
92.5°	5.6	8.2	12.7	18.8	25.9	36.2	61.1	99.2	136.4	155.8	129.8
95°	16.2	17.7	22.6	29.0	40.7	61.4	104.1	184.7	302.0	400.3	411.6
97.5°	29.1	29.1	33.3	39.2	49.3	66.6	99.5	166.0	282.8	421.6	517.1
100°	37.4	37.4	40.7	46.7	56.0	71.7	100.7	156.2	256.4	394.9	520.6
102.5°	45.2	46.0	49.0	54.5	63.5	78.4	104.6	153.4	238.7	361.5	491.1
105°	57.4	59.0	61.4	67.3	76.1	90.4	113.9	154.7	223.5	322.2	437.6
107.5°	71.0	72.0	74.5	80.8	89.2	103.2	124.8	162.0	220.8	300.2	394.4
110°	80.1	81.0	83.5	89.4	98.2	111.5	133.1	167.5	221.5	292.7	372.8



TEST NUMBER: P332687-935

CATALOG NUMBER: S124DIP-S1195D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	88.7	89.7	92.6	98.1	106.9	120.1	140.9	173.4	223.9	289.2	360.6
115°	101.2	102.6	106.1	111.0	120.4	133.6	153.3	182.7	228.4	287.3	349.2
117.5°	114.2	115.5	118.6	124.0	132.7	146.5	165.1	192.3	233.2	286.8	344.1
120°	122.8	123.8	127.2	132.6	140.9	154.7	173.4	198.9	236.8	286.8	341.4
122.5°	130.6	131.6	135.1	140.1	149.2	162.6	181.2	205.2	240.3	286.5	338.2
125°	140.9	142.9	145.9	151.3	160.6	174.4	192.0	214.6	245.6	285.9	333.0
127.5°	150.1	151.7	155.2	161.4	171.1	184.9	202.1	222.8	249.8	284.7	326.1
130°	155.2	157.1	161.1	168.5	177.8	192.0	208.7	227.9	253.0	284.4	321.7
132.5°	160.3	161.9	167.0	174.0	184.1	197.5	214.2	233.0	255.7	284.0	317.8
135°	167.5	169.4	174.4	182.7	193.0	205.8	222.0	239.7	259.8	283.4	311.9
137.5°	174.7	176.5	181.9	189.9	200.6	212.8	227.9	244.4	262.3	283.3	306.8
140°	179.8	181.2	186.7	195.0	205.3	217.1	231.9	247.5	264.2	282.9	304.0
142.5°	185.3	186.8	191.7	199.7	209.7	221.0	235.4	249.9	265.8	282.9	301.7
145°	193.0	194.5	199.4	206.3	215.6	226.4	239.2	252.4	266.7	281.9	297.6
147.5°	201.7	202.2	206.6	213.6	221.4	231.2	243.1	254.7	267.2	280.2	294.0
150°	207.2	207.8	211.7	217.6	225.0	234.3	245.1	255.9	267.2	279.0	291.3
152.5°	212.4	212.5	216.4	221.9	228.5	237.0	246.7	256.7	266.4	277.0	288.1
155°	219.6	220.1	223.0	227.9	233.3	240.6	249.0	257.4	265.2	274.1	283.4
157.5°	226.5	226.5	229.3	233.1	237.8	243.6	250.7	257.4	264.0	271.0	278.6
160°	230.8	230.8	232.8	236.3	240.1	245.6	251.5	257.4	262.8	268.6	275.1
162.5°	234.8	234.4	235.9	239.0	242.5	246.8	252.3	257.4	261.6	266.3	271.9
165°	239.2	239.2	240.1	242.6	245.1	248.1	252.4	256.4	259.3	262.8	266.7
167.5°	243.6	243.1	243.6	245.5	246.8	249.1	252.4	255.2	257.0	259.2	262.0
170°	245.6	245.1	245.6	247.0	248.1	249.5	251.9	254.4	255.4	256.8	258.8
172.5°	247.5	247.0	247.1	248.2	248.8	249.9	251.6	253.7	253.8	254.5	256.1
175°	249.5	249.0	249.0	249.5	250.0	250.0	251.0	252.4	251.9	251.9	253.0
177.5°	250.4	250.0	249.6	250.0	250.0	250.0	250.4	251.2	250.4	250.4	250.8
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332687-935

CATALOG NUMBER: S124DIP-S1195D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1709.7	1712.2	1714.6	1715.7	1715.5	1715.2	1714.9	1714.7
5°	1700.6	1703.9	1707.3	1708.7	1708.1	1707.4	1706.8	1706.2
7.5°	1681.6	1684.3	1687.0	1688.2	1687.8	1687.4	1687.0	1686.7
10°	1665.7	1668.2	1670.6	1671.5	1670.9	1670.3	1669.7	1669.0
12.5°	1646.4	1649.1	1651.8	1652.7	1651.8	1651.0	1650.1	1649.2
15°	1609.5	1611.4	1613.2	1613.6	1612.7	1611.8	1610.8	1610.0
17.5°	1567.5	1568.7	1569.8	1570.0	1569.4	1568.8	1568.2	1567.6
20°	1536.2	1537.1	1538.0	1538.2	1537.6	1537.0	1536.4	1535.7
22.5°	1503.6	1505.2	1506.8	1507.1	1506.1	1504.9	1503.8	1502.7
25°	1449.8	1450.0	1450.4	1449.8	1448.6	1447.4	1446.2	1445.0
27.5°	1389.3	1388.6	1387.8	1386.7	1385.2	1383.7	1382.2	1380.6
30°	1347.6	1346.4	1345.2	1343.8	1342.3	1340.8	1339.3	1337.7
32.5°	1305.4	1303.9	1302.4	1301.0	1299.4	1297.9	1296.4	1294.9
35°	1238.6	1236.5	1234.3	1232.5	1231.0	1229.4	1227.9	1226.4
37.5°	1168.6	1166.3	1164.0	1161.8	1159.9	1157.8	1155.8	1153.7
40°	1119.9	1116.8	1113.8	1111.5	1110.0	1108.5	1106.9	1105.4
42.5°	1072.7	1069.2	1065.7	1063.3	1062.3	1061.3	1060.2	1059.2
45°	999.7	996.3	993.0	990.8	989.9	988.9	988.1	987.1
47.5°	929.0	925.2	921.4	918.3	916.0	913.7	911.4	909.0
50°	879.6	875.3	871.1	868.0	866.2	864.4	862.5	860.7
52.5°	828.9	825.1	821.3	818.3	816.0	813.6	811.3	809.0
55°	754.3	750.7	747.0	744.2	742.4	740.6	738.7	736.9
57.5°	679.7	676.1	672.7	670.0	668.3	666.5	664.7	663.0
60°	628.3	625.6	622.8	620.7	619.1	617.6	616.1	614.6
62.5°	578.2	575.7	573.2	571.2	569.6	568.1	566.6	565.1
65°	505.3	502.3	499.2	497.0	495.4	493.9	492.3	490.9
67.5°	430.2	427.3	424.4	422.7	422.2	421.8	421.4	420.9
70°	382.8	380.4	377.9	376.3	375.3	374.4	373.5	372.6
72.5°	335.4	333.5	331.5	330.0	329.2	328.2	327.3	326.4
75°	267.0	265.8	264.6	263.8	263.6	263.2	262.9	262.6
77.5°	202.2	201.8	201.5	200.9	200.1	199.3	198.5	197.7
80°	161.0	160.4	159.8	159.4	159.0	158.7	158.4	158.1
82.5°	124.1	123.7	123.4	123.0	122.7	122.4	122.1	121.8
85°	71.5	71.5	71.5	71.4	71.0	70.7	70.4	70.1
87.5°	28.2	28.2	28.3	28.3	28.5	28.6	28.5	28.5
90°	8.9	9.3	9.8	9.8	10.3	10.8	10.3	10.3
92.5°	96.4	72.6	57.8	48.0	42.1	39.5	37.8	37.8
95°	363.9	287.8	222.0	174.4	150.3	135.1	126.2	119.9
97.5°	537.7	509.5	461.4	410.1	374.9	345.3	330.5	320.3
100°	592.4	602.2	578.1	541.7	499.0	469.1	454.3	450.4
102.5°	589.6	638.3	645.3	630.2	603.9	582.2	566.7	563.5
105°	550.1	635.1	683.7	703.9	704.8	700.9	694.0	691.0
107.5°	494.0	584.4	653.0	696.7	721.0	732.2	737.1	738.4
110°	460.2	545.2	616.4	670.5	705.3	725.9	734.8	739.2



TEST NUMBER: P332687-935

CATALOG NUMBER: S124DIP-S1195D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	435.5	510.6	577.9	631.9	671.5	696.5	708.9	716.0
115°	410.6	471.1	528.5	575.7	614.4	643.9	659.6	663.6
117.5°	398.4	448.4	493.6	533.6	566.7	591.4	607.3	610.4
120°	393.0	438.6	477.9	512.7	540.8	562.4	575.1	580.6
122.5°	388.2	432.3	468.0	498.6	522.3	540.8	551.6	557.0
125°	380.1	422.4	456.2	483.3	502.9	517.2	526.5	529.4
127.5°	370.3	410.7	444.5	470.1	489.9	502.6	510.4	513.3
130°	362.5	401.3	434.6	460.7	480.9	493.1	501.0	503.9
132.5°	354.2	390.6	423.3	449.3	469.1	482.9	490.3	493.4
135°	342.9	374.8	404.7	429.3	448.9	462.7	470.5	473.5
137.5°	332.5	359.6	384.8	407.0	425.3	438.9	445.4	448.9
140°	326.6	349.7	371.8	392.4	409.7	420.4	427.3	431.3
142.5°	321.2	341.5	360.4	378.3	393.5	403.6	409.7	412.3
145°	313.3	330.0	344.8	358.5	370.8	379.2	384.1	386.5
147.5°	306.9	320.2	332.0	342.9	351.9	359.0	362.7	363.7
150°	303.1	314.4	324.2	333.0	340.9	347.2	350.2	350.7
152.5°	298.7	308.4	317.5	324.8	331.4	336.7	338.4	338.9
155°	292.2	300.1	307.5	313.3	318.3	322.2	323.6	323.6
157.5°	285.2	291.9	298.0	302.7	306.5	309.4	310.3	310.3
160°	280.9	286.4	291.7	295.7	298.6	301.6	302.0	302.0
162.5°	276.6	281.2	285.4	289.0	291.2	294.1	294.6	294.2
165°	270.6	273.5	277.0	279.5	281.5	283.4	282.9	282.4
167.5°	264.8	267.1	269.8	271.3	272.3	273.5	273.5	273.1
170°	261.3	262.8	264.8	266.2	267.2	267.7	267.2	267.2
172.5°	258.1	259.2	260.5	261.5	262.1	262.6	262.1	261.3
175°	253.9	254.4	255.4	255.4	255.4	256.4	255.4	254.4
177.5°	251.2	251.6	251.6	251.9	251.6	251.9	251.2	250.4
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0

(END OF REPORT)