

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332676-927

Luminaire Tested: **S124DIP-S1195D365U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332676-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1195D365U927-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5210.1 lumens  
Efficiency: N/A  
Efficacy: 104.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332676-927

CATALOG NUMBER: S124DIP-S1195D365U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332676-927

CATALOG NUMBER: S124DIP-S1195D365U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58	55
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49	46
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	43	40
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	45	41	37	35
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33	30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26	24
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12745	12745	12745
5°	12783	12630	12721
10°	12703	12527	12588
15°	12549	12349	12380
20°	12345	12128	12138
25°	12113	11875	11843
30°	11828	11580	11473
35°	11532	11269	11121
40°	11225	10918	10718
45°	10904	10572	10369
50°	10550	10262	9946
55°	10166	9864	9543
60°	9783	9415	9131
65°	9352	8990	8627
70°	8868	8419	8091
75°	8125	7735	7536
80°	7234	6936	6760
85°	6326	6095	5974



TEST NUMBER: P332676-927

CATALOG NUMBER: S124DIP-S1195D365U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.7	2.9
10°-20°	418.9	8.0
20°-30°	616.5	11.8
30°-40°	716.7	13.8
40°-50°	716.8	13.8
50°-60°	627.0	12.0
60°-70°	465.6	8.9
70°-80°	264.5	5.1
80°-90°	77.4	1.5
90°-100°	12.8	0.2
100°-110°	81.6	1.6
110°-120°	156.1	3.0
120°-130°	198.2	3.8
130°-140°	212.1	4.1
140°-150°	198.3	3.8
150°-160°	159.9	3.1
160°-170°	103.2	2.0
170°-180°	35.6	0.7
0°-30°	1184.1	22.7
0°-40°	1900.8	36.5
0°-60°	3244.6	62.3
0°-90°	4052.2	77.8
90°-120°	250.6	4.8
90°-150°	859.2	16.5
90°-180°	1158.0	22.2
0°-180°	5210.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1579	1579	1579	1579	1579	
5°	1577	1572	1558	1571	1570	150
15°	1502	1496	1478	1484	1481	423
25°	1360	1350	1333	1334	1330	625
35°	1170	1161	1144	1135	1128	731
45°	955	946	926	913	908	736
55°	722	718	701	686	678	647
65°	490	483	471	458	452	485
75°	260	254	248	243	242	277
85°	68	68	66	66	64	75
90°	1	4	6	8	8	4
95°	15	6	6	8	8	20
105°	84	86	87	89	80	88
115°	157	158	158	158	158	155
125°	221	222	222	222	223	197
135°	274	274	275	276	276	211
145°	316	317	317	317	318	198
155°	347	347	346	347	347	160
165°	366	365	364	366	364	103
175°	374	373	373	375	372	36
180°	374	374	374	374	374	



TEST NUMBER: P332676-927

CATALOG NUMBER: S124DIP-S1195D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1582.7	1582.1	1581.4	1580.7	1580.0	1578.4	1576.0	1573.5	1571.1	1568.6	1570.8
5°	1577.4	1576.3	1575.2	1574.1	1573.0	1570.8	1567.7	1564.6	1561.5	1558.5	1561.5
7.5°	1562.7	1561.6	1560.5	1559.3	1558.2	1556.0	1552.5	1549.1	1545.7	1542.2	1544.8
10°	1549.6	1548.5	1547.4	1546.2	1545.1	1542.7	1539.1	1535.4	1531.8	1528.1	1530.3
12.5°	1532.4	1531.3	1530.1	1529.0	1527.9	1525.3	1521.5	1517.7	1513.8	1509.9	1512.4
15°	1501.5	1500.4	1499.3	1498.2	1497.0	1494.4	1490.1	1485.9	1481.7	1477.5	1479.2
17.5°	1464.3	1462.9	1461.5	1460.2	1458.7	1456.0	1452.0	1448.0	1444.1	1440.0	1441.1
20°	1437.0	1435.6	1434.2	1432.8	1431.4	1428.5	1424.3	1420.1	1415.9	1411.7	1412.5
22.5°	1407.6	1405.8	1404.0	1402.1	1400.3	1397.2	1393.0	1388.8	1384.6	1380.3	1381.9
25°	1359.9	1357.9	1355.9	1353.9	1351.9	1349.0	1345.0	1341.2	1337.2	1333.2	1333.6
27.5°	1305.2	1303.1	1301.2	1299.1	1297.1	1294.3	1290.6	1287.0	1283.3	1279.6	1279.0
30°	1268.8	1266.5	1264.2	1262.0	1259.8	1256.8	1253.2	1249.5	1245.9	1242.2	1241.1
32.5°	1230.3	1228.3	1226.3	1224.2	1222.2	1219.2	1215.4	1211.5	1207.6	1203.7	1202.4
35°	1170.1	1168.2	1166.2	1164.2	1162.2	1159.3	1155.3	1151.4	1147.5	1143.5	1141.5
37.5°	1106.6	1104.8	1103.0	1101.2	1099.4	1096.4	1092.2	1088.0	1083.7	1079.5	1077.4
40°	1065.1	1062.9	1060.6	1058.4	1056.1	1052.9	1048.7	1044.4	1040.2	1036.0	1033.2
42.5°	1020.6	1019.2	1017.9	1016.5	1015.2	1012.2	1007.5	1002.8	998.1	993.5	990.2
45°	955.1	953.1	951.1	949.1	947.2	944.0	939.4	934.9	930.4	926.0	922.9
47.5°	886.5	885.1	883.8	882.4	881.1	878.4	874.2	870.1	865.9	861.7	858.3
50°	840.0	838.8	837.7	836.5	835.4	832.9	828.9	825.1	821.1	817.1	813.3
52.5°	794.4	793.1	791.7	790.4	789.0	786.2	782.1	777.9	773.8	769.6	766.1
55°	722.3	721.4	720.6	719.8	718.9	716.5	712.6	708.7	704.7	700.8	697.4
57.5°	653.5	652.5	651.6	650.6	649.7	647.2	643.3	639.4	635.6	631.7	628.5
60°	605.9	604.5	603.1	601.7	600.3	597.8	594.1	590.5	586.8	583.1	580.6
62.5°	559.4	558.2	557.0	555.8	554.7	552.2	548.3	544.4	540.5	536.6	534.3
65°	489.6	488.1	486.7	485.3	483.9	481.8	479.0	476.2	473.4	470.6	467.8
67.5°	419.2	418.0	416.6	415.3	414.1	412.0	409.3	406.6	403.9	401.2	398.5
70°	375.7	373.8	371.8	369.8	367.8	365.8	363.5	361.2	358.9	356.7	354.5
72.5°	329.2	327.2	325.2	323.2	321.3	319.4	317.6	315.8	314.0	312.2	310.4
75°	260.5	259.2	257.8	256.4	254.9	253.6	252.2	250.7	249.4	248.0	246.8
77.5°	195.0	194.4	193.8	193.2	192.6	191.6	190.4	189.2	188.0	186.7	186.4
80°	155.6	154.7	153.9	153.0	152.3	151.5	151.0	150.4	149.8	149.2	148.7
82.5°	117.2	116.8	116.4	116.0	115.6	115.3	115.2	115.1	114.9	114.9	114.5
85°	68.3	68.3	68.3	68.3	68.3	68.0	67.5	66.9	66.3	65.8	65.8
87.5°	26.5	26.4	26.3	26.2	26.1	26.0	25.9	25.7	25.7	25.5	25.6
90°	0.9	1.5	2.2	2.9	3.6	4.2	4.7	5.1	5.6	6.2	6.5
92.5°	3.6	3.6	3.6	3.6	3.6	4.0	4.4	4.9	5.5	5.9	6.3
95°	15.4	13.3	11.2	9.0	7.0	5.9	5.9	6.0	6.1	6.2	6.5
97.5°	32.7	34.0	35.3	36.7	37.9	35.2	28.2	21.3	14.3	7.4	7.4
100°	45.9	47.1	48.2	49.3	50.4	46.7	38.1	29.5	20.9	12.4	11.2
102.5°	60.7	61.6	62.3	63.1	64.0	63.8	62.7	61.6	60.4	59.3	47.9
105°	84.3	84.6	85.0	85.4	85.8	86.1	86.4	86.7	87.1	87.4	87.9
107.5°	106.2	106.3	106.5	106.7	106.9	107.2	107.7	108.1	108.4	108.9	109.2
110°	121.0	121.1	121.3	121.5	121.7	122.0	122.3	122.7	123.1	123.5	123.6



TEST NUMBER: P332676-927

CATALOG NUMBER: S124DIP-S1195D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	135.3	135.6	135.9	136.3	136.7	136.9	137.0	137.2	137.4	137.6	137.5
115°	157.3	157.6	157.7	157.9	158.1	158.1	158.1	158.0	158.0	157.9	158.0
117.5°	177.2	177.4	177.7	178.0	178.2	178.4	178.6	178.7	178.8	179.0	179.0
120°	190.7	190.9	191.2	191.4	191.6	191.7	191.7	191.6	191.5	191.5	191.6
122.5°	203.2	203.4	203.5	203.7	203.8	203.9	204.0	204.1	204.1	204.3	204.3
125°	221.2	221.4	221.7	221.9	222.2	222.2	222.1	222.0	221.9	221.7	221.9
127.5°	238.2	238.3	238.3	238.4	238.4	238.6	238.9	239.2	239.5	239.8	239.7
130°	249.1	249.2	249.3	249.4	249.5	249.5	249.7	249.9	250.1	250.3	250.3
132.5°	259.3	259.4	259.4	259.6	259.7	259.8	260.1	260.3	260.5	260.8	260.9
135°	274.3	274.3	274.3	274.2	274.1	274.2	274.5	274.7	275.0	275.2	275.4
137.5°	287.7	287.8	287.8	287.8	287.9	288.0	288.3	288.5	288.8	289.1	289.2
140°	296.5	296.6	296.8	296.8	297.0	297.1	297.2	297.4	297.5	297.6	297.8
142.5°	304.4	304.5	304.8	305.0	305.2	305.4	305.5	305.5	305.6	305.7	305.8
145°	316.4	316.6	316.7	317.0	317.1	317.2	317.2	317.2	317.2	317.2	317.3
147.5°	325.9	326.3	326.6	327.0	327.3	327.5	327.4	327.3	327.3	327.3	327.3
150°	332.9	333.1	333.4	333.7	333.9	334.0	333.9	333.8	333.7	333.7	333.7
152.5°	338.7	338.9	339.1	339.3	339.5	339.5	339.5	339.3	339.2	339.1	339.2
155°	346.9	347.0	347.0	347.1	347.1	347.1	346.9	346.7	346.5	346.3	346.6
157.5°	353.8	353.7	353.7	353.6	353.6	353.5	353.3	353.1	352.8	352.7	353.0
160°	357.8	357.6	357.4	357.3	357.0	357.0	356.9	356.8	356.7	356.6	357.0
162.5°	361.4	361.2	360.9	360.7	360.4	360.3	360.2	360.1	360.1	360.0	360.4
165°	365.9	365.6	365.3	365.0	364.6	364.5	364.5	364.5	364.5	364.5	365.0
167.5°	369.5	369.2	368.8	368.5	368.2	368.0	368.0	368.0	367.9	367.9	368.4
170°	371.5	371.1	370.7	370.4	370.0	369.9	369.9	370.0	370.0	370.1	370.6
172.5°	372.9	372.5	372.1	371.8	371.4	371.2	371.3	371.4	371.4	371.5	371.9
175°	374.3	373.9	373.6	373.2	372.8	372.6	372.7	372.8	372.9	372.9	373.5
177.5°	375.0	374.6	374.3	373.9	373.6	373.4	373.6	373.7	373.8	373.8	374.3
180°	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3



TEST NUMBER: P332676-927

CATALOG NUMBER: S124DIP-S1195D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7	1578.7
2.5°	1573.0	1575.3	1577.6	1578.6	1578.3	1578.1	1577.9	1577.6
5°	1564.6	1567.7	1570.8	1572.1	1571.5	1571.0	1570.4	1569.8
7.5°	1547.2	1549.7	1552.1	1553.2	1552.9	1552.5	1552.2	1551.9
10°	1532.6	1534.9	1537.1	1537.9	1537.4	1536.8	1536.2	1535.6
12.5°	1514.8	1517.3	1519.8	1520.6	1519.8	1519.0	1518.2	1517.4
15°	1480.8	1482.6	1484.2	1484.6	1483.8	1483.0	1482.1	1481.3
17.5°	1442.2	1443.3	1444.3	1444.5	1444.0	1443.4	1442.9	1442.3
20°	1413.4	1414.2	1415.1	1415.2	1414.7	1414.1	1413.6	1412.9
22.5°	1383.4	1384.9	1386.4	1386.6	1385.7	1384.7	1383.6	1382.6
25°	1333.9	1334.1	1334.4	1334.0	1332.8	1331.7	1330.6	1329.5
27.5°	1278.3	1277.6	1276.9	1275.9	1274.5	1273.1	1271.7	1270.3
30°	1239.9	1238.8	1237.7	1236.4	1235.0	1233.7	1232.2	1230.8
32.5°	1201.0	1199.7	1198.3	1197.0	1195.6	1194.1	1192.8	1191.4
35°	1139.6	1137.7	1135.7	1134.0	1132.6	1131.2	1129.7	1128.4
37.5°	1075.2	1073.1	1071.0	1069.0	1067.1	1065.2	1063.4	1061.5
40°	1030.4	1027.5	1024.8	1022.6	1021.3	1019.9	1018.4	1017.0
42.5°	987.0	983.7	980.5	978.3	977.4	976.4	975.5	974.5
45°	919.8	916.7	913.6	911.6	910.8	909.9	909.1	908.2
47.5°	854.8	851.3	847.8	844.9	842.8	840.7	838.5	836.4
50°	809.3	805.3	801.5	798.6	796.9	795.3	793.5	791.9
52.5°	762.6	759.1	755.7	752.9	750.8	748.6	746.5	744.3
55°	694.0	690.7	687.3	684.8	683.1	681.4	679.7	678.0
57.5°	625.3	622.1	618.9	616.5	614.9	613.2	611.6	610.0
60°	578.1	575.6	573.1	571.1	569.7	568.2	566.9	565.5
62.5°	532.0	529.7	527.4	525.5	524.1	522.7	521.3	519.9
65°	464.9	462.2	459.3	457.2	455.8	454.4	453.0	451.6
67.5°	395.9	393.2	390.5	388.9	388.5	388.1	387.7	387.3
70°	352.2	350.0	347.7	346.2	345.3	344.5	343.6	342.8
72.5°	308.6	306.8	305.0	303.6	302.9	302.0	301.1	300.3
75°	245.7	244.5	243.4	242.7	242.5	242.2	241.9	241.6
77.5°	186.0	185.7	185.4	184.8	184.1	183.4	182.6	181.9
80°	148.1	147.6	147.0	146.6	146.3	146.0	145.8	145.4
82.5°	114.2	113.8	113.5	113.2	112.9	112.6	112.3	112.1
85°	65.8	65.8	65.8	65.7	65.4	65.0	64.8	64.5
87.5°	25.7	25.7	25.8	25.9	25.9	25.9	25.9	26.0
90°	6.9	7.3	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	6.7	7.1	7.4	7.6	7.7	7.7	7.7	7.8
95°	6.9	7.3	7.7	7.8	7.9	8.0	8.1	8.1
97.5°	7.4	7.5	7.5	7.6	7.7	7.7	7.8	7.8
100°	10.2	9.1	8.1	7.6	7.7	7.7	7.8	7.8
102.5°	36.5	25.1	13.7	8.0	8.0	8.0	8.1	8.1
105°	88.5	89.0	89.6	88.7	86.5	84.3	82.0	79.8
107.5°	109.5	109.7	110.0	110.3	110.5	110.7	111.0	111.2
110°	123.7	123.8	124.0	124.1	124.3	124.5	124.7	124.8





TEST NUMBER: P332676-927

CATALOG NUMBER: S124DIP-S1195D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	137.5	137.5	137.4	137.6	137.8	138.1	138.3	138.6
115°	158.1	158.3	158.4	158.4	158.4	158.4	158.4	158.4
117.5°	178.9	178.9	178.9	178.8	178.8	178.8	178.8	178.7
120°	191.7	191.9	192.0	192.0	191.9	191.7	191.6	191.5
122.5°	204.4	204.5	204.5	204.5	204.4	204.3	204.1	204.1
125°	222.1	222.3	222.4	222.6	222.7	222.8	222.8	222.8
127.5°	239.7	239.6	239.6	239.6	239.6	239.5	239.4	239.4
130°	250.4	250.5	250.6	250.6	250.6	250.6	250.6	250.6
132.5°	260.9	261.0	261.1	261.1	261.0	260.9	260.9	260.9
135°	275.4	275.6	275.7	275.8	275.9	276.1	276.2	276.3
137.5°	289.4	289.5	289.6	289.7	289.6	289.6	289.5	289.5
140°	297.9	298.2	298.3	298.5	298.6	298.6	298.7	298.7
142.5°	305.9	306.1	306.2	306.3	306.3	306.3	306.3	306.3
145°	317.3	317.4	317.4	317.5	317.7	317.8	317.9	318.1
147.5°	327.3	327.4	327.4	327.5	327.6	327.6	327.6	327.7
150°	333.7	333.7	333.7	333.7	333.8	333.9	333.9	334.0
152.5°	339.3	339.4	339.5	339.5	339.5	339.5	339.5	339.4
155°	346.8	347.1	347.3	347.4	347.1	347.0	346.8	346.6
157.5°	353.3	353.6	353.9	353.9	353.6	353.3	353.0	352.7
160°	357.4	357.8	358.1	358.1	357.8	357.4	357.0	356.6
162.5°	360.8	361.2	361.6	361.5	361.1	360.7	360.2	359.8
165°	365.5	366.0	366.5	366.5	365.9	365.4	364.8	364.2
167.5°	369.0	369.6	370.0	370.0	369.4	368.8	368.1	367.6
170°	371.1	371.6	372.1	372.0	371.5	370.8	370.2	369.6
172.5°	372.5	373.0	373.4	373.4	372.7	372.0	371.4	370.7
175°	374.1	374.6	375.2	375.1	374.3	373.6	372.8	372.1
177.5°	374.7	375.1	375.5	375.3	374.8	374.1	373.6	373.0
180°	374.3	374.3	374.3	374.3	374.3	374.3	374.3	374.3

(END OF REPORT)