

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332692-935

Luminaire Tested: **S124DIP-S1195D810U935-4F0-1E-UDD-D1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332692-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1195D810U935-4F0-1E-UDD-D1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6602.5 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332692-935

CATALOG NUMBER: S124DIP-S1195D810U935-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P332692-935

CATALOG NUMBER: S124DIP-S1195D810U935-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	99	94	89	85	92	87	83	80	76	73	70	65	63	61	55	53	52	47
2	89	81	74	69	83	76	70	65	65	61	57	56	53	50	47	45	43	38
3	81	71	63	57	75	66	59	53	57	52	47	49	45	41	42	38	36	32
4	74	62	54	48	69	58	51	45	51	45	40	44	39	35	37	33	30	27
5	68	56	47	41	63	52	44	38	45	39	34	39	34	30	33	29	26	23
6	62	50	41	35	58	47	39	33	41	34	30	35	30	26	30	26	23	20
7	58	45	36	31	54	42	35	29	37	31	26	32	27	23	27	23	20	18
8	54	41	33	27	50	38	31	26	34	27	23	29	24	21	25	21	18	16
9	50	37	29	24	46	35	28	23	31	25	21	27	22	19	23	19	16	14
10	47	34	27	22	43	32	25	21	28	23	19	25	20	17	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9912	9912	9912
5°	9942	9687	9715
10°	9882	9528	9521
15°	9793	9345	9294
20°	9660	9143	9072
25°	9509	8916	8829
30°	9346	8690	8579
35°	9161	8459	8360
40°	9014	8239	8132
45°	8795	8036	7936
50°	8610	7802	7728
55°	8420	7582	7486
60°	8121	7301	7265
65°	7793	6999	6992
70°	7397	6655	6676
75°	6845	6278	6390
80°	6233	5915	6107
85°	5446	5591	5943



TEST NUMBER: P332692-935

CATALOG NUMBER: S124DIP-S1195D810U935-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	1.8
10°-20°	333.1	5.0
20°-30°	503.7	7.6
30°-40°	609.4	9.2
40°-50°	644.3	9.8
50°-60°	606.4	9.2
60°-70°	503.1	7.6
70°-80°	353.4	5.4
80°-90°	202.4	3.1
90°-100°	176.0	2.7
100°-110°	257.9	3.9
110°-120°	347.6	5.3
120°-130°	413.8	6.3
130°-140°	441.8	6.7
140°-150°	422.9	6.4
150°-160°	353.3	5.4
160°-170°	235.0	3.6
170°-180°	82.3	1.2
0°-30°	953.1	14.4
0°-40°	1562.5	23.7
0°-60°	2813.1	42.6
0°-90°	3871.9	58.6
90°-120°	781.5	11.8
90°-150°	2060.0	31.2
90°-180°	2731.0	41.4
0°-180°	6602.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1228	1228	1228	1228	1228	
5°	1229	1225	1215	1226	1225	117
15°	1178	1179	1176	1187	1186	332
25°	1078	1086	1090	1105	1107	496
35°	943	959	973	992	997	590
45°	786	813	839	861	869	608
55°	616	646	686	712	722	549
65°	426	470	517	550	562	422
75°	236	288	345	382	396	252
85°	73	131	192	232	248	78
90°	24	87	151	193	207	17
95°	58	110	171	208	222	59
105°	169	199	251	286	300	180
115°	302	316	357	385	395	298
125°	433	434	465	489	497	386
135°	554	558	568	588	595	429
145°	671	672	673	680	684	420
155°	767	767	767	769	767	353
165°	835	833	832	836	833	235
175°	869	866	865	869	865	82
180°	870	870	870	870	870	



TEST NUMBER: P332692-935

CATALOG NUMBER: S124DIP-S1195D810U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8
2.5°	1232.2	1231.4	1230.7	1229.9	1229.2	1227.9	1225.9	1224.0	1222.0	1220.0	1221.8
5°	1229.1	1228.2	1227.3	1226.4	1225.5	1223.9	1221.8	1219.6	1217.5	1215.4	1217.8
7.5°	1218.7	1218.1	1217.5	1217.0	1216.5	1215.3	1213.6	1211.8	1210.0	1208.2	1211.0
10°	1209.9	1209.5	1209.3	1208.9	1208.7	1207.7	1206.2	1204.7	1203.2	1201.6	1204.4
12.5°	1197.7	1197.7	1197.7	1197.6	1197.6	1197.0	1195.9	1194.9	1193.9	1192.8	1195.3
15°	1178.3	1178.5	1178.9	1179.1	1179.5	1179.1	1178.3	1177.3	1176.4	1175.5	1178.3
17.5°	1151.6	1152.5	1153.4	1154.3	1155.2	1155.6	1155.5	1155.2	1155.0	1154.9	1157.7
20°	1132.9	1133.8	1134.7	1135.7	1136.5	1137.1	1137.5	1137.8	1138.1	1138.4	1141.4
22.5°	1112.0	1113.1	1114.3	1115.4	1116.6	1117.5	1118.0	1118.6	1119.1	1119.6	1122.7
25°	1077.9	1079.7	1081.6	1083.4	1085.2	1086.6	1087.5	1088.4	1089.3	1090.3	1093.6
27.5°	1039.9	1042.7	1045.3	1048.0	1050.7	1052.7	1054.1	1055.6	1057.0	1058.3	1061.4
30°	1014.6	1017.1	1019.5	1022.0	1024.4	1026.7	1028.8	1031.0	1033.1	1035.3	1038.6
32.5°	987.1	990.1	993.0	995.9	998.8	1001.5	1003.9	1006.3	1008.7	1011.1	1014.9
35°	943.1	946.8	950.5	954.2	957.8	961.1	964.2	967.2	970.3	973.4	977.7
37.5°	898.9	903.1	907.3	911.5	915.8	919.7	923.5	927.3	931.1	934.9	939.3
40°	870.3	874.3	878.2	882.2	886.1	890.3	894.6	898.9	903.1	907.4	912.0
42.5°	837.3	841.7	846.2	850.7	855.1	859.9	864.9	869.9	874.9	879.9	885.0
45°	786.4	792.2	798.1	803.8	809.6	815.5	821.2	827.1	832.8	838.7	843.9
47.5°	737.7	743.7	749.8	755.7	761.7	768.1	774.8	781.5	788.2	795.0	800.3
50°	702.6	709.3	716.0	722.7	729.4	736.2	742.9	749.6	756.3	763.0	769.1
52.5°	667.4	674.1	680.8	687.5	694.2	701.5	709.1	716.9	724.5	732.3	738.4
55°	616.0	622.3	628.8	635.2	641.6	649.4	658.6	667.7	676.9	686.0	692.2
57.5°	558.4	566.5	574.4	582.3	590.2	598.7	607.9	617.0	626.1	635.2	642.5
60°	521.1	529.0	536.9	544.9	552.8	561.9	572.0	582.0	592.1	602.2	609.2
62.5°	484.7	493.4	502.1	510.8	519.4	528.8	539.0	549.1	559.1	569.2	576.2
65°	426.2	436.0	445.7	455.6	465.3	475.4	485.8	496.2	506.5	516.9	524.6
67.5°	369.8	380.2	390.6	401.0	411.4	422.1	433.3	444.4	455.5	466.7	474.4
70°	331.3	341.7	352.1	362.5	372.9	383.9	395.5	407.1	418.7	430.3	438.6
72.5°	293.9	304.5	315.2	325.8	336.5	347.9	360.3	372.6	385.0	397.4	405.4
75°	236.5	247.8	259.1	270.4	281.7	293.8	306.6	319.4	332.3	345.1	353.6
77.5°	182.9	194.8	206.8	218.8	230.7	243.5	256.9	270.4	283.8	297.2	305.9
80°	149.9	162.0	174.3	186.5	198.7	211.5	225.0	238.5	251.9	265.4	274.5
82.5°	116.8	129.6	142.3	155.0	167.7	180.8	194.2	207.7	221.1	234.5	243.9
85°	72.8	85.7	98.5	111.3	124.2	137.5	151.2	165.0	178.7	192.5	201.6
87.5°	41.1	53.9	66.7	79.5	92.3	105.5	119.1	132.8	146.4	160.0	169.0
90°	24.0	37.9	51.7	65.6	79.5	93.6	107.9	122.3	136.6	150.9	160.7
92.5°	35.3	48.2	61.0	74.0	86.9	100.3	114.3	128.2	142.2	156.2	165.3
95°	58.3	69.7	81.1	92.6	104.0	116.5	130.0	143.6	157.2	170.7	179.4
97.5°	86.8	96.5	106.2	116.1	125.8	137.5	151.1	164.7	178.4	192.0	200.5
100°	109.3	117.9	126.5	135.0	143.5	154.5	167.7	181.0	194.2	207.5	216.0
102.5°	134.1	141.4	148.5	155.8	163.0	173.0	185.9	198.8	211.7	224.6	233.0
105°	169.2	175.5	181.8	188.0	194.2	203.4	215.2	227.1	239.0	251.0	259.0
107.5°	208.6	213.9	219.0	224.2	229.4	237.4	248.1	259.0	269.8	280.5	288.4
110°	234.5	239.0	243.7	248.2	252.8	260.4	270.9	281.5	292.0	302.6	309.3



TEST NUMBER: P332692-935

CATALOG NUMBER: S124DIP-S1195D810U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	261.4	265.2	269.1	272.9	276.8	283.7	293.6	303.5	313.5	323.4	330.1
115°	301.7	304.4	307.2	310.0	312.7	318.8	328.3	337.8	347.2	356.7	363.3
117.5°	341.0	342.8	344.6	346.4	348.1	353.4	362.3	371.3	380.1	389.0	394.9
120°	366.4	367.8	369.4	370.8	372.4	377.4	385.7	394.2	402.6	411.0	416.4
122.5°	393.8	394.2	394.6	395.0	395.5	399.8	407.9	416.1	424.2	432.4	438.0
125°	432.9	432.7	432.3	432.0	431.7	435.3	442.8	450.3	457.8	465.3	470.8
127.5°	469.4	469.6	469.7	469.8	470.0	472.9	478.5	484.1	489.7	495.3	500.6
130°	494.1	494.3	494.5	494.6	494.7	497.2	502.1	507.0	512.0	516.8	522.0
132.5°	520.6	520.6	520.6	520.6	520.6	522.5	526.3	530.1	533.9	537.7	542.7
135°	554.1	554.9	555.9	556.7	557.6	559.1	561.3	563.4	565.6	567.7	572.3
137.5°	592.0	592.1	592.2	592.4	592.5	593.1	594.4	595.7	597.0	598.2	602.4
140°	617.3	617.3	617.3	617.3	617.3	617.4	617.8	618.0	618.4	618.6	622.5
142.5°	639.4	639.6	639.8	640.1	640.3	640.2	640.0	639.6	639.4	639.0	642.6
145°	671.1	671.4	671.8	672.0	672.3	672.5	672.7	672.8	673.0	673.1	674.8
147.5°	702.9	703.4	703.7	704.1	704.6	704.7	704.6	704.5	704.3	704.2	704.3
150°	722.3	722.6	722.9	723.2	723.5	723.6	723.6	723.6	723.6	723.6	723.6
152.5°	739.5	739.8	740.1	740.4	740.7	740.9	741.0	741.1	741.2	741.4	741.8
155°	767.3	767.3	767.3	767.3	767.3	767.2	767.2	767.0	766.8	766.7	767.2
157.5°	791.1	790.7	790.5	790.2	790.0	789.8	789.8	789.8	789.7	789.7	790.1
160°	805.0	804.9	804.8	804.6	804.4	804.3	804.2	804.0	803.8	803.7	804.2
162.5°	817.9	817.6	817.2	816.8	816.4	816.1	816.0	815.9	815.7	815.5	816.4
165°	835.3	834.9	834.5	834.0	833.5	833.2	832.8	832.6	832.2	832.0	832.8
167.5°	848.7	848.0	847.4	846.8	846.2	845.8	845.8	845.9	845.9	845.9	846.9
170°	856.2	855.5	854.7	853.9	853.3	852.9	853.1	853.3	853.3	853.5	854.4
172.5°	861.6	861.0	860.3	859.7	859.1	858.8	858.8	858.8	858.8	858.9	859.9
175°	869.0	868.2	867.5	866.8	866.0	865.6	865.4	865.2	865.1	865.0	866.0
177.5°	871.4	870.8	870.2	869.6	869.0	868.7	868.7	868.7	868.7	868.7	869.5
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3



TEST NUMBER: P332692-935

CATALOG NUMBER: S124DIP-S1195D810U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8	1227.8
2.5°	1223.5	1225.2	1226.9	1227.6	1227.4	1227.1	1226.9	1226.7
5°	1220.3	1222.7	1225.1	1226.2	1225.9	1225.6	1225.3	1225.0
7.5°	1213.8	1216.5	1219.3	1220.5	1220.1	1219.9	1219.5	1219.3
10°	1207.1	1209.9	1212.6	1213.8	1213.6	1213.2	1212.9	1212.6
12.5°	1197.8	1200.3	1202.8	1204.1	1204.0	1203.9	1203.9	1203.9
15°	1181.0	1183.8	1186.5	1187.7	1187.4	1187.1	1186.8	1186.5
17.5°	1160.5	1163.3	1166.1	1167.4	1167.2	1166.9	1166.7	1166.4
20°	1144.5	1147.5	1150.6	1152.1	1152.1	1152.1	1152.1	1152.1
22.5°	1125.8	1128.9	1131.9	1133.7	1134.2	1134.6	1135.1	1135.7
25°	1097.0	1100.4	1103.7	1105.5	1105.9	1106.1	1106.5	1106.7
27.5°	1064.6	1067.7	1070.8	1072.5	1073.0	1073.3	1073.7	1074.0
30°	1042.0	1045.3	1048.7	1050.7	1051.3	1051.9	1052.5	1053.2
32.5°	1018.7	1022.6	1026.5	1028.7	1029.3	1029.9	1030.5	1031.1
35°	982.0	986.2	990.5	993.1	994.0	995.0	995.8	996.8
37.5°	943.6	947.9	952.3	954.9	955.9	956.8	957.9	958.8
40°	916.5	921.2	925.7	928.7	929.9	931.1	932.3	933.5
42.5°	890.0	895.1	900.2	903.2	904.2	905.2	906.1	907.1
45°	849.0	854.3	859.5	862.8	864.4	865.8	867.4	868.9
47.5°	805.7	811.1	816.5	820.0	821.9	823.7	825.5	827.4
50°	775.2	781.4	787.5	791.4	793.3	795.1	796.9	798.7
52.5°	744.5	750.6	756.6	760.7	762.5	764.3	766.1	768.0
55°	698.3	704.4	710.5	714.5	716.3	718.2	720.0	721.8
57.5°	649.7	657.0	664.3	668.7	670.5	672.2	673.9	675.6
60°	616.2	623.3	630.3	635.0	637.5	639.9	642.4	644.8
62.5°	583.2	590.3	597.3	602.0	604.5	606.9	609.3	611.8
65°	532.2	539.8	547.5	552.5	555.0	557.4	559.9	562.3
67.5°	482.2	489.9	497.7	502.7	505.1	507.5	509.9	512.3
70°	446.9	455.0	463.3	468.6	470.6	472.8	474.9	477.1
72.5°	413.4	421.4	429.4	434.5	437.0	439.3	441.7	444.1
75°	362.2	370.7	379.3	385.0	387.7	390.5	393.2	396.0
77.5°	314.6	323.3	331.9	337.8	340.7	343.6	346.6	349.5
80°	283.7	292.8	302.0	307.8	310.2	312.7	315.1	317.6
82.5°	253.4	262.8	272.2	278.3	280.9	283.6	286.3	289.0
85°	210.8	220.0	229.1	235.2	238.3	241.3	244.4	247.5
87.5°	178.1	187.1	196.1	202.0	204.7	207.5	210.3	213.0
90°	170.4	180.2	189.9	196.2	199.0	201.6	204.4	207.2
92.5°	174.4	183.7	192.8	198.6	201.3	203.9	206.6	209.1
95°	188.1	196.8	205.5	211.3	214.0	216.8	219.6	222.3
97.5°	209.1	217.7	226.2	231.8	234.4	237.0	239.6	242.3
100°	224.5	233.2	241.7	247.0	249.2	251.3	253.4	255.5
102.5°	241.4	249.9	258.3	263.7	266.2	268.7	271.3	273.8
105°	267.1	275.2	283.3	288.8	291.7	294.5	297.5	300.3
107.5°	296.4	304.4	312.3	317.3	319.5	321.7	323.8	326.0
110°	316.0	322.7	329.4	334.2	337.2	340.0	342.9	345.8



TEST NUMBER: P332692-935

CATALOG NUMBER: S124DIP-S1195D810U935-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	336.8	343.5	350.3	354.9	357.5	360.0	362.5	365.1
115°	369.9	376.4	383.1	387.3	389.3	391.3	393.3	395.3
117.5°	400.7	406.6	412.4	416.4	418.5	420.7	422.8	425.0
120°	421.7	427.1	432.5	436.5	439.2	442.0	444.7	447.5
122.5°	443.6	449.2	454.8	458.5	460.1	461.8	463.5	465.1
125°	476.3	481.7	487.2	490.8	492.3	493.9	495.4	497.0
127.5°	505.8	511.0	516.2	519.7	521.5	523.4	525.2	527.0
130°	527.2	532.4	537.6	540.8	542.1	543.3	544.5	545.8
132.5°	547.6	552.6	557.5	560.8	562.4	564.0	565.6	567.1
135°	576.9	581.4	586.1	589.0	590.4	591.9	593.2	594.6
137.5°	606.4	610.4	614.6	617.4	619.0	620.6	622.2	623.9
140°	626.3	630.1	634.0	636.5	637.9	639.3	640.7	642.0
142.5°	646.0	649.5	652.9	655.2	656.5	657.7	659.0	660.2
145°	676.5	678.2	679.8	681.1	681.8	682.6	683.4	684.2
147.5°	704.5	704.6	704.7	705.2	706.0	706.9	707.7	708.5
150°	723.6	723.6	723.6	723.5	723.4	723.2	723.1	722.9
152.5°	742.1	742.4	742.8	742.8	742.4	742.0	741.7	741.2
155°	767.8	768.4	769.0	769.0	768.4	767.8	767.2	766.7
157.5°	790.6	791.1	791.5	791.4	791.0	790.5	790.0	789.5
160°	804.6	805.0	805.5	805.4	804.6	803.8	803.1	802.4
162.5°	817.2	817.9	818.8	818.8	818.0	817.3	816.6	815.8
165°	833.8	834.7	835.6	835.7	835.1	834.5	833.9	833.4
167.5°	847.7	848.7	849.5	849.5	848.6	847.7	846.8	845.8
170°	855.3	856.2	857.1	857.0	856.0	855.0	853.9	852.8
172.5°	860.9	861.9	863.0	863.0	861.9	860.8	859.8	858.8
175°	867.0	868.1	869.2	869.2	868.1	867.0	866.0	865.0
177.5°	870.4	871.2	872.1	872.0	871.1	870.1	869.2	868.1
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3

(END OF REPORT)