

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332534-935

Luminaire Tested: **S124DIP-S350D1205U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332534-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S350D1205U935-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5011.7 lumens  
Efficiency: N/A  
Efficacy: 118.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332534-935

CATALOG NUMBER: S124DIP-S350D1205U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332534-935

CATALOG NUMBER: S124DIP-S350D1205U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	84	81	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	71	66	75	69	64	60	54	50	47	39	37	35	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	15
6	59	47	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	16	13	12
8	50	39	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4106	4106	4106
5°	4118	4068	4099
10°	4092	4036	4055
15°	4043	3978	3989
20°	3978	3907	3911
25°	3902	3827	3815
30°	3811	3731	3697
35°	3714	3631	3582
40°	3616	3518	3453
45°	3513	3406	3342
50°	3399	3307	3204
55°	3275	3178	3074
60°	3152	3034	2942
65°	3012	2896	2779
70°	2858	2712	2608
75°	2617	2492	2427
80°	2329	2236	2176
85°	2038	1964	1927



TEST NUMBER: P332534-935

CATALOG NUMBER: S124DIP-S350D1205U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.9	1.0
10°-20°	135.0	2.7
20°-30°	198.6	4.0
30°-40°	230.9	4.6
40°-50°	230.9	4.6
50°-60°	202.0	4.0
60°-70°	150.0	3.0
70°-80°	85.2	1.7
80°-90°	27.4	0.5
90°-100°	367.8	7.3
100°-110°	765.5	15.3
110°-120°	685.7	13.7
120°-130°	576.8	11.5
130°-140°	480.9	9.6
140°-150°	367.4	7.3
150°-160°	258.2	5.2
160°-170°	151.9	3.0
170°-180°	49.4	1.0
0°-30°	381.5	7.6
0°-40°	612.4	12.2
0°-60°	1045.3	20.9
0°-90°	1308.0	26.1
90°-120°	1819.0	36.3
90°-150°	3244.1	64.7
90°-180°	3704.0	73.9
0°-180°	5011.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	509	509	509	509	509	
5°	508	506	502	506	506	48
15°	484	482	476	478	477	136
25°	438	435	430	430	428	201
35°	377	374	368	366	364	236
45°	308	305	298	294	293	237
55°	233	231	226	221	218	208
65°	158	156	152	148	146	156
75°	84	82	80	78	78	89
85°	22	22	21	21	21	24
90°	1	8	18	20	21	3
95°	33	104	815	404	244	37
105°	117	170	656	1413	1408	125
115°	206	259	585	1125	1352	204
125°	287	341	582	957	1078	256
135°	341	406	577	849	964	264
145°	393	450	574	716	787	247
155°	447	483	558	632	659	206
165°	487	502	535	567	575	138
175°	508	509	513	520	518	48
180°	509	509	509	509	509	



TEST NUMBER: P332534-935

CATALOG NUMBER: S124DIP-S350D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6
2.5°	509.9	509.7	509.5	509.3	509.0	508.5	507.7	507.0	506.2	505.3	506.1
5°	508.2	507.8	507.5	507.1	506.8	506.1	505.1	504.1	503.1	502.0	503.1
7.5°	503.5	503.1	502.7	502.4	502.0	501.3	500.2	499.1	498.0	496.9	497.7
10°	499.2	498.9	498.5	498.2	497.8	497.1	495.8	494.6	493.5	492.3	493.0
12.5°	493.7	493.4	493.0	492.6	492.2	491.5	490.2	489.0	487.7	486.5	487.2
15°	483.7	483.4	483.0	482.7	482.3	481.5	480.1	478.7	477.3	476.0	476.6
17.5°	471.7	471.3	470.9	470.5	469.9	469.1	467.8	466.5	465.2	463.9	464.3
20°	463.0	462.5	462.1	461.6	461.2	460.3	458.9	457.5	456.2	454.8	455.1
22.5°	453.5	452.9	452.3	451.7	451.1	450.1	448.8	447.5	446.1	444.7	445.2
25°	438.1	437.5	436.9	436.2	435.6	434.6	433.3	432.0	430.8	429.6	429.6
27.5°	420.5	419.8	419.2	418.5	417.9	417.0	415.8	414.7	413.5	412.2	412.1
30°	408.8	408.0	407.3	406.6	405.9	404.9	403.7	402.5	401.4	400.2	399.8
32.5°	396.4	395.7	395.0	394.4	393.7	392.8	391.6	390.3	389.1	387.8	387.4
35°	376.9	376.3	375.7	375.1	374.4	373.5	372.2	370.9	369.7	368.4	367.8
37.5°	356.5	355.9	355.3	354.8	354.2	353.3	351.9	350.5	349.1	347.8	347.1
40°	343.1	342.4	341.7	341.0	340.3	339.2	337.9	336.5	335.1	333.8	332.9
42.5°	328.8	328.4	328.0	327.5	327.1	326.1	324.6	323.0	321.6	320.1	319.0
45°	307.7	307.0	306.4	305.8	305.1	304.1	302.6	301.2	299.8	298.3	297.3
47.5°	285.6	285.2	284.7	284.3	283.9	283.0	281.6	280.3	279.0	277.6	276.5
50°	270.6	270.3	269.9	269.5	269.1	268.4	267.1	265.8	264.5	263.3	262.0
52.5°	256.0	255.5	255.0	254.6	254.2	253.3	251.9	250.6	249.3	248.0	246.8
55°	232.7	232.5	232.1	231.9	231.6	230.8	229.5	228.3	227.0	225.8	224.7
57.5°	210.5	210.3	209.9	209.7	209.3	208.5	207.2	206.0	204.7	203.5	202.5
60°	195.2	194.8	194.3	193.8	193.4	192.6	191.4	190.2	189.1	187.9	187.1
62.5°	180.2	179.9	179.4	179.1	178.7	177.9	176.6	175.4	174.1	172.9	172.1
65°	157.7	157.3	156.8	156.4	155.9	155.2	154.3	153.4	152.5	151.6	150.7
67.5°	135.1	134.7	134.2	133.8	133.4	132.8	131.9	131.0	130.2	129.2	128.4
70°	121.1	120.4	119.8	119.2	118.5	117.8	117.1	116.4	115.6	114.9	114.2
72.5°	106.1	105.4	104.8	104.2	103.5	102.9	102.3	101.8	101.2	100.6	100.0
75°	83.9	83.5	83.1	82.6	82.1	81.7	81.3	80.8	80.3	79.9	79.6
77.5°	62.9	62.7	62.4	62.3	62.1	61.7	61.4	61.0	60.5	60.2	60.0
80°	50.1	49.9	49.6	49.3	49.1	48.8	48.6	48.5	48.3	48.1	47.9
82.5°	37.7	37.6	37.5	37.4	37.2	37.1	37.1	37.1	37.0	37.0	36.9
85°	22.0	22.0	22.0	22.0	22.0	22.0	21.7	21.5	21.4	21.2	21.2
87.5°	8.7	9.0	9.6	9.6	9.8	9.7	10.8	10.8	11.1	11.5	11.2
90°	1.0	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0
92.5°	11.4	16.6	26.0	38.2	52.9	73.6	124.5	202.1	277.8	317.4	264.3
95°	33.0	36.0	46.1	59.1	83.0	125.1	212.1	376.2	615.3	815.4	838.4
97.5°	59.2	59.2	67.8	79.8	100.5	135.7	202.7	338.2	575.8	858.8	1053.3
100°	76.0	76.0	83.0	95.1	114.1	146.1	205.1	318.1	522.3	804.3	1060.5
102.5°	92.0	93.7	99.9	111.1	129.2	159.7	213.1	312.5	486.2	736.3	1000.5
105°	117.1	120.0	125.1	137.1	155.1	184.1	232.1	315.1	455.2	656.3	891.4
107.5°	144.6	146.6	151.7	164.5	181.7	210.3	254.3	329.9	449.6	611.5	803.4
110°	163.1	165.1	170.0	182.1	200.1	227.1	271.1	341.1	451.3	596.3	759.4



TEST NUMBER: P332534-935

CATALOG NUMBER: S124DIP-S350D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	180.7	182.7	188.5	199.7	217.7	244.7	287.1	353.2	456.0	589.1	734.5
115°	206.1	209.1	216.1	226.1	245.1	272.2	312.1	372.2	465.2	585.3	711.4
117.5°	232.5	235.3	241.5	252.5	270.4	298.3	336.4	391.6	475.0	584.3	700.9
120°	250.1	252.1	259.2	270.1	287.1	315.1	353.2	405.2	482.2	584.3	695.3
122.5°	266.1	268.1	275.2	285.3	303.9	331.1	369.2	418.0	489.5	583.5	689.0
125°	287.1	291.1	297.1	308.2	327.2	355.2	391.2	437.2	500.2	582.3	678.3
127.5°	305.7	308.9	316.2	328.7	348.5	376.8	411.6	453.8	508.9	580.1	664.1
130°	316.2	320.1	328.1	343.2	362.1	391.2	425.2	464.3	515.2	579.3	655.3
132.5°	326.6	329.8	340.2	354.4	375.0	402.4	436.4	474.7	520.8	578.5	647.3
135°	341.1	345.2	355.2	372.2	393.2	419.2	452.2	488.3	529.3	577.3	635.3
137.5°	355.8	359.6	370.6	386.8	408.6	433.4	464.3	497.8	534.3	577.0	624.9
140°	366.2	369.2	380.2	397.2	418.2	442.2	472.3	504.2	538.3	576.3	619.3
142.5°	377.4	380.4	390.5	406.8	427.0	450.2	479.4	509.0	541.5	576.3	614.5
145°	393.2	396.2	406.2	420.2	439.2	461.2	487.2	514.3	543.3	574.3	606.3
147.5°	411.0	412.0	420.8	435.2	451.0	470.8	495.2	518.8	544.2	570.7	598.9
150°	422.2	423.2	431.2	443.2	458.2	477.3	499.2	521.2	544.2	568.3	593.3
152.5°	432.6	432.8	440.8	452.0	465.5	482.8	502.5	522.9	542.7	564.3	586.9
155°	447.2	448.2	454.2	464.3	475.3	490.3	507.2	524.3	540.3	558.3	577.3
157.5°	461.4	461.4	467.0	474.8	484.4	496.3	510.7	524.3	537.7	552.1	567.5
160°	470.2	470.2	474.2	481.2	489.2	500.2	512.2	524.3	535.3	547.3	560.3
162.5°	478.2	477.4	480.6	486.8	494.0	502.7	513.8	524.3	532.9	542.4	553.9
165°	487.2	487.2	489.2	494.2	499.2	505.2	514.3	522.3	528.2	535.3	543.3
167.5°	496.3	495.2	496.3	500.1	502.8	507.5	514.0	519.9	523.5	528.1	533.6
170°	500.2	499.2	500.2	503.3	505.2	508.2	513.2	518.2	520.2	523.2	527.3
172.5°	504.2	503.3	503.4	505.7	506.9	509.0	512.5	516.7	517.0	518.4	521.7
175°	508.2	507.2	507.2	508.2	509.3	509.3	511.3	514.3	513.2	513.2	515.2
177.5°	510.1	509.3	508.4	509.3	509.3	509.3	510.1	511.6	510.1	510.1	510.8
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3



TEST NUMBER: P332534-935

CATALOG NUMBER: S124DIP-S350D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6
2.5°	506.8	507.6	508.2	508.6	508.5	508.4	508.3	508.2
5°	504.1	505.1	506.1	506.4	506.3	506.1	505.9	505.8
7.5°	498.4	499.3	500.1	500.4	500.3	500.2	500.1	500.0
10°	493.8	494.5	495.2	495.5	495.3	495.1	494.9	494.7
12.5°	488.0	488.8	489.7	489.9	489.7	489.4	489.1	488.9
15°	477.1	477.6	478.2	478.3	478.0	477.8	477.5	477.3
17.5°	464.6	464.9	465.3	465.4	465.2	465.0	464.9	464.7
20°	455.4	455.6	455.9	456.0	455.7	455.6	455.4	455.2
22.5°	445.7	446.2	446.7	446.8	446.4	446.1	445.7	445.5
25°	429.7	429.8	429.9	429.8	429.4	429.0	428.7	428.3
27.5°	411.8	411.6	411.4	411.0	410.6	410.2	409.7	409.2
30°	399.5	399.2	398.7	398.4	397.9	397.4	397.0	396.6
32.5°	386.9	386.5	386.1	385.6	385.2	384.7	384.3	383.8
35°	367.1	366.5	365.8	365.3	364.9	364.5	363.9	363.5
37.5°	346.4	345.7	345.0	344.4	343.8	343.2	342.6	342.0
40°	332.0	331.1	330.2	329.5	329.0	328.6	328.1	327.7
42.5°	318.0	316.9	315.9	315.2	314.9	314.6	314.3	314.0
45°	296.4	295.3	294.4	293.7	293.4	293.2	292.9	292.7
47.5°	275.3	274.2	273.1	272.2	271.6	270.9	270.2	269.5
50°	260.7	259.5	258.2	257.3	256.8	256.2	255.6	255.1
52.5°	245.7	244.6	243.5	242.5	241.9	241.2	240.5	239.8
55°	223.6	222.5	221.4	220.6	220.1	219.6	219.0	218.4
57.5°	201.5	200.4	199.4	198.6	198.1	197.6	197.1	196.5
60°	186.2	185.5	184.6	184.0	183.6	183.0	182.6	182.2
62.5°	171.4	170.7	169.9	169.3	168.8	168.4	168.0	167.5
65°	149.8	148.9	148.0	147.3	146.9	146.4	145.9	145.5
67.5°	127.5	126.7	125.8	125.3	125.2	125.0	124.9	124.8
70°	113.5	112.8	112.0	111.5	111.2	111.0	110.7	110.5
72.5°	99.4	98.8	98.2	97.8	97.6	97.3	97.0	96.8
75°	79.1	78.8	78.4	78.2	78.1	78.0	77.9	77.8
77.5°	59.9	59.8	59.8	59.6	59.3	59.1	58.8	58.6
80°	47.7	47.5	47.4	47.3	47.1	47.0	46.9	46.8
82.5°	36.8	36.7	36.6	36.5	36.4	36.2	36.2	36.1
85°	21.2	21.2	21.2	21.2	21.1	21.0	20.8	20.8
87.5°	11.5	11.6	11.8	11.8	12.1	12.2	12.1	12.1
90°	18.0	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	196.5	147.8	117.7	97.6	85.8	80.4	77.1	77.1
95°	741.3	586.3	452.2	355.2	306.2	275.2	257.1	244.1
97.5°	1095.4	1037.7	939.9	835.4	763.5	703.4	673.3	652.6
100°	1206.6	1226.6	1177.6	1103.5	1016.5	955.5	925.5	917.5
102.5°	1201.0	1300.2	1314.4	1283.6	1230.2	1185.9	1154.3	1148.0
105°	1120.5	1293.7	1392.7	1433.7	1435.7	1427.7	1413.7	1407.6
107.5°	1006.3	1190.6	1330.1	1419.3	1468.7	1491.5	1501.5	1504.2
110°	937.5	1110.5	1255.6	1365.6	1436.7	1478.7	1496.8	1505.7





TEST NUMBER: P332534-935

CATALOG NUMBER: S124DIP-S350D1205U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	887.0	1040.1	1177.2	1287.2	1367.9	1418.7	1443.9	1458.5
115°	836.4	959.5	1076.5	1172.6	1251.6	1311.6	1343.7	1351.7
117.5°	811.6	913.4	1005.5	1086.9	1154.3	1204.8	1237.2	1243.4
120°	800.4	893.5	973.4	1044.5	1101.6	1145.6	1171.6	1182.6
122.5°	790.7	880.6	953.5	1015.7	1063.9	1101.6	1123.5	1134.5
125°	774.4	860.4	929.4	984.5	1024.5	1053.5	1072.5	1078.5
127.5°	754.3	836.6	905.4	957.7	997.9	1023.7	1039.7	1045.7
130°	738.4	817.4	885.5	938.5	979.5	1004.4	1020.5	1026.5
132.5°	721.5	795.8	862.2	915.2	955.5	983.7	998.8	1004.9
135°	698.4	763.4	824.4	874.4	914.5	942.5	958.5	964.5
137.5°	677.3	732.4	783.8	829.0	866.4	894.1	907.2	914.5
140°	665.3	712.3	757.3	799.4	834.4	856.4	870.4	878.4
142.5°	654.1	695.5	734.2	770.6	801.6	822.0	834.4	840.0
145°	638.3	672.4	702.3	730.4	755.4	772.4	782.4	787.4
147.5°	625.3	652.3	676.3	698.4	716.8	731.3	739.0	740.7
150°	617.3	640.3	660.3	678.3	694.3	707.3	713.3	714.4
152.5°	608.5	628.3	646.7	661.5	675.1	685.7	689.3	690.3
155°	595.3	611.3	626.3	638.3	648.3	656.3	659.4	659.4
157.5°	581.1	594.5	607.1	616.7	624.3	630.3	632.1	632.1
160°	572.3	583.2	594.3	602.3	608.3	614.3	615.3	615.3
162.5°	563.4	572.9	581.5	588.7	593.1	599.1	600.1	599.3
165°	551.3	557.2	564.3	569.3	573.3	577.3	576.3	575.3
167.5°	539.5	544.1	549.7	552.7	554.7	557.2	557.1	556.3
170°	532.3	535.3	539.2	542.3	544.2	545.3	544.2	544.2
172.5°	525.8	528.1	530.5	532.6	533.8	534.9	533.8	532.3
175°	517.3	518.2	520.2	520.2	520.2	522.3	520.2	518.2
177.5°	511.6	512.5	512.5	513.2	512.5	513.2	511.6	510.1
180°	509.3	509.3	509.3	509.3	509.3	509.3	509.3	509.3

(END OF REPORT)