

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332568-927

Luminaire Tested: **S124DIP-S575D1035U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332568-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S575D1035U927-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5247.8 lumens  
Efficiency: N/A  
Efficacy: 117.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332568-927

CATALOG NUMBER: S124DIP-S575D1035U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332568-927

CATALOG NUMBER: S124DIP-S575D1035U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	40	39	38	32
2	86	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32	26
3	79	70	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6211	6211	6211
5°	6229	6155	6199
10°	6190	6105	6135
15°	6115	6018	6033
20°	6016	5910	5916
25°	5903	5787	5770
30°	5764	5643	5591
35°	5619	5492	5419
40°	5469	5321	5223
45°	5313	5151	5053
50°	5141	5001	4847
55°	4954	4807	4650
60°	4766	4589	4448
65°	4556	4380	4204
70°	4322	4102	3944
75°	3961	3768	3671
80°	3524	3380	3296
85°	3084	2973	2908



TEST NUMBER: P332568-927

CATALOG NUMBER: S124DIP-S575D1035U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.5	1.4
10°-20°	204.1	3.9
20°-30°	300.5	5.7
30°-40°	349.3	6.7
40°-50°	349.3	6.7
50°-60°	305.5	5.8
60°-70°	226.9	4.3
70°-80°	128.9	2.5
80°-90°	40.3	0.8
90°-100°	36.2	0.7
100°-110°	230.6	4.4
110°-120°	441.1	8.4
120°-130°	559.9	10.7
130°-140°	599.1	11.4
140°-150°	560.2	10.7
150°-160°	451.8	8.6
160°-170°	291.4	5.6
170°-180°	100.4	1.9
0°-30°	577.0	11.0
0°-40°	926.3	17.7
0°-60°	1581.2	30.1
0°-90°	1977.3	37.7
90°-120°	707.8	13.5
90°-150°	2427.0	46.2
90°-180°	3271.0	62.3
0°-180°	5247.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	760	766	765	73
15°	732	729	720	723	722	206
25°	663	658	650	650	648	305
35°	570	566	557	553	550	356
45°	465	461	451	445	443	359
55°	352	350	342	334	330	315
65°	238	235	229	223	220	236
75°	127	124	121	118	118	135
85°	33	33	32	32	31	37
90°	2	11	17	22	24	4
95°	44	18	17	22	23	56
105°	238	243	247	252	225	249
115°	444	447	446	448	448	437
125°	625	628	626	629	630	558
135°	775	774	777	779	780	597
145°	894	896	896	897	898	558
155°	980	980	978	981	979	452
165°	1034	1030	1030	1035	1029	292
175°	1057	1053	1053	1060	1051	101
180°	1057	1057	1057	1057	1057	



TEST NUMBER: P332568-927

CATALOG NUMBER: S124DIP-S575D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	771.3	771.0	770.6	770.3	770.0	769.2	768.0	766.8	765.6	764.4	765.5
5°	768.7	768.2	767.6	767.1	766.5	765.5	764.0	762.5	761.0	759.5	761.0
7.5°	761.5	761.0	760.5	759.9	759.4	758.3	756.6	754.9	753.2	751.5	752.8
10°	755.1	754.6	754.1	753.5	753.0	751.8	750.0	748.2	746.5	744.7	745.8
12.5°	746.8	746.2	745.7	745.1	744.6	743.4	741.5	739.6	737.7	735.8	737.0
15°	731.7	731.2	730.6	730.1	729.5	728.3	726.2	724.1	722.1	720.0	720.8
17.5°	713.6	712.9	712.3	711.5	710.8	709.6	707.6	705.7	703.7	701.8	702.3
20°	700.3	699.6	698.9	698.2	697.5	696.2	694.1	692.1	690.0	687.9	688.3
22.5°	686.0	685.1	684.2	683.3	682.4	680.9	678.8	676.8	674.7	672.6	673.4
25°	662.7	661.7	660.8	659.8	658.9	657.4	655.5	653.6	651.6	649.7	649.9
27.5°	636.0	635.1	634.1	633.1	632.1	630.7	628.9	627.2	625.3	623.6	623.3
30°	618.3	617.2	616.1	615.0	613.9	612.4	610.7	608.9	607.1	605.4	604.8
32.5°	599.5	598.6	597.5	596.6	595.6	594.1	592.3	590.4	588.5	586.6	586.0
35°	570.2	569.3	568.3	567.4	566.4	564.9	563.0	561.1	559.2	557.3	556.3
37.5°	539.2	538.4	537.5	536.6	535.8	534.3	532.3	530.2	528.1	526.1	525.1
40°	519.0	517.9	516.8	515.8	514.7	513.1	511.0	509.0	506.9	504.9	503.5
42.5°	497.3	496.7	496.1	495.4	494.7	493.2	491.0	488.7	486.4	484.2	482.6
45°	465.4	464.5	463.5	462.6	461.6	460.0	457.8	455.6	453.4	451.2	449.7
47.5°	432.0	431.3	430.7	430.0	429.4	428.0	426.0	424.0	421.9	419.9	418.2
50°	409.3	408.8	408.2	407.7	407.1	405.9	404.0	402.0	400.1	398.2	396.3
52.5°	387.1	386.5	385.8	385.2	384.5	383.2	381.1	379.1	377.1	375.0	373.4
55°	352.0	351.6	351.2	350.8	350.4	349.2	347.3	345.3	343.4	341.5	339.8
57.5°	318.5	318.0	317.5	317.0	316.6	315.4	313.5	311.6	309.7	307.8	306.3
60°	295.2	294.6	293.9	293.2	292.6	291.3	289.5	287.7	286.0	284.2	283.0
62.5°	272.6	272.0	271.4	270.8	270.3	269.0	267.2	265.3	263.4	261.5	260.4
65°	238.5	237.9	237.2	236.5	235.8	234.8	233.5	232.0	230.7	229.3	227.9
67.5°	204.3	203.7	203.0	202.4	201.8	200.8	199.5	198.2	196.9	195.5	194.2
70°	183.1	182.1	181.2	180.2	179.3	178.2	177.1	176.0	174.9	173.8	172.8
72.5°	160.4	159.5	158.5	157.5	156.5	155.7	154.8	153.9	153.0	152.1	151.2
75°	127.0	126.3	125.6	124.9	124.2	123.6	122.9	122.2	121.5	120.8	120.3
77.5°	95.1	94.7	94.4	94.2	93.9	93.4	92.8	92.2	91.6	91.0	90.8
80°	75.8	75.4	75.0	74.6	74.1	73.8	73.6	73.3	73.0	72.7	72.5
82.5°	57.1	56.9	56.7	56.5	56.3	56.2	56.2	56.1	56.0	56.0	55.8
85°	33.3	33.3	33.3	33.3	33.3	33.1	32.9	32.6	32.3	32.1	32.1
87.5°	13.3	13.5	13.9	14.1	14.4	14.7	14.8	15.0	15.1	15.3	15.5
90°	2.4	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5
92.5°	10.0	10.1	10.1	10.3	10.4	11.2	12.5	13.9	15.4	16.8	17.8
95°	43.5	37.5	31.5	25.6	19.6	16.7	16.9	17.0	17.2	17.4	18.5
97.5°	92.4	96.1	99.8	103.5	107.3	99.3	79.7	60.1	40.5	20.9	21.0
100°	129.7	132.8	136.0	139.2	142.4	131.8	107.6	83.3	59.0	34.8	31.8
102.5°	171.4	173.8	176.1	178.4	180.7	180.3	177.1	174.0	170.8	167.6	135.4
105°	238.1	239.1	240.1	241.2	242.2	243.2	244.1	244.9	245.9	246.8	248.3
107.5°	299.8	300.4	301.0	301.4	302.0	302.9	304.0	305.2	306.4	307.6	308.4
110°	341.7	342.1	342.7	343.2	343.7	344.5	345.5	346.7	347.7	348.7	349.1



TEST NUMBER: P332568-927

CATALOG NUMBER: S124DIP-S575D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.1	383.1	384.0	385.0	386.0	386.7	387.1	387.6	388.1	388.6	388.6
115°	444.4	445.0	445.5	446.0	446.6	446.7	446.6	446.4	446.2	446.0	446.4
117.5°	500.6	501.3	502.0	502.7	503.4	503.9	504.3	504.7	505.1	505.5	505.4
120°	538.5	539.2	540.0	540.7	541.4	541.6	541.5	541.3	541.1	540.9	541.3
122.5°	573.9	574.4	574.8	575.2	575.7	576.0	576.2	576.5	576.7	576.9	577.2
125°	624.7	625.4	626.1	626.9	627.6	627.7	627.4	627.0	626.7	626.3	626.9
127.5°	672.8	673.0	673.2	673.4	673.5	674.0	674.9	675.7	676.4	677.2	677.2
130°	703.9	704.0	704.2	704.3	704.5	704.9	705.4	705.9	706.5	707.0	707.2
132.5°	732.3	732.6	732.9	733.2	733.6	734.0	734.7	735.4	736.0	736.7	736.9
135°	775.0	774.8	774.7	774.4	774.3	774.5	775.2	775.9	776.7	777.4	777.7
137.5°	812.8	812.9	812.9	813.0	813.1	813.5	814.3	815.1	815.8	816.6	817.0
140°	837.5	837.8	838.2	838.5	838.8	839.2	839.6	840.0	840.3	840.7	841.1
142.5°	859.6	860.2	860.9	861.5	862.1	862.5	862.8	863.0	863.2	863.4	863.8
145°	893.6	894.1	894.7	895.2	895.7	896.0	896.0	896.0	896.0	896.0	896.2
147.5°	920.7	921.6	922.7	923.6	924.6	925.0	924.8	924.6	924.5	924.3	924.5
150°	940.2	941.0	941.7	942.4	943.1	943.3	943.2	943.0	942.9	942.6	942.6
152.5°	956.7	957.3	957.8	958.4	958.9	959.1	958.8	958.5	958.1	957.8	958.1
155°	979.9	980.0	980.2	980.3	980.5	980.3	979.9	979.3	978.7	978.3	978.9
157.5°	999.3	999.2	999.0	998.9	998.9	998.5	997.9	997.3	996.7	996.1	997.0
160°	1010.7	1010.1	1009.6	1009.1	1008.5	1008.2	1008.1	1007.8	1007.7	1007.5	1008.5
162.5°	1020.8	1020.1	1019.5	1018.7	1018.1	1017.7	1017.5	1017.3	1017.2	1017.0	1018.0
165°	1033.6	1032.7	1031.8	1030.9	1030.1	1029.6	1029.6	1029.6	1029.6	1029.6	1031.0
167.5°	1043.7	1042.8	1041.9	1041.0	1040.1	1039.6	1039.4	1039.3	1039.3	1039.1	1040.7
170°	1049.4	1048.4	1047.3	1046.2	1045.2	1044.7	1044.9	1045.1	1045.3	1045.4	1046.9
172.5°	1053.2	1052.2	1051.1	1050.0	1049.0	1048.5	1048.7	1048.9	1049.1	1049.2	1050.7
175°	1057.3	1056.3	1055.2	1054.2	1053.1	1052.7	1052.8	1053.0	1053.2	1053.4	1054.9
177.5°	1059.2	1058.2	1057.2	1056.3	1055.3	1054.9	1055.2	1055.5	1055.7	1056.1	1057.2
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332568-927

CATALOG NUMBER: S124DIP-S575D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	766.6	767.7	768.8	769.3	769.1	769.1	769.0	768.8
5°	762.5	764.0	765.5	766.1	765.8	765.6	765.2	765.0
7.5°	754.0	755.2	756.4	756.9	756.8	756.6	756.5	756.2
10°	746.9	748.0	749.1	749.5	749.2	748.9	748.6	748.4
12.5°	738.2	739.4	740.6	741.0	740.6	740.2	739.9	739.5
15°	721.7	722.5	723.3	723.5	723.1	722.7	722.2	721.8
17.5°	702.8	703.3	703.9	703.9	703.7	703.4	703.1	702.9
20°	688.8	689.2	689.6	689.7	689.4	689.1	688.9	688.6
22.5°	674.1	674.9	675.7	675.7	675.3	674.8	674.3	673.8
25°	650.0	650.1	650.3	650.1	649.5	649.0	648.4	647.8
27.5°	623.0	622.6	622.3	621.8	621.1	620.4	619.7	619.0
30°	604.3	603.7	603.2	602.5	601.8	601.2	600.5	599.8
32.5°	585.3	584.6	584.0	583.3	582.7	581.9	581.2	580.6
35°	555.3	554.4	553.4	552.6	551.9	551.2	550.6	549.9
37.5°	524.0	522.9	521.9	520.9	520.1	519.1	518.2	517.3
40°	502.2	500.7	499.4	498.4	497.6	497.0	496.3	495.6
42.5°	481.0	479.3	477.8	476.7	476.3	475.9	475.4	474.9
45°	448.2	446.7	445.2	444.3	443.9	443.5	443.0	442.6
47.5°	416.5	414.8	413.1	411.8	410.7	409.6	408.6	407.6
50°	394.3	392.4	390.5	389.2	388.3	387.5	386.7	385.9
52.5°	371.6	369.9	368.3	366.9	365.8	364.8	363.8	362.7
55°	338.3	336.6	334.9	333.7	332.9	332.1	331.2	330.4
57.5°	304.8	303.2	301.6	300.4	299.6	298.8	298.0	297.2
60°	281.7	280.5	279.2	278.3	277.6	276.9	276.2	275.5
62.5°	259.3	258.1	257.0	256.1	255.4	254.8	254.1	253.3
65°	226.6	225.2	223.9	222.8	222.1	221.4	220.8	220.1
67.5°	192.9	191.6	190.3	189.5	189.3	189.2	188.9	188.8
70°	171.7	170.6	169.4	168.7	168.3	167.9	167.5	167.1
72.5°	150.4	149.5	148.6	148.0	147.6	147.2	146.8	146.3
75°	119.7	119.1	118.7	118.3	118.1	118.0	117.9	117.7
77.5°	90.6	90.5	90.3	90.1	89.7	89.4	89.0	88.6
80°	72.2	71.9	71.6	71.5	71.3	71.1	71.1	70.9
82.5°	55.6	55.5	55.3	55.1	55.1	54.9	54.7	54.6
85°	32.1	32.1	32.1	32.0	31.8	31.7	31.6	31.4
87.5°	15.8	15.9	16.2	16.3	16.4	16.5	16.5	16.6
90°	19.5	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	18.9	20.0	21.0	21.5	21.6	21.7	21.8	21.9
95°	19.5	20.6	21.6	22.3	22.4	22.6	22.7	22.9
97.5°	21.1	21.2	21.3	21.5	21.6	21.8	21.9	22.2
100°	28.8	25.8	22.8	21.5	21.6	21.8	21.9	22.2
102.5°	103.2	71.0	38.7	22.7	22.7	22.7	22.7	22.8
105°	249.9	251.4	253.0	250.7	244.4	238.1	231.7	225.4
107.5°	309.2	310.0	310.7	311.4	312.1	312.8	313.5	314.1
110°	349.4	349.8	350.1	350.6	351.1	351.6	352.2	352.7





TEST NUMBER: P332568-927

CATALOG NUMBER: S124DIP-S575D1035U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	388.5	388.4	388.3	388.6	389.3	390.0	390.6	391.3
115°	446.7	447.1	447.4	447.6	447.6	447.6	447.6	447.6
117.5°	505.3	505.3	505.2	505.2	505.1	505.0	504.9	504.9
120°	541.6	541.9	542.3	542.3	541.9	541.6	541.3	540.9
122.5°	577.4	577.6	577.8	577.7	577.4	577.0	576.7	576.3
125°	627.4	627.9	628.4	628.8	629.0	629.2	629.3	629.5
127.5°	677.1	676.9	676.8	676.7	676.6	676.4	676.3	676.1
130°	707.3	707.5	707.7	707.8	707.8	707.8	707.8	707.8
132.5°	737.0	737.3	737.4	737.4	737.3	737.1	737.0	736.9
135°	778.1	778.4	778.8	779.1	779.5	779.8	780.1	780.5
137.5°	817.4	817.8	818.2	818.2	818.2	818.1	817.9	817.8
140°	841.7	842.2	842.7	843.1	843.3	843.4	843.6	843.8
142.5°	864.2	864.6	865.0	865.1	865.2	865.2	865.3	865.3
145°	896.4	896.5	896.7	897.0	897.3	897.6	898.0	898.3
147.5°	924.6	924.7	924.9	925.0	925.2	925.3	925.6	925.7
150°	942.6	942.6	942.6	942.7	942.9	943.1	943.3	943.4
152.5°	958.4	958.7	958.9	959.0	958.9	958.9	958.7	958.6
155°	979.6	980.3	981.0	981.1	980.6	980.1	979.5	979.1
157.5°	997.9	998.9	999.7	999.7	998.9	997.9	997.0	996.1
160°	1009.6	1010.7	1011.7	1011.7	1010.7	1009.6	1008.5	1007.5
162.5°	1019.1	1020.2	1021.2	1021.1	1019.9	1018.7	1017.6	1016.4
165°	1032.5	1033.9	1035.2	1035.1	1033.6	1032.0	1030.4	1028.8
167.5°	1042.2	1043.8	1045.3	1045.2	1043.5	1041.7	1039.9	1038.2
170°	1048.3	1049.6	1051.1	1050.9	1049.2	1047.4	1045.6	1043.9
172.5°	1052.1	1053.4	1054.9	1054.6	1052.7	1050.8	1048.9	1047.0
175°	1056.5	1058.1	1059.7	1059.4	1057.3	1055.2	1053.1	1051.0
177.5°	1058.3	1059.4	1060.6	1060.3	1058.6	1056.9	1055.2	1053.5
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3

(END OF REPORT)