

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332543-935

Luminaire Tested: **S124DIP-S575D365U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332543-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D365U935-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3273.0 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332543-935

CATALOG NUMBER: S124DIP-S575D365U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332543-935

CATALOG NUMBER: S124DIP-S575D365U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66
1	101	97	93	89	95	91	88	84	81	78	76	71	69	67	62	61	59	55
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	43	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	26
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23
8	56	43	36	30	53	41	34	29	37	31	27	33	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6750	6750	6750
5°	6771	6689	6738
10°	6728	6634	6668
15°	6647	6541	6557
20°	6539	6424	6430
25°	6415	6290	6272
30°	6264	6134	6077
35°	6107	5969	5889
40°	5945	5782	5676
45°	5775	5599	5492
50°	5588	5436	5267
55°	5384	5225	5054
60°	5181	4986	4836
65°	4951	4762	4569
70°	4697	4459	4286
75°	4304	4095	3989
80°	3831	3673	3584
85°	3353	3233	3168



TEST NUMBER: P332543-935

CATALOG NUMBER: S124DIP-S575D365U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	2.4
10°-20°	221.9	6.8
20°-30°	326.6	10.0
30°-40°	379.6	11.6
40°-50°	379.6	11.6
50°-60°	332.1	10.1
60°-70°	246.6	7.5
70°-80°	140.1	4.3
80°-90°	41.3	1.3
90°-100°	111.9	3.4
100°-110°	232.8	7.1
110°-120°	208.5	6.4
120°-130°	175.4	5.4
130°-140°	146.3	4.5
140°-150°	111.7	3.4
150°-160°	78.5	2.4
160°-170°	46.2	1.4
170°-180°	15.0	0.5
0°-30°	627.2	19.2
0°-40°	1006.8	30.8
0°-60°	1718.5	52.5
0°-90°	2146.5	65.6
90°-120°	553.3	16.9
90°-150°	986.7	30.1
90°-180°	1126.0	34.4
0°-180°	3273.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	836	833	825	832	832	79
15°	795	792	783	786	784	224
25°	720	715	706	707	704	331
35°	620	615	606	601	598	387
45°	506	501	490	483	481	390
55°	382	380	371	363	359	343
65°	259	256	249	243	239	257
75°	138	135	131	129	128	147
85°	36	36	35	35	34	40
90°	0	2	6	6	6	2
95°	10	32	248	123	74	11
105°	36	52	200	430	428	38
115°	63	79	178	342	411	62
125°	87	104	177	291	328	78
135°	104	124	176	258	293	80
145°	120	137	175	218	239	75
155°	136	147	170	192	200	63
165°	148	153	163	172	175	42
175°	154	155	156	158	158	15
180°	155	155	155	155	155	



TEST NUMBER: P332543-935

CATALOG NUMBER: S124DIP-S575D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	838.3	837.9	837.6	837.2	836.9	836.0	834.7	833.4	832.1	830.8	832.0
5°	835.5	834.9	834.3	833.7	833.1	832.0	830.3	828.7	827.1	825.4	827.1
7.5°	827.7	827.1	826.6	826.0	825.4	824.1	822.3	820.5	818.6	816.8	818.2
10°	820.7	820.2	819.6	819.0	818.4	817.1	815.2	813.2	811.3	809.3	810.5
12.5°	811.7	811.1	810.5	809.9	809.3	808.0	805.9	803.8	801.8	799.7	801.0
15°	795.3	794.7	794.1	793.5	792.9	791.5	789.3	787.0	784.8	782.6	783.4
17.5°	775.6	774.8	774.1	773.4	772.6	771.2	769.0	767.0	764.8	762.8	763.3
20°	761.1	760.3	759.7	758.9	758.1	756.6	754.4	752.2	749.9	747.7	748.1
22.5°	745.5	744.6	743.6	742.6	741.7	740.0	737.8	735.6	733.3	731.1	731.9
25°	720.2	719.2	718.2	717.1	716.1	714.5	712.4	710.3	708.3	706.2	706.4
27.5°	691.3	690.3	689.1	688.1	687.0	685.5	683.5	681.7	679.7	677.8	677.4
30°	672.0	670.8	669.6	668.4	667.3	665.6	663.7	661.8	659.9	658.0	657.4
32.5°	651.6	650.6	649.5	648.4	647.4	645.8	643.8	641.7	639.6	637.6	636.9
35°	619.7	618.7	617.7	616.6	615.6	614.0	611.9	609.8	607.8	605.7	604.6
37.5°	586.1	585.1	584.2	583.2	582.3	580.7	578.5	576.3	574.0	571.8	570.7
40°	564.1	562.9	561.7	560.6	559.4	557.7	555.4	553.2	551.0	548.7	547.3
42.5°	540.5	539.8	539.2	538.4	537.7	536.1	533.6	531.2	528.7	526.2	524.5
45°	505.8	504.8	503.8	502.7	501.7	500.0	497.6	495.2	492.8	490.4	488.8
47.5°	469.5	468.8	468.1	467.4	466.7	465.2	463.0	460.8	458.6	456.4	454.5
50°	444.9	444.3	443.7	443.1	442.5	441.2	439.1	437.0	434.9	432.8	430.8
52.5°	420.8	420.1	419.3	418.6	417.9	416.5	414.2	412.1	409.8	407.6	405.8
55°	382.5	382.1	381.7	381.3	380.8	379.5	377.5	375.3	373.2	371.2	369.4
57.5°	346.1	345.6	345.1	344.6	344.1	342.9	340.8	338.7	336.7	334.6	332.9
60°	320.9	320.2	319.4	318.7	318.0	316.6	314.7	312.7	310.8	308.8	307.5
62.5°	296.3	295.7	295.0	294.4	293.8	292.4	290.4	288.3	286.3	284.2	283.0
65°	259.2	258.6	257.8	257.1	256.3	255.2	253.7	252.2	250.7	249.3	247.7
67.5°	222.1	221.4	220.7	220.0	219.3	218.3	216.8	215.4	214.0	212.5	211.1
70°	199.0	197.9	196.9	195.9	194.8	193.7	192.5	191.3	190.1	188.9	187.8
72.5°	174.4	173.3	172.3	171.2	170.1	169.2	168.2	167.3	166.3	165.3	164.4
75°	138.0	137.2	136.6	135.8	135.0	134.3	133.5	132.8	132.1	131.3	130.7
77.5°	103.3	103.0	102.6	102.4	102.0	101.5	100.8	100.2	99.5	98.9	98.7
80°	82.4	82.0	81.5	81.1	80.6	80.2	80.0	79.6	79.4	79.0	78.8
82.5°	62.1	61.8	61.6	61.4	61.2	61.0	61.0	61.0	60.9	60.9	60.6
85°	36.2	36.2	36.2	36.2	36.2	36.0	35.7	35.5	35.1	34.9	34.9
87.5°	14.0	14.0	14.0	14.0	13.9	13.9	14.0	13.9	13.9	13.9	13.9
90°	0.3	0.9	1.8	2.2	2.4	2.4	4.2	4.2	4.9	5.5	5.2
92.5°	3.4	5.1	7.9	11.6	16.1	22.4	37.9	61.5	84.5	96.5	80.4
95°	10.1	10.9	14.0	18.0	25.2	38.1	64.5	114.4	187.2	248.0	255.0
97.5°	18.0	18.0	20.7	24.3	30.6	41.2	61.6	102.9	175.1	261.2	320.4
100°	23.2	23.2	25.2	28.9	34.7	44.4	62.4	96.8	158.9	244.7	322.5
102.5°	28.0	28.5	30.4	33.8	39.3	48.6	64.8	95.1	147.9	223.9	304.3
105°	35.6	36.5	38.1	41.7	47.2	56.0	70.6	95.8	138.4	199.6	271.1
107.5°	44.0	44.6	46.1	50.0	55.3	64.0	77.3	100.4	136.7	186.0	244.4
110°	49.6	50.2	51.7	55.4	60.9	69.1	82.5	103.8	137.2	181.3	231.0



TEST NUMBER: P332543-935

CATALOG NUMBER: S124DIP-S575D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.9	55.5	57.3	60.7	66.2	74.4	87.3	107.5	138.7	179.2	223.4
115°	62.7	63.6	65.7	68.8	74.6	82.7	95.0	113.2	141.5	178.1	216.4
117.5°	70.7	71.5	73.4	76.8	82.2	90.7	102.3	119.1	144.5	177.7	213.2
120°	76.1	76.7	78.8	82.1	87.3	95.8	107.5	123.2	146.7	177.7	211.5
122.5°	80.9	81.5	83.7	86.8	92.5	100.7	112.3	127.2	148.9	177.5	209.6
125°	87.3	88.5	90.4	93.8	99.5	108.1	119.0	132.9	152.1	177.1	206.3
127.5°	93.0	93.9	96.2	100.0	106.0	114.6	125.2	138.0	154.8	176.4	202.0
130°	96.2	97.4	99.8	104.4	110.1	119.0	129.3	141.2	156.7	176.2	199.3
132.5°	99.4	100.3	103.5	107.8	114.1	122.3	132.8	144.4	158.4	176.0	196.9
135°	103.8	105.0	108.1	113.2	119.6	127.5	137.5	148.5	161.0	175.6	193.2
137.5°	108.2	109.3	112.7	117.6	124.2	131.8	141.2	151.4	162.5	175.6	190.1
140°	111.4	112.3	115.6	120.8	127.2	134.5	143.6	153.3	163.7	175.3	188.4
142.5°	114.8	115.7	118.8	123.7	129.8	136.9	145.9	154.8	164.7	175.3	186.9
145°	119.6	120.5	123.6	127.8	133.6	140.3	148.2	156.4	165.2	174.7	184.4
147.5°	125.0	125.3	128.0	132.3	137.2	143.2	150.6	157.8	165.6	173.6	182.2
150°	128.4	128.7	131.1	134.8	139.4	145.2	151.9	158.5	165.6	172.8	180.5
152.5°	131.6	131.6	134.1	137.5	141.5	146.9	152.8	159.0	165.1	171.6	178.5
155°	136.0	136.3	138.2	141.2	144.6	149.1	154.3	159.5	164.4	169.8	175.6
157.5°	140.3	140.3	142.1	144.4	147.3	150.9	155.3	159.5	163.5	167.9	172.6
160°	143.0	143.0	144.2	146.4	148.8	152.1	155.8	159.5	162.8	166.4	170.4
162.5°	145.4	145.3	146.2	148.1	150.2	152.9	156.3	159.5	162.0	165.0	168.5
165°	148.2	148.2	148.8	150.3	151.9	153.7	156.4	158.9	160.7	162.8	165.2
167.5°	150.9	150.6	150.9	152.1	152.9	154.4	156.4	158.1	159.2	160.6	162.3
170°	152.1	151.9	152.1	153.1	153.7	154.5	156.1	157.6	158.3	159.1	160.4
172.5°	153.3	153.1	153.1	153.8	154.1	154.8	155.8	157.1	157.3	157.6	158.7
175°	154.5	154.3	154.3	154.5	154.9	154.9	155.5	156.4	156.1	156.1	156.7
177.5°	155.2	154.9	154.6	154.9	154.9	154.9	155.2	155.6	155.2	155.2	155.4
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9



TEST NUMBER: P332543-935

CATALOG NUMBER: S124DIP-S575D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	836.1	836.1	836.1	836.1	836.1	836.1	836.1	836.1
2.5°	833.2	834.4	835.6	836.1	835.9	835.9	835.8	835.6
5°	828.7	830.3	832.0	832.7	832.3	832.1	831.7	831.5
7.5°	819.5	820.8	822.1	822.7	822.5	822.3	822.2	821.9
10°	811.8	813.0	814.2	814.6	814.2	814.0	813.6	813.4
12.5°	802.4	803.7	804.9	805.4	804.9	804.5	804.2	803.7
15°	784.4	785.2	786.1	786.4	785.9	785.5	785.0	784.5
17.5°	763.9	764.4	765.0	765.1	764.8	764.5	764.2	764.0
20°	748.6	749.1	749.5	749.6	749.2	749.0	748.7	748.4
22.5°	732.7	733.5	734.3	734.4	733.9	733.4	732.9	732.3
25°	706.5	706.6	706.8	706.5	705.9	705.3	704.7	704.1
27.5°	677.1	676.7	676.3	675.8	675.0	674.3	673.6	672.8
30°	656.8	656.2	655.6	654.9	654.1	653.4	652.6	651.9
32.5°	636.1	635.4	634.7	634.0	633.3	632.5	631.7	631.0
35°	603.6	602.5	601.5	600.6	599.9	599.1	598.4	597.6
37.5°	569.6	568.3	567.2	566.2	565.2	564.2	563.3	562.2
40°	545.8	544.2	542.8	541.7	540.9	540.2	539.4	538.6
42.5°	522.8	521.0	519.3	518.1	517.7	517.2	516.7	516.2
45°	487.2	485.5	483.9	482.8	482.4	482.0	481.5	481.0
47.5°	452.7	450.8	449.0	447.5	446.4	445.2	444.1	443.0
50°	428.6	426.5	424.5	423.0	422.1	421.2	420.3	419.4
52.5°	403.9	402.1	400.3	398.7	397.6	396.5	395.4	394.3
55°	367.6	365.8	364.0	362.7	361.8	360.9	360.0	359.1
57.5°	331.2	329.5	327.8	326.5	325.6	324.8	323.9	323.0
60°	306.2	304.9	303.5	302.5	301.7	301.0	300.2	299.5
62.5°	281.8	280.5	279.3	278.4	277.6	276.9	276.1	275.3
65°	246.2	244.8	243.3	242.2	241.4	240.6	240.0	239.2
67.5°	209.7	208.3	206.8	206.0	205.8	205.6	205.3	205.2
70°	186.6	185.4	184.2	183.4	182.9	182.4	182.0	181.6
72.5°	163.4	162.5	161.5	160.8	160.4	160.0	159.5	159.0
75°	130.1	129.5	129.0	128.5	128.4	128.3	128.1	127.9
77.5°	98.5	98.3	98.2	97.9	97.5	97.1	96.7	96.3
80°	78.4	78.2	77.8	77.7	77.5	77.3	77.2	77.1
82.5°	60.4	60.3	60.1	59.9	59.8	59.7	59.5	59.3
85°	34.9	34.9	34.9	34.8	34.6	34.4	34.4	34.2
87.5°	13.9	14.0	14.1	14.1	14.1	14.2	14.1	14.1
90°	5.5	5.8	6.1	6.1	6.4	6.7	6.4	6.4
92.5°	59.8	44.9	35.8	29.7	26.1	24.5	23.4	23.4
95°	225.5	178.3	137.5	108.1	93.1	83.7	78.2	74.2
97.5°	333.1	315.6	285.9	254.1	232.2	214.0	204.8	198.5
100°	367.0	373.1	358.2	335.6	309.2	290.6	281.5	279.1
102.5°	365.3	395.5	399.8	390.4	374.2	360.8	351.1	349.1
105°	340.8	393.5	423.6	436.1	436.7	434.2	430.0	428.2
107.5°	306.1	362.1	404.5	431.7	446.7	453.7	456.7	457.4
110°	285.2	337.8	381.9	415.3	437.0	449.8	455.2	458.0



TEST NUMBER: P332543-935

CATALOG NUMBER: S124DIP-S575D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	269.8	316.3	358.0	391.5	416.0	431.5	439.2	443.6
115°	254.4	291.8	327.4	356.6	380.6	398.9	408.7	411.1
117.5°	246.8	277.8	305.8	330.6	351.1	366.4	376.3	378.2
120°	243.4	271.7	296.1	317.7	335.0	348.4	356.4	359.7
122.5°	240.5	267.9	290.0	308.9	323.6	335.0	341.7	345.1
125°	235.6	261.7	282.7	299.5	311.6	320.5	326.2	328.0
127.5°	229.5	254.4	275.4	291.3	303.5	311.3	316.2	318.1
130°	224.5	248.7	269.3	285.4	297.9	305.5	310.4	312.2
132.5°	219.5	242.0	262.3	278.4	290.6	299.2	303.8	305.7
135°	212.4	232.2	250.7	266.0	278.1	286.6	291.5	293.3
137.5°	206.0	222.7	238.4	252.1	263.6	271.9	276.0	278.1
140°	202.3	216.6	230.3	243.1	253.8	260.5	264.8	267.2
142.5°	199.0	211.5	223.3	234.4	243.8	250.0	253.8	255.5
145°	194.2	204.5	213.6	222.1	229.7	234.9	238.0	239.4
147.5°	190.2	198.4	205.7	212.4	218.0	222.5	224.7	225.3
150°	187.8	194.8	200.9	206.3	211.2	215.2	217.0	217.2
152.5°	185.1	191.1	196.7	201.2	205.3	208.5	209.7	210.0
155°	181.1	185.9	190.5	194.2	197.2	199.6	200.5	200.5
157.5°	176.8	180.8	184.7	187.6	189.9	191.7	192.3	192.3
160°	174.1	177.4	180.7	183.2	185.0	186.8	187.2	187.2
162.5°	171.4	174.3	176.8	179.1	180.4	182.2	182.5	182.3
165°	167.6	169.5	171.6	173.1	174.4	175.6	175.3	175.0
167.5°	164.1	165.5	167.2	168.1	168.7	169.5	169.4	169.2
170°	161.9	162.8	164.0	165.0	165.6	165.8	165.6	165.6
172.5°	160.0	160.6	161.4	162.0	162.4	162.6	162.4	161.9
175°	157.3	157.6	158.3	158.3	158.3	158.9	158.3	157.6
177.5°	155.6	155.8	155.8	156.1	155.8	156.1	155.6	155.2
180°	154.9	154.9	154.9	154.9	154.9	154.9	154.9	154.9

(END OF REPORT)