

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332560-927

Luminaire Tested: **S124DIP-S575D810U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332560-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D810U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4198.3 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332560-927

CATALOG NUMBER: S124DIP-S575D810U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332560-927

CATALOG NUMBER: S124DIP-S575D810U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	40	38	33
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16
8	53	41	33	28	49	38	31	27	33	27	23	27	23	20	23	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6211	6211	6211
5°	6229	6155	6199
10°	6190	6105	6135
15°	6115	6018	6033
20°	6016	5910	5916
25°	5903	5787	5770
30°	5764	5643	5591
35°	5619	5492	5419
40°	5469	5321	5223
45°	5313	5151	5053
50°	5141	5001	4847
55°	4954	4807	4650
60°	4766	4589	4448
65°	4556	4380	4204
70°	4322	4102	3944
75°	3961	3768	3671
80°	3524	3380	3296
85°	3084	2973	2908



TEST NUMBER: P332560-927

CATALOG NUMBER: S124DIP-S575D810U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.5	1.7
10°-20°	204.1	4.9
20°-30°	300.5	7.2
30°-40°	349.3	8.3
40°-50°	349.3	8.3
50°-60°	305.5	7.3
60°-70°	226.9	5.4
70°-80°	128.9	3.1
80°-90°	39.6	0.9
90°-100°	52.8	1.3
100°-110°	156.5	3.7
110°-120°	265.6	6.3
120°-130°	350.2	8.3
130°-140°	393.3	9.4
140°-150°	386.4	9.2
150°-160°	325.0	7.7
160°-170°	216.2	5.2
170°-180°	75.7	1.8
0°-30°	577.0	13.7
0°-40°	926.3	22.1
0°-60°	1581.2	37.7
0°-90°	1976.6	47.1
90°-120°	474.9	11.3
90°-150°	1604.7	38.2
90°-180°	2222.0	52.9
0°-180°	4198.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	769	766	760	766	765	73
15°	732	729	720	723	722	206
25°	663	658	650	650	648	305
35°	570	566	557	553	550	356
45°	465	461	451	445	443	359
55°	352	350	342	334	330	315
65°	238	235	229	223	220	236
75°	127	124	121	118	118	135
85°	33	33	32	32	31	37
90°	2	9	14	17	19	4
95°	37	43	47	49	49	41
105°	144	145	147	149	151	153
115°	270	270	269	268	268	266
125°	393	393	393	391	390	350
135°	507	511	511	510	508	392
145°	616	619	619	619	617	386
155°	706	706	705	708	705	325
165°	769	767	766	769	767	217
175°	800	797	796	800	796	76
180°	801	801	801	801	801	



TEST NUMBER: P332560-927

CATALOG NUMBER: S124DIP-S575D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	771.3	771.0	770.6	770.3	770.0	769.2	768.0	766.8	765.6	764.4	765.5
5°	768.7	768.2	767.6	767.1	766.5	765.5	764.0	762.5	761.0	759.5	761.0
7.5°	761.5	761.0	760.5	759.9	759.4	758.3	756.6	754.9	753.2	751.5	752.8
10°	755.1	754.6	754.1	753.5	753.0	751.8	750.0	748.2	746.5	744.7	745.8
12.5°	746.8	746.2	745.7	745.1	744.6	743.4	741.5	739.6	737.7	735.8	737.0
15°	731.7	731.2	730.6	730.1	729.5	728.3	726.2	724.1	722.1	720.0	720.8
17.5°	713.6	712.9	712.3	711.5	710.8	709.6	707.6	705.7	703.7	701.8	702.3
20°	700.3	699.6	698.9	698.2	697.5	696.2	694.1	692.1	690.0	687.9	688.3
22.5°	686.0	685.1	684.2	683.3	682.4	680.9	678.8	676.8	674.7	672.6	673.4
25°	662.7	661.7	660.8	659.8	658.9	657.4	655.5	653.6	651.6	649.7	649.9
27.5°	636.0	635.1	634.1	633.1	632.1	630.7	628.9	627.2	625.3	623.6	623.3
30°	618.3	617.2	616.1	615.0	613.9	612.4	610.7	608.9	607.1	605.4	604.8
32.5°	599.5	598.6	597.5	596.6	595.6	594.1	592.3	590.4	588.5	586.6	586.0
35°	570.2	569.3	568.3	567.4	566.4	564.9	563.0	561.1	559.2	557.3	556.3
37.5°	539.2	538.4	537.5	536.6	535.8	534.3	532.3	530.2	528.1	526.1	525.1
40°	519.0	517.9	516.8	515.8	514.7	513.1	511.0	509.0	506.9	504.9	503.5
42.5°	497.3	496.7	496.1	495.4	494.7	493.2	491.0	488.7	486.4	484.2	482.6
45°	465.4	464.5	463.5	462.6	461.6	460.0	457.8	455.6	453.4	451.2	449.7
47.5°	432.0	431.3	430.7	430.0	429.4	428.0	426.0	424.0	421.9	419.9	418.2
50°	409.3	408.8	408.2	407.7	407.1	405.9	404.0	402.0	400.1	398.2	396.3
52.5°	387.1	386.5	385.8	385.2	384.5	383.2	381.1	379.1	377.1	375.0	373.4
55°	352.0	351.6	351.2	350.8	350.4	349.2	347.3	345.3	343.4	341.5	339.8
57.5°	318.5	318.0	317.5	317.0	316.6	315.4	313.5	311.6	309.7	307.8	306.3
60°	295.2	294.6	293.9	293.2	292.6	291.3	289.5	287.7	286.0	284.2	283.0
62.5°	272.6	272.0	271.4	270.8	270.3	269.0	267.2	265.3	263.4	261.5	260.4
65°	238.5	237.9	237.2	236.5	235.8	234.8	233.5	232.0	230.7	229.3	227.9
67.5°	204.3	203.7	203.0	202.4	201.8	200.8	199.5	198.2	196.9	195.5	194.2
70°	183.1	182.1	181.2	180.2	179.3	178.2	177.1	176.0	174.9	173.8	172.8
72.5°	160.4	159.5	158.5	157.5	156.5	155.7	154.8	153.9	153.0	152.1	151.2
75°	127.0	126.3	125.6	124.9	124.2	123.6	122.9	122.2	121.5	120.8	120.3
77.5°	95.1	94.7	94.4	94.2	93.9	93.4	92.8	92.2	91.6	91.0	90.8
80°	75.8	75.4	75.0	74.6	74.1	73.8	73.6	73.3	73.0	72.7	72.5
82.5°	57.1	56.9	56.7	56.5	56.3	56.2	56.2	56.1	56.0	56.0	55.8
85°	33.3	33.3	33.3	33.3	33.3	33.1	32.9	32.6	32.3	32.1	32.1
87.5°	13.2	13.4	13.5	13.8	13.9	14.1	14.3	14.3	14.4	14.6	14.7
90°	1.8	3.4	4.9	6.4	7.9	9.2	10.3	11.4	12.5	13.6	14.4
92.5°	13.2	15.0	16.7	18.5	20.2	21.5	22.2	23.0	23.8	24.6	25.0
95°	37.2	38.4	39.6	40.9	42.1	43.3	44.2	45.2	46.1	47.1	47.5
97.5°	64.9	65.9	66.9	67.9	68.8	69.9	71.1	72.2	73.3	74.5	74.9
100°	86.7	87.2	87.8	88.3	88.9	89.8	91.0	92.3	93.5	94.7	95.1
102.5°	109.5	109.7	110.0	110.2	110.4	111.1	112.2	113.3	114.5	115.6	116.0
105°	144.3	144.4	144.6	144.7	144.9	145.2	145.8	146.3	146.9	147.4	147.8
107.5°	180.9	181.0	181.2	181.3	181.5	181.6	181.7	181.8	181.9	182.0	182.4
110°	205.7	205.9	206.1	206.4	206.7	206.8	206.7	206.5	206.4	206.2	206.0



TEST NUMBER: P332560-927

CATALOG NUMBER: S124DIP-S575D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.4	231.4	231.5	231.6	231.6	231.5	231.2	231.0	230.8	230.5	230.4
115°	270.1	270.1	270.1	270.1	270.1	269.9	269.6	269.3	269.0	268.8	268.6
117.5°	306.4	306.6	306.7	306.7	306.9	306.8	306.7	306.4	306.3	306.1	305.6
120°	330.7	331.3	331.8	332.4	333.0	333.0	332.6	332.2	331.8	331.4	330.7
122.5°	356.0	356.2	356.4	356.6	356.9	356.9	356.7	356.5	356.3	356.1	355.6
125°	393.2	393.2	393.2	393.2	393.2	393.2	393.1	392.9	392.8	392.7	392.4
127.5°	427.1	427.5	427.9	428.3	428.7	428.8	428.6	428.4	428.2	427.9	427.7
130°	450.8	451.3	451.7	452.1	452.5	452.7	452.7	452.7	452.7	452.7	452.4
132.5°	475.2	475.5	475.8	476.0	476.3	476.4	476.3	476.3	476.1	476.0	475.7
135°	507.2	508.0	508.9	509.7	510.6	511.0	511.0	511.0	511.0	511.0	510.6
137.5°	542.2	542.6	542.9	543.3	543.7	544.0	544.2	544.5	544.6	544.9	544.5
140°	565.5	565.7	566.0	566.3	566.6	566.6	566.6	566.6	566.6	566.6	566.6
142.5°	586.8	587.0	587.3	587.6	587.9	588.0	587.8	587.7	587.6	587.5	587.5
145°	616.2	616.8	617.3	617.9	618.5	618.8	618.9	619.0	619.2	619.3	619.2
147.5°	645.5	646.1	646.7	647.5	648.1	648.4	648.2	648.2	648.0	647.9	647.8
150°	663.3	663.8	664.4	665.0	665.5	665.7	665.7	665.7	665.7	665.7	665.7
152.5°	680.2	680.5	680.8	681.1	681.4	681.7	681.8	681.9	682.0	682.1	682.5
155°	706.0	706.0	706.0	706.0	706.0	705.9	705.8	705.7	705.5	705.4	705.9
157.5°	727.9	727.5	727.3	727.1	726.8	726.7	726.7	726.7	726.6	726.6	727.0
160°	740.7	740.5	740.5	740.3	740.1	740.0	739.9	739.7	739.6	739.5	739.9
162.5°	752.6	752.3	751.9	751.5	751.1	750.9	750.8	750.7	750.5	750.4	751.1
165°	768.6	768.2	767.8	767.3	766.9	766.6	766.3	766.0	765.7	765.5	766.3
167.5°	780.9	780.2	779.7	779.1	778.6	778.2	778.2	778.3	778.3	778.3	779.2
170°	787.7	787.1	786.4	785.7	785.1	784.7	784.9	785.1	785.1	785.3	786.1
172.5°	792.7	792.2	791.5	791.0	790.4	790.1	790.2	790.2	790.2	790.3	791.2
175°	799.5	798.8	798.1	797.5	796.8	796.4	796.2	796.1	796.0	795.8	796.8
177.5°	801.8	801.2	800.7	800.1	799.5	799.3	799.3	799.3	799.3	799.3	800.0
180°	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7



TEST NUMBER: P332560-927

CATALOG NUMBER: S124DIP-S575D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	769.3	769.3	769.3	769.3	769.3	769.3	769.3	769.3
2.5°	766.6	767.7	768.8	769.3	769.1	769.1	769.0	768.8
5°	762.5	764.0	765.5	766.1	765.8	765.6	765.2	765.0
7.5°	754.0	755.2	756.4	756.9	756.8	756.6	756.5	756.2
10°	746.9	748.0	749.1	749.5	749.2	748.9	748.6	748.4
12.5°	738.2	739.4	740.6	741.0	740.6	740.2	739.9	739.5
15°	721.7	722.5	723.3	723.5	723.1	722.7	722.2	721.8
17.5°	702.8	703.3	703.9	703.9	703.7	703.4	703.1	702.9
20°	688.8	689.2	689.6	689.7	689.4	689.1	688.9	688.6
22.5°	674.1	674.9	675.7	675.7	675.3	674.8	674.3	673.8
25°	650.0	650.1	650.3	650.1	649.5	649.0	648.4	647.8
27.5°	623.0	622.6	622.3	621.8	621.1	620.4	619.7	619.0
30°	604.3	603.7	603.2	602.5	601.8	601.2	600.5	599.8
32.5°	585.3	584.6	584.0	583.3	582.7	581.9	581.2	580.6
35°	555.3	554.4	553.4	552.6	551.9	551.2	550.6	549.9
37.5°	524.0	522.9	521.9	520.9	520.1	519.1	518.2	517.3
40°	502.2	500.7	499.4	498.4	497.6	497.0	496.3	495.6
42.5°	481.0	479.3	477.8	476.7	476.3	475.9	475.4	474.9
45°	448.2	446.7	445.2	444.3	443.9	443.5	443.0	442.6
47.5°	416.5	414.8	413.1	411.8	410.7	409.6	408.6	407.6
50°	394.3	392.4	390.5	389.2	388.3	387.5	386.7	385.9
52.5°	371.6	369.9	368.3	366.9	365.8	364.8	363.8	362.7
55°	338.3	336.6	334.9	333.7	332.9	332.1	331.2	330.4
57.5°	304.8	303.2	301.6	300.4	299.6	298.8	298.0	297.2
60°	281.7	280.5	279.2	278.3	277.6	276.9	276.2	275.5
62.5°	259.3	258.1	257.0	256.1	255.4	254.8	254.1	253.3
65°	226.6	225.2	223.9	222.8	222.1	221.4	220.8	220.1
67.5°	192.9	191.6	190.3	189.5	189.3	189.2	188.9	188.8
70°	171.7	170.6	169.4	168.7	168.3	167.9	167.5	167.1
72.5°	150.4	149.5	148.6	148.0	147.6	147.2	146.8	146.3
75°	119.7	119.1	118.7	118.3	118.1	118.0	117.9	117.7
77.5°	90.6	90.5	90.3	90.1	89.7	89.4	89.0	88.6
80°	72.2	71.9	71.6	71.5	71.3	71.1	71.1	70.9
82.5°	55.6	55.5	55.3	55.1	55.1	54.9	54.7	54.6
85°	32.1	32.1	32.1	32.0	31.8	31.7	31.6	31.4
87.5°	14.9	15.1	15.2	15.4	15.4	15.4	15.5	15.5
90°	15.3	16.1	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	25.5	26.0	26.5	26.9	27.0	27.2	27.3	27.5
95°	47.9	48.3	48.7	49.0	49.0	49.0	49.0	49.0
97.5°	75.4	75.9	76.4	76.7	76.7	76.7	76.7	76.7
100°	95.3	95.6	95.9	96.0	96.0	96.0	96.0	96.0
102.5°	116.4	116.7	117.1	117.3	117.5	117.6	117.7	117.8
105°	148.2	148.6	149.0	149.5	149.9	150.3	150.7	151.1
107.5°	182.8	183.1	183.5	183.7	183.6	183.6	183.6	183.5
110°	205.7	205.4	205.1	205.2	205.7	206.0	206.4	206.8



TEST NUMBER: P332560-927

CATALOG NUMBER: S124DIP-S575D810U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	230.4	230.4	230.3	230.3	230.4	230.4	230.5	230.6
115°	268.5	268.4	268.2	268.1	268.0	267.8	267.7	267.5
117.5°	305.1	304.7	304.2	303.8	303.6	303.2	303.0	302.7
120°	329.9	329.2	328.6	328.4	328.7	328.9	329.2	329.5
122.5°	355.1	354.7	354.3	353.8	353.2	352.8	352.3	351.8
125°	392.1	391.8	391.6	391.3	391.0	390.7	390.5	390.1
127.5°	427.4	427.1	426.8	426.6	426.4	426.2	426.0	425.7
130°	452.2	451.9	451.6	451.2	450.7	450.1	449.6	449.0
132.5°	475.5	475.2	474.9	474.7	474.4	474.2	474.0	473.8
135°	510.4	510.1	509.8	509.5	509.1	508.7	508.3	507.9
137.5°	544.2	543.8	543.4	543.3	543.4	543.4	543.5	543.7
140°	566.4	566.3	566.1	566.0	565.9	565.7	565.5	565.5
142.5°	587.4	587.4	587.4	587.3	587.3	587.3	587.2	587.2
145°	619.0	618.9	618.8	618.5	618.1	617.7	617.3	616.9
147.5°	647.7	647.6	647.5	647.4	647.2	647.1	647.0	646.8
150°	665.7	665.7	665.7	665.7	665.6	665.4	665.3	665.1
152.5°	682.8	683.1	683.4	683.4	683.1	682.7	682.4	682.0
155°	706.5	707.0	707.6	707.6	707.0	706.5	705.9	705.4
157.5°	727.4	727.9	728.3	728.2	727.8	727.3	726.8	726.4
160°	740.3	740.7	741.1	741.0	740.3	739.6	738.9	738.2
162.5°	751.9	752.6	753.4	753.4	752.7	752.0	751.3	750.6
165°	767.1	767.9	768.8	768.9	768.3	767.8	767.2	766.8
167.5°	780.0	780.9	781.6	781.6	780.8	779.9	779.1	778.2
170°	787.0	787.7	788.6	788.5	787.6	786.6	785.6	784.7
172.5°	792.1	793.1	794.0	794.0	793.1	792.0	791.1	790.1
175°	797.7	798.7	799.7	799.7	798.7	797.7	796.8	795.8
177.5°	800.8	801.6	802.4	802.3	801.5	800.6	799.7	798.8
180°	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7

(END OF REPORT)