

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332623-927

Luminaire Tested: **S124DIP-S795D1205U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332623-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S795D1205U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6003.7 lumens  
Efficiency: N/A  
Efficacy: 105.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332623-927

CATALOG NUMBER: S124DIP-S795D1205U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332623-927

CATALOG NUMBER: S124DIP-S795D1205U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81		65	65	65		52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66		57	56	54		45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55		50	48	45		40	38	37	32
3	80	71	64	58	73	65	59	54	54	50	46		45	41	38		35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39		40	36	33		32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34		36	32	28		29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29		32	28	25		26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26		29	25	22		24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23		27	23	20		22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20		25	21	18		20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18		23	19	16		19	16	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8490	8490	8490
5°	8515	8413	8474
10°	8461	8344	8385
15°	8359	8226	8247
20°	8223	8079	8086
25°	8068	7911	7888
30°	7879	7713	7643
35°	7681	7508	7407
40°	7477	7273	7140
45°	7263	7042	6907
50°	7027	6836	6625
55°	6773	6570	6356
60°	6516	6273	6082
65°	6229	5989	5746
70°	5908	5611	5391
75°	5415	5153	5022
80°	4816	4621	4505
85°	4215	4057	3974



TEST NUMBER: P332623-927

CATALOG NUMBER: S124DIP-S795D1205U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.0	1.6
10°-20°	279.0	4.6
20°-30°	410.7	6.8
30°-40°	477.4	8.0
40°-50°	477.5	8.0
50°-60°	417.6	7.0
60°-70°	310.2	5.2
70°-80°	176.2	2.9
80°-90°	54.4	0.9
90°-100°	78.5	1.3
100°-110°	232.5	3.9
110°-120°	394.6	6.6
120°-130°	520.4	8.7
130°-140°	584.4	9.7
140°-150°	574.3	9.6
150°-160°	483.0	8.0
160°-170°	321.4	5.4
170°-180°	112.5	1.9
0°-30°	788.7	13.1
0°-40°	1266.2	21.1
0°-60°	2161.3	36.0
0°-90°	2702.1	45.0
90°-120°	705.6	11.8
90°-150°	2384.7	39.7
90°-180°	3302.0	55.0
0°-180°	6003.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1052	1052	1052	1052	1052	
5°	1051	1047	1038	1047	1046	100
15°	1000	996	984	989	987	282
25°	906	900	888	889	886	417
35°	779	773	762	756	752	487
45°	636	630	617	608	605	490
55°	481	478	467	457	452	431
65°	326	322	314	305	301	323
75°	174	169	165	162	161	184
85°	46	45	44	44	43	50
90°	3	13	20	26	28	6
95°	55	63	70	73	73	61
105°	214	216	219	222	225	228
115°	401	401	399	398	398	396
125°	584	584	584	582	580	521
135°	754	759	759	757	755	583
145°	916	919	920	919	917	573
155°	1049	1049	1048	1052	1048	483
165°	1142	1139	1138	1143	1139	322
175°	1188	1184	1183	1188	1183	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P332623-927

CATALOG NUMBER: S124DIP-S795D1205U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1054.3	1053.8	1053.4	1053.0	1052.5	1051.5	1049.8	1048.1	1046.5	1044.9	1046.3
5°	1050.8	1050.0	1049.2	1048.5	1047.7	1046.3	1044.3	1042.2	1040.1	1038.1	1040.1
7.5°	1041.0	1040.2	1039.5	1038.7	1038.0	1036.5	1034.2	1031.9	1029.6	1027.3	1029.0
10°	1032.2	1031.5	1030.7	1030.0	1029.2	1027.6	1025.2	1022.8	1020.3	1017.9	1019.4
12.5°	1020.7	1020.0	1019.2	1018.5	1017.8	1016.1	1013.5	1010.9	1008.4	1005.8	1007.4
15°	1000.2	999.4	998.7	997.9	997.2	995.5	992.6	989.8	987.0	984.2	985.3
17.5°	975.4	974.5	973.5	972.6	971.7	969.9	967.3	964.6	961.9	959.3	960.0
20°	957.2	956.2	955.4	954.4	953.5	951.6	948.8	945.9	943.2	940.4	941.0
22.5°	937.7	936.4	935.2	934.0	932.7	930.7	927.9	925.1	922.3	919.5	920.5
25°	905.8	904.5	903.2	901.9	900.6	898.6	896.0	893.3	890.7	888.1	888.3
27.5°	869.4	868.1	866.7	865.4	864.0	862.1	859.7	857.3	854.8	852.4	851.9
30°	845.2	843.7	842.2	840.7	839.2	837.2	834.7	832.3	829.9	827.4	826.7
32.5°	819.5	818.2	816.8	815.5	814.1	812.1	809.6	807.0	804.5	801.8	801.0
35°	779.4	778.1	776.8	775.5	774.2	772.2	769.6	767.0	764.4	761.8	760.4
37.5°	737.1	735.9	734.7	733.6	732.3	730.3	727.5	724.7	721.9	719.1	717.6
40°	709.5	708.0	706.5	705.0	703.5	701.3	698.5	695.7	692.9	690.1	688.2
42.5°	679.9	678.9	678.0	677.2	676.2	674.2	671.1	668.0	664.9	661.8	659.7
45°	636.2	634.9	633.6	632.2	631.0	628.8	625.8	622.8	619.8	616.8	614.7
47.5°	590.5	589.6	588.7	587.8	586.9	585.1	582.3	579.6	576.8	574.0	571.6
50°	559.5	558.7	558.0	557.2	556.5	554.8	552.2	549.6	546.9	544.3	541.7
52.5°	529.2	528.3	527.4	526.5	525.5	523.7	520.9	518.2	515.4	512.6	510.3
55°	481.2	480.5	480.0	479.4	478.9	477.3	474.7	472.1	469.4	466.8	464.5
57.5°	435.3	434.7	434.0	433.4	432.8	431.1	428.6	426.0	423.4	420.8	418.7
60°	403.6	402.7	401.7	400.8	399.9	398.2	395.8	393.3	390.9	388.5	386.7
62.5°	372.6	371.9	371.1	370.3	369.5	367.8	365.2	362.6	360.0	357.4	355.9
65°	326.1	325.2	324.2	323.3	322.3	320.9	319.1	317.2	315.3	313.5	311.6
67.5°	279.2	278.4	277.5	276.6	275.8	274.5	272.7	270.8	269.1	267.3	265.5
70°	250.3	249.0	247.6	246.3	245.0	243.6	242.1	240.6	239.1	237.7	236.1
72.5°	219.3	217.9	216.7	215.3	214.0	212.8	211.6	210.3	209.1	207.9	206.8
75°	173.6	172.6	171.7	170.8	169.8	168.9	167.9	167.0	166.1	165.2	164.4
77.5°	129.9	129.5	129.1	128.7	128.3	127.7	126.8	126.0	125.2	124.4	124.1
80°	103.6	103.1	102.5	102.0	101.4	100.9	100.5	100.2	99.8	99.4	99.0
82.5°	78.0	77.8	77.5	77.2	77.0	76.8	76.8	76.7	76.6	76.5	76.3
85°	45.5	45.5	45.5	45.5	45.5	45.3	44.9	44.6	44.2	43.8	43.8
87.5°	18.1	18.4	18.7	19.0	19.3	19.5	19.7	19.9	20.0	20.2	20.4
90°	2.8	5.0	7.3	9.5	11.7	13.7	15.4	17.0	18.6	20.3	21.5
92.5°	19.7	22.3	24.9	27.4	30.0	31.8	33.0	34.1	35.3	36.4	37.2
95°	55.2	57.0	58.9	60.8	62.6	64.2	65.7	67.1	68.5	69.9	70.6
97.5°	96.5	97.9	99.4	100.8	102.3	103.9	105.6	107.3	108.9	110.6	111.4
100°	128.9	129.7	130.5	131.3	132.1	133.5	135.3	137.1	138.9	140.9	141.2
102.5°	162.7	163.0	163.3	163.7	164.1	165.0	166.7	168.4	170.1	171.7	172.3
105°	214.4	214.7	214.8	215.1	215.2	215.8	216.6	217.4	218.2	219.0	219.7
107.5°	268.7	269.0	269.3	269.5	269.7	269.9	270.1	270.1	270.3	270.4	271.0
110°	305.5	305.9	306.3	306.8	307.2	307.3	307.1	306.9	306.7	306.5	306.1



TEST NUMBER: P332623-927

CATALOG NUMBER: S124DIP-S795D1205U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.8	344.0	344.0	344.1	344.2	344.0	343.6	343.3	342.9	342.5	342.5
115°	401.2	401.2	401.2	401.2	401.2	401.1	400.7	400.3	399.8	399.4	399.3
117.5°	455.4	455.6	455.7	455.9	456.1	456.0	455.7	455.4	455.1	454.9	454.2
120°	491.5	492.3	493.1	493.9	494.7	494.9	494.2	493.6	493.0	492.4	491.4
122.5°	529.0	529.3	529.7	530.0	530.4	530.4	530.0	529.8	529.5	529.2	528.5
125°	584.4	584.4	584.4	584.4	584.4	584.3	584.2	583.9	583.7	583.5	583.1
127.5°	634.7	635.3	635.9	636.5	637.2	637.3	636.9	636.6	636.3	636.0	635.6
130°	670.0	670.7	671.2	671.8	672.5	672.8	672.8	672.8	672.8	672.8	672.4
132.5°	706.1	706.5	707.0	707.4	707.9	708.1	707.9	707.7	707.6	707.4	706.9
135°	753.8	755.0	756.2	757.5	758.7	759.3	759.3	759.3	759.3	759.3	758.9
137.5°	805.6	806.3	806.8	807.4	807.9	808.4	808.7	809.1	809.4	809.7	809.2
140°	840.3	840.7	841.1	841.5	841.9	842.1	842.1	842.1	842.1	842.1	841.9
142.5°	872.0	872.4	872.7	873.1	873.6	873.7	873.5	873.4	873.2	873.1	873.0
145°	915.8	916.6	917.4	918.2	919.0	919.6	919.7	920.0	920.1	920.4	920.1
147.5°	959.2	960.2	961.2	962.1	963.1	963.5	963.4	963.2	963.1	962.9	962.7
150°	985.7	986.5	987.4	988.2	989.0	989.4	989.4	989.4	989.4	989.4	989.4
152.5°	1010.7	1011.2	1011.7	1012.2	1012.7	1013.0	1013.2	1013.4	1013.5	1013.7	1014.2
155°	1049.2	1049.2	1049.2	1049.2	1049.2	1049.1	1048.9	1048.7	1048.5	1048.3	1049.1
157.5°	1081.6	1081.2	1080.9	1080.5	1080.1	1079.9	1079.9	1079.8	1079.8	1079.7	1080.4
160°	1100.7	1100.6	1100.3	1100.1	1099.9	1099.7	1099.5	1099.3	1099.1	1098.9	1099.5
162.5°	1118.4	1117.8	1117.4	1116.8	1116.3	1115.9	1115.7	1115.6	1115.3	1115.1	1116.2
165°	1142.2	1141.5	1140.9	1140.3	1139.7	1139.2	1138.8	1138.4	1138.0	1137.6	1138.8
167.5°	1160.4	1159.5	1158.6	1157.8	1157.0	1156.5	1156.6	1156.6	1156.7	1156.7	1157.9
170°	1170.7	1169.7	1168.6	1167.6	1166.6	1166.2	1166.4	1166.6	1166.8	1167.0	1168.2
172.5°	1178.1	1177.2	1176.3	1175.4	1174.6	1174.2	1174.3	1174.3	1174.3	1174.4	1175.8
175°	1188.2	1187.2	1186.1	1185.1	1184.1	1183.4	1183.3	1183.0	1182.9	1182.6	1184.1
177.5°	1191.5	1190.6	1189.9	1189.1	1188.2	1187.8	1187.8	1187.8	1187.8	1187.8	1189.0
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0



TEST NUMBER: P332623-927

CATALOG NUMBER: S124DIP-S795D1205U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6	1051.6
2.5°	1047.8	1049.3	1050.8	1051.5	1051.4	1051.2	1051.1	1050.9
5°	1042.2	1044.3	1046.3	1047.2	1046.8	1046.5	1046.1	1045.7
7.5°	1030.6	1032.3	1033.9	1034.6	1034.4	1034.2	1034.0	1033.7
10°	1020.9	1022.4	1023.9	1024.5	1024.1	1023.7	1023.3	1022.9
12.5°	1009.1	1010.7	1012.3	1012.9	1012.4	1011.9	1011.3	1010.8
15°	986.4	987.5	988.6	989.0	988.4	987.9	987.3	986.7
17.5°	960.7	961.4	962.1	962.3	961.9	961.5	961.2	960.8
20°	941.5	942.1	942.6	942.7	942.3	942.0	941.6	941.2
22.5°	921.5	922.5	923.5	923.7	923.0	922.3	921.6	921.0
25°	888.5	888.7	888.9	888.6	887.9	887.1	886.4	885.6
27.5°	851.5	851.0	850.6	849.9	849.0	848.0	847.1	846.1
30°	825.9	825.2	824.4	823.6	822.7	821.7	820.8	819.9
32.5°	800.0	799.2	798.3	797.3	796.4	795.4	794.5	793.6
35°	759.1	757.8	756.5	755.3	754.4	753.5	752.6	751.6
37.5°	716.2	714.8	713.4	712.1	710.8	709.6	708.4	707.1
40°	686.3	684.5	682.6	681.2	680.2	679.4	678.4	677.5
42.5°	657.4	655.3	653.1	651.7	651.1	650.5	649.8	649.2
45°	612.7	610.6	608.6	607.3	606.7	606.1	605.5	605.0
47.5°	569.3	567.0	564.7	562.8	561.4	560.0	558.6	557.1
50°	539.1	536.5	533.9	532.0	530.8	529.7	528.6	527.5
52.5°	508.0	505.6	503.4	501.5	500.1	498.7	497.3	495.8
55°	462.3	460.1	457.8	456.1	455.0	453.9	452.7	451.6
57.5°	416.5	414.4	412.3	410.7	409.6	408.4	407.4	406.3
60°	385.1	383.4	381.7	380.4	379.5	378.5	377.6	376.7
62.5°	354.3	352.8	351.3	350.1	349.1	348.2	347.3	346.3
65°	309.7	307.8	305.9	304.6	303.6	302.7	301.7	300.8
67.5°	263.7	261.9	260.1	259.0	258.8	258.6	258.3	258.0
70°	234.6	233.1	231.6	230.6	230.0	229.5	228.9	228.4
72.5°	205.6	204.4	203.2	202.3	201.7	201.1	200.6	200.0
75°	163.7	162.9	162.2	161.7	161.5	161.3	161.1	161.0
77.5°	123.9	123.7	123.5	123.1	122.6	122.2	121.7	121.2
80°	98.7	98.3	97.9	97.7	97.4	97.3	97.1	96.9
82.5°	76.0	75.8	75.6	75.4	75.3	75.0	74.9	74.6
85°	43.8	43.8	43.8	43.7	43.6	43.3	43.2	42.9
87.5°	20.8	21.0	21.2	21.4	21.5	21.5	21.6	21.7
90°	22.7	23.9	25.2	26.0	26.4	26.8	27.2	27.6
92.5°	37.9	38.7	39.4	39.8	40.2	40.4	40.6	40.9
95°	71.1	71.8	72.4	72.7	72.7	72.7	72.7	72.7
97.5°	112.1	112.8	113.6	113.9	113.9	113.9	113.9	113.9
100°	141.6	142.0	142.4	142.7	142.7	142.7	142.7	142.7
102.5°	172.9	173.5	174.0	174.4	174.6	174.8	174.9	175.1
105°	220.3	220.9	221.5	222.1	222.8	223.3	223.9	224.6
107.5°	271.6	272.1	272.7	273.0	272.9	272.9	272.8	272.8
110°	305.6	305.2	304.8	304.9	305.5	306.2	306.8	307.4





TEST NUMBER: P332623-927

CATALOG NUMBER: S124DIP-S795D1205U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	342.4	342.3	342.2	342.2	342.4	342.5	342.6	342.8
115°	399.0	398.8	398.6	398.4	398.2	398.0	397.8	397.6
117.5°	453.4	452.7	452.0	451.5	451.1	450.7	450.3	449.9
120°	490.4	489.3	488.3	488.0	488.4	488.8	489.3	489.6
122.5°	527.8	527.1	526.4	525.7	525.0	524.3	523.5	522.8
125°	582.7	582.3	581.9	581.5	581.1	580.7	580.2	579.8
127.5°	635.2	634.8	634.3	634.0	633.7	633.3	633.0	632.6
130°	671.9	671.5	671.1	670.5	669.7	668.9	668.0	667.3
132.5°	706.5	706.2	705.8	705.4	705.0	704.7	704.4	704.1
135°	758.5	758.0	757.6	757.2	756.5	755.9	755.3	754.7
137.5°	808.7	808.1	807.6	807.4	807.6	807.6	807.8	807.9
140°	841.7	841.5	841.3	841.1	840.9	840.7	840.5	840.3
142.5°	873.0	872.9	872.9	872.8	872.8	872.7	872.7	872.7
145°	920.0	919.7	919.6	919.1	918.5	917.9	917.3	916.7
147.5°	962.6	962.4	962.2	962.0	961.9	961.6	961.4	961.2
150°	989.4	989.4	989.4	989.3	989.0	988.9	988.6	988.5
152.5°	1014.6	1015.2	1015.7	1015.7	1015.1	1014.5	1014.0	1013.5
155°	1050.0	1050.8	1051.5	1051.5	1050.8	1050.0	1049.1	1048.3
157.5°	1081.0	1081.6	1082.2	1082.2	1081.5	1080.8	1080.1	1079.4
160°	1100.1	1100.7	1101.4	1101.1	1100.1	1099.1	1098.1	1097.1
162.5°	1117.3	1118.4	1119.5	1119.6	1118.6	1117.5	1116.5	1115.5
165°	1140.0	1141.2	1142.5	1142.6	1141.9	1141.1	1140.2	1139.4
167.5°	1159.1	1160.4	1161.6	1161.6	1160.3	1159.0	1157.8	1156.5
170°	1169.5	1170.7	1172.0	1171.8	1170.4	1168.9	1167.5	1166.1
172.5°	1177.2	1178.5	1180.0	1180.0	1178.5	1177.0	1175.6	1174.2
175°	1185.5	1186.9	1188.4	1188.4	1186.9	1185.5	1184.1	1182.6
177.5°	1190.1	1191.3	1192.4	1192.3	1191.0	1189.7	1188.4	1187.1
180°	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0	1190.0

(END OF REPORT)