

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332982-935

Luminaire Tested: **S124RDIP-S1020D1205U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332982-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1020D1205U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7733.4 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332982-935

CATALOG NUMBER: S124RDIP-S1020D1205U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332982-935

CATALOG NUMBER: S124RDIP-S1020D1205U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	46
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45	40
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	42	40	38	34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	34	33	31	29	25
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	27	24	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	26	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12551	12551	12551
5°	12580	12426	12503
10°	12500	12276	12276
15°	12357	12018	11929
20°	12160	11679	11465
25°	11908	11282	10996
30°	11663	10864	10409
35°	11392	10430	9819
40°	11065	9936	9183
45°	10764	9445	8535
50°	10420	8881	7850
55°	10054	8294	7104
60°	9649	7650	6344
65°	9278	6844	5593
70°	8738	5958	4749
75°	8057	4938	3862
80°	7029	3761	3543
85°	5956	3418	3196



TEST NUMBER: P332982-935

CATALOG NUMBER: S124RDIP-S1020D1205U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	1.9
10°-20°	407.3	5.3
20°-30°	588.1	7.6
30°-40°	666.6	8.6
40°-50°	643.7	8.3
50°-60°	535.3	6.9
60°-70°	369.6	4.8
70°-80°	187.4	2.4
80°-90°	51.9	0.7
90°-100°	45.8	0.6
100°-110°	291.7	3.8
110°-120°	558.0	7.2
120°-130°	708.4	9.2
130°-140°	757.9	9.8
140°-150°	708.7	9.2
150°-160°	571.5	7.4
160°-170°	368.6	4.8
170°-180°	127.0	1.6
0°-30°	1141.4	14.8
0°-40°	1808.0	23.4
0°-60°	2987.0	38.6
0°-90°	3595.8	46.5
90°-120°	895.4	11.6
90°-150°	3070.4	39.7
90°-180°	4138.0	53.5
0°-180°	7733.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1555	1555	1555	1555	1555	
5°	1552	1547	1533	1544	1543	147
15°	1478	1467	1438	1435	1427	416
25°	1337	1314	1267	1247	1234	616
35°	1156	1117	1058	1019	996	722
45°	943	897	827	771	748	727
55°	714	665	589	530	505	639
65°	486	433	358	309	293	479
75°	258	214	158	132	124	273
85°	64	42	37	35	34	72
90°	3	14	22	28	30	6
95°	55	23	22	28	29	71
105°	301	307	312	319	285	315
115°	562	565	564	566	566	553
125°	790	794	792	795	796	705
135°	980	980	983	985	987	755
145°	1130	1133	1134	1135	1136	706
155°	1240	1240	1238	1241	1238	571
165°	1308	1303	1303	1310	1302	369
175°	1338	1332	1333	1340	1330	127
180°	1338	1338	1338	1338	1338	



TEST NUMBER: P332982-935

CATALOG NUMBER: S124RDIP-S1020D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1558.5	1557.6	1556.8	1556.0	1555.1	1553.5	1551.2	1548.9	1546.5	1544.2	1546.5
5°	1552.3	1551.3	1550.2	1549.1	1548.1	1545.9	1542.8	1539.6	1536.5	1533.3	1535.9
7.5°	1538.3	1537.1	1536.0	1534.9	1533.8	1531.2	1527.1	1522.9	1518.8	1514.7	1516.4
10°	1524.9	1523.6	1522.2	1521.0	1519.7	1516.6	1511.8	1507.1	1502.3	1497.5	1498.6
12.5°	1507.8	1506.2	1504.7	1503.2	1501.7	1498.1	1492.5	1486.9	1481.3	1475.7	1476.3
15°	1478.5	1476.1	1473.8	1471.4	1469.0	1464.5	1457.8	1451.2	1444.7	1438.0	1437.5
17.5°	1443.0	1439.6	1436.1	1432.7	1429.3	1423.6	1415.7	1407.7	1399.8	1391.8	1390.3
20°	1415.4	1412.0	1408.5	1405.1	1401.6	1395.4	1386.5	1377.4	1368.5	1359.4	1357.4
22.5°	1384.9	1381.0	1377.2	1373.4	1369.5	1362.7	1353.1	1343.5	1333.9	1324.2	1321.0
25°	1336.9	1332.1	1327.3	1322.6	1317.8	1310.0	1299.2	1288.3	1277.5	1266.6	1262.1
27.5°	1286.3	1280.4	1274.5	1268.4	1262.5	1253.7	1242.1	1230.5	1218.9	1207.3	1201.8
30°	1251.1	1244.5	1237.9	1231.3	1224.7	1215.1	1202.7	1190.2	1177.8	1165.4	1158.8
32.5°	1214.0	1206.5	1199.0	1191.6	1184.1	1174.0	1161.1	1148.3	1135.4	1122.6	1114.9
35°	1155.9	1147.5	1138.9	1130.5	1122.1	1111.2	1097.9	1084.8	1071.5	1058.3	1049.3
37.5°	1093.7	1085.0	1076.3	1067.6	1058.9	1047.1	1032.5	1017.9	1003.2	988.5	978.4
40°	1050.0	1041.2	1032.5	1023.7	1015.0	1003.2	988.1	972.9	957.9	942.8	931.7
42.5°	1008.1	998.9	989.7	980.6	971.5	959.0	943.3	927.6	911.9	896.1	884.8
45°	942.8	933.1	923.3	913.4	903.6	890.8	874.9	859.1	843.2	827.3	814.4
47.5°	875.5	865.3	855.2	845.2	835.0	821.7	805.2	788.7	772.1	755.7	742.3
50°	829.7	819.4	809.1	798.7	788.4	774.8	757.9	741.0	724.0	707.1	693.9
52.5°	783.1	772.9	762.8	752.8	742.6	728.9	711.5	694.2	676.8	659.5	646.1
55°	714.3	703.7	693.1	682.5	671.9	658.1	640.8	623.6	606.5	589.3	575.5
57.5°	646.2	635.2	624.1	613.1	602.2	588.1	571.3	554.3	537.4	520.5	506.5
60°	597.6	587.0	576.4	565.8	555.3	541.5	524.6	507.6	490.7	473.8	460.0
62.5°	553.8	542.8	531.8	520.7	509.8	495.6	478.2	460.9	443.5	426.2	413.5
65°	485.7	474.3	463.0	451.6	440.2	426.0	409.1	392.2	375.2	358.3	347.0
67.5°	415.0	404.1	393.2	382.3	371.3	358.1	342.3	326.7	310.9	295.2	285.4
70°	370.2	359.1	348.0	336.9	325.8	312.7	297.6	282.5	267.4	252.4	243.7
72.5°	322.6	312.5	302.5	292.5	282.4	270.3	256.1	241.8	227.6	213.4	205.9
75°	258.3	248.6	238.8	228.9	219.2	208.0	195.6	183.2	170.7	158.3	152.2
77.5°	193.1	184.8	176.5	168.2	159.9	150.7	140.6	130.6	120.5	110.5	106.9
80°	151.2	143.5	135.9	128.2	120.5	112.7	104.8	96.9	88.9	80.9	80.2
82.5°	115.0	108.0	100.9	93.8	86.9	81.0	76.5	72.0	67.4	62.9	62.3
85°	64.3	59.0	53.7	48.4	43.1	40.0	39.3	38.5	37.7	36.9	36.3
87.5°	22.5	21.3	20.1	18.9	17.7	17.1	17.3	17.5	17.6	17.7	17.8
90°	3.0	5.4	7.9	10.3	12.7	14.9	16.7	18.4	20.2	22.0	23.3
92.5°	12.6	12.7	12.9	13.0	13.2	14.1	15.8	17.7	19.5	21.2	22.6
95°	55.0	47.4	39.9	32.4	24.8	21.1	21.4	21.5	21.8	22.0	23.3
97.5°	116.8	121.6	126.3	131.0	135.7	125.6	100.8	76.0	51.2	26.4	26.5
100°	164.1	168.1	172.1	176.1	180.1	166.8	136.0	105.4	74.7	44.0	40.2
102.5°	216.9	219.8	222.7	225.7	228.6	228.1	224.1	220.1	216.1	212.1	171.3
105°	301.1	302.5	303.8	305.1	306.4	307.7	308.8	309.9	311.0	312.1	314.2
107.5°	379.4	380.0	380.7	381.3	382.0	383.1	384.6	386.2	387.6	389.2	390.1
110°	432.2	432.8	433.5	434.2	434.9	435.8	437.2	438.5	439.9	441.2	441.6



TEST NUMBER: P332982-935

CATALOG NUMBER: S124RDIP-S1020D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.5	484.7	485.8	487.0	488.2	489.1	489.7	490.3	491.0	491.6	491.5
115°	562.2	562.9	563.6	564.2	564.9	565.2	564.9	564.7	564.5	564.2	564.7
117.5°	633.3	634.1	635.1	635.9	636.8	637.5	638.0	638.5	639.0	639.5	639.4
120°	681.3	682.2	683.1	684.0	684.8	685.2	685.0	684.8	684.5	684.3	684.8
122.5°	726.1	726.7	727.2	727.7	728.2	728.7	729.0	729.3	729.6	730.0	730.2
125°	790.3	791.3	792.1	793.0	793.9	794.1	793.7	793.2	792.8	792.4	793.0
127.5°	851.2	851.4	851.6	851.9	852.0	852.6	853.7	854.7	855.7	856.8	856.6
130°	890.4	890.6	890.9	891.0	891.3	891.7	892.4	893.0	893.7	894.4	894.6
132.5°	926.4	926.8	927.2	927.6	928.0	928.7	929.4	930.3	931.2	932.0	932.2
135°	980.4	980.2	980.0	979.7	979.6	979.9	980.8	981.6	982.6	983.4	983.9
137.5°	1028.3	1028.4	1028.5	1028.6	1028.6	1029.2	1030.1	1031.1	1032.1	1033.0	1033.5
140°	1059.5	1059.9	1060.3	1060.8	1061.3	1061.7	1062.1	1062.6	1063.0	1063.5	1064.1
142.5°	1087.4	1088.3	1089.1	1089.9	1090.7	1091.2	1091.5	1091.7	1092.0	1092.3	1092.8
145°	1130.5	1131.2	1131.9	1132.5	1133.2	1133.5	1133.5	1133.5	1133.5	1133.5	1133.8
147.5°	1164.7	1166.0	1167.2	1168.5	1169.7	1170.2	1170.0	1169.8	1169.5	1169.3	1169.5
150°	1189.6	1190.4	1191.3	1192.2	1193.1	1193.4	1193.2	1193.0	1192.7	1192.5	1192.5
152.5°	1210.3	1211.1	1211.8	1212.5	1213.1	1213.3	1213.0	1212.5	1212.1	1211.8	1212.1
155°	1239.6	1239.8	1240.0	1240.2	1240.4	1240.2	1239.6	1238.9	1238.2	1237.5	1238.5
157.5°	1264.1	1264.0	1263.9	1263.8	1263.6	1263.2	1262.4	1261.7	1260.9	1260.2	1261.3
160°	1278.6	1277.9	1277.2	1276.6	1275.9	1275.5	1275.2	1275.0	1274.8	1274.5	1275.9
162.5°	1291.3	1290.6	1289.7	1288.8	1288.0	1287.5	1287.2	1287.0	1286.8	1286.6	1287.9
165°	1307.6	1306.5	1305.4	1304.2	1303.1	1302.6	1302.6	1302.6	1302.6	1302.6	1304.3
167.5°	1320.3	1319.2	1318.1	1316.9	1315.8	1315.1	1315.0	1314.8	1314.7	1314.6	1316.6
170°	1327.6	1326.3	1324.9	1323.6	1322.2	1321.7	1321.9	1322.2	1322.3	1322.6	1324.4
172.5°	1332.4	1331.0	1329.7	1328.4	1327.1	1326.5	1326.7	1327.0	1327.1	1327.4	1329.1
175°	1337.6	1336.3	1334.9	1333.6	1332.2	1331.7	1331.9	1332.1	1332.4	1332.6	1334.6
177.5°	1340.0	1338.8	1337.5	1336.3	1335.0	1334.6	1334.9	1335.2	1335.7	1336.0	1337.4
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332982-935

CATALOG NUMBER: S124RDIP-S1020D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7	1554.7
2.5°	1548.9	1551.2	1553.5	1554.6	1554.4	1554.2	1553.9	1553.8
5°	1538.5	1541.2	1543.9	1544.9	1544.4	1543.9	1543.3	1542.8
7.5°	1518.1	1519.8	1521.5	1521.9	1521.0	1520.2	1519.3	1518.5
10°	1499.7	1500.7	1501.8	1501.8	1500.7	1499.7	1498.6	1497.5
12.5°	1476.9	1477.6	1478.2	1477.7	1476.3	1474.8	1473.3	1471.9
15°	1437.0	1436.4	1435.9	1434.7	1432.9	1431.0	1429.2	1427.3
17.5°	1388.9	1387.4	1386.0	1383.8	1381.0	1378.2	1375.4	1372.5
20°	1355.2	1353.1	1351.0	1348.2	1344.8	1341.4	1337.9	1334.5
22.5°	1317.8	1314.7	1311.6	1308.5	1305.7	1303.0	1300.1	1297.4
25°	1257.6	1253.1	1248.6	1245.0	1242.4	1239.8	1237.1	1234.5
27.5°	1196.2	1190.7	1185.1	1180.4	1176.6	1172.8	1169.0	1165.2
30°	1152.2	1145.6	1138.9	1133.5	1129.3	1125.1	1120.8	1116.6
32.5°	1107.2	1099.6	1091.9	1086.1	1082.0	1078.0	1074.0	1070.0
35°	1040.3	1031.3	1022.3	1015.5	1010.6	1005.9	1001.2	996.3
37.5°	968.5	958.4	948.3	940.9	936.2	931.3	926.6	921.9
40°	920.6	909.5	898.4	890.4	885.7	880.9	876.2	871.4
42.5°	873.5	862.2	850.8	842.7	837.8	832.8	827.8	822.9
45°	801.4	788.4	775.5	766.6	761.9	757.1	752.3	747.6
47.5°	728.8	715.4	701.9	692.6	687.3	682.1	676.8	671.7
50°	680.6	667.4	654.2	645.1	640.1	635.0	630.0	625.0
52.5°	632.6	619.1	605.7	596.4	591.2	585.9	580.7	575.5
55°	561.7	548.0	534.3	524.9	519.8	514.8	509.8	504.7
57.5°	492.5	478.5	464.6	455.7	451.9	448.1	444.3	440.5
60°	446.3	432.5	418.8	409.7	405.5	401.3	397.1	392.9
62.5°	400.8	388.1	375.4	367.3	363.9	360.6	357.1	353.8
65°	335.5	324.2	312.8	305.6	302.4	299.2	296.0	292.8
67.5°	275.6	265.9	256.1	249.4	245.9	242.5	238.9	235.5
70°	234.9	226.2	217.5	211.7	209.1	206.5	203.8	201.2
72.5°	198.4	191.0	183.5	178.6	176.1	173.7	171.3	168.8
75°	146.2	140.1	134.0	130.2	128.5	127.0	125.4	123.8
77.5°	103.4	99.9	96.3	94.3	93.8	93.3	92.8	92.4
80°	79.4	78.6	77.7	77.2	77.0	76.7	76.5	76.2
82.5°	61.6	61.1	60.5	60.1	59.8	59.6	59.3	59.1
85°	35.8	35.3	34.8	34.5	34.5	34.5	34.5	34.5
87.5°	17.8	17.9	18.0	18.2	18.4	18.8	19.0	19.4
90°	24.7	26.0	27.4	28.2	28.7	29.1	29.5	30.0
92.5°	23.8	25.2	26.5	27.3	27.4	27.5	27.6	27.6
95°	24.7	26.0	27.4	28.2	28.3	28.6	28.8	29.0
97.5°	26.7	26.8	26.9	27.1	27.4	27.6	27.8	28.0
100°	36.4	32.7	28.9	27.1	27.4	27.6	27.8	28.0
102.5°	130.5	89.8	49.0	28.7	28.7	28.8	28.8	28.8
105°	316.2	318.1	320.1	317.1	309.1	301.1	293.2	285.2
107.5°	391.2	392.1	393.0	394.0	394.9	395.7	396.5	397.4
110°	442.1	442.6	443.0	443.5	444.2	444.9	445.6	446.2



TEST NUMBER: P332982-935

CATALOG NUMBER: S124RDIP-S1020D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	491.5	491.4	491.3	491.6	492.5	493.4	494.2	495.0
115°	565.2	565.6	566.0	566.3	566.3	566.3	566.3	566.3
117.5°	639.3	639.2	639.1	639.0	638.9	638.9	638.8	638.7
120°	685.2	685.6	686.0	686.0	685.6	685.2	684.8	684.3
122.5°	730.5	730.7	731.0	730.9	730.5	730.0	729.5	729.1
125°	793.7	794.4	795.0	795.5	795.7	795.9	796.2	796.3
127.5°	856.5	856.4	856.3	856.1	855.9	855.7	855.6	855.4
130°	894.8	895.1	895.3	895.4	895.4	895.4	895.4	895.4
132.5°	932.5	932.7	932.9	932.9	932.7	932.5	932.4	932.2
135°	984.3	984.7	985.2	985.7	986.1	986.5	987.0	987.4
137.5°	1034.1	1034.5	1035.0	1035.2	1035.1	1034.9	1034.7	1034.7
140°	1064.8	1065.5	1066.2	1066.6	1066.8	1067.0	1067.2	1067.5
142.5°	1093.3	1093.7	1094.2	1094.5	1094.6	1094.6	1094.7	1094.7
145°	1133.9	1134.2	1134.4	1134.7	1135.1	1135.6	1136.1	1136.5
147.5°	1169.7	1169.8	1170.0	1170.2	1170.4	1170.7	1170.9	1171.1
150°	1192.5	1192.5	1192.5	1192.7	1192.8	1193.1	1193.3	1193.5
152.5°	1212.5	1212.8	1213.1	1213.2	1213.1	1213.0	1212.9	1212.7
155°	1239.3	1240.2	1241.1	1241.2	1240.5	1239.8	1239.2	1238.5
157.5°	1262.5	1263.6	1264.8	1264.8	1263.6	1262.5	1261.3	1260.2
160°	1277.2	1278.6	1279.9	1279.9	1278.6	1277.2	1275.9	1274.5
162.5°	1289.3	1290.6	1291.9	1291.8	1290.3	1288.8	1287.3	1285.7
165°	1306.1	1307.9	1309.7	1309.6	1307.6	1305.5	1303.6	1301.6
167.5°	1318.5	1320.4	1322.4	1322.2	1320.1	1317.8	1315.6	1313.4
170°	1326.1	1327.9	1329.7	1329.5	1327.2	1325.0	1322.8	1320.6
172.5°	1330.9	1332.7	1334.5	1334.2	1331.8	1329.4	1327.0	1324.6
175°	1336.6	1338.6	1340.6	1340.2	1337.6	1334.9	1332.2	1329.6
177.5°	1338.9	1340.2	1341.7	1341.4	1339.2	1337.0	1334.9	1332.8
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6

(END OF REPORT)