

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332894-927

Luminaire Tested: **S124RDIP-S350D1205U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332894-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D1205U927-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4541.7 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332894-927

CATALOG NUMBER: S124RDIP-S350D1205U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332894-927

CATALOG NUMBER: S124RDIP-S350D1205U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	29	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	26	21	19	18	13
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	15	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	10
7	55	43	35	30	48	39	32	27	30	26	22	23	20	17	15	14	12	9
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3953	3953	3953
5°	3962	3914	3938
10°	3937	3867	3867
15°	3892	3786	3758
20°	3830	3679	3611
25°	3751	3553	3463
30°	3674	3422	3278
35°	3588	3286	3094
40°	3485	3130	2893
45°	3391	2975	2689
50°	3282	2798	2473
55°	3167	2612	2238
60°	3039	2409	1997
65°	2923	2157	1761
70°	2752	1876	1496
75°	2539	1556	1216
80°	2213	1186	1116
85°	1880	1074	1010



TEST NUMBER: P332894-927

CATALOG NUMBER: S124RDIP-S350D1205U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.0
10°-20°	128.3	2.8
20°-30°	185.2	4.1
30°-40°	210.0	4.6
40°-50°	202.8	4.5
50°-60°	168.6	3.7
60°-70°	116.4	2.6
70°-80°	59.0	1.3
80°-90°	17.7	0.4
90°-100°	338.4	7.5
100°-110°	704.3	15.5
110°-120°	630.9	13.9
120°-130°	530.7	11.7
130°-140°	442.5	9.7
140°-150°	338.0	7.4
150°-160°	237.6	5.2
160°-170°	139.8	3.1
170°-180°	45.5	1.0
0°-30°	359.5	7.9
0°-40°	569.5	12.5
0°-60°	940.8	20.7
0°-90°	1134.0	25.0
90°-120°	1673.6	36.9
90°-150°	2984.8	65.7
90°-180°	3408.0	75.0
0°-180°	4541.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	490	490	490	490	490	
5°	489	487	483	486	486	46
15°	466	462	453	452	450	131
25°	421	414	399	393	389	194
35°	364	352	333	321	314	227
45°	297	283	261	243	236	229
55°	225	209	186	167	159	201
65°	153	136	113	97	92	151
75°	81	67	50	42	39	86
85°	20	13	12	11	11	23
90°	1	7	17	18	19	3
95°	30	96	750	371	225	34
105°	108	156	604	1300	1295	115
115°	190	238	538	1035	1244	188
125°	264	314	536	880	992	235
135°	314	374	531	782	887	243
145°	362	414	528	659	724	227
155°	412	444	514	582	607	190
165°	448	462	492	522	529	127
175°	468	469	472	479	477	44
180°	469	469	469	469	469	



TEST NUMBER: P332894-927

CATALOG NUMBER: S124RDIP-S350D1205U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	490.9	490.6	490.4	490.1	489.8	489.3	488.6	487.9	487.1	486.4	487.1
5°	488.9	488.6	488.3	488.0	487.6	487.0	485.9	485.0	483.9	483.0	483.8
7.5°	484.5	484.2	483.9	483.5	483.2	482.3	481.0	479.7	478.4	477.1	477.6
10°	480.3	479.9	479.5	479.1	478.6	477.7	476.2	474.7	473.2	471.7	472.1
12.5°	474.9	474.4	474.0	473.5	473.0	471.9	470.1	468.3	466.6	464.8	465.0
15°	465.7	464.9	464.2	463.4	462.7	461.3	459.2	457.1	455.0	453.0	452.8
17.5°	454.6	453.4	452.3	451.3	450.2	448.4	445.9	443.4	440.9	438.4	437.9
20°	445.8	444.7	443.7	442.6	441.5	439.6	436.7	433.9	431.0	428.2	427.5
22.5°	436.3	435.0	433.8	432.6	431.3	429.2	426.2	423.2	420.2	417.1	416.1
25°	421.1	419.6	418.1	416.6	415.1	412.6	409.2	405.8	402.3	398.9	397.5
27.5°	405.2	403.3	401.4	399.6	397.7	394.9	391.3	387.6	384.0	380.3	378.5
30°	394.1	392.0	389.9	387.9	385.8	382.8	378.8	374.9	371.0	367.1	365.0
32.5°	382.4	380.0	377.7	375.3	373.0	369.8	365.8	361.7	357.7	353.6	351.2
35°	364.1	361.4	358.8	356.1	353.4	350.0	345.9	341.7	337.5	333.4	330.5
37.5°	344.5	341.7	339.1	336.3	333.5	329.9	325.2	320.6	316.0	311.4	308.2
40°	330.7	328.0	325.2	322.5	319.7	316.0	311.2	306.5	301.7	297.0	293.5
42.5°	317.5	314.7	311.7	308.9	306.0	302.1	297.1	292.2	287.2	282.3	278.7
45°	297.0	293.9	290.8	287.7	284.6	280.6	275.6	270.6	265.6	260.6	256.5
47.5°	275.8	272.6	269.4	266.2	263.0	258.8	253.7	248.4	243.2	238.1	233.8
50°	261.3	258.1	254.8	251.6	248.3	244.1	238.8	233.4	228.1	222.8	218.6
52.5°	246.7	243.4	240.3	237.1	233.9	229.6	224.1	218.6	213.2	207.7	203.5
55°	225.0	221.7	218.3	215.0	211.7	207.2	201.8	196.5	191.0	185.6	181.3
57.5°	203.5	200.0	196.6	193.1	189.6	185.3	179.9	174.6	169.3	163.9	159.5
60°	188.2	184.9	181.6	178.2	174.9	170.6	165.2	159.9	154.6	149.2	144.9
62.5°	174.4	171.0	167.5	164.1	160.6	156.1	150.7	145.2	139.7	134.3	130.2
65°	153.0	149.4	145.8	142.3	138.6	134.2	128.9	123.5	118.2	112.9	109.3
67.5°	130.7	127.3	123.8	120.4	117.0	112.8	107.8	102.9	97.9	93.0	89.9
70°	116.6	113.1	109.6	106.2	102.6	98.5	93.7	89.0	84.2	79.5	76.8
72.5°	101.6	98.5	95.3	92.1	89.0	85.2	80.6	76.1	71.7	67.2	64.9
75°	81.4	78.3	75.2	72.1	69.0	65.5	61.6	57.7	53.8	49.9	47.9
77.5°	60.8	58.2	55.6	53.0	50.4	47.5	44.3	41.1	37.9	34.8	33.7
80°	47.6	45.2	42.8	40.4	37.9	35.5	33.0	30.5	28.0	25.5	25.3
82.5°	36.2	34.0	31.8	29.5	27.3	25.5	24.1	22.7	21.2	19.8	19.6
85°	20.3	18.6	17.0	15.2	13.5	12.6	12.4	12.1	11.9	11.6	11.5
87.5°	7.1	6.9	7.0	6.6	6.3	5.9	7.0	6.9	7.2	7.5	7.3
90°	1.0	2.8	5.5	6.4	7.4	7.4	12.9	12.9	14.7	16.6	15.7
92.5°	10.5	15.3	23.9	35.2	48.6	67.7	114.5	185.9	255.6	292.0	243.2
95°	30.3	33.1	42.4	54.3	76.4	115.1	195.1	346.1	566.1	750.2	771.4
97.5°	54.5	54.5	62.4	73.4	92.4	124.8	186.5	311.2	529.8	790.2	969.2
100°	69.9	69.9	76.4	87.5	105.0	134.4	188.7	292.7	480.5	740.1	975.7
102.5°	84.7	86.2	91.9	102.2	118.9	146.9	196.1	287.6	447.3	677.5	920.5
105°	107.7	110.4	115.1	126.1	142.7	169.4	213.6	289.9	418.8	603.9	820.1
107.5°	133.1	134.9	139.6	151.3	167.2	193.5	234.0	303.6	413.7	562.6	739.2
110°	150.0	151.9	156.5	167.5	184.1	209.0	249.5	313.9	415.2	548.7	698.7



TEST NUMBER: P332894-927

CATALOG NUMBER: S124RDIP-S350D1205U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	166.3	168.1	173.4	183.7	200.3	225.1	264.2	325.0	419.5	542.0	675.8
115°	189.6	192.4	198.8	208.0	225.5	250.4	287.2	342.5	428.0	538.5	654.5
117.5°	213.9	216.5	222.2	232.3	248.7	274.5	309.5	360.3	437.0	537.6	644.9
120°	230.1	232.0	238.4	248.5	264.2	289.9	325.0	372.8	443.7	537.6	639.8
122.5°	244.9	246.7	253.2	262.5	279.6	304.7	339.7	384.6	450.4	536.9	633.9
125°	264.2	267.8	273.4	283.5	301.0	326.8	359.9	402.3	460.3	535.8	624.1
127.5°	281.3	284.2	290.9	302.5	320.7	346.7	378.7	417.6	468.2	533.7	611.0
130°	290.9	294.5	301.9	315.8	333.2	359.9	391.3	427.1	474.0	533.0	602.9
132.5°	300.5	303.4	313.0	326.1	345.0	370.3	401.6	436.7	479.2	532.3	595.6
135°	313.9	317.6	326.8	342.5	361.8	385.7	416.1	449.2	487.0	531.2	584.6
137.5°	327.3	330.8	341.0	355.8	376.0	398.8	427.1	458.0	491.5	530.9	575.0
140°	336.9	339.7	349.8	365.4	384.8	406.9	434.5	463.9	495.3	530.2	569.8
142.5°	347.2	350.0	359.3	374.3	392.8	414.2	441.1	468.3	498.2	530.2	565.4
145°	361.8	364.6	373.8	386.6	404.1	424.4	448.3	473.2	499.9	528.4	557.9
147.5°	378.1	379.1	387.1	400.4	414.9	433.2	455.7	477.4	500.7	525.1	551.0
150°	388.5	389.4	396.7	407.8	421.6	439.1	459.3	479.6	500.7	522.8	545.9
152.5°	398.0	398.2	405.6	415.9	428.3	444.3	462.3	481.1	499.3	519.2	540.0
155°	411.5	412.4	417.9	427.1	437.3	451.1	466.7	482.4	497.1	513.7	531.2
157.5°	424.5	424.5	429.7	436.9	445.7	456.6	469.8	482.4	494.7	507.9	522.1
160°	432.6	432.6	436.3	442.8	450.1	460.3	471.3	482.4	492.5	503.5	515.5
162.5°	440.0	439.3	442.2	447.9	454.6	462.5	472.8	482.4	490.3	499.1	509.6
165°	448.3	448.3	450.1	454.7	459.3	464.9	473.2	480.5	486.0	492.5	499.9
167.5°	456.6	455.7	456.6	460.1	462.6	466.9	472.9	478.3	481.6	485.8	491.0
170°	460.3	459.3	460.3	463.0	464.9	467.6	472.2	476.8	478.6	481.4	485.1
172.5°	463.9	463.0	463.2	465.2	466.4	468.3	471.5	475.4	475.7	477.0	480.0
175°	467.6	466.7	466.7	467.6	468.6	468.6	470.4	473.2	472.2	472.2	474.0
177.5°	469.3	468.6	467.8	468.6	468.6	468.6	469.3	470.7	469.3	469.3	470.0
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6



TEST NUMBER: P332894-927

CATALOG NUMBER: S124RDIP-S350D1205U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	487.9	488.6	489.3	489.6	489.6	489.6	489.5	489.4
5°	484.7	485.4	486.3	486.6	486.5	486.3	486.1	485.9
7.5°	478.2	478.7	479.3	479.3	479.1	478.9	478.6	478.3
10°	472.4	472.7	473.0	473.0	472.7	472.4	472.1	471.7
12.5°	465.2	465.4	465.6	465.5	465.0	464.5	464.1	463.6
15°	452.7	452.5	452.3	451.9	451.3	450.8	450.2	449.6
17.5°	437.4	437.0	436.6	435.9	435.0	434.1	433.2	432.4
20°	426.9	426.2	425.6	424.7	423.6	422.5	421.4	420.3
22.5°	415.1	414.1	413.1	412.2	411.3	410.4	409.6	408.6
25°	396.1	394.7	393.3	392.2	391.3	390.5	389.7	388.8
27.5°	376.8	375.0	373.3	371.9	370.6	369.4	368.2	367.0
30°	362.9	360.8	358.8	357.0	355.7	354.4	353.1	351.7
32.5°	348.8	346.3	344.0	342.1	340.8	339.5	338.3	337.0
35°	327.6	324.9	322.0	319.9	318.4	316.9	315.4	313.9
37.5°	305.1	301.9	298.7	296.4	294.9	293.3	291.8	290.3
40°	289.9	286.5	283.0	280.5	279.0	277.5	276.0	274.5
42.5°	275.1	271.6	268.0	265.5	263.9	262.3	260.7	259.2
45°	252.5	248.3	244.2	241.5	240.0	238.4	236.9	235.5
47.5°	229.6	225.3	221.1	218.2	216.5	214.8	213.2	211.6
50°	214.4	210.2	206.0	203.2	201.6	200.0	198.4	196.9
52.5°	199.2	195.0	190.8	187.8	186.2	184.6	182.9	181.3
55°	177.0	172.6	168.3	165.3	163.7	162.2	160.6	159.0
57.5°	155.1	150.8	146.3	143.5	142.4	141.2	139.9	138.7
60°	140.5	136.3	131.9	129.0	127.7	126.4	125.1	123.7
62.5°	126.3	122.2	118.3	115.7	114.6	113.6	112.5	111.5
65°	105.7	102.1	98.5	96.3	95.2	94.3	93.2	92.2
67.5°	86.8	83.7	80.6	78.6	77.5	76.4	75.3	74.1
70°	74.0	71.2	68.5	66.7	65.8	65.0	64.2	63.4
72.5°	62.5	60.1	57.8	56.2	55.5	54.7	53.9	53.2
75°	46.0	44.1	42.2	41.0	40.5	40.0	39.5	39.0
77.5°	32.6	31.4	30.3	29.7	29.5	29.4	29.2	29.1
80°	25.0	24.7	24.5	24.3	24.2	24.2	24.1	24.0
82.5°	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6
85°	11.3	11.1	10.9	10.9	10.9	10.9	10.9	10.9
87.5°	7.4	7.5	7.6	7.6	7.8	8.1	8.0	8.1
90°	16.6	17.5	18.4	18.4	19.3	20.3	19.3	19.3
92.5°	180.8	136.0	108.3	89.8	79.0	74.0	70.9	70.9
95°	682.1	539.4	416.1	326.8	281.7	253.2	236.5	224.6
97.5°	1007.8	954.7	864.7	768.7	702.5	647.1	619.5	600.4
100°	1110.2	1128.5	1083.5	1015.3	935.3	879.1	851.5	844.1
102.5°	1105.0	1196.3	1209.3	1181.0	1131.9	1091.2	1062.1	1056.2
105°	1030.9	1190.3	1281.4	1319.1	1321.0	1313.6	1300.7	1295.1
107.5°	925.8	1095.4	1223.8	1305.8	1351.3	1372.3	1381.5	1383.9
110°	862.5	1021.8	1155.2	1256.5	1321.8	1360.5	1377.1	1385.4



TEST NUMBER: P332894-927

CATALOG NUMBER: S124RDIP-S350D1205U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	816.1	957.0	1083.1	1184.3	1258.5	1305.3	1328.5	1342.0
115°	769.5	882.8	990.5	1078.9	1151.6	1206.8	1236.3	1243.6
117.5°	746.7	840.4	925.1	1000.1	1062.1	1108.5	1138.3	1144.0
120°	736.4	822.0	895.6	961.0	1013.5	1054.0	1077.9	1088.1
122.5°	727.5	810.2	877.3	934.5	978.9	1013.5	1033.7	1043.9
125°	712.5	791.6	855.2	905.8	942.6	969.3	986.8	992.3
127.5°	694.0	769.8	833.1	881.1	918.1	941.9	956.6	962.1
130°	679.4	752.1	814.7	863.5	901.2	924.2	938.9	944.4
132.5°	663.8	732.2	793.3	842.1	879.1	905.1	919.0	924.6
135°	642.5	702.3	758.5	804.5	841.4	867.1	881.9	887.4
137.5°	623.2	673.8	721.1	762.7	797.2	822.6	834.7	841.4
140°	612.1	655.4	696.8	735.5	767.7	788.0	800.8	808.2
142.5°	601.8	639.9	675.5	709.0	737.5	756.3	767.7	772.9
145°	587.3	618.6	646.2	672.0	695.0	710.7	719.9	724.5
147.5°	575.4	600.2	622.3	642.5	659.5	672.9	679.9	681.5
150°	568.0	589.1	607.5	624.1	638.8	650.8	656.3	657.3
152.5°	559.8	578.1	595.0	608.6	621.2	630.9	634.2	635.2
155°	547.7	562.4	576.2	587.3	596.5	603.9	606.7	606.7
157.5°	534.6	547.0	558.6	567.4	574.4	580.0	581.6	581.6
160°	526.6	536.6	546.8	554.1	559.7	565.2	566.1	566.1
162.5°	518.4	527.1	535.0	541.6	545.7	551.2	552.2	551.4
165°	507.2	512.7	519.2	523.8	527.4	531.2	530.2	529.3
167.5°	496.4	500.6	505.7	508.5	510.3	512.7	512.5	511.8
170°	489.7	492.5	496.1	498.9	500.7	501.7	500.7	500.7
172.5°	483.8	485.8	488.1	490.0	491.2	492.1	491.2	489.7
175°	475.9	476.8	478.6	478.6	478.6	480.5	478.6	476.8
177.5°	470.7	471.5	471.5	472.2	471.5	472.2	470.7	469.3
180°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6

(END OF REPORT)