

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332911-927

Luminaire Tested: **S124RDIP-S575D810U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332911-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S575D810U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4084.2 lumens  
Efficiency: N/A  
Efficacy: 106.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332911-927

CATALOG NUMBER: S124RDIP-S575D810U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332911-927

CATALOG NUMBER: S124RDIP-S575D810U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	37	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	35	30	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	31	26	46	35	29	24	30	25	21	26	21	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6500	6500	6500
5°	6514	6434	6474
10°	6473	6357	6357
15°	6399	6224	6177
20°	6296	6048	5936
25°	6167	5842	5694
30°	6039	5626	5390
35°	5899	5401	5084
40°	5730	5145	4755
45°	5574	4891	4419
50°	5397	4598	4064
55°	5206	4294	3678
60°	4996	3961	3284
65°	4804	3543	2896
70°	4525	3085	2460
75°	4173	2558	1999
80°	3640	1948	1836
85°	3084	1769	1658



TEST NUMBER: P332911-927

CATALOG NUMBER: S124RDIP-S575D810U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.6	1.9
10°-20°	210.9	5.2
20°-30°	304.5	7.5
30°-40°	345.2	8.5
40°-50°	333.3	8.2
50°-60°	277.2	6.8
60°-70°	191.4	4.7
70°-80°	97.0	2.4
80°-90°	27.3	0.7
90°-100°	52.8	1.3
100°-110°	156.5	3.8
110°-120°	265.6	6.5
120°-130°	350.2	8.6
130°-140°	393.3	9.6
140°-150°	386.4	9.5
150°-160°	325.0	8.0
160°-170°	216.2	5.3
170°-180°	75.7	1.9
0°-30°	591.0	14.5
0°-40°	936.2	22.9
0°-60°	1546.7	37.9
0°-90°	1862.4	45.6
90°-120°	474.9	11.6
90°-150°	1604.7	39.3
90°-180°	2222.0	54.4
0°-180°	4084.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	805	805	805	805	805	
5°	804	801	794	800	799	76
15°	766	760	745	743	739	216
25°	692	680	656	646	639	319
35°	599	578	548	528	516	374
45°	488	465	428	399	387	376
55°	370	344	305	274	261	331
65°	252	224	186	160	152	248
75°	134	111	82	68	64	141
85°	33	22	19	18	18	37
90°	2	9	14	17	19	4
95°	37	43	47	49	49	41
105°	144	145	147	149	151	153
115°	270	270	269	268	268	266
125°	393	393	393	391	390	350
135°	507	511	511	510	508	392
145°	616	619	619	619	617	386
155°	706	706	705	708	705	325
165°	769	767	766	769	767	217
175°	800	797	796	800	796	76
180°	801	801	801	801	801	



TEST NUMBER: P332911-927

CATALOG NUMBER: S124RDIP-S575D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	807.1	806.6	806.2	805.7	805.3	804.5	803.3	802.1	800.8	799.6	800.8
5°	803.8	803.3	802.7	802.2	801.7	800.6	798.9	797.3	795.6	794.0	795.4
7.5°	796.5	796.0	795.4	794.9	794.2	792.9	790.8	788.6	786.5	784.3	785.2
10°	789.6	789.0	788.3	787.6	787.0	785.4	782.9	780.4	777.9	775.5	776.0
12.5°	780.8	780.0	779.2	778.4	777.6	775.8	772.9	769.9	767.1	764.1	764.5
15°	765.6	764.4	763.2	761.9	760.7	758.4	754.9	751.5	748.1	744.7	744.4
17.5°	747.3	745.4	743.7	741.9	740.1	737.2	733.1	729.0	724.8	720.7	720.0
20°	732.9	731.2	729.4	727.6	725.8	722.6	718.0	713.3	708.6	704.0	702.9
22.5°	717.2	715.2	713.2	711.1	709.2	705.7	700.7	695.7	690.7	685.7	684.0
25°	692.3	689.8	687.3	684.8	682.4	678.3	672.7	667.1	661.5	655.9	653.6
27.5°	666.1	663.1	660.0	656.9	653.7	649.2	643.2	637.2	631.2	625.2	622.3
30°	647.8	644.4	641.0	637.6	634.2	629.2	622.8	616.4	609.9	603.5	600.1
32.5°	628.7	624.8	620.9	617.0	613.2	607.9	601.3	594.6	588.0	581.3	577.3
35°	598.6	594.2	589.8	585.4	581.1	575.4	568.5	561.7	554.8	548.0	543.4
37.5°	566.4	561.9	557.4	552.9	548.3	542.2	534.6	527.0	519.5	511.9	506.7
40°	543.7	539.2	534.6	530.1	525.6	519.4	511.7	503.8	496.1	488.2	482.4
42.5°	522.0	517.3	512.5	507.8	503.0	496.6	488.5	480.3	472.2	464.1	458.2
45°	488.2	483.2	478.1	473.0	467.9	461.3	453.0	444.9	436.7	428.4	421.7
47.5°	453.4	448.1	442.8	437.6	432.4	425.5	416.9	408.4	399.9	391.3	384.4
50°	429.7	424.3	419.0	413.6	408.3	401.2	392.4	383.7	374.9	366.1	359.3
52.5°	405.5	400.3	395.1	389.8	384.5	377.5	368.4	359.5	350.5	341.5	334.5
55°	369.9	364.4	358.9	353.4	347.9	340.7	331.8	323.0	314.0	305.1	298.0
57.5°	334.6	328.9	323.2	317.5	311.8	304.6	295.8	287.0	278.3	269.5	262.3
60°	309.4	304.0	298.5	293.0	287.6	280.4	271.6	262.8	254.1	245.3	238.2
62.5°	286.8	281.1	275.4	269.7	264.0	256.7	247.6	238.7	229.7	220.7	214.1
65°	251.5	245.7	239.7	233.9	227.9	220.6	211.8	203.1	194.3	185.5	179.7
67.5°	214.9	209.2	203.6	198.0	192.3	185.4	177.3	169.1	161.1	152.9	147.8
70°	191.7	185.9	180.2	174.4	168.7	161.9	154.1	146.3	138.5	130.7	126.2
72.5°	167.1	161.8	156.6	151.5	146.2	140.0	132.6	125.2	117.8	110.4	106.6
75°	133.8	128.7	123.7	118.6	113.5	107.7	101.3	94.8	88.4	82.0	78.8
77.5°	100.0	95.7	91.4	87.1	82.8	78.0	72.8	67.7	62.4	57.2	55.4
80°	78.3	74.3	70.3	66.4	62.4	58.4	54.3	50.1	46.0	41.9	41.5
82.5°	59.6	55.9	52.3	48.6	45.0	42.0	39.6	37.2	34.9	32.6	32.2
85°	33.3	30.6	27.8	25.0	22.3	20.8	20.4	20.0	19.5	19.1	18.9
87.5°	11.7	11.2	10.5	10.0	9.4	9.2	9.3	9.4	9.5	9.7	9.7
90°	1.8	3.4	4.9	6.4	7.9	9.2	10.3	11.4	12.5	13.6	14.4
92.5°	13.2	15.0	16.7	18.5	20.2	21.5	22.2	23.0	23.8	24.6	25.0
95°	37.2	38.4	39.6	40.9	42.1	43.3	44.2	45.2	46.1	47.1	47.5
97.5°	64.9	65.9	66.9	67.9	68.8	69.9	71.1	72.2	73.3	74.5	74.9
100°	86.7	87.2	87.8	88.3	88.9	89.8	91.0	92.3	93.5	94.7	95.1
102.5°	109.5	109.7	110.0	110.2	110.4	111.1	112.2	113.3	114.5	115.6	116.0
105°	144.3	144.4	144.6	144.7	144.9	145.2	145.8	146.3	146.9	147.4	147.8
107.5°	180.9	181.0	181.2	181.3	181.5	181.6	181.7	181.8	181.9	182.0	182.4
110°	205.7	205.9	206.1	206.4	206.7	206.8	206.7	206.5	206.4	206.2	206.0



TEST NUMBER: P332911-927

CATALOG NUMBER: S124RDIP-S575D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.4	231.4	231.5	231.6	231.6	231.5	231.2	231.0	230.8	230.5	230.4
115°	270.1	270.1	270.1	270.1	270.1	269.9	269.6	269.3	269.0	268.8	268.6
117.5°	306.4	306.6	306.7	306.7	306.9	306.8	306.7	306.4	306.3	306.1	305.6
120°	330.7	331.3	331.8	332.4	333.0	333.0	332.6	332.2	331.8	331.4	330.7
122.5°	356.0	356.2	356.4	356.6	356.9	356.9	356.7	356.5	356.3	356.1	355.6
125°	393.2	393.2	393.2	393.2	393.2	393.2	393.1	392.9	392.8	392.7	392.4
127.5°	427.1	427.5	427.9	428.3	428.7	428.8	428.6	428.4	428.2	427.9	427.7
130°	450.8	451.3	451.7	452.1	452.5	452.7	452.7	452.7	452.7	452.7	452.4
132.5°	475.2	475.5	475.8	476.0	476.3	476.4	476.3	476.3	476.1	476.0	475.7
135°	507.2	508.0	508.9	509.7	510.6	511.0	511.0	511.0	511.0	511.0	510.6
137.5°	542.2	542.6	542.9	543.3	543.7	544.0	544.2	544.5	544.6	544.9	544.5
140°	565.5	565.7	566.0	566.3	566.6	566.6	566.6	566.6	566.6	566.6	566.6
142.5°	586.8	587.0	587.3	587.6	587.9	588.0	587.8	587.7	587.6	587.5	587.5
145°	616.2	616.8	617.3	617.9	618.5	618.8	618.9	619.0	619.2	619.3	619.2
147.5°	645.5	646.1	646.7	647.5	648.1	648.4	648.2	648.2	648.0	647.9	647.8
150°	663.3	663.8	664.4	665.0	665.5	665.7	665.7	665.7	665.7	665.7	665.7
152.5°	680.2	680.5	680.8	681.1	681.4	681.7	681.8	681.9	682.0	682.1	682.5
155°	706.0	706.0	706.0	706.0	706.0	705.9	705.8	705.7	705.5	705.4	705.9
157.5°	727.9	727.5	727.3	727.1	726.8	726.7	726.7	726.7	726.6	726.6	727.0
160°	740.7	740.5	740.5	740.3	740.1	740.0	739.9	739.7	739.6	739.5	739.9
162.5°	752.6	752.3	751.9	751.5	751.1	750.9	750.8	750.7	750.5	750.4	751.1
165°	768.6	768.2	767.8	767.3	766.9	766.6	766.3	766.0	765.7	765.5	766.3
167.5°	780.9	780.2	779.7	779.1	778.6	778.2	778.2	778.3	778.3	778.3	779.2
170°	787.7	787.1	786.4	785.7	785.1	784.7	784.9	785.1	785.1	785.3	786.1
172.5°	792.7	792.2	791.5	791.0	790.4	790.1	790.2	790.2	790.2	790.3	791.2
175°	799.5	798.8	798.1	797.5	796.8	796.4	796.2	796.1	796.0	795.8	796.8
177.5°	801.8	801.2	800.7	800.1	799.5	799.3	799.3	799.3	799.3	799.3	800.0
180°	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7



TEST NUMBER: P332911-927

CATALOG NUMBER: S124RDIP-S575D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	802.1	803.3	804.5	805.0	804.9	804.8	804.7	804.6
5°	796.7	798.1	799.5	800.0	799.7	799.5	799.2	798.9
7.5°	786.1	787.0	787.9	788.1	787.7	787.2	786.8	786.3
10°	776.6	777.1	777.7	777.7	777.1	776.6	776.0	775.5
12.5°	764.8	765.1	765.5	765.2	764.5	763.7	763.0	762.2
15°	744.1	743.9	743.5	743.0	742.0	741.0	740.1	739.1
17.5°	719.2	718.4	717.6	716.5	715.1	713.7	712.2	710.7
20°	701.8	700.7	699.6	698.2	696.4	694.6	692.8	691.0
22.5°	682.5	680.8	679.1	677.6	676.1	674.7	673.3	671.8
25°	651.3	648.9	646.6	644.8	643.3	642.0	640.6	639.2
27.5°	619.4	616.6	613.7	611.2	609.3	607.3	605.4	603.4
30°	596.7	593.2	589.8	587.0	584.8	582.6	580.4	578.2
32.5°	573.4	569.4	565.4	562.4	560.3	558.3	556.1	554.1
35°	538.7	534.0	529.4	525.9	523.4	520.9	518.4	515.9
37.5°	501.5	496.3	491.1	487.3	484.7	482.3	479.8	477.4
40°	476.7	471.0	465.2	461.1	458.6	456.1	453.7	451.2
42.5°	452.3	446.5	440.6	436.4	433.8	431.3	428.6	426.1
45°	415.0	408.3	401.6	397.0	394.5	392.1	389.6	387.1
47.5°	377.4	370.4	363.5	358.6	355.9	353.2	350.5	347.8
50°	352.4	345.6	338.7	334.1	331.4	328.8	326.2	323.6
52.5°	327.6	320.6	313.7	308.9	306.1	303.4	300.7	298.0
55°	290.9	283.8	276.6	271.8	269.2	266.6	264.0	261.3
57.5°	255.0	247.8	240.6	236.0	234.0	232.0	230.0	228.1
60°	231.1	223.9	216.8	212.2	210.0	207.8	205.7	203.4
62.5°	207.6	201.0	194.4	190.2	188.5	186.7	185.0	183.2
65°	173.8	167.9	162.0	158.2	156.6	155.0	153.3	151.6
67.5°	142.8	137.7	132.6	129.2	127.4	125.6	123.7	121.9
70°	121.7	117.2	112.6	109.6	108.3	106.9	105.5	104.2
72.5°	102.7	98.9	95.0	92.4	91.2	89.9	88.6	87.4
75°	75.7	72.6	69.4	67.4	66.5	65.8	65.0	64.1
77.5°	53.6	51.7	49.8	48.8	48.6	48.3	48.1	47.8
80°	41.1	40.7	40.2	40.0	39.8	39.7	39.6	39.5
82.5°	31.9	31.6	31.4	31.1	31.0	30.8	30.7	30.6
85°	18.5	18.3	18.0	17.9	17.9	17.9	17.9	17.9
87.5°	9.7	9.8	9.8	10.0	10.1	10.3	10.5	10.6
90°	15.3	16.1	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	25.5	26.0	26.5	26.9	27.0	27.2	27.3	27.5
95°	47.9	48.3	48.7	49.0	49.0	49.0	49.0	49.0
97.5°	75.4	75.9	76.4	76.7	76.7	76.7	76.7	76.7
100°	95.3	95.6	95.9	96.0	96.0	96.0	96.0	96.0
102.5°	116.4	116.7	117.1	117.3	117.5	117.6	117.7	117.8
105°	148.2	148.6	149.0	149.5	149.9	150.3	150.7	151.1
107.5°	182.8	183.1	183.5	183.7	183.6	183.6	183.6	183.5
110°	205.7	205.4	205.1	205.2	205.7	206.0	206.4	206.8





TEST NUMBER: P332911-927

CATALOG NUMBER: S124RDIP-S575D810U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	230.4	230.4	230.3	230.3	230.4	230.4	230.5	230.6
115°	268.5	268.4	268.2	268.1	268.0	267.8	267.7	267.5
117.5°	305.1	304.7	304.2	303.8	303.6	303.2	303.0	302.7
120°	329.9	329.2	328.6	328.4	328.7	328.9	329.2	329.5
122.5°	355.1	354.7	354.3	353.8	353.2	352.8	352.3	351.8
125°	392.1	391.8	391.6	391.3	391.0	390.7	390.5	390.1
127.5°	427.4	427.1	426.8	426.6	426.4	426.2	426.0	425.7
130°	452.2	451.9	451.6	451.2	450.7	450.1	449.6	449.0
132.5°	475.5	475.2	474.9	474.7	474.4	474.2	474.0	473.8
135°	510.4	510.1	509.8	509.5	509.1	508.7	508.3	507.9
137.5°	544.2	543.8	543.4	543.3	543.4	543.4	543.5	543.7
140°	566.4	566.3	566.1	566.0	565.9	565.7	565.5	565.5
142.5°	587.4	587.4	587.4	587.3	587.3	587.3	587.2	587.2
145°	619.0	618.9	618.8	618.5	618.1	617.7	617.3	616.9
147.5°	647.7	647.6	647.5	647.4	647.2	647.1	647.0	646.8
150°	665.7	665.7	665.7	665.7	665.6	665.4	665.3	665.1
152.5°	682.8	683.1	683.4	683.4	683.1	682.7	682.4	682.0
155°	706.5	707.0	707.6	707.6	707.0	706.5	705.9	705.4
157.5°	727.4	727.9	728.3	728.2	727.8	727.3	726.8	726.4
160°	740.3	740.7	741.1	741.0	740.3	739.6	738.9	738.2
162.5°	751.9	752.6	753.4	753.4	752.7	752.0	751.3	750.6
165°	767.1	767.9	768.8	768.9	768.3	767.8	767.2	766.8
167.5°	780.0	780.9	781.6	781.6	780.8	779.9	779.1	778.2
170°	787.0	787.7	788.6	788.5	787.6	786.6	785.6	784.7
172.5°	792.1	793.1	794.0	794.0	793.1	792.0	791.1	790.1
175°	797.7	798.7	799.7	799.7	798.7	797.7	796.8	795.8
177.5°	800.8	801.6	802.4	802.3	801.5	800.6	799.7	798.8
180°	800.7	800.7	800.7	800.7	800.7	800.7	800.7	800.7

(END OF REPORT)