

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332936-935

Luminaire Tested: **S124RDIP-S795D590U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332936-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S795D590U935-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4583.0 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332936-935

CATALOG NUMBER: S124RDIP-S795D590U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332936-935

CATALOG NUMBER: S124RDIP-S795D590U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56	51
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	54	50	47	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	28	25
7	60	48	40	35	56	46	38	33	40	35	30	36	31	27	31	28	25	22
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	28	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P332936-935

CATALOG NUMBER: S124RDIP-S795D590U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	2.5
10°-20°	313.3	6.8
20°-30°	452.4	9.9
30°-40°	512.8	11.2
40°-50°	495.2	10.8
50°-60°	411.8	9.0
60°-70°	284.4	6.2
70°-80°	144.1	3.1
80°-90°	38.4	0.8
90°-100°	180.6	3.9
100°-110°	375.8	8.2
110°-120°	336.6	7.3
120°-130°	283.1	6.2
130°-140°	236.1	5.2
140°-150°	180.4	3.9
150°-160°	126.8	2.8
160°-170°	74.6	1.6
170°-180°	24.3	0.5
0°-30°	878.1	19.2
0°-40°	1390.9	30.3
0°-60°	2297.9	50.1
0°-90°	2764.8	60.3
90°-120°	893.0	19.5
90°-150°	1592.6	34.8
90°-180°	1818.0	39.7
0°-180°	4583.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	0	4	9	10	10	3
95°	16	51	400	198	120	18
105°	57	83	322	694	691	61
115°	101	127	287	552	664	100
125°	141	168	286	470	529	125
135°	168	199	283	417	474	129
145°	193	221	282	352	386	121
155°	220	237	274	310	324	101
165°	239	247	263	278	282	68
175°	250	250	252	255	254	24
180°	250	250	250	250	250	



TEST NUMBER: P332936-935

CATALOG NUMBER: S124RDIP-S795D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.0	15.8	14.8	13.6	12.4	11.7	12.1	12.0	12.0	12.1	11.8
90°	0.5	1.5	2.9	3.4	4.0	4.0	6.9	6.9	7.8	8.9	8.4
92.5°	5.6	8.2	12.7	18.8	25.9	36.2	61.1	99.2	136.4	155.8	129.8
95°	16.2	17.7	22.6	29.0	40.7	61.4	104.1	184.7	302.0	400.3	411.6
97.5°	29.1	29.1	33.3	39.2	49.3	66.6	99.5	166.0	282.8	421.6	517.1
100°	37.4	37.4	40.7	46.7	56.0	71.7	100.7	156.2	256.4	394.9	520.6
102.5°	45.2	46.0	49.0	54.5	63.5	78.4	104.6	153.4	238.7	361.5	491.1
105°	57.4	59.0	61.4	67.3	76.1	90.4	113.9	154.7	223.5	322.2	437.6
107.5°	71.0	72.0	74.5	80.8	89.2	103.2	124.8	162.0	220.8	300.2	394.4
110°	80.1	81.0	83.5	89.4	98.2	111.5	133.1	167.5	221.5	292.7	372.8



TEST NUMBER: P332936-935

CATALOG NUMBER: S124RDIP-S795D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	88.7	89.7	92.6	98.1	106.9	120.1	140.9	173.4	223.9	289.2	360.6
115°	101.2	102.6	106.1	111.0	120.4	133.6	153.3	182.7	228.4	287.3	349.2
117.5°	114.2	115.5	118.6	124.0	132.7	146.5	165.1	192.3	233.2	286.8	344.1
120°	122.8	123.8	127.2	132.6	140.9	154.7	173.4	198.9	236.8	286.8	341.4
122.5°	130.6	131.6	135.1	140.1	149.2	162.6	181.2	205.2	240.3	286.5	338.2
125°	140.9	142.9	145.9	151.3	160.6	174.4	192.0	214.6	245.6	285.9	333.0
127.5°	150.1	151.7	155.2	161.4	171.1	184.9	202.1	222.8	249.8	284.7	326.1
130°	155.2	157.1	161.1	168.5	177.8	192.0	208.7	227.9	253.0	284.4	321.7
132.5°	160.3	161.9	167.0	174.0	184.1	197.5	214.2	233.0	255.7	284.0	317.8
135°	167.5	169.4	174.4	182.7	193.0	205.8	222.0	239.7	259.8	283.4	311.9
137.5°	174.7	176.5	181.9	189.9	200.6	212.8	227.9	244.4	262.3	283.3	306.8
140°	179.8	181.2	186.7	195.0	205.3	217.1	231.9	247.5	264.2	282.9	304.0
142.5°	185.3	186.8	191.7	199.7	209.7	221.0	235.4	249.9	265.8	282.9	301.7
145°	193.0	194.5	199.4	206.3	215.6	226.4	239.2	252.4	266.7	281.9	297.6
147.5°	201.7	202.2	206.6	213.6	221.4	231.2	243.1	254.7	267.2	280.2	294.0
150°	207.2	207.8	211.7	217.6	225.0	234.3	245.1	255.9	267.2	279.0	291.3
152.5°	212.4	212.5	216.4	221.9	228.5	237.0	246.7	256.7	266.4	277.0	288.1
155°	219.6	220.1	223.0	227.9	233.3	240.6	249.0	257.4	265.2	274.1	283.4
157.5°	226.5	226.5	229.3	233.1	237.8	243.6	250.7	257.4	264.0	271.0	278.6
160°	230.8	230.8	232.8	236.3	240.1	245.6	251.5	257.4	262.8	268.6	275.1
162.5°	234.8	234.4	235.9	239.0	242.5	246.8	252.3	257.4	261.6	266.3	271.9
165°	239.2	239.2	240.1	242.6	245.1	248.1	252.4	256.4	259.3	262.8	266.7
167.5°	243.6	243.1	243.6	245.5	246.8	249.1	252.4	255.2	257.0	259.2	262.0
170°	245.6	245.1	245.6	247.0	248.1	249.5	251.9	254.4	255.4	256.8	258.8
172.5°	247.5	247.0	247.1	248.2	248.8	249.9	251.6	253.7	253.8	254.5	256.1
175°	249.5	249.0	249.0	249.5	250.0	250.0	251.0	252.4	251.9	251.9	253.0
177.5°	250.4	250.0	249.6	250.0	250.0	250.0	250.4	251.2	250.4	250.4	250.8
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0



TEST NUMBER: P332936-935

CATALOG NUMBER: S124RDIP-S795D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	11.7	11.6	11.5	11.5	11.8	12.1	12.1	12.3
90°	8.9	9.3	9.8	9.8	10.3	10.8	10.3	10.3
92.5°	96.4	72.6	57.8	48.0	42.1	39.5	37.8	37.8
95°	363.9	287.8	222.0	174.4	150.3	135.1	126.2	119.9
97.5°	537.7	509.5	461.4	410.1	374.9	345.3	330.5	320.3
100°	592.4	602.2	578.1	541.7	499.0	469.1	454.3	450.4
102.5°	589.6	638.3	645.3	630.2	603.9	582.2	566.7	563.5
105°	550.1	635.1	683.7	703.9	704.8	700.9	694.0	691.0
107.5°	494.0	584.4	653.0	696.7	721.0	732.2	737.1	738.4
110°	460.2	545.2	616.4	670.5	705.3	725.9	734.8	739.2



TEST NUMBER: P332936-935

CATALOG NUMBER: S124RDIP-S795D590U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	435.5	510.6	577.9	631.9	671.5	696.5	708.9	716.0
115°	410.6	471.1	528.5	575.7	614.4	643.9	659.6	663.6
117.5°	398.4	448.4	493.6	533.6	566.7	591.4	607.3	610.4
120°	393.0	438.6	477.9	512.7	540.8	562.4	575.1	580.6
122.5°	388.2	432.3	468.0	498.6	522.3	540.8	551.6	557.0
125°	380.1	422.4	456.2	483.3	502.9	517.2	526.5	529.4
127.5°	370.3	410.7	444.5	470.1	489.9	502.6	510.4	513.3
130°	362.5	401.3	434.6	460.7	480.9	493.1	501.0	503.9
132.5°	354.2	390.6	423.3	449.3	469.1	482.9	490.3	493.4
135°	342.9	374.8	404.7	429.3	448.9	462.7	470.5	473.5
137.5°	332.5	359.6	384.8	407.0	425.3	438.9	445.4	448.9
140°	326.6	349.7	371.8	392.4	409.7	420.4	427.3	431.3
142.5°	321.2	341.5	360.4	378.3	393.5	403.6	409.7	412.3
145°	313.3	330.0	344.8	358.5	370.8	379.2	384.1	386.5
147.5°	306.9	320.2	332.0	342.9	351.9	359.0	362.7	363.7
150°	303.1	314.4	324.2	333.0	340.9	347.2	350.2	350.7
152.5°	298.7	308.4	317.5	324.8	331.4	336.7	338.4	338.9
155°	292.2	300.1	307.5	313.3	318.3	322.2	323.6	323.6
157.5°	285.2	291.9	298.0	302.7	306.5	309.4	310.3	310.3
160°	280.9	286.4	291.7	295.7	298.6	301.6	302.0	302.0
162.5°	276.6	281.2	285.4	289.0	291.2	294.1	294.6	294.2
165°	270.6	273.5	277.0	279.5	281.5	283.4	282.9	282.4
167.5°	264.8	267.1	269.8	271.3	272.3	273.5	273.5	273.1
170°	261.3	262.8	264.8	266.2	267.2	267.7	267.2	267.2
172.5°	258.1	259.2	260.5	261.5	262.1	262.6	262.1	261.3
175°	253.9	254.4	255.4	255.4	255.4	256.4	255.4	254.4
177.5°	251.2	251.6	251.6	251.9	251.6	251.9	251.2	250.4
180°	250.0	250.0	250.0	250.0	250.0	250.0	250.0	250.0

(END OF REPORT)