

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332947-927

Luminaire Tested: **S124RDIP-S795D1035U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332947-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S795D1035U927-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5382.1 lumens  
Efficiency: N/A  
Efficacy: 103.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332947-927

CATALOG NUMBER: S124RDIP-S795D1035U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332947-927

CATALOG NUMBER: S124RDIP-S795D1035U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47																				
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40																				
2	89	82	76	71	82	75	70	66	63	60	56	52	50	47	42	41	39	34																				
3	81	72	65	59	74	66	60	55	56	52	48	47	43	40	38	35	33	29																				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25																				
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22																				
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	19																				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	25	22	20	17																				
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	23	20	18	16																				
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	19	16	14																				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8884	8884	8884
5°	8904	8795	8849
10°	8848	8689	8689
15°	8747	8507	8444
20°	8607	8267	8115
25°	8429	7986	7783
30°	8255	7690	7368
35°	8064	7383	6951
40°	7832	7032	6500
45°	7618	6687	6042
50°	7376	6286	5556
55°	7116	5871	5029
60°	6830	5414	4490
65°	6567	4846	3960
70°	6187	4216	3361
75°	5702	3497	2732
80°	4974	2664	2506
85°	4215	2418	2260



TEST NUMBER: P332947-927

CATALOG NUMBER: S124RDIP-S795D1035U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.4	1.9
10°-20°	288.3	5.4
20°-30°	416.3	7.7
30°-40°	471.8	8.8
40°-50°	455.6	8.5
50°-60°	378.9	7.0
60°-70°	261.6	4.9
70°-80°	132.6	2.5
80°-90°	37.1	0.7
90°-100°	67.4	1.3
100°-110°	199.8	3.7
110°-120°	339.1	6.3
120°-130°	447.1	8.3
130°-140°	502.1	9.3
140°-150°	493.4	9.2
150°-160°	415.0	7.7
160°-170°	276.1	5.1
170°-180°	96.7	1.8
0°-30°	807.9	15.0
0°-40°	1279.7	23.8
0°-60°	2114.3	39.3
0°-90°	2545.6	47.3
90°-120°	606.3	11.3
90°-150°	2048.8	38.1
90°-180°	2837.0	52.7
0°-180°	5382.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1099	1095	1085	1093	1092	104
15°	1047	1038	1018	1016	1010	295
25°	946	930	896	883	874	436
35°	818	790	749	721	705	511
45°	667	635	586	546	529	514
55°	506	471	417	375	357	452
65°	344	307	254	219	207	339
75°	183	151	112	93	88	193
85°	46	29	26	24	24	51
90°	2	11	17	22	24	5
95°	48	54	60	62	62	53
105°	184	185	188	191	193	196
115°	345	345	343	342	342	340
125°	502	502	501	500	498	447
135°	648	652	652	651	648	501
145°	787	790	791	790	788	492
155°	901	901	901	903	901	415
165°	981	979	977	982	979	276
175°	1021	1017	1016	1021	1016	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332947-927

CATALOG NUMBER: S124RDIP-S795D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1103.2	1102.6	1101.9	1101.4	1100.7	1099.6	1098.0	1096.4	1094.7	1093.1	1094.7
5°	1098.8	1098.0	1097.3	1096.5	1095.7	1094.3	1092.0	1089.8	1087.5	1085.3	1087.2
7.5°	1088.9	1088.1	1087.3	1086.5	1085.7	1083.9	1080.9	1078.0	1075.1	1072.1	1073.3
10°	1079.4	1078.5	1077.5	1076.6	1075.6	1073.5	1070.2	1066.8	1063.4	1060.0	1060.7
12.5°	1067.2	1066.2	1065.1	1064.0	1063.0	1060.4	1056.5	1052.4	1048.5	1044.5	1045.0
15°	1046.6	1044.9	1043.1	1041.5	1039.8	1036.6	1031.9	1027.2	1022.5	1017.9	1017.5
17.5°	1021.4	1019.0	1016.5	1014.2	1011.7	1007.7	1002.0	996.4	990.8	985.2	984.1
20°	1001.9	999.4	997.0	994.6	992.1	987.8	981.4	975.0	968.6	962.3	960.8
22.5°	980.3	977.6	974.9	972.1	969.4	964.6	957.7	950.9	944.1	937.3	935.1
25°	946.3	942.9	939.5	936.1	932.8	927.2	919.6	911.9	904.2	896.5	893.3
27.5°	910.5	906.3	902.1	897.9	893.6	887.4	879.2	871.0	862.8	854.6	850.6
30°	885.6	880.9	876.2	871.6	866.9	860.2	851.4	842.6	833.7	824.9	820.2
32.5°	859.3	854.1	848.7	843.4	838.2	831.0	821.9	812.8	803.7	794.6	789.2
35°	818.2	812.2	806.2	800.2	794.2	786.6	777.2	767.8	758.4	749.1	742.8
37.5°	774.2	768.0	761.8	755.7	749.5	741.2	730.9	720.5	710.1	699.7	692.6
40°	743.2	737.0	730.9	724.7	718.5	710.0	699.3	688.7	678.0	667.3	659.5
42.5°	713.5	707.0	700.6	694.1	687.6	678.8	667.7	656.6	645.5	634.3	626.3
45°	667.3	660.4	653.5	646.6	639.6	630.6	619.3	608.1	596.8	585.7	576.5
47.5°	619.6	612.5	605.4	598.2	591.0	581.6	570.0	558.3	546.6	534.9	525.4
50°	587.3	580.0	572.7	565.4	558.1	548.4	536.5	524.5	512.5	500.5	491.2
52.5°	554.3	547.2	540.0	532.8	525.7	515.9	503.7	491.4	479.1	466.8	457.3
55°	505.6	498.0	490.6	483.1	475.6	465.8	453.6	441.4	429.3	417.1	407.3
57.5°	457.4	449.6	441.8	434.0	426.2	416.3	404.3	392.4	380.4	368.4	358.5
60°	423.0	415.5	408.1	400.5	393.0	383.3	371.3	359.3	347.4	335.3	325.6
62.5°	392.0	384.2	376.4	368.6	360.8	350.8	338.5	326.2	313.9	301.7	292.6
65°	343.8	335.7	327.6	319.6	311.6	301.6	289.5	277.6	265.6	253.7	245.6
67.5°	293.7	286.1	278.3	270.6	262.8	253.5	242.3	231.2	220.1	209.0	202.0
70°	262.1	254.2	246.3	238.4	230.6	221.3	210.6	199.9	189.3	178.6	172.5
72.5°	228.4	221.3	214.1	207.0	199.9	191.3	181.3	171.1	161.1	151.0	145.7
75°	182.8	175.9	169.0	162.1	155.1	147.3	138.5	129.7	120.9	112.1	107.7
77.5°	136.7	130.8	124.9	119.1	113.1	106.6	99.6	92.4	85.3	78.2	75.7
80°	107.0	101.6	96.2	90.7	85.3	79.8	74.1	68.5	62.9	57.3	56.7
82.5°	81.4	76.4	71.5	66.5	61.5	57.4	54.2	50.9	47.7	44.5	44.0
85°	45.5	41.7	38.0	34.3	30.5	28.4	27.8	27.3	26.7	26.1	25.7
87.5°	16.0	15.1	14.3	13.5	12.8	12.4	12.5	12.7	12.8	12.9	13.0
90°	2.4	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5
92.5°	17.0	19.2	21.3	23.5	25.7	27.4	28.4	29.3	30.3	31.3	31.9
95°	47.5	49.0	50.6	52.2	53.8	55.1	56.4	57.7	58.9	60.1	60.6
97.5°	82.9	84.1	85.4	86.7	87.9	89.3	90.7	92.1	93.6	95.1	95.7
100°	110.7	111.4	112.1	112.8	113.5	114.6	116.2	117.8	119.4	121.0	121.4
102.5°	139.8	140.1	140.4	140.6	140.9	141.8	143.2	144.7	146.1	147.6	148.1
105°	184.3	184.4	184.6	184.7	185.0	185.4	186.1	186.8	187.5	188.2	188.7
107.5°	230.9	231.1	231.3	231.6	231.7	231.9	232.0	232.1	232.2	232.3	232.8
110°	262.5	262.8	263.2	263.6	264.0	264.0	263.8	263.6	263.5	263.3	262.9



TEST NUMBER: P332947-927

CATALOG NUMBER: S124RDIP-S795D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.4	295.5	295.6	295.6	295.7	295.6	295.2	294.9	294.6	294.3	294.2
115°	344.8	344.8	344.8	344.8	344.8	344.6	344.2	343.9	343.5	343.2	343.0
117.5°	391.3	391.4	391.5	391.7	391.8	391.7	391.5	391.3	391.0	390.8	390.1
120°	422.2	422.9	423.7	424.4	425.1	425.2	424.6	424.1	423.6	423.0	422.2
122.5°	454.5	454.8	455.0	455.3	455.6	455.7	455.4	455.1	454.9	454.6	454.1
125°	502.1	502.1	502.1	502.1	502.1	502.0	501.8	501.7	501.5	501.3	501.0
127.5°	545.3	545.8	546.3	546.8	547.4	547.5	547.2	546.9	546.7	546.4	546.1
130°	575.6	576.2	576.7	577.2	577.7	578.0	578.0	578.0	578.0	578.0	577.7
132.5°	606.7	607.0	607.4	607.8	608.2	608.3	608.2	608.0	607.8	607.8	607.4
135°	647.6	648.6	649.7	650.8	651.8	652.4	652.4	652.4	652.4	652.4	652.0
137.5°	692.2	692.7	693.2	693.6	694.2	694.5	694.8	695.1	695.4	695.7	695.2
140°	721.9	722.2	722.6	722.9	723.3	723.5	723.5	723.5	723.5	723.5	723.3
142.5°	749.1	749.5	749.8	750.2	750.5	750.6	750.5	750.4	750.2	750.0	750.0
145°	786.7	787.4	788.1	788.9	789.6	790.0	790.2	790.4	790.5	790.7	790.5
147.5°	824.1	824.9	825.8	826.6	827.4	827.8	827.7	827.5	827.4	827.3	827.1
150°	846.8	847.6	848.3	849.0	849.7	850.0	850.0	850.0	850.0	850.0	850.0
152.5°	868.4	868.8	869.2	869.7	870.1	870.3	870.4	870.6	870.8	870.8	871.3
155°	901.4	901.4	901.4	901.4	901.4	901.3	901.1	900.9	900.8	900.6	901.3
157.5°	929.2	928.9	928.6	928.3	928.0	927.8	927.7	927.7	927.7	927.6	928.2
160°	945.7	945.5	945.3	945.2	945.0	944.8	944.6	944.4	944.3	944.1	944.6
162.5°	960.8	960.4	960.0	959.5	959.0	958.7	958.5	958.4	958.2	958.0	958.9
165°	981.3	980.7	980.2	979.7	979.1	978.7	978.3	978.0	977.6	977.3	978.3
167.5°	997.0	996.2	995.5	994.7	994.0	993.6	993.6	993.7	993.7	993.8	994.8
170°	1005.8	1004.9	1004.0	1003.1	1002.3	1001.9	1002.1	1002.3	1002.4	1002.6	1003.7
172.5°	1012.1	1011.4	1010.7	1009.9	1009.2	1008.8	1008.8	1008.8	1008.9	1008.9	1010.1
175°	1020.8	1019.9	1019.1	1018.2	1017.3	1016.8	1016.6	1016.4	1016.2	1016.1	1017.3
177.5°	1023.7	1022.9	1022.2	1021.5	1020.8	1020.5	1020.5	1020.5	1020.5	1020.5	1021.4
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4



TEST NUMBER: P332947-927

CATALOG NUMBER: S124RDIP-S795D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1096.4	1098.0	1099.6	1100.4	1100.3	1100.1	1099.9	1099.8
5°	1089.0	1090.9	1092.8	1093.5	1093.1	1092.8	1092.4	1092.0
7.5°	1074.5	1075.8	1077.0	1077.2	1076.7	1076.0	1075.5	1074.8
10°	1061.5	1062.2	1063.0	1063.0	1062.2	1061.5	1060.7	1060.0
12.5°	1045.4	1045.8	1046.3	1046.0	1045.0	1043.9	1042.8	1041.8
15°	1017.2	1016.8	1016.4	1015.6	1014.2	1012.9	1011.6	1010.3
17.5°	983.1	982.1	981.0	979.5	977.5	975.5	973.5	971.5
20°	959.3	957.7	956.2	954.3	951.9	949.4	947.0	944.6
22.5°	932.9	930.6	928.4	926.2	924.2	922.3	920.3	918.3
25°	890.2	887.0	883.8	881.3	879.4	877.6	875.7	873.8
27.5°	846.7	842.8	838.8	835.5	832.8	830.1	827.4	824.7
30°	815.6	810.9	806.2	802.3	799.4	796.4	793.4	790.4
32.5°	783.7	778.3	772.9	768.7	765.9	763.0	760.2	757.3
35°	736.3	730.0	723.7	718.7	715.4	712.0	708.6	705.3
37.5°	685.5	678.3	671.2	666.0	662.7	659.3	655.9	652.5
40°	651.6	643.7	635.9	630.3	626.9	623.5	620.2	616.8
42.5°	618.3	610.3	602.3	596.5	592.9	589.5	586.0	582.4
45°	567.3	558.1	548.9	542.6	539.2	535.9	532.5	529.2
47.5°	515.9	506.4	496.9	490.2	486.6	482.8	479.1	475.4
50°	481.8	472.5	463.0	456.6	453.0	449.5	445.9	442.4
52.5°	447.8	438.3	428.7	422.2	418.4	414.7	411.1	407.3
55°	397.6	387.9	378.2	371.5	368.0	364.4	360.8	357.3
57.5°	348.6	338.7	328.8	322.6	319.9	317.2	314.5	311.8
60°	315.9	306.2	296.4	290.0	287.1	284.1	281.1	278.1
62.5°	283.7	274.7	265.7	260.0	257.6	255.2	252.8	250.4
65°	237.5	229.5	221.4	216.3	214.0	211.8	209.5	207.3
67.5°	195.1	188.2	181.3	176.6	174.1	171.6	169.1	166.7
70°	166.3	160.1	153.9	149.9	148.1	146.2	144.3	142.4
72.5°	140.5	135.1	129.8	126.4	124.7	122.9	121.2	119.5
75°	103.5	99.2	94.8	92.1	91.0	89.9	88.7	87.6
77.5°	73.2	70.7	68.1	66.7	66.4	66.1	65.8	65.4
80°	56.2	55.6	55.1	54.7	54.5	54.3	54.1	53.9
82.5°	43.6	43.3	42.9	42.5	42.4	42.1	42.0	41.8
85°	25.3	25.0	24.6	24.4	24.4	24.4	24.4	24.4
87.5°	13.1	13.1	13.2	13.3	13.5	13.7	13.9	14.2
90°	19.5	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	32.6	33.2	33.8	34.3	34.5	34.7	34.9	35.1
95°	61.2	61.7	62.2	62.5	62.5	62.5	62.5	62.5
97.5°	96.3	97.0	97.6	97.9	97.9	97.9	97.9	97.9
100°	121.7	122.0	122.4	122.6	122.6	122.6	122.6	122.6
102.5°	148.5	149.0	149.5	149.8	150.0	150.1	150.3	150.4
105°	189.3	189.8	190.3	190.8	191.3	191.9	192.4	192.9
107.5°	233.3	233.8	234.2	234.5	234.5	234.4	234.4	234.3
110°	262.6	262.2	261.9	262.0	262.5	263.0	263.6	264.1





TEST NUMBER: P332947-927

CATALOG NUMBER: S124RDIP-S795D1035U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.1	294.1	294.1	294.1	294.1	294.2	294.4	294.5
115°	342.8	342.6	342.5	342.3	342.1	341.9	341.7	341.6
117.5°	389.6	389.0	388.4	387.9	387.5	387.2	386.8	386.5
120°	421.3	420.4	419.5	419.2	419.6	419.9	420.3	420.6
122.5°	453.4	452.9	452.3	451.6	451.0	450.4	449.7	449.1
125°	500.6	500.3	499.9	499.6	499.2	498.8	498.5	498.1
127.5°	545.7	545.3	544.9	544.6	544.4	544.1	543.8	543.5
130°	577.3	576.9	576.6	576.1	575.4	574.6	573.9	573.2
132.5°	607.0	606.7	606.3	606.0	605.7	605.5	605.1	604.9
135°	651.6	651.3	650.9	650.5	650.0	649.4	648.9	648.4
137.5°	694.7	694.3	693.9	693.6	693.8	693.9	694.0	694.1
140°	723.2	722.9	722.8	722.6	722.5	722.2	722.1	721.9
142.5°	750.0	750.0	750.0	749.9	749.9	749.8	749.8	749.7
145°	790.4	790.2	790.0	789.6	789.1	788.6	788.1	787.5
147.5°	827.0	826.8	826.6	826.5	826.3	826.2	826.0	825.9
150°	850.0	850.0	850.0	849.9	849.8	849.5	849.4	849.2
152.5°	871.7	872.1	872.6	872.6	872.1	871.6	871.2	870.7
155°	902.1	902.7	903.4	903.4	902.7	902.1	901.3	900.6
157.5°	928.7	929.2	929.8	929.7	929.2	928.5	928.0	927.3
160°	945.2	945.7	946.2	946.0	945.2	944.3	943.4	942.5
162.5°	959.9	960.8	961.8	961.9	961.0	960.1	959.3	958.3
165°	979.5	980.5	981.5	981.7	981.0	980.3	979.6	978.9
167.5°	995.9	997.0	998.0	998.0	996.9	995.8	994.7	993.6
170°	1004.7	1005.8	1006.9	1006.7	1005.5	1004.2	1003.1	1001.8
172.5°	1011.3	1012.5	1013.8	1013.7	1012.5	1011.2	1010.0	1008.8
175°	1018.5	1019.8	1021.0	1021.0	1019.8	1018.5	1017.3	1016.1
177.5°	1022.5	1023.4	1024.5	1024.4	1023.3	1022.1	1021.0	1019.9
180°	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4	1022.4

(END OF REPORT)