

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332941-935

Luminaire Tested: **S124RDIP-S795D810U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332941-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S795D810U935-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5180.7 lumens  
Efficiency: N/A  
Efficacy: 112.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332941-935

CATALOG NUMBER: S124RDIP-S795D810U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332941-935

CATALOG NUMBER: S124RDIP-S795D810U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	37	34	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P332941-935

CATALOG NUMBER: S124RDIP-S795D810U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.4	2.2
10°-20°	313.3	6.0
20°-30°	452.4	8.7
30°-40°	512.8	9.9
40°-50°	495.2	9.6
50°-60°	411.8	7.9
60°-70°	284.4	5.5
70°-80°	144.1	2.8
80°-90°	39.6	0.8
90°-100°	57.4	1.1
100°-110°	170.1	3.3
110°-120°	288.6	5.6
120°-130°	380.6	7.3
130°-140°	427.4	8.3
140°-150°	420.0	8.1
150°-160°	353.3	6.8
160°-170°	235.0	4.5
170°-180°	82.3	1.6
0°-30°	878.1	16.9
0°-40°	1390.9	26.8
0°-60°	2297.9	44.4
0°-90°	2766.0	53.4
90°-120°	516.1	10.0
90°-150°	1744.1	33.7
90°-180°	2415.0	46.6
0°-180°	5180.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	2	9	15	19	20	5
95°	40	46	51	53	53	45
105°	157	158	160	162	164	166
115°	294	293	292	291	291	289
125°	427	427	427	425	424	381
135°	551	555	555	554	552	426
145°	670	672	673	672	670	419
155°	767	767	767	769	767	353
165°	835	833	832	836	833	235
175°	869	866	865	869	865	82
180°	870	870	870	870	870	



TEST NUMBER: P332941-935

CATALOG NUMBER: S124RDIP-S795D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.2	16.3	15.3	14.3	13.3	12.9	13.0	13.1	13.2	13.3	13.3
90°	2.0	3.7	5.3	7.0	8.6	10.0	11.2	12.4	13.6	14.8	15.7
92.5°	14.4	16.3	18.2	20.1	22.0	23.3	24.1	25.0	25.8	26.7	27.2
95°	40.4	41.8	43.0	44.4	45.8	47.0	48.0	49.1	50.1	51.1	51.6
97.5°	70.5	71.6	72.7	73.8	74.8	76.0	77.2	78.4	79.6	80.9	81.5
100°	94.3	94.8	95.4	96.0	96.6	97.6	98.9	100.3	101.6	103.0	103.3
102.5°	119.0	119.2	119.5	119.8	119.9	120.7	121.9	123.1	124.4	125.6	126.1
105°	156.9	157.0	157.1	157.3	157.5	157.8	158.4	159.0	159.6	160.2	160.7
107.5°	196.6	196.7	196.9	197.1	197.3	197.4	197.5	197.6	197.7	197.8	198.2
110°	223.5	223.8	224.0	224.4	224.6	224.7	224.6	224.5	224.3	224.1	223.9



TEST NUMBER: P332941-935

CATALOG NUMBER: S124RDIP-S795D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	251.5	251.5	251.6	251.7	251.8	251.6	251.3	251.1	250.8	250.6	250.5
115°	293.5	293.5	293.5	293.5	293.5	293.3	293.0	292.7	292.4	292.1	292.0
117.5°	333.0	333.2	333.3	333.4	333.6	333.5	333.3	333.0	332.9	332.7	332.2
120°	359.5	360.1	360.7	361.3	361.9	361.9	361.4	361.0	360.6	360.2	359.4
122.5°	386.9	387.1	387.4	387.6	387.9	387.9	387.7	387.4	387.3	387.0	386.5
125°	427.4	427.4	427.4	427.4	427.4	427.3	427.2	427.1	426.9	426.8	426.5
127.5°	464.2	464.6	465.1	465.5	466.0	466.1	465.8	465.6	465.4	465.1	464.9
130°	490.0	490.5	490.9	491.4	491.8	492.1	492.1	492.1	492.1	492.1	491.7
132.5°	516.4	516.8	517.1	517.4	517.7	517.8	517.7	517.6	517.5	517.4	517.0
135°	551.3	552.2	553.1	554.0	554.9	555.3	555.3	555.3	555.3	555.3	555.0
137.5°	589.3	589.7	590.0	590.5	590.9	591.2	591.5	591.8	591.9	592.2	591.9
140°	614.6	614.8	615.2	615.4	615.8	615.9	615.9	615.9	615.9	615.9	615.8
142.5°	637.7	638.0	638.3	638.6	638.9	639.0	638.9	638.8	638.6	638.5	638.5
145°	669.8	670.4	671.0	671.6	672.2	672.5	672.7	672.8	673.0	673.1	673.0
147.5°	701.5	702.2	702.9	703.7	704.4	704.7	704.6	704.5	704.3	704.2	704.1
150°	720.9	721.5	722.1	722.7	723.3	723.6	723.6	723.6	723.6	723.6	723.6
152.5°	739.3	739.6	739.9	740.3	740.6	740.9	741.0	741.1	741.2	741.4	741.8
155°	767.3	767.3	767.3	767.3	767.3	767.2	767.2	767.0	766.8	766.7	767.2
157.5°	791.1	790.7	790.5	790.2	790.0	789.8	789.8	789.8	789.7	789.7	790.1
160°	805.0	804.9	804.8	804.6	804.4	804.3	804.2	804.0	803.8	803.7	804.2
162.5°	817.9	817.6	817.2	816.8	816.4	816.1	816.0	815.9	815.7	815.5	816.4
165°	835.3	834.9	834.5	834.0	833.5	833.2	832.8	832.6	832.2	832.0	832.8
167.5°	848.7	848.0	847.4	846.8	846.2	845.8	845.8	845.9	845.9	845.9	846.9
170°	856.2	855.5	854.7	853.9	853.3	852.9	853.1	853.3	853.3	853.5	854.4
172.5°	861.6	861.0	860.3	859.7	859.1	858.8	858.8	858.8	858.8	858.9	859.9
175°	869.0	868.2	867.5	866.8	866.0	865.6	865.4	865.2	865.1	865.0	866.0
177.5°	871.4	870.8	870.2	869.6	869.0	868.7	868.7	868.7	868.7	868.7	869.5
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3



TEST NUMBER: P332941-935

CATALOG NUMBER: S124RDIP-S795D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	13.3	13.3	13.3	13.4	13.6	13.9	14.0	14.3
90°	16.6	17.5	18.4	19.0	19.3	19.6	19.9	20.2
92.5°	27.7	28.2	28.8	29.2	29.4	29.5	29.7	29.9
95°	52.1	52.5	53.0	53.2	53.2	53.2	53.2	53.2
97.5°	82.0	82.5	83.1	83.3	83.3	83.3	83.3	83.3
100°	103.6	103.9	104.2	104.4	104.4	104.4	104.4	104.4
102.5°	126.5	126.8	127.3	127.5	127.7	127.8	127.9	128.0
105°	161.1	161.5	162.0	162.5	162.9	163.3	163.8	164.3
107.5°	198.6	199.0	199.4	199.7	199.6	199.6	199.6	199.5
110°	223.5	223.3	222.9	223.0	223.5	223.9	224.4	224.8





TEST NUMBER: P332941-935

CATALOG NUMBER: S124RDIP-S795D810U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	250.4	250.4	250.3	250.3	250.4	250.5	250.6	250.6
115°	291.8	291.7	291.5	291.4	291.3	291.1	290.9	290.8
117.5°	331.7	331.1	330.6	330.2	329.9	329.6	329.3	329.0
120°	358.6	357.8	357.1	356.9	357.2	357.5	357.8	358.1
122.5°	386.0	385.6	385.0	384.5	383.9	383.4	382.9	382.4
125°	426.2	425.9	425.6	425.2	425.0	424.6	424.4	424.0
127.5°	464.5	464.3	463.9	463.6	463.4	463.2	463.0	462.7
130°	491.5	491.1	490.9	490.4	489.8	489.2	488.6	488.0
132.5°	516.8	516.4	516.2	515.9	515.7	515.4	515.1	515.0
135°	554.7	554.4	554.1	553.7	553.3	552.8	552.4	552.0
137.5°	591.4	591.1	590.6	590.5	590.6	590.6	590.7	590.9
140°	615.6	615.4	615.3	615.2	615.0	614.8	614.7	614.6
142.5°	638.4	638.4	638.4	638.3	638.3	638.3	638.3	638.3
145°	672.8	672.7	672.5	672.2	671.8	671.3	670.9	670.5
147.5°	704.0	703.9	703.7	703.6	703.4	703.3	703.2	703.0
150°	723.6	723.6	723.6	723.5	723.4	723.2	723.1	722.9
152.5°	742.1	742.4	742.8	742.8	742.4	742.0	741.7	741.2
155°	767.8	768.4	769.0	769.0	768.4	767.8	767.2	766.7
157.5°	790.6	791.1	791.5	791.4	791.0	790.5	790.0	789.5
160°	804.6	805.0	805.5	805.4	804.6	803.8	803.1	802.4
162.5°	817.2	817.9	818.8	818.8	818.0	817.3	816.6	815.8
165°	833.8	834.7	835.6	835.7	835.1	834.5	833.9	833.4
167.5°	847.7	848.7	849.5	849.5	848.6	847.7	846.8	845.8
170°	855.3	856.2	857.1	857.0	856.0	855.0	853.9	852.8
172.5°	860.9	861.9	863.0	863.0	861.9	860.8	859.8	858.8
175°	867.0	868.1	869.2	869.2	868.1	867.0	866.0	865.0
177.5°	870.4	871.2	872.1	872.0	871.1	870.1	869.2	868.1
180°	870.3	870.3	870.3	870.3	870.3	870.3	870.3	870.3

(END OF REPORT)