

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332668-840

Luminaire Tested: **S124DIP-S1020D1205U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332668-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D1205U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8685.0 lumens  
Efficiency: N/A  
Efficacy: 132.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332668-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332668-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	58	51	50	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332668-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.1	1.9
10°-20°	462.4	5.3
20°-30°	680.5	7.8
30°-40°	791.1	9.1
40°-50°	791.2	9.1
50°-60°	692.1	8.0
60°-70°	514.0	5.9
70°-80°	292.0	3.4
80°-90°	88.8	1.0
90°-100°	100.1	1.2
100°-110°	296.4	3.4
110°-120°	503.1	5.8
120°-130°	663.4	7.6
130°-140°	745.0	8.6
140°-150°	732.1	8.4
150°-160°	615.7	7.1
160°-170°	409.7	4.7
170°-180°	143.5	1.7
0°-30°	1307.0	15.0
0°-40°	2098.1	24.2
0°-60°	3581.3	41.2
0°-90°	4476.1	51.5
90°-120°	899.6	10.4
90°-150°	3040.1	35.0
90°-180°	4209.0	48.5
0°-180°	8685.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	4	16	26	33	35	8
95°	70	81	89	92	93	78
105°	273	275	279	283	286	290
115°	512	511	509	508	507	504
125°	745	745	744	741	739	664
135°	961	968	968	966	962	743
145°	1167	1172	1173	1172	1169	730
155°	1338	1337	1336	1340	1336	615
165°	1456	1453	1450	1456	1452	410
175°	1515	1509	1508	1515	1508	144
180°	1517	1517	1517	1517	1517	



TEST NUMBER: P332668-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	29.8	30.1	30.4	30.7	31.0	31.3	31.5	31.6	31.8	32.0	32.3
90°	3.5	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4
92.5°	25.1	28.4	31.7	34.9	38.3	40.6	42.1	43.5	45.0	46.5	47.4
95°	70.4	72.7	75.1	77.5	79.8	81.9	83.7	85.5	87.4	89.2	90.0
97.5°	123.0	124.8	126.7	128.6	130.5	132.5	134.6	136.7	138.9	141.0	142.0
100°	164.3	165.3	166.3	167.3	168.4	170.2	172.5	174.8	177.1	179.6	180.1
102.5°	207.4	207.8	208.2	208.6	209.1	210.4	212.5	214.7	216.8	218.9	219.6
105°	273.4	273.7	273.9	274.2	274.4	275.1	276.1	277.1	278.2	279.2	280.0
107.5°	342.5	343.0	343.3	343.6	343.9	344.1	344.3	344.4	344.6	344.7	345.5
110°	389.5	390.0	390.5	391.1	391.6	391.7	391.5	391.2	390.9	390.7	390.2



TEST NUMBER: P332668-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	438.3	438.5	438.6	438.7	438.8	438.6	438.1	437.7	437.2	436.7	436.6
115°	511.5	511.5	511.5	511.5	511.5	511.3	510.8	510.3	509.7	509.2	509.0
117.5°	580.6	580.8	581.0	581.2	581.4	581.3	580.9	580.6	580.2	579.9	579.0
120°	626.5	627.5	628.6	629.7	630.7	630.9	630.1	629.2	628.4	627.7	626.4
122.5°	674.4	674.8	675.2	675.6	676.1	676.1	675.7	675.4	675.0	674.6	673.8
125°	745.0	745.0	745.0	745.0	745.0	744.9	744.7	744.4	744.1	743.9	743.4
127.5°	809.1	809.9	810.6	811.4	812.2	812.4	811.9	811.5	811.1	810.7	810.2
130°	854.1	855.0	855.7	856.5	857.3	857.7	857.7	857.7	857.7	857.7	857.2
132.5°	900.1	900.7	901.3	901.8	902.4	902.6	902.4	902.2	902.0	901.8	901.2
135°	960.9	962.5	964.0	965.6	967.1	968.0	968.0	968.0	968.0	968.0	967.5
137.5°	1027.0	1027.8	1028.5	1029.3	1030.0	1030.6	1031.0	1031.4	1031.8	1032.2	1031.6
140°	1071.2	1071.7	1072.3	1072.8	1073.3	1073.5	1073.5	1073.5	1073.5	1073.5	1073.3
142.5°	1111.6	1112.1	1112.6	1113.1	1113.7	1113.8	1113.6	1113.4	1113.2	1113.0	1112.9
145°	1167.4	1168.4	1169.5	1170.5	1171.5	1172.3	1172.5	1172.8	1173.0	1173.3	1173.0
147.5°	1222.7	1224.1	1225.3	1226.5	1227.8	1228.3	1228.1	1227.9	1227.7	1227.5	1227.3
150°	1256.6	1257.6	1258.7	1259.7	1260.7	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2
152.5°	1288.5	1289.1	1289.7	1290.3	1291.0	1291.4	1291.6	1291.8	1292.0	1292.2	1292.8
155°	1337.5	1337.5	1337.5	1337.5	1337.5	1337.4	1337.2	1336.9	1336.6	1336.4	1337.4
157.5°	1378.8	1378.4	1377.9	1377.5	1377.0	1376.6	1376.6	1376.5	1376.5	1376.4	1377.3
160°	1403.2	1403.0	1402.7	1402.4	1402.2	1401.9	1401.7	1401.4	1401.1	1400.9	1401.7
162.5°	1425.7	1425.0	1424.4	1423.7	1423.0	1422.6	1422.3	1422.1	1421.8	1421.5	1422.9
165°	1456.0	1455.2	1454.4	1453.7	1452.9	1452.2	1451.7	1451.2	1450.7	1450.2	1451.7
167.5°	1479.3	1478.1	1477.0	1475.9	1474.9	1474.3	1474.4	1474.4	1474.5	1474.5	1476.1
170°	1492.4	1491.1	1489.8	1488.4	1487.1	1486.6	1486.9	1487.1	1487.4	1487.7	1489.2
172.5°	1501.8	1500.7	1499.5	1498.4	1497.4	1496.8	1496.9	1497.0	1497.0	1497.1	1498.8
175°	1514.7	1513.4	1512.1	1510.8	1509.4	1508.6	1508.4	1508.1	1507.9	1507.6	1509.4
177.5°	1518.9	1517.8	1516.8	1515.8	1514.7	1514.2	1514.2	1514.2	1514.2	1514.2	1515.7
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332668-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	32.6	32.9	33.2	33.4	33.5	33.6	33.7	33.8
90°	29.0	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	48.4	49.3	50.2	50.8	51.2	51.5	51.8	52.1
95°	90.7	91.5	92.3	92.7	92.7	92.7	92.7	92.7
97.5°	142.9	143.8	144.8	145.2	145.2	145.2	145.2	145.2
100°	180.6	181.1	181.6	181.9	181.9	181.9	181.9	181.9
102.5°	220.4	221.2	221.9	222.3	222.6	222.8	223.0	223.2
105°	280.8	281.6	282.4	283.2	284.0	284.7	285.5	286.3
107.5°	346.2	346.9	347.6	348.0	347.9	347.9	347.8	347.8
110°	389.6	389.1	388.6	388.7	389.5	390.3	391.1	391.8





TEST NUMBER: P332668-840

CATALOG NUMBER: S124DIP-S1020D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	436.5	436.4	436.3	436.3	436.5	436.6	436.8	437.0
115°	508.7	508.4	508.2	507.9	507.7	507.4	507.2	506.9
117.5°	578.0	577.1	576.2	575.6	575.0	574.5	574.0	573.5
120°	625.1	623.8	622.5	622.1	622.6	623.1	623.7	624.2
122.5°	672.9	672.0	671.1	670.1	669.2	668.3	667.3	666.4
125°	742.8	742.3	741.7	741.2	740.7	740.2	739.6	739.1
127.5°	809.7	809.2	808.6	808.2	807.8	807.3	806.9	806.5
130°	856.6	856.1	855.6	854.7	853.7	852.7	851.6	850.6
132.5°	900.7	900.2	899.7	899.2	898.8	898.4	898.0	897.6
135°	966.9	966.3	965.8	965.2	964.4	963.6	962.8	962.1
137.5°	1030.9	1030.2	1029.6	1029.3	1029.5	1029.6	1029.8	1029.9
140°	1073.0	1072.8	1072.5	1072.3	1072.0	1071.7	1071.5	1071.2
142.5°	1112.9	1112.8	1112.8	1112.7	1112.7	1112.6	1112.6	1112.5
145°	1172.8	1172.5	1172.3	1171.6	1170.9	1170.1	1169.3	1168.6
147.5°	1227.1	1226.9	1226.6	1226.4	1226.2	1225.9	1225.6	1225.4
150°	1261.2	1261.2	1261.2	1261.1	1260.8	1260.6	1260.3	1260.1
152.5°	1293.4	1294.1	1294.7	1294.7	1294.0	1293.3	1292.6	1292.0
155°	1338.5	1339.5	1340.5	1340.5	1339.5	1338.5	1337.4	1336.4
157.5°	1378.1	1378.8	1379.6	1379.6	1378.7	1377.8	1376.8	1376.0
160°	1402.4	1403.2	1404.0	1403.7	1402.4	1401.1	1399.9	1398.6
162.5°	1424.3	1425.7	1427.1	1427.2	1425.9	1424.6	1423.3	1422.0
165°	1453.3	1454.8	1456.4	1456.6	1455.6	1454.6	1453.5	1452.5
167.5°	1477.6	1479.3	1480.8	1480.8	1479.1	1477.5	1475.9	1474.3
170°	1490.9	1492.4	1494.0	1493.8	1492.0	1490.2	1488.3	1486.5
172.5°	1500.7	1502.4	1504.2	1504.2	1502.3	1500.5	1498.6	1496.8
175°	1511.3	1513.1	1514.9	1514.9	1513.1	1511.3	1509.4	1507.6
177.5°	1517.1	1518.6	1520.0	1519.9	1518.2	1516.6	1514.9	1513.3
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0

(END OF REPORT)