

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332632-830

Luminaire Tested: **S124DIP-S1020D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332632-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1020D365U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5369.6 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332632-830

CATALOG NUMBER: S124DIP-S1020D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332632-830

CATALOG NUMBER: S124DIP-S1020D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58	55
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49	46
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	43	40
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	45	41	37	35
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33	30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26	24
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332632-830

CATALOG NUMBER: S124DIP-S1020D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	2.9
10°-20°	431.5	8.0
20°-30°	635.2	11.8
30°-40°	738.4	13.8
40°-50°	738.4	13.8
50°-60°	645.9	12.0
60°-70°	479.7	8.9
70°-80°	272.5	5.1
80°-90°	79.9	1.5
90°-100°	28.4	0.5
100°-110°	84.2	1.6
110°-120°	142.8	2.7
120°-130°	188.3	3.5
130°-140°	211.5	3.9
140°-150°	207.8	3.9
150°-160°	174.8	3.3
160°-170°	116.3	2.2
170°-180°	40.7	0.8
0°-30°	1219.8	22.7
0°-40°	1958.2	36.5
0°-60°	3342.6	62.3
0°-90°	4174.8	77.7
90°-120°	255.4	4.8
90°-150°	863.0	16.1
90°-180°	1195.0	22.3
0°-180°	5369.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	1	5	7	9	10	5
95°	20	23	25	26	26	22
105°	78	78	79	80	81	82
115°	145	145	145	144	144	143
125°	212	211	211	210	210	188
135°	273	275	275	274	273	211
145°	331	333	333	333	332	207
155°	380	380	379	380	379	175
165°	413	412	412	413	412	116
175°	430	428	428	430	428	41
180°	431	431	431	431	431	



TEST NUMBER: P332632-830

CATALOG NUMBER: S124DIP-S1020D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	27.3	27.2	27.1	27.1	27.1	27.0	26.9	26.7	26.6	26.5	26.6
90°	1.0	1.8	2.6	3.5	4.2	5.0	5.6	6.1	6.7	7.4	7.7
92.5°	7.2	8.1	9.0	9.9	10.8	11.5	12.0	12.3	12.8	13.2	13.5
95°	20.0	20.6	21.3	22.0	22.6	23.3	23.8	24.3	24.8	25.4	25.5
97.5°	34.9	35.4	36.0	36.5	37.0	37.6	38.2	38.8	39.4	40.1	40.3
100°	46.7	46.9	47.2	47.5	47.8	48.3	48.9	49.7	50.3	51.0	51.1
102.5°	58.9	59.0	59.1	59.3	59.4	59.8	60.3	61.0	61.5	62.1	62.4
105°	77.6	77.7	77.8	77.9	77.9	78.0	78.4	78.7	79.0	79.3	79.5
107.5°	97.3	97.4	97.5	97.6	97.6	97.6	97.7	97.7	97.8	97.8	98.0
110°	110.6	110.7	110.8	111.0	111.1	111.2	111.1	111.0	110.9	110.9	110.7



TEST NUMBER: P332632-830

CATALOG NUMBER: S124DIP-S1020D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	124.4	124.4	124.5	124.5	124.5	124.5	124.3	124.2	124.1	123.9	123.9
115°	145.2	145.2	145.2	145.2	145.2	145.2	145.0	144.9	144.7	144.6	144.5
117.5°	164.8	164.9	164.9	164.9	165.0	165.0	164.9	164.9	164.7	164.6	164.4
120°	177.9	178.1	178.4	178.7	179.1	179.1	178.9	178.6	178.4	178.2	177.9
122.5°	191.4	191.5	191.7	191.8	191.9	191.9	191.8	191.7	191.6	191.5	191.2
125°	211.5	211.5	211.5	211.5	211.5	211.4	211.4	211.3	211.2	211.1	211.0
127.5°	229.7	229.9	230.2	230.4	230.5	230.6	230.5	230.4	230.3	230.2	230.0
130°	242.5	242.7	242.9	243.2	243.4	243.5	243.5	243.5	243.5	243.5	243.4
132.5°	255.5	255.7	255.8	256.0	256.2	256.2	256.2	256.1	256.1	256.0	255.8
135°	272.8	273.2	273.6	274.1	274.6	274.8	274.8	274.8	274.8	274.8	274.7
137.5°	291.5	291.8	292.0	292.2	292.4	292.6	292.7	292.8	292.9	293.0	292.8
140°	304.1	304.3	304.3	304.5	304.7	304.7	304.7	304.7	304.7	304.7	304.7
142.5°	315.6	315.7	315.8	315.9	316.1	316.2	316.1	316.0	316.0	315.9	315.9
145°	331.4	331.7	332.0	332.2	332.6	332.8	332.8	332.9	333.0	333.1	333.0
147.5°	347.1	347.5	347.8	348.2	348.6	348.6	348.6	348.6	348.6	348.5	348.4
150°	356.8	357.0	357.3	357.6	357.9	358.1	358.1	358.1	358.1	358.1	358.1
152.5°	365.8	366.0	366.1	366.3	366.5	366.6	366.6	366.7	366.7	366.8	367.0
155°	379.7	379.7	379.7	379.7	379.7	379.7	379.6	379.5	379.5	379.4	379.7
157.5°	391.4	391.2	391.2	391.1	390.9	390.8	390.8	390.8	390.8	390.8	391.0
160°	398.3	398.2	398.2	398.1	398.0	397.9	397.9	397.8	397.8	397.7	397.9
162.5°	404.7	404.5	404.4	404.2	404.0	403.9	403.8	403.7	403.6	403.5	404.0
165°	413.3	413.1	412.9	412.6	412.5	412.3	412.1	412.0	411.8	411.7	412.1
167.5°	419.9	419.6	419.3	419.0	418.7	418.5	418.6	418.6	418.6	418.6	419.1
170°	423.7	423.3	422.9	422.5	422.2	422.1	422.1	422.2	422.3	422.4	422.7
172.5°	426.3	426.0	425.7	425.4	425.1	424.9	424.9	425.0	425.0	425.0	425.5
175°	430.0	429.6	429.2	428.9	428.5	428.3	428.2	428.1	428.1	428.0	428.5
177.5°	431.2	430.9	430.6	430.3	430.0	429.9	429.9	429.9	429.9	429.9	430.3
180°	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6



TEST NUMBER: P332632-830

CATALOG NUMBER: S124DIP-S1020D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	26.7	26.8	26.9	26.9	27.0	27.0	27.0	27.1
90°	8.2	8.7	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	13.8	13.9	14.2	14.4	14.5	14.6	14.7	14.8
95°	25.7	26.0	26.2	26.3	26.3	26.3	26.3	26.3
97.5°	40.5	40.8	41.1	41.2	41.2	41.2	41.2	41.2
100°	51.3	51.4	51.6	51.7	51.7	51.7	51.7	51.7
102.5°	62.6	62.8	63.0	63.2	63.2	63.2	63.2	63.3
105°	79.7	79.9	80.1	80.4	80.6	80.9	81.1	81.2
107.5°	98.3	98.5	98.7	98.8	98.8	98.8	98.8	98.7
110°	110.7	110.5	110.3	110.4	110.6	110.8	111.0	111.2



TEST NUMBER: P332632-830

CATALOG NUMBER: S124DIP-S1020D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	123.9	123.9	123.9	123.9	123.9	123.9	123.9	124.0
115°	144.4	144.3	144.2	144.2	144.1	144.0	143.9	143.9
117.5°	164.1	163.8	163.6	163.4	163.2	163.1	163.0	162.8
120°	177.5	177.1	176.7	176.6	176.7	176.9	177.0	177.2
122.5°	191.1	190.8	190.5	190.2	190.0	189.7	189.5	189.2
125°	210.8	210.8	210.6	210.4	210.3	210.1	210.0	209.8
127.5°	229.9	229.7	229.5	229.4	229.3	229.2	229.0	228.9
130°	243.2	243.0	242.9	242.6	242.3	242.0	241.8	241.5
132.5°	255.7	255.5	255.4	255.2	255.1	255.1	255.0	254.8
135°	274.5	274.4	274.2	274.0	273.8	273.5	273.3	273.1
137.5°	292.7	292.5	292.3	292.2	292.2	292.3	292.3	292.4
140°	304.6	304.5	304.4	304.3	304.3	304.3	304.2	304.1
142.5°	315.9	315.9	315.8	315.8	315.8	315.8	315.8	315.8
145°	332.9	332.8	332.8	332.6	332.4	332.2	332.0	331.8
147.5°	348.4	348.3	348.2	348.2	348.1	348.0	347.9	347.9
150°	358.1	358.1	358.1	358.0	358.0	357.9	357.8	357.7
152.5°	367.2	367.4	367.6	367.5	367.3	367.1	366.9	366.7
155°	379.9	380.2	380.5	380.5	380.2	379.9	379.7	379.4
157.5°	391.2	391.4	391.6	391.6	391.3	391.2	390.9	390.6
160°	398.1	398.3	398.6	398.5	398.1	397.8	397.4	397.0
162.5°	404.4	404.7	405.1	405.1	404.8	404.4	404.1	403.7
165°	412.6	413.0	413.4	413.5	413.2	412.9	412.6	412.4
167.5°	419.5	419.9	420.4	420.4	419.9	419.4	419.0	418.5
170°	423.2	423.7	424.1	424.0	423.6	423.0	422.5	422.0
172.5°	426.0	426.5	427.0	427.0	426.5	425.9	425.5	424.9
175°	429.0	429.5	430.1	430.1	429.5	429.0	428.5	428.0
177.5°	430.6	431.1	431.5	431.5	431.0	430.6	430.1	429.6
180°	430.6	430.6	430.6	430.6	430.6	430.6	430.6	430.6

(END OF REPORT)