

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332697-840

Luminaire Tested: **S124DIP-S1195D1035U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332697-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1195D1035U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9543.3 lumens
Efficiency: N/A
Efficacy: 142.9 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				
1	99	95	91	88	92	89	85	82	77	74	72	65	64	62	55	54	53	48				
2	91	83	77	72	84	78	73	68	67	63	60	58	55	52	49	47	45	41				
3	83	74	66	60	77	69	62	57	60	55	51	51	48	44	43	41	38	35				
4	76	65	57	51	70	61	54	49	53	48	43	46	42	38	39	36	33	30				
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26				
6	64	52	44	39	60	49	42	37	43	37	33	37	33	29	32	29	26	23				
7	60	47	39	34	55	45	37	32	39	33	29	34	30	26	29	26	23	21				
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18				
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17				
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15713	15713	15713	15713
5°	18504	15754	13904	15754
10°	22155	15684	12518	15684
15°	26213	15525	11496	15525
20°	29190	15364	10584	15364
25°	29661	15126	9954	15126
30°	25239	14897	9755	14897
35°	19404	14526	9758	14526
40°	15125	14089	9941	14089
45°	12611	13431	10107	13431
50°	11099	12627	10451	12627
55°	10169	11667	10871	11667
60°	9529	10805	11378	10805
65°	8871	9841	11798	9841
70°	8108	8889	12066	8889
75°	7243	7820	11918	7820
80°	6072	6406	11544	6406
85°	4483	4631	11060	4631



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.6	2.0
10°-20°	584.5	6.1
20°-30°	926.8	9.7
30°-40°	1031.4	10.8
40°-50°	938.9	9.8
50°-60°	767.2	8.0
60°-70°	547.7	5.7
70°-80°	301.6	3.2
80°-90°	86.2	0.9
90°-100°	46.1	0.5
100°-110°	293.9	3.1
110°-120°	562.3	5.9
120°-130°	713.8	7.5
130°-140°	763.7	8.0
140°-150°	714.1	7.5
150°-160°	575.9	6.0
160°-170°	371.4	3.9
170°-180°	128.0	1.3
0°-30°	1700.9	17.8
0°-40°	2732.3	28.6
0°-60°	4438.4	46.5
0°-90°	5374.0	56.3
90°-120°	902.3	9.5
90°-150°	3094.0	32.4
90°-180°	4169.0	43.7
0°-180°	9543.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1946	1946	1946	1946	1946	
5°	2283	1944	1716	1944	2283	232
15°	3136	1858	1376	1858	3136	886
25°	3330	1698	1118	1698	3330	1468
35°	1969	1474	990	1474	1969	1250
45°	1105	1176	885	1176	1105	870
55°	722	829	772	829	722	653
65°	464	515	618	515	464	460
75°	232	251	382	251	232	247
85°	48	50	119	50	48	60
90°	30	3	30	3	30	15
95°	29	55	29	55	29	23
105°	287	304	287	304	287	251
115°	571	566	571	566	571	565
125°	802	796	802	796	802	715
135°	995	988	995	988	995	766
145°	1145	1139	1145	1139	1145	716
155°	1248	1249	1248	1249	1248	575
165°	1312	1318	1312	1318	1312	370
175°	1340	1348	1340	1348	1340	128
180°	1348	1348	1348	1348	1348	



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4
2.5°	2071.5	2070.8	2064.5	2063.2	2058.6	2052.9	2051.5	2041.2	2020.5	2010.8	2008.3
5°	2283.4	2299.6	2278.6	2274.5	2272.1	2245.5	2231.8	2215.6	2178.6	2156.9	2139.9
7.5°	2536.3	2538.2	2529.0	2521.6	2501.1	2477.9	2443.1	2406.0	2361.8	2315.8	2281.2
10°	2702.7	2709.2	2698.7	2697.0	2655.9	2630.1	2578.5	2535.0	2485.0	2429.3	2378.5
12.5°	2878.1	2869.1	2863.8	2829.2	2821.7	2774.6	2714.6	2669.8	2592.7	2528.7	2461.1
15°	3136.4	3118.8	3107.5	3059.9	3036.5	2971.1	2907.5	2858.3	2757.5	2661.6	2589.0
17.5°	3288.0	3305.8	3279.6	3260.1	3199.7	3153.9	3088.8	2985.6	2906.7	2787.5	2695.9
20°	3397.7	3399.3	3384.8	3364.7	3317.1	3259.0	3188.0	3075.1	2980.8	2862.4	2736.5
22.5°	3427.4	3427.7	3421.5	3402.7	3366.7	3319.6	3248.0	3153.9	3039.6	2910.7	2784.9
25°	3329.9	3326.7	3334.0	3355.0	3341.2	3326.7	3285.6	3215.5	3109.1	2972.7	2837.3
27.5°	2968.1	2990.3	3031.3	3082.9	3132.6	3170.5	3181.2	3166.7	3100.8	2988.8	2846.8
30°	2707.5	2734.9	2765.6	2817.1	2917.2	2974.4	3037.3	3084.8	3058.3	2968.8	2836.5
32.5°	2421.2	2427.9	2473.4	2532.0	2623.6	2733.8	2833.5	2930.0	2962.1	2915.2	2804.9
35°	1968.9	1980.2	2029.4	2087.5	2199.6	2334.2	2484.2	2618.0	2728.5	2772.8	2716.3
37.5°	1606.8	1639.2	1673.9	1736.3	1834.9	1956.2	2112.0	2285.2	2449.8	2560.1	2578.8
40°	1435.2	1455.3	1480.4	1527.9	1611.7	1731.1	1864.9	2063.3	2238.3	2396.3	2447.9
42.5°	1299.7	1311.5	1326.9	1369.9	1433.7	1552.5	1674.7	1849.2	2024.8	2213.7	2300.2
45°	1104.6	1116.7	1142.5	1167.5	1215.9	1298.1	1411.8	1555.3	1731.9	1914.1	2073.8
47.5°	963.7	971.4	986.7	1013.5	1054.6	1108.8	1201.3	1321.2	1484.9	1661.7	1831.9
50°	883.7	890.1	902.2	926.5	957.9	1006.2	1082.1	1194.1	1322.3	1500.5	1667.4
52.5°	820.5	823.0	831.9	848.4	873.3	914.0	976.2	1068.9	1188.1	1347.0	1513.3
55°	722.5	725.7	733.8	745.8	767.6	793.3	840.9	910.3	1014.3	1152.2	1296.5
57.5°	641.8	644.1	650.9	655.5	673.4	694.4	730.9	780.5	859.3	976.2	1105.1
60°	590.2	588.5	596.6	600.7	612.8	630.6	658.7	706.3	774.9	869.2	987.7
62.5°	539.9	537.7	544.4	549.8	556.6	571.8	594.9	632.2	687.7	773.1	875.5
65°	464.4	461.2	465.2	471.7	478.2	486.1	503.1	536.1	580.6	641.8	720.0
67.5°	388.6	392.0	392.6	395.9	399.6	410.6	422.1	445.6	476.9	525.8	592.2
70°	343.5	344.3	347.5	347.5	349.9	359.6	369.3	382.9	413.6	458.8	512.8
72.5°	298.3	301.7	300.4	303.0	304.8	311.2	318.3	331.3	357.5	391.0	436.7
75°	232.2	234.6	234.6	235.4	237.8	240.2	245.9	255.6	274.2	299.1	330.5
77.5°	169.4	169.7	170.8	173.7	173.7	177.5	181.8	189.5	198.6	215.8	235.0
80°	130.6	132.2	131.4	133.0	133.0	136.2	137.8	147.5	151.6	162.9	178.1
82.5°	95.8	97.4	97.3	99.5	100.8	101.4	103.7	107.6	111.6	121.6	127.8
85°	48.4	50.0	48.4	50.0	52.4	53.2	55.6	56.5	59.7	62.1	67.8
87.5°	20.2	22.1	22.0	22.5	23.7	24.2	24.6	23.6	26.0	26.4	28.6
90°	30.2	29.8	29.4	28.9	28.5	27.6	26.3	24.8	23.5	22.2	20.4
92.5°	27.9	27.8	27.7	27.6	27.5	26.8	25.4	24.0	22.7	21.4	19.6
95°	29.2	29.0	28.8	28.6	28.4	27.6	26.3	24.8	23.5	22.2	21.9
97.5°	28.3	28.0	27.8	27.6	27.4	27.2	27.1	26.9	26.8	26.7	51.6
100°	28.3	28.0	27.8	27.6	27.4	29.1	32.9	36.8	40.6	44.3	75.2
102.5°	29.1	29.0	29.0	28.9	28.9	49.4	90.5	131.6	172.6	213.7	217.7
105°	287.3	295.4	303.5	311.5	319.6	322.6	320.5	318.6	316.6	314.6	313.5
107.5°	400.4	399.6	398.7	397.9	397.0	396.1	395.2	394.2	393.1	392.1	390.6
110°	449.6	449.0	448.3	447.6	447.0	446.4	446.0	445.5	445.0	444.5	443.2



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	498.8	498.0	497.2	496.2	495.4	495.0	495.1	495.2	495.3	495.3	494.7
115°	570.6	570.6	570.6	570.6	570.6	570.4	570.0	569.5	569.1	568.6	568.8
117.5°	643.6	643.7	643.8	643.9	644.0	644.0	644.1	644.2	644.3	644.4	643.9
120°	689.5	690.0	690.4	690.8	691.4	691.4	690.8	690.4	690.0	689.5	689.7
122.5°	734.7	735.2	735.6	736.1	736.5	736.6	736.3	736.1	735.8	735.5	735.2
125°	802.4	802.2	802.0	801.8	801.5	801.1	800.4	799.8	799.1	798.4	798.9
127.5°	861.9	862.1	862.3	862.5	862.6	862.8	862.9	863.1	863.2	863.3	862.3
130°	902.3	902.3	902.3	902.3	902.3	902.1	901.9	901.7	901.5	901.3	900.6
132.5°	939.4	939.6	939.7	939.9	940.1	940.1	939.9	939.6	939.4	939.2	938.3
135°	995.0	994.5	994.1	993.7	993.2	992.8	992.3	991.9	991.4	991.0	990.1
137.5°	1042.6	1042.7	1042.9	1043.0	1043.1	1043.0	1042.5	1042.0	1041.5	1041.0	1040.0
140°	1075.7	1075.4	1075.2	1075.0	1074.8	1074.3	1073.7	1073.0	1072.3	1071.7	1071.2
142.5°	1103.1	1103.1	1103.0	1103.0	1102.9	1102.7	1102.2	1101.7	1101.2	1100.7	1100.3
145°	1145.2	1144.8	1144.3	1143.9	1143.5	1143.1	1142.9	1142.7	1142.5	1142.2	1142.2
147.5°	1180.1	1179.9	1179.6	1179.4	1179.2	1179.0	1178.8	1178.6	1178.5	1178.3	1178.5
150°	1202.6	1202.4	1202.2	1202.0	1201.7	1201.6	1201.6	1201.6	1201.6	1201.6	1201.9
152.5°	1222.0	1222.1	1222.3	1222.4	1222.5	1222.4	1222.1	1221.7	1221.4	1221.0	1221.4
155°	1248.1	1248.7	1249.4	1250.1	1250.7	1250.6	1249.7	1248.8	1247.9	1247.1	1247.7
157.5°	1269.8	1271.0	1272.1	1273.3	1274.4	1274.4	1273.3	1272.1	1271.0	1269.8	1270.6
160°	1284.3	1285.7	1287.1	1288.4	1289.7	1289.7	1288.4	1287.1	1285.7	1284.3	1284.5
162.5°	1295.7	1297.2	1298.7	1300.2	1301.7	1301.8	1300.5	1299.1	1297.8	1296.5	1296.7
165°	1311.5	1313.5	1315.6	1317.6	1319.6	1319.7	1318.0	1316.2	1314.3	1312.5	1312.5
167.5°	1323.4	1325.6	1328.0	1330.2	1332.4	1332.5	1330.6	1328.6	1326.7	1324.6	1324.8
170°	1330.7	1332.9	1335.2	1337.5	1339.7	1339.9	1338.1	1336.4	1334.5	1332.7	1332.5
172.5°	1334.7	1337.2	1339.6	1342.0	1344.4	1344.7	1342.9	1341.2	1339.4	1337.6	1337.4
175°	1339.8	1342.5	1345.1	1347.9	1350.5	1350.9	1348.9	1346.9	1344.8	1342.8	1342.6
177.5°	1343.0	1345.1	1347.4	1349.5	1351.6	1352.0	1350.5	1349.1	1347.7	1346.3	1345.8
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4
2.5°	2008.9	1999.9	1993.5	1988.3	1974.1	1965.7	1959.2	1950.3	1940.0	1928.9	1915.4
5°	2122.9	2095.6	2075.4	2044.8	2015.7	1991.6	1966.5	1944.0	1916.5	1886.7	1864.9
7.5°	2242.8	2202.0	2149.7	2104.5	2053.5	2009.1	1969.4	1928.8	1886.5	1845.6	1808.1
10°	2318.9	2266.4	2208.4	2139.9	2075.4	2018.1	1964.9	1913.3	1863.3	1813.3	1770.6
12.5°	2400.9	2335.5	2249.7	2169.6	2097.3	2020.7	1956.5	1893.3	1833.0	1780.5	1730.6
15°	2510.8	2416.4	2317.2	2210.0	2114.9	2025.4	1937.5	1857.6	1790.0	1720.6	1672.2
17.5°	2578.4	2461.6	2348.2	2236.1	2121.0	2008.1	1913.3	1821.3	1736.5	1667.6	1606.6
20°	2622.8	2506.8	2365.6	2253.6	2116.5	2000.4	1890.8	1788.4	1699.7	1626.3	1563.4
22.5°	2661.6	2527.4	2386.3	2238.8	2102.3	1979.1	1859.2	1756.1	1665.5	1588.2	1527.9
25°	2682.5	2528.5	2375.3	2228.6	2073.8	1927.8	1819.0	1698.1	1601.2	1519.8	1455.3
27.5°	2684.8	2520.1	2346.8	2183.7	2024.0	1888.0	1750.6	1642.5	1542.1	1456.0	1394.1
30°	2677.7	2506.0	2319.7	2143.1	1982.7	1835.1	1715.8	1598.1	1495.7	1410.2	1345.6
32.5°	2655.1	2476.3	2284.8	2098.0	1931.7	1787.4	1664.2	1552.3	1452.5	1368.3	1300.5
35°	2589.8	2413.2	2209.2	2014.9	1844.8	1698.9	1587.6	1473.9	1373.9	1294.1	1228.8
37.5°	2487.7	2328.0	2120.7	1919.7	1752.5	1606.0	1495.7	1392.9	1302.8	1221.7	1154.8
40°	2398.7	2258.5	2050.4	1854.4	1673.9	1534.4	1431.2	1336.9	1247.3	1170.7	1107.0
42.5°	2296.1	2173.9	1982.1	1774.4	1600.3	1460.2	1359.6	1274.9	1190.5	1119.7	1056.1
45°	2113.2	2032.7	1852.1	1660.1	1478.7	1346.5	1250.5	1176.4	1105.4	1036.1	982.9
47.5°	1903.0	1863.0	1710.9	1528.7	1356.5	1226.2	1143.0	1074.5	1012.2	953.5	906.6
50°	1761.7	1742.4	1610.9	1435.2	1270.7	1148.1	1064.3	1005.4	952.2	900.6	856.3
52.5°	1622.4	1621.7	1503.3	1342.3	1190.1	1072.1	988.9	933.8	887.8	845.8	806.0
55°	1409.4	1432.0	1339.3	1195.7	1059.4	953.0	878.1	828.9	796.6	761.9	732.2
57.5°	1213.8	1251.2	1174.8	1048.3	934.6	836.6	771.3	734.4	700.0	679.0	657.3
60°	1086.1	1121.6	1061.9	955.4	848.2	764.4	702.3	669.2	639.3	624.9	609.6
62.5°	972.5	1004.1	960.0	861.3	768.2	687.6	635.2	603.4	583.3	567.4	557.3
65°	810.3	837.0	799.0	727.3	647.4	583.0	540.2	515.2	495.8	489.4	478.2
67.5°	655.0	679.2	658.7	597.7	533.7	484.9	451.5	427.5	416.1	410.4	402.3
70°	562.8	586.9	565.2	512.0	462.8	421.7	390.2	376.6	364.5	362.0	350.7
72.5°	484.7	501.2	479.4	437.8	395.8	361.0	336.7	322.3	316.1	311.7	305.6
75°	363.7	378.2	363.7	331.3	301.5	277.4	256.4	250.7	243.5	241.1	237.0
77.5°	257.4	269.9	258.8	238.6	216.4	197.7	186.4	179.2	177.5	173.4	175.3
80°	196.7	204.8	194.3	180.6	162.9	150.0	141.9	137.8	133.0	131.4	134.6
82.5°	141.3	144.8	139.5	130.3	117.0	108.7	103.2	98.6	97.6	97.9	97.9
85°	73.4	72.6	71.8	63.7	59.7	54.0	50.8	50.0	49.2	50.8	52.4
87.5°	28.3	28.5	27.5	24.5	22.1	19.7	18.5	17.4	18.5	19.7	20.8
90°	18.6	16.8	15.0	12.9	10.4	8.0	5.5	3.0	5.5	8.0	10.4
92.5°	17.8	16.0	14.2	13.2	13.1	12.9	12.8	12.7	12.8	12.9	13.1
95°	21.7	21.5	21.3	24.9	32.6	40.2	47.9	55.4	47.9	40.2	32.6
97.5°	76.6	101.6	126.6	136.7	132.0	127.2	122.5	117.8	122.5	127.2	132.0
100°	106.2	137.1	168.0	181.5	177.4	173.4	169.4	165.3	169.4	173.4	177.4
102.5°	221.8	225.8	229.8	230.4	227.4	224.5	221.6	218.5	221.6	224.5	227.4
105°	312.3	311.1	310.0	308.8	307.5	306.1	304.8	303.5	304.8	306.1	307.5
107.5°	389.1	387.6	386.1	385.0	384.3	383.6	382.9	382.2	382.9	383.6	384.3
110°	441.9	440.5	439.2	438.2	437.5	436.9	436.2	435.6	436.2	436.9	437.5



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	494.1	493.5	492.9	492.0	490.8	489.6	488.4	487.2	488.4	489.6	490.8
115°	569.1	569.3	569.5	569.3	568.6	567.9	567.2	566.5	567.2	567.9	568.6
117.5°	643.4	642.9	642.4	641.8	640.9	640.0	639.0	638.1	639.0	640.0	640.9
120°	690.0	690.2	690.4	690.1	689.2	688.3	687.4	686.5	687.4	688.3	689.2
122.5°	734.9	734.6	734.3	733.9	733.3	732.8	732.3	731.6	732.3	732.8	733.3
125°	799.3	799.8	800.2	800.0	799.1	798.2	797.3	796.4	797.3	798.2	799.1
127.5°	861.3	860.3	859.2	858.6	858.4	858.2	857.9	857.7	857.9	858.2	858.4
130°	899.9	899.3	898.6	898.1	897.9	897.7	897.5	897.3	897.5	897.7	897.9
132.5°	937.5	936.6	935.7	935.1	934.7	934.3	933.9	933.5	933.9	934.3	934.7
135°	989.2	988.3	987.3	987.0	987.2	987.5	987.7	988.0	987.7	987.5	987.2
137.5°	1039.1	1038.0	1037.0	1036.5	1036.4	1036.3	1036.2	1036.1	1036.2	1036.3	1036.4
140°	1070.8	1070.3	1069.9	1069.3	1068.9	1068.5	1068.0	1067.6	1068.0	1068.5	1068.9
142.5°	1100.1	1099.8	1099.5	1099.0	1098.2	1097.4	1096.6	1095.8	1096.6	1097.4	1098.2
145°	1142.2	1142.2	1142.2	1141.9	1141.1	1140.5	1139.8	1139.1	1139.8	1140.5	1141.1
147.5°	1178.7	1178.9	1179.2	1178.7	1177.4	1176.2	1174.9	1173.7	1174.9	1176.2	1177.4
150°	1202.1	1202.3	1202.5	1202.2	1201.3	1200.4	1199.5	1198.6	1199.5	1200.4	1201.3
152.5°	1221.8	1222.2	1222.6	1222.4	1221.7	1221.0	1220.3	1219.6	1220.3	1221.0	1221.7
155°	1248.4	1249.1	1249.7	1249.9	1249.7	1249.5	1249.3	1249.1	1249.3	1249.5	1249.7
157.5°	1271.3	1272.1	1272.8	1273.3	1273.4	1273.5	1273.7	1273.8	1273.7	1273.5	1273.4
160°	1284.8	1285.1	1285.3	1285.7	1286.4	1287.1	1287.7	1288.4	1287.7	1287.1	1286.4
162.5°	1296.9	1297.1	1297.4	1297.9	1298.7	1299.6	1300.4	1301.3	1300.4	1299.6	1298.7
165°	1312.5	1312.5	1312.5	1313.1	1314.2	1315.3	1316.5	1317.6	1316.5	1315.3	1314.2
167.5°	1324.9	1325.0	1325.2	1325.9	1327.1	1328.2	1329.4	1330.5	1329.4	1328.2	1327.1
170°	1332.3	1332.0	1331.8	1332.4	1333.7	1335.0	1336.5	1337.8	1336.5	1335.0	1333.7
172.5°	1337.2	1336.9	1336.7	1337.3	1338.6	1339.9	1341.3	1342.6	1341.3	1339.9	1338.6
175°	1342.4	1342.1	1341.9	1342.5	1343.8	1345.1	1346.6	1347.9	1346.6	1345.1	1343.8
177.5°	1345.5	1345.1	1344.8	1345.2	1346.6	1347.8	1349.0	1350.3	1349.0	1347.8	1346.6
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4
2.5°	1908.9	1903.2	1894.8	1883.2	1873.5	1863.2	1860.6	1856.7	1864.4	1858.1	1856.0
5°	1846.4	1829.5	1807.7	1782.7	1768.2	1747.3	1743.2	1735.2	1727.1	1726.3	1718.2
7.5°	1780.1	1755.2	1726.8	1701.2	1677.7	1654.9	1639.8	1636.6	1624.7	1617.7	1609.6
10°	1737.6	1706.9	1673.9	1649.7	1622.2	1598.1	1581.1	1571.5	1563.4	1554.5	1546.5
12.5°	1687.3	1654.7	1627.4	1601.2	1568.7	1550.3	1522.5	1505.7	1504.1	1504.2	1483.3
15°	1628.7	1596.5	1554.5	1517.4	1499.6	1464.2	1448.9	1429.6	1417.4	1405.3	1395.7
17.5°	1561.8	1521.7	1488.8	1446.3	1412.5	1384.2	1364.1	1352.5	1334.2	1317.2	1304.7
20°	1519.8	1477.1	1442.5	1397.2	1360.2	1325.5	1308.6	1292.5	1278.8	1264.3	1250.5
22.5°	1477.2	1432.6	1390.2	1346.4	1311.8	1275.3	1258.9	1237.0	1224.0	1215.9	1202.1
25°	1410.2	1361.8	1313.4	1271.5	1236.1	1203.8	1182.0	1165.1	1150.5	1144.1	1135.3
27.5°	1337.3	1289.3	1242.5	1194.9	1154.6	1131.3	1113.8	1101.1	1092.7	1084.1	1080.2
30°	1290.9	1240.9	1190.9	1146.5	1109.4	1086.1	1070.0	1061.1	1054.6	1050.6	1046.5
32.5°	1243.7	1194.5	1141.9	1101.4	1068.1	1047.3	1035.1	1026.2	1023.0	1021.6	1020.2
35°	1168.3	1118.3	1070.0	1033.7	1002.2	994.1	983.7	978.9	977.2	982.9	985.3
37.5°	1095.3	1048.8	1004.3	969.2	948.6	936.8	933.2	933.3	939.2	944.1	950.0
40°	1048.1	1003.0	961.1	930.5	911.1	903.8	902.2	906.3	912.7	918.4	924.8
42.5°	1002.4	957.9	919.8	891.1	877.6	870.9	871.9	876.0	884.9	891.9	901.6
45°	931.3	894.1	857.1	833.7	822.4	824.0	824.0	831.3	840.1	850.6	861.1
47.5°	864.3	827.0	796.5	776.8	770.9	769.5	774.1	783.6	796.3	809.2	823.8
50°	819.2	783.8	757.1	739.3	733.0	735.4	741.7	750.6	766.0	782.1	797.4
52.5°	773.4	741.1	716.5	700.0	695.5	699.8	706.3	720.3	733.8	751.1	769.7
55°	702.3	674.9	655.5	643.4	641.8	644.2	651.5	666.8	686.1	707.9	725.7
57.5°	631.5	608.5	590.9	582.5	583.3	585.5	597.4	615.7	636.3	659.5	682.5
60°	583.7	562.8	548.3	541.8	542.6	547.4	562.0	579.0	604.7	627.3	651.5
62.5°	538.6	520.2	506.3	500.6	499.4	510.1	523.9	541.5	567.3	592.5	618.5
65°	466.1	451.5	440.2	437.0	439.4	447.5	465.2	488.6	510.4	536.9	564.4
67.5°	395.1	383.1	375.4	376.9	379.8	391.7	406.6	426.7	451.4	479.0	506.0
70°	349.9	338.6	332.1	333.0	337.8	352.3	365.3	385.4	412.0	440.2	462.8
72.5°	303.5	296.1	290.2	293.7	298.5	308.5	324.6	344.8	368.2	394.5	418.3
75°	233.0	233.0	229.7	232.2	239.4	249.1	261.3	282.2	305.6	326.6	345.9
77.5°	172.9	171.1	173.2	176.1	180.3	191.8	205.6	220.6	238.2	259.1	275.1
80°	132.2	133.0	137.0	141.9	143.5	152.4	166.9	180.6	194.3	212.1	227.4
82.5°	99.4	100.2	102.2	108.4	110.0	119.5	128.9	142.6	155.0	166.9	179.7
85°	54.0	54.0	58.1	60.5	64.5	71.0	76.5	84.6	95.9	104.0	116.1
87.5°	23.2	23.6	26.6	28.3	30.5	34.1	35.6	43.0	45.8	49.4	55.3
90°	12.9	15.0	16.8	18.6	20.4	22.2	23.5	24.8	26.3	27.6	28.5
92.5°	13.2	14.2	16.0	17.8	19.6	21.4	22.7	24.0	25.4	26.8	27.5
95°	24.9	21.3	21.5	21.7	21.9	22.2	23.5	24.8	26.3	27.6	28.4
97.5°	136.7	126.6	101.6	76.6	51.6	26.7	26.8	26.9	27.1	27.2	27.4
100°	181.5	168.0	137.1	106.2	75.2	44.3	40.6	36.8	32.9	29.1	27.4
102.5°	230.4	229.8	225.8	221.8	217.7	213.7	172.6	131.6	90.5	49.4	28.9
105°	308.8	310.0	311.1	312.3	313.5	314.6	316.6	318.6	320.5	322.6	319.6
107.5°	385.0	386.1	387.6	389.1	390.6	392.1	393.1	394.2	395.2	396.1	397.0
110°	438.2	439.2	440.5	441.9	443.2	444.5	445.0	445.5	446.0	446.4	447.0



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	492.0	492.9	493.5	494.1	494.7	495.3	495.3	495.2	495.1	495.0	495.4
115°	569.3	569.5	569.3	569.1	568.8	568.6	569.1	569.5	570.0	570.4	570.6
117.5°	641.8	642.4	642.9	643.4	643.9	644.4	644.3	644.2	644.1	644.0	644.0
120°	690.1	690.4	690.2	690.0	689.7	689.5	690.0	690.4	690.8	691.4	691.4
122.5°	733.9	734.3	734.6	734.9	735.2	735.5	735.8	736.1	736.3	736.6	736.5
125°	800.0	800.2	799.8	799.3	798.9	798.4	799.1	799.8	800.4	801.1	801.5
127.5°	858.6	859.2	860.3	861.3	862.3	863.3	863.2	863.1	862.9	862.8	862.6
130°	898.1	898.6	899.3	899.9	900.6	901.3	901.5	901.7	901.9	902.1	902.3
132.5°	935.1	935.7	936.6	937.5	938.3	939.2	939.4	939.6	939.9	940.1	940.1
135°	987.0	987.3	988.3	989.2	990.1	991.0	991.4	991.9	992.3	992.8	993.2
137.5°	1036.5	1037.0	1038.0	1039.1	1040.0	1041.0	1041.5	1042.0	1042.5	1043.0	1043.1
140°	1069.3	1069.9	1070.3	1070.8	1071.2	1071.7	1072.3	1073.0	1073.7	1074.3	1074.8
142.5°	1099.0	1099.5	1099.8	1100.1	1100.3	1100.7	1101.2	1101.7	1102.2	1102.7	1102.9
145°	1141.9	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5	1142.7	1142.9	1143.1	1143.5
147.5°	1178.7	1179.2	1178.9	1178.7	1178.5	1178.3	1178.5	1178.6	1178.8	1179.0	1179.2
150°	1202.2	1202.5	1202.3	1202.1	1201.9	1201.6	1201.6	1201.6	1201.6	1201.6	1201.7
152.5°	1222.4	1222.6	1222.2	1221.8	1221.4	1221.0	1221.4	1221.7	1222.1	1222.4	1222.5
155°	1249.9	1249.7	1249.1	1248.4	1247.7	1247.1	1247.9	1248.8	1249.7	1250.6	1250.7
157.5°	1273.3	1272.8	1272.1	1271.3	1270.6	1269.8	1271.0	1272.1	1273.3	1274.4	1274.4
160°	1285.7	1285.3	1285.1	1284.8	1284.5	1284.3	1285.7	1287.1	1288.4	1289.7	1289.7
162.5°	1297.9	1297.4	1297.1	1296.9	1296.7	1296.5	1297.8	1299.1	1300.5	1301.8	1301.7
165°	1313.1	1312.5	1312.5	1312.5	1312.5	1312.5	1314.3	1316.2	1318.0	1319.7	1319.6
167.5°	1325.9	1325.2	1325.0	1324.9	1324.8	1324.6	1326.7	1328.6	1330.6	1332.5	1332.4
170°	1332.4	1331.8	1332.0	1332.3	1332.5	1332.7	1334.5	1336.4	1338.1	1339.9	1339.7
172.5°	1337.3	1336.7	1336.9	1337.2	1337.4	1337.6	1339.4	1341.2	1342.9	1344.7	1344.4
175°	1342.5	1341.9	1342.1	1342.4	1342.6	1342.8	1344.8	1346.9	1348.9	1350.9	1350.5
177.5°	1345.2	1344.8	1345.1	1345.5	1345.8	1346.3	1347.7	1349.1	1350.5	1352.0	1351.6
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4
2.5°	1854.8	1853.5	1849.0	1848.4	1849.0	1853.5	1854.8	1856.0	1858.1	1864.4	1856.7
5°	1713.3	1709.3	1706.9	1715.8	1706.9	1709.3	1713.3	1718.2	1726.3	1727.1	1735.2
7.5°	1606.8	1603.6	1596.5	1594.2	1596.5	1603.6	1606.8	1609.6	1617.7	1624.7	1636.6
10°	1538.4	1535.2	1528.7	1527.1	1528.7	1535.2	1538.4	1546.5	1554.5	1563.4	1571.5
12.5°	1472.6	1466.1	1464.9	1466.5	1464.9	1466.1	1472.6	1483.3	1504.2	1504.1	1505.7
15°	1385.2	1382.0	1373.1	1375.5	1373.1	1382.0	1385.2	1395.7	1405.3	1417.4	1429.6
17.5°	1299.1	1295.3	1284.4	1293.9	1284.4	1295.3	1299.1	1304.7	1317.2	1334.2	1352.5
20°	1244.9	1238.5	1232.8	1232.0	1232.8	1238.5	1244.9	1250.5	1264.3	1278.8	1292.5
22.5°	1193.3	1187.5	1187.0	1181.7	1187.0	1187.5	1193.3	1202.1	1215.9	1224.0	1237.0
25°	1128.8	1123.2	1121.6	1117.5	1121.6	1123.2	1128.8	1135.3	1144.1	1150.5	1165.1
27.5°	1079.3	1076.5	1073.7	1074.9	1073.7	1076.5	1079.3	1080.2	1084.1	1092.7	1101.1
30°	1048.9	1048.1	1046.5	1046.5	1046.5	1048.1	1048.9	1046.5	1050.6	1054.6	1061.1
32.5°	1023.8	1023.7	1024.6	1024.6	1024.6	1023.7	1023.8	1020.2	1021.6	1023.0	1026.2
35°	988.6	990.9	992.5	990.1	992.5	990.9	988.6	985.3	982.9	977.2	978.9
37.5°	956.5	959.0	961.3	964.0	961.3	959.0	956.5	950.0	944.1	939.2	933.3
40°	932.1	937.8	939.3	943.3	939.3	937.8	932.1	924.8	918.4	912.7	906.3
42.5°	908.9	915.1	919.3	920.1	919.3	915.1	908.9	901.6	891.9	884.9	876.0
45°	873.2	879.7	885.3	885.3	885.3	879.7	873.2	861.1	850.6	840.1	831.3
47.5°	836.3	845.7	851.3	852.7	851.3	845.7	836.3	823.8	809.2	796.3	783.6
50°	811.1	822.4	828.1	832.1	828.1	822.4	811.1	797.4	782.1	766.0	750.6
52.5°	786.6	797.9	805.5	807.6	805.5	797.9	786.6	769.7	751.1	733.8	720.3
55°	744.2	760.3	769.2	772.4	769.2	760.3	744.2	725.7	707.9	686.1	666.8
57.5°	704.2	719.0	729.3	731.7	729.3	719.0	704.2	682.5	659.5	636.3	615.7
60°	673.3	689.3	702.3	704.7	702.3	689.3	673.3	651.5	627.3	604.7	579.0
62.5°	641.7	658.4	670.0	676.3	670.0	658.4	641.7	618.5	592.5	567.3	541.5
65°	586.9	603.9	615.2	617.6	615.2	603.9	586.9	564.4	536.9	510.4	488.6
67.5°	527.4	544.2	551.7	556.3	551.7	544.2	527.4	506.0	479.0	451.4	426.7
70°	485.3	499.1	507.2	511.2	507.2	499.1	485.3	462.8	440.2	412.0	385.4
72.5°	437.7	452.0	461.4	462.1	461.4	452.0	437.7	418.3	394.5	368.2	344.8
75°	364.5	377.4	382.1	382.1	382.1	377.4	364.5	345.9	326.6	305.6	282.2
77.5°	288.5	295.1	301.2	302.6	301.2	295.1	288.5	275.1	259.1	238.2	220.6
80°	239.4	243.5	248.3	248.3	248.3	243.5	239.4	227.4	212.1	194.3	180.6
82.5°	189.1	192.6	197.4	196.7	197.4	192.6	189.1	179.7	166.9	155.0	142.6
85°	114.5	121.8	121.0	119.4	121.0	121.8	114.5	116.1	104.0	95.9	84.6
87.5°	57.4	58.1	60.2	61.5	60.2	58.1	57.4	55.3	49.4	45.8	43.0
90°	28.9	29.4	29.8	30.2	29.8	29.4	28.9	28.5	27.6	26.3	24.8
92.5°	27.6	27.7	27.8	27.9	27.8	27.7	27.6	27.5	26.8	25.4	24.0
95°	28.6	28.8	29.0	29.2	29.0	28.8	28.6	28.4	27.6	26.3	24.8
97.5°	27.6	27.8	28.0	28.3	28.0	27.8	27.6	27.4	27.2	27.1	26.9
100°	27.6	27.8	28.0	28.3	28.0	27.8	27.6	27.4	29.1	32.9	36.8
102.5°	28.9	29.0	29.0	29.1	29.0	29.0	28.9	28.9	49.4	90.5	131.6
105°	311.5	303.5	295.4	287.3	295.4	303.5	311.5	319.6	322.6	320.5	318.6
107.5°	397.9	398.7	399.6	400.4	399.6	398.7	397.9	397.0	396.1	395.2	394.2
110°	447.6	448.3	449.0	449.6	449.0	448.3	447.6	447.0	446.4	446.0	445.5



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	496.2	497.2	498.0	498.8	498.0	497.2	496.2	495.4	495.0	495.1	495.2
115°	570.6	570.6	570.6	570.6	570.6	570.6	570.6	570.6	570.4	570.0	569.5
117.5°	643.9	643.8	643.7	643.6	643.7	643.8	643.9	644.0	644.0	644.1	644.2
120°	690.8	690.4	690.0	689.5	690.0	690.4	690.8	691.4	691.4	690.8	690.4
122.5°	736.1	735.6	735.2	734.7	735.2	735.6	736.1	736.5	736.6	736.3	736.1
125°	801.8	802.0	802.2	802.4	802.2	802.0	801.8	801.5	801.1	800.4	799.8
127.5°	862.5	862.3	862.1	861.9	862.1	862.3	862.5	862.6	862.8	862.9	863.1
130°	902.3	902.3	902.3	902.3	902.3	902.3	902.3	902.3	902.1	901.9	901.7
132.5°	939.9	939.7	939.6	939.4	939.6	939.7	939.9	940.1	940.1	939.9	939.6
135°	993.7	994.1	994.5	995.0	994.5	994.1	993.7	993.2	992.8	992.3	991.9
137.5°	1043.0	1042.9	1042.7	1042.6	1042.7	1042.9	1043.0	1043.1	1043.0	1042.5	1042.0
140°	1075.0	1075.2	1075.4	1075.7	1075.4	1075.2	1075.0	1074.8	1074.3	1073.7	1073.0
142.5°	1103.0	1103.0	1103.1	1103.1	1103.1	1103.0	1103.0	1102.9	1102.7	1102.2	1101.7
145°	1143.9	1144.3	1144.8	1145.2	1144.8	1144.3	1143.9	1143.5	1143.1	1142.9	1142.7
147.5°	1179.4	1179.6	1179.9	1180.1	1179.9	1179.6	1179.4	1179.2	1179.0	1178.8	1178.6
150°	1202.0	1202.2	1202.4	1202.6	1202.4	1202.2	1202.0	1201.7	1201.6	1201.6	1201.6
152.5°	1222.4	1222.3	1222.1	1222.0	1222.1	1222.3	1222.4	1222.5	1222.4	1222.1	1221.7
155°	1250.1	1249.4	1248.7	1248.1	1248.7	1249.4	1250.1	1250.7	1250.6	1249.7	1248.8
157.5°	1273.3	1272.1	1271.0	1269.8	1271.0	1272.1	1273.3	1274.4	1274.4	1273.3	1272.1
160°	1288.4	1287.1	1285.7	1284.3	1285.7	1287.1	1288.4	1289.7	1289.7	1288.4	1287.1
162.5°	1300.2	1298.7	1297.2	1295.7	1297.2	1298.7	1300.2	1301.7	1301.8	1300.5	1299.1
165°	1317.6	1315.6	1313.5	1311.5	1313.5	1315.6	1317.6	1319.6	1319.7	1318.0	1316.2
167.5°	1330.2	1328.0	1325.6	1323.4	1325.6	1328.0	1330.2	1332.4	1332.5	1330.6	1328.6
170°	1337.5	1335.2	1332.9	1330.7	1332.9	1335.2	1337.5	1339.7	1339.9	1338.1	1336.4
172.5°	1342.0	1339.6	1337.2	1334.7	1337.2	1339.6	1342.0	1344.4	1344.7	1342.9	1341.2
175°	1347.9	1345.1	1342.5	1339.8	1342.5	1345.1	1347.9	1350.5	1350.9	1348.9	1346.9
177.5°	1349.5	1347.4	1345.1	1343.0	1345.1	1347.4	1349.5	1351.6	1352.0	1350.5	1349.1
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4
2.5°	1860.6	1863.2	1873.5	1883.2	1894.8	1903.2	1908.9	1915.4	1928.9	1940.0	1950.3
5°	1743.2	1747.3	1768.2	1782.7	1807.7	1829.5	1846.4	1864.9	1886.7	1916.5	1944.0
7.5°	1639.8	1654.9	1677.7	1701.2	1726.8	1755.2	1780.1	1808.1	1845.6	1886.5	1928.8
10°	1581.1	1598.1	1622.2	1649.7	1673.9	1706.9	1737.6	1770.6	1813.3	1863.3	1913.3
12.5°	1522.5	1550.3	1568.7	1601.2	1627.4	1654.7	1687.3	1730.6	1780.5	1833.0	1893.3
15°	1448.9	1464.2	1499.6	1517.4	1554.5	1596.5	1628.7	1672.2	1720.6	1790.0	1857.6
17.5°	1364.1	1384.2	1412.5	1446.3	1488.8	1521.7	1561.8	1606.6	1667.6	1736.5	1821.3
20°	1308.6	1325.5	1360.2	1397.2	1442.5	1477.1	1519.8	1563.4	1626.3	1699.7	1788.4
22.5°	1258.9	1275.3	1311.8	1346.4	1390.2	1432.6	1477.2	1527.9	1588.2	1665.5	1756.1
25°	1182.0	1203.8	1236.1	1271.5	1313.4	1361.8	1410.2	1455.3	1519.8	1601.2	1698.1
27.5°	1113.8	1131.3	1154.6	1194.9	1242.5	1289.3	1337.3	1394.1	1456.0	1542.1	1642.5
30°	1070.0	1086.1	1109.4	1146.5	1190.9	1240.9	1290.9	1345.6	1410.2	1495.7	1598.1
32.5°	1035.1	1047.3	1068.1	1101.4	1141.9	1194.5	1243.7	1300.5	1368.3	1452.5	1552.3
35°	983.7	994.1	1002.2	1033.7	1070.0	1118.3	1168.3	1228.8	1294.1	1373.9	1473.9
37.5°	933.2	936.8	948.6	969.2	1004.3	1048.8	1095.3	1154.8	1221.7	1302.8	1392.9
40°	902.2	903.8	911.1	930.5	961.1	1003.0	1048.1	1107.0	1170.7	1247.3	1336.9
42.5°	871.9	870.9	877.6	891.1	919.8	957.9	1002.4	1056.1	1119.7	1190.5	1274.9
45°	824.0	824.0	822.4	833.7	857.1	894.1	931.3	982.9	1036.1	1105.4	1176.4
47.5°	774.1	769.5	770.9	776.8	796.5	827.0	864.3	906.6	953.5	1012.2	1074.5
50°	741.7	735.4	733.0	739.3	757.1	783.8	819.2	856.3	900.6	952.2	1005.4
52.5°	706.3	699.8	695.5	700.0	716.5	741.1	773.4	806.0	845.8	887.8	933.8
55°	651.5	644.2	641.8	643.4	655.5	674.9	702.3	732.2	761.9	796.6	828.9
57.5°	597.4	585.5	583.3	582.5	590.9	608.5	631.5	657.3	679.0	700.0	734.4
60°	562.0	547.4	542.6	541.8	548.3	562.8	583.7	609.6	624.9	639.3	669.2
62.5°	523.9	510.1	499.4	500.6	506.3	520.2	538.6	557.3	567.4	583.3	603.4
65°	465.2	447.5	439.4	437.0	440.2	451.5	466.1	478.2	489.4	495.8	515.2
67.5°	406.6	391.7	379.8	376.9	375.4	383.1	395.1	402.3	410.4	416.1	427.5
70°	365.3	352.3	337.8	333.0	332.1	338.6	349.9	350.7	362.0	364.5	376.6
72.5°	324.6	308.5	298.5	293.7	290.2	296.1	303.5	305.6	311.7	316.1	322.3
75°	261.3	249.1	239.4	232.2	229.7	233.0	233.0	237.0	241.1	243.5	250.7
77.5°	205.6	191.8	180.3	176.1	173.2	171.1	172.9	175.3	173.4	177.5	179.2
80°	166.9	152.4	143.5	141.9	137.0	133.0	132.2	134.6	131.4	133.0	137.8
82.5°	128.9	119.5	110.0	108.4	102.2	100.2	99.4	97.9	97.9	97.6	98.6
85°	76.5	71.0	64.5	60.5	58.1	54.0	54.0	52.4	50.8	49.2	50.0
87.5°	35.6	34.1	30.5	28.3	26.6	23.6	23.2	20.8	19.7	18.5	17.4
90°	23.5	22.2	20.4	18.6	16.8	15.0	12.9	10.4	8.0	5.5	3.0
92.5°	22.7	21.4	19.6	17.8	16.0	14.2	13.2	13.1	12.9	12.8	12.7
95°	23.5	22.2	21.9	21.7	21.5	21.3	24.9	32.6	40.2	47.9	55.4
97.5°	26.8	26.7	51.6	76.6	101.6	126.6	136.7	132.0	127.2	122.5	117.8
100°	40.6	44.3	75.2	106.2	137.1	168.0	181.5	177.4	173.4	169.4	165.3
102.5°	172.6	213.7	217.7	221.8	225.8	229.8	230.4	227.4	224.5	221.6	218.5
105°	316.6	314.6	313.5	312.3	311.1	310.0	308.8	307.5	306.1	304.8	303.5
107.5°	393.1	392.1	390.6	389.1	387.6	386.1	385.0	384.3	383.6	382.9	382.2
110°	445.0	444.5	443.2	441.9	440.5	439.2	438.2	437.5	436.9	436.2	435.6



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	495.3	495.3	494.7	494.1	493.5	492.9	492.0	490.8	489.6	488.4	487.2
115°	569.1	568.6	568.8	569.1	569.3	569.5	569.3	568.6	567.9	567.2	566.5
117.5°	644.3	644.4	643.9	643.4	642.9	642.4	641.8	640.9	640.0	639.0	638.1
120°	690.0	689.5	689.7	690.0	690.2	690.4	690.1	689.2	688.3	687.4	686.5
122.5°	735.8	735.5	735.2	734.9	734.6	734.3	733.9	733.3	732.8	732.3	731.6
125°	799.1	798.4	798.9	799.3	799.8	800.2	800.0	799.1	798.2	797.3	796.4
127.5°	863.2	863.3	862.3	861.3	860.3	859.2	858.6	858.4	858.2	857.9	857.7
130°	901.5	901.3	900.6	899.9	899.3	898.6	898.1	897.9	897.7	897.5	897.3
132.5°	939.4	939.2	938.3	937.5	936.6	935.7	935.1	934.7	934.3	933.9	933.5
135°	991.4	991.0	990.1	989.2	988.3	987.3	987.0	987.2	987.5	987.7	988.0
137.5°	1041.5	1041.0	1040.0	1039.1	1038.0	1037.0	1036.5	1036.4	1036.3	1036.2	1036.1
140°	1072.3	1071.7	1071.2	1070.8	1070.3	1069.9	1069.3	1068.9	1068.5	1068.0	1067.6
142.5°	1101.2	1100.7	1100.3	1100.1	1099.8	1099.5	1099.0	1098.2	1097.4	1096.6	1095.8
145°	1142.5	1142.2	1142.2	1142.2	1142.2	1142.2	1141.9	1141.1	1140.5	1139.8	1139.1
147.5°	1178.5	1178.3	1178.5	1178.7	1178.9	1179.2	1178.7	1177.4	1176.2	1174.9	1173.7
150°	1201.6	1201.6	1201.9	1202.1	1202.3	1202.5	1202.2	1201.3	1200.4	1199.5	1198.6
152.5°	1221.4	1221.0	1221.4	1221.8	1222.2	1222.6	1222.4	1221.7	1221.0	1220.3	1219.6
155°	1247.9	1247.1	1247.7	1248.4	1249.1	1249.7	1249.9	1249.7	1249.5	1249.3	1249.1
157.5°	1271.0	1269.8	1270.6	1271.3	1272.1	1272.8	1273.3	1273.4	1273.5	1273.7	1273.8
160°	1285.7	1284.3	1284.5	1284.8	1285.1	1285.3	1285.7	1286.4	1287.1	1287.7	1288.4
162.5°	1297.8	1296.5	1296.7	1296.9	1297.1	1297.4	1297.9	1298.7	1299.6	1300.4	1301.3
165°	1314.3	1312.5	1312.5	1312.5	1312.5	1312.5	1313.1	1314.2	1315.3	1316.5	1317.6
167.5°	1326.7	1324.6	1324.8	1324.9	1325.0	1325.2	1325.9	1327.1	1328.2	1329.4	1330.5
170°	1334.5	1332.7	1332.5	1332.3	1332.0	1331.8	1332.4	1333.7	1335.0	1336.5	1337.8
172.5°	1339.4	1337.6	1337.4	1337.2	1336.9	1336.7	1337.3	1338.6	1339.9	1341.3	1342.6
175°	1344.8	1342.8	1342.6	1342.4	1342.1	1341.9	1342.5	1343.8	1345.1	1346.6	1347.9
177.5°	1347.7	1346.3	1345.8	1345.5	1345.1	1344.8	1345.2	1346.6	1347.8	1349.0	1350.3
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4
2.5°	1959.2	1965.7	1974.1	1988.3	1993.5	1999.9	2008.9	2008.3	2010.8	2020.5	2041.2
5°	1966.5	1991.6	2015.7	2044.8	2075.4	2095.6	2122.9	2139.9	2156.9	2178.6	2215.6
7.5°	1969.4	2009.1	2053.5	2104.5	2149.7	2202.0	2242.8	2281.2	2315.8	2361.8	2406.0
10°	1964.9	2018.1	2075.4	2139.9	2208.4	2266.4	2318.9	2378.5	2429.3	2485.0	2535.0
12.5°	1956.5	2020.7	2097.3	2169.6	2249.7	2335.5	2400.9	2461.1	2528.7	2592.7	2669.8
15°	1937.5	2025.4	2114.9	2210.0	2317.2	2416.4	2510.8	2589.0	2661.6	2757.5	2858.3
17.5°	1913.3	2008.1	2121.0	2236.1	2348.2	2461.6	2578.4	2695.9	2787.5	2906.7	2985.6
20°	1890.8	2000.4	2116.5	2253.6	2365.6	2506.8	2622.8	2736.5	2862.4	2980.8	3075.1
22.5°	1859.2	1979.1	2102.3	2238.8	2386.3	2527.4	2661.6	2784.9	2910.7	3039.6	3153.9
25°	1819.0	1927.8	2073.8	2228.6	2375.3	2528.5	2682.5	2837.3	2972.7	3109.1	3215.5
27.5°	1750.6	1888.0	2024.0	2183.7	2346.8	2520.1	2684.8	2846.8	2988.8	3100.8	3166.7
30°	1715.8	1835.1	1982.7	2143.1	2319.7	2506.0	2677.7	2836.5	2968.8	3058.3	3084.8
32.5°	1664.2	1787.4	1931.7	2098.0	2284.8	2476.3	2655.1	2804.9	2915.2	2962.1	2930.0
35°	1587.6	1698.9	1844.8	2014.9	2209.2	2413.2	2589.8	2716.3	2772.8	2728.5	2618.0
37.5°	1495.7	1606.0	1752.5	1919.7	2120.7	2328.0	2487.7	2578.8	2560.1	2449.8	2285.2
40°	1431.2	1534.4	1673.9	1854.4	2050.4	2258.5	2398.7	2447.9	2396.3	2238.3	2063.3
42.5°	1359.6	1460.2	1600.3	1774.4	1982.1	2173.9	2296.1	2300.2	2213.7	2024.8	1849.2
45°	1250.5	1346.5	1478.7	1660.1	1852.1	2032.7	2113.2	2073.8	1914.1	1731.9	1555.3
47.5°	1143.0	1226.2	1356.5	1528.7	1710.9	1863.0	1903.0	1831.9	1661.7	1484.9	1321.2
50°	1064.3	1148.1	1270.7	1435.2	1610.9	1742.4	1761.7	1667.4	1500.5	1322.3	1194.1
52.5°	988.9	1072.1	1190.1	1342.3	1503.3	1621.7	1622.4	1513.3	1347.0	1188.1	1068.9
55°	878.1	953.0	1059.4	1195.7	1339.3	1432.0	1409.4	1296.5	1152.2	1014.3	910.3
57.5°	771.3	836.6	934.6	1048.3	1174.8	1251.2	1213.8	1105.1	976.2	859.3	780.5
60°	702.3	764.4	848.2	955.4	1061.9	1121.6	1086.1	987.7	869.2	774.9	706.3
62.5°	635.2	687.6	768.2	861.3	960.0	1004.1	972.5	875.5	773.1	687.7	632.2
65°	540.2	583.0	647.4	727.3	799.0	837.0	810.3	720.0	641.8	580.6	536.1
67.5°	451.5	484.9	533.7	597.7	658.7	679.2	655.0	592.2	525.8	476.9	445.6
70°	390.2	421.7	462.8	512.0	565.2	586.9	562.8	512.8	458.8	413.6	382.9
72.5°	336.7	361.0	395.8	437.8	479.4	501.2	484.7	436.7	391.0	357.5	331.3
75°	256.4	277.4	301.5	331.3	363.7	378.2	363.7	330.5	299.1	274.2	255.6
77.5°	186.4	197.7	216.4	238.6	258.8	269.9	257.4	235.0	215.8	198.6	189.5
80°	141.9	150.0	162.9	180.6	194.3	204.8	196.7	178.1	162.9	151.6	147.5
82.5°	103.2	108.7	117.0	130.3	139.5	144.8	141.3	127.8	121.6	111.6	107.6
85°	50.8	54.0	59.7	63.7	71.8	72.6	73.4	67.8	62.1	59.7	56.5
87.5°	18.5	19.7	22.1	24.5	27.5	28.5	28.3	28.6	26.4	26.0	23.6
90°	5.5	8.0	10.4	12.9	15.0	16.8	18.6	20.4	22.2	23.5	24.8
92.5°	12.8	12.9	13.1	13.2	14.2	16.0	17.8	19.6	21.4	22.7	24.0
95°	47.9	40.2	32.6	24.9	21.3	21.5	21.7	21.9	22.2	23.5	24.8
97.5°	122.5	127.2	132.0	136.7	126.6	101.6	76.6	51.6	26.7	26.8	26.9
100°	169.4	173.4	177.4	181.5	168.0	137.1	106.2	75.2	44.3	40.6	36.8
102.5°	221.6	224.5	227.4	230.4	229.8	225.8	221.8	217.7	213.7	172.6	131.6
105°	304.8	306.1	307.5	308.8	310.0	311.1	312.3	313.5	314.6	316.6	318.6
107.5°	382.9	383.6	384.3	385.0	386.1	387.6	389.1	390.6	392.1	393.1	394.2
110°	436.2	436.9	437.5	438.2	439.2	440.5	441.9	443.2	444.5	445.0	445.5



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	488.4	489.6	490.8	492.0	492.9	493.5	494.1	494.7	495.3	495.3	495.2
115°	567.2	567.9	568.6	569.3	569.5	569.3	569.1	568.8	568.6	569.1	569.5
117.5°	639.0	640.0	640.9	641.8	642.4	642.9	643.4	643.9	644.4	644.3	644.2
120°	687.4	688.3	689.2	690.1	690.4	690.2	690.0	689.7	689.5	690.0	690.4
122.5°	732.3	732.8	733.3	733.9	734.3	734.6	734.9	735.2	735.5	735.8	736.1
125°	797.3	798.2	799.1	800.0	800.2	799.8	799.3	798.9	798.4	799.1	799.8
127.5°	857.9	858.2	858.4	858.6	859.2	860.3	861.3	862.3	863.3	863.2	863.1
130°	897.5	897.7	897.9	898.1	898.6	899.3	899.9	900.6	901.3	901.5	901.7
132.5°	933.9	934.3	934.7	935.1	935.7	936.6	937.5	938.3	939.2	939.4	939.6
135°	987.7	987.5	987.2	987.0	987.3	988.3	989.2	990.1	991.0	991.4	991.9
137.5°	1036.2	1036.3	1036.4	1036.5	1037.0	1038.0	1039.1	1040.0	1041.0	1041.5	1042.0
140°	1068.0	1068.5	1068.9	1069.3	1069.9	1070.3	1070.8	1071.2	1071.7	1072.3	1073.0
142.5°	1096.6	1097.4	1098.2	1099.0	1099.5	1099.8	1100.1	1100.3	1100.7	1101.2	1101.7
145°	1139.8	1140.5	1141.1	1141.9	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5	1142.7
147.5°	1174.9	1176.2	1177.4	1178.7	1179.2	1178.9	1178.7	1178.5	1178.3	1178.5	1178.6
150°	1199.5	1200.4	1201.3	1202.2	1202.5	1202.3	1202.1	1201.9	1201.6	1201.6	1201.6
152.5°	1220.3	1221.0	1221.7	1222.4	1222.6	1222.2	1221.8	1221.4	1221.0	1221.4	1221.7
155°	1249.3	1249.5	1249.7	1249.9	1249.7	1249.1	1248.4	1247.7	1247.1	1247.9	1248.8
157.5°	1273.7	1273.5	1273.4	1273.3	1272.8	1272.1	1271.3	1270.6	1269.8	1271.0	1272.1
160°	1287.7	1287.1	1286.4	1285.7	1285.3	1285.1	1284.8	1284.5	1284.3	1285.7	1287.1
162.5°	1300.4	1299.6	1298.7	1297.9	1297.4	1297.1	1296.9	1296.7	1296.5	1297.8	1299.1
165°	1316.5	1315.3	1314.2	1313.1	1312.5	1312.5	1312.5	1312.5	1312.5	1314.3	1316.2
167.5°	1329.4	1328.2	1327.1	1325.9	1325.2	1325.0	1324.9	1324.8	1324.6	1326.7	1328.6
170°	1336.5	1335.0	1333.7	1332.4	1331.8	1332.0	1332.3	1332.5	1332.7	1334.5	1336.4
172.5°	1341.3	1339.9	1338.6	1337.3	1336.7	1336.9	1337.2	1337.4	1337.6	1339.4	1341.2
175°	1346.6	1345.1	1343.8	1342.5	1341.9	1342.1	1342.4	1342.6	1342.8	1344.8	1346.9
177.5°	1349.0	1347.8	1346.6	1345.2	1344.8	1345.1	1345.5	1345.8	1346.3	1347.7	1349.1
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4	1946.4
2.5°	2051.5	2052.9	2058.6	2063.2	2064.5	2070.8	2071.5
5°	2231.8	2245.5	2272.1	2274.5	2278.6	2299.6	2283.4
7.5°	2443.1	2477.9	2501.1	2521.6	2529.0	2538.2	2536.3
10°	2578.5	2630.1	2655.9	2697.0	2698.7	2709.2	2702.7
12.5°	2714.6	2774.6	2821.7	2829.2	2863.8	2869.1	2878.1
15°	2907.5	2971.1	3036.5	3059.9	3107.5	3118.8	3136.4
17.5°	3088.8	3153.9	3199.7	3260.1	3279.6	3305.8	3288.0
20°	3188.0	3259.0	3317.1	3364.7	3384.8	3399.3	3397.7
22.5°	3248.0	3319.6	3366.7	3402.7	3421.5	3427.7	3427.4
25°	3285.6	3326.7	3341.2	3355.0	3334.0	3326.7	3329.9
27.5°	3181.2	3170.5	3132.6	3082.9	3031.3	2990.3	2968.1
30°	3037.3	2974.4	2917.2	2817.1	2765.6	2734.9	2707.5
32.5°	2833.5	2733.8	2623.6	2532.0	2473.4	2427.9	2421.2
35°	2484.2	2334.2	2199.6	2087.5	2029.4	1980.2	1968.9
37.5°	2112.0	1956.2	1834.9	1736.3	1673.9	1639.2	1606.8
40°	1864.9	1731.1	1611.7	1527.9	1480.4	1455.3	1435.2
42.5°	1674.7	1552.5	1433.7	1369.9	1326.9	1311.5	1299.7
45°	1411.8	1298.1	1215.9	1167.5	1142.5	1116.7	1104.6
47.5°	1201.3	1108.8	1054.6	1013.5	986.7	971.4	963.7
50°	1082.1	1006.2	957.9	926.5	902.2	890.1	883.7
52.5°	976.2	914.0	873.3	848.4	831.9	823.0	820.5
55°	840.9	793.3	767.6	745.8	733.8	725.7	722.5
57.5°	730.9	694.4	673.4	655.5	650.9	644.1	641.8
60°	658.7	630.6	612.8	600.7	596.6	588.5	590.2
62.5°	594.9	571.8	556.6	549.8	544.4	537.7	539.9
65°	503.1	486.1	478.2	471.7	465.2	461.2	464.4
67.5°	422.1	410.6	399.6	395.9	392.6	392.0	388.6
70°	369.3	359.6	349.9	347.5	347.5	344.3	343.5
72.5°	318.3	311.2	304.8	303.0	300.4	301.7	298.3
75°	245.9	240.2	237.8	235.4	234.6	234.6	232.2
77.5°	181.8	177.5	173.7	173.7	170.8	169.7	169.4
80°	137.8	136.2	133.0	133.0	131.4	132.2	130.6
82.5°	103.7	101.4	100.8	99.5	97.3	97.4	95.8
85°	55.6	53.2	52.4	50.0	48.4	50.0	48.4
87.5°	24.6	24.2	23.7	22.5	22.0	22.1	20.2
90°	26.3	27.6	28.5	28.9	29.4	29.8	30.2
92.5°	25.4	26.8	27.5	27.6	27.7	27.8	27.9
95°	26.3	27.6	28.4	28.6	28.8	29.0	29.2
97.5°	27.1	27.2	27.4	27.6	27.8	28.0	28.3
100°	32.9	29.1	27.4	27.6	27.8	28.0	28.3
102.5°	90.5	49.4	28.9	28.9	29.0	29.0	29.1
105°	320.5	322.6	319.6	311.5	303.5	295.4	287.3
107.5°	395.2	396.1	397.0	397.9	398.7	399.6	400.4
110°	446.0	446.4	447.0	447.6	448.3	449.0	449.6



TEST NUMBER: P332697-840

CATALOG NUMBER: S124DIP-S1195D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	495.1	495.0	495.4	496.2	497.2	498.0	498.8
115°	570.0	570.4	570.6	570.6	570.6	570.6	570.6
117.5°	644.1	644.0	644.0	643.9	643.8	643.7	643.6
120°	690.8	691.4	691.4	690.8	690.4	690.0	689.5
122.5°	736.3	736.6	736.5	736.1	735.6	735.2	734.7
125°	800.4	801.1	801.5	801.8	802.0	802.2	802.4
127.5°	862.9	862.8	862.6	862.5	862.3	862.1	861.9
130°	901.9	902.1	902.3	902.3	902.3	902.3	902.3
132.5°	939.9	940.1	940.1	939.9	939.7	939.6	939.4
135°	992.3	992.8	993.2	993.7	994.1	994.5	995.0
137.5°	1042.5	1043.0	1043.1	1043.0	1042.9	1042.7	1042.6
140°	1073.7	1074.3	1074.8	1075.0	1075.2	1075.4	1075.7
142.5°	1102.2	1102.7	1102.9	1103.0	1103.0	1103.1	1103.1
145°	1142.9	1143.1	1143.5	1143.9	1144.3	1144.8	1145.2
147.5°	1178.8	1179.0	1179.2	1179.4	1179.6	1179.9	1180.1
150°	1201.6	1201.6	1201.7	1202.0	1202.2	1202.4	1202.6
152.5°	1222.1	1222.4	1222.5	1222.4	1222.3	1222.1	1222.0
155°	1249.7	1250.6	1250.7	1250.1	1249.4	1248.7	1248.1
157.5°	1273.3	1274.4	1274.4	1273.3	1272.1	1271.0	1269.8
160°	1288.4	1289.7	1289.7	1288.4	1287.1	1285.7	1284.3
162.5°	1300.5	1301.8	1301.7	1300.2	1298.7	1297.2	1295.7
165°	1318.0	1319.7	1319.6	1317.6	1315.6	1313.5	1311.5
167.5°	1330.6	1332.5	1332.4	1330.2	1328.0	1325.6	1323.4
170°	1338.1	1339.9	1339.7	1337.5	1335.2	1332.9	1330.7
172.5°	1342.9	1344.7	1344.4	1342.0	1339.6	1337.2	1334.7
175°	1348.9	1350.9	1350.5	1347.9	1345.1	1342.5	1339.8
177.5°	1350.5	1352.0	1351.6	1349.5	1347.4	1345.1	1343.0
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9

(END OF REPORT)