

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332713-840

Luminaire Tested: **S124DIP-S1195D1205U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332713-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1195D1205U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9377.8 lumens  
Efficiency: N/A  
Efficacy: 130.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332713-840

CATALOG NUMBER: S124DIP-S1195D1205U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332713-840

CATALOG NUMBER: S124DIP-S1195D1205U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	91	87	92	88	84	81	76	73	71	64	62	61	54	52	51	46
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332713-840

CATALOG NUMBER: S124DIP-S1195D1205U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.5	2.0
10°-20°	534.0	5.7
20°-30°	786.0	8.4
30°-40°	913.7	9.7
40°-50°	913.7	9.7
50°-60°	799.3	8.5
60°-70°	593.6	6.3
70°-80°	337.2	3.6
80°-90°	101.9	1.1
90°-100°	100.1	1.1
100°-110°	296.4	3.2
110°-120°	503.1	5.4
120°-130°	663.4	7.1
130°-140°	745.0	7.9
140°-150°	732.1	7.8
150°-160°	615.7	6.6
160°-170°	409.7	4.4
170°-180°	143.5	1.5
0°-30°	1509.5	16.1
0°-40°	2423.2	25.8
0°-60°	4136.2	44.1
0°-90°	5168.9	55.1
90°-120°	899.6	9.6
90°-150°	3040.1	32.4
90°-180°	4209.0	44.9
0°-180°	9377.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	4	16	26	33	35	9
95°	70	81	89	92	93	78
105°	273	275	279	283	286	290
115°	512	511	509	508	507	504
125°	745	745	744	741	739	664
135°	961	968	968	966	962	743
145°	1167	1172	1173	1172	1169	730
155°	1338	1337	1336	1340	1336	615
165°	1456	1453	1450	1456	1452	410
175°	1515	1509	1508	1515	1508	144
180°	1517	1517	1517	1517	1517	



TEST NUMBER: P332713-840

CATALOG NUMBER: S124DIP-S1195D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	34.2	34.5	34.8	35.1	35.3	35.6	35.7	35.9	36.0	36.2	36.5
90°	3.5	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4
92.5°	25.1	28.4	31.7	34.9	38.3	40.6	42.1	43.5	45.0	46.5	47.4
95°	70.4	72.7	75.1	77.5	79.8	81.9	83.7	85.5	87.4	89.2	90.0
97.5°	123.0	124.8	126.7	128.6	130.5	132.5	134.6	136.7	138.9	141.0	142.0
100°	164.3	165.3	166.3	167.3	168.4	170.2	172.5	174.8	177.1	179.6	180.1
102.5°	207.4	207.8	208.2	208.6	209.1	210.4	212.5	214.7	216.8	218.9	219.6
105°	273.4	273.7	273.9	274.2	274.4	275.1	276.1	277.1	278.2	279.2	280.0
107.5°	342.5	343.0	343.3	343.6	343.9	344.1	344.3	344.4	344.6	344.7	345.5
110°	389.5	390.0	390.5	391.1	391.6	391.7	391.5	391.2	390.9	390.7	390.2



TEST NUMBER: P332713-840

CATALOG NUMBER: S124DIP-S1195D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	438.3	438.5	438.6	438.7	438.8	438.6	438.1	437.7	437.2	436.7	436.6
115°	511.5	511.5	511.5	511.5	511.5	511.3	510.8	510.3	509.7	509.2	509.0
117.5°	580.6	580.8	581.0	581.2	581.4	581.3	580.9	580.6	580.2	579.9	579.0
120°	626.5	627.5	628.6	629.7	630.7	630.9	630.1	629.2	628.4	627.7	626.4
122.5°	674.4	674.8	675.2	675.6	676.1	676.1	675.7	675.4	675.0	674.6	673.8
125°	745.0	745.0	745.0	745.0	745.0	744.9	744.7	744.4	744.1	743.9	743.4
127.5°	809.1	809.9	810.6	811.4	812.2	812.4	811.9	811.5	811.1	810.7	810.2
130°	854.1	855.0	855.7	856.5	857.3	857.7	857.7	857.7	857.7	857.7	857.2
132.5°	900.1	900.7	901.3	901.8	902.4	902.6	902.4	902.2	902.0	901.8	901.2
135°	960.9	962.5	964.0	965.6	967.1	968.0	968.0	968.0	968.0	968.0	967.5
137.5°	1027.0	1027.8	1028.5	1029.3	1030.0	1030.6	1031.0	1031.4	1031.8	1032.2	1031.6
140°	1071.2	1071.7	1072.3	1072.8	1073.3	1073.5	1073.5	1073.5	1073.5	1073.5	1073.3
142.5°	1111.6	1112.1	1112.6	1113.1	1113.7	1113.8	1113.6	1113.4	1113.2	1113.0	1112.9
145°	1167.4	1168.4	1169.5	1170.5	1171.5	1172.3	1172.5	1172.8	1173.0	1173.3	1173.0
147.5°	1222.7	1224.1	1225.3	1226.5	1227.8	1228.3	1228.1	1227.9	1227.7	1227.5	1227.3
150°	1256.6	1257.6	1258.7	1259.7	1260.7	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2
152.5°	1288.5	1289.1	1289.7	1290.3	1291.0	1291.4	1291.6	1291.8	1292.0	1292.2	1292.8
155°	1337.5	1337.5	1337.5	1337.5	1337.5	1337.4	1337.2	1336.9	1336.6	1336.4	1337.4
157.5°	1378.8	1378.4	1377.9	1377.5	1377.0	1376.6	1376.6	1376.5	1376.5	1376.4	1377.3
160°	1403.2	1403.0	1402.7	1402.4	1402.2	1401.9	1401.7	1401.4	1401.1	1400.9	1401.7
162.5°	1425.7	1425.0	1424.4	1423.7	1423.0	1422.6	1422.3	1422.1	1421.8	1421.5	1422.9
165°	1456.0	1455.2	1454.4	1453.7	1452.9	1452.2	1451.7	1451.2	1450.7	1450.2	1451.7
167.5°	1479.3	1478.1	1477.0	1475.9	1474.9	1474.3	1474.4	1474.4	1474.5	1474.5	1476.1
170°	1492.4	1491.1	1489.8	1488.4	1487.1	1486.6	1486.9	1487.1	1487.4	1487.7	1489.2
172.5°	1501.8	1500.7	1499.5	1498.4	1497.4	1496.8	1496.9	1497.0	1497.0	1497.1	1498.8
175°	1514.7	1513.4	1512.1	1510.8	1509.4	1508.6	1508.4	1508.1	1507.9	1507.6	1509.4
177.5°	1518.9	1517.8	1516.8	1515.8	1514.7	1514.2	1514.2	1514.2	1514.2	1514.2	1515.7
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332713-840

CATALOG NUMBER: S124DIP-S1195D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	36.8	37.1	37.4	37.6	37.7	37.8	37.9	38.0
90°	29.0	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	48.4	49.3	50.2	50.8	51.2	51.5	51.8	52.1
95°	90.7	91.5	92.3	92.7	92.7	92.7	92.7	92.7
97.5°	142.9	143.8	144.8	145.2	145.2	145.2	145.2	145.2
100°	180.6	181.1	181.6	181.9	181.9	181.9	181.9	181.9
102.5°	220.4	221.2	221.9	222.3	222.6	222.8	223.0	223.2
105°	280.8	281.6	282.4	283.2	284.0	284.7	285.5	286.3
107.5°	346.2	346.9	347.6	348.0	347.9	347.9	347.8	347.8
110°	389.6	389.1	388.6	388.7	389.5	390.3	391.1	391.8





TEST NUMBER: P332713-840

CATALOG NUMBER: S124DIP-S1195D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	436.5	436.4	436.3	436.3	436.5	436.6	436.8	437.0
115°	508.7	508.4	508.2	507.9	507.7	507.4	507.2	506.9
117.5°	578.0	577.1	576.2	575.6	575.0	574.5	574.0	573.5
120°	625.1	623.8	622.5	622.1	622.6	623.1	623.7	624.2
122.5°	672.9	672.0	671.1	670.1	669.2	668.3	667.3	666.4
125°	742.8	742.3	741.7	741.2	740.7	740.2	739.6	739.1
127.5°	809.7	809.2	808.6	808.2	807.8	807.3	806.9	806.5
130°	856.6	856.1	855.6	854.7	853.7	852.7	851.6	850.6
132.5°	900.7	900.2	899.7	899.2	898.8	898.4	898.0	897.6
135°	966.9	966.3	965.8	965.2	964.4	963.6	962.8	962.1
137.5°	1030.9	1030.2	1029.6	1029.3	1029.5	1029.6	1029.8	1029.9
140°	1073.0	1072.8	1072.5	1072.3	1072.0	1071.7	1071.5	1071.2
142.5°	1112.9	1112.8	1112.8	1112.7	1112.7	1112.6	1112.6	1112.5
145°	1172.8	1172.5	1172.3	1171.6	1170.9	1170.1	1169.3	1168.6
147.5°	1227.1	1226.9	1226.6	1226.4	1226.2	1225.9	1225.6	1225.4
150°	1261.2	1261.2	1261.2	1261.1	1260.8	1260.6	1260.3	1260.1
152.5°	1293.4	1294.1	1294.7	1294.7	1294.0	1293.3	1292.6	1292.0
155°	1338.5	1339.5	1340.5	1340.5	1339.5	1338.5	1337.4	1336.4
157.5°	1378.1	1378.8	1379.6	1379.6	1378.7	1377.8	1376.8	1376.0
160°	1402.4	1403.2	1404.0	1403.7	1402.4	1401.1	1399.9	1398.6
162.5°	1424.3	1425.7	1427.1	1427.2	1425.9	1424.6	1423.3	1422.0
165°	1453.3	1454.8	1456.4	1456.6	1455.6	1454.6	1453.5	1452.5
167.5°	1477.6	1479.3	1480.8	1480.8	1479.1	1477.5	1475.9	1474.3
170°	1490.9	1492.4	1494.0	1493.8	1492.0	1490.2	1488.3	1486.5
172.5°	1500.7	1502.4	1504.2	1504.2	1502.3	1500.5	1498.6	1496.8
175°	1511.3	1513.1	1514.9	1514.9	1513.1	1511.3	1509.4	1507.6
177.5°	1517.1	1518.6	1520.0	1519.9	1518.2	1516.6	1514.9	1513.3
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0

(END OF REPORT)